



Science.
Applied to Life.™



Helping You

Prepare the Workplace

Solutions to Help Employee & Customer Safety

Preparing the workplace starts with planning.
We're here to help.



Protecting customers and employees has always been important, and now more than ever it's critical to address the new hazards presented by COVID-19. Many businesses are starting by creating an Infectious Disease Preparedness and Response Plan, and the next step is to implement it using engineering controls, administrative controls and safe work practices.

Cleaning & Disinfecting | Signage & Communication | Social Distancing (Employee & Customer Safety)

A person wearing brown pants and black shoes is using a spray mop on a light-colored wooden floor. A green plastic chair is visible on the left side of the frame. The mop has a black handle and a white cylindrical tank. A black rectangular mop head is being pushed across the floor.

**Create confidence
in your “clean.”**

While health and safety should be at the top of your priority list, it's also important to routinely clean and disinfect surfaces, equipment, and other elements in your work environment - and we're here to help you do it right. With the right combination of qualified, US EPA Registered Disinfectants, applicators and cleaning implements, you can help reduce hazards and instill confidence among your patrons.

Cleaning & Disinfecting

3M™ US EPA Registered Disinfectants

We offer a wide array of EPA-registered disinfectants that are certified to kill a variety of viruses.

To hear the latest from 3M on cleaning best practices, read our [Tech Talk](#) which is continually updated with the newest information.



7100034339
3M™ TB Quat Disinfectant Ready-to-Use Cleaner, Quart, 12/Case



7010386101
3M™ Quat Disinfectant Cleaner Concentrate 5A, 0.5 Gallon, 4/Case



7000052378
3M™ Quat Disinfectant Cleaner 5H, 2 Liter, 6/Case



7000002181
3M™ Quat Disinfectant Cleaner 5L, 2 Liter, 6/Case



7000053093
3M™ Quat Disinfectant Cleaner Concentrate 25H, 2 Liter, 6/Case



7010385953
3M™ Neutral Quat Disinfectant Cleaner Concentrate 25A, 0.5 Gallon, 4/Case



7000053094
3M™ Quat Disinfectant Cleaner Concentrate 25L, 2 Liter, 6/Case



7010342270
3M™ Neutral Quat Disinfectant Cleaner Concentrate 23A, 0.5 Gallon, 4/Case



7100134549
3M™ Neutral Quat Disinfectant Cleaner Concentrate 23L, 2 Liter, 6/Case

Cleaning & Disinfecting

3M™ US EPA Registered Disinfectants (cont.)



7000052529
3M™ Neutral Quat Disinfectant Cleaner Concentrate 23H, 2 Liter, 6/Case



7010342249
3M™ Disinfectant Cleaner RCT Concentrate 40A, 0.5 Gallon 4/Case



7100058966
3M™ Disinfectant Clean RCT Concentrate 40L, Gray Cap, 2 Liter 6/Case



7010385951
3M™ Disinfectant Cleaner RCT Concentrate, Gallon, 4/Case



7010385965
3M™ Non-Acid Disinfectant Bathroom Cleaner Concentrate 15A, 0.5 Gallon, 4/Case



70071591856
3M™ Non-Acid Disinfectant Bathroom Cleaner Concentrate 15L, 2 Liter, 6/Case

For the latest information on US EPA registered disinfectants, please reference our [Tech Talk](#).

3M™ Cleaners

Convenience and cleanliness go hand-in-hand with these disinfectants and dispensers that are designed to help you stay on top of your facility cleanliness management.



7010315335
3M™ Peroxide Cleaner Concentrate 34A, 0.5 Gallon, 4/Case



70071683778
3M™ Glass Cleaner & Protector Concentrate, 17L, Gray Cap, 2 Liter, 6/Case



70071658168
3M™ Neutral Cleaner Concentrate 3A, 0.5 Gallon, 4/Case

Cleaning & Disinfecting

3M™ Cleaners (cont.)



7100135687
3M™ Twist & Fill™ System Dispenser,
Gray Cap, 1/Case




7010385975
3M™ Flow Control System, Wall
Mount, Action Gap, 1 Each/Case



70071658184
3M™ Glass Cleaner & Protector
Concentrate 17A, 0.5 Gallon, 4/Case



70071683406
3M™ Neutral Cleaner Concentrate 3H,
Gray Cap, 2 Liter, 6/Case



7010342253
3M™ Flow Control Portable
Dispenser, 1/Case



7000028595
3M™ Citrus Base Cleaner Transparent, Net. Wt. 18.5 oz., 12/Case,
Not for sale or use in California. Consult local air quality rules before use.

Liquid industrial cleaner and degreaser

Used to help dissolve and remove dirt, grease, tar and many non-curing adhesives.

Cleaners & Disinfectants

For more information, or to learn what other cleaning products are available, please call **1.888.364.3577**.

Cleaning & Disinfecting


3M™ Floor Mops and Pads

Quickly switch between cleaning and finishing with floor protector application—or use disposable mop pads when laundry is unavailable or to help reduce cross-contamination for an effective clean every time.



7100172630

3M™ Scotch-Brite™ Professional 2-In-1 Flat Mop, Ergonomic Handle




7100179842

3M™ Scotch-Brite™ Professional 2-In-1 Flat Mop & Backpack Finish Applicator Kit, Ergonomic Handle




7100172627

3M™ Scotch-Brite™ Professional Standard Flat Mop




7100155486

3M™ Easy Clean Disposable Floor Mop Pad, 18 in. 30/Case




7000127862

3M™ Easy Scrub Mop White 18 in.




7000126855

3M™ Easy Scrub Mop Red 18 in.



7100135689

3M™ Easy Scrub Mop Green 18 in.



7000126856

3M™ Easy Scrub Mop Blue 18 in.

Cleaning & Disinfecting

Scotch-Brite™ Floor Cleaning and Polishing Pads

Give customers and employees confidence in your floor's cleanliness with 2-in-1 daily cleaning pads for low-speed scrubbers that gradually increase shine with repeated use.



7100148036

Scotch-Brite™ Clean & Shine Pad
11 in. 5/Case

7100147921

Scotch-Brite™ Clean & Shine Pad
12 in. 5/Case

7100148049

Scotch-Brite™ Clean & Shine Pad
13 in. 5/Case

7100148038

Scotch-Brite™ Clean & Shine Pad
14 in. 5/Case

7100148013

Scotch-Brite™ Clean & Shine Pad
15 in. 5/Case

7100148035

Scotch-Brite™ Clean & Shine Pad
16 in. 5/Case

7100148018

Scotch-Brite™ Clean & Shine Pad
17 in. 5/Case

7100148034

Scotch-Brite™ Clean & Shine Pad
18 in. 5/Case

7100148014

Scotch-Brite™ Clean & Shine Pad
19 in. 5/Case

7100148015

Scotch-Brite™ Clean & Shine Pad
20 in. 5/Case

7100148105

Scotch-Brite™ Clean & Shine Pad
21 in. 5/Case

7100147996

Scotch-Brite™ Clean & Shine Pad
22 in. 5/Case

7100148016

Scotch-Brite™ Clean & Shine Pad
23 in. 5/Case

7100148006

Scotch-Brite™ Clean & Shine Pad
24 in. 5/Case

7100148037

Scotch-Brite™ Clean & Shine Pad 1
in. x 18 in. 5/Case

7100148017

Scotch-Brite™ Clean & Shine Pad
14 in. x 20 in. 5/Case

7100147995

Scotch-Brite™ Clean & Shine Pad
14 in. x 28 in. 5/Case

7100147994

Scotch-Brite™ Clean & Shine Pad
14 in. x 32 in. 5/Case



Cleaning & Disinfecting

Scotch-Brite® Scrub Sponges, Wipes and Brush

Scotch-Brite® solutions can be used for routine cleaning in a variety of areas, including hard surfaces like countertops in kitchens or other common areas and at handwashing stations.



7100167730
Scotch-Brite® Heavy Duty Scrub Sponges, 1-Pk



7000052198
Scotch-Brite® Large Heavy Duty Scrub Sponges, 1-Pk




7000042920
3M™ Large Commercial Sponge



7010410844
Scotch-Brite® Non-scratch Wipes, 40 Sheets/Roll



7100169167
Scotch-Brite® Hand & Nail Brush



Cleaning & Disinfecting

3M™ Easy Trap™ Dusters

These convenient disposable sheets allow for quick sweeping and dusting without requiring laundry services.



7100081547

3M™ Easy Trap™ Sweep & Dust Sheets; 5 in. x 6 in. Sheets; 60 Sheets/Roll; 8 Rolls/Case



7100081546

3M™ Easy Trap™ Sweep & Dust Sheets; 8 in. x 6 in. Sheets; 60 Sheets/Roll, 8 Rolls/Case



7100081545

3M™ Easy Trap™ Sweep & Dust Sheets; 8 in. x 6 in. Sheets, 250 Sheets/Roll, 1 Roll/Case



7100081544

3M™ Easy Trap™ Sweep & Dust Sheets; 5 in. x 6 in. Sheets; 250 Sheets/Roll, 2 Rolls/Case



Signage & Communications



Helpful reminders wherever you work.

In rapidly evolving situations, a simple sign can go a long way to helping protect your workers, customers and visitors. Whether permanent, temporary or immediate, delivering critical messages at the right time and place can make a difference in good hygiene and infection control practices. Our broad range of indoor and outdoor signage and communication solutions will convey messages that help you keep customers and employees safe, from retail and office spaces.

Signage & Communications

3M™ Wall, Window and Floor Signage

Transform uncertainty into confidence with solutions for custom removable vinyl wayfinding floor graphics, indoor physical distancing markers and signs for walls and windows. As social distancing guidelines may evolve, be sure to reference latest government recommendations.



Interior Floors:

7100046800

3M™ Controltac™ Print Film 40C-10R, White, 54 in. x 50 yd.

7000130431

3M™ Scotchcal™ Luster Overlaminate 8509, 54 in. x 50 yd.



Exterior Sidewalks:

7000005221

3M™ Scotchcal™ Graphic Film 3662-10, White, 48 in. x 50 yd.

7000005220

3M™ Scotchcal™ Matte Overlaminate 3647, 48 in. x 50 yd.

Customized for you.

Create graphic films featuring your message, store or brand. To find a graphics professional near you, please call 1-800-328-3908 or visit [3M.com/SocialDistanceGraphics](https://www.3m.com/SocialDistanceGraphics).




Windows:

7100090326

3M™ Controltac™ Print Film 40C-114R, Clear, 54 in. x 50 yd.

7000130495

3M™ Scotchcal™ Gloss Overlaminate 8508, 54 in. x 50 yd.



Walls:

7100046800

3M™ Controltac™ Print Film 40C-10R, White, 54 in. x 50 yd.

7100046797

3M™ Scotchcal™ Matte Overlaminate 8510M, 54 in. x 50 yd.



Signage & Communications

Post-it® Flex Write Surface

The permanent marker whiteboard. Instantly transform your work surface into a whiteboard and write with even a permanent marker without stains. Permanent marker erases with water, no chemicals.



7100197625
Post-it® Flex Write Surface,
3 ft. x 2 ft. 7100197625, FWS3x2



7100197624
Post-it® Flex Write Surface,
4 ft. x 3 ft. 7100197624, FWS4x3



7100198315
Post-it® Flex Write Surface,
6 ft. x 4 ft. 7100198315, FWS6x4



7100198316
Post-it® Flex Write Surface,
8 ft. x 4 ft. 7100198316, FWS8x4



7100195630
Post-it® Flex Write Surface,
50 ft. x 4 ft. 7100195630, FWS50x4



Post-it® Super Sticky Easel Pads & Post-it® Extreme Notes

No matter how big or small the message, Post-it® Super Sticky Easel Pads and Extreme Notes are a quick way to capture them permanently on ink bleed-through resistant paper. Reposition, remove or dispose in seconds. Super Sticky Easel Pads work best on walls or smooth surfaces, while Extreme Notes are water-resistant and stick in tough conditions where surfaces may be rough, wet, hot or cold.



7100077241
Post-it® Super Sticky Easel Pad 559,
25 in. x 30 in., White, 30 Sheets/Pad



7100156012
Post-it® Extreme Notes, EXTRM33-
12TRYG, 3 in. x 3 in. (76 mm x 76 mm)



7100154151
Post-it® Extreme Notes, EXTRM33-
3TRYOG, 3 in. x 3 in. (76 mm x 76 mm)

Signage & Communications

Scotch™ Self-Sealing Laminating Pouches

Achieve professional, ultra-clear lamination of your letter-size signs with this no-heat, no-machine needed solution. It's a simple way to protect them and make them easy to clean.



7010369982

Scotch™ Self-Sealing Laminating Pouches
LS854-10G, 9.0 in. x 11.5 in.



Command™ Hooks, Strips and Cord Bundlers

Make temporary placements, bundle cords and add convenient hooks for hanging bags, coats and other lightweight equipment with options rated up to 5 lbs.



7100144889

Command™ Large Designer Hooks (16
hooks, 24 foam strips) contract box



7100145191

Command™ Medium Wire Hooks (35
hooks, 40 foam strips) contract box



7100144878

Command™ Large Wire Hooks (14
hooks, 24 foam strips) contract box



7010300778

Command™ Poster Strips, (256 strips)
contract box



7100205656

Command™ Large Picture Hanging
Strips (120 total pairs/ 240 total strips)
contract box



7100089521

Command™ Small Utility Hook
value pack 17002-6ES

Signage & Communications

Command™ Hooks, Strips and Cord Bundlers (cont.)



7100217717
Command™ Small Wire Hooks



7100129501
Command™ Cord Bundlers, 17304-ES,
2 bundlers, 3 strips



Social Distancing: Employee & Customer Safety



**Safe spaces make
for healthy places.**

One important step you can take to help protect your employees and customers is giving them the directions they need to follow proper social distancing. Create queues for waiting areas, lobbies or employee screening entrances. Mark lanes in your retail aisleways. Designate isolation areas for symptomatic individuals identified on-site. These are all basic infection prevention measures that can make a difference in preventing the spread of viruses in virtually any workplace.

Social Distancing: Employee & Customer Safety

3M™ Vinyl Floor Marking Tapes

Clearly delineate everything from aisles, walk-ways and traffic lanes, to work cells, temporary storage, product inspection locations or caution areas.



7100044478
3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Yellow



7010335133
3M™ Vinyl 5702 Floor Marking Tape,
2 in. x 36 yd., Black/Yellow



7100044655
3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Red



7100044652
3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Green



7100044656
3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Blue



7000048401
3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Black



7100061044
3M™ Vinyl 471 Floor Marking Tape,
2 in. x 36 yd., Orange

Use different colors for specific applications:

- Yellow: Aisles, walk-ways, work cells
- ■ Yellow/Black: Caution areas
- Red: Safety/first aid, defect/scrap or red tag areas
- ■ ■ Green/Blue/Black: Path marking & area designation
- Orange: Material/product inspection or temporary storage areas



Social Distancing: Employee & Customer Safety

3M™ Ultra Durable Floor Marking Tapes

For workplace areas that require traffic paths for heavier traffic flow, these tapes feature a tough, thick PLA backing that resists pallet drag and high forklift traffic. They're designed for long-term floor marking, yet can still come up clean, in one piece, after several years on the floor.

Customized for you.

For more information, call 1-800-831-0658 or visit [3m.com/floormarking](https://www.3m.com/floormarking).



7010300943

3M™ Ultra Durable Floor Marking Tape
971 Yellow, 2 in. x 36 yd., 1 per case

7010379511

3M™ Ultra Durable Floor Marking Tape
971 Yellow, 3 in. x 36 yd., 1 per case

7010337212

3M™ Ultra Durable Floor Marking Tape
971 Yellow, 4 in. x 36 yd., 1 per case



7100166473

3M™ Ultra Durable Floor Marking Tape
971 Orange, 2 in. x 36 yd., 1 per case

7100166566

3M™ Ultra Durable Floor Marking Tape
971 Orange, 3 in. x 36 yd., 1 per case

7100167382

3M™ Ultra Durable Floor Marking Tape
971 Orange, 4 in. x 36 yd., 1 per case



7010337213

3M™ Ultra Durable Floor Marking Tape
971 Red, 2 in. x 36 yd., 1 per case

7010293281

3M™ Ultra Durable Floor Marking Tape
971 Red, 3 in. x 36 yd., 1 per case

7010379514

3M™ Ultra Durable Floor Marking Tape
971 Red, 4 in. x 36 yd., 1 per case



7010337214

3M™ Ultra Durable Floor Marking Tape
971 White, 2 in. x 36 yd., 1 per case

7010379515

3M™ Ultra Durable Floor Marking Tape
971 White, 3 in. x 36 yd., 1 per case

7010313485

3M™ Ultra Durable Floor Marking Tape
971 White, 4 in. x 36 yd., 1 per case



7010379512

3M™ Ultra Durable Floor Marking Tape
971 Blue, 2 in. x 36 yd., 1 per case

7010313484

3M™ Ultra Durable Floor Marking Tape
971 Blue, 3 in. x 36 yd., 1 per case

7010379513

3M™ Ultra Durable Floor Marking Tape
971 Blue, 4 in. x 36 yd., 1 per case



7100167106

3M™ Ultra Durable Floor Marking Tape
971 Green, 2 in. x 36 yd., 1 per case

7100167434

3M™ Ultra Durable Floor Marking Tape
971 Green, 3 in. x 36 yd., 1 per case

7100166842

3M™ Ultra Durable Floor Marking Tape
971 Green, 4 in. x 36 yd., 1 per case

Social Distancing: Employee & Customer Safety

3M™ Safety Kit

Address minor injuries on the job with one simple kit, which includes 45 adhesive bandages, gauze and assorted pads, a cold compress, scissors and tweezers, prep/relief pads and towelettes, applicators, finger splints, exam gloves, ointments, adhesive tape and First Aid instructions. Meets ANSI/OSHA requirements.



7100168699

3M™ First Aid Kit: 118 pieces, 6/Case




Personal Protective Equipment

1. Considerations for Selection & Use of Respirators:


OSHA's [back-to-work guidance document](#)—which outlines low, medium and high exposure-risk jobs—indicates that the majority of non-medical workers likely do not require the use of respiratory protection. However, each employer is responsible for determining the risk of a job and what specific PPE that job requires. Three types of respirators offered by 3M are:

Respirators shown for example only and are not recommendations for any specific job or work environment.



2. Care for Respiratory Equipment – Cleaning & Disinfecting:

Reusable and Powered Air Purifying Respirators can be cleaned and disinfected for reuse following a potential exposure event. A variety of documentation on what respirators and filters can be cleaned and disinfected, as well as how to do so, is available on our website.



3. Respirator Fit Testing:

Disposable and reusable respirators are considered by OSHA to be tight-fitting respirators. Each wearer should be fit tested to help ensure they get the most out of their respirator. We've made it easy to access training on how to properly fit test a respirator through videos, photos and quick reference guides—all available through our website.



Respirator Resources: Find all of these up-to-date resources on our website.

[Cleaning & Disinfecting Respirators](#) ►

[3M.com/Respiratory](https://www.3m.com/Respiratory) ►



**Let's prepare the
workplace for **safety.****

**To learn more about these products,
please call 1-888-364-3577.**



Building 225-4N-15
St. Paul, MN 55144-1000

3M, Command, Controltac, Easy Trap, Post-it, Scotch, Scotch-Brite, Scotchcal and Twist & Fill are trademarks or registered trademarks of 3M.
© 3M 2020. All rights reserved.