



VHB™ Tape LSE Series

Product Data Sheet

September 2022
Supersedes: October 2019

Product Description

3M™ VHB™ Tape LSE family are white conformable double coated acrylic foam tapes with a high initial tack and a soft foam. Its design enables bonding of many low surface energy substrates/materials.
3M VHB LSE is white tapes are available in three different thicknesses with a 3M branded red siliconised polyethylene film liner.

Key Features

- Double-coated acrylic foam tape
- 100% closed cell acrylic foam
- Multi material bonding for high, medium or low surface energy substrates including many metals (e.g. stainless steel), composites and plastics (e.g. PP, PA)
- Enables bonding of many LSE substrates without primer
- Good low temperature tack
- Soft foam enables stress relaxation & an easy application
- High initial tack
- For indoor and outdoor applications

Applications & Benefits

- Capability to bond to many LSE substrates without primer makes it a good fit for applications in many industries such as plastics processing, transportation, appliances and signage

Physical Properties

	LSE-060WF	LSE-110WF	LSE-160WF
Adhesive & Carrier	Modified Acrylic on Conformable Acrylic Foam (closed cell)		
Thickness acc. to ASTM D-3652	0.60 mm	1.10 mm	1.60 mm
Density	715 kg/m ³		
Release Liner	3M branded red siliconised polyethylene film		
Tape Colour	White		

Performance Characteristics

Type	LSE-060WF	LSE-110WF	LSE-160WF
90 ° Peel adhesion to Stainless Steel acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell	30 N/cm	44 N/cm	54 N/cm
90 ° Peel adhesion to Polypropylene acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell	24 N/cm	42 N/cm	51 N/cm
90 ° Peel adhesion to Glass acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell	29 N/cm	43 N/cm	51 N/cm
90 ° Peel adhesion to ABS acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell	24 N/cm	40 N/cm	47 N/cm
Static Shear Strength on Stainless Steel acc. to ASTM D3654, after 72h @ RT dwell (Weight held for 10.000 minutes, 3.22cm ² (0.5in ²), vertical test direction)	23 ° C - 1000 g 70 ° C – 500 g 90 ° C – 250 g		
Static Shear Strength on Polypropylene acc. to ASTM D3654, after 72h @ RT dwell (Weight held for 10.000 minutes, 3.22cm ² (0.5in ²), vertical test direction Limited by substrate)	23 ° C - 1000 g 70 ° C – 500 g 90 ° C - 500 g		
Dynamic Shear acc. to ASTM D1002 on stainless steel, after 72h @ RT dwell	525 N /6.54cm ²	382 N /6.54cm ²	347 N /6.54cm ²
Normal Tensile (T-Block) acc. to ASTM D897 to Aluminium @ RT, after 72h @ RT dwell, test speed 50 mm/min	365 N /6.54cm ²	309 N /6.54cm ²	290 N /6.54cm ²
Temperature Performance	Short term (minutes, hours): 150 °C Long term (days, weeks): 90 °C		

Application Temperature Ideal application temperature range 10 °C to 38 °C. For certain applications and substrates 3M™ VHB™ LSE can be applied at temperatures as low as 0 °C if the surface is frost free. **Testing on application-specific substrates is recommended to confirm adhesion at temperatures <10 °C.**

Pressure sensitive adhesives use viscous flow to achieve substrate contact area. To obtain good performance, it is important to ensure that the surfaces are clean, dry and free of condensed moisture.

Shelf Life

18 months from date of production when stored at 16 °C – 25 °C and 40-65 % relative humidity.

Performance of tapes is not projected to change even after shelf life expires; however, 3M does suggest that 3M™ VHB™ Tapes are used prior to the shelf life date whenever possible.

Automotive Disclaimer

Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, including, but not limited to, automotive electric powertrain battery or high voltage applications. This product does not fully adhere to typical automotive design or quality system requirements, such as IATF 16949 or VDA 6.3. This product may not be manufactured in an IATF certified facility and may not meet a Ppk of 1.33 for all properties. The product may not undergo an automotive production part approval process (PPAP). Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's automotive application and for conducting incoming inspections before use of the product. Failure to do so may result in injury, death, and/or harm to property. No written or verbal statement, report, data or recommendation by 3M related to automotive use of the product shall have any force or effect unless in an agreement signed by the Technical Director of 3M's Automotive Division. Customer assumes all responsibility and risk if customer chooses to use this product in an automotive electric powertrain battery or high voltage application, and 3M will not be liable for any loss or damage arising from or related to the 3M product or customer's use of the product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity or recall costs), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. In no event shall 3M be liable for any damages in excess of the purchase price paid for the product.

NOTWITHSTANDING ANY OTHER STATEMENT TO THE CONTRARY, 3M MAKES NO REPRESENTATIONS, WARRANTIES OR CONDITIONS WHATSOEVER, EXPRESS OR IMPLIED, REGARDING THE PRODUCT IF USED IN AN AUTOMOTIVE ELECTRIC POWERTRAIN BATTERY OR HIGH VOLTAGE APPLICATION, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY ON PERFORMANCE, LONGEVITY, SUITABILITY, COMPATIBILITY, OR INTEROPERABILITY, OR ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

3M and VHB are trademarks of the 3M Company

Industrial Adhesives & Tapes Division
3M Belgium
Hermeslaan 7
1831 Diegem
Belgium

Industrial Adhesives & Tapes Division
3M Nederland
Molengraafsingel 29
2629 JD Delft
Nederland