

Effective: 01/09/2022 Supersedes: 08/12/2020

Automotive Aftermarket Division

3M™ Performance Spray Gun

1) Part Numbers

3M Part Numbers	3M Part Description		
Gun Kits			
26778	3M™ Performance HVLP Spray Gun System Gravity with PPS™ 2.0		
26978	3M™ Performance Fine Finish Spray Gun System Gravity with PPS™ 2.0		
26832	3M™ Performance Spray Gun		
26878	3M™ Performance Industrial Spray Gun System		
Replacement Parts			
26833	Pressure Whip		
26839	Ball Valve		
26840	Rebuild Kit		
26834	Whip Pin		
26841	O-Ring Kit		
Atomising Head Refill Kits – H	HVLP Pressure		
26809	Atomising Head Pressure White 0.9		
26811	Atomising Head Pressure Yellow 1.1		
26814	Atomising Head Pressure Orange 1.4		
26818	Atomising Head Pressure Clear 1.8		
26820	Atomising Head Pressure Clear 2.0		
Atomising Head Refill Kits – HVLP Gravity			
26709	Atomising Head Gravity HVLP White 0.9		
26712	Atomising Head Gravity HVLP Blue 1.2		
26713	Atomising Head Gravity HVLP Green 1.3		
26714	Atomising Head Gravity HVLP Orange 1.4		
26716	Atomising Head Gravity HVLP Purple 1.6		
26718	Atomising Head Gravity HVLP Clear 1.8		
26720	Atomising Head Gravity HVLP Red 2.0		
Atomising Head Refill Kits – Gravity Fine Finish			
26912	Atomising Head Gravity Fine Finish Blue 1.2		
26913	Atomising Head Gravity Fine Finish Green 1.3		
26914	Atomising Head Gravity Fine Finish Orange 1.4		

2) Description and end uses

Lightweight and easy to use, the 3M[™] Performance Spray Gun was built for the modern painter. Capable of spraying a wide range of coatings from either a pressure-fed source or attached gravity cup, its impact-resistant composite body makes it one of the lightest spray guns available, yet it is durable enough for demanding industrial and automotive conditions. With its versatile design, technicians can spray from either a pressure or gravity sources. The pressure-fed hose and nozzles allow for continuous bulk spraying for larger jobs. Or for spot repairs and small areas, convert the spray gun to use the 3M[™]



Effective: 01/09/2022 Supersedes: 08/12/2020

PPS™ Series 2.0 Spray Cup System –so you use just the right amount of coating to match the size and finish of the job. Simple, innovative design means fewer parts to maintain. With quick-change replaceable nozzles, paint never passes through the body of the spray gun. Clean up can be as simple as wiping the tip of the needle and replacing the head – which means no more disassembling or soaking in solvent. It's like getting a brand-new spray gun every time you put on a fresh nozzle. At sizes from 0.9 to 2.0, 3M™ Performance Atomising Heads allow you to easily spray a wide range of coatings –from stains and primers to topcoats and even adhesives. The spray gun's intuitive design means it's ready to help technicians spray right out of the box –whether you're a seasoned pro or if it's your first day on the job.

3) Physical Properties

Element	Material of construction
Body	Glass Filled Nylon 66 (PA66)
Trigger	Base: 304 Stainless Steel, Coating: TiC
Fluid Needle	17-4 SS
Control Knobs	Base: 6061 Aluminium, Coating: Type III Black Annodize
Air Inlet	Base: 361L Stainless Steel, Coating: TiC
Air Flow Control Valve	Body: Aluminium Other: Varies
Nozzle	Air Cap, Body, Face: PP, Barrel Seal: Nylon 66 (PA66)
Whip Hose	Multilayer
Ball Valve	Body: Aluminium with black annodized coating, Handle: Brass
Locking Collar	Delrin (POM)

Performance Properties

Performance Spray Gun with Gravity Nozzles				
Air Consumption HVLP	370 SLPM [13 SCFM]			
Air Consumption Fine Finish	370 SLPM [13 SCFM]			
Max HVLP Operating Air Pressure	1.38 Bar [20 psi]			
Fine Finish Optimised Air Pressure	2.0 Bar [29psi]			
Operating Pressure Range	0.5 – 2.6 Bar [7-37psi]			
Maximum Operating Temperature	50 °C [122 °F]			
Maximum Operating Overpressure	10 Bar [145 psi]			
Weight	238 g [8.4 oz]			
Air Inlet	1/4 BSP/NPS			
Nozzle Orifice Sizes	0.9, 1.2, 1.3, 1.4, 1.6, 1.8, 2.0			

Performance Spray Gun with Pressure Nozzles				
Air Consumption	370 SLPM [13 SCFM]			
Max HVLP Operating Air Pressure	1.24 Bar [18 psi]			
Operating Pressure Range	0.5 – 2.6 Bar [7-37psi]			
Maximum Operating Temperature	50 °C [122 °F]			
Maximum Operating Overpressure	10 Bar [145 psi]			
Maximum Fluid Pressure	3.4 Bar [50 psi]			
Weight	378 g [13.3 oz]			
Air Inlet	1/4 BSP/NPS			
Liquid Inlet	3/8 BSP/NPS	•		



Effective: 01/09/2022 Supersedes: 08/12/2020


Nozzle Orifice Sizes

0.9, 1.1, 1.4, 1.8, 2.0

4) Directions for Use

Gravity Assembly

1. Attach the supplied air flow valve to the bottom of the gun.



2. Attach the nozzle to the spray gun with the locking collar fully connected. **Note:** It is easier to install the nozzle while pulling the trigger backward toward the spay gun handle. To remove the nozzle from the spray gun, reverse the process.



3. Attach 3M[™] PPS[™] Series 2.0 spray cup to nozzle.



4. Once the spray gun is properly assembled you may attach the air line.

Nozzle Recommendation

* starting points only, refer to Pain Manufacturer for recommendation on fluid tip size


	2.0	1.8	1.6	1.4	1.3	1.2	0.9
High Viscosity Coatings	•	•					
Sprayable Fillers	•	•					
High Build Primer		•	•	•			
Primer Surfacer		•	•	•			
Wet on Wet Primer				•	•		
Primer Sealer				•	•		
Direct Gloss				•			
Single Stage Top Coat				•			
Solvent Base Color				•	•		
Clearcoat				•	•	•	
Waterborne Base Coat					•	•	
UV Primers					•	•	•
Midcoat / Effect Coats					•	•	•
Smart / Spot						•	•




Effective: 01/09/2022 Supersedes: 08/12/2020

Pressure Assembly


1. Attach the supplied air flow valve to the bottom of the gun.



2. Attach Fluid Hose Pressure Whip to base of spray gun.



3. Attach the nozzle to the spray gun with the locking collar fully connected. Note: It is easier to install the nozzle while pulling the trigger backward toward the spray gun handle.



4. Connect Pressure Whip to nozzle.



5. Attach fluid and pressure lines from bulk feed system (or pressure pot). **Note:** Utilise the optional manual fluid shut-off valve, if desired, between hose whip and fluid supply.

	2.0	1.8	1.4	1.1	0.9
High Viscosity Coatings	•	•			
Textured Coatings	•	•			
Epoxy / Urethane Primers		•	•	•	
1K Top Coats			•	•	
2K Top Coats			•	•	•
Clearcoat				•	•
Base Coat / Single Stage Coatings			•		
Adhesives		•	•	•	•
Release Agents				•	•
Stains / Lacquers				•	•



Effective: 01/09/2022 Supersedes: 08/12/2020

Cleaning Pressure

- 1. Once the system is adequately flushed (pot, lines), depressurize the system (or close the optional fluid valve).
- 2. After pressure is relieved, remove the hose whip from the nozzle.
- 3. Remove nozzle from spray gun to clean residue from the nozzle. Rinse out and flush cleaning solvent through the nozzle with fluid tip pointed straight down into receptacle to collect waste solvent.
- 4. Wipe needle tip. Store spray gun with a nozzle attached to protect the needle.

Gravity

- 1. Once coating application is complete, disconnect the air hose from the gun.
- 2. To drain back paint into cup invert cup, pull trigger, and tap the PPS™ cup on the table 3 times.
- 3. Rinse out nozzle spout and flush cleaning solvent through the nozzle by pulling the trigger with fluid tip pointed straight down into receptacle to collect waste solvent.
- 4. Store spray gun with a nozzle attached to protect the needle.

WARNING! Do not immerse spray gun or nozzles in cleaning solvents or gun washers. The operating pressure range of this spray gun is listed on the face of each replacement atomising head. For pressure nozzles, <u>DO NOT EXCEED 3.4 BAR [50 PSI] FLUID PRESSURE</u>.

5) Storage

Ensure equipment is cleaned prior to storage. Store spray gun with a nozzle attached to protect the needle.

6) Safety

Before using the product, reference and understand the Product Label and Product Manual for Health and Safety Information. Consult all Safety Data Sheets for chemical material used with this product. Follow all local regulations for use and disposal of all items/products associated with the use of this product.

3M™ Performance Spray Gun is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Effective: 01/09/2022 Supersedes: 08/12/2020

For Additional Health and Safety Information

3M United Kingdom plc	3M Ireland Limited	3M Denmark a/s
Automotive Aftermarket	Automotive Aftermarket	Automotive Aftermarket
3M Centre,	The Iveagh Building	Hannemanns Allé 53
Cain Road,	Carrickmines Park	2300 København S
Bracknell,	Carrickmines , Dublin 18	
RG12 8HT		
Tel: +44 (0)161 237 6391	Tel: +353 12160301	Tel: +45 43480100
aadukenquiries@mmm.com	aadukenquiries@mmm.com	aadukenquiries@mmm.com
www.3Mbodyshop.co.uk	www.3Mbodyshop.co.uk	www.3MAuto.dk
3M Finland, Suomen 3M Oy	3M Svenska AB	3M Norge AS
Autotuotteet	Automotive Aftermarket	Automotive Aftermarket
Keilaniementie 1	Herrjärva torg 4	Kanalveien 2
02151 Espoo	170 67 Solna	2004 Lillestrøm
Tel: 09 5252 1	Tel: 08-922100	Tel: 06384
aadukenquiries@mmm.com	aadukenquiries@mmm.com	aadukenquiries@mmm.com
www.3M.fi/autotuotteet	www.3M.se/bileftermarkad	www.3m.no/auto
3M Latvija	3M Eesti OU	3M Lietuva
K.Ulmana 5	Pärnu mnt. 158	A.Goštauto str. 40 A
Riga, LV-1004	11317 Tallinn	LT-01112 Vilnius
Tel: +371 67066120	Tel: +372 6 115 902	Tel: +370 5 2160780
aadukenquiries@mmm.com	aadukenquiries@mmm.com	aadukenquiries@mmm.com
www.3m.lv	www.3m.ee	www.3m.lt

3M and PPS are trademarks of 3M Company, © 3M 2022, All rights reserved.