

Commercial Ice Machine Filter Sizing for 3M™ High Flow Carbonless Series

Find the right filter to fit your commercial ice equipment needs based on the amount of ice it produces per day.

Filter Sizing for Ice Machines - Sizing Information by Model and Ice Production Capacity

3M Filtration Absolute 0.2 Micron Bacteria and Cyst Rated Systems and Filters	
3M Filter Model	Nugget Style Ice/Water Dispensers/Cube Style Ice Machines Ice Production (lbs. per day)
ICE120-A020-S-SR	Up to 500
ICE160-A020-S-SR	Up to 1000
Twin Manifold (6228505) Qty 1/HF60-A020-S-SR (5637225) Qty 2	Up to 2400
3M Filtration – Standard Cyst and Bacteria Rated Systems and Cartridges	
3M Filter Model	Nugget Style Ice/Water Dispensers/Cube Style Ice Machines Ice Production (lbs. per day)
ICE120-S-SR	Up to 750
NH3 Head (6214413) Qty 1 + HF40-S-SR (5637115) Qty 1	Up to 1200
ICE160-S-SR	Up to 1600
NH3 Head (6214413) Qty 1 + HF90-S-SR (5617105) Qty 1	Up to 2500

3M Purification Inc.
3M Separation and Purification Sciences Division
400 Research Parkway
Meriden, CT 06450 USA

Phone 1-800-243-6894
1-203-237-5541
Web 3Mfoodservice.com

Clear things up at 3MFoodService.com

3M is a trademark of 3M Company.
© 3M 2020. All rights reserved.