

Whole House Water Filtration ○ Reference the green circle on the map for this setup

Whole house water filter systems are great solutions to help protect your pipes and appliances as well as offer you great tasting drinking water from anywhere in the home.

3M's latest innovation in whole house water filtration systems, the AP900 series, offers you three levels of filtration for great tasting water throughout the house with easy change out replacement cartridges from our proprietary sanitary quick change (SQC) style heads.

AP900 Series: Sanitary Quick Change (SQC) Style Systems

- Three levels of filtration available for different water quality issues
- Stainless steel head with limited 25 year warranty
- Easy SQC replacement change-out style



AP902	AP903	AP904
Particulate	Particulate/CTO*	Particulate/CTO*/Scale*

Scale Inhibition System ○ Reference the orange circle on the map for this setup


The AP430SS system is a great add on to your tank and tankless water heater sale.

This water treatment system helps protect tank and tankless water heaters by providing a consistent, controlled dose of polyphosphate scale inhibitor, plus it helps protect the piping system from corrosion.

Scale Inhibition System

- Maintains efficiency and helps extend the life of tank and tankless water heater systems
- Stainless steel head
- 3/4" inlet/outlet connection

AP430SS
Scale* inhibition at 10 gpm



Important: Diagram shown is for reference purposes only. Read installation and operation manual prior to installing the unit.

Under Sink Water Filtration ○ Reference the pink circles on the map for this setup

Under sink water filtration systems are great solutions to provide cleaner, clearer and great tasting drinking and cooking water by reducing a wide range of contaminants that may be present in the local water.

See our streamlined portfolio of 3M™ Aqua-Pure™ and 3M™ products available differentiated by their reduction claims.



3MFF100 is certified by the Water Quality Association to WQA/ASPE/ANSI S-803 for sustainability attributes and NSF/ANSI 372 for low lead content.

Full Flow System

- Use the existing primary faucet to enjoy a high flow rate
- For strongest water flow, use the 3MFF100
- One year replacement interval** for 3MFF100



3MFF100
High Flow Rate
6,000 Gallon Capacity

Particulate/CTO/Lead/Cyst/Select VOCs***

3MRO301

Particulate/CTO/Arsenic/Barium/Cadmium/Chromium/Copper/Cyst/Fluoride/Lead/Radium/Selenium/TDS/Turbidity

Reverse Osmosis System

- Additional performance claims compared to dedicated faucet systems
- Comes with a faucet to install
- One year replacement interval**



*As tested and verified by manufacturer's laboratory.

**Filter life depends on local water quality. Replace filter cartridge at indicated intervals or when a drop in pressure is noticed.

***For additional performance claims please visit NSF.org.