

Product Data Sheet

September 2022 Supersedes: September 2018

| Product Description | 3M [™] VHB [™] GPH Series, a general purpose, high temperature, grey conformable double coated acrylic foam tape with a high initial tack and a soft foam. Available in three different thicknesses with a 3M branded red siliconised polyethylene film liner. |
|----------------------------|--|
| Key Features | Double coated acrylic foam tape 100 % closed cell acrylic foam High temperature performance (short term 230 °C) Good balance of high temperature and peel & shear performance High initial tack Soft foam enables stress relaxation & an easy application Good sealing properties For indoor and outdoor applications |
| Applications & Benefits | Its temperature performance enables bonding of materials in applications with high operating temperatures such as prior to processing in a powder coating line Capability to bond to a variety of substrates makes it a good fit for multi material bonding - those substrates have a high or medium surface energy including many metals (e.g. stainless steel) and plastics (e.g. Polyamide, PMMA, ABS) For applications in metal working, signage, appliances and specialty vehicle |

| Physical Properties | | GPH-060GF | GPH-110GF | GPH-160GF |
|------------------------|-------------------------------------|------------|--------------------------|------------|
| | Adhesive Type | A | crylic foam adhesive | |
| | Thickness acc. to ASTM D-3652 | 0.60 mm | 1.10 mm | 1.60 mm |
| | Foam Density | | 710 kg/m³ | |
| | Release Liner | 3M branded | red siliconised polyethy | rlene film |
| | Tape Colour | | Grey | |

Performance Characteristics

E

| Туре | GPH- 060GF | GPH- 110GF | GPH- 160GF |
|--|-------------------|---|-------------------|
| 90 ° Peel adhesion to Stainless Steel acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell | 25 N/cm | 37 N/cm | 34 N/cm |
| 90 ° Peel adhesion to PA6 acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell | 33 N/cm | 48 N/cm | 55 N/cm |
| 90 ° Peel adhesion to ABS acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell | 21 N/cm | 33 N/cm | 32 N/cm |
| 90 ° Peel adhesion to PMMA acc. to ASTM D3330, 90° peel angle @ RT, after 72h @ RT dwell | 21 N/cm | 34 N/cm | 37 N/cm |
| Dynamic Shear acc. to ASTM D1002 on stainless steel, after 72h @ RT dwell | 547 N/6.54 cm² | 476 N/6.54 cm² | 375 N/6.54 cm² |
| Static Shear Strength acc. to ASTM D3654, after 72h @ RT dwell (Weight held for 10.000 minutes to stainless steel, 3.32cm ² (0.5in ²) | | 23 °C - 1000 g 150 °C - 500 g | |
| Normal Tensile (T-Block) acc. to ASTM D897 to Aluminium @ RT, after 72h @ RT dwell, 6.45 cm ² , test speed 50 mm/min | 410 N/6.54 cm² | 439 N/6.54 cm² | 470 N/6.54 cm² |
| Temperature Performance | | erm (minutes, hour erm (days, weeks) | |

| Application Temperature | Ideal application temperature range is 21 °C to 38 °C. Pressure sensitive adhesives use viscous flow to achieve substrate contact area. |
|----------------------------|---|
| | Low Temperature Application: 3M ™ VHB™ GPH Tape be applied at 10 °C and down to 5 °C when using 3M Adhesion Promoter AP111 or Primer 94 |
| | To obtain good performance with all 3M [™] VHB [™] Tapes, it is important to ensure that the surfaces are clean, dry and free of condensed moisture. |
| Shelf Life | 24 months from date of production when stored at 16 °C – 25 °C and 40-65 % relative humidity. Performance of tapes is not projected to change even after shelf life expires; however, 3M does suggest that 3M™ VHB™ Tapes are used prior to the shelf life date whenever possible. |

| Automotive Disclaimer | Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, including, but not limited to, automotive electric powertrain battery or high voltage applications. This product does not fully adhere to typical automotive design or quality system requirements, such as IATF 16949 or VDA 6.3. This product may not be manufactured in an IATF certified facility and may not meet a Ppk of 1.33 for all properties. The product may not undergo an automotive production part approval process (PPAP). Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's automotive application and for conducting incoming inspections before use of the product. Failure to do so may result in injury, death, and/or harm to property. No written or verbal statement, report, data or recommendation by 3M related to automotive use of the product shall have any force or effect unless in an agreement signed by the Technical Director of 3M's Automotive Division. Customer assumes all responsibility and risk if customer chooses to use this product in an automotive electric powertrain battery or high voltage application, and 3M will not be liable for any loss or damage arising from or related to the 3M product or customer's use of the product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity or recall costs), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. In no event shall 3M be liable for any damages in excess of the purchase price paid for the product. |
|--------------------------|--|
| | ELECTRIC POWERTRAIN BATTERY OR HIGH VOLTAGE APPLICATION, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY ON PERFORMANCE, LONGEVITY, SUITABILITY, COMPATIBILITY, OR INTEROPERABILITY, OR ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. |
| Important Notice | All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law. |

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

3M Bulgaria Mladost 4 Business Park, bl.4, 2nd floor Sofia 1766 Bulgaria

3M Česko, spol. s r. o. V Parku 2343/24 148 00 - Praha 4 Czech Republic

3M East AG Branch Office Serbia Airport City Omladinskih brigada 90B 11070 Belgrade Serbia

3M (East) AG Branch Office Croatia Avenija Većeslava Holjevca 40 10010 Zagreb Croatia

3M (East) AG Branch Office Slovenia Cesta v Gorice 8 1000 Ljubljana Slovenia

3M (East) AG Representation Office Tirane

Rruga Sami Frasheri Pallati i Ri Perxhola Kati 2 Ap2 1000 Albania

3M Hellas MEPE

20 Kifissias Ave. 15125 Maroussi Athens Greece

3M Hungária Kft Neumann János u. 1/E. 1117 Budapest Hungary

3M Israel 91 Medinat Hayehudim St. Herzliya Israel

3M Poland Sp. z o.o. Aleja Katowicka 117 Kajetany 05-830 Nadarzyn Poland 3M Romania

Bucharest Business Park 12 Menuetului St. Building D, District 1 0 13713 Bucharest Romania

3M Sanayi ve Ticaret A.Ş.

Barbaros Mah., Mor Sümbül Sok. No:7/3F, 27-51, Nidakule Ataşehir Güney 34746 Atasehir, Istanbul Turkey

3M Slovensko s.r.o. Polus Tower 2 Vajnorská 142 Bratislava 83104 Slovakia