



Flexible Air Sealing Tape 8068E

FAST-G / FAST-M

Product Data Sheet

Date: June 2016
Supersedes: November 2014

Product Description

3M™ Flexible Air Sealing Tape 8068E FAST-G / FAST-M are air, moisture and water impermeable tape with an aggressive, high-tack acrylic pressure sensitive adhesive and reinforcing grid. 3M™ FAST-G is a self-wound tape, while 3M™ FAST-M has a poly-coated kraft paper release liner

Intended Use

- Seaming air of interior water vapour membranes
- Taping gaps and penetrations to stop free air flow

Key Features

- Aggressive acrylic pressure sensitive adhesive bonds to concrete, concrete block, anodized aluminium, galvanized metal, exterior gypsum and plywood without the use of any adhesion promoters.
- Reinforcing grid helps strengthen backing and reduce stretch
- Resists UV exposure up to 12 months
- Can be installed at temperatures as low as -20 °C and as warm as 50 °C
- Measurement markings for ease in cutting to the desired length

Physical Properties

	8068E FAST-M
Tape Colour	Tan, semi-translucent
Thickness of Tape (Film & Adhesive) (ASTM D-3652)	0,250 mm
Thickness of Adhesive	0,130 mm
Liner	0,150 mm
Backing	Multilayer Elastomeric Film
Release Liner	Poly-coated kraft paper
Adhesive Type	Acrylic

	8068E FAST-G (LL)
Tape Colour	Tan, semi-translucent
Thickness of Tape (Film & Adhesive) (ASTM D-3652)	0,250 mm
Thickness of Adhesive	0,130 mm
Backing	Multilayer Elastomeric Film
Adhesive Type	Acrylic

**Building Materials
Compatibility Testing
by “ift Rosenheim”**

The following building materials have been tested on compatibility (up to 60 °C) with 3M™ Flexible Air Sealing 8068E FAST-G / FAST-M by the scientific service provider and international testing institute “ift Rosenheim” with the result of no optical or function-affecting impairments.

- Concrete C35
- Exterior plaster HASIT 650 cement mortar
- Interior plaster HASIT 150
- Building plaster with Weber light mortar LM21 without primer
- Building plaster with Weber light mortar LM21 with primer
- fibreC glass fibre concrete slab 2.0
- Wood (spruce) rough, grinded / varnished / painted
- OSB panels class 3 with rough surface
- PVC-U, white
- Anodised aluminium / Powder-coated aluminium
- Vapour barrier: Ampatex DB90
- Vapour barrier: Öko Natur vapour barrier (Isozell)
- Vapour barrier: Folog Starvap D2 (PO)
- Vapour barrier: Isover Vario KM (PA)
- Vapour barrier: Siga Majpell (PE)
- Vapour barrier: D-Tack Tacolau (Alu Coating surface)

Performance Characteristics

	8068E FAST-M	8068E FAST-G (LL)
Adhesion to Stainless Steel 90° peel @room temp, 24 hr dwell, jaw speed 300mm/min (ASTM D-3330)	55 N/100mm	55 N/100mm
Adhesion to Polyethylene 90° peel @room temp, 24 hr dwell, jaw speed 300mm/min (ASTM D-3330)	33 N/100mm	33 N/100mm
Adhesion to Anodised Aluminium 90° peel @room temp, 24 hr dwell, jaw speed 300mm/min (ASTM D-3330)	77 N/100mm	77 N/100mm
Tensile Properties Longitudinal Transverse (acc. to EN 12311- 100mm/min)	138 N/50 mm / 1393 % 62 N/50 mm / 825 %	95 N/50 mm / 1466 % 64 N/50 mm / 914 %
Thermal Shock Resistance -20 °C up to 60 °C Ift Richtlinie MO-01/1 (4.3)	fulfilled	fulfilled
Dynamic Shear Strength to different substrates (acc. to EN 12311-, 5mm/min)	24 – 41 kPA	23 – 43 kPA
Light resistance and resistance to moisture penetration Ift Richtlinie MO-01/1 (4.4)	fulfilled	fulfilled

Water Penetration Around Nails (ASTM 1970)	Pass	Pass
Water Vapour Permeability (S _d value) (EN 12572:2001-06)	11.6 m	14.8 m
Application Temperature Performance	-20 °C up to 50 °C	-20 °C up to 50 °C

Application Handling

To obtain the best adhesion, 8068E FAST-G / FAST-M can be installed when outdoor temperatures range from -20 °C up to 50 °C over clean surfaces that are free from dirt and debris and have not absorbed water.

Surfaces should be free of any damaged, unsupported areas, sharp protrusions or voids.

Surfaces must be clear of snow, ice or frost

Concrete must be cured a minimum of 7 days before application.

Block or brick walls should have mortar joints stuck flush.

UV Durability

When exposed to natural sunlight in Florida and Arizona and when exposed to accelerated aging conditions, the performance of 3M™ Flexible Air Sealing Tape 8068E FAST-G / FAST-M remains stable over an extended period. Based on these tests and performance observed in actual installations, 3M is confident in claiming that the tape will remain fully functional up to 12 months of exposure to sunlight.

Storage & Shelf Life

Store at 16 °C – 25 °C and 40-65 % relative humidity in its original box. The product can be stored up to 24 months after production.

Note: Product shall not be exposed to UV radiation during storage

For Additional Information

To request additional product information or to arrange for sales assistance, call.....

Address correspondence to: 3M

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark the 3M Company.

3M Bulgaria

Mladost 4
Business Park, bl.4, 2nd floor
Sofia 1766
Bulgaria

3M Česko, spol. s r. o.

V Parku 2343/24
148 00 - Praha 4
Czech Republic

3M East AG

Representation Office Serbia

Airport City
Omladinskih brigada 90B
11070 Belgrade
Serbia

3M (East) AG

Branch Office Croatia

Avenija Većeslava Holjevca 40
10010 Zagreb
Croatia

3M (East) AG

Branch Office Slovenia

Cesta v Gorice 8
1000 Ljubljana
Slovenia

3M (East) AG Representation Office Tirane

Rruga Sami Frasherit
Pallati i Ri Perxhola Kati 2 Ap2
1000 Albania

3M Hellas MEPE

20 Kifissias Ave.
151 25 Maroussi
Athens
Greece

3M Hungária Kft

Neumann János u. 1/E.
1117 Budapest
Hungary

3M Israel

91 Medinat Hayehudim St.
Herzliya
Israel

3M Poland Sp. z o.o.

Aleja Katowicka 117 Kajetany
05-830 Nadarzyn
Poland

3M Romania

Bucharest Business Park
12 Menuetului St.
Building D, District 1
013713 Bucharest
Romania

3M Sanayi ve Ticaret A.Ş.

Barbaros Mah., Mor Sümbül
Sok.
No:7/3F, 27-51, Nidakule
Ataşehir Güney
34746 Ataşehir, Istanbul
Turkey

3M Slovensko s.r.o.

Polus Tower 2
Vajnorská 142
Bratislava 83104
Slovakia