

3M | Wrap Film



It's a wrap.

Lead the way.

You've always been one to make the bold choice. Align yourself with a leader. We're reinventing 3M™ Wrap Film with features that will leave your competition in the dust.

A Protective Film Layer on gloss colors.

Stays on during installation then is removed quickly, easily and cleanly after install to reduce surface impressions and scratches.

Unique, conformable film layers.

Provide a better fit around curves and in channels for sleek appearance and easier installation.

An improved warranty.

Gives your customers confidence with up to eight years of protection on vertical applications.*



Gloss Light Green
G16

Create a sensation.

Choose from a bold assortment of colors, patterns and textures to design a vehicle wrap that stands out from the crowd.

Gloss

Red Metallic *G203	Dark Red G83	Flame Red G53	Hot Rod Red G13	Burnt Orange G14	Deep Orange G24	Bright Orange G54	Sunflower G25
Bright Yellow G15	Lucid Yellow G55	Light Green G16	Midnight Blue GP272	Boat Blue G127	Deep Blue Metallic *G217	Blue Metallic *G227	Intense Blue G47
Blue Fire *G337	Sky Blue G77	Hot Pink G103	Ember Black *GP282	Black Rose *GP99	Galaxy Black *GP292	Black G12	Black Metallic *G212
Storm Gray G31	White Gold Sparkle *GP240	White G10	Light Ivory G79				

Satin

 <p>Vampire Red *SP273</p>	 <p>Smoldering Red *S363</p>	 <p>Bitter Yellow *S335</p>	 <p>Apple Green S196</p>	 <p>Perfect Blue *S347</p>	 <p>Ocean Shimmer *S327</p>	 <p>Key West S57</p>	 <p>Gold Dust Black *SP242</p>
 <p>Black S12</p>	 <p>Dark Gray *S261</p>	 <p>Thundercloud *S271</p>	 <p>Battleship Gray S51</p>	 <p>Frozen Vanilla *SP240</p>	 <p>White S10</p>	 <p>Pearl White *SP10</p>	 <p>White Aluminum *S120</p>


Textures

 <p>Shadow Military Green SB26</p>	 <p>Shadow Black SB12</p>	 <p>Brushed Black Metallic *BR212</p>	 <p>Matrix Black MX12</p>	 <p>Carbon Fiber Black CFS12</p>
 <p>Brushed Steel *BR201</p>	 <p>Brushed Titanium *BR230</p>	 <p>Brushed Aluminum *BR120</p>	 <p>Carbon Fiber Anthracite *CFS201</p>	


Chrome

 <p>Gloss Silver Chrome **GC451</p>
--

Matte



Color Flips



Contact your 3M sales representative
for more information or visit:

3M.com/2080

Training and testing.

Learn up-to-date installation techniques, industry best practices and 3M-specific solutions. 3M offers best-in-class graphics installation training and testing programs across the country.

- At locations in St. Paul, Minnesota; Hutchinson, Kansas; Fort Lauderdale, Florida; Addison, Texas; and Burbank, California.
- Via our fully equipped Mobile Training Vehicle that can deliver hands-on training at your location

To sign up for training, visit [3M.com/InstallationPrograms](https://www.3m.com/InstallationPrograms).

Improved warranty.

The most comprehensive warranty in the industry — up to eight years in a vertical application.*

3M™ MCS™ Warranty		Vehicle Wraps		
Product offering might vary from country to country. Local availability of selected graphics construction should be clarified with your local 3M subsidiary.			Vertical	Horizontal
		Zone 1	8 years	3 years
		Zone 2	7 years	2 years
2080	All colors	Zone 3	6 years	1 year

Visit [3M.com/GraphicsWarranties](https://www.3m.com/GraphicsWarranties) for additional applications and zone and warranty information.

*Warranty varies by zone. Warranty information is not valid for Gloss Silver Chrome GC451.

Knowledge and support.

3M™ Wrap Film Series 2080 is a durable, high-quality product that lets you express your creativity and bring your vision to life.

Backed by 3M technical support, training and certification programs that help you and your staff keep up with the latest techniques.

