



SCOTT™
Fire & Safety

3M™ Scott™ Air-Pak™ SCBA NFPA 1981/1982, 2018 Edition Specifications & Ordering Information



Reference Guide

Technical Data

Facepiece	
3M™ Scott™ AV-3000 HT Facepiece	
Weight	1.59 lbs (.72 kg)
Construction	Seal - Polyisoprene / EPDM blend; Headnet - Para-Aramid; Harness Straps - Polyaramid / polybenzimidazole fiber blend (commonly referred to as PBI® Gold)
3M™ Scott™ Vision C5 Facepiece	
Weight	1.53 lbs (.69 kg)
Construction	Seal - Polyisoprene / EPDM blend; Headnet - Para-Aramid; Harness Straps - Polyaramid / polybenzimidazole fiber blend (commonly referred to as PBI® Gold)
Backframe	
3M™ Scott™ Air-Pak™ XD SCBA	
Weight	Backframe 1.63 lb (0.73 kg) Backframe and Padded Harness* 4.26 lb (1.93 kg)
Construction	Stainless Steel 300 Series
3M™ Scott™ Air-Pak™ X3 Pro SCBA	
Weight	Backframe 1.61 lbs Backframe & Harness* 4.76 lbs
Construction	Heat-treated 6061-T6 Aluminum alloy
Harness	
3M™ Scott™ Air-Pak™ XD SCBA	
Construction	Outer Shell—Polybenzimidazole blend (commonly referred to as Armor AP™) Webbing—Kevlar™/Nomex
3M™ Scott™ Air-Pak™ X3 Pro SCBA	
Construction	Outer Shell—Polybenzimidazole blend (commonly referred to as Armor AP™) Webbing—Kevlar™/Nomex
Regulator	
3M™ Scott™ E-Z Flo+ Regulator	
Weight ⁺	0.82 lbs. (0.37 kg)
Dimension	Low-pressure supply line - .575 in (14.61 mm) OD; 0.25 in. (6.35 mm) ID
3M™ Scott™ E-Z Flo C5 Regulator	
Weight ⁺	0.94 lbs. (0.42 kg)
Dimension	Low-pressure supply line - .575 in. OD (14.61 mm); 0.25 in. ID (6.35 mm)

⁺ Includes quick disconnect hose (plug) and Heads-Up Display (HUD)

* Includes regulator holder

PBI Gold is a registered trademark of PBI Performance Products, Inc.

Armor AP is a trademark of Safety Components, Inc.

Kevlar and Nomex are registered trademarks of DuPont de Nemours, Inc.

Reference Guide

Cylinder and Valve Assemblies

Cylinder and Valve Assemblies							
Part Number	Pressure (psig)	Duration (minutes)	Dimensions (L x W)	Air Capacity (ft ³ / l ³)	Water Volume (in ³ / cm ³)	Weight** (lb / kg)	DOT/TC Exemption
Aluminum							
804101-01	2216	30	24.05 × 6.75	45 / 1274	517 / 8.4	21.0 (9.71)	3AL-2216 /3ALM-153
Carbon-Wrapped							
804840-01	2216	30	23.55 × 6.59	45 / 1274	514 / 8.4	11.64 (5.28)	SP-10915-2216 / SU 5134-153
200131-01*	2216	30	23.70 × 6.69	45 / 1274	523 / 8.5	11.89 (5.39)	SP-10915-2216 / SU 5134-153
804721-01	4500	30	21.50 × 5.44	45 / 1274	285 / 4.7	11.08 (5.03)	SP-10915-4500 / SU 5134-310
200128-01*	4500	30	21.50 × 5.44	45 / 1274	285 / 4.7	11.40 (5.17)	SP-10915-4500 / SU 5134-310
804722-01	4500	45	23.40 × 6.26	65 / 1841	418 / 6.8	14.99 (6.80)	SP-10915-4500 / SU 5134-310
200129-01*	4500	45	23.40 × 6.26	65 / 1841	418 / 6.8	15.31 (6.94)	SP-10915-4500 / SU 5134-310
804723-01	4500	60	24.79 × 6.90	87 / 2464	550 / 9.0	19.19 (8.70)	SP-10915-4500 / SU 5134-310
200130-01*	4500	60	24.79 × 6.90	87 / 2464	550 / 9.0	19.51 (8.85)	SP-10915-4500 / SU 5134-310
200930-01	5500	30	22.20 × 4.94	45 / 1274	233 / 3.8	9.99 (4.53)	SP-15136-5500 / SU-10350-379
200967-01*	5500	30	22.20 × 4.94	45 / 1274	233 / 3.8	10.30 (4.67)	SP-15136-5500 / SU-10350-379
200969-01	5500	45	22.22 × 6.00	66 / 1869	349 / 5.7	13.76 (6.24)	SP-15136-5500 / SU-10350-379
200970-01*	5500	45	22.22 × 6.00	66 / 1869	349 / 5.7	14.06 (6.38)	SP-15136-5500 / SU-10350-379
200972-01	5500	60	24.53 × 6.53	87 / 2464	465 / 7.6	17.36 (7.87)	SP-15136-5500 / SU-10350-379
200973-01*	5500	60	24.53 × 6.53	87 / 2464	465 / 7.6	17.67 (8.01)	SP-15136-5500 / SU-10350-379
200975-01	5500	75	25.51 × 7.15	111 / 3143	581 / 9.5	21.62 (9.81)	SP-15136-5500 / SU-10350-379
200976-01*	5500	75	25.51 × 7.15	111 / 3143	581 / 9.5	21.93 (9.95)	SP-15136-5500 / SU-10350-379
Carbon-Wrapped, Short & Stubby							
804722-01A	4500	45	21.30 × 6.79	65 / 1841	416 / 6.8	15.32 (6.95)	SP-10915-4500 / SU 5134-310
200129-01A*	4500	45	21.30 × 6.79	65 / 1841	416 / 6.8	15.64 (7.09)	SP-10915-4500 / SU 5134-310
Carbon-Wrapped ST7							
804721-11	4500	30	21.50 × 5.47	45 / 1274	285 / 4.6	11.08 (5.03)	SP-10915-4500 / SU 5134-310
200128-11*	4500	30	21.50 × 5.47	45 / 1274	285 / 4.7	11.40 (5.17)	SP-10915-4500 / SU 5134-310
804722-11	4500	45	23.40 × 6.29	65 / 1841	418 / 6.8	14.99 (6.80)	SP-10915-4500 / SU 5134-310
200129-11*	4500	45	23.40 × 6.29	65 / 1841	418 / 6.8	15.31 (6.94)	SP-10915-4500 / SU 5134-310
804723-11	4500	60	24.70 × 6.93	87 / 2464	550 / 9.0	19.19 (8.70)	SP-10915-4500 / SU 5134-310
200130-11*	4500	60	24.70 × 6.93	87 / 2464	550 / 9.0	19.51 (8.85)	SP-10915-4500 / SU 5134-310
Carbon-Wrapped 30-Year							
804721-35	4500	30	21.50 × 5.49	45 / 1274	285 / 4.6	11.48 (5.21)	SP-14232-4500
200128-35*	4500	30	21.50 × 5.49	45 / 1274	285 / 4.6	11.80 (5.35)	SP-14232-4500
804722-35	4500	45	23.40 × 6.31	65 / 1841	418 / 6.8	15.84 (7.18)	SP-14232-4500
200129-35*	4500	45	23.40 × 6.31	65 / 1841	418 / 6.8	16.16 (7.33)	SP-14232-4500
804723-35	4500	60	24.75 × 7.00	87 / 2464	550 / 9.0	20.49 (9.29)	SP-14232-4500
200130-35*	4500	60	24.75 × 7.00	87 / 2464	550 / 9.0	20.81 (9.44)	SP-14232-4500

* Snap-Change Cylinder Valve

** Nominal weight of charged cylinder to specified pressure

Reference Guide

3M™ Scott™ Air-Pak™ X3 Pro SCBA



Replacement Parts

3M™ Scott™ Air-Pak™ X3 Pro SCBA

1	Backframe and Harness Assembly	
	Air-Pak™ X3 Pro SCBA, Parachute Buckles	201615-23
2	Harness Components	
	Air-Pak™ X3 Pro SCBA, Parachute Buckles	
	Waist Belt, Male	201608-01
	Waist Belt, Female	201608-02
	Cylinder Retention Assembly	201180-01
	Waist-to-Shoulder Strap	31003739
	Waist Pad Assembly	201610-11
	Shoulder Pad/Strap Assembly	201609-11
	Regulator Holder	201649-01
	UEBSS Pouch	201611-02
3	Personal Alert Safety System (PASS)	
	Battery Cover Assembly	201163-01
	Battery Cover Screw	31001288
	Battery Cover Screw O-ring	31001262
	Battery Cover Seal	31001287
	Battery Cover E-Clip	31001290
4	Cylinder Valve	
	2216 psig Cylinder Valve, CGA	804097-01
	4500 psig Cylinder Valve, CGA	804098-01
	5500 psig Cylinder Valve, CGA	804098-02
	Seal Replacement Kit	200286-01
	Safety Device Kit, 2216 psig	26954-00
	Safety Device Kit, 4500 psig	26954-01
	Safety Device Kit, 5500 psig	26954-03
	2216 psig Cylinder Valve, Snap-Change	805782-01
	4500 psig Cylinder Valve, Snap-Change	805783-01
	5500 psig Cylinder Valve, Snap-Change	805783-02

Regulator Assembly (not shown)	
E-Z Flo+ Regulator	
Regulator, Standard Hose, Snap-Change	200077-67
Regulator, Standard Hose, CGA	200077-68
Regulator, Quick-Connect Hose, Rectus	200077-60
Regulator Gasket	10005368
E-Z Flo C5 Regulator	
Regulator, Standard Hose, Snap-Change	201650-07
Regulator, Standard Hose, CGA	201650-06
Regulator, Quick-Connect Hose, Rectus	201650-05
Regulator Gasket	10005368
Facepiece Assembly (not shown)	
AV-3000 HT Facepiece	
See pages 8-9	
Vision C5 Facepiece	
See pages 10-11	
High Pressure Hose Assembly (not shown)	
2216 psig Hose & Coupling Assembly	200922-01
4500 & 5500 psig Hose & Coupling Assembly	200922-02
Nipple Seal O-Ring	57264-00
Retaining Screw, Nipple Seal O-Ring	10000113

Reference Guide

3M™ Scott™ Air-Pak™ XD SCBA



Replacement Parts

3M™ Scott™ Air-Pak™ XD SCBA

1	Backframe	
	Backframe Assembly, XD	201847-01
2	Harness Components	
	Air-Pak™ XD SCBA	
	Waist Belt, Male	78-8151-3123-6
	Waist Belt, Female	78-8151-3122-8
	Cylinder Retention Assembly	78-8151-5068-1
	Waist-to-Shoulder Strap	78-8151-3121-0
	Shoulder Pad/Strap Assembly	201609-11
	Regulator Holder	201649-01
	UEBSS Pouch	201611-09
	Air-Pak™ XD SCBA, Padded Harness	
	Waist Pad, Padded, Spring Clips	201843-01
	Waist Pad, Padded, Parachute	201843-11
	Shoulder Harness & Strap Assembly, Padded, Spring Clips	201842-01
	Shoulder Harness & Strap Assembly, Padded, Parachute	201842-11
	Air-Pak™ XD SCBA, Unpadded Harness	
	Waist Pad, Unpadded, Spring Clips	201843-02
	Waist Pad, Unpadded, Parachute	201843-12
	Shoulder Harness & Strap Assembly, Padded, Spring Clips	201842-02
	Shoulder Harness & Strap Assembly, Padded, Parachute	201842-12
3	Personal Alert Safety System (PASS)	
	Battery Cover Assembly	70-0020-0962-2
	Battery Cover Screw	78-8151-2956-0
	Battery Cover Screw O-ring	31001262
	Battery Cover Seal	31001287
	Battery Cover E-Clip	31001290
4	Cylinder Valve	
	4500 psig Cylinder Valve, CGA	804098-01
	5500 psig Cylinder Valve, CGA	804098-02
	Seal Replacement Kit	200286-01
	Safety Device Kit, 4500 psig	26954-01
	Safety Device Kit, 5500 psig	26954-03

Regulator Assembly (not shown)

E-Z Flo+ Regulator	
Regulator, Standard Hose, Snap-Change	200077-67
Regulator, Standard Hose, CGA	200077-68
Regulator, Quick-Connect Hose, Rectus	200077-60
Regulator Gasket	10005368
E-Z Flo C5 Regulator	
Regulator, Standard Hose, Snap-Change	201650-07
Regulator, Standard Hose, CGA	201650-06
Regulator, Quick-Connect Hose, Rectus	201650-05
Regulator Gasket	10005368

Facepiece Assembly (not shown)

AV-3000 HT Facepiece	
See pages 8-9	
Vision C5 Facepiece	
See pages 10-11	

High Pressure Hose Assembly (not shown)

4500 & 5500 psig Hose & Coupling Assembly	200922-02
Nipple Seal O-Ring	57264-00
Retaining Screw, Nipple Seal O-Ring	10000113

Replacement Parts

3M™ Scott™ AV-3000 HT Facepiece



Replacement Parts

3M™ Scott™ AV-3000 HT Facepiece

Facepiece Assembly

3M™ Scott™ AV-3000 HT Facepiece

AV-3000 HT, 5-strap, Small	201215-01
AV-3000 HT, 5-strap, Medium	201215-02
AV-3000 HT, 5-strap, Large	201215-03
AV-3000 HT w/ RT Comm Bracket (Open), 5-Strap, Small	201215-04
AV-3000 HT w/ RT Comm Bracket (Open), 5-Strap, Medium	201215-05
AV-3000 HT w/ RT Comm Bracket (Open), 5-Strap, Large	201215-06
AV-3000 HT, 4-Strap, Small	201215-21
AV-3000 HT, 4-Strap, Medium	201215-22
AV-3000 HT, 4-Strap, Large	201215-23
AV-3000 HT w/ RT Comm Bracket (Open), 4-Strap, Small	201215-27
AV-3000 HT w/ RT Comm Bracket (Open), 4-Strap, Medium	201215-28
AV-3000 HT w/ RT Comm Bracket (Open), 4-Strap, Large	201215-29
Fenestra Lens	201134-01
Head Harness Assembly, 5-Strap*	200803-01
Temple Strap, 5-Strap**	804178-02
Neck Strap, 5-Strap	804176-02
Head Harness Assembly, 4-Strap, Small	201467-01
Head Harness Assembly, 4-Strap, Medium/Large	201467-02
Temple Strap, 4-Strap	804178-03
Neck Strap, 4-Strap	804176-03
Nosecup Assembly, Small	201126-02
Nosecup Assembly, Medium	201127-02
Nosecup Assembly, Large	201128-02
Sizing Dot, Small (Green)	31003407
Sizing Dot, Medium (Black)	31003408
Sizing Dot, Large (Red)	31003409

*Includes the temple strap sewn into the head harness

**Replacement of the temple strap on AV-3000 HT, 5-Strap products produced after August 2015 will require replacement of head harness assembly (200803-01)

Replacement Parts

3M™ Scott™ Vision C5 Facepiece



Replacement Parts

3M™ Scott™ Vision C5 Facepiece

Facepiece Assembly

3M™ Scott™ Vision C5 Facepiece

Vision C5, Small Faceseal, 4-Strap	FP1S40000000000
Vision C5, Medium Faceseal, 4-Strap	FP1M40000000000
Vision C5, Large Faceseal, 4-Strap	FP1L40000000000
Vision C5, Small Faceseal, 5-Strap	FP1S50000000000
Vision C5, Medium Faceseal, 5-Strap	FP1M50000000000
Vision C5, Large Faceseal, 5-Strap	FP1L50000000000
Nosecup Assembly, Small	201484-01
Nosecup Assembly, Medium	201486-01
Nosecup Assembly, Large	201488-01
Inhalation Valve	31002788
Temple Tab, Left	201491-01
Temple Tab, Right	201500-01
Sizing Stud, Small	31003603
Sizing Stud, Medium	31003602
Sizing Stud, Large	31003601
Headnet Buckle, Gen 1	201502-02
Headnet Buckle, Gen 2	78-8151-6243-9
Headnet Buckle with D-ring, Gen 1	201502-01
Headnet Assembly, Small, Gen 1*	201496-03
Headnet Assembly, Medium, Gen 1*	201496-02
Headnet Assembly, Large, Gen 1*	201496-01
Headnet Assembly, Small, 4-Strap, Gen 2*	78-8151-6291-8
Headnet Assembly, Medium, 4-Strap, Gen 2*	78-8151-6292-6
Headnet Assembly, Large, 4-Strap, Gen 2*	78-8151-6293-4
Headnet Assembly, Small, 5-Strap, Gen 2*	70-0020-1033-1
Headnet Assembly, Medium, 5-Strap, Gen 2*	70-0020-1034-9
Headnet Assembly, Large, 5-Strap, Gen 2*	70-0020-1035-6
Stirrup Assembly, Small, 5-Strap, Gen 2**	70-0020-1036-4
Stirrup Assembly, Medium, 5-Strap, Gen 2**	70-0020-1063-8
Stirrup Assembly, Large, 5-Strap, Gen 2**	70-0020-1064-6
Temple Strap, Gen 1	804178-05
Temple Strap, Gen 2	78-8151-6287-6
Neck Strap, Gen 1	804178-03
Neck Strap, Gen 2	78-8151-6286-8
Accessory Neck Strap	201682-01

*Includes headnet, temple and neck straps

**Includes stirrup, buckle, and sizing stud

SCBA Weights

3M™ Scott™ Air-Pak™ X3 Pro SCBA (CGA) with 3M™ Scott™ E-Z Flo+ Regulator

	Pak-Tracker			SEMS II Pro		
	Standard*	w/ QD Hose	w/UEBSS	Standard*	w/ QD Hose	w/ UEBSS
2216 psig, 30-min (Aluminum Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A
2216 psig, 30-min (Carbon Cylinder)	26.27 (11.91)	26.56 (12.05)	27.75 (12.59)	26.27 (11.91)	26.56 (12.05)	27.75 (12.59)
4500 psig, 30-min (Carbon Cylinder)	25.77 (11.69)	26.06 (11.82)	27.25 (12.36)	25.77 (11.69)	26.06 (11.82)	27.25 (12.36)
4500 psig, 45-min (Carbon Cylinder)	29.70 (13.47)	29.99 (13.60)	31.18 (14.14)	29.70 (13.47)	29.99 (13.60)	31.18 (14.14)
4500 psig, 60-min (Carbon Cylinder)	33.98 (15.41)	34.27 (15.54)	35.46 (16.08)	33.98 (15.41)	34.27 (15.54)	35.46 (16.08)
5500 psig, 30-min (Carbon Cylinder)	24.95 (11.32)	25.24 (11.45)	26.43 (11.99)	24.95 (11.32)	25.24 (11.45)	26.43 (11.99)
5500 psig, 45-min (Carbon Cylinder)	28.66 (13.00)	28.95 (13.13)	30.14 (13.67)	28.66 (13.00)	28.95 (13.13)	30.14 (13.67)
5500 psig, 60-min (Carbon Cylinder)	32.37 (14.68)	32.66 (14.81)	33.85 (15.35)	32.37 (14.68)	32.66 (14.81)	33.85 (15.35)
5500 psig, 75-min (Carbon Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A

3M™ Scott™ Air-Pak™ X3 Pro SCBA (CGA) with 3M™ Scott™ E-Z Flo C5 Regulator

	Pak-Tracker			SEMS II Pro		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/UEBSS
2216 psig, 30-min (Aluminum Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A
2216 psig, 30-min (Carbon Cylinder)	26.39 (11.97)	26.68 (12.10)	27.87 (12.64)	26.39 (11.97)	26.68 (12.10)	27.87 (12.64)
4500 psig, 30-min (Carbon Cylinder)	25.89 (11.74)	26.18 (11.87)	27.37 (12.41)	25.89 (11.74)	26.18 (11.87)	27.37 (12.41)
4500 psig, 45-min (Carbon Cylinder)	29.82 (13.53)	30.11 (13.66)	31.30 (14.20)	29.82 (13.53)	30.11 (13.66)	31.30 (14.20)
4500 psig, 60-min (Carbon Cylinder)	34.10 (15.47)	34.39 (15.60)	35.58 (16.14)	34.10 (15.47)	34.39 (15.60)	35.58 (16.14)
5500 psig, 30-min (Carbon Cylinder)	25.07 (11.37)	25.36 (11.50)	26.55 (12.04)	25.07 (11.37)	25.36 (11.50)	26.55 (12.04)
5500 psig, 45-min (Carbon Cylinder)	28.78 (13.05)	29.07 (13.18)	30.26 (13.72)	28.78 (13.05)	29.07 (13.18)	30.26 (13.72)
5500 psig, 60-min (Carbon Cylinder)	32.49 (14.74)	32.78 (14.87)	33.97 (15.41)	32.49 (14.74)	32.78 (14.87)	33.97 (15.41)
5500 psig, 75-min (Carbon Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A

3M™ Scott™ Air-Pak™ X3 Pro SCBA (Snap-Change) with 3M™ Scott™ E-Z Flo+ Regulator

	Pak-Tracker			SEMS II Pro		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/UEBSS
2216 psig, 30-min (Carbon Cylinder)	25.88 (11.74)	26.17 (11.87)	27.36 (12.41)	25.88 (11.74)	26.17 (11.87)	27.36 (12.41)
4500 psig, 30-min (Carbon Cylinder)	25.38 (11.51)	25.67 (11.64)	26.86 (12.18)	25.38 (11.51)	25.67 (11.64)	26.86 (12.18)
4500 psig, 45-min (Carbon Cylinder)	29.31 (13.29)	29.60 (13.43)	30.79 (13.97)	29.31 (13.29)	29.60 (13.43)	30.79 (13.97)
4500 psig, 60-min (Carbon Cylinder)	33.59 (15.24)	33.88 (15.37)	35.07 (15.91)	33.59 (15.24)	33.88 (15.37)	35.07 (15.91)
5500 psig, 30-min (Carbon Cylinder)	24.56 (11.14)	24.85 (11.27)	26.04 (11.81)	24.56 (11.14)	24.85 (11.27)	26.04 (11.81)
5500 psig, 45-min (Carbon Cylinder)	28.27 (12.82)	28.56 (12.95)	29.75 (13.49)	28.27 (12.82)	28.56 (12.95)	29.75 (13.49)
5500 psig, 60-min (Carbon Cylinder)	31.98 (14.51)	32.27 (14.64)	33.46 (15.18)	31.98 (14.51)	32.27 (14.64)	33.46 (15.18)
5500 psig, 75-min (Carbon Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A

3M™ Scott™ Air-Pak™ X3 Pro SCBA (Snap-Change) with 3M™ Scott™ E-Z Flo C5 Regulator

	Pak-Tracker			SEMS II Pro		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/ UEBSS
2216 psig, 30-min (Carbon Cylinder)	26.00 (11.79)	26.29 (11.92)	27.48 (12.46)	26.00 (11.79)	26.29 (11.92)	27.48 (12.46)
4500 psig, 30-min (Carbon Cylinder)	25.50 (11.57)	25.79 (11.70)	26.98 (12.24)	25.50 (11.57)	25.79 (11.70)	26.98 (12.24)
4500 psig, 45-min (Carbon Cylinder)	29.43 (13.35)	29.72 (13.48)	30.91 (14.02)	29.43 (13.35)	29.72 (13.48)	30.91 (14.02)
4500 psig, 60-min (Carbon Cylinder)	33.71 (15.29)	34.00 (15.40)	35.19 (15.96)	33.71 (15.29)	34.00 (15.40)	35.19 (15.96)
5500 psig, 30-min (Carbon Cylinder)	24.68 (11.19)	24.97 (11.33)	26.16 (11.86)	24.68 (11.19)	24.97 (11.33)	26.16 (11.86)
5500 psig, 45-min (Carbon Cylinder)	28.39 (12.88)	28.68 (13.01)	29.87 (13.55)	28.39 (12.88)	28.68 (13.01)	29.87 (13.55)
5500 psig, 60-min (Carbon Cylinder)	32.10 (14.56)	32.39 (14.69)	33.58 (15.23)	32.01 (14.52)	32.39 (14.69)	33.58 (15.23)
5500 psig, 75-min (Carbon Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A

*Includes a standard low pressure hose, standard waist belt, no buddy breathing option, and no airline option
Nominal weights in lbs. with fully charged cylinder

3M™ Scott™ Air-Pak™ XD SCBA (Padded Harness) with 3M™ Scott™ E-Z Flo+ Regulator

	Pak-Tracker			SEMS 3.0		
	Standard*	w/ QD Hose	w/UEBSS	Standard*	w/ QD Hose	w/ UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.72 (11.66)	26.01 (11.79)	27.20 (12.33)	25.72 (11.66)	26.01 (11.79)	27.20 (12.33)
4500 psig, 45-min (Carbon Cylinder)	29.62 (13.43)	29.91 (13.56)	31.10 (14.10)	29.62 (13.43)	29.91 (13.56)	31.10 (14.10)
4500 psig, 60-min (Carbon Cylinder)	33.82 (15.34)	34.11 (15.47)	35.30 (16.01)	33.82 (15.34)	34.11 (15.47)	35.30 (16.01)
5500 psig, 30-min (Carbon Cylinder)	24.62 (11.16)	24.91 (11.29)	26.10 (11.83)	24.62 (11.16)	24.91 (11.29)	26.10 (11.83)
5500 psig, 45-min (Carbon Cylinder)	28.42 (12.89)	28.71 (13.02)	29.90 (13.56)	28.42 (12.89)	28.71 (13.02)	29.90 (13.56)
5500 psig, 60-min (Carbon Cylinder)	32.02 (14.52)	32.31 (14.65)	33.50 (15.19)	32.02 (14.52)	32.31 (14.65)	33.50 (15.19)

3M™ Scott™ Air-Pak™ XD SCBA (Unpadded Harness) with 3M™ Scott™ E-Z Flo+ Regulator

	Pak-Tracker			SEMS 3.0		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.6 (11.61)	25.89 (11.74)	27.08 (12.28)	25.6 (11.61)	25.89 (11.74)	27.08 (12.28)
4500 psig, 45-min (Carbon Cylinder)	29.5 (13.38)	29.79 (13.51)	30.98 (14.05)	29.5 (13.38)	29.79 (13.51)	30.98 (14.05)
4500 psig, 60-min (Carbon Cylinder)	33.7 (15.28)	33.99 (15.41)	35.18 (15.95)	33.7 (15.28)	33.99 (15.41)	35.18 (15.95)
5500 psig, 30-min (Carbon Cylinder)	24.5 (11.11)	24.79 (11.24)	25.98 (11.78)	24.5 (11.11)	24.79 (11.24)	25.98 (11.78)
5500 psig, 45-min (Carbon Cylinder)	28.3 (12.83)	28.59 (12.96)	29.78 (13.50)	28.3 (12.83)	28.59 (12.96)	29.78 (13.50)
5500 psig, 60-min (Carbon Cylinder)	31.9 (14.46)	32.19 (14.60)	33.38 (15.14)	31.9 (14.46)	32.19 (14.60)	33.38 (15.14)

3M™ Scott™ Air-Pak™ XD SCBA (Padded Harness) with 3M™ Scott™ E-Z Flo C5 Regulator

	Pak-Tracker			SEMS 3.0		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.90 (11.75)	26.19 (11.87)	27.39 (12.42)	25.90 (11.75)	26.19 (11.87)	27.39 (12.42)
4500 psig, 45-min (Carbon Cylinder)	29.80 (13.51)	30.09 (13.64)	31.29 (14.19)	29.80 (13.51)	30.09 (13.64)	31.29 (14.19)
4500 psig, 60-min (Carbon Cylinder)	34.00 (15.42)	34.29 (15.55)	35.49 (16.09)	34.00 (15.42)	34.29 (15.55)	35.49 (16.09)
5500 psig, 30-min (Carbon Cylinder)	24.80 (11.24)	25.09 (11.38)	26.29 (11.92)	24.80 (11.24)	25.09 (11.38)	26.29 (11.92)
5500 psig, 45-min (Carbon Cylinder)	28.60 (12.97)	28.89 (13.10)	30.09 (13.64)	28.60 (12.97)	28.89 (13.10)	30.09 (13.64)
5500 psig, 60-min (Carbon Cylinder)	32.20 (14.60)	32.49 (14.73)	33.69 (15.28)	32.20 (14.60)	32.49 (14.73)	33.69 (15.28)

3M™ Scott™ Air-Pak™ XD SCBA (Unpadded Harness) with 3M™ Scott™ E-Z Flo C5 Regulator

	Pak-Tracker			SEMS 3.0		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/ UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.72 (11.66)	26.01 (11.79)	27.20 (12.33)	25.72 (11.66)	26.01 (11.79)	27.20 (12.33)
4500 psig, 45-min (Carbon Cylinder)	29.62 (13.43)	29.91 (13.56)	31.10 (14.10)	29.62 (13.43)	29.91 (13.56)	31.10 (14.10)
4500 psig, 60-min (Carbon Cylinder)	33.82 (15.34)	34.11 (15.47)	35.30 (16.01)	33.82 (15.34)	34.11 (15.47)	35.30 (16.01)
5500 psig, 30-min (Carbon Cylinder)	24.62 (11.16)	24.91 (11.29)	26.10 (11.83)	24.62 (11.16)	24.91 (11.29)	26.10 (11.83)
5500 psig, 45-min (Carbon Cylinder)	28.42 (12.89)	28.71 (13.02)	29.90 (13.56)	28.42 (12.89)	28.71 (13.02)	29.90 (13.56)
5500 psig, 60-min (Carbon Cylinder)	32.02 (14.52)	32.31 (14.65)	33.50 (15.19)	32.02 (14.52)	32.31 (14.65)	33.50 (15.19)

*Includes a standard low pressure hose, standard waist belt, no buddy breathing option, and no airline option
Nominal weights in lbs. (kg) with fully charged cylinder

Certification/Warranty

NIOSH Approvals

3M™ Scott™ Air-Pak™ XD SCBA

Model	30 Minutes	45 Minutes	60 Minutes	75 Minutes
4500 psig (300 BAR) Models	TC-13F-1092CBRN TC-13F-1130CBRN TC-13F-1136CBRN	TC-13F-1093CBRN TC-13F-1131CBRN TC-13F-1137CBRN	TC-13F-1094CBRN TC-13F-1132CBRN TC-13F-1138CBRN	N/A
5500 psig (379 BAR) Models	TC-13F-1095CBRN TC-13F-1133CBRN TC-13F-1139CBRN	TC-13F-1096CBRN TC-13F-1134CBRN TC-13F-1140CBRN	TC-13F-1097CBRN TC-13F-1135CBRN TC-13F-1141CBRN	N/A

3M™ Scott™ Air-Pak™ X3 Pro SCBA (CGA)

Model	30 Minutes	45 Minutes	60 Minutes	75 Minutes
2216 psig (150 BAR) Models	TC-13F-0972CBRN TC-13F-0988CBRN TC-13F-1032CBRN	N/A	N/A	N/A
4500 psig (300 BAR) Models	TC-13F-0974CBRN TC-13F-0990CBRN TC-13F-1034CBRN	TC-13F-0976CBRN TC-13F-0992CBRN TC-13F-1036CBRN	TC-13F-0978CBRN TC-13F-0994CBRN TC-13F-1038CBRN	N/A
5500 psig (379 BAR) Models	TC-13F-0980CBRN TC-13F-0996CBRN TC-13F-1040CBRN	TC-13F-0982CBRN TC-13F-0998CBRN TC-13F-1042CBRN	TC-13F-0984CBRN TC-13F-1000CBRN TC-13F-1044CBRN	TC-13F-0986CBRN TC-13F-1002CBRN TC-13F-1046CBRN

3M™ Scott™ Air-Pak™ X3 Pro SCBA (Snap-Change)

Model	30 Minutes	45 Minutes	60 Minutes	75 Minutes
2216 psig (150 BAR) Models	TC-13F-0973CBRN TC-13F-0989CBRN TC-13F-1033CBRN	N/A	N/A	N/A
4500 psig (300 BAR) Models	TC-13F-0975CBRN TC-13F-0991CBRN TC-13F-1035CBRN	TC-13F-0977CBRN TC-13F-0993CBRN TC-13F-1037CBRN	TC-13F-0979CBRN TC-13F-0995CBRN TC-13F-1039CBRN	N/A
5500 psig (379 BAR) Models	TC-13F-0981CBRN TC-13F-0997CBRN TC-13F-1041CBRN	TC-13F-0983CBRN TC-13F-0999CBRN TC-13F-1043CBRN	TC-13F-0985CBRN TC-13F-1001CBRN TC-13F-1045CBRN	TC-13F-0987CBRN TC-13F-1003CBRN TC-13F-1047CBRN

Warranty

3M™ Scott™ Air-Pak™ SCBA

SCBA (Including electronics and pressure reducer) - As Long As You Own It

3M™ Scott™ Vision C5 Facepiece

Facepiece (less electronics) - As Long As You Own It

Radio Direct Interface (RDI) - 5 Years

See published warranty statements for further details

Accessories / Options**Supply Hose**

Hansen	30010-XXX*
Schrader	30020-XXX*
Hansen HK	26369-XXX*
Foster	26370-XXX*

Extended Duration Airline Adapter (Rectus compatible)

Hansen	201729-01
Foster	201729-02
Hansen HK	201729-03
Schrader	201729-04

Chest Strap

Universal (Compatible with Air-Pak XD** and Air-Pak X3 Pro SCBA)	201612-01
--	-----------

Waist Belt Extension

Air-Pak™ X3 Pro SCBA	201614-01
Air-Pak™ XD SCBA	805088-01

Carrying Case

Hard Plastic	804497-01
Soft Canvas	10009324

Tool Adapter***

Snap-Change	200388-01
-------------	-----------

Facepiece

Storage Bag, Fleece	805534-01
Neck Strap Accessory, AV-3000 HT	804088-02
Neck Strap Accessory, Vision C5	201682-01
Communications Bracket, AV-3000 HT, Open, Right	201210-01
Communications Bracket, AV-3000 HT, Open, Left	201210-02
Mask Hook	804594-01

Eyeglass Kit

Standard	805753-01
Wire Frame, 52mm, AV-3000 HT	200372-52F
Wire Frame, 60mm, AV-3000 HT	200372-60F
Wire Frame, 52mm, Vision C5	200372-52FC5
Wire Frame, 60mm, Vision C5	200372-60FC5

*XXX denotes length up to 150 ft. Please contact 3M Scott Fire & Safety for more information.

**Chest strap is only compatible with the Air-Pak XD with Padded Harness

***Accommodates 2216 psig, 4500 psig, and 5500 psig Snap-Change cylinders.

**3M Scott Fire & Safety**

Personal Safety Division
Monroe Center, P.O. Box 569
Monroe, NC 28110

3M PSD products are occupational use only.

Phone: 1-800-247-7257
Email: US-3M-ScottMonroeCSR@mmm.com
Web: 3M.com/ScottFire
3M.ca/ScottFire

3M, Scott, and Air-Pak are trademarks of 3M.
Please recycle. Printed in USA © 3M, 2025. All other
trademarks are property of their respective owners.