

3M Sonderangebot!

Zusätzliche 6% Rabatt auf 3M™ Fiberscheiben

Schweißnahtvorbereitung
und Materialabtrag

Sparen
Sie
6%

SAP ID	PRODUKTBESCHREIBUNG	MOQ	MPT*	BCOM LINK
3M™ Cubitron™ II 982C Fiberscheiben				
7000028192	982C 36+ SLOT 453EQ 115X22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028192
7000028194	982C 60+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028194
7000028196	982C 80+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028196
7000028191	982C 36+ SLTD 492EQ 125x22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028191
7000028195	982C 60+ SLTD 492EQ 125 x 22MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028195
7000028197	982C 80+ SLOT 493EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028197
7000028201	982C 36+ SLTD FRMD 709EQ 180 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028201
7000028203	982C 60+ SLTD FRMD 709EQ 180 X 22MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028203
7000028204	982C 80+ SLTD FRMD 709EQ 180 X 22MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028204
3M™ Cubitron™ II 987C Fiberscheiben				
7000045159	987C 36+ SLTD 453EQ 115X22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000045159
7000045160	987C 60+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000045160
7000045161	987C 80+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000045161
7000028193	987C 36+ SLTD 492EQ 125x22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028193
7000028199	987C 60+ SLOT 492EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028199
7000028200	987C 80+ SLOT 492EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000028200
7000045188	987C 36+ SLTD FRMD 709EQ 180 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000045188
7000045186	987C 60+ SLTD FRMD 709EQ 180 X 22MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000045186
7000045187	987C 80+ SLTD FRMD 709EQ 180 X 22MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7000045187
3M™ 782C Fiberscheiben				
7100099545	782C 36+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099545
7100099250	782C 60+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099250
7100099093	782C 80+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099093
7100099576	782C 36+ SLOT 492EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099576
7100099094	782C 60+ SLOT 492EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099094
7100099095	782C 80+ SLOT 492EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099095
7100099284	782C 36+ SLOT 709EQ 180 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099284
7100099091	782C 60+ SLOT 709EQ 180 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099091
7100099237	782C 80+ SLOT 709EQ 180 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099237
3M™ 787C Fiberscheiben				
7100099787	787C 36+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099787
7100099260	787C 60+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099260
7100099254	787C 80+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099254
7100099791	787C 120+ SLOT 453EQ 115 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099791
7100099788	787C 36+ SLOT 492EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099788
7100099245	787C 60+ SLOT 492EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099245
7100099256	787C 80+ SLOT 492EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099256
7100099546	787C 120+ SLOT 492EQ 125 x 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099546
7100099257	787C 36+ SLOT 709EQ 180 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099257
7100099247	787C 60+ SLOT 709EQ 180 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099247
7100099240	787C 80+ SLOT 709EQ 180 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099240
7100099243	787C 120+ SLOT 709EQ 180 X 22 MM DC	100	15000	https://order.3m.com/store/escatalog/~d/7100099243

* Minimal Promotional Threshold



3M Deutschland GmbH
Schleif- und Poliersysteme
Carl-Schurz-Straße 1
41453 Neuss
Tel: +49 2131 14-2710
schleifen.de@3m.com
www.3m.de/schleifen

©3M 2020. Alle Rechte vorbehalten.