



# Scotch™ Filament Tape 8956

## Product Data Sheet

October 2009  
Supersedes: December 2003

**Product Description** A utility packaging tape reinforced with continuous glass filaments which gives tensile strength to the tape.

**Key Features** The ScotchPro™ bi-axially oriented polypropylene backing provides abrasion, moisture and scuff resistance. The adhesive is formulated to adhere adequately to fiberboard surfaces.

### Construction

<b>Adhesive Type</b>	Synthetic Rubber Resin (Hot Melt)
<b>Backing</b>	BOPP
<b>Reinforcement</b>	Glass Yarns
<b>Total Thickness</b> AFERA 5006	120 µm
<b>Core size (ID)</b>	76 mm (3")
<b>Colour</b>	Transparent

### Performance Characteristics

<b>Adhesion to Stainless Steel</b> AFERA 5001	8,0 N/cm
<b>Tensile Strength</b> AFERA 5004	260 N/cm
<b>Elongation at Break</b> AFERA 5004	6 %
<b>Static Shear</b> AFERA 5012	2000+ minutes

<b>Storage</b>	Store in clean dry place. Temperature of 21 °C and 50 % relative humidity are recommended.
<b>Shelf Life</b>	Scotch 8956 has a shelf life of 12 months from date of dispatch by 3M.
<b>Precautionary Information</b>	Refer to product label and Material Safety Data Sheet for health and safety information before using the product. For information please contact your local 3M Office. <a href="http://www.3M.com">www.3M.com</a>
<b>For Additional Information</b>	To request additional product information see address below
<b>Important Notice</b>	All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications.  
This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

**3M Adrique Francophone**

Société à responsabilité limitée  
Au capital de 19.756.400 Dirhams  
Siège Social: ZF Ksar Almajaz Bureau  
6 Plateforme  
Lot n°2 Immeuble 4 zénith Tanger  
R.C : 74327, I.F. : 18745050

**3M Gulf Limited**

Ein El Mreisseh  
Saint Charles City Center, 4th Floor  
P.O.Box: 11-5025  
Riad el Solh  
Beirut 1107 2180  
Lebanon

**3M Minnesota Mining &**

**Manufacturing Nigeria Limited**  
No 2 Sheraton Opebi Link Road  
Ikeja  
Lagos  
Nigeria

**3M Arabia, LLC**

Building 24-25 3M Saudi Arabia  
Zone C, Business Gate  
Airport Road Riyadh  
Saudi Arabia

**3M Gulf (Representation Office)**

Suhaim Bin Hamad St., Al Mana Towers  
Tower B, 2nd Floor, Office No.4  
Doha Qatar  
P.O.Box 14684

**3M Pakistan**

Islamic Chamber of Commerce Building  
ST-2/A, Block 9, KDA Scheme 5  
Clifton, Karachi  
Pakistan

**3M Egypt**

Finance Center, New Cairo  
Plot 140, Banking Sector  
5th settlement, Cairo  
Egypt

**3M Kenya Ltd.**

Victoria Towers, 3rd Floor  
Kilimanjaro Av, Upperhill  
Kenya

**3M South Africa & Sub-Saharan Africa**

146A Kelvin Drive  
Woodmead, Sandton  
South Africa

**3M Gulf Limited**

Dubai Internet City  
Building No. 11, 3rd Floor  
U.A.E

**3M Maroc**

Société à responsabilité limitée  
Au capital de 18.000.000 de Dirhams  
Siège Social: 33  
lot la colline II Sidi Maarouf – Casablanca  
R.C:78517, I.F.: 1084514  
Morocco