# 3M Scotch™ "Built-in Sensor" Splittable Flying Splice Tape 9351

### **Product Data Sheet**

September 2015 Supersedes: April 2012

#### **Product Description**

A double coated, splittable tape construction designed for straight line flying splices, furnished with repulpable acrylic adhesive on both sides and an easy release paper liner (also repulpable), with liner score for easy manual application and a built-in sensor layer (non-repulpable, eliminating need for the traditional aluminium sensor label on the splice pattern).

#### **Key Features**

- Built-in aluminium sensor within the tape construction eliminates the need for the traditional reflective label needed for splice detection.
- Good shear for both cold set newsprint, and heat set commercial printing processes, and are specifically designed for improved adhesion to a wide range of coated papers.
- A colour stabilized blue dye has been added to the splicing side adhesive to render the prepared splice pattern more visible after removing the liner just prior to splicing.
- Modified splittable layer to provide a slightly higher overall splitting force for improved splice reliability on core driven presses and higher speed processes
- Product can also be used on core driven presses.

#### **Physical Properties**

Adhesive Type Splicing side	Blue Repulpable on aluminium laminate	
Adhesive Type Reel side	Clear Repulpable	
Tape Colour	Blue (splicing side) White (tabbing side)	
Carrier	White splittable non-siliconised tissue/aluminium foil laminate	
Thickness (ASTM D-3652) Tape without liner Liner Total	Before splitting 0.148 mm 0.063 mm 0.211 mm	After splitting Splice side 0.091 mm Reel side 0.056 mm
Splittable Layer	cleavable layer, recessed 2 mm in from leading tape edge	
Release Liner	Silicon coated semi-bleached Kraft paper	

Bonding Strength	Good affinity to Cellulose Fibres

#### **Applications**

Designed for: Flying splice of paper webs in the printing industry

Flying splice of paper webs in newsprint, offset litho, gravure and flexographic printing processes. The splittable layer has been modified to provide a slightly higher overall splitting force for improved splice reliability on core driven presses. Please use caution when using on belt driven presses.

#### Storage

3M<sup>™</sup> Scotch<sup>™</sup> Built-in Sensor Splittable Flying Splice Tape 9351 should be stored in the original carton at 18 - 25°C and 45 - 55 % Relative Humidity or refrigerated in the original carton for maximum shelf life.

If the product is refrigerated, it should be allowed to warm to a temperature of at least 21°C before using.

It is recommended that the protective liner be removed just prior to splicing, rather than leaving paper rolls with prepared splice patterns in storage without the protective liner.

#### Shelf Life

12 months from date of manufacture by 3M when stored in the original carton

#### **Precautionary Information**

Refer to product label and Material Safety Data Sheet for health and safety information before using the product.

For information please contact your local 3M Office.

www.3M.com

#### For Additional Information

To request additional product information or to arrange for sales assistance, please call your local sales representative.

Address correspondence to: 3M

#### **Important Notice**

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications.

This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

3M is a trademark the 3M Company.

#### 3M Bulgaria

Mladost 4 Business Park, bl.4, 2nd floor Sofia 1766 Bulgaria

#### 3M Česko, spol. s r. o.

V Parku 2343/24 148 00 - Praha 4 Czech Republic

#### 3M East AG

#### Representation Office Serbia

Airport City Omladinskih brigada 90B 11070 Belgrade Serbia

#### 3M (East) AG Branch Office Croatia

Avenija Većeslava Holjevca 40 10010 Zagreb Croatia

#### 3M (East) AG Branch Office Slovenia

Cesta v Gorice 8 1000 Ljubljana Slovenia

## 3M (East) AG Representation Office Tirane

Rruga Sami Frasheri Pallati i Ri Perxhola Kati 2 Ap2 1000 Albania

#### 3M Hellas MEPE

20 Kifissias Ave. 151 25 Maroussi Athens Greece

#### 3M Hungária Kft

Neumann János u. 1/E. 1117 Budapest Hungary

#### 3M Israel

91 Medinat Hayehudim St. Herzliya Israel

#### 3M Poland Sp. z o.o.

Aleja Katowicka 117 Kajetany 05-830 Nadarzyn Poland

#### 3M Romania

Bucharest Business Park 12 Menuetului St. Building D, District 1 013713 Bucharest Romania

#### 3M Sanayi ve Ticaret A.Ş.

Barbaros Mah., Mor Sümbül Sok. No:7/3F, 27-51, Nidakule Ataşehir Güney 34746 Atasehir, Istanbul Turkey

#### 3M Slovensko s.r.o.

Polus Tower 2 Vajnorská 142 Bratislava 83104 Slovakia