

Coatings and Nozzle Size Quick Reference Guide

for 3M™ Performance Spray Gun



Spray a full range of high-performance automotive coatings with one of seven available gravity HVLP atomizing head sizes. Keep in mind that the recommended nozzle size may vary by paint manufacturer, coating type or depending on your specific application.

3M™ Performance Gravity HVLP Atomizing Head Sizes

2.0 **1.8** **1.6** **1.4** **1.3** **1.2** **0.9**

● ● ● ● ● ● ○

Automotive Coatings

- High Viscosity Coatings
- Sprayable Fillers
- High Build Primer
- Primer Surfacer
- Wet on Wet Primer
- Primer Sealer
- Direct Gloss
- Single Stage Top Coat
- Solvent Base Color
- Clearcoat
- Waterborne Base Coat
- UV Primers
- Midcoat / Effect Coats
- Smart / Spot Repair

	2.0	1.8	1.6	1.4	1.3	1.2	0.9
High Viscosity Coatings	●	●					
Sprayable Fillers	●	●					
High Build Primer		●	●	●			
Primer Surfacer		●	●	●			
Wet on Wet Primer				●	●		
Primer Sealer				●	●		
Direct Gloss				●			
Single Stage Top Coat				●			
Solvent Base Color				●	●		
Clearcoat				●	●	●	
Waterborne Base Coat					●	●	
UV Primers					●	●	○
Midcoat / Effect Coats					●	●	○
Smart / Spot Repair							○



TIPS:

- ✓ Store 3M™ Performance Spray Gun with a clean nozzle
- ✓ Change nozzles daily to maintain like-new performance
- ✓ Move up or down one size if material flow is too low or high
- ✓ Dispose in accordance with your local regulations

Part No.	Color	Size	Quantity
26709	White	0.9	5
26712	Blue	1.2	5
26713	Green	1.3	5
26714	Orange	1.4	5
26716	Purple	1.6	5
26718	Clear	1.8	5
26720	Red	2.0	5
26730	Variety Kit	6 sizes	6

Automotive Aftermarket Division
3M Center
Building 223-06S-07
St. Paul, MN 55144-1000
1-877-666-2277

For more information, visit us at
3M.com/spraygun