



ID: 1324602
RID: 2157890

Hearing Protection

Hearing protection must be right for you and your situation. For safety, productivity and comfort, it must reduce noise by the right amount, not too little and not too much. 3M can provide solutions for different individuals and applications with a wide range of earmuffs and earplugs.

#3MScienceOfSafety

The solution, protection and validation.

As a global leader in hearing protection and fit test validation, 3M delivers easy and comprehensive solutions to complex hearing protection challenges.

Ears come in a variety of sizes and shapes, and noise levels on the job vary depending on the work that is being done. Hearing protection solutions by 3M offer a wide range of shapes and sizes to fit workers' ears comfortably while offering protection for a wide range of noise levels.

Noise Detection

The first step in solving the hearing protection challenge is to measure the noise levels facing your workers, so you can select the appropriate hearing protection for the application.

Adaptable Hearing Protection

3M delivers a wide range of innovative hearing protectors, making it easy to select the right solution for the job. A variety of types and sizes of earplugs and earmuffs are available helping your team determine the right fit for each person and the right protection for the application. Our innovative products are designed for comfortable, extended wear, and they can help your team comply with your safety program.

Fit Test Validation

Integrating hearing protector fit testing into your hearing conservation program benefits everyone from new hires to high-risk workers. The 3M™ E-A-Rfit™ Validation System makes it easier to fit, train and motivate workers and to assess and manage the long-term performance of your hearing conservation program.

3M's broad range of hearing protection devices in a variety of types and styles helps you solve many of the challenges facing workers in various environments.

You can advance your hearing conservation programme with a customised and comprehensive approach to the hearing protection challenge. Implementing a solution that really makes a difference, begins with understanding the hazards, the regulation and the factors that impact protection.

Understanding sound level conversion (SLC₈₀).

An SLC₈₀ rating is determined based on how well the hearing protector performed in a laboratory. However, each hearing protector's SLC₈₀ is not always a good estimate for workplace noise reduction. Many factors, such as the relationship between the size of the wearer and size of the hearing protector, and how it has been inserted or fitted, can impact how effective that hearing protector will be. That's why it is so important to have the 3M™ E-A-Rfit™ Dual-Ear Validation System as part of your hearing conservation program and the support of a hearing protection team with over 40 years of expertise.

At 3M, we understand the challenges of the workplace, the complexities of fitting protection devices, and the importance of creating adaptable solutions for maximising hearing protection. Our innovations in noise protection and validation are designed to solve real-world challenges, providing our customers with the advanced and comprehensive solutions needed to help protect workers.

When it comes to protecting workers' hearing there is no one-size fits all solution.



The first step is an accurate assessment of the sound level. The second step is choosing the right protection for the job, and the third is to use a validation system to verify that the protection being used is at the right level for the given environment.

All of this should be consistently supported by a strong educational effort around noise awareness, fitting guidance and other motivational elements.

3M delivers a complete set of tools to **Protect** and **Validate**. It's 3M hearing protection solutions made innovatively easy.



Detection: Detecting and monitoring noise exposure is the first step in identifying where hearing protection is needed.



Protection: Protecting hearing and enhancing communication require comfortable solutions with options that make it easy to select the right protection for each employee.



Validation: 3M recommends fit testing for hearing protection. Training on the proper use of protection and measurement of attenuation levels can help you validate that your employees are protected.



What types of sounds require hearing protection?

At home and work, it's important to understand which sounds may cause hearing loss and require hearing protection:

Home Scale Decibels (dBA)*

12-Gauge Shotgun	165 dB Peak
Basketball Game Crowd Noise	120
Chainsaw	110
Rock Concert	105
Motorcycle	100
Lawn Mower	90
Vacuum Cleaner	80
Mid-Sized Auto Interior	70
Conversation	60
Floor Fan	50
Refrigerator Hum	40
Rustling Leaves	30
Watch Ticking	20

Work Scale Decibels (dBA)*

Jet Takeoff	140
Pneumatic Riveter	124
Hammer Drill	114
Tractor / Hand Drill	97
Belt Sander	93
City Traffic	78
Air Conditioning Unit	60
Electrical Transformer	45

*Information from 3M™ Noise Navigator™ Sound Level Database
www.3M.com/hearing and National Institute for Occupational Safety and Health (NIOSH) www.cdc.gov/niosh/topics/noise/noisemeter.html



Science.
Applied to Life.™



ID: 2291657
RID: 1082238

Earplugs

Our 3M Earplug range provides great comfort, fit and good protection.
3M provides a wide range of earplug types to suit your individual needs.
From disposable, reusable, push-ins or banded types.

AU/NZ Passive Hearing Selection Guide - Earplugs

		SAP ID	Legacy ID	Availability		Model #	Item Description	Qty/Case	SLC ₉₀ dB	Class
				AUS	NZ					
Disposable		7000002301	70071514940	•		311-1101	3M™ E-A-R™ Classic™ Corded	2000 pairs	21	3
		7000002399	70071514916	•		310-1001	3M™ E-A-R™ Classic™ Uncorded , Pillow Pack 310-1001, SLC ₉₀ 23dB (Class 4), 200 Pairs/Box, 10 Boxes/Case,	2000 pairs	23	4
		7000002300	70071514932	•	•	312-1201	3M™ E-A-R™ Classic™ Uncorded Earplugs 312-1201, SLC ₉₀ 23dB (Class 4), Poly Bag, 2000 Pairs/case	2000 pairs		
		7000052882	70071562774	•	•	393-2003-50	3M™ E-A-Rfit™ Classic™ Probed Test Plugs, 393-2003-50	50 pairs		
		7100099847	AT01061512 (AU) HC000664637 (NZ)	•	•	1100	3M™ Foam Earplugs 1100 Uncorded, SLC ₉₀ 21dB (Class 3), 1000 Pair/Case	1000 pairs	21	3
		7100099848	AT01061514 (AU) HC000664934 (NZ)	•	•	1110	3M™ Foam Earplugs 1110, Corded, SLC ₉₀ 21dB (Class 3), Poly Bag, 500 Pair/Case	500 pairs		
		7000002409	7007157772	•	•	393-2010-50	3M™ 1100 EARfit Probed Test Plug	50 pairs		
		7010384010	70071515848	•	•	310-4002	3M™ E-A-R™ Classic™ Platinum™ Earplugs 310-4002, Uncorded, SLC ₉₀ 23dB (Class 4), Pillow Pack, 2000 Pair/Case	2000 pairs	23	4
		7010341665	70071515871	•		310-4003	3M™ E-A-R™ Classic™ Platinum™ Earplugs 310-4003, Uncorded, SLC ₉₀ 23dB (Class 4), Poly Bag, 2000 Pair/Case	2000 pairs		
		7000052884	70071562816	•	•	393-2007-50	3M™ E-A-R™ Classic™ Platinum (Small) EARfit Probed Test Plug	50 pairs		
		XA006483649	XA006483649	•	•	311-1250	3M™ Yellow Neons™ 2000 pair/Case Regular Corded			
		7000002303	XA006483656	•	•	312-1250	3M™ E-A-Rsoft™ Yellow Neons™ Uncorded Earplugs, Poly Bag 312-1250, 200 Pairs/Box, 10 Boxes/Case, SLC 80 23dB (Class 4)	2000 pairs	23	4
		7100006342	70071515152	•	•	311-1251	3M™ E-A-Rsoft™ Yellow Neons™ Large Corded Earplugs, Poly Bag, 311-1251, 200 Pair/Box, 10 Boxes/Case, SLC 80 23dB (Class 4)	2000 pairs		
		7000127175	70071515053	•	•	312-1251	3M™ E-A-Rsoft™ Yellow Neons™ Large Uncorded Earplugs 312-1251, SLC ₉₀ 23dB (Class 4), Poly Bag, 200 Pairs/Box, 10 Boxes/Case,	2000 pairs		
		7100069736	70071562741	•	•	393-2000-50	3M™ E-A-Rfit™ E-A-Rsoft™ Yellow Neons™ Probed Test Plug, 393-2000-50, 50 ea/Case	50 pairs		
		7000148551	70071650249	•	•	393-2014-50	3M™ E-A-Rsoft™ Yellow Neons™ EARfit Probed Test Plug - Large	50 pairs	24	4
		7000002307	70071515145	•		311-1254	3M™ E-A-Rsoft™ SuperFit™ Corded Earplugs, 311-1254, SLC ₉₀ 24dB (Class 4), Poly Bag, 200 Pair/Box, 10 Boxes/Case	2000 pairs		
		7010315041	70071515061	•		312-1255	3M™ E-A-Rsoft™ SuperFit™ Earplugs 312-1255, SLC ₉₀ 24dB (Class 4), Uncorded, Poly Bag, Large , 2000 Pair/Case	2000 pairs		
		7000052720	70071515038	•		312-1256	3M™ E-A-Rsoft™ SuperFit™ Uncorded Earplugs 312-1256, SLC ₉₀ 24dB (Class 4), Poly Bag, 200 Pair/Box, 10 Boxes/Case	2000 pairs		
		7100069736	70071562741	•		393-2000-50	3M™ E-A-Rsoft™ Yellow Neons™ EARfit Probed Test Plug - Regular	50 pairs	26	5
		7000148551	70071650249	•		393-2014-50	3M™ E-A-Rsoft™ Yellow Neons™ EARfit Probed Test Plug - Large	50 pairs		
		7000127177	70071515137	•	•	312-1260	3M™ E-A-Rsoft™ FX™ Corded Earplugs 312-1260, SLC ₉₀ 26dB (Class 5), Poly Bag, 200 Pairs/Box, 10 Boxes/Case,	2000 pairs		
		7000029951	70071515046	•	•	312-1261	3M™ E-A-Rsoft™ FX™ Uncorded Earplugs 312-1261, SLC ₉₀ 26dB (Class 5), Poly Bag, 2000 Pair/Case	2000 pairs		
Push-to-Fit		70071516002	70071516002	•	•	321-2115	3M™ E-A-R™ Express™ Earplugs 321-2115, Assorted Grip, 321-2115, SLC ₉₀ 19dB (Class 3), 100 Pairs/Box, 4 Boxes/Case	400 pairs	19	3
		7010384013	70071515178	•		321-2200	3M™ E-A-R™ Express™ Pod Plugs™ Uncorded Earplugs, Assorted Color Grips, 321-2200, SLC ₉₀ 19dB (Class 3), Pillow Pack, 400 Pair/Case	400 pairs		
		7000052879	70071562725	•	•	393-2008-50	3M™ E-A-R™ Express™ PodPlugs™ EARfit Probed Test Plug	50 pairs		
		7000127185	70071520939	•		318-1000	3M™ E-A-R™ Push-Ins™ Uncorded Earplugs, 318-1002, SLC ₉₀ 23dB (Class 4), Poly Bag, 200 Pairs/Box, 10 Boxes/Case	2000 pairs	23	4
		7000052723	70071520947	•	•	318-1001	3M™ E-A-R™ Push-Ins™ Corded Earplugs, 318-1001, SLC ₉₀ 23dB (Class 4), Poly Bag, 200 Pairs/Box, 10 Boxes/Case,	2000 pairs		
		7000052881	70071562766	•	•	393-2002-50	3M™ E-A-Rfit™ E-A-R™ Push-Ins™ Probed Test Plug, 393-2002-50	50 pairs		
		7000127182	70071515640	•	•	P1300	3M™ Skull Screws™ Earplug Uncorded, P1300, SLC ₉₀ 26dB (Class 5), Poly Bag , 120 Pairs/Box, 4 Boxes/Case	480 pairs	26	5
		7000127181	70071515632	•	•	P1301	3M™ Skull Screws™ Earplug Corded, P1301, SLC ₉₀ 26dB (Class 5), Poly Bag , 120 Pairs/Box, 4 Boxes/Case	480 pairs		
		7000128264	70071647757 (AU) NT019317808 (NZ)	•	•	393-2012-50	3M™ E-A-Rfit™ Skull Screws™ Probed Test Plugs 393-2012-50	50 pairs		
		7000127180	70071515624	•	•	P2000	3M™ No-Touch™ Uncorded Earplugs, P2000, SLC ₉₀ 25dB (Class 4), Poly Bag, 400 Pairs/Case, 100 Pairs/Box	400 pairs	25	4
		7000052722	70071515616	•	•	P2001	3M™ No-Touch™ Corded Earplugs, P2001, SLC ₉₀ 25dB (Class 4), Poly Bag, 400 Pairs/Case, 100 Pairs/Box	400 pairs		
		7100033339	70071650231	•	•	393-2013-50	3M™ No Touch™ Probed Test Plugs 393-2013-50, 50 Pairs/Case	50 pairs		
		7000127672	70071561487	•		P1400	3M™ Pistonz™ Uncorded Earplugs, P1400, SLC ₉₀ 25dB (Class 4), Poly Bag , 400 Pairs/Case, 100 Pairs/Box	400 pairs	25	4
		7000127673	70071561495	•		P1401	3M™ Pistonz™ Corded Earplugs, P1401, SLC ₉₀ 25dB (Class 4), Poly Bag, 400 Pairs/Case, 100 Pairs/Box	400 pairs		
Reusable		7000002321	70071515780	•		340-4003	3M™ E-A-R™ UltraFit™ Uncorded Earplugs, 340-4003, SLC ₉₀ 18dB (Class 3), Poly Bag, 400 Pair/Case, 50 Pairs/Box, 4 Boxes/Case	200 pairs	18	3
		7000002322	70071515798	•	•	340-4002	3M™ E-A-R™ UltraFit™ Corded Earplugs, Carry Case, 340-4002, 400 Pair/Case, 50 Pairs/Box, 4 Boxes/Case	200 pairs		
		7000002320	70071515772	•	•	340-4004	3M™ E-A-R™ UltraFit™ Corded Earplugs, 340-4004, SLC ₉₀ 18dB (Class 3), Poly Bag, 400 Pair/Case, 50 Pairs/Box, 4 Boxes/Case	400 pairs		
		7000002387	70071562758	•	•	393-2001-50	3M™ E-A-R™ UltraFit™ EARfit Probed Test Plug	50 pairs		
		7011392438	HC000664785			1291	3M™ Reusable Ear Plugs Corded with Case, Cloth, 1291		19	3
		7100100654	HC000664777			1290	3M™ Reusable Ear Plugs Corded, Cloth, 1290			
		7010386152	70071675626		•	393-2024-50	393-2024-50 1290 Reusable Probed 50 PR/CS			
		7000127187	70071515723	•	•	P3000	3M™ Tri-Flange™ Corded Earplugs P3000, SLC ₉₀ 19dB (Class 3), 400 Pairs/Case, 100 Pairs/Box	400 pairs		
Metal Detectable		7000002319	70071515749	•	•	340-4007	3M™ E-A-R™ Ultrafit™ Metal Detectable Corded Earplug, 340-4007, SLC ₉₀ 18dB (Class 3), Poly Bag , 100 Pairs/Box, 4 Boxes /Case, 400 Pairs/Case	400 pairs	18	3
		7000002387	70071562758	•	•	393-2001-50	3M™ E-A-R™ UltraFit™ EARfit Probed test Plug	50 pairs		
		7000029952	70071515103	•	•	311-4106	3M™ E-A-Rsoft™ Metal Detectable Corded Earplugs, 311-4106, SLC ₉₀ 18dB (Class 3), Poly Bag, 200 Pairs/Box, 10 Boxes/Case, 2000Pairs/Case	2000 pairs	23	4
		7100069736	70071562741	•	•	393-2000-50	3M™ E-A-Rfit™ E-A-Rsoft™ Yellow Neons™ Probed Test Plug, 393-2000-50, 50 ea/Case	50 pairs		

3M Earplugs are available corded, uncorded or both depending on the model.

AU/NZ Passive Hearing Selection Guide - Earmuffs

		SAP ID	Legacy ID	Availability		Model #	Item Description	Qty/Case	SLC ₉₀ dB	Class
Banded		7100089592	AT010561135 (AU) UU004902688 (NZ)	•	•	1310	3M™ Banded Earplugs 1310, SLC ₉₀ 50 EA/Case - When worn behind the neck.	50 pairs	13	1
		7100089592	AT010561135 (AU) UU004902688 (NZ)	•	•	1310	3M™ Banded Earplugs 1310, 50 ea/Case - When worn under the chin		18	3
		7100100262	HC000664835	•	•	1311	3M™ 1311 Replacement Pod	20 pairs/box		
One Touch		7000103721	XA007701783	•	•	1100-BT	3M™ 1100-BT Earplug Refill Bottle, SLC ₉₀ 21dB (Class 3), 500 Pair/Bottle, 4 Bottles/Case, 2000 Pair/Case	500 pair/bottle 4 x bottles/case	21	3
		7000002298	70071514882	•		391-1001	3M™ E-A-R™ Classic™ One Touch™ Refill, 391-1001, SLC ₉₀ 23dB (Class 4), 500 Pair/Bottle, 4 Bottles/Case, 2000 Pair/Case	500 pair/bottle 4 x bottles/case	23	4
		7000002305	XA006483961 (AU) 70071515087 (NZ)	•	•	391-1004	3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill, Uncorded Earplugs 391-1004, SLC ₉₀ 23dB (Class 4), 500 Pair/Bottle, 4 Bottles/Case, 2000 Pair/Case	500 pair/bottle 4 x bottles/case		
		7100001858	70071521309	•		391-1005	3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill Earplugs 391-1008, SLC ₉₀ 23dB (Class 4), Large Uncorded, 1600 Pair/Case	500 pair/bottle 4 x bottles/case		
		7000042881	70071515095	•		391-1254	3M™ E-A-Rsoft™ SuperFit™ One Touch™ Refill, Uncorded Earplugs 391-1254			
		7100088422	70071674751	•	•	391-1012	3M™ E-A-Rsoft™ FX™ Dispenser Bottle Refill 391-1012, SLC ₉₀ 26dB (Class 5), 500 Pair/Bottle, 4 Bottles/Case, 2000 Pair/Case	500 pair/bottle 4 x bottles/case	26	5
		7100064963	70071674207	•	•	391-0000	3M™ One Touch™ Pro Earplug Dispenser 391-0000, Bundle with E-A-Rsoft™ One Touch™ Yellow Neons™ Refill Bottle, 500 pairs, 1 ea/Case	1		
PELTOR Earmuffs		7100315066	XA007707947	•	•	X4A	3M™ PELTOR™ X Series Headband Earmuff X4A, SLC ₉₀ 31dB (Class 5), 10 EA/Case	10	32	5
		7100314406	UU010818886	•	•	X4P3GS/E	3M™ PELTOR™ X Series Earmuff X4P3GS/E, Helmet Mounted, Light Green, SLC ₉₀ 27dB (Class 5), 10 EA/Case	10	28	
		7000104048	XA007707608	•	•	HYX4	3M™ PELTOR™ X Series XY4 Hygiene kit, 10 Kits/Case	10		
		7100062128	70071691136	•	•	393-3005-2	3M™ PELTOR™ X4/X5 Earmuff Probed Test Cushions 393-3005-2, 2 EA/Kit	2 Pairs		5
		7100315065	XA007707954	•	•	X5A	3M™ PELTOR™ X Series Headband Earmuff X5A, SLC ₉₀ 35dB (Class 5), 10 EA/Case	10	34	
		7100315069	UU010818878	•	•	X5P3GS/E	3M™ PELTOR™ X Series Earmuff X5P3GS/E, Helmet Mounted, Black, SLC ₉₀ 31 dB (Class 5), 10 EA/Case	10	33	
		7000104049	XA007707616	•	•	HYX5	3M™ PELTOR™ X Series HYX5 Hygiene kit, 10 Kits/Case	10		
		7100062128	70071691136	•	•	393-3005-2	3M™ PELTOR™ X4/X5 Earmuff Probed Test Cushions 393-3005-2, 2 EA/Kit	2 Pairs		5
		7100242340	70071730454	•	•	H510A	3M™ PELTOR™ Optime™ I Headband Format Earmuff H510A, Yellow, SLC ₉₀ 28dB (Class 5), 10 ea/Case	10	28	
		7100242342	70071730504	•	•	H510F	3M™ PELTOR™ Optime™ I Foldable Earmuff H510F, Yellow, SLC ₉₀ 28dB (Class 5), 10 EA/Case	10	28	
		7100242339	70071730421	•	•	H510B	3M™ PELTOR™ Optime™ I Neckband Format Earmuff H510B, Yellow, SLC ₉₀ 25dB (Class 4), 10 ea/Case	10	25	4
		7100242341	70071730496	•	•	H510P3GS/E	3M™ PELTOR™ Optime™ I Helmet Attach Earmuff H510P3GS/E, Yellow, SLC ₉₀ 26dB (Class 5), 10 ea/Case	10	26	5
		7000104045	XA007707574	•	•	HYX1	3M™ PELTOR™ X1 Hygiene Kit HYX1/37280(AAD), for X1 Earmuffs, 10 Kits/Case	10		5
		7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions 393-3001-2, 2 ea/Kit	2 Pairs		
		7100242344	70071730553	•	•	H520A	3M™ PELTOR™ Optime™ II Headband Earmuff H520A, Green, SLC ₉₀ 32dB (Class 5), 10 EA/Case	10	32	
		7100242347	70071730538	•	•	H520F	3M™ PELTOR™ Optime™ II Foldable Headband Earmuff H520F, Green, SLC ₉₀ 32dB (Class 5), 10 EA/Case	10	32	5
		7100242345	70071730579	•	•	H520FHV	3M™ PELTOR™ Optime™ II Foldable Headband Earmuff H520FHV, Bright Yellow, SLC ₉₀ 32dB (Class 5), 10 EA/Case	10	32	
		7100242087	70071730546	•	•	H520B	3M™ PELTOR™ Optime™ II Neckband Earmuff H520B, Green, SLC ₉₀ 27dB (Class 5), 10 EA/Case	10	27	
		7100242343	70071730520	•	•	H520P3GS/E	3M™ PELTOR™ Optime™ II Helmet Attach Earmuff H520P3GS/E, Green, SLC ₉₀ 29dB (Class 5), 10 EA/Case	10	29	5
		7000104046	XA007707582	•	•	HYX2	3M™ PELTOR™ X2 Hygiene Kit HYX2/37281(AAD), for X2 Earmuffs, 10 Kits/Case	10		
7100062126		70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions 393-3001-2, 2 ea/Kit	2 Pairs			
	7100242353	70071730603	•	•	H540A	3M™ PELTOR™ Optime™ III Headband Format Earmuff H540A, Black and Red, SLC ₉₀ 33dB (Class 5), 10 ea/Case	10	33	5	
	7100242346	70071730629	•	•	H540AHV	3M™ PELTOR™ Optime™ III Headband Earmuff H540AHV, Bright Yellow, SLC ₉₀ 33dB (Class 5), 10 EA/Case	10	33		
	7100242352	70071730595	•	•	H540B	3M™ PELTOR™ Optime™ III Neckband Format Earmuff H540B, Black and Red, SLC ₉₀ 34dB (Class 5), 10 ea/Case	10	34		
	7100242351	70071730587	•	•	H540P3GS/E	3M™ PELTOR™ Optime™ III Helmet Attach Earmuff H540P3GS/E, Black and Red, SLC ₉₀ 30dB (Class 5), 10 ea/Case	10	30	5	
	7000108016	XH001659362	•	•	HY54	3M™ PELTOR™ Earmuff Replacement Hygiene Kit HY54, OPTIME III/H10 Series	20			
	7100123728	70071676285	•	•	393-3004-2	3M™ PELTOR™ Probed Earmuff Test Cushion 393-3004-2, #35, 2 Pair/Case. Test Cushion A	2 Pairs			
	7000103787	XA007703797	•	•	H505B	3M™ PELTOR™ Welders Earmuff H505B-596-SV, SLC ₉₀ 22dB (Class 4), 10 EA/Case	10	22	4	
	7100101874	UU008049353	•	•	HY220	3M™ PELTOR™ Earmuff Hygiene Kit HY220, 1 ea/Bag	20			

Disposable Earplugs.

3M Disposable Earplugs, made from expandable slow-recovery foam, help provide a great combination of comfort and hearing protection for users. Once in the ear, foam earplugs expand to conform to the unique shape of each ear canal. 3M provides a wide range of disposable roll-down earplugs so you can choose the best solution for your individual needs.

3M™ E-A-R™ Classic™ Earplugs

3M™ E-A-R™ Classic™ earplugs meets more wearer and environmental needs with its proprietary foams, preferred cylindrical shape, and proven in-ear comfort.

Testable with the
3M™ E-A-Rfit™
Validation System



Certified Product



AS/NZS 1270
Lic. SMK1147





QR-HP-01

Scan or Click for
Tech Data Sheet

Features and Benefits:

- Moisture Resistant
- Slow-Recovery Foam
- Testable with the 3M™ E-A-Rfit™ Validation System
- Uncorded - SLC₈₀ 23dB (Class 4)
- Corded - SLC₈₀ 21dB (Class 3)
- 200 pairs/box, 10 boxes/case
- 2000 pairs/case
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000002301	70071514940	•		311-1101	3M™ E-A-R™ Classic™ Corded Earplugs 311-1101, SLC ₈₀ 21dB (Class 3), Poly Bag, 200 Pairs/Box, 10 Boxes/Case,
7000002299	70071514916	•		310-1001	3M™ E-A-R™ Classic™ Uncorded , Pillow Pack 310-1001, 200 Pairs/Box, 10 Boxes/Case, SLC ₈₀ 23dB (Class 4)
7000002300	70071514932	•	•	312-1201	3M™ E-A-R™ Classic™ Uncorded Earplugs 312-1201, Poly Bag, 2000 pairs/case
7000052882	70071562774	•	•	393-2003-50	3M™ E-A-Rfit™ Classic™ Probed Test Plugs 393-2003-50
7000002298	70071514882	•		391-1001	3M™ E-A-R™ Classic™ One Touch™ Refill 391-1001, 2000 EA/Case


Earplugs

3M™ 1100 & 1110 Earplugs

- Available with Cord
- Testable with the 3M™ E-A-Rfit™ Validation System
- SLC₈₀ 21dB (Class 3)
- Complies with Australian/ New Zealand Standard AS/ NZS 1270:2002.



393-2010-50



1100



1110

Testable with the
3M™ E-A-Rfit™
Validation System




QR-HP-02

Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100099847	AT010615121 (AU) HC000664637 (NZ)	•	•	1100	3M™ Foam Earplugs 1100 Uncorded, SLC ₈₀ 21dB (Class 3), 1000 Pair/Case
7100099848	AT010615154 (AU) HC000664934 (NZ)	•	•	1110	3M™ Foam Earplugs 1110, Corded, SLC ₈₀ 21dB (Class 3), Poly Bag, 500 Pair/Case
7000002409	70071577772	•	•	393-2010-50	3M™ E-A-Rfit™1100 Probed Test Plugs, 393-2010-50
7000103721	XA007701783	•	•	1100-BT	3M™ 1100-BT Earplug Refill Bottle, SLC ₈₀ 21dB (Class 3), 500 Pair/Bottle, 4 Bottles/Case, 2000 Pair/Case

3M™ E-A-R™ Classic™ Platinum™ (Small) Earplugs

- 7% Smaller than Classic
- Moisture Resistant
- Slow-Recovery Foam
- Testable with the 3M™ E-A-Rfit™ Validation System
- SLC₈₀ 23dB (Class 4)
- 200 pairs/box, 10 boxes/case
- 2000 pairs/case
- Complies with Australian/ New Zealand Standard AS/NZS 1270:2002.



310-4002



393-2007-50



310-4003

Testable with the
3M™ E-A-Rfit™
Validation System



QR-HP-03

Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7010384010	70071515848	•	•	310-4002	3M™ E-A-R™ Classic™ Platinum™ Earplugs 310-4002, Uncorded, Pillow Pack, SLC 80 23dB (Class 4), 2000 Pair/Case
7010341665	70071515871	•	•	310-4003	3M™ E-A-R™ Classic™ Platinum™ Earplugs 310-4003, Uncorded, Poly Bag, 2000 Pair/Case
7000052884	70071562816	•	•	393-2007-50	3M™ E-A-Rfit™ Classic™ Platinum™ Probed Test Plugs 393-2007-50




AS/NZS 1270
Lic. SMK1147

Earplugs

3M™ E-A-R™ E-A-Rsoft™ Yellow Neons™ Earplugs

- Slow-Recovery Foam
- Two sizes available
- Testable with the 3M™ E-A-Rfit™ Validation System
- SLC₈₀ 23dB (Class 4)
- 200 pairs/box, 10 boxes/case
- 2000 pairs/case
- Complies with Australian/ New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System



Scan or Click for
Tech Data Sheet



AS/NZS 1270
Lic. SMK1147

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
XA006483649	7100330558	•	•	311-1250	3M™ E-A-Rsoft™ Yellow Neons™ Earplug 311-1250, Corded, Poly Bag, Regular Size, 2000 Pair/Case (replaced 7000002306, 70071515129 3M™ E-A-Rsoft™ Yellow Neons™ Earplugs 311-1250, Corded, Poly Bag, Regular Size, 2000 Pair/Case * for NZ only)
7100330559	XA006483656	•	•	312-1250	3M™ E-A-Rsoft™ Yellow Neons™ Regular Uncorded Earplugs 312-1250, SLC ₈₀ 23dB (Class 4), Poly Bag, 200 Pairs/Box, 10 Boxes/Case (replaced 7000002303, 70071515020 3M™ E-A-Rsoft™ Yellow Neons™ Earplugs 312-1250, Uncorded, Poly Bag, 2000 Pair/Case)
7100006342	70071515152	•	•	311-1251	3M™ E-A-Rsoft™ Yellow Neons™ Large Corded Earplugs 311-1251, SLC ₈₀ 23dB (Class 4), Poly Bag, 200 Pair/Box, 10 Boxes/Case
7000127175	70071515053	•	•	312-1251	3M™ E-A-Rsoft™ Yellow Neons™ Large Uncorded Earplugs, Poly Bag, 312-1251, 200 Pairs/Box, 10 Boxes/Case, SLC ₈₀ 23dB (Class 4)
7100069736	70071562741	•	•	393-2000-50	3M™ E-A-Rfit™ E-A-Rsoft™ Yellow Neons™ Probed Test Plug 393-2000-50
7000148551	70071650249	•	•	393-2014-50	3M™ E-A-Rfit™ E-A-R™ Yellow Neon™ Large Test Plug 393-2014-50, 50 Pairs/Case
7100336038	XA006483961	•	•	391-1004	3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill Earplugs 391-1004, Uncorded, Regular Size, 2000 Pair/Case (replaced 7000002305)
7100001858	70071521309	•	•	391-1005	3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill Earplugs 391-1008, SLC ₈₀ 23dB (Class 4), Large Uncorded, 1600 Pair/Case

3M™ E-A-Rsoft™ SuperFit™ Earplugs

- Available with Cord
- Two sizes available
- Slow-Recovery Foam
- E-A-Rfit Testable
- SLC₈₀ 24dB (Class 4)
- 2000 pairs/case
- 200 pairs/box
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System



AS/NZS 1270
Lic. SMK1147




Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000002307	70071515145	•	•	311-1254	3M™ E-A-Rsoft™ SuperFit™ Corded Earplugs, 311-1254, SLC ₈₀ 24dB (Class 4), Poly Bag, 200 Pair/Box, 10 Boxes/Case
7010315041	70071515061	•	•	312-1255	3M™ E-A-Rsoft™ Superfit™ Earplugs 312-1255, SLC ₈₀ 24dB (Class 4), Uncorded, Poly Bag, Large, 2000 Pair/Case
7000052720	70071515038	•	•	312-1256	3M™ E-A-Rsoft™ SuperFit™ Uncorded Earplugs 312-1256, SLC ₈₀ 24dB (Class 4), Poly Bag, 200 Pair/Box, 10 Boxes/Case
7000042881	70071515095	•	•	391-1254	3M™ E-A-Rsoft™ SuperFit™ One Touch™ Refill, Uncorded Earplugs 391-1254
7100069736	70071562741	•	•	393-2000-50	3M™ E-A-Rfit™ E-A-Rsoft™ Yellow Neons™ Probed Test Plug 393-2000-50
7000148551	70071650249	•	•	393-2014-50	3M™ E-A-Rfit™ E-A-R™ Yellow Neon™ Large Test Plug 393-2014-50, 50 Pairs/Case

Earplugs

3M™ E-A-Rsoft™ FX™ Earplugs

- Available with Cord
- Slow-Recovery Foam
- Easy removal (bell shape)
- Testable with the 3M™ E-A-Rfit™ Validation System
- SLC₈₀ 26dB (Class 5)
- 200 pairs/box, 10 boxes/case
- 2000 pairs/case
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System



Scan or Click for
Tech Data Sheet




AS/NZS 1270
Lic. SMK1147

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000127177	70071515137	•	•	312-1260	3M™ E-A-Rsoft™ FX™ Corded Earplugs 312-1260, SLC ₈₀ 26dB (Class 5), Poly Bag, 200 Pairs/Box, 10 Boxes/Case
7000029951	70071515046	•	•	312-1261	3M™ E-A-Rsoft™ FX™ Uncorded Earplugs 312-1261, SLC ₈₀ 26dB (Class 5), Poly Bag, 2000 Pair/Case
7000052883	70071562782	•	•	393-2004-50	3M™ E-A-Rfit™ E-A-Rsoft™ FX™ Probed Test Plugs 393-2004-50
7100088422	70071674751	•	•	391-1012	3M™ E-A-Rsoft™ FX™ Dispenser Bottle Refill 391-1012, 4 Bottles/Case

3M™ E-A-R™ Taperfit™ 2 Earplugs

- Available with Cord
- Slow-Recovery Foam
- Testable with the 3M™ E-A-Rfit™ Validation System
- SLC₈₀ 26dB (Class 5)
- 200 pairs/box, 10 boxes/case
- 2000 pairs/case
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System



Scan or Click for
Tech Data Sheet



AS/NZS 1270
Lic. SMK1147

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000002310	70071515228	•		312-1219	3M™ E-A-R™ TaperFit™ 2 Regular Uncorded Earplugs 312-1219, SLC ₈₀ 26dB (Class 5), Poly Bag, 2000 Pairs/Case
7000002311	70071515236	•	•	312-1221	3M™ E-A-R™ TaperFit™ 2 Large Uncorded Earplugs 312-1221, SLC ₈₀ 26dB (Class 5), Poly Bag, 200 Pairs/Box, 10 Boxes/Case, 2000 Pair/Case
7000002313	70071515251	•		312-1224	3M™ E-A-R™ TaperFit™ 2 Large Corded Earplugs 312-1224, SLC ₈₀ 26dB (Class 5), Poly Bag, 2000 Pairs/Case
7000002388	70071562808	•		393-2006-50	3M™ E-A-Rfit™ TaperFit™ 2 Probed Test Plugs, 393-2006-50, 50 ea/Case
7100230133	70071733557	•	•	393-2027-50	3M™ E-A-R™ TaperFit™ 2 Large Probed Test Plugs 393-2027-50, 50 Pair/Case

Push-to-Fit Earplugs.

Simply hold 3M™ Push-to-Fit Earplugs by the stem then push them into place — there is no roll-down required. The soft foam tip quickly adjusts to the shape of the ear to help create a noise-reducing seal. Since you don't touch the foam tip, they are easy to insert and keep clean, even when your hands are dirty or you are wearing gloves.

3M™ E-A-R™ EXPRESS™ Pod Plugs™ Earplugs

- Available with Cord
- Testable with the 3M™ E-A-Rfit™ Validation System
- No Roll-Down Required
- SLC₉₀ 19dB (Class 3)
- 100 pairs/box, 4 boxes/Case, UOM Case
- 400 pairs/case
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System



QR-HP-08

Scan or Click for
Tech Data Sheet



AS/NZS 1270
Lic. SMK1147

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7010296628	70071516002	•	•	321-2115	3M™ E-A-R™ Express™ Pod Plugs™ Uncorded Earplugs, Assorted Color Grips, 321-2200, SLC ₉₀ 19dB (Class 3), Pillow Pack, 400 Pair/Case (replaced 7010384013, 70071516010 3M™ E-A-R™ Express™ Earplugs 321-3200, Assorted Grip, 400 Pair/Case)
7000002308	70071515178	•		321-2200	3M™ E-A-R™ EXPRESS™ Pod Plugs™ Earplugs 321-2200, Uncorded, Assorted Color Grips, Pillow Pack, 400 Pair/Case (replaced 7010384013 70071516010 3M™ E-A-R™ Express™ Earplugs 321-3200, Assorted Grip, 400 Pair/Case)
7000052879	70071562725	•	•	393-2008-50	3M™ E-A-Rfit™ E-A-R™ Express™ PodPlugs™ Probed Test Plugs 393-2008-50

3M™ E-A-R™ Push-Ins™ Earplugs

- Available with Cord
- E-A-Rform™ Foam Tip
- Testable with the 3M™ E-A-Rfit™ Validation System
- No Roll-Down Required
- SLC₉₀ 23dB (Class 4)
- 200 Pairs/box, 10 boxes/Case UOM Case
- 2000 pairs/case
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System



QR-HP-09

Scan or Click for
Tech Data Sheet



AS/NZS 1270
Lic. SMK1147

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000127213	70071520939	•		318-1000	3M™ E-A-R™ Push-Ins™ Uncorded Earplugs, 318-1000, SLC ₉₀ 23dB (Class 4), Poly Bag, 100/Box, 4 Box/Case (replaced 7000127185 70071515673 3M™ E-A-R™ Push-Ins™ Earplugs 318-1002, Uncorded, Poly Bag, 2000 Pair/Case)
7000052745	70071520947	•	•	318-1001	3M™ E-A-R™ Push-Ins™ Earplugs 318-1001, Corded, Poly Bag, 400 Pair/Case (replaced 7000052723 70071515707 3M™ E-A-R™ Push-Ins™ Earplugs 318-1003, Corded, Poly Bag, 2000 Pair/Case)
7000052881	70071562766	•	•	393-2002-50	3M™ E-A-Rfit™ E-A-R™ Push-Ins™ Probed Test Plug, 393-2002-50

Earplugs

3M™ Skull Screws™ Earplug

3M™ Skull Screws™ push-to fit foam earplugs offer convenience and noise attenuation with attitude. Soft foam helps with all day comfort. Grab the attention of your young workers with these radically designed earplugs and help boost hearing protection acceptance.

- Available with Cord
- Testable with the 3M™ E-A-Rfit™ Validation System
- No Roll-Down Required
- SLC₈₀ 26dB (Class 5)
- 120 pairs/box, 4 Boxes/Case UOM Case
- 480 pairs/case
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System



QR-HP-10

Scan or Click for
Tech Data Sheet



AS/NZS 1270
Lic. SMK1147

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000127182	70071515640	•	•	P1300	3M™ Skull Screws™ Earplug Uncorded, P1300, SLC ₈₀ 26dB (Class 5), Poly Bag , 120 Pairs/Box, 4 Boxes/Case
7000127181	70071515632	•	•	P1301	3M™ Skull Screws™ Earplug Corded, P1301, SLC ₈₀ 26dB (Class 5), Poly Bag , 120 Pairs/Box, 4 Boxes/Case
7000128264	70071647757	•	•	393-2012-50	3M™ E-A-Rfit™ Skull Screws™ Probed Test Plugs 393-2012-50

3M™ No-Touch™ Earplugs

- Available with Cord
- Testable with the 3M™ E-A-Rfit™ Validation System
- No Roll-Down Required
- SLC₈₀ 25dB (Class 4)
- 400 pairs/case
- 100 pairs/box
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System



AS/NZS 1270
Lic. SMK1147



QR-HP-11

Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000127180	70071515624	•	•	P2000	3M™ No-Touch™ Uncorded Earplugs, P2000, SLC ₈₀ 25dB (Class 4), Poly Bag, 400 Pairs/Case, 100 Pairs/Box
7000052722	70071515616	•	•	P2001	3M™ No-Touch™ Corded Earplugs, P2001, SLC ₈₀ 25dB (Class 4), Poly Bag, 400pairs/Case, 100 Pairs/Box
7100033339	70071650231	•	•	393-2013-50	3M™ No Touch™ Probed Test Plugs 393-2013-50, 50 Pairs/Case

3M™ Pistonz™ Earplugs

- Available with Cord
- No Roll-Down Required
- Flexible Stem
- SLC₈₀ 25dB (Class 4)
- 400 pairs/case
- 100 pairs/box
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



QR-HP-12

Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000127672	70071561487	•		P1400	3M™ Pistonz™ Uncorded Earplugs, P1400, SLC ₈₀ 25dB (Class 4), Poly Bag , 400 Pairs/Case, 100 Pairs/Box
7000127673	70071561495	•		P1401	3M™ Pistonz™ Corded Earplugs, P1401, SLC ₈₀ 25dB (Class 4), Poly Bag, 400 Pairs/Case, 100 Pairs/Box

Reusable Earplugs.

These durable, long-lasting earplugs are made from soft, flexible materials that are washable and reusable. The tapered tips are pre-molded for a wide range of ear sizes. Available in a variety of styles and protection levels.

3M™ E-A-R™ UltraFit™ Earplugs

A proven triple-flange design and pliable, premolded material make UltraFit earplugs a more comfortable fit for most ear canals. These durable, reusable earplugs are easy to use again and again, reducing waste. They can be cleaned easily with soap and water. Since there is no need to roll them down before fitting, simply push them into the ear canal for clean and comfortable noise reduction.

- Moisture Resistant
- Reusable, No Roll-Down
- Testable with the 3M™ E-A-Rfit™ Validation System
- SLC₈₀ 18dB (Class 3)
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the 3M™ E-A-Rfit™ Validation System



AS/NZS 1270
Lic. SMK1147



Scan or Click for Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000002321	70071515780	•		340-4003	3M™ E-A-R™ UltraFit™ Earplugs 340-4003, Uncorded, Poly Bag, 400 Pair/Case (replaced 70071521143 E-A-R™ UltraFit™ Earplugs 340-4001 200 Pair/Case) (replaced 70071521143 340-4001 E-A-R™ UltraFit™ Earplugs 200Pair/Case)
7000002322	70071515798	•	•	340-4002	3M™ E-A-R™ UltraFit™ Corded Earplugs, Carry Case, 340-4002, 400 Pair/Case, 50 Pairs/Box, 4 Boxes/Case
7000002320	70071515772	•	•	340-4004	3M™ E-A-R™ UltraFit™ Corded Earplugs, 340-4004, SLC ₈₀ 18dB (Class 3), Poly Bag, 400 Pair/Case, 50 Pairs/Box, 4 Boxes/Case
7000002387	70071562758	•	•	393-2001-50	3M™ E-A-Rfit™ E-A-R™ UltraFit™ Probed Test Plug 393-2001-50, 50 EA/Case

3M™ 1290/1291 Reusable Ear Plug

- Triple flanged design
- Soft elastomer for comfort
- Reusable, No Roll-Down
- Testable with the 3M™ E-A-Rfit™ Validation System
- 21dB (Class 3)
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the 3M™ E-A-Rfit™ Validation System




Scan or Click for Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7011392438	HC000664785		•	1291	3M™ Reusable Ear Plugs Corded with Case, Cloth, 1291
7100100654	HC000664777		•	1290	3M™ Reusable Ear Plugs Corded, Cloth, 1290
7010386152	70071675626		•	393-2024-50	393-2024-50 Reusable PRB 50 PR/CS

3M™ Tri-Flange™ Earplugs

- Moisture Resistant
- Reusable, No Roll-Down
- Vinyl cord
- Testable with the 3M™ E-A-Rfit™ Validation System
- SLC₈₀ 19dB (Class 3)
- 400 pairs/case
- 100 pairs/box
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the 3M™ E-A-Rfit™ Validation System



AS/NZS 1270
Lic. SMK1147



Scan or Click for Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000127187	70071515723	•	•	P3000	3M™ Tri-Flange™ Corded Earplugs P3000, SLC ₈₀ 19dB (Class 3), 400 Pairs/Case, 100 Pairs/Box
7000128263	70071647740	•	•	393-2011-50	3M™ E-A-Rfit™ Tri-Flange™ Probed Test Plugs 393-2011-50

Metal Detectable Earplugs.

All 3M™ Metal Detectable Earplugs contain metal components that are recognised by most metal-sensing systems. These earplugs feature an implanted stainless steel ball bearing in the plug and metal infused vinyl cord. Each earplug contains an embedded stainless steel ball bearing and a metal-infused vinyl cord, making them ideal for use in food manufacturing and pharmaceutical environments where contamination prevention is critical.

3M™ E-A-R™ Ultrafit™ Metal Detectable Earplugs

- Triple flange design
- Reusable, no Roll-down
- Implanted stainless steel ball and metal infused vinyl cord
- SLC₈₀ 18dB (Class 3)
- 100 pairs/box, 4 Boxes/Case, UOM Case
- 400 pairs/case
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System

Certified Product
AS/NZS 1270
Lic. SMK1147




Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000002319	70071515749	•	•	340-4007	3M™ E-A-R™ Ultrafit™ Metal Detectable Corded Earplug, 340-4007, SLC ₈₀ 18dB (Class 3), Poly Bag, 100 Pairs/Box, 4 Boxes /Case, 400 Pairs/Case
7000002387	70071562758	•	•	393-2001-50	3M™ E-A-Rfit™ E-A-R™ UltraFit™ Probed Test Plug 393-2001-50

3M™ E-A-Rsoft™ Yellow Neon™ Metal Detectable Earplugs

3M™ E-A-Rsoft™ Yellow Neon Metal Detectable earplugs were specially developed for food processing and other industries where it is critical to keep earplugs from contaminating products and processes.

- Slow recovery foam
- Implanted stainless steel ball and metal infused vinyl cord
- SLC₈₀ 23dB (Class 4)
- 200 pairs/box, 10 Boxes/Case UOM Case
- Corded - 2000 pairs/case
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Testable with the
3M™ E-A-Rfit™
Validation System

Certified Product
AS/NZS 1270
Lic. SMK1147



Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000029952	70071515103	•	•	311-4106	3M™ E-A-Rsoft™ Metal Detectable Corded Earplugs, 311-4106, SLC ₈₀ 23dB (Class 4), Poly Bag, 200 Pairs/Box, 10 Boxes/Case, 2000 Pairs/Case
7100069736	70071562741	•	•	393-2000-50	3M™ E-A-Rfit™ E-A-Rsoft™ Yellow Neons™ Probed Test Plug 393-2000-50

Banded Hearing Protector.

Banded hearing protectors are an easy-to-use, convenient alternative to earplugs and earmuffs. They are quick to put on and take off and may be stored around the neck in between uses, making them excellent for intermittent use.

3M™ 1310 Banded Series

- Replacement Tips Available
- Flexible Band
- Round Foam Tips
- 50 bands/case
- When Worn Under the Chin = SLC₈₀ 18 dB (Class 3)
- When Worn Behind the Neck = SLC₈₀ 13 dB (Class 1)
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100089592	AT010561135	•	•	1310	3M™ Banded Earplugs 1310, SLC ₈₀ 50 EA/Case
7100100262	H0001861683	•	•	1311	3M™ Banded Replacement Pods 1311, 100 Pair/Case

Earplugs

3M™ E-A-R™ One Touch™ Earplug Dispensers

3M™ One Touch™ Pro Earplug Dispenser gives workers convenient access to hearing protection products. A "No-Waste Funnel" accurately delivers earplugs with a slight turn. It typically dispenses a single earplug with each turn, giving the worker more control with less chance of spillage and waste of earplugs.

Features and Benefits:

- Makes it easy for workers to get the earplugs they need on the job. The dispenser holds 400-500 pairs of earplugs that are dispensed one at a time with a simple turning motion. Because the dispensing of earplugs is controlled, there should be little waste
- Our dispenser also makes it more sanitary for workers to get their earplugs as it eliminates the practice of workers reaching into a bin and touching multiple earplugs.
- The 3M One Touch Pro Earplug dispenser may be placed on flat, level surfaces such as countertops, or wall mounted in a convenient place. For wall mounting applications, a powder-coated steel backplate is included
- Accurately dispenses one earplug at a time
- Dispenses earplug directly into hand
- Durable ABS plastic for tough environments
- Can be free-standing or wall-mounted
- Shields earplugs from wind and rain
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



QR-HP-19

Scan or Click for
Tech Data Sheet



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000103721	XA007701783	•	•	1100-BT	3M™ 1100-BT Earplug Refill Bottle, SLC ₈₀ 21dB (Class 3), 500 Pair/Bottle, 4 Bottles/Case, 2000 Pair/Case
7000002298	70071514882	•		391-1001	3M™ E-A-R™ Classic™ One Touch™ Refill, 391-1001, SLC ₈₀ 23dB (Class 4), 500 Pair/Bottle, 4 Bottles/Case, 2000 Pair/Case
7100336038	XA006483961	•	•	391-1004	3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill, Uncorded Earplugs 391-1004, SLC ₈₀ 23dB (Class 4), 500 Pair/Bottle, 4 Bottles/Case (replaced 7000002305 70071515087 3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill Earplugs 391-1004, Uncorded, Regular Size, 2000 Pair/Case)
7100001858	70071521309	•		391-1005	3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill Earplugs 391-1008, SLC ₈₀ 23dB (Class 4), Large Uncorded, 1600 Pair/Case
7000042881	70071515095	•		391-1254	3M™ E-A-Rsoft™ SuperFit™ One Touch™ Refill, Uncorded Earplugs 391-1254
7100088422	70071674751	•	•	390-1012	3M™ E-A-Rsoft™ FX™ Dispenser Bottle Refill 391-1012, SLC ₈₀ 26dB (Class 5), 500 Pair/Bottle, 4 Bottles/Case, 2000 Pair/Case
7100064963	70071674207	•	•	391-0000	3M™ E-A-R™ One Touch™ Earplug Dispenser 391-0000

* Please Note: All 3M™ E-A-R™ One Touch Earplug Dispenser products are testable with the 3M™ E-A-Rfit™ Validation System



ID: 1824607
RID: 2157890

Earmuffs

The 3M™ PELTOR™ Earmuffs have been developed for demanding noisy environments and are effective in reducing even extremely low frequency sound. The result is an optimum seal with low contact pressure, which provides agreeable comfort even during long periods of use.

3M™ PELTOR™ X4 Series Earmuffs

Lightweight, low-profile earmuffs that help reduce exposure to hazardous levels of noise.

Historically higher attenuating earmuffs meant larger and bulky cups, but no longer. The 3M™ PELTOR™ Earmuffs X4 can attenuate by as much as 32dB whilst maintaining a sleek, low profile aesthetically pleasing design.

Testable with the
3M™ E-A-Rfit™
Validation System



QR-HP-20

Scan or Click for
Tech Data Sheet

Features and Benefits:

Comfort

- Easy to adjust headband
- Electrically insulated (dielectric) earmuffs available (X4A)
- Twin headband design helps reduce heat build-up and provides a good fit and balance
- Earcups tilt for optimum comfort and efficiency

Protection

- Unique attenuation as a result of optimum combination of specially-formulated foam featured in the earcups, cushions and the innovative spacer and cup design
- Designed spacer improves attenuation without excess bulk or weight
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.

Design

- Lightweight
- Integrated design for more robustness
- Easy to clean
- Slim design providing excellent compatibility with other 3M personal protection products

In the Box

- X4A - Headband Earmuffs + User Instructions on Box
- X4P3GS/E - Helmet Mounted Earmuffs with GS blade (25mm) on earmuff, and E blade (30mm) in box + User Instructions on Box.

NOTE: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100315066	XA007707947	•	•	X4A	3M™ PELTOR™ X Series Headband Earmuff X4A, SLC ₈₀ 32dB (Class 5), 10 EA/Case
7100314406	UU010818886	•	•	X4P3GS/E	3M™ PELTOR™ X Series Earmuff X4P3GS/E, Helmet Mounted, Light Green, SLC ₈₀ 28dB (Class 5), 10 EA/Case
7000104048	XA007707608	•	•	HYX4	3M™ PELTOR™ X Series Hygiene Kit XY4
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Case
7100383334	XL001642484	•	•	Z3G/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	ZGS/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062128	70071691136	•	•	393-3005-2	3M™ PELTOR™ X4/X5 Earmuff Probed Test Cushions D, 393-3005-2, 2 EA/Kit

Earmuffs

3M™ PELTOR™ X5 Series Earmuffs

The 3M™ PELTOR™ X5 remains relatively lightweight with excellent balance and wearer comfort despite the larger cups, providing ratings as high as SLC₈₀ 35dB. Testable with the 3M™ E-A-Rfit™ Validation System. Complies with Australian/New Zealand Standard AS/NZS 1270:2002.

In the Box:

- X5A - Headband Earmuffs + User Instructions on Box
- X5P3GS/E - Helmet Mounted Earmuffs with GS blade (25mm) on earmuff, and E blade (30mm) in box + User Instructions on Box.

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



X5A



X5P3GS/E



HYX5



393-3005-2

Testable with the
3M™ E-A-Rfit™
Validation System



QR-HP-21

Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100315065	XA007707954	•	•	X5A	3M™ PELTOR™ X Series Headband Earmuff X5A, SLC ₈₀ 35dB (Class 5), 10 EA/Case
7100315069	UU010818878	•	•	X5P3GS/E	3M™ PELTOR™ X Series Earmuff X5P3GS/E, Helmet Mounted, Black, SLC ₈₀ 31 dB (Class 5), 10 EA/Case
7000104049	XA007707616	•	•	HYX5	3M™ PELTOR™ X Series Hygiene Kit XY5
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Case
7100383334	XL001642484	•	•	Z3G/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	ZGS/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062128	70071691136	•	•	393-3005-2	3M™ PELTOR™ X4/X5 Earmuff Probed Test Cushions D, 393-3005-2, 2 EA/Kit

3M™ PELTOR™ Optime™ I Earmuffs

These products are designed to provide moderate level of attenuation that meets the needs of the majority of industrial applications. Testable with the 3M™ E-A-Rfit™ Validation System. Complies with Australian/New Zealand Standard AS/NZS 1270:2002.

In the Box:

- H510A; H510F; H510B - Earmuffs + User Instructions on Box
- H510P3GS/E - Helmet Mounted Earmuffs with GS blade (25mm) on earmuff, and E blade (30mm) in box + User Instructions on Box.

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



H510A



H510F (Unfolded & Folded)



H510B



HYX1



393-3001-2



H510P3GS/E

Testable with the
3M™ E-A-Rfit™
Validation System



QR-HP-22

Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100242340	70071730454	•	•	H510A	3M™ PELTOR™ Optime™ I Headband Format Earmuff H510A, Yellow, SLC ₈₀ 28dB (Class 5), 10 ea/Case
7100242342	70071730504	•	•	H510F	3M™ PELTOR™ Optime™ I Foldable Earmuff H510F, Yellow, SLC ₈₀ 28dB (Class 5), 10 EA/Case
7100242339	70071730421	•	•	H510B	3M™ PELTOR™ Optime™ I Neckband Format Earmuff H510B, Yellow, SLC ₈₀ 25dB (Class 4), 10 ea/Case
7100242341	70071730496	•	•	H510P3GS/E	3M™ PELTOR™ Optime™ I Helmet Attach Earmuff H510P3GS/E, Yellow, SLC ₈₀ 26dB (Class 5), 10 ea/Case
7000104045	XA007707574	•	•	HYX1	3M™ PELTOR™ X1 Hygiene Kit HYX1/37280(AAD), for X1 Earmuffs, 10 Kits/Case
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Case
7100383334	XL001642484	•	•	Z3G/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	ZGS/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

Earmuffs

3M™ PELTOR™ Optime™ II Earmuffs

These products are designed to provide moderate to high level of attenuation that meets the needs of many industrial applications where high levels of noise may be encountered. Testable with the 3M™ E-A-Rfit™ Validation System. Complies with Australian/ New Zealand Standard AS/NZS 1270:2002.

In the Box:

- H520A; H520F; H520FHV; H520B - Earmuffs + User Instructions on Box
- H520P3GS/E - Helmet Mounted Earmuffs with GS blade (25mm) on earmuff, and E blade (30mm) in box + User Instructions on Box.

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100242344	70071730553	•	•	H520A	3M™ PELTOR™ Optime™ II Headband Earmuff H520A, Green, SLC ₈₀ 32dB (Class 5), 10 EA/Case
7100242347	70071730538	•	•	H520F	3M™ PELTOR™ Optime™ II Foldable Headband Earmuff H520F, Green, SLC ₈₀ 32dB (Class 5), 10 EA/Case
7100242345	70071730579	•	•	H520FHV	3M™ PELTOR™ Optime™ II Foldable Headband Earmuff H520FHV, Bright Yellow, SLC ₈₀ 32dB (Class 5), 10 EA/Case
7100242087	70071730546	•	•	H520B	3M™ PELTOR™ Optime™ II Neckband Earmuff H520B, Green, SLC ₈₀ 27dB (Class 5), 10 EA/Case
7100242343	70071730520	•	•	H520P3GS/E	3M™ PELTOR™ Optime™ II Helmet Attach Earmuff H520P3GS/E, Green, SLC ₈₀ 29dB (Class 5), 10 EA/Case
7000104046	XA007707582	•	•	HYX2	3M™ PELTOR™ X2 Hygiene Kit HYX2/37281(AAD), for X2 Earmuffs, 10 Kits/Case
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Case
7100383334	XL001642484	•	•	Z3G/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	ZGS/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)
7000103752	XA007702625	•	•	Z3AF/2	3M™ Versaflo™ Back Plate Kit, Left and Right, Helmet Adapter for M-200/M-300/9100MP, 20 ea/Case

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™ Optime™ III Earmuffs

These products are designed to provide a high level of attenuation that meets the needs of many industrial applications where high levels of noise may be encountered. Testable with the 3M™ E-A-Rfit™ Validation System. Complies with Australian/ New Zealand Standard AS/NZS 1270:2002.

In the Box:

- H540A; H540AHV; H540B - Earmuffs + User Instructions on Box
- H540P3GS/E - Helmet Mounted Earmuffs with GS blade (25mm) on earmuff, and E blade (30mm) in box + User Instructions on Box.

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100242353	70071730603	•	•	H540A	3M™ PELTOR™ Optime™ III Headband Format Earmuff H540A, Black and Red, SLC ₈₀ 33dB (Class 5), 10 ea/Case
7100242346	70071730629	•	•	H540AHV	3M™ PELTOR™ Optime™ III Headband Earmuff H540AHV, Bright Yellow, SLC ₈₀ 33dB (Class 5), 10 EA/Case
7100242352	70071730595	•	•	H540B	3M™ PELTOR™ Optime™ III Neckband Format Earmuff H540B, Black and Red, SLC ₈₀ 34dB (Class 5), 10 ea/Case
7100242351	70071730587	•	•	H540P3GS/E	3M™ PELTOR™ Optime™ III Helmet Attach Earmuff H540P3GS/E, Black and Red, SLC ₈₀ 30dB (Class 5), 10 ea/Case
7000108016	XH001659362	•	•	HY54	3M™ PELTOR™ Earmuff Replacement Hygiene Kit HY10, H10 Series
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Case
7100383334	XL001642484	•	•	Z3G/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	ZGS/2 (25mm)	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100123728	70071676285	•	•	393-3004-2	3M™ PELTOR™ Probed Earmuff Test Cushion A, 393-3004-2, 2 Pairs/Case

3M™ PELTOR™ H505B Welders Earmuffs

The 3M™ PELTOR™ H505B Earmuff is available in a neckband version only and is designed to be used with 3M™ Speedglas™ Welding Shields. These earmuffs provide a moderate level of attenuation that meets the needs of most welding industry applications.

When correctly selected and worn these products help reduce exposure to hazardous levels of noise and loud sounds.

Testable with the
3M™ E-A-Rfit™
Validation System



QR-HP-25

Scan or Click for
Tech Data Sheet

Features and Benefits:

- Modern, stylish slim line cup design.
- Soft ear cushions provide a comfortable seal.
- Neckband design helps improve compatibility with other protective equipment.
- Soft wide cushions helps reduce pressure around the ears and improves comfort and wearability.
- Easy to replace cushions and inserts helps keep them hygienically clean.
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.

In the Box

- H505B Welders Earmuffs + User Instructions on Box.



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000103787	XA007703797	•	•	H505B	3M™ PELTOR™ Welders Earmuff H505B-596-SV, SLC ₈₀ 22dB (Class 4), 10 EA/Case
7100101874	UU008049353	•	•	HY220	3M™ PELTOR™ Earmuff Hygiene Kit HY220, 1 ea/Bag
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Cartron

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit



ID: 2013341
RID: 2013659

Communications

Close up or far away the 3M™ PELTOR™ Communication Solutions for noisy environments make it possible for users of hearing protectors to communicate – with their immediate environment and with people further away.

The safe way to be heard, and get things done.

Work never sounded this good.

There was a time when wearing hearing protectors meant being isolated and out of contact. Those days are over. Today, the 3M™ PELTOR™ Brand of Products offers communication solutions that not only make your working day safer and more efficient, but also much smarter.

To be effective, a hearing protector should be used 100% of the time in noisy environments. Even taking it off for a short time dramatically reduces its effectiveness and greatly increases the risk of hearing damage. 3M™ PELTOR™ Communication Solutions Products make it possible for your team to communicate more easily in high-noise areas.

Communication devices are key to both safety and productivity. Integrating a 3M™ PELTOR™ Communication Solution in your work environment will help you communicate more clearly with co-workers while reducing your exposure to potential hazardous noise. Feel free to contact us to discuss a solution to meet your specific needs.

Just what you want to hear.


Active control of incoming sounds from your surroundings lets you hear alarm signals and machines, while harmful levels of noise are filtered out by electronics.

Music to your ears.

Communication with people around you involves using our level-dependent function for ambient listening. For longer distances, you have built-in two-way radios and Bluetooth® Connections to mobile phones. Meanwhile all communication options can also be combined with a sound system so you can listen to your favourite streamed music or pod radio, with first-class sound quality.



ID: 2058278
RID 2057322



Function symbols.

To help you understand the functionality of the products, below is an explanation of the symbols you will find on the products.



Testable with the
3M™ E-A-Rfit™
Validation System



Hearing protection
with built-in AM/FM
radio



Hearing protection
with built in FM Radio



Hearing protection for
communicating with
external two-way radio



Hearing protection with
built in two-way radio



Hearing protection
with external audio
input for listen only



Level-dependent
function for ambient
listening to help improve
situational awareness



Bluetooth® MultiPoint
technology for
connecting to one or
two external devices
for hands-free talk and
streaming



Noise cancelling boom
microphone for clear
speech transmission in
noisy environments



Connect the headset
with the "3M™
Connected Equipment"
mobile app supporting
both Android and iOS







































































































































Intrinsically safe
design



Bluetooth®
Connectivity

Communication & Hearing Selection Guide

	PRODUCT DESCRIPTION	PAGE	ATTENUATION DATA			AVAILABILITY									VOX						
			HEAD BAND IN-EAR ELEC.	CAP/ HELMET ATTACH Adapter/Blade In Box	NECK BAND	AUS	NZ	Testable with the 3M™ E-A-Rfit™ Validation System	Hearing protection with built-in AM/FM radio	Hearing protection with built in FM Radio	Hearing protection with external audio input for listen only	Connect the headset with the “3M” Connected Equipment” mobile app supporting both Android and iOS	Noise cancelling boom microphone for clear speech transmission in noisy environments	Bluetooth®	Voice Operated Transmission (VOX). <i>Note: Dependant on Two Way Radio Protocol aligning with 3M PELTOR Protocol</i>	Level-dependent function for ambient listening to help improve situational awareness	Hearing protection for communicating with external two-way radio	Hearing protection with built in two-way radio	Digital two way radio according to DMR standard.	Versaflo™ M-300 Mic Connectivity	Intrinsically safe design
	3M™ PELTOR™ ProTac III Headset Slim	144	26dB (Class 5)	24dB (Class 4) E Blade (30mm)		•	•														
	3M™ PELTOR™ ProTac III Headset Standard	144	32dB (Class 5)	30dB (Class 5) E Blade (30mm)		•	•														
	3M™ PELTOR™ Worktunes Pro AM/FM Radio Headset	146	32dB (Class 5)	30dB (Class 5) E Blade (30mm)		•	•														
	3M™ PELTOR™ ProTac Hunter Headset	148	26dB (Class 5)			•	•														
	3M™ PELTOR™ ProTac Shooter Headset	148	32dB (Class 5)			•	•														
	3M™ PELTOR™ SportTac™ Hunting Folding Headset	149	24db (Class 4)			•	•														
	3M™ PELTOR™ EEP-100 Electronic Earplug	150	16-23 (Class 2 & 4)			•	•														
	3M™ PELTOR™ TEP-200 Tactical Earplug	151	16-23 (Class 2 & 4)			•															
	3M™ PELTOR™ CH-5 Ultra High Attenuation Headset J11	152	37dB (Class 5)			•	•								 Yes. Please see above 'NOTE'		 PELTOR J11 (-38) NATO J11 (-86)				
	3M™ PELTOR™ CH-5 Ultra High Attenuation Headset	152	37dB (Class 5)	35dB (Class 5) E Blade (30mm)		•	•								 Yes. Please see above 'NOTE'		 PELTOR J11 (-38)				
	3M™ PELTOR™ CH-3 FLX2 Headset with PTT	154	31dB (Class 5)	29dB (Class 5) E Blade (30mm)	30dB (Class 5)	•	•								 Yes. Please see above 'NOTE'		 FLX2 Cable -111		 MT74V/1		
	3M™ PELTOR™ CH-3 FLX2 Standard J11	156	31dB (Class 5)	29dB (Class 5) E Blade (30mm)	30dB (Class 5)	•	•								 Yes. Please see above 'NOTE'		 FLX2 Cable -110		 MT74V/1		
	3M™ PELTOR™ CH-3 FLX2 Listen Only Headset	158	31dB (Class 5)	29dB (Class 5) E Blade (30mm)	30dB (Class 5)	•	•				 FLX2 Cable -112										
	3M™ PELTOR™ WS™ Alert X Headset	162	30dB (Class 5)	29dB (Class 5) E Blade (30mm)		•	•							 Single External Device	 Yes. Please see above 'NOTE'					 MT53V/1	
	3M™ PELTOR™ WS™ Alert XPI Headset	164	30dB (Class 5)	29 dB (Class 5) E Blade (30mm)		•	•							 MultiPoint:1-2 External Devices	 Yes. Please see above 'NOTE'					 MT53V/1	
	3M™ PELTOR™ WS™ ALERT™ XPV Solar Powered Headset	166	27dB (Class 5)			•	•							 MultiPoint:1-2 External Devices	 Yes. Please see above 'NOTE'						
	3M™ PELTOR™ WS™ ProTac XPI Headset	167	32dB (Class 5)	27dB (Class 5) E Blade (30mm)		•	•							 MultiPoint:1-2 External Devices	 Yes. Please see above 'NOTE'					 MT7V/1	
	3M™ PELTOR™ WS™ ProTac XPI FLX2 Headset	167	32dB (Class 5)	27dB (Class 5) E Blade (30mm)	29dB (Class 5)	•	•							 MultiPoint:1-2 External Devices	 Yes. Please see above 'NOTE'		 FLX2 Cable -111		 MT7V/1		
	3M™ PELTOR™ WS™ LiteCom Plus with Bluetooth®	169	32dB (Class 5)	29dB (Class 5) E Blade (30mm)	30dB (Class 5)	•	•							 MultiPoint:1-2 External Devices	 Yes. Please see above 'NOTE'		 FLEX Cable FL6BR	 Non-Programmable on 433MHz		 MT7V/1	
	3M™ PELTOR™ WS™ LiteCom Pro III Headset	171	32dB (Class 5)	29dB (Class 5) E Blade (30mm)	30dB (Class 5)	•	•							 MultiPoint:1-2 External Devices	 Yes. Please see above 'NOTE'		 FLEX Cable FL6BR	 Programmable: 403-470MHz		 MT7V/1	
	3M™ PELTOR™ CH-3 FLX2 Listen Only Ex Hearing Protector	173	31dB (Class 5)	29dB (Class 5) E Blade (30mm)		•	•				 FLX2 Cable -112-50									 IECEX/ATEX/UKEX	
	3M™ PELTOR™ TWIN CUP™ Headset IECEX/ATEX	175	31dB (Class 5)	30dB (Class 5) E Blade (30mm)		•	•								 Yes. Please see above 'NOTE'		 PELTOR J11 (-38)				 IECEX/ATEX
	3M™ PELTOR™ WS™ LiteCom Pro III Headset EX	177	32dB (Class 5)	29dB (Class 5) E Blade (30mm)	30dB (Class 5)	•	•							 MultiPoint:1-2 External Devices	 Yes. Please see above 'NOTE'			 Programmable: 403-470MHz		 MT7V/1	 ANZEx/IECEX/ATEX

3M™ PELTOR™ ProTac™ III Headset



The 3M™ PELTOR™ ProTac™ III hearing protector helps safeguard against harmful noise, whilst allowing ambient sounds to be heard at a level below 82dB. This attribute can help increase your situational awareness and ability to communicate with nearby colleagues, as well as hearing warning signals, approaching vehicles or sounds produced by machines and industrial processes.



Features and Benefits:

- Standard Cup version and Slim cup version
- Voice Guided Menu System
- 3.5mm listen only input* (two-way radio, mobile)
- Approximately 100 hours of battery lifetime
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x Headset, 2 x AA batteries, 1 x User Instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.

*For user protection, output from headset is not above 82 dB for all sources at a maximum power of 300mV RMS.



MT13H220A



MT13H221A

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100088456	UU004637789	•	•	MT13H220A	3M™ PELTOR™ ProTac™ III Slim Headset Headband MT13H220A, SLC ₈₀ 26dB (Class 5), 1 ea/ Carton
7100088455	UU004637771	•	•	MT13H220P3E	3M™ PELTOR™ ProTac™ III Slim Helmet Mounted Headset MT13H220P3E, SLC ₈₀ 24dB (Class 4), 1 ea/ Carton
7100088424	UU004690622	•	•	MT13H221A	3M™ PELTOR™ ProTac™ III Headset Headband MT13H221A, SLC ₈₀ 32dB (Class 5), 1 ea/ Carton
7100088423	UU004690614	•	•	MT13H221P3E	3M™ PELTOR™ ProTac™ III Headset Helmet Mounted MT13H221P3E, SLC ₈₀ 30dB (Class 5), 1 ea/ Carton

Communications

3M™ PELTOR™ ProTac™ III Headset Accessories



HY220



HY100A



FP9007



393-3001-2



Z3G (25mm)



Z3GS (25mm)

Accessories - Cable

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000108359	XH001676952	•	•	FL6CE/1	3M™ PELTOR™ Cable FL6CE/1, with Stereo 3.5 mm Plug, 1 Each

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100101874	UU008049353	•	•	HY220	3M™ PELTOR™ Earmuff Hygiene Kit HY220, 1 ea/Bag
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•	•	FP9007	3M™ Peltor™ Padded Headset Bag FP9007, Black

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B 393-3001-2, 2 ea/Kit

3M™ PELTOR™ Worktunes Pro AM/FM Radio Headset



Features and Benefits:

- AM/FM Radio headset with built-in antenna
- Dual shell designed to protect the electronic circuitry inside the cup
- 3.5mm jack: A listen-only stereo input to connect to a mobile phone, two-way radio or other external devices*
- Approximately 100 hours of use
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x Headset, 2 x AA Batteries, 1 x User Instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.
*For user protection, output from headset is not above 82 dB for all sources at a maximum power of 250 mV RMS.



HRXS221P3E (Helmet not included)



HRXS221A

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100089368	UU004690713	•	•	HRXS221A	3M™ PELTOR™ WorkTunes™ Pro AM/FM Radio Headset Headband, HRXS221A, Black, SLC ₈₀ 32dB (Class 5), 10 EA/Case
7100089440	UU004690663	•	•	HRXS221P3E	3M™ PELTOR™ WorkTunes™ Pro AM/FM Radio Headset Helmet Mounted, HRXS221P3E, SLC ₈₀ 30dB (Class 5), 10 EA/Case

Communications

3M™ PELTOR™ WorkTunes™ Pro AM/FM Radio Headset Accessories



Accessories - Cable

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000108359	XH001676952	•	•	FL6CE/1	3M™ PELTOR™ Cable FL6CE/1, with Stereo 3.5 mm Plug, 80 1 Each

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100101874	UU008049353	•	•	HY220	3M™ PELTOR™ Earmuff Hygiene Kit HY220, 1 ea/Bag
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•		FP9007	3M™ Peltor™ Padded Headset Bag FP9007, Black

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™ ProTac Hunter/ Shooter Headset



QR-CM-03

Scan or Click for
Tech Data Sheet



Accessories



HY220



HY100A



FP9007

Features and Benefits:

- Dual shell designed to protect the electronic circuitry inside the cup
- 3.5mm jack: A listen-only stereo input to connect to a mobile phone, two-way radio or other external devices*
- Approximately 100 hours of use
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x Headset, 2 x AA Batteries, 1 x User Instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.

* For user protection, output from headset is not above 82 dB for all sources at a maximum power of 18.5 mV RMS.



MT13H222A



MT13H223A

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100088458	UU004690648	•	•	MT13H222A	3M™ PELTOR™ ProTac™ Hunter Headset Headband MT13H222A, SLC ₈₀ 26dB (Class 5), 1 EA/Carton
7100088425	UU004690630	•	•	MT13H223A	3M™ PELTOR™ ProTac™ Shooter Headset Headband, MT13H223A, SLC ₈₀ 32dB (Class 5), 1 EA/Case

Accessories - Cable

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000108359	XH001676952	•	•	FL6CE/1	3M™ PELTOR™ Cable FL6CE/1, with Stereo 3.5 mm Plug, 80 1 Each

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100101874	UU008049353	•	•	HY220	3M™ PELTOR™ Earmuff Hygiene Kit HY220, 1 ea/Bag
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Case
7100064607	XH001655360	•		FP9007	3M™ Peltor™ Padded Headset Bag FP9007, Black

3M™ PELTOR™ SportTac™ Hunting Folding Headband

Features and Benefits:

- Electronic level dependent hearing protector designed for hunting and shooting*.
- Input Jack for connection to external devices
- Approximately 600 hours operation time
- To reduce the corrosion caused by sweat the electronics are located in the outer part of the cup
- Complies with Australian/ New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x SportTac, 2 x AAA Batteries

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.

* For user protection, output from headset is not above 82 dB for all sources at a maximum power of 18.5 mV RMS.




QR-CM-04

Scan or Click for
Tech Data Sheet



MT16H210F-478-GN



Accessories



HY21



HY100A



FP9007

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100004420	XH001650049	•	•	MT16H210F-478-GN	3M™ PELTOR™ SportTac™ Hunting Model Folding Headband, MT16H210F-478-GN, SLC ₈₀ 24dB (Class 4), 1 ea/Carton, Orange/Green Cups.
7000039607	XH001650056	•		MT16H210F-478-RD	3M™ PELTOR™ SportTac™ Shooting Model Folding Headband, MT16H210F-478-RD, SLC ₈₀ 24dB (Class 4), 1 EA/Carton, Red/Black Cups.

Accessories - Cable

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000107805	XH001652078	•	•	FL6H	3M™ PELTOR™ Audio Input Cable FL6H, 3.5mm Mono Plug, 1 ea/Carton
7100064600	XH001652110	•	•	FL6N	3M™ PELTOR™ Audio Input Cable FL6N, 3.5mm Stereo Plug, 1 ea/Carton

Accessories - Cable

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000039686	XH001659305	•	•	HY21	3M™ PELTOR™ Hygiene Kit for SportTac HY21, 1 Each
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•		FP9007	3M™ Peltor™ Padded Headset Bag FP9007, Black

Protective Hearing Solutions: In-Ear

3M™ PELTOR™ EEP-100 Electronic Earplug

The 3M™ PELTOR™ Electronic Earplug helps protect your hearing, and can help improve situational awareness and communications in challenging environments. The earpieces are rechargeable via a USB jack on the charging case providing storage of the earpieces when not being used.

The small and lightweight design makes it compatible with most head borne 3M Personal Safety Equipment (PPE), such as helmets and face shields.



Features and Benefits:

- Hearing protection with interchangeable tips
- Level-dependent function (for situational awareness)
- Intuitive one-button operation
- Rechargeable
- Durable storage and charging case (IP54)
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box -**
 - 2 x Electronic Earplugs
 - 1 x Charging case
 - 2 x 3M™ UltraFit™ Communication Tips Replacement, Large
 - 2 x 3M™ UltraFit™ Communication Tips Replacement, Medium
 - 2 x 3M™ UltraFit™ Communication Tips Replacement, Small
 - 2 x 3M™ PELTOR™ Communication Tip, CCC-GRM
 - 1 x USB cable 1 x User Instructions



Scan or Click for
Tech Data Sheet



EEP-100

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100194360	70071730785	•	•	EEP-100 EU	3M™ PELTOR™ Electronic Earplug, EEP-100 EU, Light green, 1 Each
7100066388	70071673746	•	•	370-TEPL-25	3M™ PELTOR™ UltraFit™ Communication Tip Replacement 370-TEPL-25, SLC ₈₀ 16dB (Class 2), 25 Pairs/Case
7100066387	70071673738	•	•	370-TEPM-25	3M™ PELTOR™ UltraFit™ Communication Tip Replacement 370-TEPM-25, SLC ₈₀ 16dB (Class 2), 25 Pairs/Case
7100066371	70071673720	•	•	370-TEPS-25	3M™ PELTOR™ UltraFit™ Communication Tip Replacement 370-TEPS-25, SLC ₈₀ 16dB (Class 2), 25 Pairs/Case
7100103087	70071675212	•	•	CCC-GRM-25	3M™ PELTOR™ Triple-C Communication Eartips CCC-GRM-25, SLC ₈₀ 23dB (Class 4), 25 Pair/Case
7000128201	70071615275	•	•	370-1019-10	3M™ PELTOR™ Skull Screw Communication Replacement Tip 370-1019-10, PELTIPS-01 (Not in Kit), SLC ₈₀ 23dB (Class 4), 10 EA/Case

Accessories

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100074090	70071673795	•		TEP-CORD	3M™ PELTOR™ Earplug Connecting Cord, TEP-CORD, 1 Each

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100225700	70071734456	•	•	393-2032-50	3M™ UltraFit™ Small, 393-2032-50, UltraFit Sm, 50 Pair/Case
7100225705	70071734464	•	•	393-2033-50	3M™ UltraFit™ Medium, 393-2033-50, UltraFit Med, 50 Pair/Case
7100225706	70071734472	•	•	393-2034-50	3M™ UltraFit™ Large, 393-2034-50, UltraFit Lg, 50 Pair/Case
7100225704	70071734449	•	•	393-2031-50	3M™ PELTOR™ Probed Electronic Earplug 393-2031-50, CCC-GRM-25, 50 Pair/Case
7100225703	70071734431	•	•	393-2030-50	3M™ Skull Screws/Torque™, 393-2030-50, SkullSc/Torq, 50 Pair/Case

Protective Hearing Solutions: In-Ear

3M™ PELTOR™ TEP-200 Tactical Earplug

The 3M™ PELTOR™ Tactical Earplug helps protect your hearing, and can help improve situational awareness and communications in challenging environments. Integrated with level-dependent technology, the TEP-200 helps provide hearing protection in noise and situational awareness in quiet environments.



Features and Benefits:

- Hearing protection with interchangeable tips
- Level-dependent function (for situational awareness)
- Intuitive one-button operation
- Rechargeable through storage and portable charging case (IP67)
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box -**
 - 2 x Electronic Earplugs
 - 1 x Charging case
 - 2 x 3M™ Ultra Fit™ Communication Tips Replacement, Large
 - 2 x 3M™ Ultra Fit™ Communication Tips Replacement, Medium
 - 2 x 3M™ Ultra Fit™ Communication Tips Replacement, Small
 - 2 x 3M™ PELTOR™ Communication Tip, CCC-GRM
 - 1 x USB cable 1 x User Instructions



TEP-200

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100141803	70071677010	•		TEP-200	3M™ PELTOR™ Tactical Earplug TEP-200 EU, Black, 1 Each
7100066388	70071673746	•	•	370-TEPL-25	3M™ PELTOR™ UltraFit™ Communication Tip Replacement 370-TEPL-25, SLC ₈₀ 16dB (Class 2), 25 Pairs/Case
7100066387	70071673738	•	•	370-TEPM-25	3M™ PELTOR™ UltraFit™ Communication Tip Replacement 370-TEPM-25, SLC ₈₀ 16dB (Class 2), 25 Pairs/Case
7100066371	70071673720	•	•	370-TEPS-25	3M™ PELTOR™ UltraFit™ Communication Tip Replacement 370-TEPS-25, SLC ₈₀ 16dB (Class 2), 25 Pairs/Case
7100103087	70071675212	•	•	CCC-GRM-25	3M™ PELTOR™ Triple-C Communication Eartips CCC-GRM-25, SLC ₈₀ 23dB (Class 4), 25 Pair/Case
7000128201	70071615275	•	•	370-1019-10	3M™ PELTOR™ Skull Screw Communication Replacement Tip 370-1019-10, PELTIPS-01 (Not in Kit), SLC ₈₀ 23dB (Class 4), 10 EA/Case

Accessories

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100074090	70071673795	•		TEP-CORD	3M™ PELTOR™ Earplug Connecting Cord, TEP-CORD, 1 Each

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100225700	70071734456	•	•	393-2032-50	3M™ UltraFit™ Small, 393-2032-50, UltraFit Sm, 50 Pair/Case
7100225705	70071734464	•	•	393-2033-50	3M™ UltraFit™ Medium, 393-2033-50, UltraFit Med, 50 Pair/Case
7100225706	70071734472	•	•	393-2034-50	3M™ UltraFit™ Large, 393-2034-50, UltraFit Lg, 50 Pair/Case
7100225704	70071734449	•	•	393-2031-50	3M™ PELTOR™ Probed Electronic Earplug 393-2031-50, CCC-GRM-25, 50 Pair/Case
7100225703	70071734431	•	•	393-2030-50	3M™ Skull Screws/Torque™, 393-2030-50, SkullSc/Torq, 50 Pair/Case

3M™ PELTOR™ CH-5 High Attenuation Headset



These 3M PELTOR headsets are intended to help provide protection against hazardous noise levels and very loud sounds. With innovative technology and design, the CH-5 headset achieve a very high attenuation. A new water tight boom microphone (IP68) is also developed for this product which allows for operation in wet conditions. Easy to use and maintain.

Designed to be used in extreme military environments such as tanks (crew headsets), ground crew around fighter jets and helicopters together with 3M PELTOR™ PTT Adapters or direct to an intercom system.

Features and Benefits:

- Robust construction, easy to maintain
- Waterproof microphone (IP68)
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x Headset, 1 x User Instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100099845	UU008027532	•	•	MT73H450A-38	3M™ PELTOR™ CH-5 High Attenuation Headset Headband, MT73H450A-38, J11 plug, Gray/Black, SLC ₈₀ 37dB (Class 5), 1 EA/Case
7100099883	UU008027565	•	•	MT73H450A-86	3M™ PELTOR™ CH-5 High Attenuation Headset Headband MT73H450A-86, J11 Plug, NATO Wired, Gray/Black SLC ₈₀ 37dB (Class 5), 1 ea/Case
7100106703	UU008117143	•	•	MT73H450A GB	3M™ PELTOR™ CH-5 High Attenuation Headset Headband, MT73H450A GB, J11 plug, Bright Green, SLC ₈₀ 37dB (Class 5), 1 EA/Case
7100106867	UU008117184	•	•	MT73H450P3E GB	3M™ PELTOR™ CH-5 High Attenuation Headset Helmet Mounted, MT73H450P3E GB, J11, Bright Green, SLC ₈₀ 29dB (Class 5), 1 EA/Case

Communications

3M™ PELTOR™ CH-5 High Attenuation Headset Accessories



HY45



MT73/1



MT171/2



HY100A



HYM1000



FP9007



393-3005-2



Z3G (25mm)



Z3GS (25mm)

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100107408	UU008117135	•	•	HY45	Replacement Hygiene Kit for CH-5 Headsets
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•	•	FP9007	3M™ Peltor™ Padded Headset Bag FP9007, Black

Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100112094	UU008163634	•	•	MT73/1	3M™ PELTOR™ Water Resistant Standard Boom Microphone MT73/1, 1 Each
7100112112	UU008159483	•	•	M171/2	3M™ Peltor™ Wind Protector, M171/2, 1 Each
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062128	70071691136	•	•	393-3005-2	3M™ PELTOR™ X4/X5 Earmuff Probed Test Cushions D, 393-3005-2, 2 EA/Kit

3M™ PELTOR™ CH-3 FLX2 Headset with PTT




CH-3 FLX2 Headset with PTT is the solution when you want a smooth and easy to use set-up with fewer cables and easy access to the PTT on your left side of the headset.

Features and Benefits:

- Waterproof microphone (IP68)
- Easy access PTT (Push-to-Talk) button on side of the cup
- Detachable down lead FLX2 connector for major 2 way radios (-111)
- Improved speaker efficiency to fit today's digital device
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/ New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x 3M™ PELTOR™ CH-3 FLX2 Headset, 1 x User instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



MT74H52P3E-111 SV



MT74H52A-111 SV



MT74H52P3E-111



MT74H52A-111

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100203638	UU010250932	•	•	MT74H52A-111	3M™ PELTOR™ CH-3 FLX2 Headset with PTT Headband, MT74H52A-111, SLC ₈₀ 31dB (Class 5), 1 Each
7100205729	UU010249074	•	•	MT74H52B-111	3M™ PELTOR™ CH-3 FLX2 Headset with PTT Neckband, SLC ₈₀ 30dB (Class 5), 1 Each
7100203150	UU010247599	•	•	MT74H52P3E-111	3M™ PELTOR™ CH-3 FLX2 Headset with PTT Helmet Mounted, MT74H52P3E-111, SLC ₈₀ 29dB (Class 5), 1 Each
7100326362	UU012969471	•	•	MT74H52A-111 SV	3M™ PELTOR™ CH-3 FLX2 Headset with PTT Headband, MT74H52A-111 SV, SLC ₈₀ 31dB (Class 5), 1 Each, Black
7100325910	UU012969463	•	•	MT74H52P3E-111 SV	3M™ PELTOR™ CH-3 FLX2 Headset with PTT, MT74H52P3E-111 SV, Helmet Mounted, SLC ₈₀ 29dB (Class 5), 1 Each, Black

3M™ PELTOR™ CH-3 FLX2 Headset with PTT Accessories



HY84



HY100A



FP9007



MT74V/1



Z3G (25mm)



Z3GS (25mm)



Z3AF/2

Accessories - FLX2 Cables

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100197719	UU010126348	•		FLX2-111	3M™ PELTOR™ FLX2 Cable FLX2-111, Hytera PD7 Series, 1 Each
7100197556	UU010124293	•	•	FLX2-35	3M™ PELTOR™ FLX2 Cable FLX2-35, Icom 2-Pin Angled, 1 Each
7100197565	UU010124301	•		FLX2-44	3M™ PELTOR™ FLX2 Cable FLX2-44, Icom Multipin S8, 1 Each
7100197568	UU010126330	•	•	FLX2-64	3M™ PELTOR™ FLX2 Cable FLX2-64, Icom F34/F44, 1 Each
7100193170	UU010054110	•	•	FLX2-36	3M™ PELTOR™ FLX2 Cable FLX2-36, Kenwood 2-Pin, 1 Each
7100185797	UU009731132	•		FLX2-107	3M™ PELTOR™ FLX2 Cable Kenwood Multipin, FLX2-107, 1 Each
7100197566	UU010126314	•		FLX2-18	3M™ PELTOR™ FLX2 Cable FLX2-18, Motorola XTS Series, 1 Each
7100193228	UU009898113	•	•	FLX2-21	3M™ PELTOR™ FLX2 Cable FLX2-21, Motorola CP200/2-Pin, 1 Each
7100193227	UU009879477	•	•	FLX2-32	3M™ PELTOR™ FLX2 Cable FLX2-32, Motorola HT Series, 1 Each
7100185795	UU009731124	•	•	FLX2-63	3M™ PELTOR™ FLX2 Cable Motorola DP4000, FLX2-63, 1 Each
7100197572	UU010126322	•	•	FLX2-65	3M™ PELTOR™ FLX2 Cable FLX2-65, Motorola ex500/ex600, 1 Each
7100220865	UU010902672	•	•	FLX2-69	3M™ PELTOR™ FLX2 Cable FLX2-69, for Motorola M9 Plug, 1 Each
7100197718	UU010123584	•		FLX2-101	3M™ PELTOR™ FLX2 Cable FLX2-101, Sepura 800/900 Series, 1 Each
7100193229	UU009898071	•	•	FLX2-28	3M™ PELTOR™ FLX2 Cable FLX2-28, Mobile/DECT Phone, 1 Each
7100331614	UU013051055	•	•	FLX2-114	3M™ PELTOR™ FLX2 Cable to Motorola R7 FLX2-114, Fits -111 Headsets, 1 Each
7100329802	UU013035025	•	•	FLX2-115	3M™ PELTOR™ FLX2 Cable to Tait TP3 TP8 and TP9 Series FLX2-115, Fits -111 Headsets, 1 Each

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adaptors for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adaptors for 3M Scott Safety Visor Z3GS/2 (25mm)
7000103752	XA007702625	•	•	Z3AF/2	3M™ Versaflo™ Back Plate Kit, Left and Right, Helmet Adapter for M-300

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100212095	UU010391918	•	•	HY84	3M™ PELTOR™ Hygiene Kit HY84, for CH-3 FLX2 Headset, 1 Each
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/ Carton
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each
7100064607	XH001655360	•		FP9007	3M™ Peltor™ Padded Headset Bag FP9007, Black


Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100324955	UU012802037	•	•	MT74V/1	3M™ PELTOR™ Microphone for Versaflo M-300 Helmet

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™ CH-3 FLX2 Standard J11 Headset



The CH-3 FLX2 Headset is the solution for easy Push-To-Talk (PTT) in rough and dirty environment where it's more convenient to have an external PTT on your chest to control your 2-way radio. Alternatively, you can connect into various types of vehicle intercom.

Features and Benefits:

- Bright yellow colour for enhanced visibility
- Waterproof microphone (IP68)
- Detachable down lead FLX2 connector for high flexibility
- Improved speaker efficiency to fit todays digital device
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x 3M™ PELTOR™ CH-3 FLX2 Headset, 1 x User instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



MT74H52A-110 SV



MT74H52P3E-110

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100203637	UU010246302	•	•	MT74H52A-110	3M™ PELTOR™ CH-3 FLX2 Headset Headband, MT74H52A-110, SLC ₈₀ 31dB (Class 5), 1 Each
7100203636	UU010246914	•	•	MT74H52B-110	3M™ PELTOR™ CH-3 FLX2 Headset Neckband, MT74H52B-110, SLC ₈₀ 30dB (Class 5), 1 Each
7100203635	UU010246922	•	•	MT74H52P3E-110	3M™ PELTOR™ CH-3 FLX2 Headset Helmet Mounted, MT74H52P3E-110, SLC ₈₀ 29dB (Class 5), 1 Each
7100325909	UU012969455	•	•	MT74H52A-110 SV	Black CH-3 FLX2 Standard J11 Headset, Headband SLC80 31dB (Class 5)
7100325911	UU012969489	•	•	MT74H52P3E-110 SV	Black CH-3 FLX2 Standard J11 Headset, Helmet Att. SLC80 29dB (Class 5)

Communications

3M™ PELTOR™ CH-3 FLX2 Standard J11 Headset Accessories



HY84



HY100A



FP9007



MT74V/1



Z3G (25mm)



Z3GS (25mm)



Z3AF/2

Accessories - FLX2 Cables

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100185799	UU009731140	•	•	FLX2-200	3M™ PELTOR™ FLX2 Cable J11, FLX2-200, 1 Each
7100207323	UU010325718	•	•	FLX2-201	3M™ PELTOR™ FLX2 Airline Cable FLX2-201, 1 Each
7100331595	UU013052517	•	•	FLX2-200-02	3M™ PELTOR™ FLX2 Cable with J11 connector FLX2-200-02, NATO Wired, Fits -110 Headsets, 1 Each

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)
7000103752	XA007702625	•	•	Z3AF/2	3M™ Versaflo™ Back Plate Kit, Left and Right, Helmet Adapter for M-300

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100212095	UU010391918	•	•	HY84	3M™ PELTOR™ Hygiene Kit HY84, for CH-3 FLX2 Headset, 1 Each
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Cartron
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each
7100064607	XH001655360	•		FP9007	3M™ Peltor™ Padded Headset Bag FP9007, Black

Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100324955	UU012802037	•	•	MT74V/1	3M™ PELTOR™ Microphone for Versaflo M-300 Helmet

3M™ E-A-Rfit™ Dual Ear Validation System

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™ CH-3 FLX2 Listen Only Headset



The 3M™ PELTOR™ CH-3 FLX2 Listen only Hearing Protector can enhance communication in noisy environments. Suitable for workers connected to 'listen only' 2-way handheld radio, mobile or fixed systems.

Features and Benefits:

- Bright yellow colour for enhanced visibility
- Detachable down lead FLX2 connector for high flexibility (-112)
- Improved speaker efficiency to fit todays digital device
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x 3M™ PELTOR™ CH-3 FLX2 Headset, 1 x User instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



Scan or Click for
Tech Data Sheet



HT52A-112



HT52P3E-112



HT52B-112

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100203299	UU010252029	•	•	HT52A-112	3M™ PELTOR™ CH-3 FLX2 Listen Only Headset Headband, HT52A-112, SLC ₈₀ 31dB (Class 5), 1 Each
7100203298	UU010252037	•	•	HT52B-112	3M™ PELTOR™ CH-3 FLX2 Listen Only Headset Neckband, HT52B-112, SLC ₈₀ 30dB (Class 5), 1 Each
7100203302	UU010252045	•	•	HT52P3E-112	3M™ PELTOR™ CH-3 FLX2 Listen Only Headset Helmet Mounted, HT52P3E-112, SLC ₈₀ 29dB (Class 5), 1 Each

Communications

3M™ PELTOR™ CH-3 FLX2 Listen Only Headset Accessories



HY84



HY100A



FP9007



MT74V/1



Z3G (25mm)



Z3GS (25mm)



Z3AF/2

Accessories - FLX2 Cables

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100191443	UU009898089	•	•	FLX2-202	3M™ PELTOR™ FLX2 Cable FLX2-202, 3.5mm Stereo, 1 Each
7100191444	UU009898097	•	•	FLX2-204	3M™ PELTOR™ FLX2 Cable FLX2-204, 1/4" Stereo, 1 Each
7100207324	UU010346730	•	•	FLX2-208	3M™ PELTOR™ FLX2 Cable FLX2-208, 3.5mm Stereo Threaded, 1 Each

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)


Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100212095	UU010391918	•	•	HY84	3M™ PELTOR™ Hygiene Kit HY84, for CH-3 FLX2 Headset, 1 Each
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•	•	FP9007	3M™ Peltor™ Padded Headset Bag FP9007, Black

3M™ E-A-Rfit™ Dual Ear Validation System


SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

CH-3 Headsets - Selection Guide



3M™ PELTOR™ WS™ ALERT™ X Headset

Hearing protection with Bluetooth® technology and Mobile App interface.



The Bluetooth® headset with noise-cancelling boom microphone connects to your mobile phone for hands free calls and streaming in noisy environments. The headset helps to protect against hazardous noise and at the same time helps promote your situational awareness via the level-dependent function for ambient listening. The headset also syncs to a mobile app so users can easily set-up and adjust the headset.

Features and Benefits:

- Attenuating hearing protector comes in two models: headband or a safety helmet attachment
- Bluetooth® technology for connection to an external Bluetooth® device allows for hands-free talking and streaming
- Noise-cancelling boom microphone for clear speech transmission in noisy environments
- Level-dependent function for ambient listening to help promote auditory situational awareness
- Connection to an iOS and Android compatible mobile app, 3M™ Connected Equipment, to more easily set-up and adjust the headset. The app is available to download from App Store and Google Play.
- Mobile app allows you to receive reminders when to change replacement cushions (hygiene kit) and choose the frequency of these alerts
- Push-to-Listen feature to easily and instantaneously listen to your surroundings
- Voice guided feedback after setting adjustment. No need to remove the headset for any adjustments
- Replaceable cushions (hygiene-kit)
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x Headset, 2 x AA batteries, 1 x User Instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



MRX21A4WS6



MRX21P3E4WS6

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100257811	UU011469580	•	•	MRX21A4WS6	3M™ PELTOR™ WS™ ALERT™ X Headset Headband, Bluetooth® APP, MRX21A4WS6, Bright Yellow, SLC ₈₀ 30dB (Class 5), 1 Each
7100256658	UU011469598	•	•	MRX21P3E4WS6	3M™ PELTOR™ WS™ ALERT™ X Headset Helmet Mounted, Bluetooth® APP, MRX21P3E4WS6, Bright Yellow, SLC ₈₀ 29dB (Class 5), 1 Each

Communications

3M™ PELTOR™ WS™ ALERT™ X Headset Accessories



HY82



MT53N-14/1



M995/2



MT53V/1



HY100A



FP9007



HYM1000



393-3001-2



Z3G (25mm)



Z3GS (25mm)



Z3AF/2

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adaptors for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adaptors for 3M Scott Safety Visor Z3GS/2 (25mm)
7000103752	XA007702625	•	•	Z3AF/2	3M™ Versaflo™ Back Plate Kit, Left and Right, Helmet Adapter for M-300

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100122439	UU008567388	•	•	HY82	3M™ PELTOR™ Hygiene Kit HY82, 1 Each
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•	•	FP9007	3M™ PELTOR™ Padded Headset Bag FP9007, Black


Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100264326	UU011614862	•	•	MT53N- 14/1	3M™ PELTOR™ Electret Boom Microphone, MT53N-11/1, 240mm with Plug Including Windshield M995/2
7010044372	XH001679154	•	•	M995/2	3M™ PELTOR™ Windshield for Electret Boom Microphone M995/2
7100098955	UU008013581	•	•	MT53V/1	3M™ PELTOR™ Boom Microphone MT53V/1, Electret, for Versaflo M-300 Helmet, 1 Each
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each

3M™ E-A-Rfit™ Dual-Ear Validation System - Probe

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™
WS™ ALERT™ XPI Headset



MultiPoint bluetooth headset with noise-cancelling microphone and situational awareness.

The 3M™ PELTOR™ WS™ ALERT™ XPI Headset is the next generation protective communication solution. With Bluetooth® wireless communication, noise-cancelling boom microphone, integrated FM Radio and level-dependent function for ambient listening, the WS™ ALERT™ XPI Headset not only helps protect you against hazardous noise, but also makes it easy to make phone calls with both hands free in noisy environments.



Features and Benefits:

- High attenuating hearing protector in two models: stand-alone headband or safety helmet attachment
- Bluetooth® MultiPoint Technology for connection to one or two external devices for hands-free talk and streaming Noise cancelling boom microphone for clear speech transmission in noisy environments
- Level-dependent function for ambient listening to help promote auditory situational awareness.
- Push-to-Listen feature to easily and instantaneously listen to your surroundings
- Built-in FM-Radio with radio volume limited to 82dB
- Voice guided menu system with announced FM-Radio frequencies
- Digital station search
- Ability to store up to 4 favourite stations
- Auto power off: The headset will turn off after 4 hrs of non-use to save battery
- Connectivity to Mobile App - Helps you to set up and navigate your headset via the 3M Connected Equipment Mobile App
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- In the Box - 1 x Headset, 2 x AA batteries, 1 x User Instruction, 1 x Hygiene Kit, 1 x Wind protection for the mic



MRX21A3WS6-AZ

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100205577	UU010322954	•	•	MRX21A3WS6-AZ	3M™ PELTOR™ WS™ ALERT™ XPI Headset Headband, Bluetooth® APP, MRX21A3WS6-AZ, Yellow, SLC ₈₀ 30dB (Class 5), 1 Each
7100205576	UU010322962	•	•	MRX21P3EWS6-AZ	3M™ PELTOR™ WS™ ALERT™ XPI Headset Helmet Mounted, Bluetooth® APP, MRX21P3E3WS6-AZ, Yellow, SLC ₈₀ 29dB (Class 5), 1 Each

Communications

3M™ PELTOR™ WS™ Alert™ XPI Headset Accessories



HY82



MT53N-14/1



M995/2



MT53V/1



HY100A



FP9007



HYM1000



393-3001-2



Z3G (25mm)



Z3GS (25mm)



Z3AF/2

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)
7000103752	XA007702625	•	•	Z3AF/2	3M™ Versaflo™ Back Plate Kit, Left and Right, Helmet Adapter for M-300

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100113964	UU008197921	•	•	HY82	3M™ PELTOR™ Hygiene Kit HY82, 1 Each
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•	•	FP9007	3M™ PELTOR™ Padded Headset Bag FP9007, Black

Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100264326	UU011614862	•	•	MT53N-14/1	3M™ PELTOR™ Electret Boom Microphone, MT53N-11/1, 240mm with Plug Including Windshield M995/2, 1 Each
7010044372	XH001679154	•	•	M995/2	3M™ PELTOR™ Windshield for Electret Boom Microphone M995/2
7100098955	UU008013581	•	•	MT53V/1	3M™ PELTOR™ Boom Microphone MT53V/1, Electret, for Versaflo M-300 Helmet, 1 Each
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each

3M™ E-A-Rfit™ Dual-Ear Validation System - Probe

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™ WS™ ALERT™ XPV Solar Powered Headset

Bluetooth® MultiPoint headset with noise-cancelling microphone is self-charging by photovoltaic power and connects to a mobile app to more easily set-up and adjust the headset. The headset helps to protect the user against hazardous noise, but also makes it easy to make phone calls with both hands-free in noisy environments.

Features and Benefits:

- Multifunction Button (Choose between pre-defined functions)
- Music and Pod Mode
- Support Qualcomm® aptX™ HD
- WAP (Work Audio Profiles)
- Bluetooth® MultiPoint technology for connection to one or two external Bluetooth devices for hands-free talk and streaming
- Noise-cancelling boom microphone for clear speech transmission in noisy environments
- Level-dependent function for ambient listening to help promote auditory situational awareness
- Self-charging consisting of a seamlessly integrated solar cell material that converts all forms of light, both indoors and outdoors into sustainable electrical energy
- Connection to an iOS and Android compatible mobile app to more easily set-up, adjust settings, and view power status of the headset. The 3M™ Connected Equipment mobile app is available to download from App Store and Google Play
- Over-the-Air (OTA) firmware update
- Push-to-Listen feature to listen to your surroundings easily and instantaneously
- Voice-guided menu system
- Auto power off: The headset will turn off after 4 hours of non-use to save battery
- Low-battery warning at low battery level
- Replaceable cushions (hygiene kit)
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x Headset (Lithium Ion Battery inbuilt), 1 x User Instructions

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



Accessories



QR-CM-14

Scan or Click for
Tech Data Sheet

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100282733	UU012025084	•	•	MRX21A1WS7	3M™ PELTOR™ WS™ ALERT™ XPV Headset Headband, Powerfyle™ Cell, Bluetooth®, APP, MRX21A1WS7, Green, SLC ₈₀ 27dB (Class 5), 1 Each

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100113964	UU008197921	•	•	HY82	3M™ PELTOR™ Hygiene Kit HY83, 1 Kit/Bag, 10 Bags/Case
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Case
7100064607	XH001655360	•	•	FP9007	3M™ PELTOR™ Padded Headset Bag FP9007, Black

Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100264326	UU011614862	•	•	MT53N-14/1	3M™ PELTOR™ Electret Boom Microphone, MT53N-11/1, 240mm with Plug Including Windshield M995/2, 1 Each
7010044372	XH001679154	•	•	M995/2	3M™ PELTOR™ Windshield for Electret Boom Microphone M995/2
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each

3M™ PELTOR™ WS™ ProTac XPI Headset

The 3M™ PELTOR™ WS™ ProTac XPI Headset is an active hearing protector that features Bluetooth® 4.2 connectivity. This enables work with both hands-free while taking calls via two-way radio or mobile phones. The ambient listening function lets users hear surrounding noise and converse with colleagues.

Features and Benefits:

- Bluetooth 4.2 including MultiPoint.
- FLX2 flex jack (for -111 headsets)
- Noise-cancelling water resistant speech microphone
- Support for Bluetooth A2DP, streaming (selectable in Set-up mode)
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002
- **In the Box** - 1 x Hearing Protector, 2 x AA batteries (non re-chargeable), 1 x User instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



MT15H7AWS6



QR-CM-15

Scan or Click for Tech Data Sheet

New QR Code Required

XXX

Scan or Click for Pushback Communication made easy

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100196045	UU010123527	•	•	MT15H7AWS6	3M™ PELTOR™ WS™ ProTac XPI Headset Headband, MT15H7AWS6, SLC ₈₀ 32dB (Class 5), 1 Each
7100195960	UU010123535	•	•	MT15H7P3EWS6	3M™ PELTOR™ WS™ ProTac XPI Headset Helmet Mounted, MT15H7P3EWS6, SLC ₈₀ 27dB (Class 5), 1 Each
7100195906	UU010123543	•	•	MT15H7AWS6-111	3M™ PELTOR™ WS™ ProTac XPI FLX2 Headset Headband, MT15H7AWS6-111, SLC ₈₀ 32dB (Class 5), 1 Each
7100195976	UU010123568	•	•	MT15H7BWS6-111	3M™ PELTOR™ WS™ ProTac XPI FLX2 Headset Neckband, MT15H7BWS6-111, SLC ₈₀ 29dB (Class 5), 1 Each
7100195961	UU010123550	•	•	MT15H7P3EWS6-111	3M™ PELTOR™ WS™ ProTac XPI FLX2 Headset Helmet Mounted, MT15H7P3EWS6-111, SLC ₈₀ 27dB (Class 5), 1 Each

Communications

3M™ PELTOR™ WS™ ProTac XPI Headset Accessories



Accessories - FLX2 Cables

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100197719	UU010126348	•		FLX2-111	3M™ PELTOR™ FLX2 Cable FLX2-111, Hytera PD7 Series, 1 Each
7100197556	UU010124293	•	•	FLX2-35	3M™ PELTOR™ FLX2 Cable FLX2-35, Icom 2-Pin Angled, 1 Each
7100197565	UU010124301	•		FLX2-44	3M™ PELTOR™ FLX2 Cable FLX2-44, Icom Multipin S8, 1 Each
7100197568	UU010126330	•	•	FLX2-64	3M™ PELTOR™ FLX2 Cable FLX2-64, Icom F34/F44, 1 Each
7100193170	UU010054110	•	•	FLX2-36	3M™ PELTOR™ FLX2 Cable FLX2-36, Kenwood 2-Pin, 1 Each
7100185797	UU009731132	•		FLX2-107	3M™ PELTOR™ FLX2 Cable Kenwood Multipin, FLX2-107, 1 Each
7100197566	UU010126314	•		FLX2-18	3M™ PELTOR™ FLX2 Cable FLX2-18, Motorola XTS Series, 1 Each
7100193228	UU009898113	•	•	FLX2-21	3M™ PELTOR™ FLX2 Cable FLX2-21, Motorola CP200/2-Pin, 1 Each
7100193227	UU009879477	•	•	FLX2-32	3M™ PELTOR™ FLX2 Cable FLX2-32, Motorola HT Series, 1 Each
7100185795	UU009731124	•	•	FLX2-63	3M™ PELTOR™ FLX2 Cable Motorola DP4000, FLX2-63, 1 Each
7100197572	UU010126322	•	•	FLX2-65	3M™ PELTOR™ FLX2 Cable FLX2-65, Motorola ex500/ex600, 1 Each
7100220865	UU010902672	•	•	FLX2-69	3M™ PELTOR™ FLX2 Cable FLX2-69, for Motorola M9 Plug, 1 Each
7100197718	UU010123584	•		FLX2-101	3M™ PELTOR™ FLX2 Cable FLX2-101, Sepura 800/900 Series, 1 Each
7100193229	UU009898071	•	•	FLX2-28	3M™ PELTOR™ FLX2 Cable FLX2-28, Mobile/DECT Phone, 1 Each
7100331614	UU013051055	•	•	FLX2-114	3M™ PELTOR™ FLX2 Cable to Motorola R7 FLX2-114, Fits -111 Headsets, 1 Each
7100329802	UU013035025	•	•	FLX2-115	3M™ PELTOR™ FLX2 Cable to Tait TP3 TP8 and TP9 Series FLX2-115, Fits -111 Headsets, 1 Each

Accessories - Ground Mechanic Adaptor

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100325526		•	•	FL61007-WS7	3M™ PELTOR™ WS Adapter G3, Ground Mechanic

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)
7000103752	XA007702625	•	•	Z3AF/2	3M™ Versaflo™ Back Plate Kit, Left and Right, Helmet Adapter for M-300

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100113964	UU008197921	•	•	HY83	3M™ PELTOR™ Hygiene Kit HY83, 1 Kit/Bag, 10 Bags/Case
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•		FP9007	3M™ PELTOR™ Padded Headset Bag FP9007, Black

Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100112094	UU008163634	•	•	MT73/1	3M™ PELTOR™ Water Resistant Standard Boom Microphone MT73/1, 1 Each
7100099097	UU008014308	•	•	MT7V/1	3M™ PELTOR™ Microphones for 3M™ Versaflo™ M-300 Helmets MT7V/1, 1 Each
7100112112	UU008159483	•		M171/2	3M™ Peltor™ Wind Protector, M171/2, 1 Each
7000039650	XH001652532	•	•	M60/2	3M™ PELTOR™ Cup Mic Windsock M60/2, 1 Each
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each


Accessories - Power

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100075338		•	•	ACK053	3M™ PELTOR™ ACK053 Rechargeable NiMH battery, 2100mAh, 1 Each
7100075611		•	•	FR09	3M™ PELTOR™ FR09 Power supply charging cable with USB connector, 1 Each
7000108521	XH001680194	•	•	FR08	3M™ PELTOR™ FR08 5V DC Power Supply with USB connector, 1 Each

3M™ E-A-Rfit™ Dual-Ear Validation System - Probe

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™ WS™ LiteCom Plus with Bluetooth®



3M™ PELTOR™ WS™ LiteCom Plus with Bluetooth® opens up a world of communication. You become a mobile, hands-free communication center, the built-in two-way radio and wireless connections to your computer and cell phone. You can take your calls, or stream music thanks to electronics that let you switch easily between functions.

The level-dependent technology lets you hear ambient sounds such as external alarm signals or approaching vehicles. It also allows face-to-face communication at close distance. Robust design (IP54 certified), clear controls and an intuitive menu system



Features and Benefits:

- Built in two-way radio communication
- Range of up to 2km depending on conditions
- **69 channels (LPD 433 MHz)**
- 121 subchannels
- IP54 certified
- Level-dependent function for ambient listening
- Connect different devices via Bluetooth® MultiPoint
- Rechargeable lithium-ion battery with up to 20 hours operating time
- Noise-cancelling waterproof microphone (IP68)
- Voice operated transmission (VOX)
- Auto power off function
- Battery status indication
- Voice guided menu system
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** – 1 x 3M™ PELTOR™ WS™ LiteCom Plus Headset, 1 x Battery (ACK081B/1), 1 x Power Supply FR08, 1 x Cable AL2AI (for ACK081B/1), 1 x Hygiene Kit HY83, 1 x Mic Tape HYM1000, 1 x User instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100204437	UU010265963	•	•	MT73H7A4310WS6AZ	3M™ PELTOR™ WS™ LiteCom Plus Headset Headband LPD 433 MHz Analog, MT73H7A4310WS6AZ, SLC ₈₀ 32dB (Class 5), 1 Each
7100204438	UU010265971	•	•	MT73H7B4310WS6AZ	3M™ PELTOR™ WS™ LiteCom Plus Headset Neckband LPD 433 MHz Analog, MT73H7B4310WS6AZ, SLC ₈₀ 30dB (Class 5), 1 Each
7100204439	UU010264578	•	•	MT73H7P3E4310WS6AZ	3M™ PELTOR™ WS™ LiteCom Plus Headset Helmet Mounted LPD 433 MHz Analog, MT73H7P3E4310WS6AZ, SLC ₈₀ 29dB (Class 5), 1 Each

Communications

3M™ PELTOR™ WS™ LiteCom Plus with Bluetooth® Accessories



Accessories - FLEX Cable

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100016085	XH001652029	•	•	FL6BR	3M™ PELTOR™ External Radio Patch Cord FL6BR, 1 Each

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adapters for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adapters for 3M Scott Safety Visor Z3GS/2 (25mm)
7000103752	XA007702625	•	•	Z3AF/2	3M™ Versaflo™ Back Plate Kit, Left and Right, Helmet Adapter for M-300

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100113964	UU008197921	•	•	HY83	3M™ PELTOR™ Hygiene Kit HY83, 1 Kit/Bag, 1 Each
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•	•	FP9007	3M™ PELTOR™ Padded Headset Bag FP9007, Black

Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100112094	UU008163634	•	•	MT73/1	3M™ PELTOR™ Water Resistant Standard Boom Microphone MT73/1, 1 Each
7100099097	UU008014308	•	•	MT7V/1	3M™ PELTOR™ Microphones for 3M™ Versaflo™ M-300 Helmets MT7V/1, 1 Each
7100112112	UU008159483	•	•	M171/2	3M™ Peltor™ Wind Protector, M171/2, 1 Each
7000039650	XH001652532	•	•	M60/2	3M™ PELTOR™ Cup Mic Windsock M60/2, 1 Each
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each


Accessories - Power

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100330766	UU013044324	•	•	ACK081B/1	3M™ PELTOR™ Rechargeable LI-ION Battery Pack ACK081B/1, 3,7 Volt, 2150mAh, 8Wh, 50 EA/Case (replaced ACK081)
7100088372	UU004895189	•	•	AL2AI	3M™ PELTOR™ Lite-Com™ Charging Cable AL2AI, 1 Each
7000108521	XH001680194	•	•	FR08	3M™ PELTOR™ FR08 Power Supply with USB connectors, 1 Each

3M™ E-A-Rfit™ Dual-Ear Validation System - Probe

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™ WS™ Litecom Pro III Headset



The 3M™ PELTOR™ WS™ LiteCom Pro III Headset is the next generation protective communication solution. With an integrated, programmable analog/digital two-way radio, Bluetooth® MultiPoint connectivity, noise-cancelling microphone, and level-dependent function for ambient listening, the WS™ LiteCom Pro III Headset not only helps protect you against hazardous noise, but also makes it easy to communicate in noisy environments and helps you maintain situational awareness.

Application: The 3M™ PELTOR™ WS™ LiteCom Pro III Headset offers wireless communication in noisy environments. Suitable for work in industrial and construction applications, where hands-free communication and hearing protection are needed.

Features and Benefits:

- Programmable analog/digital DMR two-way radio communication
- **Frequency range: 403 – 470 MHz**
- Bluetooth® MultiPoint functionality
- Watertight microphone (IP68)
- Level-dependent function for ambient listening
- Voice menu with multiple language selection
- Push-to-Listen function
- Rechargeable battery, Li-Ion
- Voice operated transmission (VOX)
- Busy channel indication
- External connection jack
- Auto power off function
- Battery status indication
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x 3M™ PELTOR™ WS™ LiteCom Pro III, Headset, 1 x Battery (ACK081B/1), 1 x Power Supply FR08, 1 x Cable AL2AI, 1 x Hygiene Kit HY83, 1 x Mic Tape HYM1000, 1 x User instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100098910	UU008013599	•	•	MT73H7A4D10EU	3M™ PELTOR™ WS™ LiteCom Pro III Headset Headband 403-470 MHz Analog/Digital, MT73H7A4D10EU, SLC ₈₀ 32dB (Class 5), 1 Each
7100098956	UU008013607	•	•	MT73H7B4D10EU	3M™ PELTOR™ WS™ LiteCom Pro III Headset Neckband 403-470 MHz Analog/Digital, MT73H7B4D10EU, SLC ₈₀ 30dB (Class 5), 1 Each
7100098974	UU008014241	•	•	MT73H7P3E4D10EU	3M™ PELTOR™ WS™ LiteCom Pro III Headset Helmet Mounted 403-470 MHz, Analog/Digital, MT73H7P3E4D10-EU, SLC ₈₀ 29dB (Class 5), 1 Each

Communications

3M™ PELTOR™ WS™ Litecom Pro III Headset Accessories



Accessories - FLEX Cable

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100016085	XH001652029	•	•	FL6BR	3M™ PELTOR™ External Radio Patch Cord FL6BR, 1 ea/Case

Accessories - Ground Mechanic Adaptor

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100325526		•	•	FL61007-WS7	3M™ PELTOR™ WS Adapter G3, Ground Mechanic

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adaptors for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adaptors for 3M Scott Safety Visor Z3GS/2 (25mm)
7000103752	XA007702625	•	•	Z3AF/2	3M™ VersaFlo™ Back Plate Kit, Left and Right, Helmet Adapter for M-300

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100113964	UU008197921	•	•	HY83	3M™ PELTOR™ Hygiene Kit HY83, 1 Kit/Bag, 10 Bags/Case
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Case
7100064607	XH001655360	•	•	FP9007	3M™ PELTOR™ Padded Headset Bag FP9007, Black

Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100112094	UU008163634	•	•	MT73/1	3M™ PELTOR™ Water Resistant Standard Boom Microphone MT73/1, 1 Each
7100099097	UU008014308	•	•	MT7V/1	3M™ PELTOR™ Microphones for 3M™ VersaFlo™ M-300 Helmets MT7V/1, 1 Each
7100112112	UU008159483	•	•	M171/2	3M™ Peltor™ Wind Protector, M171/2, 1 Each
7000039650	XH001652532	•	•	M60/2	3M™ PELTOR™ Cup Mic Windsock M60/2, 1 ea/Case
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each

Accessories - Power

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100330766	UU013044324	•	•	ACK081B/1	3M™ PELTOR™ Rechargeable LI-ION Battery Pack ACK081B/1, 3,7 Volt, 2150mAh, 8Wh, 50 EA/Case (replaced ACK081)
7100088372	UU004895189	•	•	AL2AI	3M™ PELTOR™ Lite-Com™ Charging Cable AL2AI, 1 Each
7000108521	XH001680194	•	•	FR08	3M™ PELTOR™ FR08 Power Supply with USB connectors, 1 Each

3M™ E-A-Rfit™ Dual-Ear Validation System - Probe

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™ CH-3 FLX2 Listen Only Ex Hearing Protector



The 3M™ PELTOR™ CH-3 FLX2 Listen Only Ex Hearing Protector will bring hearing protection and communication in noisy environments into a new level of performance with newly designed speakers. The newly designed dual mould cup gives a modern and slim look, along with a bright blue colour to indicate Ex/IS certified design.



Features and Benefits:

- IECEx/ATEX/UKEX/ Ex/IS/CSA approved for use in areas where intrinsic safety is required
- Bright blue colour indicates Ex/IS certified design
- Slim cup design
- Detachable down lead connector for high flexibility
- Improved speaker efficiency to fit today's digital device
- Newly designed headband
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x Headset, 1 x User Instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



HT52A-112-50



HT52P3E-112-50

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100203639	UU010250916	•	•	HT52A-112-50	3M™ PELTOR™ CH-3 Listen Only FLX2 Ex Headset Headband, HT52A-112-50, SLC ₉₀ 31dB (Class 5), 1 Each
7100203297	UU010250924	•	•	HT52P3E-112-50	3M™ PELTOR™ CH-3 Listen Only FLX2 Ex Headset Helmet Mounted, HT52P3E-112-50, SLC ₉₀ 29dB (Class 5), 1 Each

Communications

3M™ PELTOR™ CH-3 FLX2 Listen only Ex Hearing Protector Accessories



HY84



HY100A



FP9007



Z3G (25mm)



Z3GS (25mm)

Accessories - FLX2 Cables

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100185762	UU009731157	•	•	FLX2-203-50	3M™ PELTOR™ FLX2 Cable 2,5mm Mono Ex Approved, FLX2-203-50, 120 ea/Case
7100185800	UU009731165	•	•	FLX2-205-50	3M™ PELTOR™ FLX2 Cable 3,5mm Mono Ex Approved, FLX2-205-50, 1 Each

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100212095	UU010391918	•	•	HY84	3M™ PELTOR™ Hygiene Kit HY84, for CH-3 FLX2 Headset, 1 Each
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•		FP9007	3M™ PELTOR™ Padded Headset Bag FP9007, Black

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adaptors for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adaptors for 3M Scott Safety Visor Z3GS/2 (25mm)

3M™ E-A-Rfit™ Dual-Ear Validation System - Probe

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™
TWIN CUP™ Headset IECEx/ATEX



QR-CM-20

Scan or Click for
Tech Data Sheet

The PELTOR™ TWIN CUP™ Headset IECEx/ATEX has high-attenuating shells with optimised acoustic design and excellent space for the ears. Noise-cancelling boom microphone for clear and reliable communication.

Features and Benefits:

- IECEx/ATEX/UKEX/CSA approved for use in areas where intrinsic safety is required
- Dynamic noise-cancelling microphone
- Twin-Cup technique for increased attenuation
- **No ANZEx Certification - Product can not be used where ANZEx Certification is required.**
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x Headset, 1 x User Instruction

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



MT7H72H540A

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100271680	UU011743018	•	•	MT72H540A-50	3M™ PELTOR™ Twin Cup Headset Headband IECEx/ATEX, MT72H540A-50, SLC ₈₀ 31dB (Class 5), 1 Each
7000108283	XH001674254	•	•	MT72H540P3E-50	3M™ PELTOR™ Twin Cup Headset Helmet Mounted IECEx/ATEX, MT72H540P3E-50, SLC ₈₀ 30dB (Class 5), 1 Each

Communications

3M™ PELTOR™ TWIN CUP™ Headset IECEx/ATEX Accessories



HY13



MT171/2



HYM1000



HY100A



FP9007



393-3001-2



Z3G (25mm)



Z3GS (25mm)

Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adaptors for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adaptors for 3M Scott Safety Visor Z3GS/2 (25mm)

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000108013	XH001659297	•	•	HY13	3M™ PELTOR™ Hygiene Kit HY13, for H10/H540 Headsets, 1 Each
7100112112	UU008159483	•		M171/2	3M™ PELTOR™ Wind Protector, M171/2, 1 Each
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Carton
7100064607	XH001655360	•		FP9007	3M™ PELTOR™ Padded Headset Bag FP9007, Black

3M™ E-A-Rfit™ Dual-Ear Validation System - Probe

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100123728	70071676285	•	•	393-3004-2	3M™ PELTOR™ Probed Earmuff Test Cushions A, 393-3004-2, 2 Pairs/Case

3M™ PELTOR™ WS™ LiteCom Pro III Ex Headset ANZEx Certified


The 3M™ PELTOR™ WS™ LiteCom Pro III Ex Headset ANZEx Certified is the next generation protective communication solution. With an integrated, programmable analog/digital two-way radio, Bluetooth® MultiPoint connectivity, **noise-cancelling microphone**, and level-dependent function for ambient listening, the 3M™ PELTOR™ WS™ LiteCom Pro III Ex Headset ANZEx Certified not only helps protect you against hazardous noise, but also makes it easy to communicate in noisy environments and helps you maintain situational awareness.

Application: The 3M™ PELTOR™ WS™ LiteCom Pro III Ex Headset, ANZEx-certified, offers wireless communication in noisy environments. Can be used for work in Oil & Gas Industry, Mining and where intrinsic safety products are required. Approved for use in potentially explosive environments in accordance with the ANZEx scheme and the IECEx scheme for dust, gas and underground mining.

Features and Benefits:

- Programmable analog/digital DMR two-way radio communication
- **Frequency range: 403 – 470 MHz**
- Bluetooth® MultiPoint functionality
- IS (Intrinsically Safe) approval ANZEx/IECEx/ATEX
- Watertight microphone (IP68)
- Level-dependent function for ambient listening
- Voice menu with multiple language selection
- Push-to-Listen function
- Rechargeable battery, Li-Ion
- Voice operated transmission (VOX)
- Busy channel indication
- External connection jack
- Auto power off function
- Battery status indication
- Testable with the 3M™ E-A-Rfit™ Validation System
- Complies with Australian/New Zealand Standard AS/NZS 1270:2002.
- **In the Box** - 1 x 3M™ PELTOR™ WS™ LiteCom Pro III Ex Headset, 1 x Battery (ACK082), 1 x Power Supply FR08, 1 x Cable AL2AH (for ACK082), 1 x Hygiene Kit HY83, 1 x Mic Tape HYM1000, 1 x User Instruction, 1 x Intrinsic Safety Guide

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



MT73H7F4D10EU-50



MT73H7P3E4D10EU-50



MT73H7B4D10EU-50

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100098897	UU008014225	•	•	MT73H7F4D10EU-50	3M™ PELTOR™ WS™ LiteCom Pro III EX Headset Headband 403-470 MHz Analogue/Digital, MT73H7F4D10EU-50, SLC ₈₀ 32dB (Class 5), 1 Each
7100098836	UU008014233	•	•	MT73H7P3E4D10EU-50	3M™ PELTOR™ WS™ LiteCom Pro III EX Headset Helmet Mounted 403-470 MHz Analog/Digital, MT73H7P3E4D10EU-50, SLC ₈₀ 29dB (Class 5), 1 Each
7100098898	UU008014217	•	•	MT73H7B4D10EU-50	3M™ PELTOR™ WS™ LiteCom Pro III EX Headset Neckband 403-470 MHz Analogue/Digital, MT73H7B4D10EU-50, SLC ₈₀ 30dB (Class 5), 1 Each

Communications

3M™ PELTOR™ WS™ Litecom Pro III Ex Headset ANZEx Certified Accessories



Accessories - Helmet Adaptors/Backplates

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100383334	XL001642484	•	•	Z3G/2	3M™ PELTOR™ Helmet Adaptors for 3M Visor Range Z3G/2 (25mm)
7100383325	UU010853503	•	•	Z3GS/2	3M™ PELTOR™ Helmet Adaptors for 3M Scott Safety Visor Z3GS/2 (25mm)
7000103752	XA007702625	•	•	Z3AF/2	3M™ Versaflo™ Back Plate Kit, Left and Right, Helmet Adapter for M-300

Accessories - Hygiene

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100113964	UU008197921	•	•	HY83	3M™ PELTOR™ Hygiene Kit HY83, 1 Kit/Bag, 10 Bags/Case
7100064410	XH001651351	•	•	HY100A	3M™ PELTOR™ Clean Hygiene Pads HY100A, 100 Pairs/Case
7100064607	XH001655360	•	•	FP9007	3M™ PELTOR™ Padded Headset Bag FP9007, Black

Accessories - Microphone

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100112094	UU008163634	•	•	MT73/1	3M™ PELTOR™ Water Resistant Standard Boom Microphone MT73/1, 1 Each
7100099097	UU008014308	•	•	MT7V/1	3M™ PELTOR™ Microphones for 3M™ Versaflo™ M-300 Helmets MT7V/1, 1 Each
7100112112	UU008159483	•	•	M171/2	3M™ PELTOR™ Wind Protector, M171/2, 1 Each
7000039650	XH001652532	•	•	M60/2	3M™ PELTOR™ Cup Mic Windsock M60/2, 1 ea/Case
7100064281	AT010580697 (AU) XH001651328 (NZ)	•	•	HYM1000	3M™ PELTOR™ Hygiene Tape for Microphone, HYM1000, 4.5 M, 1 Each

Accessories - Power

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100112102	UU008176040	•	•	ACK082	3M™ PELTOR™ Rechargeable Li-Ion Battery, ACK082, for 3M™ PELTOR™ WS™ Litecom Pro III Ex, 1 Each
7100067410	11003072094	•	•	AL2AH	3M™ PELTOR™ Charging Cable, AL2AH, 1 EA/Case
7000108521	XH001680194	•	•	FR08	3M™ PELTOR™ FR08 Power Supply with USB connectors, 1 Each

3M™ E-A-Rfit™ Dual-Ear Validation System - Probe

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ X1/X2 Earmuff Probed Test Cushions B, 393-3001-2, 2 ea/Kit

3M™ PELTOR™ WS™ Adapter G3, Ground Mechanic for Aircraft Pushback Operation

Introducing the 3M™ PELTOR™ WS™ Adapter G3, Ground Mechanic - the ultimate solution for ramp communication during aircraft pushback operations. With our expertise in Bluetooth technology, we provide a safe and reliable wireless connection that revolutionises ground crew communication.



Features and Benefits:

- Detachable and rechargeable Li-Ion battery pack
- Clear, green-LED battery status indicators for best visibility in bright sunlight
- Easy-to-use 2-button operation
- Wideband audio supports better sound quality
- Enhanced duplex performance
- Low latency minimises echo sounds
- Connector strain relief with an enlarged and robust grip area
- IP54 classified
- Compliant with both WS ProTac XPI and WS LiteCom headsets
- **In the box**
 - 1x 3M PELTOR WS Adapter G3
 - 1x Safety Hook
 - 1x Rechargeable battery pack
 - 1x “REMOVE BEFORE FLIGHT” flag
 - 1x User instructions

Note: 3M recommends replacing the hygiene kit every six months to maintain acceptable noise reduction, hygiene and comfort. In hot and humid environments more frequent changes may be required to maintain acceptable hygiene.



SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100325526		•	•	FL61007-WS7	3M™ PELTOR™ WS Adapter G3, Ground Mechanic



TKD5005/SP



DE0352/SP



FE0352/SP



ACK081B/1



AL2AI/SP*



FR08*

Accessories

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100245137		•	•	TKD5005/SP	Clip
7100332577		•	•	DE0352/SP	Safety hook
7100331988		•	•	FE0352/SP	“REMOVE BEFORE FLIGHT” flag
7100330766	UU013044324	•	•	ACK081B/1	3M™ PELTOR™ Rechargeable LI-ION Battery Pack ACK081B/1, 3,7 Volt, 2150mAh, 8Wh, 50 EA/Case (replaced ACK081)
7100088372	UU004895189	•	•	AL2AI/SP	3M™ PELTOR™ Lite-Com™ Charging Cable AL2AI, 1 Each
7000108521	XH001680194	•	•	FR08	3M™ PELTOR™ FR08 Power Supply with USB connectors, 1 Each

* Not included in the box. Sold separately.

Communications

3M™ PELTOR™ Handheld PTT Adapters



FL5035



FL5046



FLX2-201

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7000039629	XH001651021	•		FL5035	3M™ PELTOR™ MT Series In-Line PTT Adaptor FL5035, Kenwood, 1 EA/Case
7000107881	XH001654256	•		FL5044	FL5044 Adaptor ICOM F31/F41, F51/F61
7000039661	XH001654314	•		FL5063	3M™ PELTOR™ PTT Adaptor FL5063, Motorola Turbo, 1 EA/Case
7000108319	XH001675269	•		FL50101	3M™ PELTOR™ PTT Adapter FL50101, for Sepura Testra STP8000
7000108481	XH001679352	•		FL5046	3M™ PELTOR™ PTT Adapter FL5046, for Icom™ A3E, A6, A15, A22E, A24 Airband
7100207323	UU010325718	•	•	FLX2-201	3M™ PELTOR™ FLX2 Airline Cable FLX2-201



Science.
Applied to Life.™



3M™ E-A-Rfit™ Dual-Ear Validation System

ID:1921084
RD:1927093

3M™ E-A-Rfit™ Dual-Ear Validation System utilizes F-MIRE technology to measure and obtain an objective, quantitative level of worker hearing protection in under 5 seconds. Workers receive their own personal attenuation rating (PAR) and learn how correctly inserting earplugs can increase their level of protection.

3M™ E-A-Rfit™ Dual-Ear Validation System.

Get results you can trust. The E-A-Rfit™ Dual-Ear Validation System measures the effectiveness of the hearing protection for both ears, providing accurate, quantitative results. And because you can simultaneously test both ears, you'll have more time to educate Worker's on the importance of fit and compliance.



CLICK HERE

to view E-A-Rfit™ Validation System brochure.

① Fit.

Have the employee insert their earplugs or put on their earmuffs.

② Test.

Connect to microphones and begin speaker test sound.

③ Assess.

Use PAR to customize hearing protector selection.

The challenge of hearing protection.

How do you know if your workforce is protected?

Protecting workers from hazardous noise levels is an ongoing challenge for many organizations. One of the most commonly recorded occupational illnesses in the manufacturing sector is permanent hearing loss. The success of your safety program depends on many factors and requires more than just offering hearing protection.

Individual Fit Testing Using F-MIRE.

Using F-MIRE (Field Microphone-In-Real-Ear) technology, the E-A-Rfit™ Dual-Ear Validation System generates a Personal Attenuation Rating (PAR) less than 5 seconds for both ears, taking into account the seven standard measured testing frequencies.

- Measures how well 3M's most popular earplugs, earmuffs and communications headsets perform
- Delivers a quantitative measurement of personal noise reduction for each Worker
- Can help identify whether or not the Worker has adequate protection




CLICK HERE

to view the 3M™ E-A-Rfit™
Dual-Ear Validation System
Short Introduction Video











3M™ E-A-Rfit™ Dual-Ear Validation System & Accessories

[CLICK HERE](#) for the 3M™ E-A-Rfit™ Global Cross Over Guide

Product	SAP ID	Legacy ID	Availability		Model #	Description	Case Qty
			AUS	NZ			
	7100062125	70071674116	•	•	393-1100	3M™ E-A-Rfit™ Dual-Ear Validation System 393-1100 • In conformance with ANSI/ASA S12.71-2018.	1EA
	7100077867	70071674694	•	•	073-781	3M™ E-A-Rfit™ Dual-Ear Microphone Assembly 073-781	1EA
	7100105873	70071676160	•		073-100	3M™ E-A-Rfit™ Dual-Ear Microphone Assembly Replacement Clips 073-100, 10 ea/Pack	x10 Clips per pack





Testing Probes

Disposables




Product	SAP ID	Legacy ID	Availability		Model #	Description	Case Qty
			AUS	NZ			
	7000052884	70071562816	•	•	393-2007-50	3M™ E-A-Rfit™ Classic™ Platinum™ Probed Test Plugs 393-2007-50	50 PR/Case (5 bags of 10 pair each)
	7000052882	70071562774	•	•	393-2003-50	3M™ E-A-Rfit™ Classic™ Probed Test Plugs 393-2003-50	50 PR/Case (5 bags of 10 pair each)
	7000002409	70071577772	•	•	393-2010-50	3M™ E-A-Rfit™ 1100 Probed Test Plugs, 393-2010-50	50 PR/Case (5 bags of 10 pair each)
	7100069736	70071562741	•	•	393-2000-50	3M™ E-A-Rfit™ E-A-Rsoft™ Yellow Neons™ Probed Test Plug 393-2000-50	50 PR/Case (5 bags of 10 pair each)
	7000148551	70071650249	•	•	393-2014-50	3M™ E-A-Rfit™ E-A-R™ Yellow Neon™ Large Test Plug 393-2014-50	50 PR/Case (5 bags of 10 pair each)
	7000002388	70071562808	•		393-2006-50	3M™ E-A-Rfit™ TaperFit™ 2 Probed Test Plugs, 393-2006-50	50 PR/Case (5 bags of 10 pair each)
	7100230133	70071733557	•	•	393-2027-50	3M™ E-A-R™ TaperFit™ 2 Large Probed Test Plugs 393-2027-50	50 PR/Case (5 bags of 10 pair each)
	7000052883	70071562782	•	•	393-2004-50	3M™ E-A-Rfit™ E-A-Rsoft™ FX™ Probed Test Plugs 393-2004-50	50 PR/Case (5 bags of 10 pair each)

E-A-Rfit™ Validation


Push-To-Fit

Product	SAP ID	Legacy ID	Availability		Model #	Description	Case Qty
			AUS	NZ			
	7000052881	70071562766	•	•	393-2002-50	3M™ E-A-Rfit™ E-A-R™ Push-Ins™ Probed Test Plug, 393-2002-50	50 PR/Case (5 bags of 10 pair each)
	7000052879	70071562725	•	•	393-2008-50	3M™ E-A-Rfit™ E-A-R™ Express™ PodPlugs™ Probed Test Plugs 393-2008-50	50 PR/Case (5 bags of 10 pair each)
	7000128264	70071647757	•	•	393-2012-50	3M™ E-A-Rfit™ Skull Screws™ Probed Test Plugs 393-2012-50	50 PR/Case (5 bags of 10 pair each)
	7100033339	70071650231	•	•	393-2013-50	3M™ No Touch™ Probed Test Plugs 393-2013-50	50 PR/Case (5 bags of 10 pair each)




Reusable

Product	SAP ID	Legacy ID	Availability		Model #	Description	Case Qty
			AUS	NZ			
	7000002387	70071562758	•	•	393-2001-50	3M™ E-A-Rfit™ E-A-R™ UltraFit™ Probed Test Plug 393-2001-50	50 PR/Case (5 bags of 10 pair each)
	7010386152	70071675626		•	393-2024-50	1290 Probed Test Plug, 393-2024-50	50 PR/Case (5 bags of 10 pair each)
	7000128263	70071647740	•	•	393-2011-50	3M™ E-A-Rfit™ Tri-Flange™ Probed Test Plugs 393-2011-50	50 PR/Case (5 bags of 10 pair each)

In Ear Earplug Probe Range

Product	SAP ID	Legacy ID	Availability		Model #	Description	Case Qty
			AUS	NZ			
	7100225703	70071734431	•	•	393-2030-50	3M™ Skull Screws/Torque™ (regular and metal detectable), 393-2030-50	50 PR/Case (5 bags of 10 pair each)
	7100225704	70071734449	•	•	393-2031-50	CCC-GRM-25, 393-2031-50, CCC-GRM-25	50 PR/Case (5 bags of 10 pair each)
	7100225700	70071734456	•	•	393-2032-50	3M™ UltraFit™ Small, 393-2032-50, UltraFit Sm	50 PR/Case (5 bags of 10 pair each)
	7100225705	70071734464	•	•	393-2033-50	3M™ UltraFit™ Medium, 393-2033-50, UltraFit Med	50 PR/Case (5 bags of 10 pair each)
	7100225706	70071734472	•	•	393-2034-50	3M™ UltraFit™ Large, 393-2034-50, UltraFit Lg	50 PR/Case (5 bags of 10 pair each)

Probed Muffs

Product	SAP ID	Legacy ID	Availability		Model #	Description	Case Qty
			AUS	NZ			
	7100123728	70071676285	•	•	393-3004-2	3M™ PELTOR™ Earmuff Probed Test Cushion A EARMUFFS <ul style="list-style-type: none"> 3M™ PELTOR™ Optime III™ (All Versions) HEADSETS <ul style="list-style-type: none"> 3M™ PELTOR™ TWIN CUP™ (Helmet Attach) 	2EA/Case (2 pair each per case)
						3M™ PELTOR™ Earmuff Probed Test Cushion B EARMUFFS <ul style="list-style-type: none"> 3M™ PELTOR™ Optime I™ (All Versions) 3M™ PELTOR™ Optime II™ (All Versions) H505B Welding Earmuff, Neckband HEADSETS <ul style="list-style-type: none"> 3M™ PELTOR™ Wortunes™ Pro™ AM/FM 3M™ PELTOR™ ProTac™ III (All Versions) 3M™ PELTOR™ CH-3 FLX2 (All Versions Incl. ATEX CH-3)* 3M™ PELTOR™ WS™ Alert™ X, Headband, MRX21A4WS6* (Foam Cushions) 3M™ PELTOR™ WS™ ProTac XPI (All Versions) 3M™ PELTOR™ LiteCom Plus 3M™ PELTOR™ WS™ LiteCom Plus <ul style="list-style-type: none"> All Versions M-300 Versaflo™ Headtop Attach 3M™ PELTOR™ WS™ LiteCom Pro III <ul style="list-style-type: none"> All Versions M-300 Versaflo™ Headtop Attach 3M™ PELTOR™ ComTac™ XPI (Folding Headband) 3M™ PELTOR™ ComTac™ VI (Folding Headband and Neckband) 3M™ PELTOR™ ComTac™ VIII Headset, Headband, MT14H418A* (Foam Cushions) 3M™ PELTOR™ ComTac™ VIII Headset, Headband, MT14H418A* (Gel Cushions) 3M™ PELTOR™ ComTac™ VII (Headband) 	
						3M™ PELTOR™ Earmuff Probed Test Cushion D EARMUFFS <ul style="list-style-type: none"> 3M™ PELTOR™ X4 Series (All Versions)* 3M™ PELTOR™ X5 Series (All Versions)* HEADSET <ul style="list-style-type: none"> 3M™ PELTOR™ CH-5 (All Versions) 	
	7100062126	70071691110	•	•	393-3001-2	3M™ PELTOR™ Earmuff Probed Test Cushion B EARMUFFS <ul style="list-style-type: none"> 3M™ PELTOR™ Optime I™ (All Versions) 3M™ PELTOR™ Optime II™ (All Versions) H505B Welding Earmuff, Neckband HEADSETS <ul style="list-style-type: none"> 3M™ PELTOR™ Wortunes™ Pro™ AM/FM 3M™ PELTOR™ ProTac™ III (All Versions) 3M™ PELTOR™ CH-3 FLX2 (All Versions Incl. ATEX CH-3)* 3M™ PELTOR™ WS™ Alert™ X, Headband, MRX21A4WS6* (Foam Cushions) 3M™ PELTOR™ WS™ ProTac XPI (All Versions) 3M™ PELTOR™ LiteCom Plus 3M™ PELTOR™ WS™ LiteCom Plus <ul style="list-style-type: none"> All Versions M-300 Versaflo™ Headtop Attach 3M™ PELTOR™ WS™ LiteCom Pro III <ul style="list-style-type: none"> All Versions M-300 Versaflo™ Headtop Attach 3M™ PELTOR™ ComTac™ XPI (Folding Headband) 3M™ PELTOR™ ComTac™ VI (Folding Headband and Neckband) 3M™ PELTOR™ ComTac™ VIII Headset, Headband, MT14H418A* (Foam Cushions) 3M™ PELTOR™ ComTac™ VIII Headset, Headband, MT14H418A* (Gel Cushions) 3M™ PELTOR™ ComTac™ VII (Headband) 	2EA/Case (2 pair each per case)
						3M™ PELTOR™ Earmuff Probed Test Cushion D EARMUFFS <ul style="list-style-type: none"> 3M™ PELTOR™ X4 Series (All Versions)* 3M™ PELTOR™ X5 Series (All Versions)* HEADSET <ul style="list-style-type: none"> 3M™ PELTOR™ CH-5 (All Versions) 	
						3M™ PELTOR™ Earmuff Probed Test Cushion D EARMUFFS <ul style="list-style-type: none"> 3M™ PELTOR™ X4 Series (All Versions)* 3M™ PELTOR™ X5 Series (All Versions)* HEADSET <ul style="list-style-type: none"> 3M™ PELTOR™ CH-5 (All Versions) 	
	7100062128	70071691136	•	•	393-3005-2	3M™ PELTOR™ Earmuff Probed Test Cushion D EARMUFFS <ul style="list-style-type: none"> 3M™ PELTOR™ X4 Series (All Versions)* 3M™ PELTOR™ X5 Series (All Versions)* HEADSET <ul style="list-style-type: none"> 3M™ PELTOR™ CH-5 (All Versions) 	2EA/Case (2 pair each per case)
						3M™ PELTOR™ Earmuff Probed Test Cushion D EARMUFFS <ul style="list-style-type: none"> 3M™ PELTOR™ X4 Series (All Versions)* 3M™ PELTOR™ X5 Series (All Versions)* HEADSET <ul style="list-style-type: none"> 3M™ PELTOR™ CH-5 (All Versions) 	
						3M™ PELTOR™ Earmuff Probed Test Cushion D EARMUFFS <ul style="list-style-type: none"> 3M™ PELTOR™ X4 Series (All Versions)* 3M™ PELTOR™ X5 Series (All Versions)* HEADSET <ul style="list-style-type: none"> 3M™ PELTOR™ CH-5 (All Versions) 	

NOTES:

1) E-A-Rfit™ can only be used to fit test the specific 3M hearing protectors listed in the Crossover Product column using the corresponding test probe. E-A-Rfit™ test results are not valid for any other 3M or non-3M hearing protectors <https://multimedia.3m.com/mws/media/1650261O/3m-earfit-global-crossover-guide.pdf>.

2) If the earmuffs are worn in conjunction with a liftable visor, the visor should be in the up position when fit testing.

* Remove gray back plate from the probed test cushion when fit testing all CH-3 headsets.



Fit Testing

3M strongly recommends personal fit testing of hearing protectors. Research suggests that users may receive less noise reduction than indicated by the attenuation label value(s) on the packaging due to variation in fit, fitting skill, and motivation of the user.

Warning

These hearing protectors help reduce exposure to hazardous noise and other loud sounds. Misuse or failure to wear hearing protectors at all times that you are exposed to noise may result in hearing loss or injury. For proper use, see supervisor or User Instructions.

Always ensure the hearing protection device (HPD) is:

- **Suitable for the application;**
- **Fitted correctly;**
- **Worn during all periods of exposure;**
- **Replaced when necessary.**

If there is any drainage from your ear or you have an ear infection, consult with your physician before wearing earplugs.

PSD products are occupational use only.



3M Australia Pty Ltd

Bld A, 1 Rivett Road
North Ryde, NSW 2113
Customer Services: 1300 363 565
Email: 3msupport.safety.au@mmm.com
3M.com.au/ppesafety

3M New Zealand Limited

94 Apollo Drive
Rosedale, Auckland 0632
Customer Services: 0800 252 627
Email: 3msupport.safety.nz@mmm.com
3M.com/nz/ppesafety

3M is a trademark of 3M Company.
Please recycle.

© 3M 2025. All rights reserved. 3M, Adjust-a-Net, Anchor on the Go, Aura, DBI-SALA, Delta, Duo-Lok, ExoFit NEX, ExoFit STRATA, Evolution, EZ-Link, EZ-Stop, Fast-Line, First, First-Man-Up, FlexiGuard, Force2, Glyder, HI-10, Lad-Saf, LIFTech, Mobi-Lok, Nano-Lok, PolarMesh, PRO-Line, Protecta, RailDog, Raillok, Rebel, REPEL, Revolver, Rollgliss, RoofSafe, Rope-Mate, Rope-Safe, Saflok, Sayflite, SafRig, SecuraSpan, Tech-Lite, Ultra-Lok, UniRail, Uni-8 and WrapBax are trademarks of 3M Company.

PSD Products are Occupational Use Only. 3M, PELTOR, E-A-R, E-A-Rfit, Versaflo, SportTac, ProTac, WS, ALERT, Optime, X4, X5, H505B, CH-3, LiteCom Plus, ComTac, Classic, E-A-Rsoft, FX, Yellow Neons, Taperfit, Express Pod plugs, Push Ins, UltraFit, Skull Screws, Pistonz, Tri-Flange, No Touch, Superfit are trademarks of 3M. Bluetooth is trade mark of Bluetooth Inc. All other marks are the property of their respective owner.

Product and Content accurate at the time of publication. Products and product information is subject to change. Application images may show product not available in ANZ. Note: 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence or fraudulent misrepresentation