



Introducing the new

3M™ Clean Sanding System

Designed with technicians
and shop owners in mind.

The 3M™ Clean Sanding System is a complete sanding solution for efficiently moving through your essential surface preparation and finishing work. The system includes our dust extractor, pneumatic and/or electric random orbital sanders, mobile workstation, wide selection of quality abrasives, and personal protective equipment.



Designed to reduce dust in the air from sanding for a cleaner workspace.



Helps shops boost productivity and efficiency by helping to reduce rework and cleanup time.



Compact and mobile. Designed for easy, flexible use around the shop.



Compatible with pneumatic and/or electric sanders.



Tech-friendly design including auto on/off, antistatic hose, rubber wheels, brake locks, and LED indicator lights.

Smarter. Faster. Cleaner.

A clean shop can mean less rework, better cycle times, and the peace of mind that you are doing what you can to improve the shop environment. For you, your technicians and your customers.



Dust Extractor

3M™ Dust Extractor

33755 45 Liter, 230V, Plug Type I

Orbital Sanders

3M™ Precision Random Orbital Sander

33632 150 mm (6 in), 2.5 mm (3/32) Orbit

33633 150 mm (6 in), 5 mm (3/16) Orbit

38505 75 mm (3 in), 5 mm (3/16) Orbit

3M™ Elite Orbital Sander

28529 70 mm x 198 mm, 1/8 in Orbit

Accessories

33645	3M™ Antistatic Pneumatic Hose
33765	3M™ Dust Extractor Handle Extension
33647	3M™ Dust Extractor Filter
33648	3M™ Dust Filter Bag
33652	3M™ Dust Extractor Y-Connector
33653	3M™ Clean Sanding System Workstation
33654	3M™ Clean Sanding System Workstation Extension
05174	3M™ Multi-Hole Block Hose, 6 m
05209	3M™ Hookit™ Sanding Block D/F, 70mm x 396mm
05208	3M™ Hookit™ Sanding Block D/F, 70mm x 198mm
05207	3M™ Hookit™ Sanding Block D/F, 70mm x 127mm
05216	3M™ Hookit™ Sanding Block D/F, 115mm x 225mm
50728	3M™ Hookit™ Purple+ Curved Adapter Set Multi-Hole, 70 mm x 127 mm
50545	3M™ Hookit™ Soft Interface Pad, 150 mm x 5 mm, Multi-Hole
50544	3M™ Hookit™ Soft Interface Pad, 150 mm x 10 mm, Multi-Hole



Automotive Aftermarket Division
3M Center
Building 223-06S-07
St. Paul, MN 55144-1000

For more information, visit us at
3M.com

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: 3M warrants this tool will be free of defects in workmanship and materials under normal operating conditions for two (2) years from the date of purchase by the initial end-user customer. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If this tool does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the tool or refund of the purchase price. User must operate the tool in accordance with all applicable instructions, safety precautions, and other procedures stated in the operating manual. 3M will have no obligation to refund the purchase price or to repair or replace any tool or part that fails as a result of normal wear, inadequate or improper maintenance, inadequate cleaning, nonlubrication, improper operating environment, improper utilities, operator error or misuse, alteration or modification, mishandling, lack of reasonable care, or any accidental cause. Warranty claims must be made within two (2) years from the date of the end-user customer's purchase.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com. 3M, Cubitron, Hookit and Stikit are trademarks of 3M COMPANY. All other trademarks are property of their respective owners. Please recycle. © 3M 2020. All rights reserved. 60-4402-8107-3