

**3M** Science.  
Applied to Life.™

Introducing the new

# 3M™ Performance Industrial Spray Gun

## Engineered for the industrial painter.

The 3M™ Performance Spray Gun is the industrial coating solution that can help reduce variability in your process and boost productivity by giving technicians a smarter way to spray.



# Throw down paint like a seasoned pro with a simple, intuitive design.

Lightweight and easy to use, the 3M™ Performance Spray Gun was built with the industrial painter in mind. Made from an advanced impact-resistant composite material, the spray gun is one of the lightest in the industry yet durable enough for the toughest industrial conditions. From the trigger to the body, the spray gun was optimised by kinesiologists to enhance comfort specifically for the high demands of all-day spraying.

With its versatile design, technicians can spray from either a pressurized source or a gravity cup. The pressure-fed hose and nozzles allow for continuous bulk spraying for larger jobs. Or for spot repairs and small areas, convert the spray gun to use the 3M™ PPS™ Series 2.0 Spray Cup System—so you use just the right amount of coating to match the size and finish of the job.

Simple, innovative design means fewer parts to maintain. With quick-change replaceable nozzles, paint never passes through the body of the spray gun. Cleanup can be as simple as wiping the tip of the needle and replacing the head – which means no more disassembling or soaking in solvent. It's like getting a brand new spray gun every time you put on a fresh nozzle. At sizes from 1.1mm to 2.0mm, 3M™ Performance Atomising Heads allow you to easily spray a wide range of coatings – from stains and primers to topcoats and even adhesives.





## Specifications

**Air Consumption:** 370 SLPM [13 SCFM]  
**Recommended Air Inlet Pressure:** 1.24 Bar  
**Maximum Operating Temperature:** 50 °C  
**Maximum Operating Overpressure:** 10 Bar  
**Weight:** 378 g  
**Air Inlet:** 1/4 BSP  
**Liquid Inlet:** 3/8 BSP  
**Nozzle Orifice Sizes:** 1.1mm, 1.4mm, 1.8mm



## Lightweight and Durable

One of the lightest spray guns in the industry, the impact-resistant composite body is built to withstand demanding industrial environments.



## Low Maintenance and Easy

Simple, intuitive design means fewer parts to maintain or rebuild and can help achieve more consistent performance whether you're a beginner or a pro.



## Replaceable Nozzles

With quick-change replaceable atomising heads ranging from 1.1mm to 2.0mm, it's like getting a brand new spray gun with every new nozzle.



## Built for Versatility

Sprays a wide range of coatings, including, stains, primers, basecoats, topcoats, clearcoats, and adhesives – from either a pressure-fed system or with 3M™ PPS™ Series 2.0 Spray Cup System.

## Spray Gun and Systems

### Part No. Components

**3M™ Performance Industrial Spray Gun System**  
26878 Spray gun, air control valve, pressure whip, pressure and gravity atomising heads, PPS™ Series 2.0

**3M™ Performance Spray Gun**  
26832 Spray gun and air control valve

## Replacement Parts and Accessories

### Part No. Product

**3M™ Performance Spray Gun**  
26833 Pressure Whip  
26839 Ball Valve  
26835 Locking Collar  
26840 Rebuild Kit  
26834 Whip Pin  
26838 Needle

## Atomising Head Refill Kits

Part No.	Colour	Size
<b>Pressure</b>		
26811	Yellow	1.1
26814	Orange	1.4
26818	Clear	1.8
26830	Variety Kit	3 sizes (1.1, 1.4, 1.8)
<b>Gravity</b>		
26712	Blue	1.2
26713	Green	1.3
26714	Orange	1.4
26716	Purple	1.6
26718	Clear	1.8
26720	Red	2.0
26730	Variety Kit	6 sizes (1.2, 1.3, 1.4, 1.6, 1.8, 2.0)

# Ditch the old systems.

The high-maintenance metal guns that require more fuss than they're worth, the spray cans, the paint brushes and rollers – try the new 3M™ Performance Spray Gun and help bring consistency and quality back into your paint operations.



For industrial/occupational use only.  
Not for consumer sale or use.



**3M Automotive Aftermarket Division**  
Building A, 1 Rivett Rd  
North Ryde, NSW, 2113

Phone 136-136  
Web [www.3M.com.au/collisionrepair](http://www.3M.com.au/collisionrepair)

**3M Automotive Aftermarket Division**  
94 Apollo Drive  
Rosedale, Albany  
North Shore City Auckland

Phone 0800 362 886  
Web [www.3M.co.nz/collisionrepair](http://www.3M.co.nz/collisionrepair)

3M and PPS are trademarks of 3M Company.  
All other trademarks are property of their respective owners.  
Please recycle. Printed in Australia. © 3M 2020. All rights reserved.