

3M Science.
Applied to Life.™

The Electrical Tape

For excellent primary insulation
and moisture protection

Scotch® Tape 23

Rubber Splicing Tape



Choose Scotch® Rubber Splicing Tape 23 for insulating, splicing, and padding low- to high-voltage cables, especially in outdoor or underground applications. Adding rubber tapes to your toolbox can help reinforce your work for years of maintenance-free service.

Product Highlights:

- Primary insulation for splicing all types of solid dielectric insulated cables through 69 kV
- Self-fusing material provides immediate moisture seals and void-free build-ups
- Removable liner protects from dust and dirt during installation
- Rated for 90°C continuous operating temperature and overload temperatures up to 130°C
- Compatible with common, solid dielectric cable insulation
- Provides extra padding and highly conformable for irregularly-shaped objects
- Weather resistant



Outdoor or
Underground



Moist and Corrosive
Environments



Clean,
Removable Liner



Self-Fusing and
Excellent Stretch

Important Notice

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

3M United Kingdom PLC
3M Centre
Cain Road, Bracknell
Berkshire RG12 8HT
t: 0870 60 800 60
www.3M.co.uk/electrical