




# 3M™ Double Coated Tapes GPT-020, GPT-020F and GPT-020TF

Global NPI Toolkit

ID: [1949330](#)



## PURPOSE

This **activation plan** is designed to **help guide** you through the launch and activation the upgraded **GPT-020 family**, with focus launch **GPT-020TF** to 3M's line of General Purpose Tapes.

## KEY CONTACTS



— **Joe Otte**

Global Marketing Manager



— **Jesper Nilsson**

EMEA Portfolio Manager




— **Sandy Fenton**

Global Product Content Specialist



— **Bruce Wamstad**

Global Application Engineer



— **Petr Nepras**

EMEA Application Engineer

“  
**INTEGRATED  
MARKETING**  
is an approach to  
creating a unified and  
seamless experience  
for customers to  
interact with our  
brand.

## MESSAGE CONSISTENCY is KEY!

Consistency of message is one of the most important elements of integrated marketing. The copy style and content should be consistent across all media.

When customers attend our events, visit our website, watch one of their peers in our testimonials or talk to our selling armies, they will perceive the same benefit statements in each communication.

Consistency in communication requires teamwork, focus and discipline. It advances the idea that one message can have many facets and many voices, but still sounds unified. It also advances the concept of simpler by design, one message that can cut through the clutter and reach a target audience.



# Customer Communication

3M Industrial Adhesives and Tapes Division

3M Center, Building 220-05-E-06  
St. Paul, MN 55144-1000



[01] May 2025

**Subject: Notification of 3M™ Double Coated Tapes GPT-020 and GPT-020F Product Modification and a new line extension 3M™ Double Coated Tape GPT-020TF**

Dear Valued Customer,

We are writing to inform you that as a continuous improvement effort, 3M has made a minor modification to the adhesive used in 3M™ Double Coated Tape GPT-020 and GPT-020F. The new formulation is expected to have no impact to performance characteristics or fit, form, and function of the product. All GPT-020 are manufactured using 3M's proprietary solventless technology.

Starting in June 2025, 3M will begin phasing out material IDs associated with the legacy adhesive formulation and begin phasing in new IDs. The transition is expected to be completed by the end of 2025. With these changes, 3M strives to improve 3M's manufacturing process and enable a more stable supply chain.

In addition, we are excited to announce the launch of a new line extension to current GPT-020 products, designated as GPT-020TF. This new addition will utilize the same adhesive but will feature an 80µm polypropylene translucent red film liner. The new range will be available in select widths (see appendix 1).

We are committed to delivering the highest quality product that meets your expectations. The listed products are still manufactured in an ISO 9001 certificated location with a quality management system in place.

If you have questions regarding this change or need additional technical/product information, please contact your local 3M Sales Representative.

Thank you for your continued support of 3M solutions.

Sincerely,

Jesper Nilsson  
EMEA Portfolio Manager  
Industrial Adhesives & Tapes Division

Appendix 1,

Products in scope for change				Suggest alternative			
3M™ GPT-020 (Paper Liner, white with red 3M™ logo)				3M™ GPT-020 (Paper Liner, white with red 3M™ logo)			
UU011690888	7100269551	GPT-020 DCT PaperLiner 1540mmx500m 1/PAL	->	UU013578453	7100369920	GPT-020 DCT PaperLiner 1540mmx500m 1/PAL	
UU011691647	7100269604	GPT-020 DCT Paper Liner 1540mmx50m 1/CV	->	UU013569890	7100369857	GPT-020 DCT Paper Liner 1540mmx50m 1/CV	
UU011691639	7100269603	GPT-020 DCT Paper Liner 1000MMX50M 1/CV	->	UU013581424	7100369936	GPT-020 DCT Paper Liner 1000mmx50m 1/CV	
UU011691621	7100269705	GPT-020 DCT Paper Liner 50MMX50M 6/CV	->	UU013578529	7100369955	GPT-020 DCT Paper Liner 50mm x 50m 6/CV	
UU011691613	7100269704	GPT-020 DCT Paper Liner 38MMX50M 10/CV	->	UU013577034	7100369984	GPT-020 DCT Paper Liner 38mm x 50m 10/CV	
UU011690904	7100269552	GPT-020 DCT Paper Liner 25MMX50M 10/CV	->	UU013578479	7100369922	GPT-020 DCT Paper Liner 25mm x 50m 10/CV	
UU011690896	7100269702	GPT-020 DCT Paper Liner 19MMX50M 16/CV	->	UU013578297	7100370006	GPT-020 DCT Paper Liner 19mm x 50m 16/CV	
UU011690870	7100269550	GPT-020 DCT Paper Liner 15MMX50M 16/CV	->	UU013578206	7100369880	GPT-020 DCT Paper Liner 15mm x 50m 16/CV	
UU011690862	7100269834	GPT-020 DCT Paper Liner 12MMX50M 20/CV	->	UU013570559	7100369698	GPT-020 DCT Paper Liner 12mmx50m 20/CV	
UU011691654	7100269835	GPT-020 DCT Paper Liner 9MMX50M 27/CV	->	UU013578446	7100369919	GPT-020 DCT Paper Liner 9mm x 50m 27/CV	
UU011628946	7100264010	GPT-020 DCT Paper Liner Config Roll	->	UU013565773	7100369197	GPT-020 DCT Paper Liner Config Roll PL	
3M™ GPT-020F (Film Liner, white with red 3M™ logo)				3M™ GPT-020F (Film Liner, white with red 3M™ logo)			
UU010956207	7100224762	GPT-020F DCT 1540MMX500M 1/CV	->	UU013577752	7100369819	GPT-020F DCT Film Lnr 1540mm x 500m 1/CV	
UU010956199	7100223650	GPT-020F DCT 1540MMX50M 1/CV	->	UU013578461	7100369921	GPT-020F DCT Film Lnr 1540mm x 50m 1/CV	
UU010956181	7100224321	GPT-020F DCT 100MMX50M 5/CV	->	UU013577760	7100369820	GPT-020F DCT Film Lnr 100mm x 50m 5/CV	
UU010956173	7100224385	GPT-020F DCT 50MMX50M 6/CV	->	UU013578719	7100369902	GPT-020F DCT Film Lnr 50mm x 50m 6/CV	
UU010987558	7100225997	GPT-020F DCT 25MMX50M 11/CV	->	UU013581432	7100369937	GPT-020F DCT Film Lnr 25mm x 50m 11/CV	
UU010987541	7100225996	GPT-020F DCT 19MMx50M 15/CV	->	UU013578438	7100369918	GPT-020F DCT Film Lnr 19mm x 50m 15/CV	
UU010987905	7100226020	GPT-020F DCT 12MMX50M 24/CV	->	UU013577554	7100369845	GPT-020F DCT Film Lnr 12mm x 50m 24/CV	
UU010914842	7100220792	GPT020F Double Coated Tape Config Roll	->	UU013565781	7100369198	GPT-020F DCT Film Lnr Config Roll PL	
Products in scope, replaced with Line Extension				Line Extension			
3M™ GPT-020F (Film Liner, white with red 3M™ logo)				3M™ GPT-020TF (Film Liner, red translucent)			
				UU013480817	7100363393	GPT-020TF DCT 1540mm x 500m 1/CV	
				UU013480916	7100363413	GPT-020TF DCT 1540mm x 50m 1/CV	
UU011218847	7100243951	GPT-020F DCT LW 19mmx2000m 1/CV	->	UU013568439	7100369529	GPT-020TF DCT 19mm x 2000m 1/CV	
UU011218839	7100243950	GPT-020F DCT LW 12mmx3850m 1/CV	->	UU013570641	7100369719	GPT-020TF DCT 12mm x 3000m 1/CV	
UU011218821	7100243949	GPT-020F DCT LW 9mmx3850m 1/CV	->	UU013570542	7100369697	GPT-020TF DCT 9mm x 4000m 1/CV	
UU011218813	7100243948	GPT-020F DCT LW 6mmx5000m 1/CV	->	UU013568173	7100369500	GPT-020TF DCT 6mm x 5000m 1/CV	

Letters:

US-EN: [2585975](#)

CA-EN: [2590517](#)

CA-FR: [2590518](#)

Product Cross Reference Lists:

US-EN: [2585307](#)

CA-EN: [2585307](#)

CA-FR: [2585308](#)






# Family Comparison

All three GPT products are 200-micron double coated tapes with 95-microns of acrylic adhesive coated on each side of a 12-micron clear PET carrier.


Each product has a unique liner option to provide customers with flexibility to optimize their converting process.

- GPT-020: 58# PCK branded liner  
Yellow Core with red 3M™ logo
- GPT-020F: 100-micron branded BOPP liner  
Yellow Core with red 3M™ logo
- GPT-020TF: 80-micron unbranded, translucent red BOPP liner  
Yellow Core with red 3M™ logo





# Go To Market Strategy





<b>Un-branded Product (GPT-020TF) - designed for Converter Markets business model and Select GIC</b>	
Cost Effective Solution	Position products as cost-effective alternatives for budget-conscious customers. Highlight competitive pricing while ensuring quality standards are met.
Customization and Flexibility	3M™ will offer logs and level wound. Business model builds on Converters market/offer customization solutions/widths to meet market needs and preferences.
Targeted Marketing	Targeted calls & marketing to competitive conversions and applications such as long length applications. Support Converters to market narrow rolls and converted parts offering unique advantages.
Volume Sales and Contracts	Encourage bulk purchasing with deal pricing, long-term contracts to secure sales and inventory in warehouse, Offer deals on incentives for large orders to attract business clients. Sales Promotion and/or Sales competition with giveaways.
Product Selection	3M™ offer is log 1540mm and 4 widths (6,9,12,19mm) level wounds. Converters/Dual-House offering narrow rolls on their own or in collaboration with GIC. End-users with automatic or continuous tape application using level wound/spools (extrusion, profiles, cardboard, plastics, etc.) can source from existing partners.

<b>3M™ branded Products (GPT-020 &amp; GPT-020F) - designed for GIC and Converter Markets</b>	
Brand Strength	Leverage the established reputation and trust of the 3M brand to attract customers.
Premium Pricing Strategy	Position branded products as premium offerings with superior quality and performance. Justify higher pricing through the value-added benefits and reliability associated with the 3M brand
Customer Loyalty Programs	Implement loyalty programs to reward repeat customers and encourage brand loyalty. Offer exclusive deals and promotions to loyal customers to increase retention.
Channel Partnerships	Develop strong partnerships with distributors and retailers who value the 3M brand. Provide training and support to partners to effectively sell and promote branded products.
Product Selection	Selection of logs from 1540mm to narrow 9mm rolls plus configurable ID's to close any gap in width & length.

<b>Integration of Both Models</b>	
Cross-Promotion	Use 3M™ branded products to cross-promote unbranded offerings, showcasing the breadth of options available.
Market Segmentation	Segment the market to identify which customer groups prefer branded versus unbranded product, tailoring strategies accordingly.
Feedback and Improvement	Gather customer feedback on both product types to continuously improve offerings and address market demands.

# Creating designs in applications.



## Application Ideas

- ▶ POP/POS displays
- ▶ Light boxes
- ▶ Indoor-outdoor signs
- ▶ Paper bonding and packaging
- ▶ Metal fabrication
- ▶ Splicing and bonding
- ▶ Sports equipment
- ▶ Home decoration
- ▶ Trim attachment in appliance
- ▶ Mounting of plastic parts
- ▶ Mounting in electronics
- ▶ Furniture trim attachment

Rising to the challenge in many markets including:



General Industrial



Specialty Vehicle  
(Truck, Bus, Rail, RVs)



Medical Devices



Sign & Display



Appliance



Outdoor Power Equipment

# 3M™ Double Coated Tapes: GPT-020 and GPT-020F

## Video



3M™ Double Coated Tape GPT-020 Video  
[1930222](#)




3M™ Double Coated Tape GPT-020  
Demonstration Video  
[2069929](#)

3M\_Double\_Coated\_Tape\_GPT-020\_Video Source File.zip: [2088837](#)

# 3M™ Double Coated Tapes: GPT-020 and GPT-020F

# Static Assets



### 3M™ Double Coated Tape GPT-020

GPT: General Purpose Tape  
020: 200-micron (8 mil)

**Application Ideas**

- POP/POS displays
- Light boxes
- Indoor-outdoor signs
- Paper bonding and packaging
- Metal fabrication
- Splicing and bonding
- Sports equipment
- Home decoration
- Trim attachment in appliance
- Mounting of plastic parts
- Mounting in electronics
- Furniture trim attachment

**Top Markets**

- General Industrial
- Appliance
- Sign & Display
- Medical Devices
- Specialty Vehicle
- Outdoor Power Equipment

**Product Characteristics**

- Excellent peel performance on a variety of substrates
- Excellent initial adhesion on most LSE and HSE surfaces
- Superior high temperature shear
- Solvent-free adhesive coating technology
- High thermal and humidity resistance

Bonds to many high surface energy substrates and some low surface energy substrates, including:

- Stainless steel
- HCPB
- ABS
- Acrylic
- PP
- Polycarbonate
- Aluminum
- Glass

SAP ID	Material Description
7100369137	GPT-020 DCT Paper Lin
7100369220	GPT-020 DCT Paper Lin
7100369145	GPT-020 DCT Paper Lin
7100369077	GPT-020 DCT Paper Lin
7100369336	GPT-020 DCT Paper Lin
7100369055	GPT-020 DCT Paper Lin
7100369594	GPT-020 DCT Paper Lin
7100369222	GPT-020 DCT Paper Lin
7100370006	GPT-020 DCT Paper Lin
7100369890	GPT-020 DCT Paper Lin
7100369038	GPT-020 DCT Paper Lin
7100369918	GPT-020 DCT Paper Lin

### 3M™ Double Coated Tape GPT-020F

GPT: General Purpose Tape  
020: 200-micron (8 mil)  
F: 100-micron (3.9 mil) Polypropylene Liner

**Application Ideas**

- POP/POS displays
- Light boxes
- Indoor-outdoor signs
- Paper bonding and packaging
- Metal fabrication
- Splicing and bonding
- Sports equipment
- Home decoration
- Trim attachment in appliance
- Mounting of plastic parts
- Mounting in electronics
- Furniture trim attachment

**Top Markets**

- General Industrial
- Appliance
- Sign & Display
- Medical Devices
- Specialty Vehicle
- Outdoor Power Equipment

**Product Characteristics**

- Excellent peel performance on a variety of substrates
- Excellent initial adhesion on most LSE and HSE surfaces
- Superior high temperature shear
- Solvent-free adhesive coating technology
- High thermal and humidity resistance

Bonds to many high surface energy substrates and some low surface energy substrates, including:

- Stainless steel
- HCPB
- ABS
- Acrylic
- PP
- Polycarbonate
- Aluminum
- Glass

SAP ID	Material Description
7100369198	GPT-020F DCT Film L
7100369819	GPT-020F DCT Film L
7100369281	GPT-020F DCT Film L
7100369820	GPT-020F DCT Film L
7100369802	GPT-020F DCT Film L
7100369857	GPT-020F DCT Film L
7100369918	GPT-020F DCT Film L
7100369845	GPT-020F DCT Film L

### 3M™ Double Coated Tape GPT-020TF

GPT: General Purpose Tape  
020: 200-micron (8 mil)  
TF: 80-micron (3.1 mil) Polypropylene Liner

**Application Ideas**

- POP/POS displays
- Light boxes
- Indoor-outdoor signs
- Paper bonding and packaging
- Metal fabrication
- Splicing and bonding
- Sports equipment
- Home decoration
- Trim attachment in appliance
- Mounting of plastic parts
- Mounting in electronics
- Furniture trim attachment

**Top Markets**

- General Industrial
- Appliance
- Sign & Display
- Medical Devices
- Specialty Vehicle
- Outdoor Power Equipment

**Product Characteristics**

- Excellent peel performance on a variety of substrates
- Excellent initial adhesion on most LSE and HSE surfaces
- Superior high temperature shear performance
- Solvent-free adhesive coating technology
- High thermal and humidity resistance

Bonds to many high surface energy substrates and some low surface energy substrates, including:

- Stainless steel
- HCPB
- ABS
- Acrylic
- PP
- Polycarbonate
- Aluminum
- Glass

**Technical Overview (See TDS for details)**

Adhesive	Solventless acrylic
Carrier type (thickness)	PET 12-micron (0.5 mil)
Liner type (thickness)	Red translucent 80-micron (3.1 mil) Polypropylene Liner
Total tape thickness without liner	200-micron (8 mil)
High temperature performance	98°F (144°C), 1000g/1" x 1"
Static Shear	>10,000 minutes (9000° F (83°C))
Color	Transparent

SAP ID	Material Description
7100363393	GPT-020TF DCT 1540mm x 500m 1/ CV
7100363413	GPT-020TF DCT 1L Film 1540mm x 50m 1/ CV
7100369829	GPT-020TF DCT 18mm x 3000m 1/ CV
7100369719	GPT-020TF DCT 12mm x 3000m 1/ CV
7100369897	GPT-020TF DCT 8mm x 5000m 1/ CV
7100369500	GPT-020TF DCT 6mm x 5000m 1/ CV
TBD	GPT-020TF DCT 1L Film 5mm x 5000m 1/ CV
TBD	GPT-020TF EXT LNR Left 5mm x 3000m 1/ CV
TBD	GPT-020TF EXT LNR Right 5mm x 3000m 1/ CV



External Presentation [2025000](#)

3M™ GPT-020 Double Coated Tape Brochure [1808755](#)  
Native Files: [1808793](#)

Native Files.zip: [1808793](#)



Converter College Presentation [TBC 2311137](#)




# Sustainability

In 3M's proprietary solvent-free adhesive coating process:

- Raw materials are combined to create a solvent free adhesive mixture which is coated on a release liner or backing.
- The coated substrate runs through a proprietary process to transform the adhesive to a pressure sensitive adhesive tape.
- Since there are no solvents involved, this process uses less energy and has lower CO<sub>2</sub> equivalents per square meter than a comparable product construction made with a solvent-based adhesive coating process.

Included in Product Impact Analyzer (PIA)  
Carbon footprint information



[2362854](#)

# 3M™ Double Coated Tape GPT-020

# Product Information

## Prioritized products


3M SAP ID	Legacy SKU ID	Marketplace Formal Name	Technical Data Sheet
7100369197	UU013578453	3M™ Double Coated Tape GPT-020, Paper Liner, Roll, Config	<p style="text-align: center;">GPT-020 Technical Data Sheet <a href="#">2365949</a></p>
7100369920	UU013569890	3M™ Double Coated Tape, GPT-020, Paper Liner, 1540mm x 500m, 1 Roll/Case	
7100369857	UU013581424	3M™ Double Coated Tape, GPT-020, Paper Liner, 1540mm x 50m, 1 Roll/Case	
7100369936	UU013578529	3M™ Double Coated Tape, GPT-020, Paper Liner, 1000mm x 50m, 1 Roll/Case	
7100369955	UU013577034	3M™ Double Coated Tape, GPT-020, Paper Liner, 50mm x 50m, 6 Roll/Case	
7100369984	UU013578479	3M™ Double Coated Tape, GPT-020, Paper Liner, 38mm x 50m, 10 Roll/Case	
7100369922	UU013578297	3M™ Double Coated Tape, GPT-020, Paper Liner, 25mm x 50m, 10 Roll/Case	
7100370006	UU013578206	3M™ Double Coated Tape, GPT-020, Paper Liner, 19mm x 50m, 16 Roll/Case	
7100276858	UU011824842	3M™ Double Coated Tape, GPT-020, Paper Liner, 19mm x 50m, 4 Roll/Case (blister pack)	
7100369880	UU013570559	3M™ Double Coated Tape, GPT-020, Paper Liner, 15mm x 50m, 16 Roll/Case	
7100369698	UU013578446	3M™ Double Coated Tape, GPT-020, Paper Liner, 12mm x 50m, 20 Roll/Case	
7100369919	UU013578446	3M™ Double Coated Tape, GPT-020, Paper Liner, 9mm x 50m, 27 Roll/Case	
7100270927	UU011729074	3M™ Double Coated Tape Paper Liner GPT-020, 210 mm x 295 mm, 25 Sheet/Case, <b>Restricted</b>	

[Base ID: B5005400014 Product Detail Page](#)

# 3M™ Double Coated Tapes: GPT-020 and GPT-020F

## Images

### Product Rendering



[2250581](#)




[2328049](#)



[2329384](#)




[2250684](#)



### 1540mm x 50m



[1802337](#)



[1802351](#)



[1802352](#)

### 100mm x 50m



[1802357](#)



[1802358](#)



[1802359](#)



[1802360](#)

### 50mm x 50m




[2329390](#)



[1802362](#)




[1802363](#)



[1802336](#)

### 25mm x 50m



[1795552](#)



[1795553](#)



[1795554](#)



[1795555](#)

### 19mm x 50m



[1802341](#)



[1802342](#)



[1802343](#)



[1802344](#)

### 12mm x 50m



[1802345](#)



[1802346](#)



[1802347](#)



[1802348](#)




# 3M™ Double Coated Tape GPT-020

# Banner Ads – No CTA\*




360x240  
[2660757](#)



1200x267  
[2660763](#)




360x240  
[2660759](#)



1200x267  
[2660765](#)



360x240  
[1406719](#)




1200x267  
[2660758](#)

# 3M™ Double Coated Tape GPT-020

# Banner Ads - CTA




360x240  
[1924157](#)



1200x267  
[1924160](#)




360x240  
[1924159](#)



1200x267  
[1924162](#)




360x240  
[1924158](#)




1200x267  
[1924161](#)

# 3M™ Double Coated Tape GPT-020

# Images



[2605853](#)




[2605854](#)

**3M™ Double Coated Tape GPT-020**  
Available in a range of sizes



- High Tack
- Easily Conformable
- Versatile
- Eco-Friendly

[2419956](#)



**Instant High Tack**  
8 mil tape thickness that is engineered to instantly grab onto a variety of materials

[2419957](#)




**Strong and Durable**  
Provides high peel and shear performance

[24199453](#)



**High Temperatures**  
Short-term use up to 300 °F (149 °C) or long-term up to 200 °F (93 °C)

[2604352](#)




**Versatile Applications**  
Strong adhesive instantly adheres to high and low surface energy materials

[24199561](#)



**Environmentally-Friendly**  
Uses a solventless manufacturing process that may produce less odor and greenhouse gas emissions

[2419967](#)



**Standard Roll**  
Widths 9 mm to 1540 mm and lengths of 50 m

**Range of Sizes**  
Available in standard roll format, as well as a 1540 mm width and 500 m long roll

[2419960](#)

# 3M™ Double Coated Tape GPT-020F

# Product Information

## Prioritized products


3M SAP ID	Legacy SKU ID	Marketplace Formal Name	Technical Data Sheet
7100369198	UU013565781	3M™ Double Coated Tape GPT-020F, Film Liner, Roll, Config	GPT-020F Technical Data Sheet <a href="#">2365981</a>
7100224762	UU013577752	3M™ Double Coated Tape, GPT-020F, Film liner, 1540mm x 500m, 1 Roll/Case	
7100223650	UU013578461	3M™ Double Coated Tape, GPT-020F, Film liner, 1540mm x 50m, 1 Roll/Case	
7100224321	UU013577760	3M™ Double Coated Tape, GPT-020F, Film liner, 100mm x 50m, 5 Roll/Case	
7100224385	UU013578719	3M™ Double Coated Tape, GPT-020F, Film liner, 50mm x 50m, 6 Roll/Case	
7100225997	UU013581432	3M™ Double Coated Tape, GPT-020F, Film liner, 25mm x 50m, 11 Roll/Case	
7100225996	UU013578438	3M™ Double Coated Tape, GPT-020F, Film liner, 19mm x 50m, 15 Roll/Case	
7100226020	UU013577554	3M™ Double Coated Tape, GPT-020F, Film liner, 12mm x 50m, 24 Roll/Case	
7100226020	UU013577042	3M™ Double Coated Tape, GPT-020F, Film liner, 19mm x 5m, 60 Roll/Case, <b>Sample</b>	
7100226380	UU013577752	3M™ Double Coated Tape GPT-020F, 19 mm x 5 m, 60 Rolls/Case, Sample	
7100229602	UU011009642	3M™ Double Coated Tape GPT-020F, 210 mm x 295 mm, 25 Sheet/Case, <b>Restricted</b>	

[Base ID: B5005163007 Product Detail Page](#)

# 3M™ Double Coated Tapes: GPT-020 and GPT-020F

## Images

### Product Rendering



[2250581](#)




[2328049](#)



[2329384](#)




[2250684](#)



### 1540mm x 50m



[1802337](#)



[1802351](#)



[1802352](#)

### 100mm x 50m



[1802357](#)



[1802358](#)



[1802359](#)



[1802360](#)

### 50mm x 50m



[2329390](#)



[1802362](#)




[1802363](#)



[1802336](#)

### 25mm x 50m



[1795552](#)



[1795553](#)



[1795554](#)



[1795555](#)

### 19mm x 50m



[1802341](#)



[1802342](#)



[1802343](#)



[1802344](#)

### 12mm x 50m



[1802345](#)



[1802346](#)



[1802347](#)



[1802348](#)




# 3M™ Double Coated Tape GPT-020F

# Banner Ads – No CTA




360x240  
[1808794](#)



1200x267  
[1808816](#)



360x240  
[1808809](#)



1200x267  
[1808814](#)




360x240  
[1808807](#)



1200x267  
[1808810](#)


# 3M™ Double Coated Tape GPT-020F

# Images



[2605853](#)

[2605854](#)




[2419948](#)




[2419959](#)




[2419945](#)



[2604352](#)



[2419955](#)



[2604354](#)



[2419947](#)

# 3M™ Double Coated Tape GPT-020TF

# External Presentation & Brochure

## External Use



[2601994](#)



[1808755](#)

Native Files: [2601994](#)

## Prioritized products

3M SAP ID	Legacy SKU ID	Marketplace Formal Name	Technical Data Sheet
7100363393	UU013480817	GPT-020TF DCT 1540mm x 500m 1/CV	<p>GPT-020TF Technical Data Sheet <a href="#">2583862</a></p>
7100363413	UU013480916	GPT-020TF DCT 1540mm x 50m 1/CV	
7100369500	UU013568173	GPT-020TF DCT 6mm x 5000m 1/CV	
7100369697	UU013570542	GPT-020TF DCT 19mm x 2000m 1/CV	
7100369719	UU013570641	GPT-020TF DCT 9mm x 4000m 1/CV	
7100369529	UU013568439	GPT-020TF DCT 12mm x 3000m 1/CV	
7100363373	UU013480718	GPT-020TF DCT 210MMx295MM 25/CV <b>Restricted</b> GTML	

[Base ID: B5005578007 Product Detail Page](#)

# 3M™ Double Coated Tape GPT-020TF

# Images

## Product Renderings



[9123870](#)

## Master and Log Rolls

1540mm x 50m



[2583029](#)



[2583033](#)



[2583032](#)



[2628148](#)

## Level Wound Rolls



[2583030](#)



[2583031](#)



[2617503](#)



[2617502](#)



[2617501](#)



[2617500](#)

# 3M™ Double Coated Tape GPT-020TF

# Level Wound Roll Images

6mm x 5000m:



[2624016](#)



[2624012](#)



[2624015](#)



[2624013](#)



[2624014](#)

12mm x 3000m:



[2624017](#)



[2624022](#)



[2624021](#)



[2624019](#)



[2624020](#)



[2624018](#)



[2617503](#)



[2617501](#)



[2617500](#)



[2617502](#)

19mm x 2000m:



[2624028](#)



[2624027](#)



[2624024](#)



[2624026](#)



[2624025](#)




[2624023](#)


*Note: The 12mm x 3000m roll size images can be used to represent the 9mm x 4000m rolls.*

# 3M™ Double Coated Tape GPT-020TF


# Banner Ads - CTA



360x240  
[2660760](#)



1200x267  
[2660768](#)




360x240  
[2660762](#)



1200x267  
[2660767](#)




360x240  
[2660761](#)




1200x267  
[2660766](#)

# 3M™ Double Coated Tape GPT-020TF

# Images




[2605852](#)



[2605854](#)

## 3M™ Double Coated Tape GPT-020TF

Available in different sizes




- Flexible and Strong
- High Initial Tack
- High Temperatures
- Multipurpose

[2604349](#)




**Flexible and Strong**  
8 mil (200 µm) thick with an unbranded, 3.1 mil (80 µm) polypropylene liner

[2604350](#)




**High Initial Tack**  
Strong adhesive sticks to high and low surface energy materials

[2604351](#)




**High Temperatures**  
Short-term use up to 300 °F (149 °C) or long-term up to 200 °F (93 °C)

[2604352](#)



**Multipurpose**  
Point-of-purchase displays, signage bonding, billboard mounting, & more

[2604353](#)



**Product Options**  
Available in standard roll format and level wound rolls

[2604354](#)



### Ideal For Materials Like:

- Stainless Steel
- Aluminum
- Polycarbonate
- Acrylic
- Glass

[2604355](#)



## 3M™ Double Coated Tape GPT-020TF

Available in different sizes

- Flexible and Strong
- High Initial Tack
- High Temperatures
- Multipurpose

[2609031](#) - Video

**Thank you**