



**Scotchlite™**  
Reflective Material

[ better \*  
stronger  
brighter ]

The next generation of  
industrial wash transfer films

9725 /// 9745 // 5525 / 5545



Added wash  
durability



Disinfective  
wash



OEKO-TEX®  
certified



Full Portfolio

\*Compared to existing 3M Scotchlite products wash performance.

# A winning product family

---

In today's fast changing world, your garments need to withstand more demands than ever, including an increased number of wash cycles, higher temperatures and harsher washing conditions.

**To help you meet these demands we're introducing the next generation of 3M™ Scotchlite™ Industrial Wash and Industrial Wash Flame Resistant reflective transfer films, which offer the strongest wash durability ever offered by 3M – Increasing longevity, which may reduce the cost of ownership for specifier.**

Put your trust in an ingredient brand that uses high performance materials backed by the powerful 3M™ Scotchlite™ Reflective Material brand. Everyone deserves a garment made for today's needs – whether its construction workers, welders, train drivers, paramedics or firefighters. Together, we can give it to them.

**Better. Stronger. Brighter.\***

\*Compared to existing 3M Scotchlite products wash performance.



Together with our existing reflective fabrics 9925 and 9945, we're offering a full high-performance industrial wash portfolio that delivers durability, high brightness, disinfectant washability, anti-static compatibility\* and a variety of design options, all in a more sustainable design that's certified as OEKO-TEX® Standard 100 Class 1.

[ 5525 ]

Segmented  
Industrial Wash Trim

[ 9725 ]

Industrial Wash  
Transfer Film

[ 9925 ]

Industrial Wash  
Fabric

[ 5545 ]

Segmented  
Industrial Wash  
Flame Resistant Trim

[ 9745 ]

Industrial Wash  
Flame Resistant  
Transfer Film

[ 9945 ]

Industrial Wash  
Flame Resistant  
Fabric

\*Can be used as an attachment  
to garments certified to EN 1149-5.

# Industrial Wash

# Transfer Film

[ 9725 ]

**75**  
cycles industrial wash  
ISO 15797  
table 4, procedure 2

**100**  
cycles home wash  
ISO 6330-6N

**50**  
cycles disinfectant  
industrial wash  
ISO 15797  
table 1, procedure 2

**50**  
cycles dry cleaning  
ISO 3175-2

Flame resistant	X
Certificates	ISO 20471
OEKO-TEX® Standard 100	Class 1
Tumble Dryer	✓
Tunnelfinisher	✓

**75**  
cycles industrial wash  
ISO 15797  
table 4, procedure 2

**50**  
cycles home wash  
ISO 6330-6N

**30**  
cycles disinfectant  
industrial wash  
ISO 15797  
table 1, procedure 2

**50**  
cycles dry cleaning  
ISO 3175-2

[ 5525 ]


# Segmented

# Industrial Wash Trim

## Shedding light on reflective technology

3M is a pioneer in developing the science behind retroreflection and has been advancing the technology in new and groundbreaking ways for over 80 years. 3M™ Scotchlite™ Reflective Material works by returning light rays back to the original source, a result of the retroreflective properties of thousands of microscopic glass beads incorporated into the material.

This means retroreflective materials appear brightest to an observer located near the original light source, such as a car's headlights. Since very little light is scattered when the light is returned, retroreflective materials enhance the contrast of the wearer to an observer located near the original light source.



# Industrial Wash Flame Resistant Transfer Film

[ 9745 ]

**100**

cycles industrial wash  
ISO 15797  
table 4, procedure 2

**100**

cycles home wash  
ISO 6330-6N

**50**

cycles disinfectant  
industrial wash  
ISO 15797  
table 1, procedure 2

**25**

cycles dry cleaning  
ISO 3175-2

Flame resistant	✓
Certificates	ISO 20471 ISO 11611 ISO 11612 ISO 14116 EN 469 EN 1149-5*
OEKO-TEX® Standard 100	Class 1
Tumble Dryer	✓
Tunnelfinisher	✓

**100**

cycles industrial wash  
ISO 15797  
table 4, procedure 2

**100**

cycles home wash  
ISO 6330-6N

**40**

cycles disinfectant  
industrial wash  
ISO 15797  
table 1, procedure 2

**25**

cycles dry cleaning  
ISO 3175-2

[ 5545 ]

# Segmented Industrial Wash Flame Resistant Trim

\*Can be used as an attachment  
to garments certified to EN 1149-5.





Scotchlite.com



**3M Deutschland GmbH**  
Carl-Schurz-Str. 1  
41453 Neuss  
Germany

© 3M 2022. All rights reserved.  
3M and Scotchlite are trademarks of 3M,  
used under license in Canada. Please recycle.