

**3M** Science.  
Applied to Life.™

3M™ Print Wrap Film

**IJ280**

## Goes from 0 to wrapped, faster.

Preferred by installers globally,\* this print wrap film for vehicles is up to 20% faster to install<sup>^</sup> and proven to lift 2x less.\* It boasts exceptional performance and ease of use that will help you finish first.

- ▶ Excellent print quality and durability
- ▶ Conforms with less heat\*
- ▶ New 3M™ Comply™ v4 Air Release for max air flow and smooth results
- ▶ New, proprietary adhesive with optimized initial tack, slide and repositionability
- ▶ Removes cleanly at end of life with heat

Wrap fast. Wrap fearlessly.

**3M.com/IJ280**

\*When compared to Avery Dennison® 1105EZRS/1460Z, Arlon SLX®/3210, & 3M™ IJ180Cv3/mC/8518.

<sup>^</sup>When compared to Avery Dennison® 1105EZRS/1460Z, Arlon SLX®/3210, & 3M™ IJ180Cv3/mC/8518 with experienced installers applying 3M™ IJ280/8428G for the first time.

© 3M 2021. All rights reserved. 3M and Comply are trademarks of 3M.



Realizing full product benefits requires use of 3M™ Gloss Wrap Overlaminate 8428G.

75-5100-2837-8