

A red car is shown in a paint booth, partially covered with clear plastic and yellow masking tape. Several large, glowing orange heating lamps are positioned to the left of the car. The car's surface is highly reflective, showing the surrounding environment.


Scotch®

Masking Tape 2800

Masking performance that can take the heat.


Scotch® Masking Tape 2800 is easy to apply and is highly conformable on even the most challenging contours.

Unlike tapes that are prone to tracking and ghosting, Scotch® Masking Tape 2800's high temperature acrylic adhesive consistently delivers sharp paint lines and excellent color separation. Designed specifically for TPO (thermoplastic olefin) surface applications in auto, truck, marine, bus and rail, it also proved effective on painted metal and other substrates. Scotch® Masking Tape 2800 is compatible with most industrial paints and painting processes.




3M

Balanced conformity for superior masking. You'll experience the difference, every time.




Excellent performance in high temperature paint processes.

- ▶ **Conforms to surface contours** — provides superior masking on TPO (thermoplastic olefin) surfaces
- ▶ **Won't fail under high heat** — formulated for bake cycles up to 300°F/150°C for 30 minutes
- ▶ **Sharp lines every time** — removes cleanly: no residue, tracking, bleeding and resists ghosting
- ▶ **Wide paint compatibility** — specially designed to work with most industrial paints
- ▶ **Clean removal** — up to 7 days outdoors




Superior high temperature performance.



Sharp, accurate paint lines.



Mask with confidence.
Translucent backing assists in placement and allows visual confirmation of adhesive wet out on surface.



Product	Tape Structure (Backing/Adhesive)	Thickness mils (mm)	Adhesion to Steel oz/in (N/100 mm)	Tensile Strength lb/in (N/100 mm)	Elongation at Break %	Heat Resistance °F (°C)	Comments
Based on ASTM Test Method:		D-3652	D-3330	D-3759	D-3759		
Scotch® Masking Tape							
2800	Plasticizer-Free Polyolefin/Acrylic	4.1 (0.05)	16 (17)	25 (430)	1000	300°F (149°C) 30 Minutes	Clean removal up to 7 days outdoors

Note: This technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product	3M UPC	Size	Rolls/Case
2800	04549395894864	1200mm x 50m	1
	04549395894871	12mm x 50m	100
	04549395894888	19mm x 50m	64

Product	3M UPC	Size	Rolls/Case
2800	04549395894895	25mm x 50m	48
	04549395894901	50mm x 50m	24

For more information on Scotch® Masking Tapes, contact your local 3M representative or call 1-800-362-3550.



3M Closure and Masking Systems Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 877-369-2923 (Fax)
3M.com/masking

Warranty and Limited Remedy: 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except for the limited remedy above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal or equitable theory asserted.

3M, the Plaid and Scotch are trademarks of 3M. © 3M 2021. All rights reserved. Please recycle.