



3M™ Scott™ 200 and 300 Bar Steel Cylinders

Specification

	CYL-600	CYL-1200	CYL-820
Water capacity	3 litres	6 litres	3 litres
Charging pressure	200 bar	200 bar	300 bar
Test pressure	300 bar	300 bar	300 bar
Volume of air at rated charging pressure	600 litres	1200 litres	820 litres
Material	Steel	Steel	Steel
Colour	Painted grey body with black and white quartered neck	Painted grey body with black and white quartered neck	Painted grey body with black and white quartered neck
Specification	CE specification in accordance with PED 2014/68/EU. Manufactured in accordance with ISO9809-1.	CE specification in accordance with PED 2014/68/EU. Manufactured in accordance with ISO9809-1.	CE specification in accordance with PED 2014/68/EU. Manufactured in accordance with ISO9809-2.
Dimensions of shell	Approx 115mm diameter x 400mm long	Approx 140mm diameter x 520mm long	Approx 115mm diameter x 415mm long
Shell weight	Approx 3.5kg	Approx 6.2kg	Approx 3.9kg
Fully charged weight	Approx 5.0kg	Approx 8.5kg	Approx 5.6kg
Duration based on 40 l/min	15 minutes	30 minutes	20 minutes
	CYL-600 is fitted with a 200 bar cylinder valve	CYL-1200 is fitted with a 200 bar cylinder valve	CYL-820 is fitted with a 300 bar cylinder valve

3M Scott Fire & Safety

Pimbo Road
Skelmersdale
Lancashire, WN8 9RA
United Kingdom

Phone +44 (0)1695 711711
E-Mail skelmenq@mmm.com
Web www.3Mscott.com

ISO 9001 Registered. © 3M 2021. All rights reserved. 3M and Scott are trademarks of 3M Company. OMG149517