



**3M**

**SCOTT™**

**Reliable facepieces for  
work environments.**

**3M™ Scott™ AV-3000 Series Facepieces**



# Face the hazards of your job with confidence.

When you choose 3M Scott facepieces, you're choosing premium, proven performance for challenges you encounter.

The 3M™ Scott™ AV-3000 SureSeal and 3M™ Scott™ AV-3000 HT facepieces offer common design features for improved comfort, fit and performance for industrial workers, firefighters and hazmat teams.



**3M™ Scott™**  
**AV-3000 SureSeal Facepiece**



**3M™ Scott™**  
**AV-3000 HT Facepiece**

## Common Features

- Fully open front port enables easy communication and breathing without any obstruction while off air
- Easy to maintain with no moving parts to clean or manipulate
- Dual voicemitters allow easy communication without electronics and enhanced voice transmission around the wearer
- Optional electronic communications systems are available to meet different needs
- SureSeal faceseal technology for enhanced comfort, fit and performance
- Head harnesses include 5 points of attachment to enable secure fit
- Positioning tab to assist with proper and quick donning (5-strap Kevlar® and polyester versions)
- Facepieces contain no natural rubber latex to reduce the possibility of allergic reactions

## Additional Features

### AV-3000 SureSeal only

- Available with Kevlar®, Polyester, or Rubber head harness to meet customer needs

## Additional features





















### AV-3000 HT only

- ANSI/ISEA Z87.1-2020, Impact rated Z87+
- Incorporates lens and bezel thermal performance introduced in NFPA 1981 Standard, 2013 edition
- High visibility inhalation valves for easy inspection
- Kevlar® head harness available with either 4 or 5-straps

NIOSH Approved Respirators (excluding PAPR)	AV-3000 SureSeal with Polyester Harness	AV-3000 SureSeal with Rubber Harness	AV-3000 SureSeal with Kevlar® Harness	AV-3000 HT with Kevlar® 5-Strap Harness**	AV-3000 HT with Kevlar® 4-Strap Harness**
3M Scott Industrial Respirators	●	●	●	●	●
3M Scott CBRN APR Respirators		●	●	●	●
Approved with 3M Scott NFPA SCBA, 2018 Edition				●	●

\*\*Approvals shown are for AV-3000 HT facepieces without SIGHT installed



AV-3000 SureSeal Polyester	AV-3000 SureSeal Rubber	AV-3000 SureSeal Kevlar®	AV-3000 HT Kevlar® 5-Strap**	AV-3000 HT Kevlar® 4-Strap**	<div>TOP-DOWN CONVERTIBILITY</div> <div></div> <div>This AV-Series facepiece design platform, pioneered by 3M Scott, allows one facepiece to be used in numerous respiratory protection assemblies, from supplied air to air purification. This one-facepiece concept reduces the cost of inventory, training and fit testing multiple facepieces for each employee.</div>				
Air-Purifying Respirators									
•	•	•	•	•	→	3M™ Scott™ AV-632 Bayonet Adapter	 AV-632	→	 3M™ Particulate Filters, 2000 and 7093 Series
									 3M™ Gas/Vapor Cartridges, 6000 Series
									 3M™ Combination Cartridges / P100 Particulate Filters, 6000 Series
•	•	•	•	•	→	3M™ Scott™ 40 mm Cartridge Adapter	 805059-01	→	 3M™ Scott™ MPC Cartridge, PN 805557-01
									 3M™ Scott™ P100/HEPA Filter, PN 052683
									 3M™ Scott™ Enforcement Cartridge, PN 045123
	•	•			→	3M™ Scott™ First Responder Adapter	 200423-01	→	 3M™ Scott™ CBRN Cap-1 Canister, PN 045135  (First Responder Adapters are also compatible with 40 mm cartridges above)
			•	•	→	3M™ Scott™ First Responder Adapter	 200423-02		
Supplied Air Respirators									
•	•	•	•	•	→	 3M™ Scott™ E-Z Airline Respirator			
•	•	•	•	•	→	 3M™ Scott™ Ska-Pak AT SAR	 3M™ Scott™ Ska-Pak Plus SAR	 3M™ Scott™ Ska-Pak SAR	
Self Contained Breathing Apparatus									
•	•	•	•	•	→	 3M™ Scott™ Air-Pak™ 75i SCBA	 3M™ Scott™ ISCBA	 3M™ Scott™ ACSi SCBA	
			•	•	→	 3M™ Scott™ Air-Pak™ X3 Pro SCBA (NFPA 1981, 2018 Edition)			

\*\*Approvals shown are for AV-3000 HT facepieces without SIGHT installed  
 Note: This list is not inclusive of all approved or certified respirator configurations



**AV-3000 HT Facepieces with 5 points of attachment. Available with 4- or 5- Strap Kevlar® Head Harness**

Facepiece Size	Part Number	Part Number	
	Kevlar® 4-Strap Head Harness	Kevlar® 5-Strap Head Harness	Notes
AV-3000 HT (Small)	201215-21	201215-01	All variants with Kevlar® head harnesses are also available with communication brackets installed on right or left side. Communication brackets can also be ordered and installed separately.
AV-3000 HT (Medium)	201215-22	201215-02	
AV-3000 HT (Large)	201215-23	201215-03	

**AV-3000 SureSeal Facepiece with 5 points of attachment. Available with 5- Strap Kevlar®, Polyester or Rubber Head Harness**

Facepiece Size	Part Number	Part Number	Part Number	
	Kevlar® 5-Strap Head Harness	Polyester Head Harness	Rubber Head Harness	Notes
AV-3000 SureSeal (Small)	805773-81	805774-81	805775-81	All variants with Kevlar® head harness are also available with communication brackets installed on right side. Communication brackets can also be ordered and installed separately.
AV-3000 SureSeal (Medium)	805773-82	805774-82	805775-82	
AV-3000 SureSeal (Large)	805773-83	805774-83	805775-83	

**AV-3000 Series Accessories**

Part Number	Description
<b>Adapters</b>	
XP-1008-4113-7	AV-632 Bayonet Adapter, 5 per box (for use with 3M bayonet style cartridges and filters)
805059-01	40 mm Cartridge Adapter (for use with 40 mm cartridges and filters)
200423-01	40 mm First Responder Adapter for AV-3000 SureSeal (for use with CBRN Cap-1 Canister or 3M Scott 40 mm cartridges and filters)
200423-02	40 mm First Responder Adapter for AV-3000 HT (for use with CBRN Cap-1 Canister or 3M Scott 40 mm cartridges and filters)
601	3M™ Fit Test Adapter [3M ID: 70070406544] (for fit testing with 3M filters using AV-632 Bayonet Adapter)
805628-01	40 mm Quantitative Fit Test Adapter (for fit testing with 40 mm Cartridge adapter and 40 mm filter)
<b>Other Accessories</b>	
200715-01	EPIC Communication Bracket (right) (for use with AV-3000 SureSeal)
201210-01	EPIC Communication Bracket (right) (for use with AV-3000 HT) (Left side bracket is also available)
805753-01	AV-3000 Series Standard Eyeglass kit
200372-52F	52 mm Wire Frame Eyeglass kit
200372-60F	60 mm Wire Frame Eyeglass kit
805534-01	Fleece Facepiece Bag
804088-02	Neck Strap Assembly

**AV-3000 SureSeal and AV-3000 HT Facepieces**Compatible with EPIC 3 communications devices:

EPIC 3 RDI – Bluetooth Radio Direct Interface  
 EPIC 3 RI – Bluetooth Radio Interface with Speaker Mic  
 EPIC 3 Voice Amplifier



These respirators help to protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of applicable jurisdiction, as appropriate. Improper use may result in sickness or death. For correct use, see supervisor and User Instructions, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.

Kevlar® is a registered trademark of E.I. Du Pont de Nemours and Company.

The Bluetooth® registered mark and logos are registered trademarks owned by Bluetooth SIG, Inc.

Please recycle. Printed in USA © 2021, 3M. All rights reserved. 3M, Scott and Air-Pak are trademarks of 3M. Used under license in Canada. HS 7731A EN 4/21 ISO 9001 Registered 210119366



**Personal Safety Division**  
**3M Scott Fire & Safety**  
 Monroe Center, P.O. Box 569  
 Monroe, NC 28110

3M PSD products are for occupational use only.

1-800-247-7257  
 3M.com/ScottIndustrial (US)  
 3M.ca/ScottSafety (Canada)