

3M™ Flat Glass Window Film – Single Pane 1/4" (6mm) Clear

Film	SHGC	VLT	Visible Reflection Exterior	Visible Reflection Interior	U Value	LSG (Light to Solar Gain)	UV Block	SC	TSER	Glare Reduction	Heat Loss Reduction	Heat Gain Reduction
1/4" Clear Glass	0.82	89%	8%	9%	1.03	1.1	38%	0.94	19%	NA	NA	NA
Thinsulate CC75	0.53	74%	15%	12%	0.63	1.4	99.9%	0.61	47%	17%	40%	35%
Prestige 20	0.38	21%	5%	6%	1.02	0.5	99.9%	0.44	62%	76%	0%	54%
Prestige 40	0.40	39%	7%	7%	0.99	1.0	99.9%	0.46	60%	55%	3%	50%
Prestige 50	0.44	50%	8%	7%	0.99	1.1	99.9%	0.50	56%	44%	3%	46%
Prestige 60	0.47	60%	8%	8%	0.99	1.3	99.9%	0.54	53%	32%	3%	42%
Prestige 70	0.50	69%	9%	9%	0.99	1.4	99.9%	0.58	50%	22%	3%	38%
Prestige 20 Exterior	0.34	21%	5%	5%	1.03	0.6	99.9%	0.39	66%	76%	0%	59%
Prestige 40 Exterior	0.39	42%	6%	5%	1.02	1.1	99.9%	0.44	61%	53%	0%	53%
Prestige 70 Exterior	0.48	71%	7%	7%	1.02	1.5	99.9%	0.55	52%	20%	0%	41%
Prestige 90 Exterior	0.64	88%	9%	9%	1.02	1.4	99.9%	0.74	36%	1%	0%	21%
Ceramic 30	0.41	36%	17%	15%	1.02	0.9	99%	0.47	59%	60%	0%	50%
Ceramic 40	0.47	44%	14%	12%	1.03	0.9	99%	0.54	53%	50%	0%	43%
Ceramic 50	0.53	53%	12%	10%	1.03	1.0	99%	0.61	47%	40%	0%	35%
Night Vision 15	0.28	15%	38%	11%	0.98	0.5	99%	0.32	72%	83%	4%	66%
Night Vision 25	0.39	24%	19%	7%	1.00	0.6	99%	0.45	61%	73%	2%	52%
Night Vision 35	0.48	36%	13%	7%	1.03	0.7	99%	0.55	52%	59%	0%	41%
Silver P18	0.23	17%	56%	58%	0.93	0.7	99%	0.26	77%	81%	9%	72%
Neutral 20	0.38	15%	21%	19%	0.99	0.4	99%	0.44	62%	83%	3%	53%
Neutral 35	0.44	36%	20%	18%	0.99	0.8	99%	0.51	56%	60%	4%	46%
Neutral 50	0.56	52%	12%	11%	1.03	0.9	98%	0.64	44%	41%	0%	31%
Neutral 70	0.68	69%	9%	8%	1.03	1.0	98%	0.78	32%	22%	0%	17%
Affinity 15	0.21	9%	58%	25%	1.00	0.4	99%	0.24	79%	90%	2%	74%
Affinity 30	0.39	33%	29%	19%	0.94	0.8	99%	0.45	61%	63%	8%	52%
LE 20	0.24	20%	52%	58%	0.79	0.8	99%	0.28	76%	77%	24%	71%
LE 35	0.25	30%	54%	60%	0.85	1.2	99%	0.29	75%	67%	17%	69%
Silver 15 External	0.19	17%	61%	56%	1.02	0.9	99%	0.22	81%	81%	0%	77%
Neutral 35 External	0.49	44%	10%	13%	1.02	0.9	99%	0.56	51%	50%	0%	40%
Ultra Prestige S50	0.44	48%	9%	7%	1.02	1.1	99.9%	0.50	56%	46%	1%	46%
Ultra Prestige S70	0.51	68%	10%	9%	1.02	1.4	99.9%	0.58	50%	23%	1%	38%
Ultra Night Vision S25	0.40	24%	19%	7%	1.02	0.6	99.9%	0.46	60%	73%	1%	51%
Safety Neutral S35	0.43	39%	23%	13%	1.02	0.9	99%	0.54	57%	56%	0%	47%
Safety Silver S20	0.25	18%	61%	62%	1.02	0.7	99%	0.26	76%	80%	0%	70%
Scotchshield Ultra S800	0.79	87%	9%	9%	1.04	1.1	99.9%	0.90	21%	2%	0%	3%
Safety S40	0.82	87%	8%	8%	1.03	1.1	99%	0.94	19%	2%	0%	0%
Safety S70	0.79	87%	9%	9%	1.02	1.1	99%	0.91	21%	2%	0%	3%
Safety S80	0.79	87%	9%	9%	1.03	1.1	99%	0.90	21%	2%	0%	3%
Safety S140	0.78	85%	10%	10%	1.03	1.1	99%	0.90	22%	4%	0%	4%
Safety S20 Exterior	0.80	88%	9%	9%	1.02	1.1	99.9%	0.92	20%	0%	1%	2%
Safety S40 Exterior	0.80	89%	9%	9%	1.02	1.1	99.9%	0.92	20%	0%	0%	2%
Safety S70 Exterior	0.79	88%	8%	8%	1.02	1.1	99.9%	0.91	21%	0%	0%	3%
Anti Graffiti 4 & 6	N/A	N/A	N/A	N/A	N/A	N/A	99.9%	N/A	N/A	N/A	N/A	N/A

Commercial Solutions Division

3M Center, Building 220-12E-04 St. Paul, MN 55144
3M.com/windowfilm

© 3M 2021. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, January 2021. Please recycle.



3M™ Flat Glass Window Film – Single Pane ¼” (6mm) Tinted

Film	SHGC	VLT	Visible Reflection Exterior	Visible Reflection Interior	U Value	LSG (Light to Solar Gain)	UV Block	SC	TSER	Glare Reduction	Heat Loss Reduction	Heat Gain Reduction
1/4" Tinted Glass	0.63	53%	6%	6%	1.03	0.8	NA	0.72	37%	NA	NA	NA
Thinsulate CC75	0.40	44%	8%	10%	0.63	1.1	99.9%	0.46	60%	17%	40%	37%
Prestige 20	0.36	13%	5%	5%	0.47	0.4	99.9%	0.42	64%	76%	0%	43%
Prestige 40	0.37	24%	5%	6%	0.99	0.6	99.9%	0.42	63%	55%	3%	41%
Prestige 50	0.39	30%	6%	6%	0.99	0.8	99.9%	0.45	61%	43%	3%	38%
Prestige 60	0.41	36%	6%	7%	0.99	0.9	99.9%	0.47	59%	32%	3%	34%
Prestige 70	0.43	42%	6%	7%	0.99	1.0	99.9%	0.50	57%	22%	3%	31%
Prestige 20 Exterior	0.31	13%	5%	5%	1.02	0.4	99.9%	0.35	69%	77%	0%	52%
Prestige 40 Exterior	0.33	25%	5%	5%	1.02	0.8	99.9%	0.38	67%	53%	0%	47%
Prestige 70 Exterior	0.39	42%	6%	5%	1.02	1.1	99.9%	0.44	61%	20%	0%	39%
Prestige 90 Exterior	0.50	53%	6%	6%	1.02	1.1	99.9%	0.57	50%	1%	0%	21%
Ceramic 30	0.38	21%	9%	15%	1.02	0.6	99%	0.43	63%	60%	0%	40%
Ceramic 40	0.41	27%	8%	11%	1.03	0.6	99%	0.47	59%	50%	0%	34%
Ceramic 50	0.45	32%	7%	9%	1.03	0.7	99%	0.52	55%	40%	0%	28%
Night Vision 15	0.30	9%	16%	11%	0.98	0.3	99%	0.34	70%	82%	4%	52%
Night Vision 25	0.36	14%	10%	7%	1.00	0.4	99%	0.41	64%	74%	2%	43%
Night Vision 35	0.42	22%	8%	6%	1.03	0.5	99%	0.48	58%	58%	0%	33%
Silver P18	0.27	10%	23%	58%	0.93	0.4	99%	0.30	74%	82%	9%	58%
Neutral 20	0.32	9%	10%	19%	0.99	0.3	99%	0.37	68%	83%	3%	49%
Neutral 35	0.39	21%	10%	18%	0.99	0.5	99%	0.45	61%	60%	4%	38%
Neutral 50	0.47	31%	7%	10%	1.03	0.7	99%	0.54	53%	41%	0%	25%
Neutral 70	0.55	42%	6%	7%	1.03	0.8	99%	0.63	45%	22%	0%	13%
Affinity 15	0.27	5%	24%	25%	1.00	0.2	99%	0.31	73%	91%	2%	57%
Affinity 30	0.37	20%	14%	19%	0.94	0.5	99%	0.43	63%	62%	8%	41%
LE 20	0.26	12%	22%	58%	0.79	0.5	99%	0.29	75%	78%	24%	60%
LE35	0.27	17%	22%	60%	0.85	0.7	99%	0.31	73%	67%	17%	57%
Silver 15 External	0.16	10%	61%	23%	1.02	0.6	99%	0.18	84%	82%	0%	75%
Neutral 35 External	0.41	27%	10%	8%	1.02	0.6	99%	0.47	59%	50%	0%	34%
Ultra Prestige S50	0.40	29%	6%	7%	1.02	0.7	99.9%	0.46	60%	45%	1%	37%
Ultra Prestige S70	0.44	41%	6%	8%	1.02	0.9	99.9%	0.51	56%	23%	1%	30%
Ultra Night Vision S25	0.38	15%	10%	7%	1.02	0.4	99.9%	0.43	62%	73%	1%	40%
Safety Neutral S35	0.36	23%	22%	8%	1.02	0.6	99%	0.48	64%	56%	0%	42%
Safety Silver S20	0.30	11%	25%	62%	1.02	0.4	99%	0.33	71%	80%	0%	53%
Scotchshield Ultra S800	0.62	52%	6%	7%	1.02	0.8	99.9%	0.71	38%	1%	0%	2%
Safety S40	0.62	53%	6%	6%	1.02	0.8	99%	0.71	38%	1%	0%	1%
Safety S70	0.62	53%	6%	6%	1.02	0.8	99%	0.71	38%	1%	0%	1%
Safety S80	0.62	52%	6%	7%	1.02	0.8	99%	0.71	38%	1%	0%	2%
Safety S140	0.62	52%	6%	7%	1.02	0.8	99%	0.71	38%	1%	0%	2%
Safety S20 Exterior	0.62	53%	6%	6%	1.02	0.9	99.9%	0.72	38%	0%	0%	1%
Safety S40 Exterior	0.62	53%	6%	6%	1.02	0.9	99.9%	0.72	38%	0%	0%	1%
Safety S70 Exterior	0.62	53%	6%	6%	1.02	0.9	99.9%	0.71	38%	0%	0%	2%
Anti Graffiti 4 & 6	N/A	N/A	N/A	N/A	N/A	N/A	99%	N/A	N/A	N/A	N/A	N/A

Commercial Solutions Division

3M Center, Building 220-12E-04 St. Paul, MN 55144
3M.com/windowfilm

© 3M 2021. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, January 2021. Please recycle.



3M™ Flat Glass Window Film – Double Pane 1/4" (6mm) Clear

Film	SHGC	VLT	Visible Reflection Exterior	Visible Reflection Interior	U Value	LSG (Light to Solar Gain)	UV Block	SC	TSER	Glare Reduction	Heat Loss Reduction	Heat Gain Reduction
Dual 1/4" Clear	0.70	79%	15%	15%	0.47	1.1	NA	0.80	30%	NA	NA	NA
Thinsulate CC75	0.51	66%	21%	17%	0.35	1.3	99.9%	0.58	49%	16%	26%	27%
Prestige 20	0.51	19%	13%	5%	0.47	0.4	99.9%	0.58	42%	77%	0%	27%
Prestige 40	0.51	35%	14%	8%	0.47	0.7	99.9%	0.59	49%	55%	2%	27%
Prestige 50	0.53	45%	15%	9%	0.47	0.8	99.9%	0.61	47%	44%	2%	25%
Prestige 60	0.54	54%	15%	11%	0.47	1.0	99.9%	0.62	46%	32%	2%	22%
Prestige 70	0.56	62%	15%	13%	0.47	1.1	99.9%	0.64	44%	22%	2%	21%
Prestige 20 Exterior	0.24	18%	12%	6%	0.47	0.4	99.9%	0.27	76%	77%	0%	66%
Prestige 40 Exterior	0.29	37%	7%	13%	0.47	1.3	99.9%	0.33	71%	53%	1%	59%
Prestige 70 Exterior	0.39	63%	12%	14%	0.47	1.6	99.9%	0.44	61%	20%	0%	45%
Prestige 90 Exterior	0.56	78%	15%	16%	0.47	1.4	99.9%	0.64	45%	1%	1%	21%
Ceramic 30	0.50	32%	22%	16%	0.47	0.6	99%	0.58	50%	60%	1%	28%
Ceramic 40	0.54	40%	20%	14%	0.47	0.7	99%	0.62	46%	50%	1%	23%
Ceramic 50	0.57	47%	18%	12%	0.47	0.8	99%	0.66	43%	40%	1%	18%
Night Vision 15	0.40	14%	39%	11%	0.46	0.4	99%	0.46	60%	82%	3%	43%
Night Vision 25	0.49	22%	24%	8%	0.47	0.4	99%	0.57	51%	72%	1%	29%
Night Vision 35	0.55	32%	19%	8%	0.47	0.6	99%	0.64	45%	60%	1%	21%
Silver P18	0.33	15%	55%	58%	0.45	0.5	99%	0.37	67%	80%	5%	53%
Neutral 20	0.46	14%	25%	19%	0.47	0.3	99%	0.53	54%	83%	2%	34%
Neutral 35	0.51	32%	24%	19%	0.46	0.6	99%	0.59	49%	60%	2%	27%
Neutral 50	0.59	46%	18%	13%	0.48	0.8	99%	0.67	41%	41%	0%	16%
Neutral 70	0.64	62%	16%	12%	0.48	1.0	99%	0.74	36%	22%	0%	8%
Affinity 15	0.32	8%	57%	26%	0.47	0.3	99%	0.37	68%	90%	1%	54%
Affinity 30	0.46	30%	32%	20%	0.45	0.7	99%	0.53	54%	62%	5%	34%
LE 20	0.33	19%	52%	58%	0.40	0.4	99%	0.38	67%	76%	15%	53%
LE 35	0.32	28%	53%	61%	0.42	0.8	99%	0.37	68%	65%	11%	54%
Silver 15 External	0.14	15%	61%	54%	0.47	1.1	99%	0.17	86%	81%	0%	79%
Neutral 35 External	0.38	40%	12%	18%	0.47	1.1	99%	0.43	62%	50%	0%	46%
Ultra Prestige S50	0.53	43%	15%	9%	0.47	0.8	99.9%	0.61	47%	46%	0%	25%
Ultra Prestige S70	0.56	61%	16%	13%	0.47	1.1	99.9%	0.64	44%	23%	1%	20%
Ultra Night Vision S25	0.50	22%	24%	8%	0.47	0.4	99.9%	0.58	50%	73%	0%	28%
Safety Neutral S35	0.49	35%	27%	14%	0.47	0.7	99%	.63	51%	55%	1%	30%
Safety Silver S20	0.33	17%	59%	62%	0.47	0.5	99%	0.37	67%	79%	0%	53%
Scotchshield Ultra S800	0.69	77%	16%	16%	0.48	1.1	99.9%	0.79	31%	2%	0%	2%
Safety S40	0.68	77%	15%	15%	0.47	1.1	99%	0.78	32%	3%	0%	3%
Safety S70	0.68	77%	16%	16%	0.47	1.1	99%	0.78	32%	3%	0%	3%
Safety S80	0.68	77%	16%	16%	0.47	1.1	99%	0.78	32%	3%	0%	3%
Safety S140	0.68	72%	16%	16%	0.47	1.1	99%	0.78	32%	9%	0%	3%
Safety S20 Exterior	0.69	79%	15%	15%	0.47	1.1	99.9%	0.79	31%	0%	0%	2%
Safety S40 Exterior	0.68	79%	15%	15%	0.47	1.2	99.9%	0.78	32%	0%	0%	3%
Safety S70 Exterior	0.68	79%	15%	15%	0.47	1.2	99.9%	0.78	32%	0%	0%	3%
Anti Graffiti 4 & 6	N/A	N/A	N/A	N/A	N/A	N/A	99%	N/A	N/A	N/A	N/A	N/A

Commercial Solutions Division

3M Center, Building 220-12E-04 St. Paul, MN 55144
3M.com/windowfilm

© 3M 2021. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, January 2021. Please recycle.



3M™ Flat Glass Window Film – Double Pane 1/4" (6mm) Tinted

Film	SHGC	VLT	Visible Reflection Exterior	Visible Reflection Interior	U Value	LSG (Light to Solar Gain)	UV Block	SC	TSER	Glare Reduction	Heat Loss Reduction	Heat Gain Reduction
Dual 1/4" tint	0.51	47%	8%	13%	0.47	0.9	NA	0.58	49%	NA	NA	NA
Thinsulate CC75	0.37	40%	10%	15%	0.35	1.1	99.9%	0.42	63%	15%	26%	27%
Prestige 20	0.39	11%	8%	5%	0.47	0.4	99.9%	0.45	61%	76%	0%	24%
Prestige 40	0.39	21%	8%	8%	0.47	0.5	99.9%	0.45	61%	55%	2%	23%
Prestige 50	0.40	27%	8%	9%	0.47	0.7	99.9%	0.46	60%	44%	2%	22%
Prestige 60	0.41	32%	8%	10%	0.47	0.8	99.9%	0.47	59%	32%	2%	20%
Prestige 70	0.42	37%	8%	12%	0.47	0.9	99.9%	0.48	59%	22%	2%	18%
Prestige 20 Exterior	0.20	11%	12%	5%	0.47	0.4	99.9%	0.23	80%	77%	0%	61%
Prestige 40 Exterior	0.23	22%	6%	12%	0.47	1.0	99.9%	0.26	77%	53%	0%	55%
Prestige 70 Exterior	0.29	38%	7%	13%	0.47	1.3	99.9%	0.33	71%	21%	0%	43%
Prestige 90 Exterior	0.41	47%	9%	13%	0.47	1.2	99.9%	0.47	60%	1%	0%	20%
Ceramic 30	0.38	19%	11%	16%	0.47	0.5	99%	0.44	62%	60%	1%	25%
Ceramic 40	0.40	24%	10%	13%	0.47	0.6	99%	0.46	60%	50%	1%	21%
Ceramic 50	0.43	28%	9%	11%	0.47	0.7	99%	0.49	58%	40%	1%	16%
Night Vision 15	0.32	8%	17%	11%	0.46	0.3	99%	0.37	68%	83%	3%	37%
Night Vision 25	0.37	13%	12%	8%	0.47	0.4	99%	0.43	63%	73%	1%	27%
Night Vision 35	0.41	19%	10%	7%	0.47	0.5	99%	0.47	59%	60%	1%	19%
Silver P18	0.27	9%	23%	58%	0.45	0.3	99%	0.31	73%	81%	5%	47%
Neutral 20	0.36	8%	12%	19%	0.47	0.2	99%	0.41	64%	83%	2%	30%
Neutral 35	0.39	19%	12%	19%	0.46	0.5	99%	0.45	61%	60%	2%	23%
Neutral 50	0.44	28%	10%	13%	0.48	0.6	99%	0.50	57%	41%	0%	14%
Neutral 70	0.47	37%	9%	11%	0.48	0.8	99%	0.54	53%	22%	0%	7%
Affinity 15	0.27	5%	23%	25%	0.47	0.2	99%	0.31	73%	89%	1%	47%
Affinity 30	0.36	18%	15%	20%	0.45	0.5	99%	0.41	64%	62%	5%	29%
LE 20	0.27	11%	21%	58%	0.40	0.4	99%	0.31	73%	77%	15%	47%
LE 35	0.26	16%	22%	61%	0.42	0.6	99%	0.30	74%	66%	11%	48%
Silver 15 External	0.11	9%	61%	27%	0.47	0.8	99%	0.13	89%	81%	0%	78%
Neutral 35 External	0.29	24%	10%	14%	0.47	0.8	99%	0.34	71%	50%	0%	42%
Ultra Prestige S50	0.40	26%	9%	9%	0.47	0.6	99.9%	0.46	60%	46%	0%	21%
Ultra Prestige S70	0.42	37%	9%	12%	0.47	0.9	99.9%	0.48	58%	23%	0%	17%
Ultra Night Vision S25	0.38	13%	11%	8%	0.47	0.3	99.9%	0.44	62%	73%	0%	24%
Safety Neutral S35	0.38	21%	13%	14%	0.47	0.6	99%	0.47	62%	56%	0%	25%
Safety Silver S20	0.28	10%	24%	62%	0.47	0.4	99%	0.31	72%	79%	0%	45%
Scotchshield Ultra S800	0.5	46%	9%	14%	0.48	0.9	99%	0.58	50%	2%	0%	1%
Safety S40	0.5	47%	9%	14%	0.48	0.9	99%	0.58	50%	2%	0%	1%
Safety S70	0.5	47%	9%	14%	0.48	0.9	99%	0.58	50%	2%	0%	1%
Safety S80	0.5	46%	9%	14%	0.48	0.9	99%	0.58	50%	2%	0%	1%
Safety S140	0.5	46%	9%	14%	0.48	0.9	99%	0.58	50%	2%	0%	1%
Safety S20 Exterior	0.5	47%	8%	13%	0.47	0.9	99.9%	0.57	50%	0%	0%	2%
Safety S40 Exterior	0.5	47%	8%	13%	0.47	0.9	99.9%	0.57	50%	0%	0%	2%
Safety S70 Exterior	0.5	47%	8%	13%	0.47	1.0	99.9%	0.57	51%	1%	0%	2%
Anti Graffiti 4 & 6	N/A	N/A	N/A	N/A	N/A	N/A	99%	N/A	N/A	N/A	N/A	N/A

Commercial Solutions Division

3M Center, Building 220-12E-04 St. Paul, MN 55144
3M.com/windowfilm

© 3M 2021. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, January 2021. Please recycle.



Abbreviations

SHGC – Solar Heat Gain Coefficient

VLT – Visible Light Transmission

LSG – Light to Solar Gain

UV Block – Percent of UV light (300-380nm) blocked

SC – Shading Coefficient

TSER – Total Solar Energy Rejected

Health and Safety

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to [3M.com/SDS](https://www.3m.com/SDS), or by mail or in case of an emergency, call 1-888-364-3577 or 1-651-737-6501. When using any equipment, always follow the manufacturers' instructions for safe operation.

Technical Information

Technical information and data, recommendations, and other statements provided by 3M are based on information, tests, or experience which 3M believes to be reliable, but the accuracy or completeness of such information is not guaranteed. Such technical information and data are intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. The typical values shown should not be used for the purpose of specification limits. If you have questions about this Product, contact the Customer Service Department at 1-800-852-9722.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty

3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

Limited Remedy

If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

No Extension of Warranty

In the case of an approved warranty claim, the replacement Product will carry only the remaining term of the original warranty period.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

Commercial Solutions Division

3M Center, Building 220-12E-04 St. Paul, MN 55144

[3M.com/windowfilm](https://www.3m.com/windowfilm)

© 3M 2021. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.

All other trademarks are property of their respective owners. Revision A, January 2021. Please recycle.

