



The science of shine.

Advanced technology for a premium finish.

This is where groundbreaking science and real-world performance combine. A professional ceramic coating that's easy to apply, with a fast-cure formula for same-day service. Our treatment helps enrich paint gloss and shine, for a durable new-polish look that will last.



3M™ Ceramic Coating

Simplified application.

- Cures quickly with no special equipment, allowing for same-day service
- 100% active ingredients and low-VOC formula with no carrier solvents or strong vapors/odors
- One formula for use on multiple surfaces, including metal, plastic trim, glass and wheels
- Unique applicator system for ease of coverage

Premium performance.

- Long-lasting coating with excellent water beading
- High-gloss shine maintains new-polish “wet look”
- Durable chemical resistance stands up to salt, acid rain, tree sap and more
- Extremely slick surface allows for easier removal of dirt and debris



Treatment options

Deluxe (one layer) — Lasts up to 3 years with regularly scheduled maintenance

Premier (two layers) — Lasts up to 5 years with regularly scheduled maintenance

Engineered to lead the industry.

	Application Time < 2 hrs.	Low VOC/ Low Odor	Slickness < 0.1 Coefficient of Friction (CoF)	Initial Receding Contact Angle ≥ 100	Receding Contact Angle Post-Scrub ≥ 100	Durability Static Contact Angle (SCA) ≥ 90 After 1 Year
3M™ Ceramic Coating	✓	✓	✓	✓	✓	✓
Competitor A	✓	✗	✗	✗	✗	✗
Competitor B	✓	✓	✗	✗	✗	✓
Competitor C	✗	✗	✗	✗	✗	✗

Order Information

Part Number	Product Description
39901	3M™ Ceramic Coating, 4 kits per case
39903	3M™ Glass Pre-Treatment, 4 fl. oz. (118 mL), 6 per case
39905	3M™ Ceramic Boost Spray, 8 U.S. fl. oz. (236 mL), 6 per case

Discover the science of shine at [3M.com/CeramicCoating](https://www.3m.com/CeramicCoating).



3M Automotive Aftermarket Division

3M Center, Building 223-06S-07

St. Paul, MN 55144-1000

1-877-666-2277

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment. **Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. For industrial/occupational use only. Not for consumer sale or use.

©3M 2021. All rights reserved. 3M is a trademark of 3M Company. All other trademarks are property of their respective owners. Please recycle. Printed in USA.

60-4405-0064-7