



Fall Protection



Support at every level.


3M™ DBI-SALA® ExoFit™ X-Series Harnesses

X100 | X200 | X300


Designed for ultimate productivity and performance.

Wherever your work takes you, staying comfortably fitted in your safety harness is critical. Precision-tuned for performance and productivity, our new line of 3M™ DBI-SALA® ExoFit™ X-Series Harnesses change the way you work and redefine what you should expect from a safety harness.


3M™ DBI-SALA® ExoFit™ X100 Harness



3M™ DBI-SALA® ExoFit™ X200 Harness



3M™ DBI-SALA® ExoFit™ X300 Harness



3M™ DBI-SALA® ExoFit™ X-Series Harnesses come equipped with these standard harness features:

Revolving Torso Adjusters**

- Patented buckles lock webbing into place to maintain a safe and comfortable fit.

Personal SRL Adapter**

- Confidently connect personal SRLs to the harness with ease.

Anti-Slide Dorsal D-Ring Pad

- Greatly reduces dorsal D-ring slide and allows for adjustment to help ensure a proper and safe fit.

Suspension Trauma Relief Straps*

- Integrated low-profile design between harness webbing.

Auto-Resetting Lanyard Keepers*

- Fast and easy parking of snap hooks and carabiners.

Comfort Padding

- Features breathable mesh under-side.

Integrated RFID

- RFID technology for simplified inventory, inspection and record management.

ANSI/OSHA

- Tested and certified to ANSI/ASSP Z359.11-2021 (310 lbs.) standard. Conforms to the requirements of 29 CFR OSHA 1910.140 and 1926.502. (420 lbs.) regulations.

*3M Patented Design/Feature
**Available on select models

3M™ DBI-SALA® ExoFit™ X300 Harness

For those who refuse to compromise.

One of the most advanced harnesses just got better. With industry-leading comfort and fit, it's optimized to help increase the performance and productivity of professionals who take pride in a job done right.

Personal SRL adapter^{*,}** allows for connection of personal SRLs with confidence and ease

Automatic stand-up back D-ring^{*} conveniently connect faster and easier

Anti-slide dorsal D-ring pad

Weight Distribution System^{*} takes weight off your shoulders^{**}

3M™ Scotchlite™ reflective panels to enhance visibility in low-light environments

Auto-resetting lanyard keepers^{*}

Integrated low-profile suspension trauma relief straps^{*}

Integrated RFID tag, enabling inventory, inspection and record management

Auto-locking quick-connect buckles^{*,}** to help maintain fit—greatly reducing buckle slide

Comfort back pad with built-in durable shoulder caps

Radio/cell phone holster^{}**

Revolving torso adjusters^{*,}** are fast and easy to adjust and lock webbing into place—maintaining a comfortable and safe harness fit

Lightweight aluminum tongue-buckle and durable belt^{}**

Lightweight aluminum D-rings

Comfort hip pad^{}** with robust belt loops and rigid belt for tool pouch-carrying convenience

3M Patented Design/Feature
****Available on select models**

3M™ DBI-SALA® ExoFit™ X-Series Harnesses

Feature Matrix



ExoFit™ X100
Harness



ExoFit™ X200
Harness



ExoFit™ X300
Harness

| Feature | X100 | X200 | X300 |
|---|-------------------------|----------------------------|-----------------------------|
| Personal SRL Adapter* ** | Molded Tunnel | Steel | Aluminum |
| Exclusive Weight Distribution System Models Available* ** | ✓ | | ✓ |
| Breathable Shoulder Pads | Removable | Mesh Design | Durable Shoulder Cap Design |
| Leg Padding | Accessory Kit Available | ✓ | ✓ |
| Exclusive Automatic Stand-Up D-ring* | | Steel | Aluminum |
| Exclusive Locking Buckles Available* ** | | Dual-Locking Quick-Connect | Auto-Locking Quick-Connect |
| Lightweight Aluminum Hardware Models Available | | ✓ | ✓ |
| 3M™ Scotchlite™ Reflective Material | | | Padding Panels |
| Exclusive X-Style Quick-Connect Chest Buckle Models Available* ** | | | ✓ |

Please check our full product list to find the harnesses that best accommodate you and your team.

*3M Patented Design/Feature
**Available on select models

New ExoFit™ comfort harnesses available in a variety of styles:

- Vest
- Vest Climbing
- Vest Positioning
- Vest Retrieval
- Vest Climbing/Positioning
- Vest Climbing/Positioning/Retrieval
- X-Style
- Construction
- Construction Climbing
- Construction Positioning
- Construction Climbing/Positioning
- Construction Weight Distribution Positioning
- Construction Weight Distribution Climbing/Positioning
- Tower Climbing/Positioning
- Wind Energy Vest Climbing/Positioning
- Wind Energy Construction Climbing/Positioning
- Oil & Gas Vest Climbing/Positioning
- Oil & Gas Construction Climbing/Positioning
- Construction Mining

Find the fit for your industry and application.

In our dedicated pursuit to help workers stay safe at heights, we have developed performance optimizations for a variety of industries and working applications.



General Industry

Equipped with lightweight aluminum dorsal D-ring (automatic stand-up D-ring design enables easier connections).



Construction

Equipped with robust belt loops, lightweight aluminum positioning D-rings and supportive tongue-buckle belt on comfort hip pad.



Construction Weight Distribution

Equipped with robust construction hip pad and lightweight back bar to redistribute weight and fatigue from shoulder area.



Wind Energy

Equipped with front D-ring for climbing, side D-rings and seat sling for comfortable positioning at height.



Telecommunications

Equipped with front D-ring for climbing, side D-rings and seat sling for comfortable positioning at height.

| Featured X300 Harness | |
|-----------------------|---------|
| Small | 1113001 |
| Medium | 1113004 |
| Large | 1113007 |
| X-Large | 1113010 |
| 2X-Large | 1113013 |

| Featured X300 Harness | |
|-----------------------|---------|
| Small | 1113121 |
| Medium | 1113124 |
| Large | 1113127 |
| X-Large | 1113130 |
| 2X-Large | 1113133 |

| Featured X300 Harness | |
|-----------------------|---------|
| Small | 1403098 |
| Medium | 1403099 |
| Large | 1403100 |
| X-Large | 1403101 |
| 2X-Large | 1403102 |

| Featured X300 Harness | |
|-----------------------|---------|
| Small | 1113210 |
| Medium | 1113211 |
| Large | 1113212 |
| X-Large | 1113213 |
| 2X-Large | 1113214 |

| Featured X300 Harness | |
|-----------------------|---------|
| Small | 1113190 |
| Medium | 1113191 |
| Large | 1113192 |
| X-Large | 1113193 |
| 2X-Large | 1113194 |

Find the fit for your industry and application with our NEW 3M™ DBI-SALA® ExoFit™ X-Style Harnesses.

Backed by science to fit your body. Our new quick-connect chest buckle, simplified harness sizing ranges, and leg straps have been designed with you in mind. No matter the season, wardrobe or body shape, the 3M™ DBI-SALA® ExoFit™ X300 Comfort X Style Safety Harness will help ensure you select a harness that fits your body securely.



**X-Style
General
Industry**



**X-Style
Construction**



**X-Style
General Industry
Climbing**



**X-Style
Climbing/
Positioning
(Wind Energy)**



**X-Style
Tower Climbing
(Telecommunications)**

Equipped with contoured form-fitting chest configuration to don easily in 'X' shape. X-Style harness buckle contours to your body, providing an optimal central connection. New horizontal leg straps complement the range of motion workers require on the jobsite.

| Featured X300 Harness | |
|-----------------------|---------|
| 3X-Small/ 2X-Small | 1403237 |
| X-Small/ Small | 1403198 |
| Medium/ Large | 1403199 |
| X-Large/ 2X-Large | 1403200 |

| Featured X300 Harness | |
|-----------------------|---------|
| 3X-Small/ 2X-Small | 1403240 |
| X-Small/ Small | 1403207 |
| Medium/ Large | 1403208 |
| X-Large/ 2X-Large | 1403209 |

| Featured X300 Harness | |
|-----------------------|---------|
| 3X-Small/ 2X-Small | 1403238 |
| X-Small/ Small | 1403201 |
| Medium/ Large | 1403202 |
| X-Large/ 2X-Large | 1403203 |

| Featured X300 Harness | |
|-----------------------|---------|
| 3X-Small/ 2X-Small | 1403242 |
| X-Small/ Small | 1403213 |
| Medium/ Large | 1403214 |
| X-Large/ 2X-Large | 1403215 |

| Featured X300 Harness | |
|-----------------------|---------|
| 3X-Small/ 2X-Small | 1403241 |
| X-Small/ Small | 1403210 |
| Medium/ Large | 1403211 |
| X-Large/ 2X-Large | 1403212 |



3M Fall Protection
3833 SALA Way
Red Wing, MN 55066 USA

Phone 800.328.6146
Email 3Mfallprotection@mmm.com
Web 3M.com/FallProtection

3M, DBI-SALA, ExoFit, and Scotchlite are trademarks of 3M.
© 3M 2024. All rights reserved. 70-0717-6094-10