

















Goggle features overview

		GOGGLES							
		4700 Series	4800 Series	GoggleGear™ 500	2890 Series	GoggleGear™ 6000	Fahrenheit™	Solus™ 1000 TPE Kits	Modul-R™
									
Protection properties	Impact protection	B	B	BT	BT: 2890, 2890S, 2891, 2891S FT: 2890A, 2890SA BT: 2890S B: 2895S	BT	BT: -71360-00011, 00012, 00014 F: 71360-00013, 00015, 00017	BT	BT
	3 Splash/droplet		●	●	●	●	●	S1201SGAF-TSKT S1101NSGAF-TSKT	●
	4 Large dust particles			●	●	●	●	S1201SGAF-TSKT S1101NSGAF-TSKT	●
	5 Gas and fine dust				2890SA, 2895S, 2891S				
	9 Molten metals and hot solids				2891, 2891S		71360-00013, 00015, 00017		
	K Resistance to surface damage by fine particles			●	2890, 2890S, 2895S, 2891, 2891S	●		●	
	N Resistance to fogging			●	●	●		●	
Design	Over the Glasses (OTG)				●	●	●		●
	Elasticated textured strap	●	●	●	●	●	●	●	●
	Neoprene strap			GG501N SGAF		GG6001N SGAF	71360-00015	S1101NSGAF-TSKT	
	Direct ventilation	●							
	Indirect ventilation			●	2890, 2890A, 2891	●	71360-00011; 00012; 00013; 00014	●	●
	Sealed				2890S, 2890SA, 2895S, 2891S		71360-00015, 00017		
	Approx. weight	66g	66g	50g	86g-99g	82g	128g	44g	81g

Goggle features overview

		GOGGLES							
		4700 Series	4800 Series	GoggleGear™ 500	2890 Series	GoggleGear™ 6000	Fahrenheit™	Solus™ 1000 TPE Kits	Modul-R™
									
Accessory	Prescription insert			●				●	
	Replaceable lens				2890A, 2890SA				
Lens colour	Clear UV Filter 2-1.2 Reference end 01	●	●	●	2890, 2890A, 2890S, 2890SA, 2891, 2891S	●	●	●	●
	Dark Grey Filter 3.1 Reference end 02			●		●		●	
	Amber UV Filter 2-1.2 Reference end 03							●	
	Indoor/outdoor							●	
	Shade 5			●	2895S				
	Scotchgard™ Anti-Fog (K&N)			●	2891, 2891S	●		●	
Coatings	Traditional anti-fog (with anti-scratch properties)		4800AF		2890, 2890A, 2890S, 2890SA, 2895S		71360-00011, 00013, 00014, 00015, 00017		●
	Traditional anti-scratch						71360-00012		