

3M™ Visible-light Reflective PGU (VRP)

Product Description

3M™ Visible-light Reflective PGU (VRP) is a reflective polarizing film used in Head-up Display (HUD) applications to provide high brightness for the projected image while reducing undesired visible light sources projected back to the Picture Generating Unit (PGU) through the HUD assembly. It is a multilayer polyester-based film with 3M's optically clear adhesive.

Construction Description

Multilayer structure with optically clear adhesive, adhesive release liner, and multilayer film protective liner. Cross-section representation with protective masking (not to scale).

| Performance Metrics | |
|-----------------------|--------------|
| Thickness | 73um ± 5um |
| Transmission in Pass | 80% Minimum |
| Reflectivity in Block | 90% Minimum |
| Haze | 1.5% Maximum |



Removable Protective Film

Multilayer Optical Film

Optically Clear Adhesive

Adhesive Release Liner

| Environmental Metrics | |
|-----------------------|---|
| Heat resistance | 105°C x 1,000 hours |
| Cold resistance | -40°C x 1,000 hours |
| Humidity resistance | 65°C, 95%RH x 1,000 hours |
| Thermal shock | (-40°C x 1hr / 95°C x 1hr) x 100 cycles |

| Testing Description Results | |
|-----------------------------|---|
| Appearance | No significant appearance changes by naked eye observation |
| Transmittance | Equal or greater than 80% of initial value |
| Reflectivity | Equal or greater than 80% of initial value |
| Change of Color | Difference from initial value, ΔE^* , is equal or less than 2.0 |

Technical Information

The technical information, recommendations and other statements contained in this document are based on tests or experience 3M believes reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within the user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



3M Display Materials & Systems Division

3M Center, Building 235-1E-54
St. Paul, MN 55144-1000 U.S.A.

Phone 1-800-3M HELPS

3M is a trademark of 3M Company.

All other trademarks herein are the property of their respective owners.

© 3M 2021. All rights reserved.

dz29671