



Tools that take it to  
**the next level.**

Introducing New  
3M™ Power Tools.



3M™ Pneumatic  
Angle Grinder



3M™ Pneumatic  
Sander\*



# New 3M™ Pneumatic Angle Grinders and 3M™ Pneumatic Sanders

These powerful tools feature superior performance and world-class ergonomic designs. They're built with robust components for durability and reliability in the harshest industrial conditions.



**3M™ Pneumatic Angle Grinder**



**3M™ Pneumatic Sander**

*\*Not for use with abrasives that require a guard.*

- ▶ 1.5HP (1100 W Power)
- ▶ Wheel autobalancer
- ▶ Spindle lock
- ▶ Vibration-reducing side handle with added padding—interchangeable for right or left hand usage.
- ▶ Available accessories provide maximum functionality and flexibility
- ▶ Rear exhaust directs exhaust and swarf away from the workpiece

These tools can be used with a variety of right right angle abrasives - Fibre Discs, Bonded Wheels, Flap Discs and select non-woven Scotch-Brite™ abrasives.



## Get the system advantage.

When you combine our new pneumatic tools with the new 3M™ Cubitron™ II Fibre Discs 982CX Pro and the new 3M™ Disc Back-up Pad, you're setting yourself up to a new level of productivity. Each component of this system has been engineered to optimize abrasive life, cut rate and consistency—helping to improve productivity and lower overall costs.

UPC	Tool Dia. In. (mm)	Motor HP (W)	Max RPM	Airflow Rate SCFM (LPM)	Weight Pound (kg)	Length In. (mm)	Height In. (mm)	Air Inlet Thread	Thread Size
<b>3M™ Pneumatic Angle Grinder</b>									
06-38060-88566-6	115–125 (4.5–5.0)	1.5 (1100)	12,000	43 (1.2)	5.3 (2.4)	11.0 (279)	105 (4.0)	3/8 NPT	5/8-11
<b>3M™ Pneumatic Sander</b>									
06-38060-88577-2	115–125 (4.5–5.0)	1.5 (1100)	12,000	43 (1.2)	4.9 (2.2)	11.0 (279)	105 (4.0)	3/8 NPT	5/8-11

Accessories	UPC	Diameter (Inches)	Max RPM	Min/Case
	<b>3M™ Disc Back-up Pad, Ribbed, Extra Hard – One Piece</b>			
	06-38060-88655-7	4 1/2	13,300	10
	06-38060-88656-4	5	12,000	10
	06-38060-88657-1	7	8,600	10
	<b>3M™ Disc Back-up Pad Mounting Kit (Optional. Not needed with the new 3M tools.)</b>			
	06-38060-88968-8	Includes 3M™ Retainer Nut PN 02618, 3/8" PG Wheel Spacer and 1/2" Spacer.	N/A	1

### TECH TIP:

**NEW, convenient one piece back-up pad, and Mounting Kit (both sold separately)**

**For 3M™ Power Tool Warranty and Repair Service, call 1-800-362-3550**  
Available in the US only

**For occupational use only. Not for consumer sale or use.**

**Warranty and Limited Remedy:** 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal or equitable theory asserted.



**Abrasive Systems Division**  
3M Center, Building 233-6N-02  
St. Paul, MN 55144-1000  
1-866-279-1235

**Take advantage of performance and productivity that will set your shop up for success.**  
**3M.com/Metalworking**

3M and Cubitron are trademarks of 3M Company.  
Please recycle. Printed in USA.  
© 3M 2021. All rights reserved. 61-5005-0011-3