

Performance Guarantee Warranted Durabilities Warranty is stated in years for ZONE 2 First number represents vertical warranty / second number represents non-vertical warranty of graphics Release: March 2021
3M Australia & New Zealand

| Please review the notes below the table | Transportation | | | Exterior | | | Interior | | | Watercraft | | |
|---|-------------------------------------|--------|------|---------------|--------|------|---------------|--------|------|---------------------------------|--------|------|
| | Car, Van, Truck, Bus, Trailer, Rail | | | Exterior Sign | | | Interior Sign | | | Personal watercraft, Boat, Ship | | |
| | Good | Better | Best | Good | Better | Best | Good | Better | Best | Good | Better | Best |
| SV480 / LX480 | 4/1 | 4/2 | 4/3 | 3 | 4 | 4 | 6 | 6 | 6 | - | 2 | 2 |
| IJ180**/ IJ280 | 4/1 | 4/2 | 4/3 | 3 | 4 | 4 | 6 | 6 | 6 | - | 2 | 2 |
| IJ380 | - | 4/2 | - | - | - | - | - | - | - | - | - | - |
| IJ680, IJ680CR, 780 | 4/1 | 4/2 | 4/3 | 3 | 4 | 4 | 6 | 6 | 6 | - | 2 | 2 |
| IJ8150 | - | - | - | 3 | 3 | 3 | 5 | - | - | - | - | - |
| IJ3650 | - | - | - | 3 | 4 | 4 | 6 | 6 | 6 | - | - | - |
| IJ3630, IJ3730 | - | - | - | 3 | - | 4 | 6 | 6 | 6 | - | - | - |
| Panagraphics 3, FS-1 | - | - | - | 3 | - | 4 | 6 | - | 6 | - | - | - |
| 40C, IJ40 | 3 | - | - | 3 | - | - | 4 | - | - | 1 | - | - |
| IJ35 | 3 | - | - | 3 | - | - | 4 | - | - | 1 | - | - |
| IJ39 | 3 | - | - | 3 | - | - | 4 | - | - | 1 | - | - |
| 48C | 3 | - | - | 3 | - | - | 4 | - | - | 1 | - | - |

| Protection Options | Good | Better | Best |
|----------------------|--|---------------------|--------------|
| SV480 / LX480 | 8518, 8519, 8520, 8588G, 8590M, 8993* | 8548G, 8549L, 8550M | 8528 |
| IJ180**/ IJ280 | 8518, 8519, 8520, 8588G, 8590M, 8428G, 8993* | 8548G, 8549L, 8550M | 8528 |
| IJ380 | - | 8548G, 8549L, 8550M | - |
| IJ680, IJ680CR, 780 | 8518, 8519, 8588G, 8993* | 8548G, 8549L | 8528 |
| IJ8150 | IJ8150, 8518 | - | - |
| IJ3650 | 8518, 8519, 8520, 8588G, 8590M, 8993* | 8548G, 8549L, 8550M | 8528 |
| IJ3630, IJ3730 | 8518, 8519, 8520 | - | 3658G, 3660M |
| Panagraphics 3, FS-1 | 8518, 8519, 8520 | - | 3658G, 3660M |
| 40C, IJ40 | 8508, 8509, 8510, IJ40-114, IJ40-124 | - | - |
| IJ35 | 8508, 8509, 8510, IJ40-114, IJ40-124 | - | - |
| IJ39 | 8508, 8509, 8510, IJ40-114, IJ40-124 | - | - |
| 48C | 8048G, 8050M | - | - |

* 8993 for vertical applications only
** Excludes IJ180mC-10UR

For CMYKLCmLk inks only
All boxes with only 1 number do not have a non-vertical warranty

3M Performance Guarantee covers only the performance of the recommended 3M Graphics Products used in the graphic construction for the stated periods when imaged with the printers and OEM inks listed in the most current version of the 3M Performance Guarantee Matrix. To find the best combination of film and graphic protection for your application, including conformability, gloss, adhesion to substrate, limitations of end use and other attributes, please review relevant product and instruction bulletins. For additional warranty information follow this link to the [3M Graphics Warranty Bulletin](#)

Definitions

Zone 2: All locations South of a straight line between Hervey Bay QLD and Yankep WA
 Transportation: Application to any vehicle that is in regular use (no static exposure of graphic)
 Exterior: Application with a static geographic direction without exposure to adjacent reflecting surfaces
 Interior: Application inside a building without direct exposure to the elements
 Watercraft: Application to any type of watercraft above the static waterline
 Vertical: The entire face of the graphic is +/- 15° from vertical