

**Performance Guarantee Warranted Durabilities** Warranty is stated in years for ZONE 3 First number represents vertical warranty / second number represents non-vertical warranty of graphics Release: March 2021  
3M Australia & New Zealand

Please review the notes below the table	Transportation			Exterior			Interior			Watercraft		
	Car, Van, Truck, Bus, Trailer, Rail			Exterior Sign			Interior Sign			Personal watercraft, Boat, Ship		
	Good	Better	Best	Good	Better	Best	Good	Better	Best	Good	Better	Best
SV480 / LX480	3	3/1	3/2	2	3	3	6	6	6	-	1	1
IJ180**/ IJ280	3	3/1	3/2	2	3	3	6	6	6	-	1	1
IJ380	-	3/1	-	-	-	-	-	-	-	-	-	-
IJ680, IJ680CR, 780	3	3/1	3/2	2	3	3	6	6	6	-	1	1
IJ8150	-	-	-	2	2	2	5	-	-	-	-	-
IJ3650	-	-	-	2	3	3	6	6	6	-	-	-
IJ3630, IJ3730	-	-	-	2	-	3	6	6	6	-	-	-
Panagraphics 3, FS-1	-	-	-	2	-	3	6	-	6	-	-	-
40C, IJ40	2	-	-	2	-	-	4	-	-	-	-	-
IJ35	2	-	-	2	-	-	4	-	-	-	-	-
IJ39	2	-	-	2	-	-	4	-	-	-	-	-
48C	2	-	-	2	-	-	4	-	-	-	-	-

Protection Options	Good	Better	Best
SV480 / LX480	8518, 8519, 8520, 8588G, 8590M, 8993*	8548G, 8549L, 8550M	8528
IJ180**/ IJ280	8518, 8519, 8520, 8588G, 8590M, 8428G, 8993*	8548G, 8549L, 8550M	8528
IJ380	-	8548G, 8549L, 8550M	-
IJ680, IJ680CR, 780	8518, 8519, 8588G, 8993*	8548G, 8549L	8528
IJ8150	IJ8150, 8518	-	-
IJ3650	8518, 8519, 8520, 8588G, 8590M, 8993*	8548G, 8549L, 8550M	8528
IJ3630, IJ3730	8518, 8519, 8520	-	3658G, 3660M
Panagraphics 3, FS-1	8518, 8519, 8520	-	3658G, 3660M
40C, IJ40	8508, 8509, 8510, IJ40-114, IJ40-124	-	-
IJ35	8508, 8509, 8510, IJ40-114, IJ40-124	-	-
IJ39	8508, 8509, 8510, IJ40-114, IJ40-124	-	-
48C	8048G, 8050M	-	-

\* 8993 for vertical applications only  
\*\* Excludes IJ180mC-10UR

For CMYK/LmLk inks only  
All boxes with only 1 number do not have a non-vertical warranty

**Definitions**

Zone 3: All locations North of a straight line between Hervey Bay QLD and Yancheep WA  
 Transportation: Application to any vehicle that is in regular use (no static exposure of graphic)  
 Exterior: Application with a static geographic direction without exposure to adjacent reflecting surfaces  
 Interior: Application inside a building without direct exposure to the elements  
 Watercraft: Application to any type of watercraft above the static waterline  
 Vertical: The entire face of the graphic is +/- 15° from vertical

3M Performance Guarantee covers only the performance of the recommended 3M Graphics Products used in the graphic construction for the stated periods when imaged with the printers and OEM inks listed in the most current version of the 3M Performance Guarantee Matrix. To find the best combination of film and graphic protection for your application, including conformability, gloss, adhesion to substrate, limitations of end use and other attributes, please review relevant product and instruction bulletins. For additional warranty information follow this link to the [3M Graphics Warranty Bulletin](#)