

# Your ultimate printing solution.

---







Get the flexibility you need to solve  
your biggest fabrication challenges  
with 3M Digital Printing Solutions.



# Why 3M? Because finding a printer tailored to your business is important.

Other sheeting manufacturers might only offer one brand of printer. We're different. We work with three leading digital printer manufacturers to give you the flexibility to choose the best solution for your unique application.



Model	Durst Rho 163 TS   HS	EFI H1625-RS	HP Latex 1500	HP Latex 700	HP Latex 800	HP Latex 360/365
						
	Hybrid printer (roll-to-roll and flatbed)	Hybrid printer (roll-to-roll and flatbed)	Roll-to-roll printer with dual roll capabilities	Roll-to-roll printer	Roll-to-roll printer	Roll-to-roll printer
Productivity	25 m <sup>2</sup> /hr, 275 ft <sup>2</sup> /hr 50 m <sup>2</sup> /hr, 550 ft <sup>2</sup> /hr	18 m <sup>2</sup> /hr 200 ft <sup>2</sup> /hr	12 m <sup>2</sup> /hr, 199 ft <sup>2</sup> /hr 24 m <sup>2</sup> /hr, 260 ft <sup>2</sup> /hr	16 m <sup>2</sup> /hr 172 ft <sup>2</sup> /hr	17 m <sup>2</sup> /hr 182 ft <sup>2</sup> /hr	8 m <sup>2</sup> /hr 96 ft <sup>2</sup> /hr
Ink Technology	UV	UV	Latex	Latex	Latex	Latex
Ink	3M™ Piezo InkJet 8900UV Series	3M™ Piezo InkJet 8900UV Series	HP Series 881	HP Series 832	HP Series 873	HP Series 831/871
Ink Volume	3 litre	1 litre/bottle (2/carton)	5 Litre	1 Litre	3 Litre	775 mL/cartridge
RIP Software	Caldera GrandRIP+	EFI Fiery XF RIP	FlexiPRINT & CUT Authorized 3M Traffic Edition L 1500	FlexiPRINT & Cut Authorized 3M™ Traffic Edition 21	FlexiPRINT & Cut Authorized 3M™ Traffic Edition 21	FlexiPrint & Cut 3M Authorized Traffic Edition 21
Contact	<a href="http://www.durst.it">www.durst.it</a>	<a href="http://www.efi.com">www.efi.com</a>	<a href="http://www.hp.com/go/Latex1500">www.hp.com/go/Latex1500</a>	<a href="http://www.hp.com/go/latex700series">www.hp.com/go/latex700series</a>	<a href="http://www.hp.com/go/latex800series">www.hp.com/go/latex800series</a>	<a href="http://www.hp.com/go/Latex365">www.hp.com/go/Latex365</a>



# Your work helps keep our roads safe. Let us help.

---


Going above and beyond the minimum safety requirements will set your business apart from the competition. That's why we continue to advocate for new safety standards during our product development process.



## 3M™ MCS™ Warranty\*

When your signs are made start to finish with 3M™ MCS™ components, you're covered by the most robust Warranty in the business.

\*3M offers a 12-year warranty for 3M™ Diamond Grade™ DG<sup>3</sup> Reflective Sheeting.







# Support when you need it.

No matter how complex your  
application becomes, we're there  
to make sure the job gets done.

## 24/7

support from  
Application Engineers  
around the world.

## Put 80 years of experience on your side.

See how 3M Digital Printing can benefit you.  
Visit [3M.ca/DigitalSignPrinting](https://3M.ca/DigitalSignPrinting) or contact  
your local 3M representative.



**3M Transportation Safety Division**  
**3M Canada**  
P.O. Box 5757  
London, Ontario N6A 4T1  
1-800-267-4414  
[3M.ca/RoadSafety](https://3M.ca/RoadSafety)

3M, 3M Science. Applied to Life., MCS and Diamond Grade are  
trademarks of 3M. Used under license in Canada.  
© 2021, 3M. All rights reserved. All other trademarks are the  
property of their respective owners. 2108-21644 E