

11

Three duct tapes that can do it all

Coversion manual

3M[™] Duct Tapes DT Series

88.1) m 8,42 x mm 8,



Be equipped for the day

Tackle your everyday tasks with 3M[™] Duct Tapes DT Series in three strengths. They resist curling, have a consistent unwind and tear off the roll cleanly for the ultimate in ease of handling and application.

Enlarged photo to show unique texture of 3M[™] Super Duty Duct Tape DT17.







The rolls you always want to keep on hand

3M[™] Duct Tapes DT Series offer hand tearability, high tensile strength and conformability.



Conformable with instant bond

Unique design offers high instant adhesion coupled with maximum conformability.



- Ideal for contoured surfaces and quick labeling
- Good tensile strength for light-duty bundling
- Use for quick repairs, splicing, temporary holding and fast attachments



Versatility with holding power

Good holding power with a broad attribute performance make this the go-to choice for demanding jobs.



- Sticks immediately and stays on irregular, hard-tobond surfaces without lifting — even on most plastics
- Water-resistant, polyethylene backing resists wear and light abrasion — good for securing temporary floor coverings
- Moisture-resistant seal in many containment situations, such as pipe sealing and attaching heavy poly draping
- Low-tack roll edges so rolls stay cleaner



Super thick for super tough jobs

Ultra-thick, water-resistant backing resists wear and abrasion while still tearing easily by hand.



- Aggressive rubber adhesive grips instantly to a variety of surfaces including metal, glass, plastic and sealed concrete
- Excellent for repairing, seaming, extra-strength bundling and helps in protecting metal parts and surfaces against sandblast overspray
- Superior strength for the most demanding applications
- Low-tack roll edges so rolls stay cleaner

Duct tape simplified

Three tapes in three strengths to tackle the bulk of your everyday duct taping tasks.

3M" DT Series	Backing material	Adhesive type	Thickness (mm)	Tensile strength N/cm	Elongation at break %	Adhesion to steel N/cm	Instant adhesion	Roll size	Color
	Based on ASTM Test Method:		D-3652*	D-3759	D-3759	D-3330			
3M [™] All Purpose Duct Tape DT8	Polyethylene film over cloth scrim	Synthetic/natural rubber blend	0.20	40.7	20%	7.5	~	48 mm x 54.8 m	Silver, Black
								48 mm x 22.9 m	Silver, Black
3M [™] Heavy Duty Duct Tape DT11	Polyethylene film over cloth scrim	Synthetic/natural rubber blend	0.27	49	20%	8.4	~	48 mm x 54.8 m	Silver, Black
3M [™] Super Duty Duct Tape DT17	Polyethylene film over cloth scrim	Synthetic/natural rubber blend	0.42	65.7	18%	9.2	~	48 mm x 32 m	Black

*ASTM D-3652 tested at 2.7 psi (18kPa).

Product Selection and Use: Many factors beyond 3Ms control and uniquely within users knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customers application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3Ms option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



3M Closure and Masking Systems Division

3M United Kingdom PLC 3M Centre, Cain Road Bracknell, Berkshire RG12 8HT Phone 0870 6080050 www.3M.co.uk

3M Ireland Limited The Iveagh Building Carrickmines 18 Phone 353-1-280355 www.3Mireland.ie



• Patching

- Bundling
- Reinforcing
- Taping/splicing insulation
- Capping pipe
- Securing conduit ends
- Marking
- Labeling

3M is a trademark of 3M. © 3M 2021.

All rights reserved. Please recycle.

(04/2021)

- Performing temporary repairs
- Hanging polyethylene drapes
- Protecting against sandblast overspray