



3M™ MCS™ Warranty

Release: June 2021

Qualified OEM Printer and Ink List

Manufacturer	Printer Model	Ink	Ink Type
EFI™ VUTEk®	5r+, 3r+	EFI™ 3M™ SuperFlex XF UV Ink	UV (LED)
EFI™	Pro 32r, Pro 32r+	EFI™ 3M™ SuperFlex XF UV Ink	UV (LED)
EFI™ VUTEk®	D5r, D3r	EFI™ 3M™ SuperFlex XF UV Ink	UV (LED)
EFI™ VUTEk®	Q5r, Q3r	EFI™ 3M™ SuperFlex XF UV Ink	UV (LED)
EFI™ VUTEk®	GS5500, 5250, 3250 LXr (incl. Pro/UD Series)	EFI™ VUTEk® GSLXr 3M™ SuperFlex UV Ink	UV (LED)
EFI™ VUTEk®	GS3250, 2000 LX (incl. Pro/UD Series)	EFI™ VUTEk® GSLX 3M™ SuperFlex UV Ink	UV (LED)
EFI™ Quantum®	5, 5+, 3, 3+	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI™	Pro 32r, Pro 32r+	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI™ VUTEk®	D5r, D3r	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI™ VUTEk®	5r, 5r+, 3r, 3r+	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI™ VUTEk®	H5, H3	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI™ VUTEk®	Q5r, Q3r	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI™ VUTEk®	GS5500, 5250, 3250 LXr (incl. Pro/UD Series)	EFI™ 3M™ SuperRange Ink	UV (LED)
EFI™ VUTEk®	GS3250, 2000 LX (incl. Pro/UD Series)	EFI™ 3M™ SuperRange Ink	UV (LED)
EFI™ VUTEk®	LX3 Pro	EFI™ 3M™ SuperRange Ink	UV (LED)
EFI™ VUTEk®	32h	EFI™ 3M™ SuperRange Ink	UV (LED)
EFI™	H1625 LED	EFI™ H1625 LED Series 3M™ Inks/ EFI™ Prographics UV-3M™	UV (LED)
EFI™	Pro 16h	EFI™ Pro 16h - 3M™ Inks/ EFI™ Prographics UV-3M™	UV (LED)
EFI™ VUTEk®	GS3250, 3200, 2000 (incl. Pro Series)	EFI™ VUTEk® GS 3M™ Premium UV ink	UV
EFI™ VUTEk®	GS5000r, 3250r	EFI™ VUTEk® GSr 3M™ Premium UV ink	UV
EFI™ VUTEk®	5300, 5000, 3360, 3300, 3000, 2360, 150	3M™ Piezo Inkjet Ink Series 1500v2	Solvent
Epson SureColor®	S80600, S80610, S80650, S80670, S80680	Epson® - 3M™ UltraChrome® GS3 Ink with Red	Solvent
Epson SureColor®	S60600, S60610, S60650, S60670, S60680	Epson® - 3M™ UltraChrome® GS3 Ink	Solvent
Epson SureColor®	S40600, S40610, S40650, S40670, S40680	Epson® - 3M™ UltraChrome® GS3 Ink	Solvent
HP Latex	R1000, R1000 Plus, R2000 Plus	HP 872 / 882 / 886 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP Latex	700, 700W, 800, 800W	HP 832 / 873 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP Latex	3200, 3100, 3000	HP 881 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP Latex	3800, 3600, 3500	HP 3M 891 Latex Inks	Latex
HP Latex	1500	HP 881 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP Latex	570, 560, 375, 370, 365, 360	HP 831, 871 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP Designjet	L65500 / Scitex LX850, 820, 800, 600 / Latex 850, 820	HP LX610 Latex Ink, a 3M™ MCS™ Warranty Component	Latex
HP Designjet	L28500, 26500 / Latex 280, 260, 210	HP 792 Latex Ink, a 3M™ MCS™ Warranty Component	Latex
Mimaki	UJV500-160	MIMAKI UV Piezo Inkjet Ink Series LUS-200 Manufactured by 3M	UV (LED)
Mimaki	UCJV300	MIMAKI UV Piezo Inkjet Ink Series LUS-200 Manufactured by 3M	UV (LED)
Mimaki	UJV160 / JFX-1631, 1615R	MIMAKI UV Piezo Inkjet Ink Series LF-200 Manufactured by 3M	UV (LED)
OKI data ColorPainter™	M-64s	3M™ SX Ink series from OKI	Solvent
OKI data ColorPainter™	H3-104s	3M™ SX Ink series from OKI	Solvent
OKI data ColorPainter™	E-64s	3M™ SX Ink series from OKI	Solvent
OKI data ColorPainter™	H-74s, 104s / H2-74s, 104s / W-54s, 64s	3M™ GX Ink series from OKI	Solvent
Roland TrueVIS	SG/SG2/VG/VG2/VF2	TrueVIS TR2 Inks, a 3M™ MCS™ Warranty Component	Solvent