

 Release: February 2024	3M™ MCS™ Warranty		
	Qualified OEM Printer and Ink List		
Manufacturer	Printer Model	Ink	Ink Type
Canon	Colorado 1630	Uvgel 460	UVgel (LED)
Canon	Colorado 1650	Uvgel 460	UVgel (LED)
Canon	Colorado M-series	Uvgel 460	UVgel (LED)
EFI	VUTEk® 5r+, 3r+	EFI™ 3M™ SuperFlex XF UV Ink	UV (LED)
EFI	Pro 32r, Pro 32r+	EFI™ 3M™ SuperFlex XF UV Ink	UV (LED)
EFI	VUTEk® D5r, D3r	EFI™ 3M™ SuperFlex XF UV Ink	UV (LED)
EFI	VUTEk® Q5r, Q3r	EFI™ 3M™ SuperFlex XF UV Ink	UV (LED)
EFI	VUTEk® GS5500, 5250, 3250 LXr (incl. Pro/UD Series)	EFI™ VUTEk® GSLXr 3M™ SuperFlex UV Ink	UV (LED)
EFI	VUTEk® GS3250, 2000 LX (incl. Pro/UD Series)	EFI™ VUTEk® GSLX 3M™ SuperFlex UV Ink	UV (LED)
EFI	Quantum® 5, 5+, 3, 3+	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI	Pro 32r, Pro 32r+	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI	VUTEk® D5r, D3r	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI	VUTEk® 5r, 5r+, 3r, 3r+	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI	VUTEk® H5, H3	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI	VUTEk® Q5r, Q3r	EFI™ 3M™ SuperRange XF Ink	UV (LED)
EFI	VUTEk® GS5500, 5250, 3250 LXr (incl. Pro/UD Series)	EFI™ 3M™ SuperRange Ink	UV (LED)
EFI	VUTEk® GS3250, 2000 LX (incl. Pro/UD Series)	EFI™ 3M™ SuperRange Ink	UV (LED)
EFI	VUTEk® LX3 Pro	EFI™ 3M™ SuperRange Ink	UV (LED)
EFI	VUTEk® 32h	EFI™ 3M™ SuperRange Ink	UV (LED)
EFI	H1625 LED	EFI™ H1625 LED Series 3M™ Inks/ EFI™ Prographics UV-3M™	UV (LED)
EFI	Pro 16h	EFI™ Pro 16h - 3M™ Inks/ EFI™ Prographics UV-3M™	UV (LED)
EFI	VUTEk® GS3250, 3200, 2000 (incl. Pro Series)	EFI™ VUTEk® GS 3M™ Premium UV ink	UV
EFI	VUTEk® GS5000r, 3250r	EFI™ VUTEk® GSr 3M™ Premium UV ink	UV
Epson	SureColor® S80600, S80610, S80650, S80670, S80680	Epson® - 3M™ UltraChrome® GS3 Ink with Red	Solvent
Epson	SureColor® S60600, S60610, S60650, S60670, S60680	Epson® - 3M™ UltraChrome® GS3 Ink	Solvent
Epson	SureColor® S40600, S40610, S40650, S40670, S40680	Epson® - 3M™ UltraChrome® GS3 Ink	Solvent
HP	Latex 630, 630W	HP883 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP	Latex 2700, 2700W	HP883 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP	Latex R1000, R1000 Plus R2000 Plus	HP 872 HP 882 HP 886 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP	Latex 700, 700W 800, 800W	HP 832 HP 873 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP	Latex 3200, 3100, 3000	HP 881 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP	Latex 3800, 3600, 3500	HP 3M 891 Latex Inks	Latex
HP	Latex 1500	HP 881 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
HP	Latex 570, 560 375, 370, 365, 360	HP 831, 871 Latex Inks, a 3M™ MCS™ Warranty Component	Latex
Mimaki	UJV500-160	MIMAKI UV Piezo Inkjet Ink Series LUS-200 Manufactured by 3M	UV (LED)
Mimaki	UCJV300	MIMAKI UV Piezo Inkjet Ink Series LUS-200 Manufactured by 3M	UV (LED)
OKI data	ColorPainter™ M-64s	3M™ SX Ink series from OKI	Solvent
OKI data	ColorPainter™ H3-104s	3M™ SX Ink series from OKI	Solvent
OKI data	ColorPainter™ E-64s	3M™ SX Ink series from OKI	Solvent
Roland	TrueVIS SG, SG2. SG3 VG, VG2, VG3 VF2	TrueVIS TR2 Inks, a 3M™ MCS™ Warranty Component	Solvent