

**3M** Science.  
Applied to Life.™



Introducing the new

# **3M™ Clean Sanding System and Random Orbital Sander**

Designed with technicians and shop owners in mind.

Australia

# Smarter. Faster. Cleaner.

A clean shop can mean less rework, better cycle times, and the peace of mind that you are doing what you can to improve the shop environment. For you, your technicians and your customers.

Proper surface preparation is the key to a quality repair, but it all starts with using the right abrasives and the right tool for the job.

When you prep vehicle surfaces day in and day out, you need a sander that helps you produce your finest finishes without grinding you down. The 3M™ Random Orbital Sander is an effective pneumatic DA sanding tool designed to help improve the performance of 3M™ Abrasives. The 3M™ Random Orbital Sander delivers quality, professional surface prep and finishing results.










New

## 3M™ Clean Sanding System

The 3M™ Clean Sanding System is a complete sanding solution for efficiently moving through your essential surface preparation and finishing work. The system includes our dust extractor, pneumatic random orbital sanders, mobile workstation, wide selection of quality abrasives, and personal protective equipment.

-  Designed to reduce dust in the air from sanding for a cleaner workspace.
-  Helps shops boost productivity and efficiency by helping to reduce rework and cleanup time.
-  Compact and mobile. Designed for easy, flexible use around the shop.
-  Compatible with pneumatic sanders.
-  Tech-friendly design including auto on/off, antistatic hose, rubber wheels, brake locks, and LED indicator lights.





New

## 3M™ Random Orbital Sander

The 3M™ Random Orbital Sander helps deliver high-quality surface preparation and finishing results with your 3M™ Abrasives.



Variable speed adjustment lets you adjust to your task



Multi-hole back up pad and shroud offer strong dust extraction when used with the 3M™ Clean Sanding System



Large variable speed lever and composite power lever with added wrist support are easy to see and use



Compatible with the 3M™ Clean Sanding System and other dust extraction systems and abrasives

# 3M™ Abrasive Discs for Automotive Repair



## Cubitron™ II

### Material/Technology

3M™ Precision Shaped Grain

### Grades

40+, 80+, 120+, 150+, 180+, 220+, 240+, 320+, 400+

### Sizes

75mm, 150mm

### Hole Pattern

Multi-hole

### Dust Extraction



### Attachment Type

Hookit™

### Cut



### Disc Life



## Blue

### Material/Technology

Engineered Ceramic Mineral Blend

### Grades

40, 80, 120, 150, 180, 220, 240, 320, 400, 500, 600, 800

### Sizes

150mm

### Hole Pattern

Multi-hole

### Dust Extraction



### Attachment Type

Hookit™

### Cut



### Disc Life



## Gold

### Material/Technology

Aluminum Oxide Mineral

### Grades

P80, P100, P120, P150, P180, P220, P240, P320, P360, P400, P500

### Sizes

150mm

### Hole Pattern

15 hole

### Dust Extraction



### Attachment Type

Hookit™

### Cut



### Disc Life



## Dust Extractor

### 3M™ Dust Extractor

33757 45 L, 230V, Plug Type I

## Orbital Sanders

### 3M™ Random Orbital Sander

33623 75 mm, 5 mm Orbit

33627 150 mm, 2.5 mm Orbit

33628 150 mm, 5 mm Orbit

33629 150 mm, 8 mm Orbit

## Accessories

33645 3M™ Anti-static Pneumatic Hose

33646 3M™ Anti-static Electric Hose

33765 3M™ Dust Extractor Handle Extension

33647 3M™ Dust Extractor Filter

33648 3M™ Dust Filter Bag

33652 3M™ Dust Extractor Y-Connector

33653 3M™ Clean Sanding System Workstation

33654 3M™ Clean Sanding System Workstation Extension

05215 3M™ Dust Free Hose Extension Kit Purple 6M

05209 3M™ Hookit™ Sanding Block D/F, 70mm x 396mm

05208 3M™ Hookit™ Sanding Block D/F, 70mm x 198mm

05207 3M™ Hookit™ Sanding Block D/F, 70mm x 127mm

05216 3M™ Hookit™ Sanding Block D/F, 115mm x 225mm

50545 3M™ Hookit™ Soft Interface Pad, 150mm x 5mm, Multi-Hole

50544 3M™ Hookit™ Soft Interface Pad, 150mm x 10mm, Multi-Hole



**3M Automotive Aftermarket Division**  
Building A, 1 Rivett Rd  
North Ryde, NSW, 2113

Phone 136-136  
Web [www.3M.com.au/collisionrepair](http://www.3M.com.au/collisionrepair)

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.



/3Mcollision



/3Mcollision



/3Mcollision



/3MAADAustralia

3M, Clean Sand, Cubitron & Hookit are trademarks of 3M Company.  
Printed in Australia. © 3M 2021. All rights reserved.