



# Scotch-Weld™

## DP8600NS Series

### Preliminary Technical Data Sheet

July 2021

#### Product Description

3M™ Scotch-Weld™ DP8600NS Series Adhesives are low odor, high elongation, two-part acrylic structural adhesives that offer excellent shear, peel, and impact performance. These products provide excellent adhesion to many painted/coated metals, plastics, glass, and bare metals. These special formulations provide outstanding flexibility for bonding dissimilar materials, and can reduce or eliminate read-through for improved aesthetics.

#### Features

- Excellent strength and durability on a wide variety of common materials
- High elongation
- Outstanding flexibility
- Minimal surface preparation
- Contains ceramic beads to control bond line thickness

**Note: The following data is taken from tests conducted on limited production runs. 3M will continue to test samples from additional product runs and will issue a new data page if the test results change.**

**Note: Unless otherwise indicated, all properties measured at 72°F (22°C).**

#### Typical Uncured Physical Properties

**Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

Property		3M™ Scotch-Weld™	
		DP8610NS	DP8625NS
Color	Base (B)	Black	
	Accelerator (A)	Gray	
Viscosity <sup>1</sup>	Base (B)	90,000 cP	
	Accelerator (A)	15,000 cP	
Density <sup>2</sup>	Base (B)	1.11 g/cm <sup>3</sup>	
	Accelerator (A)	1.08 g/cm <sup>3</sup>	
Mix ratio	By volume	10 Parts B : 1 Part A	
	By weight	10 Parts B : 1 Part A	
		<b>Note: Cure times are approximate and depend on adhesive temperature.</b>	
Work life <sup>3</sup>		10 minutes	22-24 minutes
Open time <sup>4</sup>		10-15 minutes	20-30 minutes
Time to handling strength <sup>5</sup>		16-20 minutes	35-40 minutes
Time to structural strength <sup>6</sup>		25-35 minutes	50-60 minutes

1. Viscosity measured using cone-and-plate viscometer; reported viscosity at 4 sec<sup>-1</sup> shear rate.

2. Density measured using pycnometer.

3. Maximum time that adhesive can remain in a static mixing nozzle and still be expelled without undue force on the applicator.

4. Maximum time allowed after applying adhesive to one substrate before bond must be closed and fixed in place.

5. Minimum time required to achieve 50 psi of overlap shear strength.

6. Minimum time required to achieve 1,000 psi of overlap shear strength.

# 3M™ Scotch-Weld™

## DP8600NS

### Typical Mixed Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Property	3M™ Scotch-Weld™	
	DP8610NS	DP8625NS
Color	Black	
Full cure time	24 hours	
Viscosity	90,000 cP	
Density	1.11 g/cm <sup>3</sup>	
Shore A Hardness	35	

### Typical Cured Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### Overlap Shear (psi)<sup>7</sup>

Substrate	3M™ Scotch-Weld™	
	DP8610NS	DP8625NS
Etched Aluminum	1,022 CF	TBD
Cold Rolled Steel	915 CF	TBD
ABS	426 CF	TBD
Acrylic	252 AF	TBD
Polycarbonate	241 AF	TBD
Polyester resin (fiber-reinforced)	553 CF	TBD
Epoxy Resin (fiber-reinforced)	755 AF	TBD
Etched Aluminum (tested at -40°F)	3499 CF	TBD
Etched Aluminum (tested at 120°F)	508 CF	TBD
Etched Aluminum (tested at 180°F)	279 CF	TBD

7. Overlap shear values measured using ASTM D1002; 1 min open time; adhesive allowed to cure for 24 hours at room temperature; 1/2" overlap; 0.010" bond line thickness; samples pulled at 0.1 in/min for metals and 2 in/min for plastics. Metals and fiber-reinforced polymers were prepared by cleaning with acetone, light abrasion and a final acetone clean. Plastics were prepared by cleaning with isopropyl alcohol. Substrates used were 1/16" thick metals and 1/8" thick plastics. Failure modes:

AF: adhesive failure      CF: cohesive failure      SF: substrate failure

**Note: This adhesive also has relatively low adhesion to low surface energy plastics (such as polypropylene, polyethylene, TPO, and PTFE). Applications involving any of these materials should be carefully evaluated by the end user for suitability.**

**Note: The presence of oxygen inhibits the cure of acrylic structural adhesives. Therefore, any exposed surfaces of the mixed adhesive will cure much more slowly than adhesive contained within the bond line. With methyl methacrylate (MMA) acrylic adhesives, any uncured adhesive on the surface flashes off immediately, leaving a surface that feels dry to the touch. With this low odor acrylic adhesive, uncured adhesive on exposed surfaces does not evaporate away as quickly, leaving a tacky film of partially cured material. For manufacturing processes that need a dry surface quickly, such as for subsequent sanding or painting operations, consider instead using a standard MMA acrylic adhesive.**

# 3M™ Scotch-Weld™

## DP8600NS

### Typical Cured Physical Properties (continued)

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Mechanical Properties<sup>8</sup>

Property	3M™ Scotch-Weld™	
	DP8610NS	DP8625NS
Tensile modulus	102 psi	TBD
Tensile strength	215 psi	TBD
Tensile strain at break	200%	TBD
Shore A hardness	35	TBD

8. Tensile properties measured using ASTM D638; adhesives allowed to cure for 2 weeks at room temperature; 1/8" thick Type I test specimens; samples pulled at 0.2 in/min. Strains measured using digital image correlation.

### Environmental Resistance<sup>9</sup>

Condition	Substrate	3M™ Scotch-Weld™	
		DP8610NS	DP8625NS
392°F (200°C) for 30 minutes	Etched Aluminum	TBD	TBD
392°F (200°C) for 30 minutes	Cold Rolled Steel	TBD	TBD
85°F (29°C) + 85% relative humidity for 500 hours	Etched Aluminum	82%	TBD
120°F (49°C) + 80% relative humidity for 500 hours	PVC	TBD	TBD
Ambient Water Soak for 500 hours	Etched Aluminum	59%	TBD
Diesel Fuel Soak for 500 hours	Etched Aluminum	TBD	TBD
Gasoline Soak for 500 hours	Etched Aluminum	TBD	TBD
Salt Water Soak (5 wt% in water) for 500 hours	Etched Aluminum	71%	TBD

9. Values indicate overlap shear test performance retained after 500 hours of continuous exposure relative to a control sample left at room temperature; samples conditioned for 24 hours at room temperature and 50% relative humidity prior to tests.

**Note:** Fully-cured structural adhesives can withstand short-term incidental contact with almost any solvent, chemical, or environmental condition. However, long-term continuous exposure of this acrylic structural adhesive to the following liquids should be avoided:

1. Elevated temperature (>120°F) water
2. Ketone-type solvents (acetone, MEK)

# 3M™ Scotch-Weld™ DP8600NS

---

## Typical Cured Physical Properties (continued)

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Floating Roller Peel (lb/inch width)<sup>10</sup>

Substrate	3M™ Scotch-Weld™	
	DP8610NS	DP8625NS
Aluminum	100 CF	TBD

10. Floating roller peel values measured using ASTM D3167; adhesives allowed to cure for 24 hours at room temperature; 1" wide samples; 0.017" bond line thickness; samples pulled at 6 in/min; aluminum surfaces etched; substrates used were 1/16" thick and 0.020" thick aluminum; failure modes:

AF: adhesive failure      CF: cohesive failure      SF: substrate failure

**Note:** The data in this sheet were generated using the 3M™ EPX™ Applicator System equipped with an EPX static mixer, according to manufacturer's directions. Thorough hand-mixing will afford comparable results.

---

## Dispensing Characteristics

Material Characteristic	8610NS	8625NS
Thixotropic Index	4.2	TBD
Mix Nozzle Recommendation – 45mL	Quadro Mixing Nozzle Mix Elements: 16 Length (mm): 90 Volume (ml): 1.72 3M Stock #:7100202930	Quadro Mixing Nozzle Mix Elements: 16 Length (mm): 90 Volume (ml): 1.72 3M Stock #:7100202930
Mix Nozzle Recommendation – 490mL	Helical Mixing Nozzle Mix Elements: 18 Length (mm): 221.9 Volume (ml): 12.96 3M Stock #: 7100015959	Helical Mixing Nozzle Mix Elements: 18 Length (mm): 221.9 Volume (ml): 12.96 3M Stock #: 7100015959
Alterative Mix Nozzle Recommendation – 490mL	Helical Low waste Mixing Nozzle Mix Elements: 24 Length (mm): 136.7 Volume (ml): 6.28 3M Stock #:7100066351	Helical Low waste Mixing Nozzle Mix Elements: 24 Length (mm): 136.7 Volume (ml): 6.28 3M Stock #:7100066351
Abrasive Fillers	Ceramic Beads, 0.01” NOM	Ceramic Beads, 0.01” NOM
Packaging – 45 mL	MixPac B System	MixPac B System
Packaging – 490 mL	MixPac F system	MixPac F system
Packaging – 5 gallon kit	5 gallon straight sided pail - steel	5 gallon straight sided pail - steel
Packaging – 55 gallon kit	55 gallon straight sided drum - steel	55 gallon straight sided drum - steel
Base Pumping Equipment Recommendation – High Flow	25.0 cc/rev EPDM Progressive Cavity Pump	25.0 cc/rev EPDM Progressive Cavity Pump
Accelerator Pumping Equipment Recommendation – High Flow	3.0 cc/rev Viton ETP Progressive Cavity Pump	3.0 cc/rev Viton ETP Progressive Cavity Pump
Base Pumping Equipment Recommendation – Low Flow	3.0 cc/rev EPDM Progressive Cavity Pump	3.0 cc/rev EPDM Progressive Cavity Pump
Accelerator Pumping Equipment Recommendation – Low Flow	0.3 cc/rev Viton ETP Progressive Cavity Pump	0.3 cc/rev Viton ETP Progressive Cavity Pump

### Directions for Use

1. To obtain the highest strength structural bonds, paint, oxide films, oils, dust, mold release agents, and all other surface contaminants must be completely removed. The amount of surface preparation depends on the required bond strength and environmental aging resistance desired by user. For suggested surface preparations on common substrates, see the section on surface preparation.

### 2. Mixing

#### For Duo-Pak Cartridges

Store cartridges with cap end up to allow any air bubbles to rise towards the tip. To use, simply insert the cartridge into the EPX applicator and start the plunger into the cylinders using light pressure on the trigger. Then remove the cap and expel a small amount of adhesive to ensure material flows freely from both sides of cartridge. For automatic mixing,

attach an EPX mixing nozzle to the cartridge and begin dispensing the adhesive. For hand mixing, expel the desired amount of adhesive and mix thoroughly. Mix approximately 15 seconds after obtaining a uniform color.

**For Bulk Containers**

Mix thoroughly by weight or volume in the proportion specified on the product label or in the typical uncured properties section. Mix approximately 15 seconds after obtaining a uniform color.

3. Apply adhesive and join surfaces within the open time listed for the specific product. Larger quantities and/or higher temperatures will reduce this working time. The adhesive and all materials should be at 60°F (16°C) or above to achieve highest bond strength.
4. Allow adhesive to cure at 60°F (16°C) or above until completely firm. Applying heat up to 150°F (66°C) will increase cure speed.
5. Keep parts from moving during cure. Apply contact pressure or fixture in place if necessary. Optimum bond line thickness ranges from 0.005 to 0.020 inch; shear strength will be maximized with thinner bond lines, while peel strength reaches a maximum with thicker bond lines.
6. Excess uncured adhesive can be cleaned up with ketone-type solvents.\*

**\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.**

# 3M™ Scotch-Weld™ DP8600NS

---

## Surface Preparation

3M™ Scotch-Weld™ Acrylic Adhesives are designed to be used on painted/coated metals, most bare metals, and most plastics and composite materials. The following cleaning methods are suggested for common surfaces:

### **Painted/coated metals:**

1. Wipe surface free of dust and dirt with clean cloth and pure isopropyl alcohol.\*
2. Sandblast or lightly abrade using clean fine grit abrasives. Do not completely remove the paint layer or coating down to bare steel.
3. Wipe again with clean cloth and pure isopropyl alcohol to remove loose particles.\*

### **Bare metals:**

1. Wipe surface free of dust and dirt with clean cloth and pure acetone.\*
2. Sandblast or lightly abrade using clean fine grit abrasives.
3. Wipe again with clean cloth and pure acetone to remove loose particles.\*

### **Plastics and composite materials:**

1. Wipe surface free of dust and dirt with clean cloth and pure isopropyl alcohol.\*
2. Lightly abrade using fine grit abrasives.
3. Wipe again with clean cloth and pure isopropyl alcohol to remove loose particles.\*

**\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.**

---

## Storage

Store product at 80°F (27°C) or below. Refrigeration at 40°F (4°C) will help extend shelf life. Do not freeze. Allow product to reach room temperature prior to use.

---

## Shelf Life

3M™ Scotch-Weld™ Adhesives DP8610NS and DP8625NS have a shelf life of 12 months from date of manufacture in unopened original containers kept at recommended storage conditions.

# 3M™ Scotch-Weld™ DP8600NS

---

**Precautionary  
Information**

Refer to Product Label and Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

---

**Important Notice and Disclaimer:** This 3M product is an experimental or developmental product that has not been introduced or commercialized for general sale, and its formulation, performance characteristics, and other properties, specifications (if any), availability, and pricing are not guaranteed and are subject to change or withdrawal without notice. User is solely responsible for evaluating third party intellectual property rights and for ensuring that user's use of this 3M product does not violate any third party intellectual property rights.

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating this 3M product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty Disclaimer:** This 3M product is sold or made available "AS IS." 3M MAKES NO WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.

**Limitation of Liability:** Except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to this 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and other limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, death, or property damage. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com). [1]

---

**ISO 9001**

· This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.





**Industrial Adhesives and Tapes Division**

3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
[www.3M.com/StructuralAcrylics](http://www.3M.com/StructuralAcrylics)

3M, Scotch-Weld and EPX are  
trademarks of 3M Company.

Printed in U.S.A.  
©3M 2019 (9/19)