

Dust Extraction Solutions Guide

Introducing the new 3M™ Net Abrasives

Go for performance. Leave the dust behind.

Dust.

The hidden — or maybe not-so-hidden — enemy of any body shop.

You know dust is a problem. It can sap your efficiency, create defects and rework, and steal the life from your abrasive.

Once it's in the air, it can settle on your work surfaces in your shop and even creep into your office and waiting room.

The best way to stop dust? The right combination of tools and abrasives let you capture it at the source.



Why dust extraction matters.

When it comes to improving the efficiency and cleanliness of your body shop, proper dust extraction can't be an afterthought. Here's how our dust extraction system can help:

- Reduces the amount of dust in the air from sanding, leading to less rework, driving improved cycle time and process efficiency.
- Reduces cleanup time.
- Enhances workplace efficiency by reducing time spent searching for tools and materials.
- Workcenter enables the use of abrasives to end of life, leading to reduced material spend.
- Increased technician mobility.





The 3M™ Clean **Sanding System**

A complete solution for efficient surface preparation and finishing work.

The system includes our dust extractor, pneumatic random orbital sanders, mobile workstation, wide selection of quality abrasives, and personal protective equipment.

Learn more at 3M.com/auto-abrasives

Introducing


3M™ Net Abrasives




Premium

3M™ Cubitron™ II Net Abrasives

In abrasives, premium quality has a name: 3M™ Cubitron™ II. We're reinventing abrasives with innovative net technology coupled with 3M Precision Shaped Grain, so that you no longer have to compromise between peak performance and dust extraction.











Advanced

3M™ Blue Net Abrasives

This is the surge in productivity you've been asking for. 3M™ Blue Net Abrasives feature an engineered ceramic mineral blend for bestin-class performance and dust extraction at a mid-tier price point.

Learn more at 3M.com/auto-abrasives

3M™ Net Abrasives

Benefits



Performance:

Faster cutting and longer lasting than leading net abrasives in the market.



Efficient:

Helps shops productivity and efficiency by helping to reduce rework and cleanup time.



Dust Extraction:

Designed to help reduce dust in the air from sanding for a cleaner workspace.



Versatile:

Compatible with pneumatic and/or electric sanders with or without dust extraction capabilities.



Construction:

Open net structure is designed to provide a virtually dust-free environment for a cleaner, healthier shop.





3M™ Net Abrasives

Features



Net construction for 95% + highly efficient dust extraction performance.



Precision Shaped Grain and engineered Ceramic mineral blend technology for faster cut and longer life.



Able to use multi-hole back-up pads and blocks for easy disc hole alignment and dust extraction.



3M™ Cubitron™ II Net Abrasives are compatible with your existing dust extraction equipment.




Center hole for easy disc alignment and storage.






Cubitron™ II Net



The open net structure in the new 3M™ Cubitron™ II Net Abrasives provides a virtually dust-free environment.



Precision-Shaped Grain

Cubitron™ II mineral paired with dust extraction equipment can help to save shops time and materials delivering better value and higher performance.

Cut Rate



Disc Life



Dust Extraction



Grades

80+, 120+, 150+, 180+, 220+, 240+, 320+

Sizes

75 mm (3"), 125 mm (5"), 150 mm (6"), 203 mm (8")

Technology

3M™ Precision Shaped Grain

Material

Net

Attachment Type

Hookit™

3M[™] Blue Net Abrasives **Advanced**





Blue Net

Cut Rate





Disc Life



Dust Extraction



Grades

80, 120, 150, 180, 220, 240, 320

Sizes

150 mm (6")

Technology


Engineered Ceramic Mineral Blend

Material

Net

Attachment Type

Hookit™



3M™ Blue Net Abrasive Discs deliver outstanding abrasive performance with an excellent cut rate and life.



Dust Extraction Capability

3M™ Blue Net discs provide excellent dust removal for most applications and repairs when used on existing or new dust extraction systems.

Cubitron™ II Net **Abrasives**

For Dry Sanding

Get the job done sooner with 3M™ Cubitron™ II Net Abrasives, our fastestcutting and longest-lasting net abrasive discs and sheets. This family of net abrasives delivers the exceptional cut rate and extended life of a Cubitron II abrasive. All the while, letting dust extractors perform their best by leaving virtually no dust on the work surface and in the environment.

- Available in grades from 80+ to 320+ and in the most-popular disc sizes, compatible with existing dust-extraction sanders.
- The 3M™ Hookit™ attachment makes installing a new disc quick and saving a partially-used disc easy.
- Premium net disc help allows for virtually dust-free sanding.











	3M [™] Hookit [™] Attachment				
Grade	Net Sheet Roll 70 mm x 10M 6 Rolls/Case	Net Sheet Roll 80 mm x 10 M 6 Rolls/Case	Net Sheet Roll 115 mm x 10 M 6 Rolls/Case		
80+	34561	34550	34572		
120+	34562	34551	34573		
150+	34563	34552	34574		
180+	34564	34553	34575		
220+	34565	34554	34576		
240+	34566	34555	34577		
320+	34560	34556	34578		









	3M™ Hookit™ Attachment				
Grade	203 mm (8") Net Disc 25 Discs/Carton 6 Cartons/Case	150 mm (6") Net Disc 50 Discs/Roll 6 Rolls/Case	125 mm (5") Net Disc 50 Discs/Roll 6 Rolls/Case	75 mm (3") Net Disc 50 Discs/Roll 6 Rolls/Case	
80+	31641	31650	31665	31679	
120+	31642	31651	31666	31680	
150+	31643	31652	31667	31681	
180+	31644	31653	31668	31682	
220+	31645	31654	31669	31683	
240+	31646	31655	31670	31684	
320+	31647	31656	31671	31685	

Blue **Abrasives**

Get outstanding performance at an affordable price with 3M[™] Blue Net Abrasives high-quality net abrasive discs and sheets for value-focused professionals. Built with an engineered ceramic-mineral blend, they deliver an excellent cut rate and life. From body repair to paint prep, 3M™ Blue Net Abrasives are excellent performers that can help you keep your shop in the black and leave competition in the dust.



Delivering great life and dust extraction to help value focused businesses boost productivity and efficiency.



Available in grades from 80 to 320 and in the most-popular disc sizes, compatible with existing dust-extraction sanders.



The 3M™ Hookit™ attachment makes installing a new disc quick and saving a partiallyused disc easy.







	3M [™] Hookit [™] Attachment	3M [™] Hookit [™] Attachment		
Grade	150 mm (6") Net Disc 100 Discs/Roll 8 Rolls/Case	Net Sheet Roll 70 mm (W) x 10 m (L) 10 Rolls/Case	Net Sheet Roll 115 mm (W) x 10 m (L) 10 Rolls/Case	
80	36420	36462	36470	
120	36421	36463	36471	
150	36422	36464	36472	
180	36423	36465	36473	
220	36424	36466	36474	
240	36425	36467	36475	
320	36426	36468	36476	



Good enough is no longer an option.

Pair our new net abrasives with our outstanding dust extraction system for added speed and performance. Or take your existing tools to the next level with our biggest advancement in clean sanding in decades.



Prime Performance

It's time to tackle dust at the source with 3M™ Cubitron™ II Net and Blue Net Abrasives.



Peak Productivity



Virtually Dust-Free



For more information, visit www.3M.com/auto-abrasives



Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for proper evaluation (including, but not limited to, fitness for purpose and suitability of application), selection, and use of 3M products. Safety products should always be selected and used in accordance with all applicable regulations and standards (e.g., OSHA, ANSI, and others), after conducting a proper hazard assessment. Failure to properly evaluate, select, and use a 3M product may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

3M, Cubitron and Hookit and are trademarks of 3M Company. © 3M 2021. All rights reserved.

