

3M Science.
Applied to Life.™

Construction

Personal Protective Equipment (PPE) Catalog






Table of Contents

Contact Info	3
Fall Protection	5
Fall Protection for Tools	21
Confined Spaces	25
Respiratory Protection	28
Welding Equipment	46
Hearing Protection	52
Communication Solutions	61
Eye Protection	67
Head and Face Protection	82
3M™ Scott™ Fire & Safety	87





Personal Safety Division

3M helps protect workers in a changing world. Across diverse industries and applications our technology, expertise and energy drive innovative solutions to help protect you from hazards in the work environment so you can focus on the job at hand.

3M provides safety solutions that can help improve comfort while helping employers increase compliance, with personal protective equipment for your eyes and head to hearing and respiratory system.

This catalog was prepared by:

3M United States

Personal Safety Division

Website: [3M.com/PPE](https://www.3m.com/PPE)

Technical Assistance ***1-800-243-4630***

Customer Service ***1-800-328-1667***

Direct Government Orders ***1-800-752-3623***

Fall Protection Product Support ***1-800-328-6146***


Construction safety. Backed by science.

Construction workers create great things — they also face great hazards. Worksite hazards include noise and respiratory hazards, falling objects, and the risk of falls from height and head and eye injuries. 3M offers integrated safety and health solutions designed to help you keep your employees protected and comfortable.



Personal protective equipment for

- Respiratory hazards
- Falling object hazards
- Working at height hazards
- Noise hazards
- Foreign body eye injury hazards
- Impact to the head hazards



Fall Protection

Elevate your safety.

10 feet in the air or 100, you need solutions to help keep you safe at height no matter where the job takes you. That's why our dedicated team of Fall Protection specialists meets with customers out in the field. We work to understand the unique challenges you face and develop the products, systems and services that help keep you safe and compliant with fall protection standards in a variety of industries.

[3M.com/FallProtection](https://www.3m.com/FallProtection)



The **ABCs** of Fall Protection

A typical Personal Fall Arrest System (PFAS) incorporates three components, often described as the ABCs of fall protection. The anchorage/anchorage connector, body support and connecting device—when used together—form a complete system for maximum worker protection. But don't forget the other important components of a comprehensive fall protection program: descent and rescue, education and fall protection for tools.

A

Anchorage

are a secure point of attachment. Anchorage connectors vary by industry, job, type of installation and structure. They must be able to support the intended loads and provide a sufficient factor of safety for fall arrest.



B

Body support

harnesses distribute fall forces over the upper thighs, pelvis, chest and shoulders. They provide a connection point on the worker for the personal fall arrest system.



C

Connectors

such as energy-absorbing lanyards or self-retracting lifelines connect a worker's harness to the anchorage.



D

Descent and rescue

devices are used to raise or lower a fallen injured worker to safety or retrieve them from a confined space.



E

Education

is essential. We offer a variety of training and consultative services to fit your needs.

F

Fall protection for tools

helps make work environments safer and more productive by reducing dropped object incidents.

Anchors

3M™ DBI-SALA® Sliding Beam Anchor, 19" x 3" x 4" (48 cm x 8 cm x 10 cm)

3M™ DBI-SALA® Sliding Beam Anchor fits 3-½" to 14" wide I-beams (9 cm to 35.5 cm) up to 1-¼" thick (3.2 cm).

Manufacturer Part Number	SKU
2104710	70804485541



3M™ DBI-SALA® Web Tie-Off Adaptor, yellow, 6' (0.9 m)

6' (0.9 m) 3M™ DBI-SALA® Web Tie-Off Adaptor, pass-through type.

Manufacturer Part Number	SKU
1003006	70007703237



3M™ DBI-SALA® Construction Roof Anchor

3M™ DBI-SALA® Construction Roof Anchor installs to rebar during pre-cast concrete work. Installs in seconds utilizing built-in ratcheting securement system. Built-in ratcheting securement system allows a user to secure anchor in place quickly. Dual-use design can also be used as end anchors for a 2-person temporary 3M™ DBI-SALA® HLL System. For use with 3M™ DBI-SALA® Smart Lock LE Self-Retracting Lifelines (Sold Separately).

Manufacturer Part Number	SKU
2190074	70804491267



3M™ DBI-SALA® Concrete D-ring Anchor, silver, yellow zinc, 5.7" x 3" x 4.4" (14.4 cm x 7.6 cm x 11 cm)

3M™ DBI-SALA® Concrete D-ring Anchor for 1/16", 3/4" or 18 mm hole with swiveling D-ring.

Manufacturer Part Number	SKU
2104560	70007441168

- 2104561 Concrete D-Ring Anchor with 5 additional bolts.
- 2104562 Concrete D-Ring Anchor with 11 additional bolts.
- 2100066 10-pack of Replacement Bolts for Concrete D-Ring Anchor.



3M™ Protecta® Dual-ring Tie-Off Adaptor, 6' (1.8 m)

6' (1.8 m) ¼" galvanized cable dual-ring tie-off adaptor, carabiner at one end, two D-rings at the other.

Manufacturer Part Number	SKU
2190102	70007442265



3M™ Protecta® Swiveling Roof Anchor

3M™ Protecta® Roof Anchors are durable to help you get the job done efficiently day after day, month after month. They're easy to install on flat or sloped roofs and ideal for wood or metal surfaces. Built-in Swiveling SRL bracket provides 360-degree mobility and accommodates 3M™ Protecta® Self-Retracting Lifelines rated as SRL-LE. Compatible with various fall arrest systems.

Manufacturer Part Number	SKU
2190070	70804491226



Harnesses

3M™ DBI-SALA® ExoFit™ STRATA™ Construction Style Positioning Harness

3M™ DBI-SALA® ExoFit™ STRATA™ Construction-Style Positioning Harness features aluminum back and side D-rings, Tri-Lock Revolver™ Quick-Connect Buckles and waist pad and belt. Featuring the exclusive LIFTech™ Load Distribution System, the ExoFit™ STRATA™ literally takes the weight off your shoulders and redistributes it down to your hips, dramatically reducing shoulder strain and fatigue. Additionally, its PolarMesh™ Padding delivers advanced breathability, the EZ-Link™ Quick SRL Adapter simplifies connecting and disconnecting your personal SRL, like the Nano-Lok™ and Nano-Lok™ Edge. If your safety harness is weighing you down, Lighten Up with the ExoFit™ STRATA™.

Manufacturer Part Number	SKU	Size
1112535	70007425302	Small
1112536	70007651709	Medium
1112537	70007651717	Large
1112538	70007657045	X-large



3M™ DBI-SALA® ExoFit NEX™ Plus Comfort Construction Style Positioning Harnesses

3M™ DBI-SALA® ExoFit™ NEX™ Plus Comfort Vest-Style Positioning/Climbing Harness features an integrated easy-link SRL adapter, a fixed back D-ring and auto-resetting lanyard keepers. The way you work is changing, and our products are evolving to fit your needs. Now you can get the same comfort of the ExoFit NEX harness with new time-saving features. Connect and disconnect personal self-retracting lifelines quickly and easily to the integrated easy-link SRL adapter. Reduce the need for readjustment throughout the workday with the fixed back D-ring. Position the auto-resetting lanyard keepers anywhere along the harness chest area webbing. Now it's easier and more comfortable to get your job done safely and efficiently.

Manufacturer Part Number	SKU	Size
1113031	70007419842	X-small
1113034	70007419875	Small
1113037	70007419883	Medium
1113040	70007419925	Large



3M™ DBI-SALA® Delta™ Vest-Style Harness

3M™ DBI-SALA® Delta™ Vest-Style Harness features coated, corrosion-resistant hardware, a back D-ring, tongue buckle leg straps and detachable shoulder padding. The Delta triangular harness design means you can don this harness quickly and easily without worrying about tangling. Water-repellent and abrasion-resistant webbing keeps you safe even in tough conditions. Delta padding incorporates web spreading technology to help position the webbing wider apart on shoulder straps so the harness can sit comfortably without irritating your skin.

Chest Buckle	Leg Buckles	D-rings (Back, Hips, Chest, Shoulder)	Universal Size
Pass-Through	Pass-Through	1B, 2S	1101781
Pass-Through	Tongue Buckle	1B, 2S	1101254
Quick Connect	Quick Connect	1B, 2S	1110602
Pass-Through	Tongue Buckle	1B	1102000
Quick Connect	Quick Connect	1B	1110600
Pass-Through	Pass-Through	1B	1103321
Pass-Through	Tongue Buckle	1B, 2H	1102008
Quick Connect	Quick Connect	1B, 2H	1110625
Pass-Through	Pass-Through	1B, 2H	1103875
Quick Connect	Quick Connect	1B, 1C	1102090
Pass-Through	Tongue Buckle	1B, 1C	1107807
Pass-Through	Pass-Through	1B, 1C	1112126
Pass-Through	Parachute Buckle	1B	1102001
Quick Connect	Pass-Through	1B, Conductive-resistant hardware	1104725



3M™ Protecta® Comfort Construction Style Positioning Harness, black

3M™ Protecta® Comfort Construction-Style Positioning Harness with an easy-link web adapter, a fixed D-ring to minimize workday readjustment and breathable Back/Hip Padding. Plus, a durable and sturdy belt, tongue-buckle leg connection, pass-through chest connection and back and side D-rings. Specially designed for added comfort, these harnesses are rated for 420 lb (190 kg) total weight capacity.


Manufacturer Part Number	SKU	Size
1161204	70007765426	Small
1161205	70007765319	Medium/Large
1161207	70007766598	X-large
1161208	70007767257	2 X-large



We're taking a stand to help prevent suspension trauma.

3M™ Fall Protection Suspension Trauma Safety Straps are being added to all 3M™ DBI-SALA® and 3M™ Protecta® Harnesses — with select models shipping now.

When a fallen worker is suspended for too long, their harness leg straps may constrict their veins, reducing the flow of oxygenated blood to their heart, brain and kidneys. Not every worker will experience suspension trauma, but for those who do, it can lead to unconsciousness and possibly death. It's why we're taking this crucial step to help prevent suspension trauma.



Lanyards

3M™ Protecta® Pack Shock Absorbing Lanyard

3M™ Protecta® Pack Shock Absorbing Lanyard offer compliance and confidence, with 3,600 lb (16 kN) gated hooks, durable lanyard material construction, and forged alloy steel hardware for strength and corrosion resistance.

Manufacturer Part Number	SKU	Length	Weight Capacity
1341002	70007703856	3' (0.9 m)	55-140 kg
1341004	70007703856	4' (1.2 m)	55-140 kg
1341001	70007701652	6' (1.8 m)	55-140 kg



3M™ DBI-SALA® EZ-Stop™ Shock Absorbing Lanyard

Durable and easy to use, 3M™ DBI-SALA® EZStop™ Shock Absorbing Lanyards are designed to meet or exceed rigorous industry safety standards. This is a single leg web lanyard with snap hooks at each end.

Manufacturer Part Number	SKU	Length	Weight Capacity
1246012	70007444659	3' (0.9 m)	55-140 kg
1246017	70007433165	4' (1.2 m)	55-140 kg
1246019	70007433181	5' (1.5 m)	55-140 kg
1246011	70007444642	6' (1.8 m)	55-140 kg



SRLs: Class SRL-LE

3M™ DBI-SALA® Nano-Lok™ Edge Twin-Leg Self Retracting Lifeline, cable, quick connect, 8' (2.4 m) web

The 3M™ DBI-SALA® Nano-Lok™ Edge Twin-Leg Self Retracting Lifeline, 3500227 is a self retracting lifeline (SRL) designed with a speed sensing brake system that stops a fall within inches to keep you safe when you're working at heights. Equipped with 8' (2.4 m) of $\frac{3}{16}$ " (5 mm) galvanized steel cable, thermoplastic housing and corrosion-resistant hardware, this lifeline also includes a swiveling anchorage loop, steel rebar hooks and a built-in connector for twin-leg direct attachment to a harness. Specially engineered for foot-level tie-off, this lightweight SRL stays out of your way as you work, retracting as needed to minimize trip hazards.



Manufacturer Part Number	SKU	Length
3500227	70007462727	8' (2.4 m)

3M™ DBI-SALA® Nano-Lok™ Edge Twin-Leg Quick Connect Self Retracting Lifeline with Comfort Grip snap hooks – Cable

3M™ DBI-SALA® Nano-Lok™ Edge with Comfort Grip connector is specifically designed for foot level tie-off and sharp edge applications. It is ergonomically designed for ease-of-use and is ideal for direct connection to most harnesses. The Comfort Grip has a 2- $\frac{1}{4}$ " gate opening and is transverse load rated to allow safe tie off in multiple orientations directly to various structures.



Manufacturer Part Number	SKU	Length
3500257	70804440876	8' (2.4 m)

3M™ DBI-SALA® Smart Lock Self-Retracting Lifeline

Our smartest SRLs yet. From reducing nuisance lockups, to simplifying inspections, every detail of the 3M™ DBI-SALA® Smart Lock Self-Retracting Lifelines is designed to help increase your productivity, safety and convenience. Using advanced motion capture technology, we studied the forces applied to the SRL during typical at-height tasks. This data helped us engineer a new arrest mechanism that can more easily detect the difference between a fall and normal work motion, tailoring a SRL for your work application.

Manufacturer Part Number	SKU	Description
3503802	70804492521	Leading Edge, Galvanized Cable, 20', Class SRL-LE
3503822	70804492588	Leading Edge, Galvanized Cable, 30', Class SRL-LE



3M™ PROTECTA® Rebel™ Self Retracting Lifeline, 3590540, Leading Edge, Red, 20' (6.1 m)

The 3M™ PROTECTA® Rebel™ Self Retracting Lifeline is a durable self retracting lifeline (SRL) that ensures protection against sharp, abrasive and leading edges. Lightweight thermoplastic housing construction and corrosion-resistant hardware mean this SRL can withstand harsh conditions. Equipped with 20' (6.1 m) of 7/32 in (5.5 mm) galvanized steel wire rope, this high-strength lifeline also features a carabiner, a swiveling self-locking snap hook with impact indicator and swiveling anchorage point to make it easy to connect this SRL to most safety harnesses. Tie off the SRL at foot-level and if a fall occurs, a speed-sensing brake system activates an internal and external energy absorption system minimizes harmful forces on your body.

Manufacturer Part Number	SKU
3590540	70007460390



Compatible with the 3M™ DBI-SALA® Roof Top Freestanding Counterweight Anchor (page 8).

SRLs: Class-SRL

3M™ DBI-SALA® Ultra-Lok™ Self Retracting Lifeline, 3504430C, 30' (9.1 m) galvanized steel cable

The 3M™ DBI-SALA® Ultra-Lok™ Self Retracting Lifeline, 3504430C is a self retracting lifeline (SRL) designed with an anti-ratcheting, self-adjusting, twin disc brake system that stops a fall within inches to keep you safe when you're working at heights. Equipped with 30' (9.1 m) of $\frac{3}{16}$ in. (5 mm) galvanized steel cable and thermoplastic housing, this SRL also includes corrosion-resistant hardware—a swiveling anchorage point and a swiveling snap hook with impact indicator.

Manufacturer Part Number	SKU
3504430	70007456596



3M™ DBI-SALA® Smart Lock Self-Retracting Lifeline

Our smartest SRLs yet. From reducing nuisance lockups, to simplifying inspections, every detail of the new 3M™ DBI-SALA® Smart Lock Self-Retracting Lifelines is designed to help increase your productivity, safety and convenience. Using advanced motion capture technology, we studied the forces applied to the SRL during typical at-height tasks. This data helped us engineer a new arrest mechanism that can more easily detect the difference between a fall and normal work motion, tailoring a SRL for your work application.

Manufacturer Part Number	SKU	Description
3503800	70804492505	Galvanized Cable, 30', Class SRL
3503801	70804492513	Stainless Steel Cable, 30', Class SRL
3503803	70804492539	Galvanized Cable, 20', Class SRL
3503804	70804492547	Stainless Steel Cable, 20', Class SRL
3503820	70804492562	Rope, 35', Class SRL
3503821	70804492570	Stainless Steel Cable, 35', Class SRL
3503823	70804492596	Stainless Steel Cable, 50', Class SRL
3503824	70804492604	Galvanized Cable, 50', Class SRL



3M™ DBI-SALA® Nano-Lok™ Twin-Leg Quick Connect Self Retracting Lifeline – Web 3101473, Blue, 6' (1.8 m)

The 3M™ DBI-SALA® Nano-Lok™ Personal Self-Retracting Lifeline unites light weight design with industrial-strength durability and function. The extremely compact and lightweight design is virtually unnoticeable on your back, staying out of the worker's way and making it ideal as a lanyard replacement. The Nano-Lok's smart activating brake system achieves fall clearance as low as 4' (1.2 m) – providing more protection at low heights. In addition, tension is always kept on the lifeline, which reduces dragging, snapping and trip falls.

Manufacturer Part Number	SKU
3101473	70007455648



3M™ Protecta® Rebel™ Twin-Leg Self Retracting Lifeline, web

The 3M™ Protecta® Rebel™ Twin-Leg Self Retracting Lifeline, 3100414 is a durable self retracting lifeline (SRL) with a speed-sensing brake system that stops a fall within inches to keep you safe when you're working at heights. Equipped with 6' (1.8 m) of 1" (2.5 cm) polyester web, this lifeline also features corrosion-resistant hardware—self-locking swiveling snap hook, a triple locking carabiner and swiveling anchorage loops. A built-in connector for twin-leg direct attachment to a harness makes it convenient to attach this SRL system to a harness. Designed with the worker in mind, this SRL moves with you as you work and offers nearly double the working area of a lanyard without falling slack.

Manufacturer Part Number	SKU
3100414	70007442950



3M™ DBI-SALA® Nano-Lok™ Extended Length Self Retracting Lifeline

With 3M™ DBI-SALA® Nano-Lok™ Extended Length Self-Retracting Lifelines we've advanced the versatility of 3M™ DBI-SALA® Nano-Lok™ SRLs, now available in 15' (4.5 m), and now 20' (6.1 m) lengths.

Manufacturer Part Number	SKU	Description
3101684	70804486234	Galvanized Steel Cable, 15'
3103865	70804493040	Stainless Steel Cable, 15'
3103866	70804493057	Web, 20'
3103872	70804485590	Web, 20'
3103873	70804485608	Web, 20'
3501694	70804497579	Galvanized Cable, 15'
3501695	70804497587	Stainless Steel Cable, 15'



3M™ Protecta® Rebel™ Self Retracting Lifeline – Cable 33' (10 m), 1 EA/case

The 3M™ Protecta® Rebel™ Self Retracting Lifeline, 3590500 is a durable self retracting lifeline (SRL) with a speed-sensing brake system that stops a fall within inches to keep you safe when you're working at heights. Equipped with 33' (10 m) of $\frac{3}{16}$ " (5 mm) stainless steel wire rope, this high-strength cable lifeline also features a carabiner, a steel, self-locking snap hook and swiveling anchorage to make it easy to connect this SRL to most safety harnesses. The SRL's lightweight design means it stays out of your way for comfort and ease of use.

Manufacturer Part Number	SKU
3590500	70007458592



SRLs: Class-SRL-R

3M™ DBI-SALA® Ultra-Lok™ Self Retracting Lifeline, Retrieval/Bracket, Cable 3501102, 50' (15.2 m)

Ultra Lok™ self retracting lifelines (SRLs) are rugged, yet extremely lightweight and superbly engineered devices you can count on for safety, efficiency and comfort. Stainless steel components, an anti ratcheting brake system and a semi sealed design provide the user with a system built to last. Our SRLs are backed by decades of proven field service for absolute confidence, safety and reliability. An SRL's lifeline will extend as the user moves away, and retract automatically enabling the user to move about within a recommended working area at normal speeds. Should a fall occur, a speed sensing brake system will activate stopping the fall and reducing the forces imposed on the user to safe levels.

Manufacturer Part Number	SKU
3501102	70007462891



Rescue


3M™ DBI-SALA® Rollgliss™ R550 Rescue and Descent Device, yellow

3M™ DBI-SALA® Rollgliss™ Rescue and Descent Device with a rescue wheel, anchor sling, 2 carabiners and a carrying bag.



Manufacturer Part Number	SKU	Length
3327050	70007448338	50' (16 m)
3327100	70007448361	100' (30.4 m)
3327150	70007448387	150' (46 m)




New 3M customers can trade in:



Trade in competitive fall protection products.




Purchase comparable qualifying* 3M Fall Protection products.





Receive a cash rebate.


Existing 3M customers can trade up:



Trade in current 3M Fall Protection products.



Purchase new, upgraded qualifying** 3M Fall Protection products.



Receive a cash rebate.

It's easy to get started.

- 1. Identify**
Find the fall protection products you want to trade in or trade up.
- 2. Choose**
Select from over 1,200 eligible 3M Fall Protection products at go.3M.com/FPtradein.
- 3. Order**
Contact us to place your order.
- 4. Register**
Confirm your purchase and initiate your rebate payment at go.3M.com/FPtradein.

Trade in or trade up at
go.3M.com/FPtradein today.

What you'll need:

- Digital copy of your receipt of purchase from a 3M authorized distributor
- Digital images proving your old equipment was taken out of service (e.g. Harnesses with D-rings cut off, SRLs and Lanyards with hooks cut off)

End user rebate only. Distributors and wholesalers excluded. Must follow requirements online to receive rebate. Visit go.3M.com/FPtradein for full terms and conditions.

*Comparable qualifying products means anchor for anchor, harness for harness, etc. Except as noted in the Terms & Conditions.

**Upgraded qualifying products means current 3M customer must purchase a higher value comparable product to qualify for a rebate. (Example: Delta™ Harness traded in for an ExoFit NEX™ Harness. ExoFit NEX™ Harness for ExoFit™ STRATA Harness. 3M™ Protecta® SRL for 3M™ DBI-SALA® SRL.)

Fall Protection for Tools

3M™ DBI-SALA®

Hook2Quick Ring Coil with Tail

Stop the drop.



3M™ DBI-SALA® Hard Hat Tether, 10 pack

Introducing the new heavy-duty 3M™ DBI-SALA® Hard Hat Tether. Work with confidence knowing that if your hard hat falls off, it's not going anywhere. The new 3M™ DBI-SALA® Hard Hat Tether features a new proprietary clip design that prevents deformation of the clip over extended use. This helps ensure a secure attachment, helping to further reduce the number of dropped hard hats.



Manufacturer Part Number	SKU
1500178	70804486085

3M™ DBI-SALA® Hook2Loop Bungee Tether, yellow, 32" to 47" (81 cm to 119 cm)

Tool lanyard, bungee tether, 15 lb (6.8 kg) capacity, self-locking carabiner.



Manufacturer Part Number	SKU
1500047	70007449047

3M™ DBI-SALA® Safe Bucket 100 lb (45.4 kg) Load Rated Hook and Loop Canvas, black, yellow, 15" x 12" (38.1 cm x 31.7 cm)

Canvas bucket with hook and loop closure system, 100 lb (45.4 kg) capacity.

Manufacturer Part Number	SKU
1500134	70007439121



Fall Protection for Tools

3M™ DBI-SALA® Parts Pouch canvas, black, small

Small parts pouch with self-closure system in canvas black.

Manufacturer Part Number	SKU
1500119	70007439055



3M™ DBI-SALA® Quick Wrap Tape II, yellow, 1" x 108" (2.5 cm x 274 cm), 10 pack

3M™ DBI-SALA® Quick Wrap Tape II, used with 3M™ DBI-SALA® D-rings and 3M™ DBI-SALA® Tool Cinches.

Manufacturer Part Number	SKU
1500175	70804440223



Use with:

3M™ DBI-SALA® D-ring Attachment 0.5" x 2.25", 1500003, 10 ea/pack

Manufacturer Part Number	SKU
1500003	70007448809



3M™ DBI-SALA® D-Ring Attachment 1" x 3.5", 1500007, 10 ea/pack

Manufacturer Part Number	SKU
1500007	70007448841



3M™ DBI-SALA® Dual D-ring Attachment, 1500001, Small, 10 ea/pack

Manufacturer Part Number	SKU
1500001	70007448783



3M™ Dual Wing Cinch Tool Attachment Point 1500017, 80 lb Capacity, 1 ea

Manufacturer Part Number	SKU
1500017	70007448882



3M™ DBI-SALA® Hook2Rail Tool Tether, 81" Heavy Duty 1500052, 1 ea

Manufacturer Part Number	SKU
1500052	70007437844



3M™ DBI-SALA® Tape Measure Holster with Medium Sleeve and Retractor 1500100, 1 ea

Manufacturer Part Number	SKU
1500100	70007438966



3M™ DBI-SALA® Scaffold Wrench Holster with Retractor, Belt 1500096, 1 ea

Manufacturer Part Number	SKU
1500096	70007438925



3M™ DBI-SALA® Adjustable Radio/Cell Phone Holster, with Clip2Loop Coil and Micro D-ring, black, 5.25" x 2.25" (13.3 cm x 5.7 cm)

Adjustable radio/cell phone holster combo, includes coil tether and cell phone attachment point.

Manufacturer Part Number	SKU
1500089	70007438891



3M™ DBI-SALA® Clip2Loop Coil Tether, black, yellow, 10-pack

Tool lanyard, coil tether, 2 lb (0.9 kg) capacity

Manufacturer Part Number	SKU
1500060	70007437885



3M™ DBI-SALA® 5 lb Tool Retractor

The 3M™ DBI-SALA® 5 lb (2.3 kg) Retractable Tool Tether features a lightweight, compact housing and a high-strength Dyneema® fiber web lifeline. This design helps minimize tool tangling, as well as minimizing job site tripping hazards and entanglements, while reducing weight on workers' belts and harnesses.

Manufacturer Part Number	SKU
1500156	70804436908



3M™ DBI-SALA® Harness Adaptor 1500161

Harness adaptor provides an attachment point for a tool lanyard to your harness webbing. Third-party certified to a 5 lb (2.3 kg) maximum capacity.

Manufacturer Part Number	SKU
1500161	70804436940



Confined Spaces



3M™ DBI-SALA® 5-Piece Davit Set

**Get in easily.
Get out safely.**

3M™ DBI-SALA® Advanced 4-in-1 Davit Guard System, green

3M™ DBI-SALA® Advanced 4-in-1 Davit Guard System with guardrail and winch/SRL mounting bracket.

Manufacturer Part Number	SKU
8530352	70007600102



3M™ DBI-SALA® Salalift II Winch, galvanized wire rope, anodized yellow and black plastic housing, 60' (18 m)

3M™ DBI-SALA® Salalift II Winch with 60' (18 m) of ¼" (6.3 mm) galvanized steel wire rope and indicating swivel snap hook, mounting bracket and carrying bag.

Manufacturer Part Number	SKU
8102001	70007491502



3M™ Protecta® PRO™ Confined Space System

3M™ Protecta® Confined Space System includes 8' (2.4 m) AK105A aluminum tripod with 359108 50' (15 m) galvanized 3-way self retracting lifeline, 3590498 mounting bracket and AK020A1 pulley.

Manufacturer Part Number	SKU
8308005	70007713368



3M™ DBI-SALA® Advanced Aluminum Tripod, silver, 7" (2.1 m)

7" (2.1 m) 3M™ DBI-SALA® Advanced Aluminum Tripod with adjustable locking legs, safety chain, safety shoes, top pulley and quick-mount bracket for winches/SRLs.

Manufacturer Part Number	SKU
8000000	70007488417



3M™ DBI-SALA® Advanced Portable Fall Arrest Post

3M™ DBI-SALA® Advanced Portable Fall Arrest Post with three independent 360 degree swiveling anchor points for up to three users.

Manufacturer Part Number	SKU
8516691	70007495354



3M™ DBI-SALA® Advanced Bare Steel Uni-Anchor, with tie-off, gray, 9.8" x 8" x 29" (25 cm x 20.3 cm x 73 cm)

Bare steel uni-anchor with tie-off anchor for 3M™ DBI-SALA® Advanced Portable Fall Arrest Post.

Manufacturer Part Number	SKU
8517412	70007495594




3M™ DBI-SALA® Advanced Bare Steel Uni-Anchor, gray, 9.8" x 8" x 29" (25 cm x 20.3 cm x 73 cm)

3M™ DBI-SALA® Advanced Bare Steel Uni-Anchor for 3M™ DBI-SALA® Advanced Portable Fall Arrest Post.

Manufacturer Part Number	SKU
8510816	70007491965



Respiratory Protection



Breathe easy.

Help protect yourself from potentially hazardous exposures with 3M's selection of respiratory protection. Choose the appropriate protection for your working conditions.

[3M.com/RespiratoryProtection](https://www.3m.com/RespiratoryProtection)

Filtering Facepiece Respirators

3M™ Particulate Respirator 8210, N95

3M™ Particulate Respirator 8210 is a classic disposable N95 particulate respirator designed to help provide comfortable, reliable respiratory protection against certain non-oil based particles. This respirator incorporates 3M's proprietary technology with advanced electrostatically charged microfiber filter media, designed for ease of breathing.

Manufacturer Part Number	SKU
8210	7100132742



3M™ Particulate Respirator 8210V, N95

The 3M™ Particulate Respirator 8210V featuring 3M™ Cool Flow™ Valve is designed to help provide comfortable, reliable respiratory protection against certain non-oil based particles. This respirator incorporates 3M's proprietary technology with advanced electrostatically charged microfiber filter media, designed for ease of breathing. Its adjustable nose clip and cushioning nose foam help provide a custom and secure seal.

Manufacturer Part Number	SKU
8210V	7000002462



3M™ Particulate Respirator 8511, N95

The 3M™ Particulate Respirator 8511 features the proprietary 3M™ Cool Flow™ Exhalation Valve and helps provide comfortable, reliable respiratory protection. It is ideally suited for hot/dusty work settings that require long periods of wear.

Manufacturer Part Number	SKU
8511	7000002056



3M™ Particulate Respirator 8577, P95

The 3M™ P95 Particulate Respirator 8577 helps provide respiratory protection against certain oil and non-oil based particles. This respirator features the 3M™ Cool Flow™ Exhalation Valve and includes a carbon layer to help reduce exposure to nuisance level organic vapors.

Manufacturer Part Number	SKU
8577	7000002062



3M™ Particulate Respirator 8576, P95

This disposable P95 particulate respirator helps provide reliable respiratory protection against certain oil and non oil based particles. The respirator features a carbon layer to help provide relief against nuisance levels of acid gases.

Manufacturer Part Number	SKU
8576	7000002061



3M™ Aura™ Series Particulate Respirator 9205+, N95

The 3M™ Aura™ Series Particulate Respirator 9205+, N95 is a three-panel, flat-fold disposable respirator designed to help provide comfortable, reliable worker protection against non-oil based particles.

Manufacturer Part Number	SKU
9205+	7100232940



Reusable (Elastomeric) Respirators – half facepiece

3M™ Rugged Comfort Quick Latch Half Facepiece Reusable Respirator, 6500QL, 10/case

3M™ Rugged Comfort Quick Latch Half Facepiece Reusable Respirator series 6500QL combines comfort, durability, and stability. The proprietary quick latch design offers an easy, one-hand touch drop-down mechanism for putting the facepiece on and/off while moving in and out of contaminated areas.



Manufacturer Part Number	SKU
6501QL	7000128237
6502QL	7000128239
6503QL	7000128241

3M™ Half Facepiece Reusable Respirator, 6000, 24/case

The 3M™ Half Facepiece Reusable Respirator 6000 series offers reliable and convenient respiratory protection and is suitable for many situations, helping provide protection against particulates and a wide variety of gases and vapors according to NIOSH approvals.



Manufacturer Part Number	SKU
6100	7000001932
6200	7000001933
6300	7000001934

Reusable (Elastomeric) Respirators – full facepiece

3M™ Full Facepiece Reusable Respirator, 6000, 4/case

The 3M™ Full Facepiece 6000 series offers lightweight comfort and ease of use. Combine with appropriate 3M™ particulate filters or cartridges to help provide respiratory protection against particulates and/or a variety of gases and vapors.

Manufacturer Part Number	SKU
6700	7000002029
6800	7000002030
6900	7000002037



3M™ Ultimate FX Full Facepiece Reusable Respirator, FF-400, 4/case

Engineered for maximum comfort, durability and visibility, the 3M™ Ultimate FX Full Facepiece Reusable Respirator FF-400 series is the only respirator with Scotchgard™ Protector. This respirator features a passive speaking that helps ensure clear communications between workers, soft yet durable silicone material and a large lens for superior peripheral vision.

Manufacturer Part Number	SKU
FF-401	7000029940
FF-402	7000002284
FF-403	7100001847



3M™ Particulate Filters and Gas/Vapor Cartridges

All 3M Particulate Filters and Gas/Vapor Cartridges can be used interchangeably with 3M™ Half and Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments.

3M™ Particulate Filters 2000 and 2200 Series



- Lightweight and easy to breathe through
- Assortment of filters available for a wide range of applications
- Easier breathing through 3-layer advanced Electret Filter Media in 2200 Series Filters

Part Number	Description
2071	Particulate Filter, P95
2076HF	Particulate Filter, Hydrogen Fluoride/P95, with Nuisance Level Acid Gas Relief*
2078	Particulate Filter, P95, with Nuisance Level Organic Vapor/Acid Gas Relief*
2091	Particulate Filter, P100
2096	Particulate Filter, P100, with Nuisance Level Acid Gas Relief*
2097	Particulate Filter, P100, with Nuisance Level Organic Vapor Relief*
2291	Advanced Particulate Filter, P100
2296	Advanced Particulate Filter, P100, with Nuisance Level Acid Gas Relief*
2297	Advanced Particulate Filter, P100, with Nuisance Level Organic Vapor Relief*


3M™ Particulate Filters 7093 Series

- Unique, spring-loaded filter cover design simplifies negative pressure user seal checks
- Swept-back design provides enhanced field of view and greater comfort
- 7093C offers a lightweight, low profile design that combines P100 filtration with carbon-loaded features found in heavier combination cartridge products



7093	Particulate Filter, P100
7093B	Particulate Filter, P100, Bulk
7093C	Cartridge/Filter, Hydrogen Fluoride, P100, with Nuisance Level Organic Vapor and Acid Gas Relief*

3M™ Gas/Vapor Cartridges 6000 Series



- Low-profile design helps maintain good field of vision
- Full range of cartridges to meet your needs

6001	Cartridge, Organic Vapor
6002	Cartridge, Acid Gas**
6003	Cartridge, Organic Vapor/Acid Gas**
6004	Cartridge, Ammonia/Methylamine
6005	Cartridge, Formaldehyde/Organic Vapor
6006	Cartridge, Multi Gas/Vapor**
6007	Cartridge, Mercury Vapor or Chlorine

3M™ Combination Cartridges/P100 Particulate Filters 6000 Series



- Particulate filter is permanently attached to cartridge for easy, one-step assembly
- Unique design for enhanced comfort and visibility

60921	Cartridge/Filter, Organic Vapor/P100
60922	Cartridge/Filter, Acid Gas/P100**
60923	Cartridge/Filter, Organic Vapor/Acid Gas/P100**
60924	Cartridge/Filter, Ammonia/Methylamine/P100
60925	Cartridge/Filter, Formaldehyde/Organic Vapor/P100
60926	Cartridge/Filter, Multi-Gas/Vapor/P100**
60927	Cartridge/Filter, Mercury Vapor/Chlorine Gas/P100
60928	Cartridge/Filter, Organic Vapor/Acid Gas/P100***

* 3M recommended for relief against nuisance levels of organic vapors and/or acid gases. Nuisance level organic vapor and acid gas refers to concentrations not exceeding OSHA PEL or applicable government occupational exposure limits, whichever is lower.

** Reminder: These cartridges are approved for respiratory protection from hydrogen sulfide gas up to 10 times the permissible exposure limit (PEL) with half facepiece respirators and full facepiece respirators when qualitatively fit tested, or up to less than 300 parts per million (ppm) with full facepiece respirators when quantitatively fit tested or according to specific OSHA standards or applicable government regulations, whichever is lower. 300 ppm is the concentration considered Immediately Dangerous to Life or Health (IDLH) for hydrogen sulfide.

† As recommended by the California Department of Pesticide Regulation No. 01-009-Methyl Bromide Field Fumigation. 3M recommended for use against radioiodine and methylbromide. Note: not NIOSH approved for methylbromide or radioiodine.

Reusable (Elastomeric) Respirator Filters and Cartridges

3M™ Particulate Filter, 2091, P100, 50 pairs/case

The 3M™ Particulate Filter 2091 is NIOSH approved for environments containing certain oil and non-oil based particles. Use with 3M™ Half and Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments.

Manufacturer Part Number	SKU
2091	7000051991

3M™ Particulate Filter, 2097, P100, with nuisance level organic vapor relief, 50 pairs/case

The 3M™ Particulate Filter 2097 is NIOSH approved for environments containing certain oil and non-oil based particles. 3M recommended for nuisance odor relief for organic vapor levels below the Permissible Exposure Level (PEL) and for ozone protection up to 10X OSHA PEL. Use with 3M™ Half and Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments.

Manufacturer Part Number	SKU
2097	7000029657



Respiratory Protection

3M™ Particulate Filter, 7093, P100, 30 pairs/case, 7093B, P100, 72 pairs/case

The 3M™ Particulate Filter 7093 is NIOSH approved for environments containing certain oil and non-oil based particles. Use with 3M™ Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments or with 3M™ Cartridge 6000 Series with 3M™ Filter Adapter 502. NIOSH approved for environments containing certain oil and non-oil based particles. Plastic filter encasement designed for high heat or wet applications.



Manufacturer Part Number	SKU
7093	7000002154
7093B	7000002155

3M™ Hydrogen Fluoride Cartridge/Filter, 7093C, P100, 30 pairs/case, 7093CB, P100, 72 pairs/case

The 3M™ Hydrogen Fluoride Cartridge/Filter 7093C is NIOSH approved and provides protection against hydrogen fluoride and oil/non-oil based particles. 3M recommended for nuisance odor relief for organic vapor and acid gas levels below the Permissible Exposure Level (PEL). For use with 3M™ Half and Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments or with 3M™ Cartridge 6000 Series with 3M™ Filter Adapter 502. Plastic filter encasement designed for high heat or wet applications.



Manufacturer Part Number	SKU
7093C	7000052600
7093CB	7000126938

3M™ Organic Vapor Cartridge, 6001, 30 pairs/case

The 3M™ Organic Vapor Cartridge 6001 is NIOSH approved against certain organic vapors. Use with 3M™ Half and Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments.

Manufacturer Part Number	SKU
6001	7000051851



3M™ Organic Vapor/Acid Gas Cartridge, 6003, 30 pairs/case

The 3M™ Organic Vapor/Acid Gas Cartridge 6003 helps provide respiratory protection against certain organic vapors or acid gases. Use with 3M™ Half and Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments.

Manufacturer Part Number	SKU
6003	7000051849



3M™ Multi-Gas/Vapor Cartridge, 6006, 30 pairs/case

The 3M™ Multi-Gas/Vapor Cartridge 6006 is NIOSH approved against certain organic vapors, acid gases, ammonia, methylamine or formaldehyde. Use with 3M™ Half and Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments.

Manufacturer Part Number	SKU
6006	7000002040



3M™ Organic Vapor Cartridge/Filter 60921, P100, 30 pairs/case

The 3M™ Organic Vapor Cartridge/Filter 60921 is NIOSH approved against certain organic vapors and particulates. Use with 3M™ Half and Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments.

Manufacturer Part Number	SKU
60921	7000029639



3M™ Organic Vapor/Acid Gas Cartridge/Filter 60923, P100, 30 pairs/case

The 3M™ Organic Vapor/Acid Gas Cartridge/Filter 60923 is NIOSH approved against certain organic vapors, acid gases and particulates. Use with 3M™ Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Full Facepiece, FF-400 Series with bayonet attachments.

Manufacturer Part Number	SKU
60923	7000029640



3M™ Multi-Gas/Vapor Cartridge/Filter, 60926, P100, 30 pairs/case

The 3M™ Multi-Gas/Vapor Cartridge/Filter 60926 is NIOSH approved for protection against certain organic vapors, acid gases, ammonia, methylamine, formaldehyde and particulates. Use with 3M™ Full Facepiece, 6000 Series, 3M™ Half and Full Facepiece, 7000 Series, and 3M™ Half and Full Facepiece, FF-400 Series with bayonet connections or attachments.

Manufacturer Part Number	SKU
60926	7000002041



3M™ Particulate Filter, 5P71, P95, 50 pairs/case

The 3M™ Particulate Filter 5P71 is NIOSH approved for environments containing certain oil and non-oil based particles. Use with 3M™ Cartridges 6000 Series or 3M™ Filter Adapter 603, and 3M™ Filter Retainer 501.

Manufacturer Part Number	SKU
5P71	7000002054



3M™ Filter Retainer, 501, 20/pack

The 3M™ Filter Retainer 501, is designed for use with any 3M™ Cartridge to attach the 3M™ Particulate Filter, 5P71, P95 where there is a need for both particulate and gas/vapor protection such as in a paint spray application.

Manufacturer Part Number	SKU
501	7000001912



3M™ Respirator Cleaning Wipe 504, 500 EA/Case

The 3M™ Respirator Cleaning Wipe 504 is used to clean 3M™ Reusable Respirators. Individually-packed 8" x 10" (20.32 cm x 25.40 cm) towelettes are alcohol-free and will not damage the facepiece materials.

Manufacturer Part Number	SKU
504	70070317139



Powered Air Purifying Respirators

3M™ Versaflo™ Heavy Industry Powered Air Purifying Respirator Kit, TR-300N+ HIK

The 3M Versaflo Heavy Industry Powered Air Purifying Respirator Kit, TR-300N+ HIK is a complete, ready-to-use High Efficiency (HE) PAPR system for industrial applications. Helps provide protection against particulates.

Manufacturer Part Number	SKU
TR-300N+ HIK	70071696770



3M™ Versaflo™ Heavy Industry Powered Air Purifying Respirator Kit, TR-600-HIK

The 3M™ Versaflo™ Heavy Industry Powered Air Purifying Respirator Kit, TR-600-HIK is a complete Powered Air Purifying Respirator and includes everything required to get started. This ready-to-use kit provides a simple way to purchase a complete PAPR system for use in rugged environments such as industrial, demolition, grinding, metal finishing, and casting operations.

Manufacturer Part Number	SKU
TR-600-HIK	70071618436




3M™ Versaflo™ Powered Air Purifying Respirator Heavy Industry Kit, TR-800-HIK

The 3M™ Versaflo™ Powered Air Purifying Respirator Heavy Industry Kit is a complete Powered Air Purifying Respirator featuring an Intrinsically Safe motor/blower and including everything required to get started. This ready-to-use kit provides a simple way to purchase a complete PAPR system for use in rugged industrial environments. The new standard in intrinsically safe protection – The TR-800 is a PAPR blower rated at Division I for Classes I, II, and III under the most current UL standard (UL 60079, 6th Edition, 2013)

Manufacturer Part Number	SKU
TR-800-HIK	70071697182



Powered Air Purifying Respirator Filters and Cartridges

Marketplace Formal Name		Manufacturer Part Number	SKU
	3M™ Versaflo™ Prefilter, TR-3600, for 3M™ Versaflo™ Powered Air Purifying Respirator, TR- 300+, 100/case	TR-3600	7000127713
	3M™ Versaflo™ Spark Arrestor, TR-362, for 3M™ Versaflo™ Powered Air Purifying Respirator, TR- 300+, 2/bag	TR-362	7000052905
	3M™ Versaflo™ High Efficiency (HE) Filter, TR-3712N-5, 5/case	TR-3712N	70071765047
	3M™ Versaflo™ TR-300N+ Series PAPR Filter Cover TR-371+ 1 EA/Case	TR-371+	7100156020
	3M™ Versaflo™ Prefilter, TR-6600, for 3M™ Versaflo™ Powered Air Purifying Respirator, TR-600, 10/bag	TR-6600	70071618246
	3M™ Versaflo™ Spark Arrestor, TR-662, for 3M™ Versaflo™ Powered Air Purifying Respirator, TR-600, 2/pack	TR-662	70071618253
	3M™ Versaflo™ High Efficiency (HE) Filter, TR-6710N, 40/case	TR-6710N	70071618287
	3M™ Versaflo™ Organic Vapor/Acid Gas/HEPA Cartridge TR-6530N, for TR-600/800 PAPR	TR-6530N	7100021007
	3M™ Versaflo™ Multi-Gas/High Efficiency (HE) Cartridge, TR-6590N, 5/case	TR-6590N	70071618352
	3M™ Versaflo™ High Efficiency (HE) and Nuisance Organic Vapor/Acid Gas Filter/Cartridge, TR-6820N, 5/case	TR-6820N	70071618295
	3M™ Versaflo™ Filter Cover, TR-6700FC, 1/case	TR-6700FC	70071618261
	3M™ Versaflo™ Filter Cover, TR-6800FC, 1/case	TR-6800FC	70071622040
	3M™ Versaflo™ Filter Cover, TR-6500FC, 1/case	TR-6500FC	70071622073

Select Respiratory Protection Application Chart

Step 1: Identify the hazard				
Hazard	Silica	Wood dust	Solvents	Welding and other metal fumes
Task	Cutting, sawing, drilling, jack hammering, demolition, crushing and grinding	Cutting and finishing wood, carpentry work and demolition	Painting, waterproofing, roofing, joining, gluing, applying synthetic butyl rubber membrane, spraying coatings, fireproofing, equipment and clean-up	Welding, gouging and cutting processes such as polishing, grinding, torch cutting, brazing or soldering
Source	Silica dust from concrete, brick, mortar, ceramic tiles, rocks or stones	Dust from softwood, hardwood and medium density fiberboard (MDF)	Solvents from paint, adhesive, sealants, brick and material treatments such as toluene, xylene, methyl ethyl ketone (MEK), acetone	Fumes from various metals that may contain manganese, steel alloys such as hexavalent chromium, iron oxide, aluminum, zinc oxides, cadmium oxide, lead or nickel, and gases such as ozone

Step 2: Select your respirator				
Product	Silica	Wood dust	Certain Organic Solvents	Welding and other metal fumes
3M™ Filtering Facepiece Respirators Lightweight, easy to use, maintenance free. Select models include an exhalation valve. Consider for those tasks where particulate exposures are up to 10 times the occupational exposure limit (OEL).				
 8210	✓	✓		
 8210V	✓	✓		
 8511	✓	✓		
 8515	✓	✓		✓ Welding specialty respirator
 8212	✓	✓		✓ Welding specialty respirator
 8214 ^{1,2}	✓	✓	✓ For organic vapor odor relief when exposure is below OEL	✓ Welding specialty respirator
 8577 ²	✓	✓	✓ For organic vapor odor relief when exposure is below OEL	
 9211+	✓	✓		
 9205+	✓	✓		

Select your reusable respirator, filter and/or cartridge.

Product	Silica	Wood dust	Certain Organic Solvents	Welding and other metal fumes
3M™ Reusable Respirators, Filters and Cartridges Adjustable respirators, available in small, medium and large, with interchangeable filter/cartridge combinations that help provide protection against particulate and organic vapors. Consider for those tasks where exposures are up to 10 times the occupational exposure limit (OEL). When quantitatively fit tested per 29 CFR 1910.134, full facepieces may be considered for tasks up to 50 times the OEL. Reusable respirators can be cleaned and sanitized per user instructions.				
 6000	2091 7093	2091 7093	6001 with 5P71 (3M™ Filter Retainer 501) or 60921	2097 ²
 6500QL	2091 7093	2091 7093	6001 with 5P71 (3M™ Filter Retainer 501) or 60921	2097 ²
 6000	2091 7093	2091 7093	6001 with 5P71 (3M™ Filter Retainer 501) or 60921	Does not fit under a welding helmet
 FF-400	2091 7093	2091 7093	6001 with 5P71 (3M™ Filter Retainer 501) or 60921	Does not fit under a welding helmet
 7800S	2091 7093	2091 7093	6001 with 5P71 (3M™ Filter Retainer 501) or 60921	2097 ² Add 7990 welding clip

3M™ Filters and Cartridges	 2091	 7093	 6001, 5P71, 501	 60921	 2097
----------------------------	--	--	--	---	--



¹ 3M recommended for ozone protection up to 10X OSHA PEL or applicable government occupational exposure limits, whichever is lower. Not NIOSH-approved for ozone.

² 3M recommended for relief against nuisance levels of organic vapors.

³ 3M recommended for relief against nuisance levels of organic vapor/acid gases.

Respiratory Protection

Product	Silica	Wood Dust	Solvents	Welding and other metal fumes
3M™ Powered Air Purifying Respirators Work with comfort and ease of use for extended periods of time. We've got your back, but you won't feel it, thanks to our ergonomic design.				
 Adflo™	15-0299-99 (filter) with 15-0099-99 (pre-filter) and 15-0009-99 (spark arrestor)	15-0299-99 (filter) with 15-0099-99 (pre-filter) and 15-0009-99 (spark arrestor)	15-0299-99 (filter) together with 15-0499-99 (cartridge) and 15-0099-99 (pre-filter) and 15-0009-99 (spark arrestor)	15-0299-99 (filter) with 15-0099-99 (pre-filter) and 15-0009-99 (spark arrestor) (Optional OV nuisance odor filter 35-0699-99)
 TR-300+	TR-3712N	TR-3712N	N/A	TR-3712N with TR-362 (spark arrestor)
 TR-600	TR-6710N	TR-6710N	TR-6530N	TR-6710N OR TR-6820N with TR-662 (The filter cover is required when using a pre-filter or spark arrestor.)
 TR-800 If an Intrinsically Safe (IS) rated powered air purifying respirator is required, select the TR-800.	TR-6710N	TR-6710N	TR-6530N	TR-6710N OR TR-6820N with TR-662 (The filter cover is required when using a pre-filter or spark arrestor.)

3M™ Powered Air Purifying Respirator Filters and Cartridges	 15-0009-99	 15-0099-99	 15-0299-99	 15-0499-99	 35-0699-99	 TR-3600	 TR-362
	 TR-3712N	 TR-6600	 TR-662	 TR-6710N	 TR-6510N	 TR-6590N	 TR-6820N
	 TR-6500FC	 TR-6700FC	 TR-6800FC				

WARNING

Selection of appropriate respiratory protective equipment (RPE) will depend on the particular situation and should be made only by a competent person knowledgeable of the actual working conditions and the limitations of RPE.

Details regarding performance and limitations are set out on the respirator packaging and User Instructions. 3M respirators help protect against certain airborne contaminants. No respirator is capable of preventing all airborne contaminants.

Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. This guide summarizes certain U.S. and Canada respiratory requirements and considerations. Local requirements may vary.

Follow all local regulations. In the U.S., a written respiratory protection program must be implemented meeting all the requirements of OSHA 29 CFR 1910.134 including training, fit testing, and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. Misuse may result in sickness or death. For correct use, consult supervisor and User Instructions, or call 3M Personal Safety Division (PSD) Technical Service in the U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414.

3M™ Reusable Respirator Trade-in Program

Get FREE 3M™ Reusable Respirator facepieces* in exchange for competitive facepieces and your purchase of 3M™ Cartridges and/or Filters.**

What's in it for you?

Cost savings. Upgrade your existing reusable respirator facepieces for free.

Convenience. All 3M reusable respirators have the same bayonet-style connector allowing for flexibility in facepiece style and filter and cartridges selection.

Support. Whether it's your regional sales representative, our technical service team or our online resources, we're here to help you along the way.

What do you do to make it happen?

1. Contact your local 3M safety representative to confirm and process trade-in request, or call our customer service number: 1-800-328-1667.
2. User must order cartridges and filters from a 3M Authorized Distributor.
3. 3M will ship free facepieces to the distributor or end-user.
4. User and/or distributor collects and appropriately disposes of competitive facepieces.

Trade-in Offer Example

Trade in your competitive facepieces...
(Minimum quantity: 10)



Get the same number of 3M™ Reusable Respirator facepieces FREE...
(Mix and match styles)



...when you order the appropriate number of cartridges and/or filters from a 3M distributor
(See chart below)



Trade-in Ratio of Cartridges/Filters per Facepiece

Facepiece	Half			Full	
	6000 Series	6500 Series	7500 Series	6000 Series	FF-400 Series
					
Cartridges and/or Filter Purchase Quantity per Facepiece	2 pairs	2 pairs	3 pairs	4 pairs	10 pairs

*A minimum selection of 10 assorted facepieces necessary to meet trade-in program requirements.

**See chart for trade-in ratio of cartridges or filters to be purchased for each qualifying trade-in facepiece.

Interested in getting started? Learn more at [3M.com/RRtradein](https://www.3m.com/RRtradein)

Request a demo.

Reach out to your 3M Core Safety Specialist to learn how
you can demo our product – 3M.com/FindPPeRep



TR-300N+ HIK



9100MP



TR-600-HIK



G5-01



TR-800-HIK



M-409SG

3M.com/Versaflo

3M.com/WeldingSafety

3M reserves the right to discontinue or terminate this offer at any time. 3M reserves the right to demo 3M™ Versaflo™ and Adflo™ Powered Air Respirators to those who complete the web request form and qualify for the demo. No purchase necessary. No substitutions, refunds, transfers or cash equivalent payments will be allowed. One demo per person. For occupational use only. Please allow 2-4 weeks for follow up. 3M is not liable for undelivered demonstrations. A maximum of 100 demos will be conducted. 3M will only use this information to respond to your requests and interests and as further described in our Privacy Policy.

Welding Equipment



**Comfort.
Without
compromise.**

We've committed ourselves to developing tools that will greatly improve the world of the welder. From the first ground breaking auto-darkening welding helmet in 1981 to our current line up of state-of-the-art welding safety products, we continue to revolutionize your world.

[3M.com/WeldingSafety](https://www.3M.com/WeldingSafety)

Welding Helmet Information

3M™ Speedglas™ Welding Helmets

Mid-Range	Premium	Premium with Air	Multi-Protection
 9002NC	 9100 9100 FX	 G5-01	 9100 FX
Improved optics in the Speedglas™ 9002NC welding filter helps you see your welds in a new light, providing more contrast and natural-looking color.	We have a passion for welding and we know the challenges of your profession. We share the enthusiasm and pride you put into your welding — so it's natural for us to want to address the ergonomic, safety, and health challenges facing you every day. Your thoughts and opinion are at the forefront of our continuous search for innovation.		
For specialty welding, TIG and quick tasks.	Designed with the professional welder in mind. 9100 and 9100FX can be worn with standard suspension or used with a hard hat adapter. 9100FX, G5-01 and 9100MP have a clear grinding visor.	Optimal respiratory protection and comfort for increased productivity and demanding environments. Combines respiratory, hearing, head, eye and face protection in one.	Combines respiratory, hearing, head, eye and face protection in one.
These headtops provide eye and face protection only.		These headtops are compatible with certain Powered Air and Supplied Air Respirators.	

Reliability

We know harsh welding environments: We build our products to thrive in them. From creating reliable arc sensing/shade switching to selecting highly durable materials to designing equipment for long-lasting mechanical operation.

Comfort

Comfort means a helmet that vents exhaled air. It means a headband that avoids scientifically determined pressure points around your head. And how a helmet provides eye and face protection while being comfortable for a full shift.

View

Every helmet design detail can affect your view. That's why we provide high performance auto-darkening welding filters, our side windows lenses, and large, protective clear visors. Each of these, and many more, helmet design elements maximize your ability to see.

Protection

UV/IR radiation. High-speed grinding particles. Falling objects. Respiratory hazards. List your workplace hazards—then find the right Speedglas helmet, accessories, and respiratory protection. Have a unique workplace hazard? Contact a rep for even more 3M solutions.

Welding Helmets

3M™ Speedglas™ Helmet – 9002NC

Precision optics of the Speedglas™ Welding Filter 9002NC provide a lighter, brighter, more realistic view with better control of the weld puddle. More comfortable suspension for longer wear-time; lighter weight, slim profile means less constriction in tight spaces; exhaust vent built into the helmet helps to reduce lens fogging; simplified interface that is easy to operate and maintain.

Manufacturer Part Number	SKU
04-0100-20NC	7010302093

Accessory

3M™ Speedglas™ Hard Hat Adapter for 3M™ Speedglas™ 9002NC Welding Helmet, no hard hat, 1/case

The 3M™ Speedglas™ Hard hat Adapter helps attach the 3M™ Speedglas™ 9002NC Series Welding Helmets to your hard hat.

Manufacturer Part Number	SKU
07-0014-00NR	7000030042



3M™ Speedglas™ Welding Helmet 9100 with 3M™ Speedglas™ Auto-Darkening Filter 9100XXi

3M™ Speedglas™ Welding Helmet 9100 with Auto Darkening Filter 9100XXi can be used for Stick, MIG, and TIG welding processes. The 3M™ Speedglas™ Auto Darkening Filter 9100XXi allows you to more readily recognize colors.

Manufacturer Part Number	SKU
06-0100-30iSW	7010302093

Accessory

3M™ Speedglas™ Hard Hat Adapter for 3M™ Speedglas™ Welding Helmet 9100

The 3M Speedglas Hard hat Adapter 06-0014-00NR helps attach the 3M Speedglas Welding Helmets 9100 Series to your hard hat.

Manufacturer Part Number	SKU
06-0014-00NR	7000127722



3M™ Speedglas™ Welding Helmet, 9100 FX, with 9100XX Auto-Darkening Filter

The 3M™ Speedglas™ Welding Helmet 9100 FX features a flip-up 9100XX dark shade 5, 8-13 auto-darkening filter assembly, shade 5 Side Windows and a clear 8" x 4.25" (200 mm x 110 mm) faceshield.

Manufacturer Part Number	SKU
06-0600-30SW	7010341109

Accessory

3M™ Speedglas™ Hard Hat Adapter for 3M™ Speedglas™ Welding Helmet 9100-FX

The 3M™ Speedglas™ Hard hat Adapter 06-0014-00NR helps attach the 3M Speedglas Welding Helmet 9100-FX to your hard hat. All mounting hardware is included.

Manufacturer Part Number	SKU
06-0614-00NR	7000148536



3M™ Speedglas™ Welding Helmet 9100MP with 3M™ Adflo™ Powered Air Purifying Respirator

The 3M™ Speedglas™ Welding Helmet 9100MP is designed for professional welders who require optimum comfort, trusted protection, and ultimate performance.

Manufacturer Part Number	SKU
37-1101-00SW	70071623600
37-1101-00SWHA	70071693462
37-1101-20SW	70071735123
37-1101-30SW	70071735131



3M™ Speedglas™ G5-01 Heavy-Duty Welding Helmet with 3M™ Adflo™ High-Altitude PAPR Assembly

The 3M™ Speedglas™ G5-01 Heavy-Duty Welding Helmet with 3M™ Adflo™ High-Altitude PAPR Assembly uses next-generation technology to help provide dynamic welding protection. Intuitively designed for the challenges faced on the job, this ergonomic helmet setup includes a clear, wide-view protective visor for grinding and related jobs. Use the welding technology of the future, today — equip the 3M™ Speedglas™ G5-01 Heavy-Duty Welding Helmet with 3M™ Adflo™ High-Altitude PAPR Assembly.



Manufacturer Part Number	SKU
46-1101-30i	7100214392
46-1101-30iVC	7100214375

3M™ Speedglas™ G5-02 Welding Helmet 08-0100-50iC, with Curved ADF, Headband, Cleaning Wipe and Bag

Thanks to the improved optics, the 3M™ Speedglas™ Curved Welding Filter G5-02 (621120) allows you to more readily recognize colors, using the 3M™ Speedglas™ Natural Color Technology.



Manufacturer Part Number	SKU
08-0100-50iC	7100239917

3M™ Adflo™ PAPR and 3M™ Versaflo™ M-Series Helmet Kit with 3M™ Speedglas™ Welding Shield

The 3M™ Adflo™ PAPR and 3M™ Versaflo™ M-Series Helmet Kit with 3M™ Speedglas™ Welding Shield helps keep the user safe in a variety of working environments. With an assigned protection factor (APF) of 1000, this kit provides a high-efficiency particulate respiratory protection system for welders housed in a lightweight, compact design. Facilitate proper welding protection with the advanced technology of the 3M™ Adflo™ PAPR and 3M™ Versaflo™ M-Series Helmet Kit with 3M™ Speedglas™ Welding Shield. Can be outfitted with a 3M™ Speedglas™ 9100XXi ADF with Natural Color Technology.



Manufacturer Part Number	SKU
38-1101-00SW	70071730488

Consumables and Accessories

Product Description	CAT ID	For Use With
3M™ Speedglas™ Auto-Darkening Filter 9100X, shades 5 and 8-13	06-0000-20	9100, 9100 QR, 9100-Air, 9100 FX, 9100 FX-Air, 9100MP, M-407SG, M-409SG
3M™ Speedglas™ Auto-Darkening Filter 9100XX, shades 5 and 8-13	06-0000-30	9100, 9100 QR, 9100-Air, 9100 FX, 9100 FX-Air, 9100MP, M-407SG, M-409SG
3M™ Speedglas™ Auto-Darkening Filter 9100XXi, shades 5 and 8-13	06-0000-30i	9100, 9100 QR, 9100-Air, 9100 FX, 9100 FX-Air, 9100MP, M-407SG, M-409SG
3M™ Speedglas™ Welding Starter Kit 9100X	06-0201-20	9100X (9100, 9100 QR, 9100-Air, 9100 FX, 9100 FX-Air)
3M™ Speedglas™ Welding Starter Kit	06-0201-30	9100XX, 9100XXi (9100, 9100 QR, 9100-Air, 9100 FX, 9100 FX-Air)
3M™ Speedglas™ Welding Starter Kit for 9100 MP	06-0202-30	9100XX, 9100XXi (9100MP, M-407SG, M-409SG)
3M™ Speedglas™ G5-01 Starter Kit	45-1101-99	G5-01
3M™ Speedglas™ Magnification Plate, 1.5 x magnification	06-0500-56	3M™ Speedglas™ 9100 Series Auto Darkening Filters and 3M™ Speedglas™ G5-01
3M™ Speedglas™ Magnification Plate, 2 x magnification	06-0500-57	3M™ Speedglas™ 9100 Series Auto Darkening Filters and 3M™ Speedglas™ G5-01
3M™ Speedglas™ Magnification Plate, 2.5 x magnification	06-0500-58	3M™ Speedglas™ 9100 Series Auto Darkening Filters and 3M™ Speedglas™ G5-01
3M™ Speedglas™ Magnification Plate, 3 x magnification	06-0500-59	3M™ Speedglas™ 9100 Series Auto Darkening Filters and 3M™ Speedglas™ G5-01
3M™ Speedglas™ G5-01 Magnifying Lens Holder	46-0680-00	G5-01
3M™ PELTOR™ Earmuff Assembly, for Versaflo™ M-100 and M-300 Products	M-985	9100MP
3M™ Speedglas™ G5-01 Task Light Kit with Light, Protection Plate, and Cables	46-0500-01	G5-01

	Marketplace Formal Name	Manufacturer Part Number	SKU
	3M™ Adflo™ Spark Arrestor, 37142, 15-0009-99X02, 2/case	15-0009-99	7000126730
	3M™ Adflo™ Prefilter, 37144, 15-0099-99X06, welding safety, 6/case	15-0099-99	7000126731
	3M™ Adflo™ High-Efficiency Particulate Filter, 15-0299-99X02, 2/case	15-0299-99	70071544616
	3M™ Adflo™ Replacement Cartridges, 15-0499-99X02, 2/case	15-0499-99	7000128118
	3M™ Adflo™ Nuisance Odor Pad Assembly, 35-0699-99X01, 1/case	35-0699-99	70071652005

Hearing Protection

Help Prevent noise-induced hearing loss

with properly fitted hearing protection. We offer a wide range of hearing protection products including numerous types of earplug and earmuff options.

Earplugs

3M™ E-A-R™ Classic Earplugs, yellow, uncorded, NRR 29 dB

3M™ E-A-R™ Classic Uncorded Earplugs are constructed from slow-recovery foam, the disposable earplug conforms to the shape of the ear canal for comfortable hearing protection. Noise Reduction Rating (NRR): 29 dB*.

Manufacturer Part Number	SKU
312-1201	7000002300



3M™ E-A-Rsoft™ Yellow Neon Earplugs, regular, uncorded, NRR 33 dB

3M™ E-A-Rsoft™ Yellow Neon Earplugs feature soft foam and a tapered design to fit comfortably in the ear canal. Noise Reduction Rating (NRR): 33 dB*.

- Soft, pliable foam offers comfort for wearing over an extended time

Manufacturer Part Number	SKU
312-1250	7000002303



3M™ Foam Earplugs, orange, uncorded, NRR 29 dB

3M™ Foam Earplugs 1100 feature soft, foam and a tapered design to fit comfortably in the ear canal. Noise Reduction Rating (NRR): 29 dB*.

- Tapered design fits comfortably in ear canals
- Soft, pliable foam offers comfort for wearing over an extended time

Manufacturer Part Number	SKU
1100	7100099847



*See warning statements on the last page of this catalog.

3M™ E-A-R™ Flexible Fit HA Earplug 328-1000, Uncorded, NRR 25/30 dB

The 3M™ E-A-R™ Flexible HA Fit Earplug has a soft foam tip and a flexible fitting stem that allows easy insertion into the ear using one or two hands. The foam tip conforms to the unique shape of the ear canal to help block out noise. The Flexible Fit Earplugs are well suited for activities that require gloves or cause dirty hands or situations when only one hand is free to fit the earplugs.



The Noise Reduction Rating is 30 dB when using the traditional two-hand insertion method and 25 dB when using the alternate one-hand insertion method.*

Manufacturer Part Number	SKU
328-1000	70071732245

Corded Earplugs

3M™ E-A-R™ Classic Earplugs, corded, NRR 29 dB

3M™ E-A-R™ Classic Corded Earplugs are constructed from slow-recovery foam, the disposable earplug conforms to the shape of the ear canal for comfortable hearing protection. Noise Reduction Rating (NRR): 29 dB*.



Manufacturer Part Number	SKU
311-1101	7000002301

3M™ E-A-Rsoft Yellow Neon Earplugs, foam roll down, corded, NRR 33 dB

3M™ E-A-Rsoft Yellow Neon Earplugs are a comfortable earplug constructed from soft foam to conform to the unique shape of each ear canal for comfortable hearing protection. Noise Reduction Rating (NRR): 33 dB*.



Manufacturer Part Number	SKU
311-1250	7000002306

*See warning statements on the last page of this catalog.

3M™ E-A-R™ UltraFit™ Earplugs, yellow, corded, NRR 25 dB

3M™ E-A-R™ UltraFit™ Corded Earplugs feature a pre-molded, triple-flange design that fits comfortably in most ear canals. These durable, corded reusable earplugs are easy to use again and again, reducing waste. Push-to-fit products provide in-ear comfort and convenience. Noise Reduction Rating (NRR): 25 dB*.



Manufacturer Part Number	SKU
340-4004	7000002320

3M™ No-Touch Push-to-Fit Earplugs P2001, Corded 100 pair per box, NRR 29 dB

3M™ No-Touch Foam Plugs create a noise-reducing seal in the ear canal with soft foam and a push-to-fit design. Noise Reduction Rating (NRR): 29 dB*.



Manufacturer Part Number	SKU
P2001	7000052722

3M™ E-A-R™ Flexible Fit HA Earplug 328-1001, Corded, NRR 25/30 dB

The 3M™ E-A-R™ Flexible Fit Earplug has a soft foam tip and a flexible fitting stem that allows easy insertion into the ear using one or two hands. The soft foam tip conforms to the unique shape of the ear canal to help block out noise. The cord keeps earplugs readily available and helps keep foam ear tips clean between uses. The Flexible Fit Earplugs are well suited for activities that require gloves or cause dirty hands or situations when only one hand is free to fit the earplugs.

The Noise Reduction Rating is 30 dB when using the traditional two-hand insertion method and 25 dB when using the alternate one-hand insertion method.*



Manufacturer Part Number	SKU
328-1001	70071732278

*See warning statements on the last page of this catalog.

3M™ E-A-R™ Push-Ins Earplugs, yellow, corded, NRR 28 dB

3M™ E-A-R™ Push-Ins Earplugs provide hearing comfort, convenience, and protection. Noise Reduction Rating (NRR): 28 dB*.

Manufacturer Part Number	SKU
318-1001	7000052745



3M™ E-A-R™ Skull Screws, gray, corded, NRR 32 dB

3M™ E-A-R™ Skull Screws Earplugs offer noise attenuation with attitude. Noise Reduction Rating (NRR): 32 dB*.

Manufacturer Part Number	SKU
P1301	7000127181



Earmuffs

3M™ PELTOR™ X4 Earmuffs X4B, Behind-the-Head, 10 EA/Case

3M™ PELTOR™ Earmuffs X4 are lightweight, low-profile earmuffs that offer a high level of protection and visibility. Noise Reduction Rating (NRR): 27 dB*.

Manufacturer Part Number	SKU
X4B	UU008197848



*See warning statements on the last page of this catalog.

3M™ PELTOR™ Hard Hat Attached Electrically Insulated Earmuffs X4P5E, NRR 25 dB

3M™ PELTOR™ X4 Earmuffs are lightweight, low-profile earmuffs that offer mid to high level of protection and visibility. Noise Reduction Rating (NRR): 25 dB*.

Manufacturer Part Number	SKU
X4P5E	7100097429



3M™ PELTOR™ X4 Earmuffs X4P51E, full brim hard hat attached electrically insulated, NRR 26 dB

3M™ PELTOR™ X Series Earmuffs help keep your hearing protected while you're on the job. Compatible with 3M™ PELTOR™ Full Brim Hard Hats, the 3M™ PELTOR™ Earmuffs X4P51E is a lightweight, low profile earmuff designed for protection against mid to high level industrial noise and other loud sounds, with a Noise Reduction Rating (NRR): 26 dB*.

Manufacturer Part Number	SKU
X4P51E	UU008938811



*See warning statements on the last page of this catalog.

3M™ PELTOR™ X5 Earmuffs

3M™ PELTOR™ X5 Earmuffs are designed for very high noise situations, offering a Noise Reduction Rating (NRR) of 31 dB for headband, hard hat attached and back-band models. The high attenuation provided by these earmuffs is a result of the combination of specially-formulated foam in the earcups and cushions and the innovative spacer and cup design.

3M™ PELTOR™ X5 Earmuffs X5B, Behind-the-Head, 10 EA/Case

Manufacturer Part Number	SKU
X5A	7000104074
X5B	7100123163



3M™ PELTOR™ X5 Earmuffs X5P3E37279 (AAD), Hard Hat Attached

Manufacturer Part Number	SKU
X5P3E	7000104079



3M™ PELTOR™ Hard Hat Attached Electrically Insulated Earmuffs X5P5E

Manufacturer Part Number	SKU
X5P5E	7100097527



*See warning statements on the last page of this catalog.

Hearing Protection

**3M™ PELTOR™
X Series
Earmuffs**



It starts with **PAR.**

How do you decide what Hearing Protection you will offer to your workers?

If you are simply using the NRR found on the box of earplugs as a guide you may not be providing adequate protection levels for every worker. Ears come in many shapes and sizes and to make sure all workers are getting the protection they need, you need to know their Personal Attenuation Rating (PAR).



29 dB

Pass.

A “pass” result means the hearing protection is inserted properly and provides sufficient protection for the worker’s specific job.



10 dB

Fail.

A “fail” result means the hearing protection is either not inserted properly or is the wrong type or size for the worker’s ear canal.



NOTE: Finding each employee’s PAR is an essential step in a comprehensive hearing conservation program. Once a worker’s PAR is measured, you can determine if they’re using the right hearing protection and that they are trained on proper use.

What’s your PAR?

Every employee is different. Every job is different. Every ear is different. Finding each employee’s PAR will help you have assurance that workers’ hearing is protected and they are compliant with the law. That’s why we made the new 3M™ E-A-Rfit Dual-Ear Validation System fast, accurate and easy.

Fit testing is key.

Get results you can trust. The 3M™ E-A-Rfit Dual-Ear Validation System measures the effectiveness of the earplug or earmuff inside the employee’s ear providing accurate, quantitative results. Because you can simultaneously test both ears, you have more time to focus on education including the importance of fit and protection.

Why 3M?

As a leader in hearing protection, 3M offers a complete solution, with dual-ear and earmuff testing capabilities plus a user-friendly interface. The 3M™ E-A-Rfit Dual-Ear Validation System is the fast and easy way to find your employees’ PAR, because we know how important it is to make your hearing conservation program fit seamlessly into your operation.

3M™ E-A-Rfit Dual-Ear Validation System

Features

- ▶ Dual-ear testing
- ▶ Fast, clear accurate results
- ▶ Earmuff and Earplug testing capability
- ▶ Tests all 7 frequencies
- ▶ Seamless software integration
- ▶ Science-based, quantitative testing
- ▶ Compact design
- ▶ ANSI/ASA S12.71-2018 compliant

Communications

Confidence with clarity.

You have two great reasons to protect your hearing – your ears. 3M™ PELTOR™ Communication Headsets help you focus on your work and communicate with colleagues in noisy environments, without being tempted to remove your hearing protection.



Headsets

3M™ PELTOR™ WS™ LiteCom Plus Headset

The 3M™ PELTOR™ WS™ LiteCom Plus Headset has integrated, pre-programmed analog two-way radio, Bluetooth® Multipoint connectivity, noise-cancelling microphone, and environmental listening. The headset not only helps protect you against hazardous noise, but also makes it easy to communicate in noisy environments and helps promote auditory situational awareness.



Headband

Manufacturer Part Number	SKU	NRR
MT73H7A4610WS6NA	7100204433	27 dB*



Neckband

Manufacturer Part Number	SKU	NRR
MT73H7B4610WS6NA	7100204390	27 dB*

Hard-Hat Attached

Manufacturer Part Number	SKU	NRR
MT73H7P3E4610WS6NA	7100204436	25 dB*



*See warning statements on the last page of this catalog.

3M™ PELTOR™ WS™ ProTac XPI Headset

The 3M™ PELTOR™ WS™ ProTac XPI Bluetooth® Headset is equipped with environmental microphones for ambient sounds and communication in low noise environments. Bluetooth® connectivity for seamless connection to Bluetooth® enabled devices. Bright yellow color that can provide extra visibility in severe conditions. IP68 classified noise-cancelling microphone. Noise Reduction Rating (NRR): 26 dB*.



Headband

Manufacturer Part Number	SKU
MT15H7AWS6	7100196045



Hard Hat Attached

Manufacturer Part Number	SKU
MT15H7P3EWS6	7100195960

*See warning statements on the last page of this catalog.

3M™ PELTOR™ Electronic Earplug, EEP-100

The 3M™ PELTOR™ EEP-100 Electronic Earplugs allow sounds less than 82 dBA to pass through the environmental microphones, yet help provide protection when noise levels increase. This kit includes a protective charging case and an assortment of eartips. Choice of replaceable communications eartips designed to fit most ear canal sizes: 3M™ UltraFit™ Communication Eartips (NRR: 23 dB*), 3M™ PELTOR™ CCC-GRM-25 Communication Eartips (NRR: 27 dB*) and 3M™ Skull Screw™ Communication Eartips (NRR: 30 dB*)

Manufacturer Part Number	SKU
EEP-100	7100193144



3M™ PELTOR™ Level-Dependent Earplug, LEP-200

The 3M™ PELTOR™ Level Dependent Earplugs allow sounds less than 82 dBA to pass through, yet help provide protection when noise levels increase. Replaceable communication eartips help provide hearing protection in noisy environments. Multiple sizes and types designed to fit most ear canals. Ear pieces also include a small antenna to allow audio signals to be received wirelessly from a neckloop accessory (accessory sold separately).

Manufacturer Part Number	SKU
LEP-200	7010316631




Accessories and Earplug Tips

Product Number	3M ID Number	Product Description
TEP-CORD	7100074090	Replacement Cord
370-TEPL-25	7100066388	UltraFit™ Communication Tips Replacement, Large, 25 pairs
370-TEPM-25	7100066387	UltraFit™ Communication Tips Replacement, Medium, 25 pairs
370-TEPS-25	7100066371	UltraFit™ Communication Tips Replacement, Small, 25 pairs
CCC-GRM-25	7100103087	Triple-C Communication Ear tips, 25 pairs
370-1019-10	7000128201	Skull Screw™, Communication Tips, 10 pairs
TEP-WINDSCREEN	7100113748	Foam Windscreen for TEP/LEP and EEP

*See warning statements on the last page of this catalog.

Flexible and Adaptable

The CH-3 and FLX2 platform allows you to pair your protective communication needs with your existing handheld devices.



3M™ PELTOR™ CH-3 Headset

The CH-3 Headsets are intended to be plugged into an external PTT adapter that allows for convenient placement of the Push-To-Talk button, or can also be connected to a vehicle intercom system.



MT74H52A-110
NRR 26 dB*



MT74H52P3E-110
NRR 24 dB*



MT74H52B-110
NRR 24 dB*

3M™ PELTOR™ CH-3 Listen Only Hearing Protector

The CH-3 Listen Only Hearing Protectors allow you to connect to your lapel mic or handheld communication device.



HT52A-112
NRR 26 dB*



HT52P3E-112
NRR 25 dB*



HT52B-112
NRR 25 dB*

3M™ PELTOR™ CH-3 Headset with PTT

The CH-3 Headsets with an integrated Push-To-Talk button on the earcup allow for a direct connection to your handheld communication device.



MT74H52A-111
NRR 26 dB*



MT74H52P3E-111
NRR 24 dB*



MT74H52B-111
NRR 24 dB*

3M™ PELTOR™ FLX2 Cables

FLX2 Cables for Headset with Built-In PTT

Part No	Description
FLX2-107-50	Kenwood Multi-pin
FLX2-63-50	Motorola APX/XPR
FLX2-32	Motorola HT Series
FLX2-36	Kenwood 2-pin
FLX2-21	Motorola CP200/2-pin
FLX2-28	2.5 mm
FLX2-18	Motorola XTS Series
FLX2-65	Motorola ex500/ex600
FLX2-64	Icom F34/44
FLX2-44	Icom Multipin S8
FLX2-35	Icom 2-Pin Angled
FLX2-111	Hytera PD7 Series
FLX2-101	Sepura 800/900

FLX2 Cables for Headset with External PTT

Part No	Description
FLX2-200	Cable J11 Standard
FLX2-201	Cable J11 for Ground Mech

FLX2 Cables for Listen-Only

Part No	Description
FLX2-202	Cable 3.5 mm Stereo
FLX2-203	Cable 2.5 mm Mono
FLX2-204	Cable 1/4" Stereo
FLX2-205	Cable 3.5 mm Mono
FLX2-208	Cable 3.5 mm Threaded

Eye Protection



**Tough jobs
deserve a
great fit.**

Help protect against on-the-job eye injuries with 3M™ Protective Eyewear. 3M's ANSI compliant range of eyewear offers a wide range of styles, coatings and lens tints to help you get the job done.

Feature Selection Guide

Product	Series	Regulatory		Design										Available Accessory		Lens Colour												Lens Coating		
		Impact Rated, Z87+	CSA Z94.3	PDT Temples	Lens Tilt Ratchet	Dual Lens	Soft Nose Bridge	Molded Nose Bridge	Hinge Screw	OTG	Readers	Brow Guard	Gasket	Strap	Clear	Gray	Indoor/Outdoor	Photochromic	Polarized	Brown	Amber	Orange	Blue*	IR Lens	Mirrored Options	AS	AF/AS	SGAF/AS		
SecureFit™	200	●	●	●				●	●					●	●						●		●			●	●	●		
	400	●	●	●			●		●			●		●	●	●				●		●		●	●	●	●			
	500	●	●	●	●			●	●			●		●	●	●				●			●			●	●			
	3700	●	●	●	●		●		●	●				●	●					●		●	●		●		●			
Solus CCS	1000	●	●				●					●	●	●	●	●				●							●			
Maxim Elite	1000	●	●			●		●	●					●	●	●	●	●	●								●			
Virtua	CCS	●	●					●	●		●			●	●	●										●				



CLEAR

Highest visual acuity and color recognition



POLARIZED

Reduces overall brightness, glare and reflected light



VERMILLION

Helps improve visual acuity and contrast



ORANGE

Reduces blue light in specific applications, e.g., blue light curing



GRAY

Reduces overall brightness of visible light



BROWN

Reduces overall brightness, typically allowing color recognition



BLUE (excl. “sodium blue”)

Reduces brightness and glare from yellow light sources. Not intended for use in glass blowing.



PHOTOCHROMIC

Darkens when exposed to UV light (outdoors) and lightens when UV light is reduced (indoors)



INDOOR/OUTDOOR

Slightly reduces overall brightness of visible light



AMBER

Increases contrast by filtering hazy and blue-colored light



INFRARED FILTERS

Reduces infrared radiation



MIRRORED

Reflects light sources, helping reduce brightness

Safety Eyewear

3M™ Virtua™



Economical eye protection with a variety of lens tints and features.



11326-00000-20

Manufacturer Part Number	SKU	Treatment
7100110886	11326-00000-100	VIRTUA CL TEM CL LNS HC (Clear Anti-Scratch Lens)
7100109223	11326-00000-20	VIRTUA CLR TEM CLR LNS HC (Clear Anti-Scratch Lens)
7100114636	11327-00000-20	VIRTUA GRY TEM GRY LNS HC (Gray Anti-Scratch Lens)
7010315357	11329-00000-100	VIRTUA CL TEM CL LNS AF (Clear Anti-Fog Lens)
7100112434	11329-00000-20	VIRTUA CLR TEM CLR LNS AF (Clear Anti-Fog Lens)

The benefits are clear.

Fogged lenses can be frustrating and dangerous. But 3M™ SecureFit™ Protective Eyewear models featuring 3M™ Scotchgard™ Protector Anti-Fog Coating can help workers see clearly for longer, thanks to an active ingredient that bonds the coating to the lens.



Uncoated

Microscopic water droplets bead up, forming condensation and fog, which obscure vision.



3M™ Scotchgard™ Protector Anti-Fog Coating

Reduced contact angle flattens water beads into a thin, transparent film that allows light to pass through.



3M™ Scotchgard™ Protector Anti-Fog Coating

- Resists fogging longer than traditional anti-fog coatings through up to 25 washings with water.*
- Helps provide scratch resistance in tough work environments.
- Designed for working in challenging situations, such as hot and humid conditions, indoor/outdoor work, physically demanding tasks and climate-controlled areas.
- Workers can feel confident wearing 3M eye protection that meets both the Impact-Rated Protector and Anti-Fog Performance (X) requirements of the ANSI-ISEA Z87.1-2020 Standard.

*Based on 3M internal testing per EN168 test method when compared with traditional anti-fog coatings.

3M™ Solus 1000 Series Protective Eyewear with Scotchgard™ Protector Anti-Fog Lens



3M™ Solus Protective Eyewear 1000 Series with Scotchgard™ Anti-Fog Lens help workers see clearly, longer – providing longer lasting fog resistance than traditional anti-fog coatings. Removable temples enable the use of the optional strap. Optional foam gasket helps reduce eye exposure. Available in several frame colors and lens tints and meets the Impact-Rated Protector requirement of the ANSI-ISEA Z87.1-2020 Standard.

S1101SGAF



S1102SGAF



S1103SGAF



S1107SGAF



S1101SGAF-KT



S1102SGAF-KT



Manufacturer Part Number	SKU	Treatment	Frame Color
S1101SGAF	7100079183	Clear Scotchgard™ Anti-Fog Lens	Black/Blue
S1102SGAF	70071694528	Gray Scotchgard™ Anti-Fog Lens,	Black/Blue
S1103SGAF	70071694536	Amber Scotchgard™ Anti-Fog Lens,	Black/Blue
S1107SGAF	70071677143	Indoor/Outdoor Scotchgard™ Anti-Fog Lens	Black/Blue
S1101SGAF-KT	70071694544	Clear Scotchgard™ Anti-Fog Lens, Kit	Black/Blue
S1102SGAF-KT	70071676525	Gray Scotchgard™ Anti-Fog Lens, Kit	Black/Blue
S1107SGAF-KT	7100131819	Indoor/Outdoor Scotchgard™ Anti-Fog Lens	Black/Blue

Accessories

3M™ Solus 1000 Series Accessories

Manufacturer Part Number	SKU
Solus-Foam	70071694551
Solus-Strap	70071694569
Insert with Gasket	7100234547



Designed to Perform



3M™ Pressure Diffusion Temple Technology

3M's innovative temple design features slotted ribs that provide comfortable pressure equalization, allowing the temples to flex and self-adjust to the size of the wearer's head.



Curved temples for enhanced security

Our design applies pressure on the less sensitive back of the head instead of the temples, achieving a comfortable fit even during rapid head movement.

3M™ SecureFit™ Protective Eyewear 400 Series

3M™ SecureFit™ Protective Eyewear 400 Series features soft adjustable nose pads, dual injected temples, and proprietary 3M™ Pressure Diffusion Temple Technology that helps diffuse pressure over the ear to enhance frame comfort while not compromising the security of fit across a diverse workforce. Lightweight, cool safety glasses. Meets the Impact-Rated Protector requirement of the ANSI-ISEA Z87.1-2020 Standard.

SF401AF



SF402AF




SF403AF



SF410AF



SF415AF | SF420AF | SF425AF



Manufacturer Part Number	SKU	Treatment
SF401AF	70071676350	Clear Anti-Fog Lens
SF402AF	70071695350	Gray Anti-Fog Lens
SF403AF	70071676616	Amber Anti-Fog Lens
SF410AS	70071695368	Indoor/Outdoor Mirror Anti-Scratch Lens
SF415AF	70071695376	Clear, +1.5
SF420AF	70071695384	Clear, +2.0
SF425AF	70071695392	Clear, +2.5

3M™ SecureFit™ Protective Eyewear 400/X Series with Scotchgard™ Anti-fog Technology



Get excellent vision and durability even in extreme working conditions. We've extended the 3M™ SecureFit™ Protective Eyewear 400 Series by adding the premium 3M™ Scotchgard™ Anti-Fog coating as well as an optional foam gasket or brow guard. 3M™ SecureFit™ Protective Eyewear 400X Series offers models with stylized colors, proprietary Pressure Diffusion Temple (PDT) technology for comfort as well as a contoured brow guard to help provide additional coverage from flying particles. Meets the Impact-Rated Protector requirement of the ANSI-ISEA Z87.1-2020 Standard.

SF401SGAF-BLU



SF402SGAF-BLU



SF407SGAF-BLU



SF401SGAF-BLU-F



SF402SGAF-BLU-F



SF407SGAF-BLU-F



Manufacturer Part Number	SKU	Treatment
SF401SGAF-BLU	70071730645	Clear Scotchgard™ Anti-Fog Lens
SF402SGAF-BLU	70071730710	Gray Scotchgard™ Anti-Fog Lens
SF407SGAF-BLU	70071730652	Indoor/Outdoor Scotchgard™ Anti-Fog Lens
SF401SGAF-BLU-F	70071730678	Foam, Clear Scotchgard™ Anti-Fog Lens
SF402SGAF-BLU-F	70071730686	Foam, Gray Scotchgard™ Anti-Fog Lens
SF407SGAF-BLU-F	70071730660	Foam, Indoor/Outdoor Scotchgard™ Anti-Fog Lens

3M™ SecureFit™ Protective Eyewear 400/X Series
with Scotchgard™ Anti-fog Technology with Brow Guard



SF401XSGAF-BLU



SF402XSGAF-BLU



SF407XSGAF-BLU



SF403XSGAF-YEL



Manufacturer Part Number	SKU	Treatment
SF401XSGAF-BLU	70071731635	Clear Scotchgard™ Anti-Fog Lens with Brow Guard
SF402XSGAF-BLU	70071731643	Gray Scotchgard™ Anti-Fog Lens with Brow Guard
SF407XSGAF-BLU	70071731650	Indoor/Outdoor Scotchgard™ Anti-Fog Lens with Brow Guard
SF403XSGAF-YEL	70071731684	Amber Scotchgard™ Anti-Fog Lens with Brow Guard

3M™ SecureFit™ Protective Eyewear 200 Series



3M™ SecureFit™ Protective Eyewear 200 Series features the premium 3M™ Scotchgard™ Anti-Fog coating on select models, as well as the proprietary 3M™ Pressure Diffusion Temple Technology that helps diffuse pressure over the ear to enhance frame comfort while not compromising the security of fit across a diverse workforce. Meets the Impact-Rated Protector requirement of the ANSI-ISEA Z87.1-2020 Standard.

SF201AF | SF201AS



SF202AF



SF203AF



Manufacturer Part Number	SKU	Treatment
SF201AF	7100090435	Clear
SF202AF	7100090616	Gray
SF203AF	7100090617	Amber

3M™ CCS Protective Eyewear

3M™ Cord Control System (CCS) is designed to keep a corded earplug attached, untangled, and ready for use. The foam gasket helps limit eye exposure to nuisance dust while providing additional cushioning. Meets the Impact-Rated Protector requirement of the ANSI-ISEA Z87.1-2020 Standard.

11873-00000-20



SCCS02SGAF-GRN-F

11874-00000-20



SCCS01SGAF-GRN

11872-00000-20



SCCS07SGAF-GRN-F

VC215AF | VC220AF | VC225AF



SCCS02SGAF-GRN



SCCS07SGAF-GRN



SCCS01SGAF-GRN-F



Manufacturer Part Number	SKU	Treatment
11872-00000-20	7000128259	Clear Anti-Fog Lens, Foam Gasket
11873-00000-20	7000128260	Foam Gasket, Gray Anti-Fog Lens
11874-00000-20	7000128261	Foam Gasket, Indoor-outdoor mir Anti-Fog Lens
VC215AF	70071654084	Clear Anti-Fog Lens, +1.5 dioptr
VC220AF	70071654092	Clear Anti-Fog Lens, +2.0 dioptr
VC225AF	70071654100	Clear Anti-Fog Lens, +2.5 dioptr
SCCS02SGAF-GRN-F	7100196397	Gray Scotchgard Anti-Fog FM
SCCS01SGAF-GRN	7100196396	Clear Scotchgard Anti-Fog FM
SCCS07SGAF-GRN-F	7100196398	Indoor-outdoor Gray Scotchgard Anti-Fog
SCCS02SGAF-GRN	7100196395	Gray Scotchgard Anti-Fog
SCCS07SGAF-GRN	7100196394	Indoor-outdoor Gray Scotchgard Anti-Fog
SCCS01SGAF-GRN-F	7100196393	Clear Scotchgard Anti-Fog FM

3M™ Maxim™ Elite 1000 Series



Influenced by lifestyle eyewear, 3M's Maxim™ Elite 1000 Series offers performance fused with modern accents and a variety of coating options. Choose from clear, gray, blue mirror, photochromic or brown polarized lens tints to help you focus on your work instead of brightness and glare.

MXE1001SGAF-BLK



MXE1002SGAF-BLK



MXE1029AF-BLK



MXE1013SGAF-BLK



MXE1007SGAF-BLK



MXE1008AF-CLR



MXE1014SGAF-GRN



Manufacturer Part Number	SKU	Treatment
MXE1001SGAF-BLK	70071734050	Clear Scotchgard™ Anti-Fog Lens
MXE1002SGAF-BLK	70071734076	Gray Scotchgard™ Anti-Fog Lens
MXE1029AF-BLK	70071734092	Blue Anti-Fog Lens
MXE1013SGAF-BLK	70071734100	Photochromic Scotchgard™ Anti-Fog Lens
MXE1007SGAF-BLK	70071734225	I/O Gray Scotchgard™ Anti-Fog Lens
MXE1008AF-CLR	70071734084	Blue Anti-Fog Lens
MXE1014SGAF-GRN	7100222271	Brown Polarized Scotchgard™ Anti-Fog Lens

3M™ SecureFit™ Protective Eyewear 500



3M™ SecureFit™ 500 Series features a contemporary lens design coupled with adjustable ratcheting temples and Pressure Diffusion Temple (PDT) technology to help provide a more personalized fit. Utilizing a contemporary lens shape, this sporty new model also offers self-adjusting colored temples, a variety of lens tints and models with Scotchgard™ Protector Anti-fog coating.

SF501SGAF-BLK



SF501SGAF-BLK-FM



SF502SGAF-BLK



SF507SGAF-BLK



SF502SGAF-BLK-FM



SF507SGAF-BLK-FM



SF503SGAF-BLK



SF505SGAF-DGR



SF509AF-BLK



SF500-FOAM



Manufacturer Part Number	SKU	Treatment
SF501SGAF-BLK	7100238910	Clear, SGAF/AS
SF501SGAF-BLK-FM	7100238909	Clear w/Foam Gasket
SF502SGAF-BLK	7100239089	Gray, SGAF/AS
SF507SGAF-BLK	7100239091	Indoor/Outdoor Gray, SGAF/AS
SF502SGAF-BLK-FM	7100239195	Gray w/Foam Gasket
SF507SGAF-BLK-FM	7100239092	Indoor/Outdoor Gray w/Foam Gasket
SF503SGAF-BLK	7100239090	Amber, SGAF/AS
SF505SGAF-DGR	7100239191	Brown, SGAF/AS
SF509AF-BLK	7100239203	Silver Mirror, SAF/AS
SF500-FOAM	7100239114	Foam Gasket Accessory

3M™ SecureFit™ 3700 Series



Get over-the-glass protection with all day wearability with the 3M™ SecureFit™ 3700 Series. Featuring Pressure Diffusion Temple (PDT) Technology and an adjustable ratcheting temple, the SecureFit 3700 Series offers over-the-glass protection with a personalized fit.

SF3701SGAF-BLU
SF3701AS-BLU



SF3702SGAF-BLU
SF3702AS-BLU



SF3707SGAF-BLU
SF3707AS-BLU



SF3701XSGAF-BLU
SF3701XAS-BLU



SF3702XSGAF-BLU



SF3707XSGAF-BLU



Manufacturer Part Number	SKU	Treatment
SF3701SGAF-BLU	70071731965	Clear
SF3701AS-BLU	70071731973	Clear
SF3701AS-ORG	70071732997	Clear
SF3701XSGAF-BLU	70071732039	Clear
SF3701XAS-BLU	70071732047	Clear
SF3702XSGAF-BLU	70071732054	Gray
SF3702SGAF-BLU	70071731981	Gray
SF3702AS-BLU	70071731999	Gray
SF3707SGAF-BLU	70071732062	I/O Gray
SF3707AS-BLU	70071732070	I/O Gray
SF3701SGAF-ORG	70071732948	Clear
SF3707XSGAF-BLU	70071732179	I/O Gray
SF3701XSGAF-RED	70071733003	Clear

3M™ GoggleGear Splash Goggle with Clear Scotchgard™ Anti-Fog Lens



The 3M™ GoggleGear Splash Goggle with Clear Scotchgard™ Anti-Fog Lens help keep lenses clear, in steamy and wet environments. Featuring a low-profile design with an adjustable strap and indirect ventilation. Meets the Impact-Rated Protector requirement of the ANSI-ISEA Z87.1-2020 Standard.

GG501SGAF




GG500-PI



Manufacturer Part Number	SKU	Treatment
GG501SGAF	70071674967	Clear Scotchgard™ Anti-Fog Lens, Black/Red
GG500-PI	70071675055	500 Series Lens Prescription Insert
GG6001SGAF-GRN	7100191925	Clear Scotchgard™ Anti-Fog Lens
GG6001SGAF-BLK	7100191924	Clear Scotchgard™ Anti-Fog Lens
GG2891-SGAF	7010386529	Goggle Vent Clear Scotchgard™ Anti-Fog Lens

Head and Face Protection



Safeguard yourself.

3M incorporates the needs of industries to help design and produce hard hats, faceshields, and combination systems to deliver protection, comfort, and performance to help meet the needs of your job.

Hard Hats

3M™ H-700 Series Hard Hat

The 3M™ H-701R-UV Hard Hat is a protective hard hat with comfortable 4-point ratchet suspension, standard brow pad and Uvicator™ Sensor.

Manufacturer Part Number	SKU	Description
H-701R-UV	7000053152	White
H-701V-UV	7000053153	White – Vented
H-702R-UV	7000128173	Yellow
H-702V-UV	70000128177	Yellow – Vented
H-707R-UV	7100046566	Hi-Viz Orange
H-707V-UV	7010385061	Hi-Viz Orange– Vented



3M™ Full Brim H-800 Series Hard Hats

Help give your workers an excellent blend of comfort, style, and safety with 3M™ Full Brim Hard Hats. The tough, durable shell and adjustable suspension system work together to help absorb the impact of small falling objects and help protect workers from bumping into fixed objects. The Suspension sits lower on the head to help reduce pressure and increase security. Uvicator™ sensor lets wearer know when to replace hard hat due to UV exposure.

Manufacturer Part Number	SKU	Description
H-801R-UV	7000053179	White
H-801V-UV	7000144986	White – Vented
H-802R-UV	7000144976	Yellow
H-802V-UV	7000144987	Yellow – Vented
H-807R-UV	7000144981	Hi-Viz Orange



3M™ SecureFit™ X5000 Series Safety Helmets

The 3M™ SecureFit™ Safety Helmet X5000 provides comfort and security for workers in a variety of situations because it features a climbing helmet-inspired design that meets occupational safety requirements, works with a variety of 3M faceshields, earmuffs and other accessories, and the suspension incorporates exclusive 3M™ patented Pressure Diffusion technology.

Manufacturer Part Number	SKU	Description
X5001VX-ANSI	7100175562	White-vented with reflective
X5001X-ANSI	7100175554	White



Faceshields

3M™ PELTOR™ Clear Polycarbonate V2C-10P*

Brimless, lightweight clear polycarbonate visor helps provide high impact face protection. Must be used with hard hat. Faceshield snaps into 3M™ PELTOR™ Hard Hat Adapter P3EV/2 or 3M™ PELTOR™ Cap-Mounted Earmuffs.

Manufacturer Part Number	SKU
V2C-10P	7000103812



3M™ PELTOR™ Clear Acetate Faceshield V2A-10P*

Brimless, lightweight clear acetate visor helps provide face protection from splash and other debris. Must be used with hard hat. Faceshield snaps into 3M™ PELTOR™ Hard Hat Adapter P3EV/2 or 3M™ PELTOR™ Cap-Mounted Earmuffs.

Manufacturer Part Number	SKU
V2A-10P	7000103810



3M™ PELTOR™ Clear Acetate MultiVisor Faceshield System, V4D-10P, with Anti-Fog Coating, Lightweight*

Lightweight system with excellent ventilation and face protection features an anti-fog coating system that can be used with a variety of hard hats or with 3M™ PELTOR™ Muffs.

Manufacturer Part Number	SKU
V4D-10P	7000103816



*These faceshields are approved with H-700 model 3M hard hats only.

3M™ W Series Face Shields and Visors

For workers requiring face protection, the 3M™ W-Series Faceshields offer optical clarity and high-performance durability in unpredictable environments that involve exposure to impact hazards and flying debris.

Peak performance where it matters most

Helping protect your workers and elevating their comfort and safety is our number one priority. That’s why our personal protective equipment features tough materials and a construction that is suitable in harsh environments.

No hassles for workers with glasses

Protective headgear requires a comprehensive approach to safety that delivers optimal comfort for your workers. Protective eyewear fits easily inside our W-Series Faceshields so that your crewmembers can wear safety glasses comfortably and without hassle.

Face protection when you need it

Knowing that every minute counts on the job, our faceshield face protectors combine ease and strength without sacrificing safety. These face protectors mount easily and securely onto your 3M hard hat or headgear system—no tools, snaps, cams.

	Manufacturer Part Number	SKU
	H18	7000002291
	H24M	7000002292
	WCP96	7000052753
	WP96	7000002339

3M Scott Fire & Safety



**Rugged,
dependable
SCBA
protection.**

The 3M™ Scott™ Air-Pak™ SCBA offers proven, trusted performance to help get the job done safely.

3M™ Scott™ ELSA Emergency Escape Breathing Device-N

The 3M™ Scott™ ELSA EEBD-N respirator enables workers to escape from certain toxic environments, even in atmospheres immediately dangerous to life or health (IDLH). Designed with wearers in mind, the respirator is fully enclosed in a chemical-resistant PVC carry bag to keep it clean and free of insects and debris, and ready for use. The clear hood with patent-pending neck seal fits all wearers, and pulls on with no additional steps to secure, making it easy to train and use properly. The cost effective 3M™ Scott™ ELSA EEBD-N system fits into standard wall cases, has indefinite shelf life, and comes with a 3 year warranty. The respirator is available with 5-, 10- or 15-minutes of air to enable choices for different escape routes. The 10 and 15 minute variants meet SOLAS Chapter II-2, Part D requirements.



3M™ Scott™ Industrial Self-Contained Breathing Apparatus (ISCBA)

Designed for quick and easy use, the ISCBA provides IDLH-level respiratory protection in non-fire environments. The ISCBA features a simple, dependable single stage pressure reducer combined with the 3M™ Scott™ E-Z Flo mask-mounted regulator with first breath activation.

The ISCBA has a sturdy wire-formed back-frame with the option of a nylon or Kevlar® harness. It is available in 2216 psig low-pressure or 4500 psig high-pressure models, both with an option for a dual-port reducer and extended duration airline.



3M™ Scott™ AV-632 Bayonet Adapter

We've made it easy and intuitive to securely attach 3M filters and cartridges to your existing 3M Scott facepieces.

- Enable facepieces for use in a variety of applications
- Attaches with a simple, quick quarter turn
- Consistent attachment simplifies training across multiple applications
- Approved for use with 3M™ Scott™ AV-3000 SureSeal Facepiece and 3M™ Scott™ AV-3000 HT Facepiece



▶ 3M™ Particulate Filters

Filters particulates (e.g., dust, mists, fumes, fibers and biological particles, including mold spores and particles containing bacteria and viruses). Some filters also have nuisance-level gas and vapor capabilities.



▶ 3M™ Gas and Vapor Cartridges

Various cartridges are available to filter a variety of gases and vapors found in workplaces.



▶ 3M™ Combination Cartridges/Filters

Combines gas and vapor protection with a built-in particulate filter. As with gas and vapor cartridges, various cartridges are available for the specific hazard in the workplace.

3M™ Scott™ AV-3000 SureSeal Facepiece

Key Specifications

- ▶ Reverse reflex faceseal.
- ▶ Kevlar®, polyester or rubber head harness.
- ▶ Positioning tab (Kevlar® and Polyester).
- ▶ Wide, low-profile PPE interface.

Head harness sizes have been optimized to help prevent bunching and discomfort under helmets and hard hats.

Positioning tab (Kevlar® and Polyester versions) for proper positioning and quick donning.

Facepiece contains no natural rubber latex to help reduce or eliminate allergic reactions.

Buckles are strategically positioned to not interfere with head suspension in helmets and hard hats.

This mounting seal provides a wide, low-profile landing area for reliable PPE interface.

Reverse reflex technology offers a flexible U-shaped design for comfort and dependability.

Approved Configurations



AP75i SCBA



Ska-Pak AT Respirator

Did you know?

TOP ⬆️ DOWN
CONVERTIBILITY



- ▶ Single facepiece for multiple applications
- ▶ Helps reduce fit-testing, cost and training
- ▶ Lower total cost of ownership

Hearing Protection

WARNING

These hearing protectors help reduce exposure to hazardous noise and other loud sounds. Misuse or failure to wear hearing protectors at all times that you are exposed to noise may result in hearing loss or injury. For correct use, consult supervisor and User Instructions, or call 3M PSD Technical Service in the USA at 1-800-665-2942.

WARNING

U.S. EPA specifies the NRR as the measure of hearing protector noise reduction. However, 3M makes no warranties as to the suitability of the NRR for this purpose. 3M strongly recommends personal fit testing of hearing protectors. Research suggests that users may receive less noise reduction than indicated by the attenuation label value(s) on the packaging due to variation in fit, fitting skill, and motivation of the user. Refer to applicable regulations or guidance on how to adjust attenuation label values. It is recommended that the NRR be reduced by 50% to better estimate typical protection.

Eye Protection

WARNING

These eye or face protection products help provide limited eye and face protection. Misuse or failure to follow warning and instruction may result in serious potential injury, including blindness or death. For proper use, selection and applications against flying particles, optical radiation and/or splash see supervisor, read User Instructions and warning on the package or call 3M PSD Technical Service in the USA at 1-800-243-4630. In Canada, call 1-800-267-4414. 3M PSD products are for occupational use only.

Head Protection

WARNING

3M Head and Face Products provide limited protection only. Misuse or failure to follow warnings and User Instructions may result in serious personal injury or death. For proper use, see supervisor, User Instructions, or call 3M Personal Safety Division Technical Assistance at 800-243-4630.

Fall Protection

WARNING

Compliant fall protection and emergency rescue systems help prevent serious injuries associated with fall events. Users must read and understand the User Instructions provided with the product, and must be properly trained by their employers in the safe use of these systems before using them, per OSHA 1910.140 and 1926.503 or applicable local standards. Misuse or failure to follow warnings and instructions may result in serious personal injury or death. For proper use, see supervisor, User Instructions, or call 800-328-6146 (Opt. 1).

Respiratory Protection

WARNING

These respirators help to protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of applicable jurisdiction, as appropriate. Improper use may result in sickness or death. For correct use, see supervisor and User Instructions, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.

3M Scott Fire and Safety

WARNING

These respirators help to protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of applicable jurisdiction, as appropriate. Improper use may result in sickness or death. For correct use, see supervisor and User Instructions, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.



Personal Safety Division
3M Company

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

Technical Assistance 1-800-243-4630
Customer Service 1-800-328-1667
Fall Protection Product Support 1-800-328-6146

3M.com/ConstructionSafety

3M PSD products are occupational use only.

3M, 3M Science, Applied to Life., E-A-R, E-A-Rsoft, UltraFit, NEX, Exofit, DBI-Sala, Protecta, Nano-Lok, Ultra-Lok, Rebel, Scott, PELTOR, Optime, Aura, Powerflo, Cool Flow, Versaflo, Speedglas, SecureFit, Scotchgard, STRATA, LIFTech, Revolver, EZ-Link, Delta, Sealed-Blok, Saflok, Rollgliss, Dyneema, Cool Flow, Adflo, WS, Air-Pak and Uvicor are trademarks of 3M. Used under license by 3M subsidiaries and affiliates. © 3M 2021. All rights reserved. Please recycle. Printed in USA.
Kevlar® is a registered trademarks of E.I. du Pont de Nemours and Company.
The Bluetooth word mark is a registered trademark owned by Bluetooth SIG, Inc. and any use of such marks by 3M is under license.
All other trademarks are property of their respective owners.