



3M™ Carbon Fibre Cylinders for 3M™ Scott Safety SCBA & Modulair Airline Trolley

Description

3M™ Scott Safety's Carbon Fibre Cylinders provide a lightweight solution for containing the air required by 3M™ Scott Safety Breathing Apparatus.

The reduction in weight lowers the user burden leading to more effective air use and less strain on the wearer.

- Constructed of an aluminium alloy inner shell and overwrapped entirely with carbon-fibre, fibreglass and epoxy resin.
- Available with right angle valve (RAV) or T Valve; the valves are nickel plated naval brass
- 9L 300 Bar Carbon Cylinder
- Supplied empty

Applications

Suitable for 3M™ Scott Safety Self Contained Breathing Apparatus (SCBA) and 3M™ Scott Safety Modulair Airline Trolley.

Standards

The 3M™ Scott Safety cylinders conform to EN 12245.

Maintenance & Cleaning

3M™ Scott Safety recommends that these basic regular maintenance procedures be followed for all composite cylinders:

- Ensure lubricants, if used, and components are compatible with both the cylinder and the gas mixture
- Keep the inside of the cylinder free from moisture, oil, dirt and other contaminants.
- Avoid completely discharging your cylinder
- Never artificially heat your cylinder
- Never remove, obscure or alter cylinder labels or markings
- Never use corrosive, caustic or acidic paint strippers or solvents to remove paint.
- Never repaint the cylinder with paints that require curing at elevated temperatures.
- Do not fill cylinder if damaged



Right Angle Valve Cylinder

T-Valve Cylinder

Periodic Inspection and Testing

Cylinders shall be subjected to periodic inspection and testing by an approved test station according to the requirements of AS 2030.1-2009.

Storage

The cylinder must be stored in a dry, cool, clean place free from acids, oils, grease, or highly combustible materials. Store away from direct heat and sunlight; storage temperature should not exceed -10°C to +40°C. Do not store the cylinder in a place where welding operations are likely to take place.

Service/Training

Users need to be trained in the safe operation of this equipment. Routine checks must be carried out in accordance with the user instructions. Cleaning should also only be carried out as specified in the user instructions.

For training requirements please contact 3M Training Department on Phone: 1800 445 867 or Email: anzfallprotectiontraining@mmm.com

All servicing must be carried out by trained personnel who have been trained and are deemed competent by the manufacturer and hold a current 3M Scott Safety SCBA technician's certificate.

For Annual SCBA Servicing requirements please contact 3M Scott Fire & Safety Service department on Phone: 131 772 or Email: scbaservice@mmm.com

Disposal

Empty cylinders should be treated as special waste and disposed of according to local and state guidelines.

Cylinder Capacity

3M Code	Model #	Water Volume (Litres)	Charging Pressure (Bar)	Free Air Volume (Litres)	Nominal Duration (Min)	Outside Diameter (mm)	Overall Length (mm)	Empty Weight (size)	Standard Thread (size)
NT070008692	1127413TNZ	9.0	300	2430	61	174	556	4.8	M18x1.5 C-6h
AT010787961	1127413RAVNZ	9.0	300	2430	61	174	556	4.8	M18x1.5 C-6h


Cylinder Label Specifications

1. Manufacturer's name
2. The design specification (eg. EN 12245)
3. The cylinder serial number
4. Date (month & year) of first hydrostatic pressure test
5. Inspector's mark
6. Filling pressure
7. Test pressure
8. Water capacity in litres
9. Empty weight of cylinder
10. The aluminium alloy of the liner
11. Cylinder thread identity
12. Luxfer part number
13. Design life
14. Safety information
15. Dates of hydrostatic pressure re-tests

Duration is nominal and based on an average wearer consumption rate of 40 litres and are for fully charged cylinders.

Total duration for the apparatus is calculated from the following formula:

Total Duration = Cylinder Free air capacity/average wearer consumption rate



3M Australia Pty Ltd
Personal Safety Division
 Bldg A, 1 Rivett Road
 North Ryde NSW 2113
 TechAssist Helpline: 1800 024 464
 Customer Service: 1300 363 565
 Email: techassist@mmm.com
 Web: www.3M.com/au/ppesafety

3M New Zealand Ltd
Personal Safety Division
 94 Apollo Drive, Rosedale
 Auckland 0632
 TechAssist Helpline: 0800 364 357
 Customer Service: 0800 252 627
 Email: techassist@mmm.com
 Web: www.3M.com/nz/ppesafety

3M is a trademark of 3M Company.
 Please recycle. Printed in Australia.
 © 3M 2019. All rights reserved.
 AV011474580



Specifications

Carbon Fibre Cylinders	
Liner	Lightweight aluminium liner
Overwrap	High performance carbon fibre overwrap in epoxy resin matrix
Protective Layer	High strength fibreglass reinforced plastic (FRP)
Shipping Dimensions	Height: 0.2 m Depth: 0.2 m Width: 0.650 m
Shipping Volume	9 L
Weight	9L = 10 kg

Ordering Information

3M Code	Model#	Description
AT010787961	1127413RAVNZ	9L 300 Bar Carbon Fibre Cylinder - Right Angle Valve (RAV)
NT070008692	1127413TNZ	9L 300 Bar Carbon Fibre Cylinder - T Valve (T)

Important Notice

To the extent permitted by law, 3M shall not be liable for any loss or damage including any loss of business, loss of profits, or for any indirect, special, incidental or consequential loss or damage arising from reliance upon any information herein provided by 3M. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence.