

# 3M™ Polyurethane Protective Tape 8671/8671HS

## Technical Data Sheet

### Product Description

3M™ Polyurethane Protective Tape 8671 is made from an abrasion-resistant polyurethane elastomer that resists punctures, tearing, abrasion and erosion. It is formulated for resistance to ultraviolet light. 3M 8671 tape provides a simple, easy method of protecting a surface from corrosion, abrasion and minor impact damage. 3M 8671 tape is constructed with a long-aging, solvent-resistant, pressure-sensitive acrylic adhesive that is protected with an easy to release polyethylene liner. Also available in high shear adhesive.

### Typical Physical Properties and Performance Characteristics

1. The following technical information and data should be considered repetitive of typical only and should not be used for specification purposes.
2. ASTM = American Society of Testing and Materials.
3. Metric values are listed in parenthesis.

### Dimensions

<b>Approximate applied Thickness*</b>	0.012 inch (0.30 mm) Film 0.002 inch (0.05 mm) Adhesive Total Thickness 0.014 (0.35 mm)
<b>Standard Roll Length</b>	36 yd (32.9 m)
<b>Available Widths</b>	Minimum ½ inch Maximum 24 inches (1.25 cm to 61 cm)
<b>Approximate Weight*</b>	0.81 lb/yd <sup>2</sup> (439 g/m <sup>2</sup> )

\*Excludes the poly liner that is removed from the tape prior to application.

### Typical Physical Properties and Performance Characteristics:

Property	Test Method	Units U.S. (SI)	Typical Value
Tensile Strength @ Break	ASTM D882	lb/in (N/100 mm)	80 (1,401)
Hardness	ASTM D2240	Shore A	80
Elongation % @ Break	ASTM D882	%	500
Peel Adhesion @ 70°F (21°C) to: Anodized, Alclad Aluminum Glossy Polyurethane Paint Mil-P-27733 Epoxy Primer 304 Brite # 7 SS Steel Panel	ASTM D-1000, 24 hr Dwell	oz/in (N/100 mm)	100 (110) 52 (57) 90 (99) 60 (66)
Max. Service Temperature		°F (°C)	180 (82°C)

## General Information

- 3M™ Polyurethane Protective Tape has weather resistance properties and has been used to isolate and protect substrates from environmental damage and corrosive elements.
- Polyurethane Protective Tape may be painted per 3M Technical Bulletin, Polyurethane Protective Tape, Painting instructions

## Shipping and Storage

No special/hazardous labeling or packaging required and no regulations for air, ground or water shipment for this product.

Keep film in clean area, away from excessive moisture and out of direct sunlight. Store rolls in the shipping carton. Return partially used rolls to shipping carton.

Shelf Life: Two (2) years from date of manufacture or as expressly certified by 3M.

## Additional Information

In the U.S. call toll free 1-800-235-2376, or fax 1-800-435-3082 or 651-737-2171. For U.S. Military, call 1-866-556-5714. If you are outside of the U.S., please contact your nearest 3M representative.

*These products were manufactured under a 3M Quality Management System registered to the AS9100 standard*

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information. **Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. **Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Automotive & Aerospace Solutions Division  
3M Center  
St. Paul, MN 55144-1000  
Phone 1-800-328-1684  
Web [www.3M.com/aerospace](http://www.3M.com/aerospace)

8671/8671HS  
Issue date: 9/2021

3M is a trademark of 3M Company  
© 3M 2021. All rights reserved.