

Commercial Solutions Division

3M™ Scotchcal™ Photoluminescent Film

Series VP1587

Product Description

3M™ Scotchcal™ Photoluminescent Film Series VP1587 is a dimensionally stable, durable, multi-layer film which can be electrocut, hand cut, cold and hot kiss cut or screen printed to produce interior 'glow in the dark' signs and markings, including safety signage in buildings, ships and trains.

Product Line VP1587-30
VP1587-50
VP1587-180

light yellow-green, opaque, glossy, permanent adhesive.

VP1587-50 and VP1587-180 are certified as marine equipment according to Marine Equipment Directive 2014/90/EU for the application as Low-location lighting systems (components only). The Mark of Conformity is affixed to the label of the packed material including the identification number of the notified body and the year in which the mark is affixed.



0736/2017

Product Characteristics

These are indicative values for unprocessed products. Contact your 3M representative for a custom specification.

Physical & Application

Material	cast vinyl	
Surface finish	glossy	
Thickness (film)	200 µm (0.2 mm)	
Notice!	film plus adhesive	
Adhesive type	solvent acrylic; pressure-sensitive	
Adhesive appearance	grey	
Liner	paper	
Adhesion	see notice below	FTM 1: 180° peel, substrate: glass; cond: 24 h 23°C/50%RH
	works on typical substrates in the market of VP1587 without delamination in use	
Application method	dry only!	
Applied shrinkage	< 0.8 mm	FTM 14
Application temperature (minimum air and substrate)	+10°C to +35°C	for flat surfaces
Service temperature (after application)	-34°C to +90°C	(not for extended periods of time at the extremes)
Surface type	flat to simple curved	
Substrate type	aluminium, glass, PMMA, PC*, ABS, paint	
	* Might require drying with heat before use	
Graphic removal	Removable with heat and/or chemicals from supported substrates.	
	No liability is given for ease or speed of removal of any graphic. Pay attention to adequate air and substrate temperature.	
Notice!	3M™ Citrus Base Cleaner is recommended for the removal of adhesive residue from substrates.	

The values above are the results of illustrative lab test measurements and shall not be considered as a commitment from 3M.

Storage	Shelf life	Use within two years from the date of manufacture on the sealed original box. Use within one year after opening the box.
	Storage conditions	+4°C to +40°C, out of sunlight, original container in clean and dry area.

The shelf life as defined above remains an indicative and maximum data, subject to many external and non-controllable factors. It may never be interpreted as warranty.

Flammability Flammability standards are different from country to country. Ask your local 3M contact for details, please.

Durability

The durabilities mentioned in the table below are the results of illustrative lab tests. The values show the best performance expected from these products, provided that the film will be processed and applied professionally according to 3M's recommendations.

The durability statements do not constitute warranties of quality, life and characteristics.

The durability of products is also influenced by:


- the type of substrate and thorough preparation of the surface (with 3M™ Surface Preparation System)
- application procedures
- environmental factors
- the method and the frequency of cleaning

Unprocessed film The following durability data are given for unprocessed film only!

Climatic zones Graphic durability is largely determined by the climate and the angle of exposure.

Exposure types

Vertical:



The face of the graphic is $\pm 10^\circ$ from vertical.

Interior:

Interior means an application inside a building without direct exposure to sunlight.

Vertical outdoor exposure

2 years

Notice!

Non-vertical applications will have a significant decrease in durability!

Interior application

10 years

Visit www.3mgraphics.com for getting more details about 3M's comprehensive graphic solutions.

Limitations of End Uses

3M specifically does not recommend or warrant the following uses, but please contact us to discuss your needs to recommend other products.

Graphics applied to

- flexible substrates incl. 3M™ Panagraphics™ III Wide Width Flexible Substrate and 3M™ Envision™ Flexible Substrate FS-1
- low surface energy substrates or substrates with low surface energy coating.
- other than flat or moderate curved/corrugated surfaces.
- painted or unpainted rough wallboards, gypsum boards and wallpapers.
- substrates with tendency of outgassing.
- surfaces that are not clean and smooth.
- surfaces with poor paint to substrate adhesion.

Graphic removal from

- signs or existing graphics that must remain intact.

Graphics subjected to

- gasoline vapours or spills.

Important Notice!

3M Commercial Solutions products are not tested against automotive manufacturer specifications!

Luminance Characteristic

The afterglow of photoluminescent film degrades with time once the charging light source is removed. This characteristic must be taken into account when designing and locating signs and markings.

The amount of afterglow visibility (luminance level) depends upon the observation conditions such as ambient light, observer, etc. Typical afterglow (luminance) values for photoluminescent film are [mcd/m²]:

Typical afterglow	VP1587-30		30 mcd/m ²
	VP1587-50	10 min:	50 mcd/m ²
	VP1587-180		180 mcd/m ²
	VP1587-30		6 mcd/m ²
	VP1587-50	60 min:	8 mcd/m ²
	VP1587-180		22 mcd/m ²

Graphics Manufacturing

Graphic protection can improve the appearance, performance and durability of printed graphics. Any printed graphic exposed to abrasive conditions (including vehicles), harsh cleaners or chemicals must include graphic protection in order to be warranted.

When to use an overprint clear or overlaminate

See instruction bulletin GPO 'graphic protection options' for further information about selection and use of protective overlaminates and printable clears.

[> Product Bulletin Graphic Protection Options <](#)

Shipping finished graphics

Flat, or rolled film side out on 130 mm (5 inch) or larger core. These methods help to prevent the liner from wrinkling or application tape, if used, from popping off.

Converting Information

Screen Printing

Formulations and processing conditions can affect ink durability. Refer to the 3M Product and Instruction Bulletins for your ink for limitations and proper usage. Graphic protection can improve the appearance, performance and durability of your graphic.

A clear coat also prevents chalking on unprinted films. Use equipment designed to handle high viscosity materials and make sure the coating is evenly applied to the specifications given in the clear's Instruction Bulletin.

Abrasion and Loss of Gloss

Abrasion damage and loss of gloss are not covered by any 3M warranty. This is considered normal wear and tear.

Application

See product bulletin ATR 'application tape recommendations' for information about selection and use of suitable application tapes for this product, please.

[> Product Bulletin Application Tape Recommendations <](#)

Refer to Instruction Bulletin 5.1 'select and prepare substrates for graphic application', for general application information.

[>Instruction Bulletin 5.1 'select and prepare substrates for graphic application'<](#)

Maintenance and Cleaning

Use a cleaner designed for high-quality painted surfaces. The cleaner must be wet, non-abrasive, without strong solvents, and have a pH value between 3 and 11 (neither strongly acidic nor strongly alkaline).

Refer to Instruction Bulletin 6.5 'storage, handling, maintenance and removal of films and sheetings', for general maintenance and cleaning information.

[>Instruction Bulletin 6.5 'Storage, Handling, Maintenance and Removal of Films and Sheetings'<](#)

Important Safety Remark

Application to glass

The application of coloured or printed film onto glass with sunlight exposure can lead to glass breakage through thermal expansion of the glass. The local conditions must be examined for the danger of glass break by uneven heat absorption through sun exposure. Type of glass (insulation glass, float glass, LSG, toughened safety glass, semi-tempered glass, etc.), glass dimension, joint condition, flexibility of the sealant, quality of the edge finishing, geographical orientation and partial shadow during sun exposure are the determining factors. Light colour designs and application on the outside of the window are to be preferred. A free non-applied framework of 4 mm around the entire window front can help to dissipate the absorbed warmth. According to common knowledge a thermal crack can occur at temperature differences of approx. +130°C (toughened safety glass), approx. +40°C (float glass) or approx. +110°C (semi-tempered glass). Coldest place is usually under the framework in the embedded joined window part, the warmest place is typically on the darkest place in the format. Because of the many above mentioned factors, glass breakage cannot be fully predicted, therefore 3M does not accept liability for glass breakage when using this film for window graphics.

Remarks

This bulletin provides technical information only.

Important notice All questions of warranty and liability relating to this product are governed by the terms and conditions of the sale, subject, where applicable, to the prevailing law.
Before using, the user must determine the suitability of the product for its required or intended use, and the user assumes all risk and liability whatsoever in connection therewith.
As outdoor graphics age, natural weathering occurs causing a gradual reduction in gloss, slight colour changes, some lifting of the graphic at the edges or around rivets, and ultimately a minor amount of cracking.

These changes are not evidence of product failure and are not covered by a 3M warranty.

Additional information Visit the web site of your local subsidiary at www.3Mgraphics.com for getting:

- more details about 3M™ MCS™ Warranty and 3M™ Performance Guarantee
- additional instruction bulletins
- a complete product overview about materials 3M is offering

Responsible for this technical bulletin:

3M Deutschland GmbH
Safety & Graphics Laboratory
Carl-Schurz-Str. 1
41453 Neuss, Germany

3M, Scotchcal, MCS and Panagraphics are trademarks of 3M Company. All other trademarks are the property of their respective owners.

The use of trademark signs and brand names in this bulletin is based upon US standards. These standards may vary from country to country outside the USA.



Commercial Solutions Division

3M United Kingdom PLC
Cain Road
Bracknell, RG12 8HT
UK
Tel: 01344 858000

Commercial Solutions Division

3M Ireland (Dublin)
The Iveagh Building
The Park, Carrickmines
Dublin 18, Ireland
Tel: 00 353 1 280 3555