


3M™ Bonding Solutions
for IoT Electronics

APPLICATION PROFILES



Electronics Bonding Applications by Device Category



A person is lying down, wearing large over-ear headphones and holding a smartphone in their right hand. They are also wearing a smartwatch on their left wrist. The background is a warm, orange-toned image of a person's face and upper body, suggesting a relaxed or sleep environment. The overall image has a soft, warm aesthetic with a monochromatic orange color scheme.

3M™ Bonding Solutions for IoT Electronics

Wearables/Hearables



SMARTWATCH

ELECTRONICS

Safe turns.

Even if most smartwatches use touch displays, users still find it convenient to scroll through menus using a “crown” on the side. This small and important part contains components that need to be bonded carefully. **3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White** provides a unique combination of optimal viscosity, high bonding strength and low temperature curing to help ensure careful assembly.

Smartwatch crown bonding.

High bonding strength and appropriate viscosity with 3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White.






TWS (TRUE WIRELESS STEREO)

ELECTRONICS

Small size. Strong resistance.

Wireless earphones are getting smaller and more sophisticated. That is why internal components need to be carefully assembled without coming apart over time. Both **3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6011LV** and **3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White** provide an ideal combination of resistance to chemicals, adhesion to plastics, good jetting performance, fast curing at low temperature, and a long pot life at room temperature.



Earphone assembly.

Reduce the risk of clogging jetting nozzle with 3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6011LV and 3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White.





TWS (TRUE WIRELESS STEREO)

ELECTRONICS

Stay charged.

Earphone chargers are essential to avoid running out of power while listening to your favorite music, binge watching the latest series or participating in your next virtual meeting. **3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6011LV** maintains excellent adhesion to difficult-to-bond substrates, including a variety of plastics, and can be dispensed precisely to avoid leaking on other parts.



Bond metal to plastic.

Maintain strong adhesion and precise dispensing with 3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6011LV.



SMARTWATCH

ELECTRONICS

Wear it tight.

Fabrics provide a stylish and comfortable fit for smartwatch bands but can be challenging to fasten without help.

To get a tighter grip, these materials are being combined with various plastics – but they need their own secure assembly.

3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White provides a combination of excellent bonding strength together with low temperature curing to help protect sensitive materials.



Simplify wristband assembly.

Excellent bonding strength with
3M™ Scotch-Weld™ One-Part
Epoxy Adhesive 6101 Off-White.





TWS (TRUE WIRELESS STEREO)

ELECTRONICS

Play on.

Foldable, over-the-ear headphones are convenient, comfortable, fashionable and provide great sound – the last thing you'd want is for them to fall apart!

3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White delivers strong, reliable bonds to difficult substrates like silicone, for long-term bonding performance and to help ensure a consistent, good fit fold after fold.



Strong, flexible, stable.

High bonding strength to silicone with 3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White.



3M™ Bonding Solutions for IoT Electronics

Smart Home





SMART SECURITY

ELECTRONICS

True security.

Safety and security means more than a clear feed, it means a reliable outdoor camera designed to last. **3M™ Scotch-Weld™**

One-Part Epoxy Adhesive 6101

Off-White rises to the challenge with a unique combination of strong bonds on rubber and TPU and high shear strength, designed to ensure a robust seal against water and weather. All of this helps keep the system in place, so it can help provide a sense of security for homeowners.



Ensure security.

Help keep your system in place with the high bonding strength of 3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White.



ELECTRONICS

On the button.

As a household item made to be used and washed daily, electric toothbrushes come with a unique set of design challenges.

3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White helps keep things water-tight with a strong bond between drastically different substrates, including aluminum and TPU, and is designed to effectively seal electronics to help improve water resistance.



Get a good seal.

High bonding strength to TPU and aluminum with 3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White.



3M™ Bonding Solutions for IoT Electronics

Other





ELECTRONICS

Power up.

Cell phone power adapters contain complex circuitry and components that require careful assembly to ensure a safe, reliable charge. **3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White** provides outstanding adhesion to difficult-to-bond substrates (including a variety of plastics), good jetting performance for small parts, and meets UL94 HB flammability requirements. Plus, you can save time and costs with a quick cure at low temperatures, and long-term stability at room temperature storage.



Strong, speedy adhesion.

Get a fast, precise bond with 3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White.



NOTEBOOK PCs

ELECTRONICS


Stable material. Strong adhesion.

Between virtual meetings, regular streaming and online shopping, keeping your laptop charged and working is vital.

3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White helps you power up with strong adhesion to difficult substrates (including many plastics used in power adapters), good jetting performance for small parts, fast curing times, and long-term stability – all while meeting UL94 HB flammability requirements.

Powered up.

Quick, accurate, effective adhesion with 3M™ Scotch-Weld™ Epoxy Adhesive 6101 Off-White.





DISPLAYS

ELECTRONICS

Eye catching displays.

Large displays can create beautiful, eye-catching images. **3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White** provides strong holding power with low temperature curing – helping ensure reliable bonding performance for large displays.



Display with confidence.

Bond large displays with
3M™ Scotch-Weld™ One-Part
Epoxy Adhesive 6101 Off-White.





OUTDOOR DEVICES

ELECTRONICS

Bonds as brave as you are.

Frigid mountaintops, rough mountain paths, deep beneath the ocean – sports cameras go where the action goes. With strong bonds and high temperature and impact resistance, **3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White** helps these hardworking cameras stay bonded and in place wherever your adventure may take you.

Weather the storm, capture the moment

Film everywhere with confidence with 3M™ Scotch-Weld™ One-Part Epoxy Adhesive 6101 Off-White.



Thank you.

For more information visit
3M.com/electronicsbonding

Safety Data Sheet: Consult Safety Data Sheet before use.

Regulatory: For regulatory information about this product, contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.** If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.



Electronics Device Bonding
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
1-800-362-3550 phone
1-877-369-2923 fax
www.3M.com/electronicbonding

3M is a trademark of 3M Company. ©3M 2021. All rights reserved. Issued: 10/21 16795HB 60-5005-0325-9