

3M Advanced Materials Division

3M™ Dyneon™ Ultra High Purity PFA FLEX 8515UHPZ

Features and Benefits

- Meets SEMI C90-1015
- Extremely low extractable impurities
- Improved ESCR (Stress Crack Resistance)
- Excellent chemical resistance
- Injection moldable
- Temperature capability up to 240°C

Typical Properties (Not for specification purposes)

Property	Units	Value
Melting Point [ISO 12086]	°C	294
Melt Index 372°C/5 kg [ISO 12086]	g/10 min	15
Specific Gravity @ 23°C [ISO 12086]	cm ³	2.14
Tensile Strength at Break @ 23°C [ISO 12086]	MPa (psi)	31 (4,500)
Elongation at Break @ 23°C [ISO 12086]	%	310
Flexural Modulus @ 23°C [ISO 178]	GPa	0.6
Hardness Shore D [ISO 868]		60
Limiting Oxygen Index (LOI) [ASTM D2863/Type IV/Proc.A]	%	>95

Product Description

3M™ Dyneon™ PFA FLEX 8515UHPZ is an excellent option for ultra high purity injection molded parts with enhanced stress crack resistance. This PFA combines the durability benefits from Dyneon's enhanced stress crack PFA architecture with a lower molecular weight polymer to support higher shear processing.

Ultra High Purity

3M™ Dyneon™ Ultra High Purity PFA "UHPZ" materials offer very low levels of extractable impurities making them an exceptional option for critical semiconductor liquid chemical components. Dyneon PFA UHPZ materials have been shown to meet low extractable levels required by SEMI C90-1015 for raw material pellets.

Stress Crack Resistance

3M™ Dyneon™ PFA FLEX UHPZ series have enhanced environmental stress crack resistance (ESCR) compared to our standard PFA grades. This can be particularly useful when parts are subjected to aggressive stress cracking agents such as fluorosurfactant solutions.

Processing Recommendations

3M™ Dyneon™ Ultra High Purity PFA can be processed using typical melt processing methods. Dyneon PFA FLEX 8515UHPZ is processed using methods including injection molding and extrusion. 'Hot end' temperatures for Dyneon PFA can be up to 370°C. These processing temperatures are for melting, pumping, and mold-forming - they should not be confused with use temperatures of finished articles.

Note: Data in this document are not for specification purposes.

ISO Registrations

3M™ Dyneon™ UHP PFA is manufactured at ISO 9001 and 14001 registered facilities.

Corrosion Resistant Tools

To avoid breakdown and contamination due to corrosion, processing equipment that contacts molten PFA or fumes should be made from highly corrosion resistant materials such as high-nickel alloys. In the case of lower wear elements, nickel plating may be used. In addition to longer process tool lifespan, use of corrosion resistant materials is a very important step to help reduce impurities introduced into the final parts during processing of the PFA.

Processing EHS

Hazardous off-gases are generated during hot processing of PFA resins. These gases must be managed via an appropriate exhaust fume management system. Such care is often required for areas where the materials are in a hot 'in-process' condition and also where molded articles cool. For additional information on safe processing for PFA consult the health/safety section on this data sheet, the material label, Safety Data Sheet (SDS), and industry guidance on safe handling of fluoropolymer materials.

Product Form and Packaging

3M™ Dyneon™ Ultra High Purity PFA are supplied in pellet form and packaged in 25 kg (55 lbs.) plastic bags 2 each inside a plastic container for a package unit of 50 kg (110 lbs).

Storage and Material Handling

3M™ Dyneon™ Ultra High Purity PFA shelf life has not been determined. Storage time has not been shown to have a material impact on PFA properties. It should be stored in a clean, dry place. Containers should only be opened in clean environments and should be tightly resealed and stored in a clean area away from contaminants. Static charge, such as those that can result from transport, may exacerbate the risk of contamination. PFA is hydrophobic and generally does not require drying. If ambient humidity is high, drying may be used to reduce the risk of water inclusion from condensation on pellet surfaces.

Safety/Toxicology

PFA is a fluoropolymer, so standard precautions observed with fluoropolymers should be followed. Read and follow all precautions and directions for use. Additional safe handling information can be found on the process safety section on this data sheet, the product label, Safety Data Sheet, and in published industry guides. General handling/processing precautions include, but are not limited to: (1) Processing and equipment cleaning only in well ventilated areas; (2) Do not smoke in areas contaminated with powder/residue from these products; (3) Avoid eye contact; (4) After handling these products wash any contacted skin with soap and water. Potential hazards, including evolution of toxic vapors, can exist when processing occurs under typical temperature conditions. Appropriate exhaust ventilation such as vapor extractor units should be installed above processing equipment. When cleaning processing equipment: do so under proper ventilation, use the lowest temperature possible and never use open flame as a heat source.

Customer Service

Europe

Dyneon GmbH
3M Advanced Materials Division
Carl-Schurz-Straße
41453 Neuss
Germany
Phone: +00 800 396 366 27
Fax: +00 800 396 366 39

USA

3M Advanced Materials Division
3M Center, 280-01W-03
St. Paul, MN 55144-1000
United States
Phone: 1 800 810 8499

Latin America

3M Brasil
Via Anhanguera km
110 Sumare
Sao Paulo CEP 13181-900
Brasil
Phone: 0800 0132333

3M Mexico
Santa Fe 190, Col. Santa Fe
Deleg. Alvaro Obregon
Mexico D.F., C.P. 01210
México
Phone: 0052 5552700 400
Ext 82935

Asia

3M Japan
6-7-29, Kita-Shinagawa
Shinagawa-ku
Tokyo 141-8684
Japan
Phone: 81 570 022 123

3M Korea
19F, 82, Uisadang-daero
Yeongdeungpo-gu, Seoul, 150-705
Korea
Phone: 82 2 3771 4027

3M Taiwan

6F, No.95, Sec. 2
Dunhua S. Rd.
Taipei 10682
Taiwan
Phone: 886 2 2704 9011

3M Thailand

150 Soi Chalongkrung 31
Ladkrabang Bangkok, 10520
Thailand
Phone: 66 2739 4803 9
Ext 2354

Please visit 3M.com/semifluidhandling or 3M.com/fluoropolymers for additional information.

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. User is solely responsible for evaluating third party intellectual property rights and for ensuring that user's use of 3M product does not violate any third party intellectual property rights. User is solely responsible for ensuring compliance of their products with all applicable regulations. Unless a different warranty is specifically stated in the applicable product literature or packaging insert, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OF NON-INFRINGEMENT OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.** If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damages arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

Technical Information: Technical information, recommendations, and other statements contained in this document or provided by 3M personnel are based on tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed. Such information is intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.



3M Advanced Materials Division
St. Paul, MN 55144
Phone 1-800-810-8499
Web www.3m.com/advancedmaterials

3M and Dyneon are trademarks of
3M Company. Used under license.
© 3M 2023. All rights reserved.
Issued: 02/2023