


**3M** Science.  
Applied to Life.™

# Industrial Maintenance and Repair Solutions

For every job,  
a solution.









# Keep your facility going — inside and out.

Every day, you're tasked with the critical job of keeping a large, complex operation running smoothly. That's why you insist on tools that help you get the job done right, world-class know-how to solve real-world challenges and products that perform as promised.

Rely on 3M Industrial Maintenance and Repair Solutions. Hundreds of products all in one place. Decades of expertise. Together, we can help you make sure all systems run smoothly and efficiently — one job, one solution at a time.



## Everything you need to get it all done.

3M Industrial Maintenance and Repair Solutions for:

 **Machines and Equipment**

 **Surfaces**

 **Cleaning and Disinfecting**

 **Electrical**

 **HVAC and Plumbing**

 **Metal Repair**





**Tackle your to-do list with  
a complete set of solutions  
to help maximize your day.**





## Machine and Equipment Maintenance and Repair

We've got the supplies you need to fix it, maintain it, protect it — quickly and reliably.

- Lubricate moving parts
- Remove rust
- Eliminate grease, tar and oil
- Contain drips
- Bonding and sealing

## Cleaning and Disinfecting

From everyday clean-up to less frequent deep cleans, our trusted products help you keep your facility clean and well maintained.

- Clean and disinfect hard non-porous surfaces
- Sweep dust and debris
- Clean windows and mirrors
- Remove marks, stains, overspray and adhesive

## HVAC and Plumbing

Keep operations flowing with solutions for your HVAC and plumbing jobs.

- Indoor and outdoor taping
- Connect and insulate conductor ends
- Cut ductwork and pipes
- Firestop HVAC and plumbing pipes

## Surface Repair, Maintenance and Protection

Make the most of your floors and walls, from improving traffic flow to making your facility safer and easier to navigate.

- Safety and lane marking
- Surface protection
- Hanging and attachment

## Electrical Maintenance and Repair

Maximize your efficiency with reliable solutions that help you keep the lights on and equipment running.

- Insulate and protect
- Connect low-voltage wiring
- Firestop cables and conduit
- Identify and secure cables and wires

## Metal Repair

Whatever kind of repair you're working with, we've got options to help you get it done right.

- Grind, bevel, cut and finish
- Surface preparation, coating and rust removal
- Replace rivets, screws, nuts/bolts and welds
- Worker health and safety solutions

Plus many more tasks — ask your 3M representative for details.

# Keep your facility going.

## Task

## Solution

### 1 Lobby and Common Areas

|                                       |                     |
|---------------------------------------|---------------------|
| Clean and strip hard floors           | Floor mops and pads |
| Protect floors in heavy traffic areas | Matting             |
| Mount signs permanently               | Foam tapes          |

### 2 Restrooms

|                           |                         |
|---------------------------|-------------------------|
| Clean and disinfect       | Cleaning chemicals      |
| Daily surface care        | Cleaners and degreasers |
| Clean fixtures            | Handheld cleaning tools |
| Mount signs permanently   | Foam tapes              |
| Clean windows and mirrors | Glass cleaners          |

### 3 Cafeteria/Break Room

|                           |                           |
|---------------------------|---------------------------|
| Make quick work of dishes | Handheld cleaning tools   |
| Make clean-ups easier     | Scouring pads and sponges |
| Sweep, scrub and mop      | Floor care products       |
| Hang things permanently   | Foam tapes                |

### 4 Safety Supply Room

|                                     |  |
|-------------------------------------|--|
| Mark hazards                        | Hazard and safety tapes  |
| Help prevent workplace injuries     | Personal Protective Equipment: <ul style="list-style-type: none"> <li>• Head and face protection</li> <li>• Protective eyewear</li> <li>• Earplugs and earmuffs</li> <li>• Disposable and reusable respirators</li> <li>• Fall protection</li> </ul> |
| Help prevent slip and trip injuries | Slip-resistant tapes and treads  |
| Hang safety and wayfinding signage  | Foam tapes   |

### 5 Outdoor Maintenance and Facility Grounds

|  |                               |
|--|-------------------------------|
| Seal and fill gaps                           | Adhesive sealants             |
| Insulate, pad and seal electrical components | Mastic tapes                  |
| Safely secure wires                          | Wire connectors               |
| Clean windows and mirrors                    | Glass cleaners                |
| Help keep workers safe                       | Personal protective equipment |
| Manage leaks and spills                      | Petroleum sorbents            |
| Mount things permanently                     | Foam tapes                    |

### 6 Janitorial Closet

|  |   |
|--|---|
| Permanently bond lightweight materials | Aerosol adhesives                           |
| Clean and disinfect everyday surfaces  | Cleaning chemicals, sponges, mops and tools |
| Remove gunk and grime and degreasers   | General and specialty cleaners; hand pads   |


### 7 Maintenance Shop

|                                    |  |
|------------------------------------|--|
| Sand, cut, grind and finish        | Abrasives, hand pads and cut-off wheels                    |
| Maintain electrical components     | Electrical supplies: tapes, connectors, gloves, cable ties |
| Patch and paint drywall            | Compound, plates, and masking tape                         |
| Help keep workers safe             | Personal protective equipment                              |
| Manage leaks and spills            | Maintenance sorbents                                       |
| Make quick fixes                   | Duct tapes   |
| Protect surfaces and ease clean-up | Self-stick liquid protection fabric                        |

### 8 HVAC/Power Generation

|   |                              |
|---|------------------------------|
| Repair metal                              | Cut-off and grinding wheels  |
| Bond metals and plastics                  | Contact adhesives            |
| Attach removable access panels            | Reclosable fasteners         |
| Prevent injuries on the ground            | Fall protection for tools    |
| Repair duct work                          | Foil, HVAC and seaming tapes |
| Keep fire, smoke and fumes from spreading | Fire protection              |

See map on next page.



## Task

## Solution

### 9 Loading Dock/Shipping and Receiving

|                                     |                                 |
|-------------------------------------|---------------------------------|
| Help prevent slips, trips and falls | Slip-resistant tapes and treads |
| Increase worker comfort             | Cushion matting                 |
| Make packages tamper-evident        | Security use tapes              |
| Bundle and reinforce                | High strength tapes             |
| Secure pallets                      | Stretchable tape                |
| Clearly mark hazards                | Safety tapes                    |
| Mount things temporarily            | Repositionable tapes            |
| Increase visibility                 | Reflective tapes                |

### 10 Engineering Lab

|                             |                               |
|-----------------------------|-------------------------------|
| Keep clean areas clean      | Sticky mats                   |
| Label beakers and equipment | Masking tape                  |
| Help keep workers safe      | Personal protective equipment |

### 11 Production Floor and Equipment; Warehouse

|   |                                       |
|---|---------------------------------------|
| Lubricate moving parts                          | Lubricants                            |
| Seal threaded assemblies                        | Threadlockers                         |
| Fix rusty fasteners or frozen threaded parts    | Penetrants                            |
| Remove grease, oil, tar or adhesive             | Industrial cleaner or brake cleaner   |
| Clean stainless steel equipment                 | Stainless steel cleaner and protector |
| Bond rubber gaskets to metal surfaces           | Rubber and gasket adhesive            |
| Mark floors and walls for visibility and safety | Marking and safety tapes              |
| Manage leaks and spills                         | Maintenance sorbents                  |
| Keep fire, smoke and fumes from spreading       | Fire protection                       |
| Clean and disinfect surfaces                    | Disinfecting wipes                    |
| Reduce worker fatigue                           | Cushion matting                       |
| Keep clean areas clean                          | Sticky mats                           |
| Talk and be heard in noisy areas                | Protective communication              |
| Increase visibility                             | Reflective tapes                      |



# Products that work as hard as you do.

Elevate your crew's productivity with trusted 3M products in these categories:

## Abrasive Systems

Abrasive Belts, Discs and Wheels;  
Hand Finishing; Scotch-Brite™  
Nonwoven Abrasives; Random Orbital  
Sanding; Right Angle; Roloc™ Systems;  
Specialty Abrasives

## Adhesives and Sealants

Aerosol Adhesives; Hot Melt Adhesives;  
Instant and Anaerobic Adhesives;  
Solvent-Based Adhesives; Contact  
Adhesives; Structural Adhesives;  
Adhesive Sealants; Applicators

## Electrical Products

Scotch™ Electrical Tapes; Mastics,  
Coatings and Cleaners; Wire and  
Cable Connectors; Wire and Cable  
Accessories; Work Gloves

## Facility Maintenance

Lubricants; Matting; Handheld  
Cleaning Tools; Sponges and Pads;  
Cloths and Wipes; Floor Care  
Products; Cleaning Chemicals

## Fire Protection

Fire Barrier Sealants; Through-  
Penetration Products; Fire Barrier Tapes

## Painting and Coating

Prep; Spray Equipment; Finishing

## Personal Protective Equipment

Eye Protection; Head and Face  
Protection; Hearing Protection;  
Protective Hearing and Communication;  
Respiratory Protection; Welding Safety;  
Safety Clothing; Fall Protection

## Reclosable Fasteners

3M™ Dual Lock™ Reclosable Fasteners;  
Hook and Loop

## Sorbents

Chemical; Maintenance; Petroleum

## Tapes

Masking; Duct; Foil, HVAC and  
Seaming; Marking and Safety;  
Foam and Specialty; Repositionable;  
Packaging; Adhesive Transfer; Double  
Coated; Treads

## Everything you need to get it all done.

When you've got the world's largest array of trusted maintenance, repair, cleaning and safety products, there's no task too big, no process too complex. Together, we take on what each day brings, break it down and get things done. All your ingenuity. All our technology. All working together.

**Rely on 3M. Ask your 3M representative.**



3M Australia Pty Ltd  
Bld A, 1 Rivett Road  
North Ryde NSW 2113  
Phone: 136 136  
[www.3M.com.au](http://www.3M.com.au)

3M New Zealand Limited  
94 Apollo Drive  
Rosedale, Auckland 0632  
Customer Services: 0800 252 627  
[www.3M.co.nz](http://www.3M.co.nz)

Please recycle. © 3M 2022.  
All rights reserved. 3M, Command, Post-it,  
Roloc, Scotch, Scotch-Brite and Dual Lock are  
trademarks of 3M.