

3M™ Fire Protection Products
3M™ Fire Barrier Self-Locking Pillows



Fast, Simple & Secure Re-enterable Firestop

Self-contained, intumescent pillows designed to firestop a wide variety of through-penetrations.

3M™ Fire Barrier Self-Locking Pillows help deliver code-compliant fire barrier protection in a variety of new and retrofit through-penetration firestop systems. Quick to install and remove, self-locking and re-usable pillows easily lock in place creating an efficient and affordable firestop. An ideal solution when re-enterability is needed.



3M™ Fire Barrier Self-Locking Pillows

Easy-to-install 3M™ Fire Barrier Self-Locking Pillows help control the spread of fire, smoke and toxic gasses before, during and after exposure to a fire. These self-contained, intumescent pillows are great for use in a wide variety of new and retrofit through-penetration firestops:

- ✓ **Cable trays**
- ✓ **Conduit**
- ✓ **Blank openings**

These simple-to-use pillows feature a unique hook-and-loop interlocking strip that allows quick and secure installation in floors or walls. Pillows can also be easily field cut, removed or repositioned if needed. This product versatility allows the proper combination of pillows to fit securely and conform to most openings. 3M™ Fire Barrier Self-Locking Pillow Systems achieve up to 3-hour fire ratings when tested in accordance with ASTM E 814 (UL 1479). Pillow systems can achieve L-Rating (air leakage) when installed with 3M™ Fire Barrier Moldable Putty+.

Easy-To-Use



Stack and Compress
Align interlocking strips and compress to lock pillows together. This is one of several ways pillows can be easily prepared for installation.

Field Cutting (optional)



Step 1: Cut
Self-locking pillows can be field cut lengthwise if needed.



Step 2: Tape
Reseal self-locking pillow with two-inch wide packaging tape.



Step 3: Ready for Installation
Re-sealed self-locking pillow ready for installation.

Ordering Information

Product	Size	UPC	3M Stock No.	Units/Case
3M™ Fire Barrier Self-Locking Pillow	Small (2"x 4"x 9")	500-51115-16578-3	98-0400-5472-2	24
	Medium (2"x 6"x 9")	500-51115-16579-0	98-0400-5473-0	16
	Large (3"x 6"x 9")	500-51115-16580-6	98-0400-5474-8	20



LISTED

FILL, VOID OR CAVITY
90G9



CLASSIFIED
UL
FILL, VOID OR CAVITY
FOR USE IN THROUGH-PENETRATION
FIRESTOP SYSTEMS
SEE UL FIRE RESISTANCE DIRECTORY
90G9



APPROVED

SUBJECT TO THE CONDITIONS OF APPROVAL
AS A WALL & FLOOR PENETRATION
FIRESTOP WHEN INSTALLED AS DESCRIBED
IN THE CURRENT EDITION OF THE FMRC
APPROVAL GUIDE

Important Notice to User:

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty and Limited Remedy: 3M warrants that each 3M Fire Protection Product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.



Building and Commercial Services Division
3M Center
Building 223-2N-21
St. Paul, MN 55144-1000
800-328-1687
www.3M.com/firestop

© 3M 2012. All rights reserved.
Printed in U.S.A. 98-0213-4320-1 REV B Please recycle.

3M is a trademark of 3M. Used under license in Canada. All other trademarks are the property of their respective owners.



At a glance...

- Up to 3-hour UL Listings per ASTM E 814 (system dependent)
- Easy installation helps save time and labor
- Optional field cutting, if needed
- Easy to remove or re-enter
- Passes hose stream test without additional support
- Achieves as low as 2 CFM/sq. ft. L-Rating (system dependent)
- Listings for blank or filled openings in gypsum wallboard or concrete
- 3M logo helps provide quality assurance with instant product identification
- Three pillow sizes to accommodate various opening requirements

