

**3M** Science.  
Applied to Life.™



**Safety backed  
by science.**

**3M™ SecureFit™  
Protective Eyewear**

# Performance. Style. Comfort.

## 3M™ SecureFit™ Protective Eyewear

Protecting your vision on the job is important. But it doesn't have to mean sacrificing style or comfort. Get eyewear that performs — and looks good doing it. Featuring a comfortable fit and a sleek profile designed to work with other personal protective equipment, 3M™ SecureFit™ Protective Eyewear helps keep you safe and comfortable on the job.






## The science of comfort.

We collected data on head and face shapes around the world to develop a patented design that self-adjusts to individual head sizes. This design provides the same level of comfort to individuals across a diverse workforce.

Regardless of head size, from small heads to large heads, our 3M™ SecureFit™ Pressure Diffusion Temple Technology is designed to provide a secure and comfortable fit for an extended period of wear time.



## Designed to perform.



### Curved temples for enhanced security

Our design applies pressure on the less sensitive back of the head instead of the temples, achieving a comfortable fit even during rapid head movement.



### 3M™ Pressure Diffusion Temple Technology

3M's innovative temple design features slotted ribs that provide comfortable pressure equalization, allowing the temples to flex and self-adjust to the size of the wearer's head.



## The benefits are clear.

Fogged lenses can be frustrating and dangerous. But 3M™ SecureFit™ Protective Eyewear models featuring 3M™ Scotchgard™ Protector Anti-Fog Coating can help workers see clearly for longer, thanks to an active ingredient that bonds the coating to the lens.



**Uncoated**



Microscopic water droplets bead up, forming condensation and fog, which obscure vision.

**3M™ Scotchgard™ Protector Anti-Fog Coating**



Reduced contact angle flattens water beads into a thin, transparent film that allows light to pass through.



### 3M™ Scotchgard™ Protector Anti-Fog Coating

- Resists fogging longer than traditional anti-fog coatings through up to 25 washings with water.\*
- Helps provide scratch resistance in tough work environments.
- Designed for working in challenging situations, such as hot and humid conditions, indoor/outdoor work, physically demanding tasks and climate-controlled areas.
- Workers can feel confident wearing 3M eye protection that meets both the Impact-Rated Protector and Anti-Fog Performance (X) requirements of the ANSI-ISEA Z87.1-2020 Standard.



# 3M™ SecureFit™


Family of Protective Eyewear

There's a lot of variety to choose from in the 3M™ SecureFit™ family, all with the comfort, safety and style your workforce demands. Find the series with the right mix of features and value for you.

100 Series



200 Series




400 Series



400X Series



500 Series



3700 Series




# 100 Series

Sleek, comfortable eye protection  
at an economical price.



# 100 Series

3M™ SecureFit™ 100 Series Protective Eyewear features a sleek, sporty lens shape and self-adjusting temples, providing a stylish yet comfortable fit for an extended period of time.





# 100 Series



Product ID: **SF101AF**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF101AS**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Anti-Scratch**

## Available SKUs

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF101AF	7100238174	3M™ SecureFit™ 100 Series SF101AF, Black, Clear Anti-Fog/Anti-Scratch Lens	Black	Clear	AF/AS	20
SF101AS	7100238173	3M™ SecureFit™ 100 Series SF101AS, Black, Clear Anti-Scratch Lens	Black	Clear	AS	20


# 200 Series

Lightweight comfort at  
an affordable price.



# 200 Series

The right fit changes everything. 3M™ SecureFit™ 200 Series Protective Eyewear features temples that automatically self-adjust to help provide a secure, comfortable fit every time.



# 200 Series



Product ID: **SF201AF**  
Lens: **Clear**  
Frame: **Clear**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF201AS**  
Lens: **Clear**  
Frame: **Clear**  
Coating: **Anti-Scratch**



Product ID: **SF201SGAF-BLU**  
Lens: **Clear**  
Frame: **Blue**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

## Available SKUs

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF201AF	70071676251	3M™ SecureFit™ 200 Series SF201AF, Clear Anti-Fog/Anti-Scratch Lens	Clear	Clear	AF/AS	20
SF201AS	70071647682	3M™ SecureFit™ 200 Series SF201AS, Clear Anti-Scratch Lens	Clear	Clear	AS	20
3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING						
SF201SGAF-BLU	70071731577	3M™ SecureFit™ 200 Series SF201SGAF-BLU, Blue, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue	Clear	SGAF/AS	20




# 400 Series

Enhanced comfort and sleek design available in a variety of contemporary colors.




# 400 Series


Take the next step in comfort with 3M™ SecureFit™ 400 Series Protective Eyewear, featuring 3M™ Pressure Diffusion Temple Technology, a soft one-piece nose bridge, dual-injected temples and a range of options, including lens colors, premium coatings, readers and more.



# 400 Series



Product ID: **SF401AF**  
Lens: **Clear**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF401AF-FM**  
Lens: **Clear w/Foam Gasket**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**


# 400 Series

with 3M™ Scotchgard™ Protector  
Anti-Fog Coating

Advanced coating technology  
for premium performance.




Product ID: **SF401SGAF-BLU-F**  
Lens: **Clear w/Foam Gasket**  
Frame: **Blue/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF401SGAF-RED**  
Lens: **Clear**  
Frame: **Red/Gray**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

# 400X Series

with Brow Guard



Product ID: **SF401XAS-GRN**  
Lens: **Clear**  
Frame: **Green/Black**  
Coating: **Anti-Scratch**



Product ID: **SF401XSGAF-GRN**  
Lens: **Clear**  
Frame: **Hi-Vis Green/Clear**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

Helps provide additional coverage  
from particles.

## Available SKUs

400 Series

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF401AF	70071676350	3M™ SecureFit™ 400 Series, SF401AF, Green/Black, Clear Anti-Fog/Anti-Scratch Lens	Green/Black	Clear	AF/AS	20
SF401AF-FM	70071675337	3M™ SecureFit™ 400 Series, SF401AF-FM, Green/Black, Clear Anti-Fog/Anti-Scratch Lens, Foam Gasket	Green/Black	Clear	AF/AS	20
3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING						
SF401SGAF-BLU-F	70071730678	3M™ SecureFit™ 400 Series, SF401SGAF-BLU-F, Blue/Gray, Clear. Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, Foam Gasket	Blue/Gray	Clear	SGAF/AS	20
SF401SGAF-RED	70071730512	3M™ SecureFit™ 400 Series, SF401SGAF-RED, Red/Gray, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Red/Gray	Clear	SGAF/AS	20

## Available SKUs

400X Series  
with Brow Guard

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF401XAF-GRN	70071731593	3M™ SecureFit™ 400 Series, SF401XAF-GRN, Green/Black, Clear Anti-Fog/Anti-Scratch Lens	Green/Black	Clear	AF/AS	20
3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING						
SF401XSGAF-GRN	70071731627	3M™ SecureFit™ 400 Series, SF401XSGAF-GRN, Hi-Vis Green/Clear, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Hi-Vis Green/Clear	Clear	SGAF/AS	20



# 500 Series



Contemporary safety glasses featuring a sporty, streamlined lens shape.



## PPE Compatibility

Sporty design with contemporary lens shape and a sleek profile of safety glasses that can combine well with other personal protective equipment.


SecureFit's flat and flexible temple design combines well with 3M™ Protective Earmuffs




The adjustable ratcheting temples of the SecureFit™ 500 Series are designed to help improve the positioning of the eyewear when worn with half-facepiece respirators

# 500 Series


3M™ SecureFit™ 500 Series features a contemporary lens design coupled with adjustable ratchet temples and 3M™ Pressure Diffusion Temple (PDT) technology to help provide a more personalized fit. This sporty eyewear also offers self-adjusting colored temples, a variety of lens tints and models with Scotchgard™ Protector Anti-Fog Coating.



# 500 Series



Product ID: **SF501AF-BLK**  
 Lens: **Clear**  
 Frame: **Black**  
 Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF501AS-BLK**  
 Lens: **Clear**  
 Frame: **Black**  
 Coating: **Anti-Scratch**



Product ID: **SF501SGAF-GRN**  
 Lens: **Clear**  
 Frame: **Green/Black**  
 Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF501SGAF-BLK-FM**  
 Lens: **Clear w/Foam Gasket**  
 Frame: **Black**  
 Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

## Available SKUs

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF501AF-BLK	7100228736	3M™ SecureFit™ 500 Series, SF501AF, Black, Clear Anti-Fog/Anti-Scratch Lens	Black	Clear	AF/AS	20
SF501AS-BLK	7100228758	3M™ SecureFit™ 500 Series, SF501AS, Black, Clear Anti-Scratch Lens	Black	Clear	AF/AS	20
<b>3M™ SCOTCHGARD™ PROTECTOR ANTI-FOG COATING</b>						
SF501SGAF-GRN	7100239087	3M™ SecureFit™ 500 Series, SF501SGAF-GRN, Green/Black, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Green/Black	Clear	SGAF/AS	20
SF501SGAF-BLK-FM	7100238909	3M™ SecureFit™ 500 Series, SF4501SGAF-BLK-F, Black, Clear Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens, Foam Gasket	Black	Clear	SGAF/AS	20




# 3700 Series

Over-the-glass protection designed with self-adjusting temple technology for all-day wearability.




# 3700 Series


3M™ SecureFit™ 3700 Series is designed to offer eye protection with all-day wearability for workers with prescription eyeglasses. Since prescription glasses may not be anti-fog coated, you can choose between a standard anti-scratch coating or 3M™ Scotchgard™ Protector Anti-Fog Coating.



# 3700 Series



Product ID: SF3701SGAF-BLU  
 Lens: **Clear**  
 Frame: **Blue/Blue**  
 Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: SF3702SGAF-BLU  
 Lens: **Gray**  
 Frame: **Blue/Blue**  
 Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

## Available SKUs

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating Performance	Each/Case
SF3701SGAF-BLU	70071731965	3M™ SecureFit™ 3700 Series, SF3701SGAF-BLU, Blue/Blue, Clear OTG Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Blue	Clear	SGAF/AS	10
SF3702SGAF-BLU	70071731981	3M™ SecureFit™ 3700 Series, SF3702SGAF-BLU, Blue/Blue, Gray OTG Scotchgard™ Protector Anti-Fog Coating/Anti-Scratch Lens	Blue/Blue	Gray	SGAF/AS	10

## Series Comparison Chart

Features/Options	200 Series	400 Series	400X Series	3700 Series	Features/Options	200 Series	400 Series	400X Series	3700 Series
3M™ Pressure Diffusion Temple Technology	X	X	X	X	Sporty Lens Shape				
3M™ Scotchgard™ Protector Anti-Fog Coating	X	X	X	X	Dual Lens Design				
Rugged Anti-Scratch Coating					Readers		X		
Soft Nose Bridge		X	X	X	Alternate Fit				X
Molded Nose Bridge	X				Food Segment	X			
Adjustable Ratchet Temples				X	Bulk Packaging Available				
Brow Guard			X		RX Insert Accessory Available	X	X		
Removable Foam Gasket		X			Impact Rated, Z87+	X	X	X	X



## Additional resources

### Fit testing

Eye injuries can occur even while wearing eye protection if the safety glasses do not fit properly. When fitted properly, eyewear should cover the soft tissue around the eye. Small spectacles on larger heads can leave exposed areas. Spectacles that are too large for a person can leave gaps. Selecting the proper eye protection for the task and ensuring proper-fitting eyewear can help to reduce worker eye injuries.

3M has developed a step-by-step method to ensure you can find your best-fitting protective eyewear, and can help you to validate properly fitting eyewear.







## A difference you can see and feel.

Eyewear that's lightweight and comfortable — believe it. Contact your 3M sales rep to request trial wear samples of 3M™ SecureFit™ Protective Eyewear and feel the difference the instant you put them on. See for yourself.

► Visit [3M.com/SecureFit](https://www.3m.com/SecureFit)

**3M Personal Safety Division - WeWork Prestige Central**  
3rd floor, 36 Infantry Road,  
Bangalore, Karnataka – 560001, India

**Call: 1800 425 3030 (Toll-free)**  
**Email: [3mpersonalsafety.in@mmm.com](mailto:3mpersonalsafety.in@mmm.com)**