



Automotive Aftermarket Division

3M™ Performance Green Masking Tape 233+

1) Part Numbers

3M Part Numbers	3M Part Descriptor
26334	18 mm x 55 m, 48 rolls per case
26336	24 mm x 55 m, 24 rolls per case
26338	36 mm x 55 m, 16 rolls per case
26340	48 mm x 55 m, 12 rolls per case

2) Description and end uses

3M™ Performance Green Masking Tape 233+ is a bright green coloured high performance versatile crepe paper masking tape and designed specifically for the collision repair industry. It's a high conforming paper tape for easiest usability with excellent stick & stay properties and with solvent and moisture resistance and controlled unwind.

3) Physical Properties

NOTE: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Adhesion to Steel	0.233 Nm/2.54cm (ASTM D-3330)
Tensile Strength	31.2 Nm/ 2.54cm (ASTM D-3759)
Elongation at Break	14% (ASTM D-3759)
Temperature Use Range	Up to 120°C (250°F) for 30 mins
Tape Thickness	0.17 mm (6.7 mils) (ASTM D-3652)



4) Directions for Use

Tape is designed for indoor use – exposure to sun and heat may cause tape to become more difficult to remove.

- Make sure surfaces are thoroughly clean and dry before applying masking tape.
- Some surfaces, such as rubber gaskets and mouldings, should be cleaned with a solvent to remove residual release agents from the manufacturing process before applying masking tape.
- For best adhesion, surface temperatures should range from 15°C to 32°C when tape is applied.
- For easier application and removal, apply long continuous strips of tape in flat, straight areas and break the as needed when going around contours or curves (such as wheel arches). The objective when back masking and over taping is to keep the tape lying flat and rolled back, away from the paint edge in order to produce the cleanest look.

Tape removal:

- For general applications, tape should be removed back over itself at a 45° angle.
- For removal on delicate surfaces (such as old weathered paint), tape should be removed as close to a 180° angle as possible.





Technical Data Sheet

Effective: 29/10/2025 Supersedes: 07/11/2023

5) Storage

Store product in the original carton under normal conditions of 21°C and 50% relative humidity. When stored at the recommended conditions in original, unopened containers, this product has a shelf life of 24 months.

6) Safety

Before using this product, please reference Product Label and/or Safety Data Sheet for Health and Safety Information. Note: Laws controlling the acceptable amounts of Volatile Organic Compounds (VOCs) vary by country, and in some cases by locality. For surface preparation and clean-up activities, consult local regulations regarding use of products containing VOCs in your area.

3M™ Performance Green Masking Tape 233+ is designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 29/10/2025 Supersedes: 07/11/2023

For Additional Health and Safety Information

<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk</p>
<p>3M Finland, Suomen 3M Oy Autotuotteet Keilaniementie 1 02151 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet</p>	<p>3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad</p>	<p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto</p>
<p>3M Latvija K.Ulmana 5 Rīga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv</p>	<p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee</p>	<p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt</p>

3M is a trademark of 3M Company, © 3M 2025. All rights reserved.