



# ■ Table of Contents

Discs		
	Fibre Grinding Discs	18
	Flap Discs	24
	Film Discs	27
	Cloth Discs	31
	Paper Discs	34
	Non-woven Discs	36
	Quick Change Discs	43
Wheels	S	
	Cut-off & Grinding Wheels	54
	Deburring & Finishing Wheels	60
Brushe	es	
	Bristle Brushes & Discs	66
	Flap Brushes	71
Sheets	s & Rolls	
	Non-woven Sheets & Rolls	74
Handh	eld Abrasives	
	Hand Pads	78
Belts		
	Cloth belts	85
	Non-woven Belts	97
Abrasiv	ve Tools & Accessories	
	Holders & Back-up Pads	100

# ■ Table of Contents

Power Sanders	106
Power Grinders	110
Dust Extraction Systems	111



# A new era of abrasive performance is here.

Introducing 3M re-engineered Precision-Shaped Grain, boosting the speed and life of 3M™ Cubitron™ Performance Abrasives to new heights. This advancement prioritises operator safety, maximises sustainability, and amplifies time and labour efficiency.

3M™ Cubitron™ 3 Fibre Disc 1182C, 36+


Up to


60%


- → Faster sustained cut rate
- → More total material removed

vs. 3M™ Cubitron™ II Fibre Disc 982C, 36+

#### **Enhanced mineral orientation**







#### Re-shaping the way work gets done.

Gubitr⇒n™ 3

#### Our latest 3M Precision-Shaped Grain

Re-engineered precision-shaped ceramic triangular grain using a proprietary breakthrough in grain shape. This helps increase productivity and lower overall grinding costs.

#### 3M Precision-Shaped Grain

3M pioneered the first precision-shaped grain using 3M microreplication technology to form consistent sharp peaks that easily "slice" through metal—cutting cooler, faster, and lasting longer than conventional abrasive grain.

#### Conventional ceramic abrasive

Conventional ceramic abrasive grain tends to "plough" through metal, causing heat to build up in the workpiece and abrasive, resulting in a slower cut and shorter abrasive life compared to our latest precision-shaped grain.





# Transforming work for over 40 years with pioneering abrasive grain technology.

For over 40 years, 3M<sup>™</sup> Cubitron<sup>™</sup> Performance Abrasives have always delivered maximum productivity, but now the best have gotten even better! Introducing 3M<sup>™</sup> Cubitron<sup>™</sup> 3 Performance Abrasives - the next generation of awesome.

Our new product line uses groundbreaking advancements in precision-shaped grain to deliver 3X the performance in life and cut rate than ever before\*. Discover the difference with 3M™ Cubitron™ 3 Performance Abrasives and experience improvements in all areas of your shop through productivity, worker safety and sustainability.



Our portable bonded wheels have evolved.



Cubitr**⊳**n<sup>™</sup> 3

Launched in 2012, this was the first range of portable bonded wheels using 3M's precision-shaped triangular grain abrasives.

This range will now be replaced by our latest and best offering.



Significantly raising the benchmark for cut rate and product life in heavy grinding and cutting applications.


We've re-engineered precision-shaped ceramic triangular grain using proprietary breakthroughs in molecular bonding technology.





# **3M<sup>™</sup> Abrasive technologies**






The science of smooth

Scotch-Brite™ line of surface conditioning abrasives includes a variety of non-woven synthetic fibre webs suitable for a wide range of applications. Are well-suited for cleaning, blending, deburring, finishing and polishing, and improve surfaces without significantly changing the shape or dimension of the workpiece. Scotch-Brite abrasives run cool, and resist loading due to their open web construction, reducing the risk of part discolouration and warping.

### Scotch-Brite<sup>™</sup> Non-woven technology. Prepared for perfection.

A tough, non-woven nylon web impregnated with resin and mineral throughout its structure

- ➤ Spring-like action produces smooth, burr-free surface
- ► Easy to use, less rework, fewer rejects








# **3M<sup>™</sup> Abrasive technologies**

# **Trizact**<sup>TM</sup>



The science of finishing

Micro and macro-replicated abrasives.


Using another proprietary technology, Trizact™
abrasives derive from 3M's vast experience in the art
of microreplication. Unlike conventional abrasives,
which are constructed from randomly spaced and
irregular-shaped minerals, the uniform configuration
of Trizact abrasives helps deliver a more consistent
finish with higher cut rates, and cooler grinding and
finishing temperatures. The fast, fine, consistent
finishes made possible with Trizact abrasives help
reduce reject rates and improve worker productivity.

# The science of consistent finishes

Derived from patented 3M microreplication technology, 3M™ Trizact™ Abrasives consist of precisely-shaped three-dimensional structures distributed uniformly over the substrate.

- Uniform configuration for consistent performance
- ► Faster cut
- ► Multi-layer mineral

Conventional abrasives start out sharp, but dull quickly.






The three-dimensional structures of 3M™ Trizact™ Abrasives contain multiple layers of mineral. As these structures wear, fresh, sharp mineral is constantly exposed to the workpiece, resulting in faster, more consistent cutting throughout the life of the belt.











# Carbon steel grinding

26% Faster initial cut rate\*




Carbon Steel: the 'initial cut rate' claim is determined from averaging the cut/cycle from cycles 1-2 (first two minutes of grinding). Each cycle on the test method is 1 minute of grinding time. Error bars represent the results with a 95% confidence level.

36% Faster sustained cut rate\*



Carbon Steel: the 'sustained cut rate' claim is determined from averaging the cut/cycle from cycles 7–20 (which is 14 minutes of grinding). Error bars represent the results with a 95% confidence level.

34% More total material removed\*



Carbon Steel: the 'total material removed' claim is determined by averaging the amount of metal ground over the entire test method (30 cycles or 30 minutes of grinding). Error bars represent the results with a 95% confidence level.

<sup>\*</sup>Compared to Competitive Shaped Grain Product A. Results are based on an automated, 30-minute, high pressure test on 1018 steel using 180mm 36+ grit fibre discs and 3M™ Disc Pad Face Plate Ribbed 80514 on a servo motor.

# 3M<sup>™</sup> Cubitron<sup>™</sup> 3 Fibre Disc 1187C, 36+

#### Faster cut rate

Long lasting and faster cutting fibre discs help increase productivity and your bottom line

## Total material removed

Fewer changeouts needed and less downtime

#### Less operator fatigue

Designed to cut with less pressure

#### Grinding aid

Reduces the risk of discoloration from thermal damage in heat sensitive metals











# Stainless steel grinding

43% Faster initial cut rate\*




Stainless Steel: the 'initial cut rate' claim is determined from averaging the cut/cycle from cycles 1–2 (first two minutes of grinding). Each cycle on the test method is 1 minute of grinding time. Error bars represent the results with a 95% confidence level.

61%
Faster sustained cut rate\*



Stainless Steel: the 'sustained cut rate' claim is determined from averaging the cut/cycle from cycles 3–6 (which is 4 minutes of grinding). Error bars represent the results with a 95% confidence level.

52% More total material removed\*



Stainless Steel: the 'total material removed' claim is determined by averaging the amount of metal ground over the entire test method (10 cycles or 10 minutes of grinding). Error bars represent the results with a 95% confidence level.

<sup>\*</sup>Compared to Competitive Shaped Grain Product A. Results are based on an automated, 10-minute, high pressure test on 304 steel using 180mm 36+ grit fibre discs and 3M™ Disc Pad Face Plate Ribbed 80514 on a servo motor.



# Geformance. Deavethe dust behind.

3M Xtract<sup>™</sup> Cubitron<sup>™</sup> II Net Disc 710W

The first high-performance sanding system from 3M.



#### 3M Xtract<sup>™</sup> Cubitron<sup>™</sup> II Net Disc 710W

Premium patterned product

- Unique hole pattern
- Up to 97% dust extraction
- Industry-leading cut-rate
- Designed to require less pressure



#### **Fibre Grinding Discs**

Focus

#### 3M™ Cubitron™ 3 Fibre Disc 1182C

The 3M™ Cubitron™ 3 Fibre Disc 1182C features re-engineered 3M Precision Shaped Grain — taking the legendary speed and life of 3M™ Cubitron™ Performance Abrasives to a whole new level. These product benefits include allowing for increased productivity and lower overall grinding costs vs. other fiber discs and depressed center grinding wheels when grinding mild or carbon steels. Delivering up to 60% more total material removed compared to the 3M™ Cubitron™ II Fibre Disc 982C, 36+, this long-lasting fibre disc has a fast cut rate with high stock removal across a wide range of application pressures. Additionally, this disc is designed to help reduce exposure to hand-arm vibration, increase throughput, and complete more parts-per-disc when tackling medium to high-pressure grinding applications.



- RE-ENGINEERED 3M PRECISION-SHAPED GRAIN: Uses Re-Engineered Precision Shaped Grain, a proprietary technology designed with sharp, angular structures that continuously fracture to form sharp points to wear evenly, run cool, and optimize mineral breakdown
- A WHOLE NEW CUT LEVEL: Delivers up to 51% faster initial cut rate and up to 61% faster sustained cut rate compared to the 3M™ Cubitron™ II Fibre Disc 982C, 36+
- BUILT TOUGH: A stiff fiber backing and strong resin bond provide durability and tear resistance for heavy grinding applications, such as medium to high-pressure grinding, weld removal, and beveling — including robotic operations

Product ID	Product Name	MOQ	OU
7100309905	3M™ Cubitron™ 3 Fibre Disc 1182C, 36+, 100 mm x 16 mm, Slotted, 25/Bag, 100 ea/Case	100	Each
7100308530	3M™ Cubitron™ 3 Fibre Disc 1182C, 36+, 115 mm x 22 mm, Slotted, 25/Bag, 100 ea/Case	100	Each
7100308531	3M™ Cubitron™ 3 Fibre Disc 1182C, 36+, 125 mm x 22 mm, Slotted, 25/Bag, 100 ea/Case	100	Each
7100309790	3M™ Cubitron™ 3 Fibre Disc 1182C, 36+, 150 mm x 22 mm, Slotted, 25/Bag, 100 ea/Case	100	Each
7100309904	3M™ Cubitron™ 3 Fibre Disc 1182C, 36+, 177.8 mm x 22.23 mm, 25/Bag, 100 ea/Case	100	Each
7100309794	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Fibre Disc 1182C, 36+, 180 mm x 22 mm, Slotted, 25/Bag, 100 ea/Case	100	Each



Focus

#### 3M™ Cubitron™ 3 Fibre Disc 1187C

3M™ Cubitron™ 3 Fibre Disc 1187C offers significant gains in productivity on medium to heavy-duty operations thanks to the exceptionally high-performing 3M new Precision-Shaped Grain combined with a stiff fiber backing. This disc achieves a higher cut-rate, greater durability, and longer life than other fiber discs — all with less grinding pressure.



- RE-ENGINEERED 3M PRECISION-SHAPED GRAIN: Uses Re-Engineered Precision Shaped Grain, a proprietary technology designed with sharp, angular structures that continuously fracture to form sharp points to wear evenly, run cool, and optimize mineral breakdown
- A WHOLE NEW CUT LEVEL: Delivers up to 53% faster initial cut rate and up to 43% faster sustained cut rate compared to the 3M™ Cubitron™ II Fibre Disc 987C, 36+
- COOL CUTTING: Features a grinding aid and requires less pressure to use, enabling predictable wear while helping to reduce metal discoloration and the risk of stress cracks on heat-sensitive alloys, such as stainless steel, and non-ferrous metals

Product ID	Product Name	MOQ	OU
7100309798	3M™ Cubitron™ 3 Fibre Disc 1187C, 36+, 100 mm x 16 mm, Slotted, 25/Bag, 100 ea/Case	100	Each
7100309789	3M™ Cubitron™ 3 Fibre Disc 1187C, 36+, 115 mm x 22 mm, Slotted, 25/Bag, 100 ea/Case	100	Each
7100310794	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Fibre Disc 1187C, 36+, 125 mm x 22 mm, Slotted, 25/Bag, 100 ea/Case	100	Each
7100309787	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Fibre Disc 1187C, 36+, 150 mm x 22 mm, Slotted, 25/Bag, 100 ea/Case	100	Each
7100309795	3M™ Cubitron™ 3 Fibre Disc 1187C, 36+, 180 mm x 22 mm, Slotted, 25/Bag, 100 ea/Case	100	Each

# Discs

#### 3M™ Cubitron™ II Fibre Disc 982C

3M™ Cubitron™ II Fibre Disc 982C outperforms conventional ceramic industrial abrasive discs. Our discs feature 3M Precision Shaped Grain technology, offering up to twice the cut rate, durability and lifespan of conventional discs with less grinding pressure required.

- 3M Precision Shaped Grain technology cuts exceptionally fast with less pressure, outperforming all conventional ceramic industrial abrasive discs
- Lasts up to twice as long as conventional discs
- Get significantly longer disc life, completing more parts per disc with fewer disc changes required



700000402       3M** Cubitron** II Fibre Disc 982C, 100 mm x 16 mm, 96+       100       Each         7000000403       3M** Cubitron** II Fibre Disc 982C, 100 mm x 16 mm, 60+       100       Each         70000028192       3M** Cubitron** II Fibre Disc 982C, 115 mm x 22 mm, 36+, Slotted       100       Each         7000028194       3M** Cubitron** II Fibre Disc 982C, 115 mm x 22 mm, 60+, Slotted       100       Each         7000028196       3M** Cubitron** II Fibre Disc 982C, 115 mm x 22 mm, 80+, Slotted       100       Each         7000028191       3M** Cubitron** II Fibre Disc 982C, 125 mm x 22 mm, 36+, Slotted       100       Each         7000028195       3M** Cubitron** II Fibre Disc 982C, 125 mm x 22 mm, 60+, Slotted       100       Each         7000028197       3M** Cubitron** II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted       100       Each         7000045230       3M** Cubitron** II Fibre Disc 982C, 150 mm x 22 mm, 80+, Slotted       100       Each         7000028201       3M** Cubitron** II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M** Cubitron** II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M** Cubitron** II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028204       3M** Cubitron** II Fibre Disc 982C, 178	Product ID	Product Name	MOQ	OU
7000000404       3M™ Cubitron™ II Fibre Disc 982C, 100 mm x 16 mm, 80+       100       Each         7000028192       3M™ Cubitron™ II Fibre Disc 982C, 115 mm x 22 mm, 36+, Slotted       100       Each         7000028194       3M™ Cubitron™ II Fibre Disc 982C, 115 mm x 22 mm, 60+, Slotted       100       Each         7000028196       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted       100       Each         7000028191       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 36+, Slotted       100       Each         7000028195       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 60+, Slotted       100       Each         7000028197       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted       100       Each         7000045230       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted       100       Each         7000028201       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	7000000402	3M™ Cubitron™ II Fibre Disc 982C, 100 mm x 16 mm, 36+	100	Each
7000028192       3M™ Cubitron™ II Fibre Disc 982C, 115 mm x 22 mm, 36+, Slotted       100       Each         7000028194       3M™ Cubitron™ II Fibre Disc 982C, 115 mm x 22 mm, 60+, Slotted       100       Each         7000028196       3M™ Cubitron™ II Fibre Disc 982C, 115 mm x 22 mm, 80+, Slotted       100       Each         7000028191       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 36+, Slotted       100       Each         7000028195       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 60+, Slotted       100       Each         7000028197       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted       100       Each         7000045230       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted       100       Each         7000045234       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 60+       100       Each         7000028201       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	700000403	3M™ Cubitron™ II Fibre Disc 982C, 100 mm x 16 mm, 60+	100	Each
7000028194       3M™ Cubitron™ II Fibre Disc 982C, 115 mm x 22 mm, 60+, Slotted       100       Each         7000028196       3M™ Cubitron™ II Fibre Disc 982C, 115 mm x 22 mm, 80+, Slotted       100       Each         7000028191       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 36+, Slotted       100       Each         7000028195       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 60+, Slotted       100       Each         7000028197       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted       100       Each         7000045230       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted       100       Each         7000045234       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 60+       100       Each         7000028201       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	7000000404	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 982C, 100 mm x 16 mm, 80+	100	Each
7000028196       3M™ Cubitron™ II Fibre Disc 982C, 115 mm x 22 mm, 80+, Slotted       100       Each         7000028191       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 36+, Slotted       100       Each         7000028195       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 60+, Slotted       100       Each         7000028197       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted       100       Each         7000045230       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted       100       Each         7000045234       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 60+       100       Each         7000028201       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         700000393       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	7000028192	3M™ Cubitron™ II Fibre Disc 982C, 115 mm x 22 mm, 36+, Slotted	100	Each
7000028191       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 36+, Slotted       100       Each         7000028195       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 60+, Slotted       100       Each         7000028197       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted       100       Each         7000045230       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted       100       Each         7000045234       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 60+       100       Each         7000028201       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         700000393       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	7000028194	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 982C, 115 mm x 22 mm, 60+, Slotted	100	Each
7000028195       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 60+, Slotted       100       Each         7000028197       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted       100       Each         7000045230       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted       100       Each         7000045234       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 60+       100       Each         7000028201       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         700000393       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	7000028196	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 982C, 115 mm x 22 mm, 80+, Slotted	100	Each
7000028197       3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted       100       Each         7000045230       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted       100       Each         7000045234       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 60+       100       Each         7000028201       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         700000393       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	7000028191	3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 36+, Slotted	100	Each
7000045230       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted       100       Each         7000045234       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 60+       100       Each         7000028201       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         700000393       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	7000028195	3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 60+, Slotted	100	Each
7000045234       3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 60+       100       Each         7000028201       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         700000393       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	7000028197	3M™ Cubitron™ II Fibre Disc 982C, 125 mm x 22 mm, 80+, Slotted	100	Each
7000028201       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         700000393       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted       100       Each         7000028203       3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted       100       Each	7000045230	3M™ Cubitron™ II Fibre Disc 982C, 150 mm x 22 mm, 36+, Slotted	100	Each
700000393 3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted 100 Each 7000028203 3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted 100 Each	7000045234	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 982C, 150 mm x 22 mm, 60+	100	Each
7000028203 3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted 100 Each	7000028201	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted	100	Each
,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	7000000393	3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 36+, Slotted	100	Each
7000028204 3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 80+, Slotted 100 Each	7000028203	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 982C, 178 mm x 22 mm, 60+, Slotted	100	Each
	7000028204	3M™ Cubitron™ II Fibre Disc 982C, 178 mm x 22 mm, 80+, Slotted	100	Each
7000144562 3M™ Cubitron™ II Fibre Disc 982C, 230 mm x 22 mm, 36+, Slotted 100 Each	7000144562	3M™ Cubitron™ II Fibre Disc 982C, 230 mm x 22 mm, 36+, Slotted	100	Each



#### 3M™ Cubitron™ II Fibre Disc 987C

3M™ Cubitron™ II Fibre Disc 987C gives a higher cut rate, greater durability and longer life than other fibre discs and grinding discs. Our discs use 3M Precision Shaped Grain combined with a stiff fibre backing for increased productivity on medium to heavy duty operations.

- Engineered to cut faster and last longer than competitive ceramic products
- Stiff fibre backing and strong resin bond provide durability and tear resistance during heavyweight applications
- Contains 3M Precision Shaped Grain which runs significantly cooler and longer than rival products, completing more parts per disc for less disc changes



Product ID	Product Name	MOQ	OU
7000000405	3M™ Cubitron™ II Fibre Disc 987C, 100mm x 16mm, 36+	100	Each
7000000406	3M™ Cubitron™ II Fibre Disc 987C, 100mm x 16mm, 60+	100	Each
7000000407	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 987C, 100mm x 16mm, 80+	100	Each
7000045159	3M™ Cubitron™ II Fibre Disc 987C, 115 mm x 22 mm, 36+, Slotted	100	Each
7000045160	3M™ Cubitron™ II Fibre Disc 987C, 115 mm x 22 mm, 60+, Slotted	100	Each
7000045161	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 987C, 115 mm x 22 mm, 80+, Slotted	100	Each
7000028193	3M™ Cubitron™ II Fibre Disc 987C, 125 mm x 22 mm, 36+, Slotted	100	Each
7000028199	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 987C, 125mm x 22mm, 60+, Slotted	100	Each
7000028200	3M <sup>™</sup> Cubitron <sup>™</sup> II Fibre Disc 987C, 125mm x 22mm, 80+, Slotted	100	Each
7000045188	3M™ Cubitron™ II Fibre Disc 987C, 178 mm x 22 mm, 36+, Slotted	100	Each
7000045186	3M™ Cubitron™ II Fibre Disc 987C, 178 mm x 22 mm, 60+, Slotted	100	Each
7000045187	3M™ Cubitron™ II Fibre Disc 987C, 178 mm x 22 mm, 80+, Slotted	100	Each

# Discs

#### 3M™ Fibre Disc 782C

3M™ Fibre Disc 782C is a fibre disc engineered for an ultra-rapid cut on carbon steel. These discs feature our advanced abrasive technology, 3M Precision Shaped Grain. Their stiff fibre backing and strong resin bond provides durability and tear resistance.



These discs are compatible with 3M disc pad face plates and hubs (sold separately).

- Premium mineral excels at heavy weight applications
- 3M Precision Shaped Grain yields higher cut rates
- Reduce costs with long lasting abrasive completes more parts than conventional discs

Product ID	Product Name	MOQ	OU
7100099264	3M <sup>™</sup> Fibre Disc 782C, 100 mm x 16 mm, 36+, Slotted	100	Each
7100099249	3M <sup>™</sup> Fibre Disc 782C, 100 mm x 16 mm, 60+, Slotted	100	Each
7100099092	3M <sup>™</sup> Fibre Disc 782C, 100 mm x 16 mm, 80+, Slotted	100	Each
7100099545	3M <sup>™</sup> Fibre Disc 782C, 115 mm x 22 mm, 36+, Slotted	100	Each
7100099250	3M <sup>™</sup> Fibre Disc 782C, 115 mm x 22 mm, 60+, Slotted	100	Each
7100099093	3M <sup>™</sup> Fibre Disc 782C, 115 mm x 22 mm, 80+, Slotted	100	Each
7100099576	3M <sup>™</sup> Fibre Disc 782C, 125 mm x 22 mm, 36+, Slotted	100	Each
7100099094	3M <sup>™</sup> Fibre Disc 782C, 125 mm x 22 mm, 60+, Slotted	100	Each
7100099095	3M <sup>™</sup> Fibre Disc 782C, 125 mm x 22 mm, 80+, Slotted	100	Each
7100099284	3M <sup>™</sup> Fibre Disc 782C, 180 mm x 22 mm, 36+, Slotted	100	Each
7100099091	3M <sup>™</sup> Fibre Disc 782C, 180 mm x 22 mm, 60+, Slotted	100	Each
7100099237	3M <sup>™</sup> Fibre Disc 782C, 180 mm x 22 mm, 80+, Slotted	100	Each



#### 3M™ Fibre Disc 787C

3M™ Fibre Disc 787C is a fibre disc featuring our advanced abrasive technology, 3M Precision Shaped Grain. These discs have a stiff fibre backing and strong resin bond that provide durability and tear resistance. They're constructed with a grinding aid and are engineered for ultra-rapid cut.

+

- Premium mineral excels at heavy weight applications
- 3M Precision Shaped Grain yields higher cut rates
- Grinding aid minimises grinding temperatures for heat-sensitive alloys

Product ID	Product Name	MOQ	OU
7100099238	3M™ Fibre Disc 787C, 100 mm x 16 mm, 36+, Slotted	100	Each
7100099258	3M™ Fibre Disc 787C, 100 mm x 16 mm, 60+, Slotted	100	Each
7100099252	3M™ Fibre Disc 787C, 100 mm x 16 mm, 80+, Slotted	100	Each
7100099241	3M™ Fibre Disc 787C, 100 mm x 16 mm, 120+, Slotted	100	Each
7100099787	3M™ Fibre Disc 787C, 115 mm x 22 mm, 36+, Slotted	100	Each
7100099260	3M™ Fibre Disc 787C, 115 mm x 22 mm, 60+, Slotted	100	Each
7100099254	3M™ Fibre Disc 787C, 115 mm x 22 mm, 80+, Slotted	100	Each
7100099791	3M™ Fibre Disc 787C, 115 mm x 22 mm, 120+, Slotted	100	Each
7100099788	3M <sup>™</sup> Fibre Disc 787C, 125 mm x 22 mm, 36+, Slotted	100	Each
7100099245	3M™ Fibre Disc 787C, 125 mm x 22 mm, 60+, Slotted	100	Each
7100099256	3M <sup>™</sup> Fibre Disc 787C, 125 mm x 22 mm, 80+, Slotted	100	Each
7100099546	3M™ Fibre Disc 787C, 125 mm x 22 mm, 120+, Slotted	100	Each
7100099257	3M™ Fibre Disc 787C, 180 mm x 22 mm, 36+, Slotted	100	Each
7100099247	3M™ Fibre Disc 787C, 180 mm x 22 mm, 60+, Slotted	100	Each
7100099240	3M™ Fibre Disc 787C, 180 mm x 22 mm, 80+, Slotted	100	Each
7100099243	3M™ Fibre Disc 787C, 180 mm x 22 mm, 120+, Slotted	100	Each



#### Flap Discs

#### 3M™ Cubitron™ II Flap Disc 969F

3M™ Cubitron™ II Flap Disc 969F is made with layers of abrasive material. Our flap discs are unique in design and feature a fast cutting abrasive material on flaps of tough polyester cloth. These discs come with a grinding aid and semi-flexible, Y-weight, backing gives each flap excellent strength.

0

- Abrasive flap design provides a soft and smooth cut on rounded or irregular surfaces
- Flaps wear down to expose fresh abrasive mineral, assuring a fast and consistent cut
- Cubitron™ II abrasive cuts exceptionally fast, helping increase productivity

Product ID	Product Name	MOQ	OU
7100105847	3M™ Cubitron™ II Flap Disc 969F, 115 mm, 40+, Conical	10	Each
7100105859	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 969F, 115 mm, 40+, Flat	10	Each
7100105848	3M™ Cubitron™ II Flap Disc 969F, 115 mm, 60+, Conical	10	Each
7100105860	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 969F, 115 mm, 60+, Flat	10	Each
7100105849	3M™ Cubitron™ II Flap Disc 969F, 115 mm, 80+, Conical	10	Each
7100105861	3M™ Cubitron™ II Flap Disc 969F, 115 mm, 80+, Flat	10	Each
7100105850	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 969F, 125 mm, 40+, Conical	10	Each
7100105862	3M™ Cubitron™ II Flap Disc 969F, 125 mm, 40+, Flat	10	Each
7100105851	3M™ Cubitron™ II Flap Disc 969F, 125 mm, 60+, Conical	10	Each
7100105863	3M™ Cubitron™ II Flap Disc 969F, 125 mm, 60+, Flat	10	Each
7100105852	3M™ Cubitron™ II Flap Disc 969F, 125 mm, 80+, Conical	10	Each
7100105864	3M™ Cubitron™ II Flap Disc 969F, 125 mm, 80+, Flat	10	Each
7100105853	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 969F, 150 mm, 40+, Conical	15	Each
7100105854	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 969F, 150 mm, 60+, Conical	15	Each
7100105855	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 969F, 150 mm, 80+, Conical	15	Each
7100105856	3M™ Cubitron™ II Flap Disc 969F, 178 mm, 40+, Conical	10	Each
7100105865	3M™ Cubitron™ II Flap Disc 969F, 178 mm, 40+, Flat	10	Each
7100105857	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 969F, 178 mm, 60+, Conical	10	Each
7100105866	3M™ Cubitron™ II Flap Disc 969F, 178 mm, 60+, Flat	10	Each
7100105858	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 969F, 178 mm, 80+, Conical	10	Each
7100105867	3M™ Cubitron™ II Flap Disc 969F, 178 mm, 80+, Flat	10	Each



#### 3M™ Cubitron™ II Flap Disc 967A

3M™ Cubitron™ II Flap Disc 967A delivers superior cut rates in low to medium-high pressure applications. Our discs are ideal for flat surfaces or outside edgework, especially where final finish and gouge resistance are important.

- 0
- Engineered to cut faster and last longer than competitive ceramic products with 3M Precision Shaped Grain
- Cool operating temperature decreases metal discolouration/oxidation and heat related stress cracks
- Flap discs grind and blend in a single step meaning they can replace bonded wheels and fibre discs

Product ID	Product Name	MOQ	OU
7000104357	3M™ Cubitron™ II Flap Disc 967A, 100 mm, Conical, G40, PN65049	700	Each
7000104368	3M™ Cubitron™ II Flap Disc 967A, 100 mm, G40, PN65063	700	Each
7000104359	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 967A, 115 mm, 40+, Conical	10	Each
7000104371	3M™ Cubitron™ II Flap Disc 967A, 115 mm, 40+, Flat	10	Each
7000104360	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 967A, 115 mm, 60+, Conical	10	Each
7000104372	3M™ Cubitron™ II Flap Disc 967A, 115 mm, 60+, Flat	10	Each
7000104361	3M™ Cubitron™ II Flap Disc 967A, 115 mm, 80+, Conical	10	Each
7000104373	3M™ Cubitron™ II Flap Disc 967A, 115 mm, 80+, Flat	10	Each
7100011310	3M™ Cubitron™ II Flap Disc 967A, 125 mm, 40+, Conical	10	Each
7000104374	3M™ Cubitron™ II Flap Disc 967A, 125 mm, 40+, Flat	10	Each
7100011144	3M™ Cubitron™ II Flap Disc 967A, 125 mm, 60+, Conical	10	Each
7000104375	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 967A, 125 mm, 60+, Flat	10	Each
7100011569	3M™ Cubitron™ II Flap Disc 967A, 125 mm, 80+, Conical	10	Each
7000104376	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 967A, 125 mm, 80+, Flat	10	Each
7100026188	3M™ Cubitron™ II Flap Disc 967A, 150 mm, 40+, Conical	15	Each
7000104365	3M™ Cubitron™ II Flap Disc 967A, 178 mm, 40+, Conical	10	Each
7000104377	3M™ Cubitron™ II Flap Disc 967A, 178 mm, 40+, Flat	10	Each
7000104366	3M™ Cubitron™ II Flap Disc 967A, 178 mm, 60+, Conical	10	Each
7000104378	3M™ Cubitron™ II Flap Disc 967A, 178 mm, 60+, Flat	10	Each
7000104367	3M™ Cubitron™ II Flap Disc 967A, 178 mm, 80+, Conical	10	Each
7000104379	3M <sup>™</sup> Cubitron <sup>™</sup> II Flap Disc 967A, 178 mm, 80+, Flat	10	Each

# Discs

#### 3M™ Flap Disc 769F

3M™ Flap Disc 769F is our long-lasting, high-performance abrasive flap disc featuring 3M™ Precision-Shaped Grain and a durable polyester backing.



- Delivers long-lasting high-performance and versatility
- Cuts faster and lasts longer than conventional abrasive grain thanks to 3M™ Precision-Shaped Grain
- Proven to outperform traditional alumina zirconia flap discs

Product ID	Product Name	MOQ	OU
7100239219	3M <sup>™</sup> Flap Disc 769F, 40+, Y-weight, T29, 150 mm x 22.23 mm	20	Each
7100196818	3M <sup>™</sup> Flap Disc 769F, 115 mm, 40+, Conical	10	Each
7100196540	3M <sup>™</sup> Flap Disc 769F, 115 mm, 40+, Flat	10	Each
7100196816	3M <sup>™</sup> Flap Disc 769F, 115 mm, 60+, Conical	10	Each
7100196817	3M <sup>™</sup> Flap Disc 769F, 115 mm, 60+, Flat	10	Each
7100196789	3M <sup>™</sup> Flap Disc 769F, 115 mm, 80+, Conical	10	Each
7100196820	3M <sup>™</sup> Flap Disc 769F, 115 mm, 80+, Flat	10	Each
7100196539	3M <sup>™</sup> Flap Disc 769F, 115 mm, 120+, Conical	100	Each
7100196819	3M <sup>™</sup> Flap Disc 769F, 115 mm, 120+, Flat	10	Each
7100196812	3M <sup>™</sup> Flap Disc 769F, 125 mm, 40+, Conical	10	Each
7100196813	3M <sup>™</sup> Flap Disc 769F, 125 mm, 40+, Flat	10	Each
7100196797	3M <sup>™</sup> Flap Disc 769F, 125 mm, 60+, Conical	10	Each
7100196799	3M <sup>™</sup> Flap Disc 769F, 125 mm, 60+, Flat	10	Each
7100196791	3M <sup>™</sup> Flap Disc 769F, 125 mm, 80+, Conical	10	Each
7100196790	3M <sup>™</sup> Flap Disc 769F, 125 mm, 80+, Flat	10	Each
7100196815	3M <sup>™</sup> Flap Disc 769F, 125 mm, 120+, Conical	10	Each
7100196821	3M <sup>™</sup> Flap Disc 769F, 125 mm, 120+, Flat	10	Each
7100197061	3M <sup>™</sup> Flap Disc 769F, 180 mm, 40+, Conical	5	Each
7100196538	3M <sup>™</sup> Flap Disc 769F, 180 mm, 40+, Flat	5	Each
7100196798	3M <sup>™</sup> Flap Disc 769F, 180 mm, 60+, Conical	5	Each
7100196800	3M <sup>™</sup> Flap Disc 769F, 180 mm, 60+, Flat	5	Each
7100196794	3M <sup>™</sup> Flap Disc 769F, 180 mm, 80+, Conical	5	Each
7100197431	3M <sup>™</sup> Flap Disc 769F, 180 mm, 80+, Flat	5	Each
7100196793	3M <sup>™</sup> Flap Disc 769F, 180 mm, 120+, Conical	5	Each
7100196792	3M <sup>™</sup> Flap Disc 769F, 180 mm, 120+, Flat	5	Each
7100239223	3M <sup>™</sup> Flap Disc 769F, 28716, 60+ Y-weight, T29, 150 mm x 22.23 mm	20	Each
7100240279	3M <sup>™</sup> Flap Disc 769F, 28901, 80+ Y-weight, T29, 150 mm x 22.23 mm	20	Each
7100239224	3M <sup>™</sup> Flap Disc 769F, 28919, 120+ Y-weight, T29, 150 mm x 22.23 mm	20	Each



#### Film Discs

#### 3M Xtract™ Cubitron™ II Film Disc 775L

3M Xtract™ Cubitron™ II Film Disc 775L features a 3M™ proprietary multi-hole pattern for improved dust extraction in finishing applications. Part of the 3M Xtract™ Series, designed for optimal dust removal. Our innovative multi-hole pattern extracts dust better than 5- or 6-hole products — increasing cut and dramatically increasing disc life. The design does not need to align with the disc pad holes, making switching the discs fast, easy, and convenient. Featuring 3M Precision Shaped Ceramic Grain, a revolutionary advancement in abrasive technology. The triangular shaped ceramic mineral is designed to slice through the substrate, rather than gouging or "ploughing" like conventional abrasives, resulting in a disc that cuts up to 2x as fast and lasts up to 6x as long as conventional abrasives. The film backing delivers outstanding tear resistance, flexibility and a consistent, uniform finish on a variety of substrates.



- 3M Xtract™ proprietrary multi-hole pattern provides superior dust extraction to prevent loading, increase productivity, and provide a cleaner work environment
- Revolutionary 3M™ Precision Shaped Grain technology provides fast cut and long life
- Cuts up to 2x as fast as conventional abrasives

Product ID	Product Name	MOQ	OU
7100106717	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Film Disc 775L, 76 mm, 150+	250	Each
7100111238	3M Xtract™ Cubitron™ II Film Disc 775L, 76 mm, 180+	250	Each
7100106716	3M Xtract™ Cubitron™ II Film Disc 775L, 76 mm, 220+	250	Each
7100145460	3M Xtract™ Cubitron™ II Film Disc 775L, 76 mm, 240+	250	Each
7100145433	3M Xtract™ Cubitron™ II Film Disc 775L, 76 mm, 320+	250	Each
7100145452	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Film Disc 775L, 76 mm, 400+	250	Each
7100045070	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Film Disc 775L, 127 mm, 80+ 500LG, 50 per inner, 250 per case	250	Each
7100045071	3M Xtract™ Cubitron™ II Film Disc 775L, 127 mm, 120+ 500LG, 50 per inner, 250 per case	250	Each
7100064175	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Film Disc 775L, 127 mm, 150+ 500LG, 50 per inner, 250 per case	250	Each
7100064177	3M Xtract™ Cubitron™ II Film Disc 775L, 127 mm, 180+ 500LG, 50 per inner, 250 per case	250	Each
7100064270	3M Xtract™ Cubitron™ II Film Disc 775L, 127 mm, 220+, 500LG, 50 per inner, 250 per case	250	Each
7100145362	3M Xtract™ Cubitron™ II Film Disc 775L, 127 mm, 240+ 500LG, 50 per inner, 250 per case	250	Each
7100145363	3M Xtract™ Cubitron™ II Film Disc 775L, 127 mm, 320+ 500LG, 50 per inner, 250 per case	250	Each
7100145404	3M Xtract™ Cubitron™ II Film Disc 775L, 127 mm, 400+ 500LG, 50 per inner, 250 per case	250	Each
7100045072	3M Xtract™ Cubitron™ II Film Disc 775L, 152 mm, 80+, 600LG	250	Each
7100045073	3M Xtract™ Cubitron™ II Film Disc 775L, 152 mm, 120+	250	Each
7100065918	3M Xtract™ Cubitron™ II Film Disc 775L, 152 mm, 150+	250	Each
7100064178	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Film Disc 775L, 152 mm, 180+	250	Each
7100064271	3M Xtract™ Cubitron™ II Film Disc 775L, 152 mm, 220+	250	Each
7100145316	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Film Disc 775L, 152 mm, 240+	250	Each
7100141692	3M Xtract™ Cubitron™ II Film Disc 775L, 152 mm, 320+	250	Each
7100145455	3M Xtract™ Cubitron™ II Film Disc 775L, 152 mm, 400+	250	Each
7100246422	3M Xtract™ Cubitron™ II Film Disc 775L, 203 mm, Clean Sand, 80+, PN17775	250	Each
7100246524	3M Xtract™ Cubitron™ II Film Disc 775L, 203 mm, Clean Sand, 120+, PN59938	250	Each
7100248339	3M Xtract™ Cubitron™ II Film Disc 775L, 203 mm, Clean Sand, 150+, PN33568	250	Each
7100248337	3M Xtract™ Cubitron™ II Film Disc 775L, 203 mm, Clean Sand, 180+, PN73495	250	Each
7100246533	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Film Disc 775L, 203 mm, Clean Sand, 220+, PN94374	250	Each
7100246535	3M Xtract™ Cubitron™ II Film Disc 775L, 203 mm, Clean Sand, 240+, PN42667	250	Each
7100246534	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Film Disc 775L, 203 mm, Clean Sand, 320+, PN46340	250	Each
7100246525	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Film Disc 775L, 203 mm, Clean Sand, 400+, PN11458	250	Each



#### 3M™ Cubitron™ II Hookit™ Film Disc 775L

3M™ Cubitron™ II Hookit™ Film Disc 775L features 3M Precision Shaped Ceramic Grain a revolutionary advancement in abrasive technology. Our film discs can cut up to twice as fast and last up to six times as long as normal abrasives.

- Contains 3M Precision Shaped Grain which cuts up to twice as fast and lasts up to six times as long as other abrasives
- Film backing provides greater tear resistance and edge retention
- Ideal for a variety of applications focused primarily on stock removal

Product ID	Product Name	MOQ	OU
7100106678	3M™ Cubitron™ II Hookit™ Film Disc 775L, 76 mm, Clean Sand, 80+	250	Each
7100106714	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 76 mm, Clean Sand, 120+	250	Each
7100106742	3M™ Cubitron™ II Hookit™ Film Disc 775L, 76 mm, No Hole, 80+	250	Each
7100106764	3M™ Cubitron™ II Hookit™ Film Disc 775L, 76 mm, No Hole, 120+	250	Each
7100106768	3M™ Cubitron™ II Hookit™ Film Disc 775L, 76 mm, No Hole, 180+	250	Each
7100106766	3M™ Cubitron™ II Hookit™ Film Disc 775L, 76 mm, No Hole, 220+	250	Each
7100145430	3M™ Cubitron™ II Hookit™ Film Disc 775L, 76 mm, No Hole, 240+	250	Each
7100145431	3M™ Cubitron™ II Hookit™ Film Disc 775L, 76 mm, No Hole, 320+	250	Each
7100145477	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 76 mm, No Hole, 400+	250	Each
7100046325	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 127 mm, No Hole, 80+	250	Each
7100046326	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 127 mm, No Hole, 120+	250	Each
7100064174	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 127 mm, No Hole, 150+	250	Each
7100064176	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 127 mm, No Hole, 180+	250	Each
7100064179	3M™ Cubitron™ II Hookit™ Film Disc 775L, 127 mm, No Hole, 220+	250	Each
7100145403	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 127 mm, No Hole, 240+	250	Each
7100145405	3M™ Cubitron™ II Hookit™ Film Disc 775L, 127 mm, No Hole, 320+	250	Each
7100145436	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 127 mm, No Hole, 400+	250	Each
7100046327	3M™ Cubitron™ II Hookit™ Film Disc 775L, 152 mm, No Hole, 80+	250	Each
7100046328	3M™ Cubitron™ II Hookit™ Film Disc 775L, 152 mm, No Hole, 120+	250	Each
7100064273	3M™ Cubitron™ II Hookit™ Film Disc 775L, 152 mm, No Hole, 150+	250	Each
7100064272	3M™ Cubitron™ II Hookit™ Film Disc 775L, 152 mm, No Hole, 180+	250	Each
7100064274	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 152 mm, No Hole, 220+	250	Each
7100145407	3M™ Cubitron™ II Hookit™ Film Disc 775L, 152 mm, No Hole, 240+	250	Each
7100145462	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 152 mm, No Hole, 320+	250	Each
7100145469	3M™ Cubitron™ II Hookit™ Film Disc 775L, 152 mm, No Hole, 400+	250	Each
7100249319	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 203 mm, No Hole, 80+	250	Each
7100249473	3M™ Cubitron™ II Hookit™ Film Disc 775L, 203 mm, No Hole, 120+	250	Each
7100249427	3M™ Cubitron™ II Hookit™ Film Disc 775L, 203 mm, No Hole, 150+	250	Each
7100249431	3M™ Cubitron™ II Hookit™ Film Disc 775L, 203 mm, No Hole, 180+	250	Each
7100249320	3M™ Cubitron™ II Hookit™ Film Disc 775L, 203 mm, No Hole, 220+	250	Each
7100249321	3M™ Cubitron™ II Hookit™ Film Disc 775L, 203 mm, No Hole, 240+	250	Each
7100249322	3M™ Cubitron™ II Hookit™ Film Disc 775L, 203 mm, No Hole, 320+	250	Each
7100249443	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Film Disc 775L, 203 mm, No Hole, 400+	250	Each



#### 3M Xtract™ Film Disc 360L

3M Xtract™ Film Disc 360L features a 3M™ proprietary multi-hole pattern for improved dust extraction in finishing applications. Part of the 3M Xtract™ Series, designed for optimal dust removal. Our innovative multi-hole pattern extracts dust better than 5- or 6-hole products — increasing cut and dramatically increasing disc life. The design does not need to align with the disc pad holes, making switching the discs fast, easy, and convenient. Advanced Series Abrasives from 3M are designed to deliver an unbeatable combination of performance and value.



- 3M Xtract™ proprietrary multi-hole pattern provides superior dust extraction to prevent loading, increase productivity, and provide a cleaner work environment
- Open coat and load-resistant coating prevents clogging to optimize cut and product life
- 3M™ Hookit™ attachment system provides easy disc changes and optimizes disc life

Product ID	Product Name	MOQ	OU
7100010261	3M Xtract <sup>™</sup> Film Disc 360L, 76 mm, 300LG, P600	500	Each
7100010263	3M Xtract <sup>™</sup> Film Disc 360L, 76 mm, 300LG, P1000	500	Each
7010029938	3M Xtract <sup>™</sup> Film Disc 360L, 127 mm, 500LG, P600	500	Each
7010029936	3M Xtract <sup>™</sup> Film Disc 360L, 127 mm, P240	500	Each
7100028668	3M Xtract <sup>™</sup> Film Disc 360L, 127 mm, P280, 500LG	500	Each
7010029939	3M Xtract <sup>™</sup> Film Disc 360L, 127 mm, P800	500	Each
7100077620	3M Xtract <sup>™</sup> Film Disc 360L, 152 mm, P220	500	Each
7100077621	3M Xtract <sup>™</sup> Film Disc 360L, 152 mm, P240	500	Each
7010029944	3M Xtract <sup>™</sup> Film Disc 360L, 152 mm, P280	500	Each
7100077622	3M Xtract <sup>™</sup> Film Disc 360L, 152 mm, P320	500	Each
7100077623	3M Xtract <sup>™</sup> Film Disc 360L, 152 mm, P400	500	Each
7100077624	3M Xtract <sup>™</sup> Film Disc 360L, 152 mm, P500	500	Each
7100077625	3M Xtract <sup>™</sup> Film Disc 360L, 152 mm, P600	500	Each
7100077626	3M Xtract <sup>™</sup> Film Disc 360L, 152 mm, P800	500	Each
7100077975	3M Xtract <sup>™</sup> Film Disc 360L, 152 mm, P1000	500	Each



#### 3M™ Trizact™ Hookit™ Film Disc Roll 466LA

3M™ Trizact™ Hookit™ Film Disc Roll 466LA is the clear coat repair disc that is used by most Automotive manufacturers worldwide. Each disc will last for many repairs because fresh abrasive mineral is exposed as the disc wears. The consistent, surface roughness (low Rz) reduces the the polishing time required, and helps prevent quality audit failures. The end result is a cost effective, robust process.



- Silicone Carbide Mineral
- Ideal for the 3M two-step paint defect repair process for automotive finishes
- Available in a convenient disc roll form

Product ID	Product Name	MOQ	OU
7000034236	3M™ Trizact™ Abrasive Disc 466LA, 31.7 mm, P3000	1000	Each
7000028142	3M™ Trizact™ Hookit™ Abrasive Disc 466LA, Grey, 35 mm, A5	1	Each
7000028143	3M™ Trizact™ Hookit™ Abrasive Disc 466LA, Purple, 35 mm, A7	2000	Each



#### **Cloth Discs**

#### 3M™ Cubitron II Hookit Cloth Disc 784F

3M™ Cubitron™ II Hookit™ Cloth Disc 784F features 3M Precision-Shaped Grain for longer life and a faster, more consistent cut than aluminum oxide discs. A precise mix of shaped ceramic and premium aluminum oxide delivers optimal cut in medium pressure grinding and blending applications. The disc also features a waterproof backing and grinding aid.



- 3M Precision-Shaped Grain blend provides up to 2x longer life than comparable aluminum oxide discs
- Proprietary mineral provides consistent, faster results on medium pressure applications, increasing production rate
- Reduces changeouts and downtime in finishing applications

Product ID	Product Name	MOQ	OU
7100222630	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Cloth Disc 784F, 127 mm, No hole, 36+	200	Each
7100211074	3M™ Cubitron™ II Hookit™ Cloth Disc 784F, 127 mm, No hole, 60+	200	Each
7100222628	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Cloth Disc 784F, 127 mm, No hole, 80+	200	Each
7100222757	3M™ Cubitron™ II Hookit™ Cloth Disc 784F, 127 mm, No hole, 120+	200	Each



#### 3M™ Cubitron™II Hookit™ Cloth D/F Disc 947A

3M™ Cubitron™ II Hookit™ Cloth Disc 947A is a cloth disc featuring 3M Precision Shaped Grain. Our cloth discs are constructed on a durable X-weight poly-cloth backing for high performance on a wide range of metals.

- Cuts hard and fast to slice through metals
- 3M Precision Shaped Grain yields higher cut rates
- Delivers consistent performance on a wide range of metals



Product ID	Product Name	MOQ	OU
7100113118	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 76 mm, 3-Hole, 40+	200	Each
7100113113	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 76 mm, 3-Hole, 120+	200	Each
7100113114	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 76 mm, No Hole, 40+	200	Each
7100113109	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 76 mm, No Hole, 60+	200	Each
7100113126	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 76 mm, No Hole, 80+	200	Each
7100113117	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 76 mm, No Hole, 120+	200	Each
7100169959	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 115 mm, No Hole, 40+	200	Each
7100169950	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Cloth Disc 947A, 115 mm, No Hole, 60+	200	Each
7100169962	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 115 mm, No Hole, 80+	200	Each
7100169949	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Cloth Disc 947A, 115 mm, No Hole, 120+	200	Each
7100113110	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 127 mm, 5-Hole, 40+	200	Each
7100113096	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 127 mm, 5-Hole, 60+	200	Each
7100113111	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 127 mm, 5-Hole, 80+	200	Each
7100113075	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 127 mm, 5-Hole, 120+	200	Each
7100113120	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 127 mm, No Hole, 40+	200	Each
7100113137	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 127 mm, No Hole, 60+	200	Each
7100112980	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 127 mm, No Hole, 80+	200	Each
7100085514	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 127 mm, No Hole, 120+	200	Each
7100113143	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 152 mm, 6-Hole, 40+	200	Each
7100113076	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 152 mm, 6-Hole, 60+	200	Each
7100113107	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 152 mm, 6-Hole, 80+	200	Each
7100113121	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 152 mm, No Hole, 40+	200	Each
7100113142	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 152 mm, No Hole, 60+	200	Each
7100113080	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 152 mm, No Hole, 80+	200	Each
7100113139	3M™ Cubitron™II Hookit™ Cloth Disc 947A, 152 mm, No Hole, 120+	200	Each



#### 3M Xtract™ Cubitron™ II Cloth Disc 900DZ

3M Xtract™ Cubitron™ II Cloth Disc 900DZ features a 3M proprietary multi-hole pattern for improved dust extraction in finishing applications. Part of the 3M Xtract™ Series, designed for optimal dust removal. The innovative multi-hole pattern extracts dust better than 5- or 6-hole products — increasing cut and dramatically increasing disc life. The design does not need to align with the disc pad holes, making switching the discs fast, easy and convenient. Featuring ceramic 3M Precision-Shaped Grain, a revolutionary advancement in abrasive technology. The triangular shaped ceramic mineral is designed to slice through the substrate, rather than gouging or "plowing" like conventional abrasives, resulting in a disc that cuts up to 2x as fast as conventional abrasives. The J-weight cloth backing delivers outstanding tear resistance, durability and a consistent, uniform finish on a variety of substrates.



- COVERS A WIDE RANGE OF APPLICATIONS: Versatile disc handles applications from finishing and sanding to grinding and de-flashing
- DESIGNED FOR CLEAN SANDING: 3M Xtract™ proprietary multi-hole pattern provides superior dust extraction to prevent loading, increase productivity and provide a cleaner work environment
- VERSATILE PERFORMANCE: Disc performs well on aluminum, fiberglass, gelcoat, hard and soft woods

Product ID	Product Name	MOQ	OU
7100284886	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 40+ J-weight, 76 mm, Die 300LG, 50/Carton, 250 ea/Case	250	Each
7100284662	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 40+ J-weight, 127 mm, Die 500LG, 50/Carton, 250 ea/Case	250	Each
7100284769	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 40+ J-weight, 152 mm, Die 600LG, 50/Carton, 250 ea/Case	250	Each
7100284565	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 40+ J-weight, 203 mm, Die 800LG, 50/Carton, 250 ea/Case	250	Each
7100284341	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 60+ J-weight, 76 mm, Die 300LG, 50/Carton, 250 ea/Case	250	Each
7100284216	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 60+ J-weight, 127 mm, Die 500LG, 50/Carton, 250 ea/Case	250	Each
7100284218	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 60+ J-weight, 152 mm, Die 600LG, 50/Carton, 250 ea/Case	250	Each
7100284340	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 60+ J-weight, 203 mm, Die 800LG, 50/Carton, 250 ea/Case	250	Each
7100284521	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 80+ J-weight, 76 mm, Die 300LG, 50/Carton, 250 ea/Case	250	Each
7100284531	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 80+ J-weight, 127 mm, Die 500LG, 50/Carton, 250 ea/Case	250	Each
7100284530	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 80+ J-weight, 152 mm, Die 600LG, 50/Carton, 250 ea/Case	250	Each
7100284518	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 80+ J-weight, 203 mm, Die 800LG, 50/Carton, 250 ea/Case	250	Each
7100284266	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 120+ J-weight, 76 mm, Die 300LG, 50/Carton, 250 ea/Case	250	Each
7100284520	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 120+ J-weight, 127 mm, Die 500LG, 50/Carton, 250 ea/Case	250	Each
7100284508	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 120+ J-weight, 152 mm, Die 600LG, 50/Carton, 250 ea/Case	250	Each
7100284343	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 120+ J-weight, 203 mm, Die 800LG, 50/Carton, 250 ea/Case	250	Each
7100284506	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 150+ J-weight, 76 mm, Die 300LG, 50/Carton, 250 ea/Case	250	Each
7100284353	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 150+ J-weight, 127 mm, Die 500LG, 50/Carton, 250 ea/Case	250	Each
7100284342	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 150+ J-weight, 152 mm, Die 600LG, 50/Carton, 250 ea/Case	250	Each
7100284344	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 150+ J-weight, 203 mm, Die 800LG, 50/Carton, 250 ea/Case	250	Each
7100282513	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 180+ J-weight, 76 mm, Die 300LG, 50/Inner, 250 ea/Case	250	Each
7100282219	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 180+ J-weight, 127 mm, Die 500LG, 50/Carton, 250 ea/Case	250	Each
7100281804	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 180+ J-weight, 152 mm, Die 600LG, 50/Carton, 250 ea/Case	250	Each
7100281803	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 180+ J-weight, 203 mm, Die 800LG, 50/Carton, 250 ea/Case	250	Each
7100282510	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 220+ J-weight, 76 mm, Die 300LG, 50/Inner, 250 ea/Case	250	Each
7100281811	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 220+ J-weight, 127 mm, Die 500LG, 50/Carton, 250 ea/Case	250	Each
7100281806	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 220+ J-weight, 152 mm, Die 600LG, 50/Carton, 250 ea/Case	250	Each
7100281810	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 220+ J-weight, 203 mm, Die 800LG, 50/Carton, 250 ea/Case	250	Each
7100284356	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 320+ J-weight, 76 mm, Die 300LG, 50/Carton, 250 ea/Case	250	Each
7100284268	3M Xtract <sup>™</sup> Cubitron <sup>™</sup> II Cloth Disc 900DZ, 320+ J-weight, 127 mm, Die 500LG, 50/Carton, 250 ea/Case	250	Each
7100284271	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 320+ J-weight, 152 mm, Die 600LG, 50/Carton, 250 ea/Case	250	Each
7100284267	3M Xtract™ Cubitron™ II Cloth Disc 900DZ, 320+ J-weight, 203 mm, Die 800LG, 50/Carton, 250 ea/Case	250	Each
	, , , , , , , , , , , , , , , , , , , ,		



#### **Paper Discs**

#### 3M™ Cubitron™ II Hookit™ Disc 950U

3M™ Cubitron™ II Hookit™ Disc 950U is an abrasive disc designed to deliver high performance in body-in-white applications. It's powered by fast-cutting, long-lasting 3M Precision-Shaped Grain in a super-open-coat construction that resists loading with sanding swarf. The E-weight paper backing is specially designed for sanding metal.



- Ideal for prepping and repairing flat surfaces, including body-in-white applications
- Super-open-coat construction for reduced loading allowing metal and paint particles to escape
- 3M™ Precision-Shaped Grain delivers a consistent, high cut-rate and long life

Product ID	Product Name	MOQ	OU
7100190726	3M™ Cubitron™ II Hookit™ Disc 950U, 127 mm, 5-Hole, 60+	250	Each
7100190724	3M™ Cubitron™ II Hookit™ Disc 950U, 127 mm, 5-Hole, 80+	250	Each
7100190722	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Disc 950U, 127 mm, 5-Hole, 120+	250	Each
7100190725	3M™ Cubitron™ II Hookit™ Disc 950U, 127 mm, 5-Hole, 150+	250	Each
7100190723	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Disc 950U, 127 mm, 5-Hole, 180+	250	Each
7100187017	3M™ Cubitron™ II Hookit™ Disc 950U, 127 mm, No Hole, 60+	250	Each
7100187016	3M™ Cubitron™ II Hookit™ Disc 950U, 127 mm, No Hole, 80+	250	Each
7100187015	3M™ Cubitron™ II Hookit™ Disc 950U, 127 mm, No Hole, 120+	250	Each
7100187014	3M™ Cubitron™ II Hookit™ Disc 950U, 127 mm, No Hole, 150+	250	Each
7100187013	3M™ Cubitron™ II Hookit™ Disc 950U, 127 mm, No Hole, 180+	250	Each
7100226878	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, 15-Hole, 60+	250	Each
7100226892	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Disc 950U, 152 mm, 15-Hole, 80+	250	Each
7100226879	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, 15-Hole, 120+	250	Each
7100226891	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Disc 950U, 152 mm, 15-Hole, 150+	250	Each
7100226890	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, 15-Hole, 180+	250	Each
7100226887	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, 17-Hole, 60+	250	Each
7100226884	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, 17-Hole, 80+	250	Each
7100226886	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, 17-Hole, 120+	250	Each
7100226885	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Disc 950U, 152 mm, 17-Hole, 150+	250	Each
7100226888	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, 17-Hole, 180+	250	Each
7100190718	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Disc 950U, 152 mm, No Hole, 60+	250	Each
7100190719	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, No Hole, 80+	250	Each
7100190721	3M <sup>™</sup> Cubitron <sup>™</sup> II Hookit <sup>™</sup> Disc 950U, 152 mm, No Hole, 120+	250	Each
7100190720	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, No Hole, 150+	250	Each
7100190717	3M™ Cubitron™ II Hookit™ Disc 950U, 152 mm, No Hole, 180+	250	Each



#### 3M Xtract™ Paper Disc 236U

3M Xtract™ Paper Disc 236U features a 3M™ proprietary multi-hole pattern for improved dust extraction in finishing applications. Part of the 3M Xtract Series, designed for optimal dust removal. Our innovative multi-hole pattern extracts dust better than 5- or 6-hole products — increasing cut and dramatically increasing disc life. The design does not need to align with the disc pad holes, making switching the discs fast, easy, and convenient. Advanced Series Abrasives from 3M are designed to deliver an unbeatable combination of performance and value. Open coat construction and a load-resistant coating further prevent clogging.



- 3M Xtract™ proprietrary multi-hole pattern provides superior dust extraction to prevent loading, increase productivity, and provide a cleaner work environment
- Open coat and load-resistant coating prevents clogging to optimize cut and product life
- 3M™ Hookit™ attachment system provides easy disc changes and optimizes disc life

Product ID	Product Name	MOQ	OU
7000119606	3M Xtract <sup>™</sup> Paper Disc 236U, 76 mm, 300LG, P320	50	Each
7000119607	3M Xtract <sup>™</sup> Paper Disc 236U, 76 mm, 300LG, P400, C-Weight	50	Each
7000119608	3M Xtract <sup>™</sup> Paper Disc 236U, 76 mm, 300LG, P500, C-Weight	50	Each
7010029935	3M Xtract <sup>™</sup> Paper Disc 236U, 127 mm, 500LG, P500	50	Each
7010029932	3M Xtract <sup>™</sup> Paper Disc 236U, 127 mm, P240	250	Each
7010029933	3M Xtract <sup>™</sup> Paper Disc 236U, 127 mm, P320	50	Each
7010029934	3M Xtract <sup>™</sup> Paper Disc 236U, 127 mm, P400	250	Each
7100078157	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, 600LG, P220	50	Each
7100078181	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, 600LG, P500	50	Each
7100078180	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, 600LG, P400, C-Weight	250	Each
7100078152	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, P80, C-Weight	250	Each
7100078153	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, P100	50	Each
7100078154	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, P120	250	Each
7100078155	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, P150	50	Each
7100078156	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, P180	250	Each
7100078158	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, P240	50	Each
7100078159	3M Xtract <sup>™</sup> Paper Disc 236U, 152 mm, P320	50	Each



#### **Non-woven Discs**

#### Scotch-Brite™ Clean and Strip XT Pro Disc

Scotch-Brite™ Clean and Strip XT Pro Disc features silicon carbide abrasive mineral incorporated into an open nylon web. Our discs effectively remove rust, paint, mill scale, coatings and adhesives from surfaces without significantly altering the base material.



- Removes rust, paint, mill scale and coatings from metal fast
- High-strength fibre resists chunking and performs well on edges
- High conformability provides a larger contact patch for faster removal rates

Product ID	Product Name	MOQ	OU
7100192708	Scotch-Brite™ Clean and Strip XT Pro Disc XA-ZS, 75 mm x 25 mm x 6mm, S XCRS, Purple	10	Each
7100192711	Scotch-Brite™ Clean and Strip XT Pro Disc XA-ZS, 100 mm x 25 mm x 6 mm, S XCRS, Purple	10	Each
7100192333	Scotch-Brite™ Clean and Strip XT Pro Disc XO-DB, 115 mm x 22 mm, S XCRS, Purple	10	Each
7100192334	Scotch-Brite™ Clean and Strip XT Pro Disc XO-DB, 178 mm x 22 mm, S XCRS, Purple	10	Each
7100176374	Scotch-Brite™ Clean and Strip XT Pro Disc XO-DC, 100 mm x 13 mm, S XCRS, Purple	30	Each
7100176347	Scotch-Brite™ Clean and Strip XT Pro Disc XO-DC, 150 mm x 13 mm, S XCRS, Purple	20	Each
7100176348	Scotch-Brite™ Clean and Strip XT Pro Disc XO-DC, 200 mm x 13 mm, S XCRS, Purple	12	Each
7100192330	Scotch-Brite™ Clean and Strip XT Pro Disc XO-RD, 115 mm x 22 mm, S XCRS, Purple	10	Each
7100192331	Scotch-Brite™ Clean and Strip XT Pro Disc XO-RD, 125 mm x 22 mm, S XCRS, Purple	10	Each
7100192335	Scotch-Brite™ Clean and Strip XT Pro Disc XO-RD, 125 mm x M14, S XCRS, Purple	10	Each
7100192332	Scotch-Brite™ Clean and Strip XT Pro Disc XO-RD, 178 mm x 22 mm , S XCRS, Purple	10	Each
7100192707	Scotch-Brite™ Clean and Strip XT Pro Disc XO-ZS, 75 mm x 13 mm x 6mm, S XCRS, Purple	10	Each
7100192709	Scotch-Brite <sup>™</sup> Clean and Strip XT Pro Disc XO-ZS, 100 mm x 13 mm x 6 mm, S XCRS, Purple	10	Each
7100192710	Scotch-Brite™ Clean and Strip XT Pro Disc XO-ZS, 150 mm x 13 mm x 8 mm, S XCRS, Purple	6	Each



## Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc

Scotch-Brite<sup>TM</sup> Clean and Strip XT Pro Extra Cut Disc features aluminium oxide abrasive mineral incorporated into an open nylon web. Our discs are designed to remove tough coatings, such as heavy rust, thick paint and corrosion, while also blending and refining the bare metal underneath.




- Quickly removes heavy rust, thick paint, corrosion and cleans welds
- Aluminium oxide mineral aggressively removes top layer and refines to the bare metal underneath
- High conformability provides a larger contact patch for faster removal rates

Product ID	Product Name	MOQ	OU
7100192736	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XB-ZS, 75 mm x 25 mm x 6 mm, A XCRS, Green	10	Each
7100192739	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XB-ZS, 100 mm x 25 mm x 6 mm, A XCRS, Green	10	Each
7100192339	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-DB, 115 mm x 22 mm, A XCRS, Green	10	Each
7100192340	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-DB, 178 mm x 22 mm, A XCRS, Green	10	Each
7100175138	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-DC, 100 mm x 13 mm, A XCRS, Green	30	Each
7100175139	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-DC, 150 mm x 13 mm, A XCRS, Green	20	Each
7100191877	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-DC, 150mm x 22mm, A XCRS, Green	20	Each
7100175140	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-DC, 200 mm x 13 mm, A XCRS, Green	12	Each
7100192336	Scotch-Brite <sup>™</sup> Clean and Strip XT Pro Extra Cut Disc XC-RD, 115 mm x 22 mm, A XCRS, Green	10	Each
7100192337	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-RD, 125 mm x 22 mm, A XCRS, Green	10	Each
7100192341	Scotch-Brite <sup>™</sup> Clean and Strip XT Pro Extra Cut Disc XC-RD, 125 mm x M14, A XCRS, Green	10	Each
7100192338	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-RD, 178 mm x 22 mm , A XCRS, Green	10	Each
7100192735	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-ZS, 75 mm x 13 mm x 6 mm, A XCRS, Green	10	Each
7100192737	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-ZS, 100 mm x 13 mm x 6 mm, A XCRS, Green	10	Each
7100192738	Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc XC-ZS, 150 mm x 13 mm x 8 mm, A XCRS, Green	6	Each

## Scotch-Brite™ Fiber Backed Clean and Strip Disc

Scotch-Brite™ Fibre Backed Clean and Strip Disc is specially engineered to effectively clean welds, remove rust and strip paint. Our extra coarse grade open web discs provide a smooth running loading resistant wheel and fibre backing for a superb finish in soft or aggressive applications.



- Reach into tight corners for complete cleaning, stripping and surface preparation
- Cover a bigger surface area than with wire brushes
- Uses extra coarse grade silicon carbide for aggressive cutting and a finer finish than with wire brushes

Product ID	Product Name	MOQ	OU
7000077940	Scotch-Brite™ Fiber Backed Clean and Strip Disc CS-DB. 115 mm x 63 mm x 22 mm. A CRS	10	Each



## Scotch-Brite™ Surface Conditioning Disc SC-DH

Scotch-Brite™ Surface Conditioning Disc comes in a wide variety of grades and sizes and is an ideal first-step for cleaning, blending, deburring, and finishing. Durable, non-woven fiber construction conforms well on irregular or contoured surfaces without undercutting or damaging the base material.



- Variety of abrasive grades and sizes provide an ideal starting point for cleaning, finishing, blending, and light deburring
- Open web material runs cool and resists loading for prolonged operation
- Conformable disc conditions surfaces without gouging, undercutting, or damaging the base material

Product ID	Product Name	MOQ	OU
7100233775	Scotch-Brite™ Surface Conditioning Disc SC-DH, 178 mm x 22 mm, A MED	20	Each
7100233805	Scotch-Brite™ Surface Conditioning Disc SC-DH, 178 mm x No Hole, A VFN	20	Each
7100233605	Scotch-Brite <sup>™</sup> Surface Conditioning Disc SC-DH, 100 mm x 16 mm, A CRS , Brown	22	Each
7100233780	Scotch-Brite™ Surface Conditioning Disc SC-DH, 100 mm x 16 mm, A MED, Red	22	Each
7100233781	Scotch-Brite <sup>™</sup> Surface Conditioning Disc SC-DH, 100 mm x 16 mm, A VFN, Blue	22	Each
7100200101	Scotch-Brite™ Surface Conditioning Disc SC-DH, 100 mm x 16 mm, No Slot, A CRS,	40	Each
7100233608	Scotch-Brite™ Surface Conditioning Disc SC-DH, 115 mm x 22 mm, A CRS, Brown	20	Each
7100233774	Scotch-Brite™ Surface Conditioning Disc SC-DH, 115 mm x 22 mm, A CRS, Brown	20	Each
7100233812	Scotch-Brite™ Surface Conditioning Disc SC-DH, 115 mm x 22 mm, A MED, Red	20	Each
7100233795	Scotch-Brite™ Surface Conditioning Disc SC-DH, 115 mm x 22 mm, A VFN, Blue	20	Each
7100233813	Scotch-Brite™ Surface Conditioning Disc SC-DH, 115 mm x No Hole, S SFN	20	Each
7000046019	Scotch-Brite <sup>™</sup> Surface Conditioning Disc SC-DH, 115 mm, No Hole, A CRS, Brown	50	Each
7000046018	Scotch-Brite™ Surface Conditioning Disc SC-DH, 115 mm, No Hole, A MED, Red	50	Each
7100233776	Scotch-Brite <sup>™</sup> Surface Conditioning Disc SC-DH, 115 mm, No Hole, A MED, Red	20	Each
7100233439	Scotch-Brite™ Surface Conditioning Disc SC-DH, 115 mm, No Hole, A VFN, Blue	20	Each
7100233609	Scotch-Brite™ Surface Conditioning Disc SC-DH, 125 mm x 22 mm, A CRS, Brown	20	Each
7100233803	Scotch-Brite™ Surface Conditioning Disc SC-DH, 125 mm x 22 mm, A MED, Red	20	Each
7100234045	Scotch-Brite™ Surface Conditioning Disc SC-DH, 125 mm x 22 mm, A VFN	20	Each
7100233623	Scotch-Brite™ Surface Conditioning Disc SC-DH, 125 mm, No Hole, A CRS, Brown	20	Each
7100233806	Scotch-Brite™ Surface Conditioning Disc SC-DH, 125 mm, No Hole, A MED, Red	20	Each
7100233440	Scotch-Brite <sup>™</sup> Surface Conditioning Disc SC-DH, 125 mm, No Hole, A VFN, Blue	20	Each
7100233777	Scotch-Brite™ Surface Conditioning Disc SC-DH, 150 mm, No Hole, A VFN, Blue	20	Each
7100233794	Scotch-Brite <sup>™</sup> Surface Conditioning Disc SC-DH, 178 mm x 22 mm, A CRS, Brown	20	Each
7100233809	Scotch-Brite™ Surface Conditioning Disc SC-DH, 178 mm x 22 mm, A VFN, Blue	20	Each
7100200772	Scotch-Brite <sup>™</sup> Surface Conditioning Disc SC-DH, 178 mm x 22 mm, No Slot, A CRS,	10	Each
7100233606	Scotch-Brite™ Surface Conditioning Disc SC-DH, 178 mm, No Hole, A CRS, Brown	20	Each
7100233804	Scotch-Brite™ Surface Conditioning Disc SC-DH, 178 mm, No Hole, A MED, Red	20	Each



## Scotch-Brite™ SE Surface Conditioning Disc SE-DB

Scotch-Brite™ SE Surface Conditioning Disc combines an aggressive, non-woven disc to perform heavy-duty deburring and finishing with the efficiency of a hook and loop attachment system. Our heavy-duty non-woven fiber construction conforms well to help preserve edges as well as irregular or contoured surfaces.

- Provides extra cut and longer life than SC and PD Surface Conditioning discs for heavy duty deburring and finishing
- High, fast cutting yet conformable disc is ideal for edge deburring
- Conformability combined with secure, hook and loop attachment provides aggressive cutting without damaging the base material

Product ID	Product Name	MOQ	OU
7100233797	Scotch-Brite™ SE Surface Conditioning Disc SE-DB, 100 mm x NH, A CRS	25	Each
7100233779	Scotch-Brite™ SE Surface Conditioning Disc SE-DB, 115 mm x No Hole, A CRS	20	Each
7100233816	Scotch-Brite™ SE Surface Conditioning Disc SE-DB, 178 mm x No Hole, A CRS	120	Each
7000046034	Scotch-Brite™ SE Surface Conditioning Disc SE-DH, 114 mm, No Hole, A MED	50	Each
7000046091	Scotch-Brite™ SE Surface Conditioning Disc SE-DH, 127 mm , No Hole, A MED	50	Each
7100233811	Scotch-Brite <sup>™</sup> SE Surface Conditioning Disc, SE-DH, A CRS, 100 mm x 16 mm	330	Each
7000046214	Scotch-Brite™ SE Surface Conditioning Disc SE-BS, 114 mm, No Hole, A FIN	50	Each
7100233607	Scotch-Brite <sup>™</sup> SE Surface Conditioning Disc SE-DB, 115 mm x 22 mm, A CRS	20	Each
7100200774	Scotch-Brite™ SE Surface Conditioning Disc SE-DB, 178 mm x 22 mm, A CRS	40	Each

## Scotch-Brite™ Surface Conditioning Disc SL-DH

Durable, aggressive non-woven abrasive product for weld refinement applications. Blends and finishes consistently,often in one step.

- Good flexibility
- Fast cutting
- Most durable finishing options



Product ID	Product Name	MOQ	OU
7100233614	Scotch-Brite™ Surface Conditioning Disc SL-DH, Heavy Duty, 100 mm x 16 mm, A CRS	22	Each
7100233783	Scotch-Brite™ Surface Conditioning Disc SL-DH, Heavy Duty, 178 mm x 22 mm, A CRS	100	Each
7100233801	Scotch-Brite™ Surface Conditioning Disc SL-DH, Super Duty, 100 mm x 16 mm, A CRS	22	Each
7100233819	Scotch-Brite™ Surface Conditioning Disc SL-DH, 115 mm x 22 mm, A CRS HD	20	Each
7100234046	Scotch-Brite™ Surface Conditioning Disc SL-DH, 115 mm x 22 mm, A CRS SD	20	Each



## Scotch-Brite™ Light Grinding and Blending Disc GB-DH

Scotch-Brite™ Light Grinding and Blending Disc uses a ceramic abrasive grain blend to achieve a high cut-rate for optimal weld grinding and blending in mild-steel applications. In these instances, Light Grinding and Blending discs are designed to effectively blend and refine a grade 36 scratch or finer.

- Grinds and blends in a single step
- 3M™ ceramic aluminum oxide abrasives cut fast and consistent over the life of the disc
- Durable construction resists edge wear



Product ID	Product Name	MOQ	OU
7000046244	Scotch-Brite™ Light Grinding and Blending Disc GB-DH, 114 mm x 22 mm, Heavy Duty	50	Each
7000046263	Scotch-Brite™ Light Grinding and Blending Disc GB-DH, 115 mm x 22 mm, Heavy Duty	50	Each
7000046264	Scotch-Brite™ Light Grinding and Blending Disc GB-DH, 115 mm x 22 mm, Super Duty	50	Each
7000046245	Scotch-Brite™ Light Grinding and Blending Disc GB-DH, 127 mm x 22 mm, Heavy Duty	50	Each
7000046247	Scotch-Brite™ Light Grinding and Blending Disc GB-DH, 127 mm x 22 mm, Super Duty	50	Each
7000046248	Scotch-Brite™ Light Grinding and Blending Disc GB-DH, 178 mm x 22 mm, Heavy Duty	25	Each
7000046249	Scotch-Brite™ Light Grinding and Blending Disc GB-DH, 178 mm x 22 mm, Heavy Duty	25	Each
7000046246	Scotch-Brite™ Roloc™ Light Grinding and Blending Disc , 101 mm x 15 mm, A CRS	100	Each

#### Scotch-Brite™ Deburr and Finish PRO Unitized Disc DP-UD

Our Scotch-Brite™ Deburr and Finish PRO Unitized Disc is a new disc designed to make a variety of metalworking applications easier and more efficient for industrial professionals. Typically, abrasives excel in one area: deburring, finishing or blending. This multi-purpose disc is unique, because it's engineered to do all three.



- Unitized production enhances abrasive durability and strength, helping prolong service life
- 3M precision-shaped grain is engineered to cut fast and sharp, enabling quicker burr removal
- Open coat construction permits dust and debris to escape, minimizing loading

Product ID	Product Name	MOQ	OU
7010412238	Scotch-Brite™ Deburr and Finish PRO Unitized Disc DP-UD, 114 mm x 22 mm, 2S FIN	5	Each

#### Scotch-Brite™ Clean and Strip Disc

Scotch-Brite™ Clean and Strip Disc is designed to effectively clean welds, remove rust and strip paint. Our extra coarse grade open web discs provide a smooth running loading-resistant wheel, which is ideal for removing soft coatings.



- Thin width gets into tight corners for complete cleaning, stripping, and surface prep
- Provides greater surface area than wire brushes
- Extra coarse grade silicon carbide provides aggressive cutting and leaves a finish than wire brushes

Product ID	Product Name	MOQ	OU
7100182579	Scotch-Brite™ Clean and Strip Disc CG-DC, 200 mm x 13 mm, Blue, S XCRS	12	Each
7100182637	Scotch-Brite™ Clean and Strip Disc CS-RD, 150 mm x 13 mm, Blue	20	Each



### Scotch-Brite™ Cut and Polish Disc

Scotch-Brite™ Cut and Polish Disc is engineered to produce satin or high lustre finishes and can be used for cleaning or light deburring on a variety of metals. Our cut and polish discs feature a durable open-web construction designed to resist loading and greatly increase the life of the disc.

- Aluminium oxide mineral delivers an aggressive cut with a polished surface
- Durable non-woven web construction resists loading, prolonging service life of the disc
- Versatile disc may be used on bench motor or straight shaft tool

Product ID	Product Name	MOQ	OU
7010329036	Scotch-Brite™ Cut and Polish Disc, CP-DC, A/O Very Fine, 152 mm x 12,7 mm, 100 ea/Case	100	Each

## Scotch-Brite™ Precision Surface Conditioning Disc

Scotch-Brite™ Precision Surface Conditioning Discs set a new standard in surface conditioning performance. These reformulated multi-purpose discs feature 3M Precision-Shaped Grain technology incorporated into the nonwoven web, bringing a new level of productivity and abrasive life to the Scotch-Brite™ lineup.

- Now with 3M<sup>™</sup> precision shaped grain technology setting a new standard of performance.
- Designed for ease of use and consistent surface finishing results
- Conformable disc conditions surfaces without gounging, undercutting, or damaging the base material.



Product ID	Product Name	MOQ	OU
7100275261	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Coarse, 100 mm x 16 mm, 25 per inner, 100 per case	100	Each
7100274705	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Coarse, 100 mm x NH, 25 per inner, 100 per case	100	Each
7100274279	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Coarse, 115 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100274273	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Coarse, 115 mm x NH, 25 per inner, 100 per case	100	Each
7100274275	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Coarse, 125 mm x NH, 25 per inner, 100 per case	100	Each
7100274227	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Coarse, 125 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100274660	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Coarse, 150 mmx NH, 25 per inner, 100 per case	100	Each
7100274665	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Coarse, 178 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100275259	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Coarse, 178 mmx NH, 25 per inner, 100 per case	100	Each
7100275260	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Extra Coarse, 100 mm x 16 mm, 25 per inner, 100 per case	100	Each
7100274706	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Extra Coarse, 100 mm x NH, 25 per inner, 100 per case	100	Each
7100274225	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Extra Coarse, 115 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100274270	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Extra Coarse, 115 mm x NH, 25 per inner, 100 per case	100	Each
7100274272	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Extra Coarse, 125 mm x NH, 25 per inner, 100 per case	100	Each
7100274226	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Extra Coarse, 125 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100274661	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Extra Coarse, 150 mmx NH, 25 per inner, 100 per case	100	Each
7100274664	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Extra Coarse, 178 mm x 22,23 mm, 25 per inner, 100 per case	100	Each



## Scotch-Brite™ Precision Surface Conditioning Disc

Scotch-Brite™ Precision Surface Conditioning Discs set a new standard in surface conditioning performance. These reformulated multi-purpose discs feature 3M Precision-Shaped Grain technology incorporated into the nonwoven web, bringing a new level of productivity and abrasive life to the Scotch-Brite™ lineup.

- Now with 3M<sup>™</sup> precision shaped grain technology setting a new standard of performance.
- Designed for ease of use and consistent surface finishing results
- Conformable disc conditions surfaces without gounging, undercutting, or damaging the base material.

Product ID	Product Name	MOQ	OU
7100275256	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Extra Coarse, 178 mmx NH, 25 per inner, 100 per case	100	Each
7100275837	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Fine, 100 mm x 16 mm, 25 per inner, 100 per case	100	Each
7100274670	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Fine, 100 mm x NH, 25 per inner, 100 per case	100	Each
7100275836	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Fine, 115 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100274222	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Fine, 115 mm x NH, 25 per inner, 100 per case	100	Each
7100274274	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Fine, 125 mm x NH, 25 per inner, 100 per case	100	Each
7100276268	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Fine, 125 mm x 22.23 mm	100	Each
7100274663	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Fine, 150 mmx NH, 25 per inner, 100 per case	200	Each
7100274667	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Fine, 178 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100275255	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Fine, 178 mmx NH, 25 per inner, 100 per case	100	Each
7100275899	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Medium, 100 mm x 16 mm, 25 per inner, 100 per case	100	Each
7100274669	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Medium, 100 mm x NH, 25 per inner, 100 per case	100	Each
7100275844	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Medium, 115 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100274223	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Medium, 115 mm x NH, 25 per inner, 100 per case	100	Each
7100274271	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Medium, 125 mm x NH, 25 per inner, 100 per case	100	Each
7100274229	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Medium, 125 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100274662	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Medium, 150 mmx NH, 25 per inner, 100 per case	100	Each
7100274666	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Medium, 178 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100275258	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Medium, 178 mmx NH, 25 per inner, 100 per case	100	Each
7100275838	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Very Fine, 100 mm x 16 mm, 25 per inner, 100 per case	100	Each
7100274671	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Very Fine, 100 mm x NH, 25 per inner, 100 per case	100	Each
7100275845	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Very Fine, 115 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100274224	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Very Fine, 115 mm x NH, 25 per inner, 100 per case	100	Each
7100274277	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Very Fine, 125 mm x NH, 25 per inner, 100 per case	100	Each
7100274228	Scotch-Brite <sup>™</sup> Precision Surface Conditioning Disc, PN-DH, Very Fine, 125 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100274704	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Very Fine, 150 mmx NH, 25 per inner, 100 per case	100	Each
7100274668	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Very Fine, 178 mm x 22,23 mm, 25 per inner, 100 per case	100	Each
7100275253	Scotch-Brite™ Precision Surface Conditioning Disc, PN-DH, Very Fine, 178 mmx NH, 25 per inner, 100 per case	100	Each



## **Quick Change Discs**

#### 3M™ Cubitron™ II Roloc™ Fibre Disc 982C

3M™ Cubitron™ II Roloc™ Fibre Disc 982C offers outstanding performance and productivity for medium to high pressure grinding applications. Our discs are perfect for use on carbon steel when a smaller disc is needed.



- Features 3M Precision Shaped Grain which gives improved cut and longevity
- Disc life is significantly increased, completing more parts per disc for less disc changes
- Roloc™ quick attachment system makes for easy disc changes between grades or applications

Product ID	Product Name	MOQ	OU
7000118429	3M™ Cubitron™ II Roloc™ Fibre Disc 982C, 50 mm, 36+	200	Each
7000044902	3M <sup>™</sup> Cubitron <sup>™</sup> II Roloc <sup>™</sup> Fibre Disc 982C, 76 mm, R300V, 60+	200	Each
7100126838	3M™ Cubitron™ II Roloc™ Fibre Disc 982C, 76 mm, RS300VM, 36+	200	Each

### 3M™ Cubitron™ II Roloc™ Cloth Disc 984F

3M™ Cubitron™ II Roloc™ Durable Edge Disc 984F offers a superior solution for tackling medium to high pressure grinding applications when a smaller-sized disc is needed. It excels in stainless steel, cobalt chrome, and nickel alloy applications.



- 3M Precision-Shaped Grain (PSG) maintains super-sharp points that cut exceptionally fast with less pressure
- Disc life is significantly longer, completing more parts per disc and requiring fewer disc changes
- Grinding aid incorporated on the disc minimizes grinding temperatures for stainless steel and other heat-sensitive alloys

Product ID	Product Name	MOQ	OU
7000045166	3M™ Cubitron™ II Roloc™ Cloth Disc 984F, 38 mm, R150S, 36+	200	Each
7000045171	3M <sup>™</sup> Cubitron <sup>™</sup> II Roloc <sup>™</sup> Cloth Disc 984F, 38 mm, R150S, 60+	200	Each
7000045175	3M <sup>™</sup> Cubitron <sup>™</sup> II Roloc <sup>™</sup> Cloth Disc 984F, 38 mm, R150S, 80+	200	Each
7100001474	3M™ Cubitron™ II Roloc™ Cloth Disc 984F, 50 mm, R200P, 36+	200	Each
7100001475	3M™ Cubitron™ II Roloc™ Cloth Disc 984F, 50 mm, R200P, 60+	200	Each
7100001473	3M™ Cubitron™ II Roloc™ Cloth Disc 984F, 50 mm, R200P, 80+	200	Each
7000045167	3M™ Cubitron™ II Roloc™ Cloth Disc 984F, 76 mm, R300V, 36+	200	Each
7000045172	3M™ Cubitron™ II Roloc™ Cloth Disc 984F, 76 mm, R300V, 60+	200	Each
7000045176	3M <sup>™</sup> Cubitron <sup>™</sup> II Roloc <sup>™</sup> Cloth Disc 984F, 76 mm, R300V, 80+	200	Each



### 3M™ Cubitron™ II Roloc™ Disc 984F

3M™ Cubitron™ II Roloc™ Disc 984F offers a superior solution for tackling metalworking applications where flexibility is required, such as weld grinding, beveling, flame-cut edge clean-up and deburring.

- 3M Precision Shaped Ceramic Grain (PSG) maintains super-sharp points that cut exceptionally fast with less pressure compared to conventional abrasives
- Disc life is significantly longer, completing more parts per disc and requiring fewer disc changes compared to conventional abrasives
- Grinding aid incorporated on the disc minimizes grinding temperatures for stainless steel and other heat-sensitive alloys



Product ID	Product Name	MOQ	OU
7010361116	3M™ Cubitron™ II Roloc™ Cloth Disc 984F, 50 mm, R200P, 60+	200	Each

## 3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A

3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A is a poly-cotton backed, heavyweight, sharp cutting disc. Our strong, durable discs are easy to use and ideal for edge work.

- Precision-Shaped Grain delivers sharp, cool, consistent cutting action
- Poly-cotton backing offers water resistance and great tensile strength, enhancing durability of grains
- Heavy weight backing makes it more durable and tear resistant, great for edge work



7100077039       3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 50 mm, 40+       200       Eac         7100077047       3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 50 mm, 60+       200       Eac         7100076925       3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 50 mm, 80+       200       Eac         7100076933       3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 50 mm, 120+       200       Eac
7100076925 3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 50 mm, 80+ 200 Eac 7100076933 3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 50 mm, 120+ 200 Eac
7100076933 3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 50 mm, 120+ 200 Eac
7400077040 OMMOU'S MURLING HIELDS 0474 70 40.
7100077040 3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 76 mm, 40+ 200 Eac
7100076898 3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 76 mm, 60+ 200 Eac
7100076926 3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 76 mm, 80+ 200 Eac
7100076934 3M™ Cubitron™ II Roloc™ Durable Edge Disc 947A, 76 mm, 120+ 200 Eac



### 3M™ Roloc™ Fibre Disc 782C

3M™ Roloc™ Fibre Disc 782C is a fibre disc featuring our advanced abrasive technology, 3M Precision Shaped Grain. These discs have a stiff fibre backing and strong resin bond that provide durability and tear-resistance.

- Cuts carbon steel rapidly
- Premium mineral excels at heavy weight applications
- 3M Precision Shaped Grain yields higher cut rates



Product ID	Product Name	MOQ	OU
7100100976	3M™ Roloc™ Fibre Disc 782C, 50 mm, 36+	200	Each
7100100989	3M™ Roloc™ Fibre Disc 782C, 50 mm, 60+	200	Each
7100100999	3M™ Roloc™ Fibre Disc 782C, 50 mm, 80+	200	Each
7100100942	3M™ Roloc™ Fibre Disc 782C, 76 mm, 36+	200	Each
7100100885	3M™ Roloc™ Fibre Disc 782C, 76 mm, 60+	200	Each
7100100986	3M™ Roloc™ Fibre Disc 782C, 76 mm, 80+	200	Each

### 3M™ Roloc™ Fibre Disc 787C

3M™ Roloc™ Fibre Disc 787C is a fibre disc featuring our advanced abrasive technology, 3M Precision Shaped Grain. These discs have a stiff fibre backing and strong resin bond that provide durability and tear-resistance. They are constructed with a grinding aid.



- Cuts hard and fast to grind metals like stainless steel and high nickel alloys
- 3M Precision Shaped Grain yields higher cut rates and excels at heavy weight applications
- Grinding aid minimises grinding temperatures for heat-sensitive alloys

Product ID	Product Name	MOQ	OU
7100100974	3M™ Roloc™ Fibre Disc 787C, 50 mm, 36+	200	Each
7100100982	3M <sup>™</sup> Roloc <sup>™</sup> Fibre Disc 787C, 50 mm, 60+	200	Each
7100100962	3M <sup>™</sup> Roloc <sup>™</sup> Fibre Disc 787C, 50 mm, 80+	200	Each
7100100964	3M <sup>™</sup> Roloc <sup>™</sup> Fibre Disc 787C, 50 mm, 120+	200	Each
7100100981	3M <sup>™</sup> Roloc <sup>™</sup> Fibre Disc 787C, 75 mm, 36+	200	Each
7100100979	3M <sup>™</sup> Roloc <sup>™</sup> Fibre Disc 787C, 75 mm, 60+	200	Each
7100100966	3M <sup>™</sup> Roloc <sup>™</sup> Fibre Disc 787C, 75 mm, 120+	200	Each
7100100961	3M <sup>™</sup> Roloc <sup>™</sup> Fibre Disc 787C, 76 mm, 80+	200	Each



### Scotch-Brite™ Roloc™ Clean and Strip XT Pro Disc

Scotch-Brite™ Roloc™ Clean and Strip XT Pro Disc features silicon carbide abrasive mineral incorporated into an open nylon web. Our discs effectively remove rust, paint, mill scale, coatings and adhesives from surfaces without significantly altering the base material.



- Removes rust, paint, mill scale and coatings from metal fast
- High-strength fibre resists chunking and performs well on edges
- High conformability provides a larger contact patch for faster removal rates

Product ID	Product Name	MOQ	OU
7100175521	Scotch-Brite™ Roloc™ Clean and Strip XT Pro Disc XO-DR, 50 mm, S XCRS, Purple	60	Each
7100173795	Scotch-Brite™ Roloc™ Clean and Strip XT Pro Disc XO-DR, 76 mm, S XCRS, Purple	40	Each
7100192704	Scotch-Brite™ Roloc™+ Clean and Strip XT Pro Disc XO-ZR, 100 mm x 13 mm x 6 mm, S XCRS, Purple	10	Each
7100192705	Scotch-Brite™ Roloc™+ Clean and Strip XT Pro Disc XO-ZR, 125 mm x 13 mm x 6 mm, S XCRS, Purple	8	Each
7100192706	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> + Clean and Strip XT Pro Disc XO-ZR, 150 mm x 13 mm x 6 mm, S XCRS, Purple	6	Each

### Scotch-Brite™ Roloc™ Clean and Strip XT Pro Extra Cut Disc

Scotch-Brite™ Roloc™ Clean and Strip XT Pro Extra Cut Disc features aluminium oxide abrasive mineral incorporated into an open nylon web. Our discs are designed to remove tough coatings, such as heavy rust, thick paint and corrosion, while also blending and refining the bare metal underneath.



- Quickly removes heavy rust, thick paint, corrosion and cleans welds
- Aluminium oxide mineral aggressively removes top layer and refines the bare metal underneath
- High conformability provides a larger contact patch for faster removal rates

Product ID	Product Name	MOQ	OU
7100179815	Scotch-Brite™ Roloc™ Clean and Strip XT Pro Extra Cut Disc XC-DR, 50 mm, A XCRS, Green	60	Each
7100173790	Scotch-Brite™ Roloc™ Clean and Strip XT Pro Extra Cut Disc XC-DR, 76 mm, A XCRS, Green	40	Each

## Scotch-Brite™ Roloc™+ Clean and Strip XT Pro Extra Cut Disc

Scotch-Brite™ Roloc™+ Clean and Strip XT Pro Extra Cut Disc features aluminium oxide abrasive mineral incorporated into an open nylon web. Our discs are designed to remove tough coatings, such as heavy rust, thick paint and corrosion while also blending and refining the bare metal underneath.



- Quickly removes heavy rust, thick paint, corrosion and cleans welds
- Aluminium oxide mineral aggressively removes top layer and refines the bare metal underneath
- High conformability provides a larger contact patch for faster removal rates

Product ID	Product Name	MOQ	OU
7100192712	Scotch-Brite™ Roloc™+ Clean and Strip XT Pro Extra Cut Disc XO-ZR, 100 mm x 13 mm x 6 mm, A XCRS, Green	10	Each
7100192733	Scotch-Brite™ Roloc™+ Clean and Strip XT Pro Extra Cut Disc XO-ZR, 125 mm x 13 mm x 6 mm, A XCRS, Green	8	Each
7100192734	Scotch-Brite™ Roloc™+ Clean and Strip XT Pro Extra Cut Disc XO-ZR, 150 mm x 13 mm x 6 mm, A XCRS, Green	6	Each



## Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR

The Scotch-Brite™ Roloc™ Surface Conditioning Disc combines our durable, non-woven disc with the efficient 3M™ Roloc™ quick-change attachment system for an effective disc that cleans, finishes, blends, and deburrs. Our non-woven fiber construction conforms well to help preserve irregular or contoured surfaces and the Roloc™ backing supports the disc for aggressive cutting.



- Tough non-woven disc aggressively deburrs and finishes
- Conformable, non-woven disc combined with Roloc backing allows for aggressive cutting
- Open-web construction resists loading and runs cool, allowing for consistent finishes

Product ID	Product Name	MOQ	OU
7000000704	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 25 mm, A CRS, Brown	200	Each
7000021280	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 25 mm, A MED, Red	200	Each
7000021279	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Surface Conditioning Disc SC-DR, 25 mm, A VFN, Blue	200	Each
7000045888	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 38 mm, A MED, Red	200	Each
7000028507	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Surface Conditioning Disc SC-DR, 50 mm, A CRS, Brown	100	Each
7000000752	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 50 mm, A CRS, Brown	200	Each
7000028506	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 50 mm, A MED, Red	100	Each
7000000751	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 50 mm, A MED, Red	200	Each
7000000750	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 50 mm, A VFN, Blue	200	Each
7000028508	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 50 mm, A VFN, Blue	100	Each
7000028509	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 50 mm, S FIN, Grey	100	Each
7000000753	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Surface Conditioning Disc SC-DR, 50 mm, S SFN, Grey	50	Each
7000046114	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 76 mm, A CRS, Brown	4	Carton
7000000756	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Surface Conditioning Disc SC-DR, 76 mm, A CRS, Brown	100	Each
7000000755	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 76 mm, A MED, Red	100	Each
7000046113	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 76 mm, A MED, Red	4	Carton
7000000754	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 76 mm, A VFN, Blue	100	Each
7000046108	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 76 mm, A VFN, Blue	4	Carton
7000028501	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 76 mm, S SFN, Grey	100	Each
7100007009	Scotch-Brite™ Roloc™ Surface Conditioning Disc SC-DR, 102 mm, A CRS	100	Each



### Scotch-Brite™ Roloc™ Surface Conditioning Disc SE-DR

Scotch-Brite™ Roloc™ SE Surface Conditioning Disc combines a coarse, non-woven disc to perform heavy-duty deburring and finishing with the efficiency of the 3M™ Roloc™ quick-change attachment system. Our heavy-duty non-woven fiber construction conforms well to help preserve irregular or contoured surfaces and our Roloc™ backing supports the disc to allow for aggressive cutting.



- Course, tough non-woven disc aggressively deburrs and finishes
- Open-web construction resists loading and runs cool, producing consistent finishes
- Conformable disc conditions surfaces without gouging, undercutting, or damaging the base material

Product ID	Product Name	MOQ	OU
7000046111	Scotch-Brite™ Roloc™ Surface Conditioning Disc SE-DR, 50 mm, A CRS, Brown	200	Each
7000046110	Scotch-Brite™ Roloc™ Surface Conditioning Disc SE-DR, 50 mm, A MED, Red	200	Each
7000042733	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Surface Conditioning Disc SE-DR, 76 mm, A CRS, Brown	100	Each
7000046112	Scotch-Brite™ Roloc™ Surface Conditioning Disc SE-DR, 76 mm, A MED, Red	100	Each
7000046149	Scotch-Brite™ Roloc™ Surface Conditioning Disc SE-DR, 76 mm, A VFN, Red	100	Each

## Scotch-Brite™ Roloc™ SL Surface Conditioning Disc

The Scotch-Brite™ Roloc™ SL Surface Conditioning Disc is a durable product that combines blending and finishing capability with aggressive cut. Our unique web construction and formulation allows the disc to resist loading while giving you an aggressive cut and long product life – on both edges and flat surfaces.



- Specially engineered light grinding and blending disc can last up to twice as long as other surface conditioning discs
- Blending and finishing capability saves process steps and provides desired finish without sacrificing cut-rate
- Versatile disc performs grindline refinement, metal blending, and surface preparation

Product ID	Product Name	MOQ	OU
7000121083	Scotch-Brite™ Roloc™ Surface Conditioning Disc SL-DR, 50 mm, A MED	200	Each
7000046219	Scotch-Brite™ Roloc™ Surface Conditioning Disc SL-DR, 50 mm, CRS, Heavy Duty	200	Each
7000046221	Scotch-Brite™ Roloc™ Surface Conditioning Disc SL-DR, 50 mm, CRS, Super Duty	200	Each
7000046218	Scotch-Brite™ Roloc™ Surface Conditioning Disc SL-DR, 75 mm, CRS, Heavy Duty	100	Each
7000046220	Scotch-Brite™ Roloc™ Surface Conditioning Disc SL-DR, 75 mm, CRS, Super Duty	100	Each
7100029968	Scotch-Brite™ Roloc™ Surface Conditioning Disc SL-DR, 76 mm, A CRS	100	Each
7000121082	Scotch-Brite™ Roloc™ Surface Conditioning Disc SL-DR, 76 mm, A MED	100	Each



## Scotch-Brite™ Roloc™ Light Grinding and Blending Disc GB-DR

We constructed our Scotch-Brite™ Roloc™ Light Grinding and Blending Discs with a ceramic abrasive grain blend to achieve a high cut-rate for optimal weld grinding and blending in mild-steel applications. In these instances, Light Grinding and Blending discs are designed to effectively blend and refine a grade 36 scratch or finer.




- Grinds and blends in a single step
- 3M<sup>™</sup> ceramic aluminum oxide abrasives combines high cut-rate with blending ability to eliminate finishing steps
- Disc backup pad helps provide high edge durability for consistent finishing and long disc life

Product ID	Product Name	MOQ	OU
7100019197	Scotch-Brite™ Roloc™ Light Grinding and Blending Disc GB-DR, 25 mm, A CRS	200	Each
7100048019	Scotch-Brite™ Roloc™ Light Grinding and Blending Disc GB-DR, 38 mm, A CRS	200	Each
7000046250	Scotch-Brite™ Roloc™ Light Grinding and Blending Disc GB-DR, 50 mm, Heavy Duty	200	Each
7000046251	Scotch-Brite™ Roloc™ Light Grinding and Blending Disc GB-DR, 50 mm, Super Duty	200	Each
7100007318	Scotch-Brite™ Roloc™ Light Grinding and Blending Disc GB-DR, 76 mm, Heavy Duty	100	Each
7100009310	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Light Grinding and Blending Disc GB-DR, 76 mm, Super Duty	100	Each

### Scotch-Brite™ Clean and Strip Disc CG-RD

Aggressively removes paint and rust from most substrates without damaging the workpiece. Conformable to get into difficult-to-reach areas. 3 dimensional abrasive web reists loading. Safer than wire tools.



- Load resistant
- Smear resistant

Allen
WIND THE RESERVE TO THE PERSON OF THE PERSON
The same of the sa

Product ID	Product Name	MOQ	OU
7100093978	Scotch-Brite™ Roloc™ Clean and Strip Disc CG-RD, 100 mm x 13 mm	10	Each

## Scotch-Brite™ Roloc™ Coating Removal Disc CR-DR

Scotch-Brite™ Roloc™ Coating Removal Disc features extra coarse silicon carbide abrasive to effectively remove paint and rust from metal surfaces and welds. Together with the conformable, non-woven material, silicon carbide abrasives remove coatings without gouging, undercutting, or damaging the base material, especially on hard surfaces.



- Strips coatings and preps surfaces more effectively than wire brushes
- Cleans welding scale, discoloration, and seams
- Non-woven material aggressively removes coating without damaging the base material

Product ID	Product Name	MOQ	OU
7000046010	Scotch-Brite™ Roloc™ Coating Removal Disc CR-DR, 50 mm	60	Each
7000046009	Scotch-Brite™ Roloc™ Coating Removal Disc CR-DR, 76 mm	40	Each



## Scotch-Brite™ Roloc™ Deburr & Finish PRO Unitized Wheel

Scotch-Brite™ Roloc™ Deburr & Finish PRO Unitized Wheel is our new metalworking tool with 3M precision shaped grain woven throughout the abrasive. These unitised wheels have a soft nylon fibre backing and include a Roloc™ attachment for swift, easy connection to power tools.



- Unitised construction enhances abrasive durability and strength, helping prolong service life
- Non-woven construction permits dust and debris to escape, minimising loading
- Perfect for moderate to heavy deburring

Product ID	Product Name	MOQ	OU
7100081368	Scotch Brite™ Roloc™ Deburr and Finish PRO Unitized Wheel, 50 mm x 3.2 mm, 6C MED+	60	Each
7100081367	Scotch Brite™ Roloc™ Deburr and Finish PRO Unitized Wheel, 50 mm x 6.35 mm, 6C MED+	60	Each
7010300983	Scotch Brite™ Roloc™ Deburr and Finish PRO Unitized Wheel, 76 mm x 3.2 mm, 4C MED+	40	Each
7100081366	Scotch Brite™ Roloc™ Deburr and Finish PRO Unitized Wheel, 76 mm x 3.2 mm, 6C MED+	40	Each
7100109130	Scotch Brite™ Roloc™ Deburr and Finish PRO Unitized Wheel, 76 mm x 3.2 mm, 8C CRS+,	40	Each
7100081365	Scotch Brite™ Roloc™ Deburr and Finish PRO Unitized Wheel, 76 mm x 6 mm, 6C MED+	40	Each
7010329346	Scotch Brite™ Roloc™ Deburr and Finish PRO Unitized Wheel, 76 mm x 6.35 mm, 2S FIN,	40	Each
7010295274	Scotch Brite™ Roloc™ Deburr and Finish PRO Unitized Wheel, 76 mm x 6.35 mm, 4C MED+,	40	Each
7100109110	Scotch Brite <sup>™</sup> Roloc <sup>™</sup> Deburr and Finish PRO Unitized Wheel, 76 mm x 6.35 mm, 8C CRS+	40	Each
7100290649	Scotch-Brite™ Roloc™ Deburr & Finish PRO Unitized Wheel, DP-UR, 50,8 mm x 6 mm, TR, 9C XCRS+	60	Each
7100291543	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Deburr & Finish PRO Unitized Wheel, DP-UR, 76,2 mm x 6 mm, TR, 9C XCRS+	40	Each



## Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc

Scotch-Brite™ Roloc™ Precision Surface Conditioning Discs set a new standard in surface conditioning performance. These reformulated multi-purpose discs feature 3M Precision-Shaped Grain technology incorporated into the nonwoven web, bringing a new level of productivity and abrasive life to the Scotch-Brite™ lineup.

- Now with 3M™ precision shaped grain technology, setting a new standard of performance.
- Consistency and ease of use, to improve surfaces without significantly changing the workpiece.
- Conformable, non-woven disc combined with Roloc™ backing allows for aggressive cutting and a convenient, efficient attachment system.

Product ID	Product Name	MOQ	OU
7100271028	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Coarse, TR, 25.4 mm, 50/Inner, 200 ea/ Case, Dispenser Pack	200	Each
7100264164	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Coarse, TR, 38.1 mm, 25/inner, 100 ea/ Case, Dispenser Pack	100	Each
7100264169	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Precision Surface Conditioning Disc, PN-DR, Coarse, TR, 38.1 mm, 50/inner, 200 ea/ Case, Dispenser Pack	200	Each
7100272236	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Coarse, TR, 50.8 mm , 25/Inner, 100 ea/ Case, Dispenser Pack	100	Each
7100264090	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Coarse, TR, 50.8 mm , 50/inner, 200 ea/ Case, Dispenser Pack	200	Each
7100264092	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Coarse, TR, 50.8 mm, 1000 ea/Case, Bulk	1000	Each
7100264197	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Coarse, TR, 76.2 mm, 25/inner, 100 ea/ Case, Dispenser Pack	100	Each
7100264427	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Coarse, TR, 76.2 mm, 1000 ea/Case, Bulk	1000	Each
7100264203	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Coarse, TR, 101.6 mm, 25/inner, 100 ea/ Case, Dispenser Pack	100	Each
7100264150	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Extra Coarse, TR, 25.4 mm, 50/inner, 200 ea/Case, Dispenser Pack	200	Each
7100264165	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Extra Coarse, TR, 38.1 mm, 25/inner, 100 ea/Case, Dispenser Pack	100	Each
7100264170	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Extra Coarse, TR, 38.1 mm, 50/inner, 200 ea/Case, Dispenser Pack	200	Each
7100264172	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Extra Coarse, TR, 50.8 mm , 25/inner, 100 ea/Case, Dispenser Pack	100	Each
7100264091	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Precision Surface Conditioning Disc, PN-DR, Extra Coarse, TR, 50.8 mm , 50/inner, 200 ea/Case, Dispenser Pack	200	Each
7100264193	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Extra Coarse, TR, 50.8 mm , 1000 ea/Case, Bulk	1000	Each
7100264198	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Extra Coarse, TR, 76.2 mm, 25/inner, 100 ea/Case, Dispenser Pack	100	Each
7100264438	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Extra Coarse, TR, 76.2 mm, 1000 ea/Case, Bulk	1000	Each
7100270872	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Precision Surface Conditioning Disc, PN-DR, Extra Coarse, TR, 101.6 mm, 25/Inner, 100 ea/Case, Dispenser Pack	100	Each
7100264159	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Fine, TR, 25.4 mm, 50/inner, 200 ea/Case, Dispenser Pack	200	Each
7100264167	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Precision Surface Conditioning Disc, PN-DR, Fine, TR, 38.1 mm, 50/inner, 200 ea/Case, Dispenser Pack	200	Each
7100264171	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Fine, TR, 50.8 mm , 25/inner, 100 ea/Case, Dispenser Pack	100	Each
7100264174	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Fine, TR, 50.8 mm , 50/inner, 200 ea/Case, Dispenser Pack	200	Each
7100264139	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Precision Surface Conditioning Disc, PN-DR, Fine, TR, 50.8 mm , 1000 ea/Case, Bulk	1000	Each



## Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc

Scotch-Brite™ Roloc™ Precision Surface Conditioning Discs set a new standard in surface conditioning performance. These reformulated multi-purpose discs feature 3M Precision-Shaped Grain technology incorporated into the nonwoven web, bringing a new level of productivity and abrasive life to the Scotch-Brite™ lineup.

- Now with 3M<sup>™</sup> precision shaped grain technology, setting a new standard of performance.
- Consistency and ease of use, to improve surfaces without significantly changing the workpiece.
- Conformable, non-woven disc combined with Roloc™ backing allows for aggressive cutting and a convenient, efficient attachment system.

Product ID	Product Name	MOQ	OU
7100264195	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Fine, TR, 76.2 mm, 25/inner, 100 ea/Case, Dispenser Pack	100	Each
7100271030	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Fine, TR, 76.2 mm, 1000/Case, Bulk	1000	Each
7100264204	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Fine, TR, 101.6 mm, 25/inner, 100 ea/Case, Dispenser Pack	100	Each
7100264161	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Medium, TR, 25.4 mm, 50/inner, 200 ea/ Case, Dispenser Pack	200	Each
7100264168	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Precision Surface Conditioning Disc, PN-DR, Medium, TR, 38,1 mm, 50/inner, 200 ea/ Case, Dispenser Pack	200	Each
7100272016	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Medium, TR, 50.8 mm , 25/Inner, 100 ea/ Case, Dispenser Pack	100	Each
7100264089	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Medium, TR, 50.8 mm , 50/inner, 200 ea/ Case, Dispenser Pack	200	Each
7100264141	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Medium, TR, 50.8 mm , 1000 ea/Case, Bulk	1000	Each
7100264196	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Medium, TR, 76.2 mm, 25/inner, 100 ea/ Case, Dispenser Pack	100	Each
7100264428	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Medium, TR, 76.2 mm, 1000 ea/Case, Bulk	1000	Each
7100264142	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Medium, TR, 101.6 mm, 25/inner, 100 ea/ Case, Dispenser Pack	100	Each
7100264156	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Very Fine, TR, 25.4 mm, 50/inner, 200 ea/ Case, Dispenser Pack	200	Each
7100264151	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Very Fine, TR, 38.1 mm, 25/inner, 100 ea/ Case, Dispenser Pack	100	Each
7100264166	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Precision Surface Conditioning Disc, PN-DR, Very Fine, TR, 38.1 mm, 50/inner, 200 ea/ Case, Dispenser Pack	200	Each
7100272237	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Very Fine, TR, 50.8 mm , 25/Inner, 100 ea/Case, Dispenser Pack	100	Each
7100264173	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Precision Surface Conditioning Disc, PN-DR, Very Fine, TR, 50.8 mm , 50/inner, 200 ea/ Case, Dispenser Pack	200	Each
7100264138	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Very Fine, TR, 50.8 mm , 1000 ea/Case, Bulk	1000	Each
7100264194	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Precision Surface Conditioning Disc, PN-DR, Very Fine, TR, 76.2 mm, 25/inner, 100 ea/ Case, Dispenser Pack	100	Each
7100264429	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Very Fine, TR, 76.2 mm, 1000 ea/Case, Bulk	1000	Each
7100264199	Scotch-Brite™ Roloc™ Precision Surface Conditioning Disc, PN-DR, Very Fine, TR, 101.6 mm, 25/inner, 100 ea/ Case, Dispenser Pack	100	Each



## **Cut-off & Grinding Wheels**

Focus

## 3M™ Cubitron™ 3 Cut-Off Wheel

The 3M™ Cubitron™ 3 Cut-Off Wheel creates perpendicular cuts using the outer edge of the wheel, making it ideal for cutting through metal, including autobody or marine sheet metal, stainless steel tubing, exhaust pipes, clamps, rusted fasteners and more.

Additionally, the 3M™ Cubitron™ 3 Cut-Off Wheel is powered by 3M Re-Engineered Precision Shaped Grain using proprietary breakthroughs in molecular bonding technology designed with sharp, angular structures that continuously fracture to form sharp points. These clean, sharp points help create an abrasive that slices faster, runs cooler, and lasts much longer than conventional abrasives.

3M™ Cubitron™ Performance Abrasives are made for professionals who need more from their equipment — so experience the next generation in abrasive performance by choosing the 3M™ Cubitron™ 3 Cut-Off Wheel.

- SPECIALISED FUNCTIONALITY: Creates perpendicular cuts using the outer edge of the wheel, making them ideal for cutting through metal, including autobody or marine sheet metal, stainless steel tubing, exhaust pipes, clamps, rusted fasteners and more.
- ENHANCED SPEED: Delivers up to 10% increased cut rate compared to 3M™ Cubitron™ II Performance Abrasives to help reduce the amount of time and pressure required to get the job done.
- LESS CHANGEOVER: Removes up to 3x more material compared to 3M<sup>™</sup> Cubitron<sup>™</sup> II Performance Abrasives.



Product ID	Product Name	MOQ	OU
7100305230	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 60+, T41, 180 mm x 1.6 mm x 22.23mm	50	Each
7100303829	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 86412, 36+, T41, 125 mm x 1.6 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100304304	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 86457, 60+, T41, 125 mm x 1.3 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100304056	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 86542, 60+, T41, 150 mm x 2 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100304127	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 86580, 80+, T41, 125 mm x 0.8 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100304305	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 86581, 80+, T41, 115 mm x 0.8 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100304120	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 86616, 60+, T41, 115 mm x 1 mm x 22.23 mm, EN, 25/ Pack, 50 ea/Case	50	Each
7100304306	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 86647, 60+, T41, 125 mm x 1 mm x 22.23 mm, EN, 25/ Pack, 50 ea/Case	50	Each
7100303830	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 86997, 36+, T41, 100 mm x 2 mm x 15.88 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100303831	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 87338, 36+, T42, 125 mm x 3 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100303832	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 87371, 36+, T41, 230 mm x 3 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100303993	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 87378, 36+, T42, 230 mm x 2.5 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100303994	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 87396, 36+, T42, 180 mm x 2.5 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100303995	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 87963, 36+, T42, 125 mm x 2.5 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100303996	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 88383, 36+, T42, 115 mm x 2.5 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100303997	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 88404, 36+, T41, 230 mm x 2.5 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100303998	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 88732, 36+, T41, 230 mm x 2 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100303999	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 88768, 36+, T41, 180 mm x 2 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100304000	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 88775, 36+, T41, 125 mm x 2 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100304003	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 89573, 36+, T41, 115 mm x 1.6 mm x 22.23 mm, EN, 25/Pack, 50 ea/Case	50	Each
7100304121	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 89623, 60+, T41, 75 mm x 1 mm x 9.53 mm, EN, 25/ Pack, 50 ea/Case	50	Each
7100303861	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 90230, 60+, T41, 75 mm x 1 mm x 6.35 mm, EN, 25/ Pack, 50 ea/Case	50	Each
7100304123	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 91045, 60+, T41, 75 mm x 1 mm x 10 mm, EN, 25/ Pack, 50 ea/Case	50	Each
7100304124	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut-Off Wheel, 91564, 60+, T41, 75 mm x 1 mm x 8 mm, EN, 25/Pack, 50 ea/Case	50	Each



Focus

### 3M™ Cubitron™ 3 Depressed Center Grinding Wheel

The 3M™ Cubitron™ 3 Depressed Center Grinding Wheel is an exceptionally fast-cutting and long-lasting rigid-bonded wheel for heavy weld removal and other heavy-duty grinding applications. Utilising a depressed centre to enable grinding at any angle, this wheel works well on almost all materials while being specially formulated for use on stainless steel, mild steel, and aerospace alloys.

Additionally, the 3M<sup>™</sup> Cubitron<sup>™</sup> 3 Depressed Center Grinding Wheel is powered by 3M Re-Engineered Precision Shaped Grain using proprietary breakthroughs in molecular bonding technology designed with sharp, angular structures that continuously fracture to form sharp points. These clean, sharp points help create an abrasive that slices faster, runs cooler, and lasts much longer than conventional abrasives. 3M<sup>™</sup> Cubitron<sup>™</sup> Performance Abrasives are made for professionals who need more from their equipment — so experience the next generation in abrasive performance by choosing the 3M<sup>™</sup> Cubitron<sup>™</sup> 3 Depressed Center Grinding Wheel.



- HEAVY-DUTY: Designed for heavy weld removal and other heavy-duty grinding applications on almost all materials while being specially formulated for use on stainless steel, mild steel, and aerospace alloys.
- ENHANCED PERFORMANCE: Delivers up to 14% increased cut rate compared to 3M™ Cubitron™ II Abrasives to help reduce the amount of time and pressure required to get the job done.
- LESS CHANGEOVER: Removes up to 2x more material compared to 3M<sup>™</sup> Cubitron<sup>™</sup> II Performance Abrasives.

Product ID	Product Name	MOQ	OU
7100312955	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Depressed Center Grinding Wheel, 43616, 36+, T27, 125 mm x 7 mm x 22.23 mm, Gouge Special EN, 20 ea/Case	20	Each
7100303963	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Depressed Center Grinding Wheel, 74433, 36+, T27, 150 mm x 7 mm x 22.23 mm, Gouge Special EN, 10/Pack 20 ea/Case	20	Each
7100305453	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Depressed Center Grinding Wheel, 97618, 36+, T27, 180 mm x 7 mm x 22.23 mm, Gouge Special EN, 10/Pack 20 ea/Case	20	Each
7100303979	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Depressed Center Grinding Wheel, 98291, 36+, T27, 230 mm x 7 mm x 22.23 mm, EN, 10/ Pack, 20 ea/Case	20	Each
7100303980	$3M$ <sup>™</sup> Cubitron $^{\infty}$ 3 Depressed Center Grinding Wheel, 98418, 36+, T27, 180 mm x 7 mm x 22.23 mm, EN, 10/Pack, 20 ea/Case	20	Each
7100303981	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Depressed Center Grinding Wheel, 98452, 36+, T27, 150 mm x 7 mm x 22.23 mm, EN, 10/ Pack, 20 ea/Case	20	Each
7100303982	$3M$ <sup>™</sup> Cubitron $^{\infty}$ 3 Depressed Center Grinding Wheel, 98647, 36+, T27, 125 mm x 7 mm x 22.23 mm, EN, 10/Pack, 20 ea/Case	20	Each
7100303983	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Depressed Center Grinding Wheel, 99306, 36+, T27, 115 mm x 7 mm x 22.23 mm, EN, 10/ Pack, 20 ea/Case	20	Each



Focus

#### 3M™ Cubitron™ 3 Cut and Grind Wheel

The 3M™ Cubitron™ 3 Cut and Grind Wheel is a versatile solution designed to be used both as a grinding wheel and cut-off wheel — making it ideal for cutting, grinding, gouging, and more. Unlike other abrasive products, which are designed for just one job, this wheel can meet multiple challenges thanks, in part, to a flat, reinforced inner surface that can shape or grind objects and a thin outer edge that can be used to make perpendicular cuts and gouges. This inclusive design removes the need for multiple abrasive tools and can help to maximise production.



Additionally, the 3M<sup>™</sup> Cubitron<sup>™</sup> 3 Cut and Grind Wheel is powered by 3M Re-Engineered Precision Shaped Grain using proprietary breakthroughs in molecular bonding technology designed with sharp, angular structures that continuously fracture to form sharp points. These clean, sharp points help create an abrasive that slices faster, runs cooler, and lasts much longer than conventional abrasives. 3M<sup>™</sup> Cubitron<sup>™</sup> Performance Abrasives are made for professionals who need more from their equipment — so experience the next generation in abrasive performance by choosing the 3M<sup>™</sup> Cubitron<sup>™</sup> 3 Cut and Grind Wheel.

- MULTIPLE FUNCTIONS: Used both as a grinding wheel and cut-off wheel, making it ideal for cutting, grinding, gouging, and more
- ENHANCED SPEED: Delivers up to 5% increased cut rate compared to 3M™ Cubitron™ II Performance Abrasives to help reduce the amount of time and pressure required to get the job done.
- RIGID, REINFORCED, RESIN-BONDED WHEEL: Designed to be used both as a grinding wheel and as a cut-off wheel on both stainless and mild steel substrates.

Product ID	Product Name	MOQ	OU
7100305148	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 47563, 36+, T27, 150 mm x 3.2 mm x 22.23 mm, EN, 10/Pack, 20 ea/ Case	20	Each
7100305445	$3M$ <sup>™</sup> Cubitron <sup>™</sup> $3$ Cut and Grind Wheel, $93314$ , $36+$ , $727$ , $100$ mm $\times$ $3.2$ mm $\times$ $15.88$ mm, EN, $10$ /Pack, $20$ ea/Case	20	Each
7100305446	$3M^{\rm T}$ Cubitron $^{\rm T}$ 3 Cut and Grind Wheel, 93395, 36+, T27, 230 mm x 3.8 mm x 22.23 mm, EN, 10/Pack, 20 ea/Case	20	Each
7100305447	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 93473, 36+, T27, 180 mm x 3.5 mm x 22.23 mm, EN, 10/Pack, 20 ea/ Case	20	Each
7100305448	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 93498, 36+, T27, 125 mm x 3.2 mm x 22.23 mm, EN, 10/Pack, 20 ea/Case	20	Each
7100305449	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 94159, 36+, T27, 115 mm x 3.2 mm x 22.23 mm, EN, 10/Pack, 20 ea/ Case	20	Each
7100303971	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 94343, 36+, T27, 230 mm x 4.2 mm x 22.23 mm, EN, 10/Pack, 20 ea/ Case	20	Each
7100303972	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 94542, 36+, T27, 180 mm x 4.2 mm x 22.23 mm, EN, 10/Pack, 20 ea/ Case	20	Each
7100303973	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 94888, 36+, T27, 150 mm x 4.2 mm x 22.23 mm, EN, 10/Pack, 20 ea/Case	20	Each
7100303974	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 94946, 36+, T27, 125 mm x 4.2 mm x 22.23 mm, EN, 10/Pack, 20 ea/ Case	20	Each
7100303975	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 95344, 36+, T27, 115 mm x 4.2 mm x 22.23 mm, EN, 10/Pack, 20 ea/Case	20	Each
7100305450	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cut and Grind Wheel, 95508, 36+, T27, 100 mm x 4.2 mm x 15.88 mm, EN, 10/Pack, 20 ea/ Case	20	Each

## 3M™ Silver Cut-Off Wheel

3M™ Silver Cut-Off Wheel is designed to deliver an unbeatable combination of performance and value. It cuts quickly through metal pipes, tubes and flat sheets. The long-lasting wheel uses our Precision Shaped Grain to deliver a fast, consistent cut.

- Cuts cleanly with minimal burrs
- Cuts quickly through metal pipes, tubes, flat sheets and more
- 3M Precision Shaped Grain cuts cleanly and fast, helping to increase productivity

Product ID	Product Name	MOQ	OU
7100139207	3M™ Silver Cut-Off Wheel, T41, 75 mm x 0.9 mm x 6.35 mm	50	Each
7100139209	3M <sup>™</sup> Silver Cut-Off Wheel, T41, 75 mm x 0.9 mm x 10 mm	50	Each
7100139211	3M™ Silver Cut-Off Wheel, T41, 75 mm x 1.6 mm x 9.53 mm	50	Each
7100139213	3M™ Silver Cut-Off Wheel, T41, 100 mm x 0.9 mm x 6.35 mm	50	Each
7100139216	3M™ Silver Cut-Off Wheel, T41, 100 mm x 1 mm x 9.53 mm	50	Each
7100139217	3M™ Silver Cut-Off Wheel, T41, 100 mm x 1 mm x 16 mm	50	Each
7100139218	$3M^{\text{\tiny M}}$ Silver Cut-Off Wheel, T41, 100 mm x 1.3 mm x 16 mm	50	Each
7100139219	3M™ Silver Cut-Off Wheel, T41, 105 mm x 1 mm x 10 mm	50	Each
7100139223	$3M^{\text{\tiny M}}$ Silver Cut-Off Wheel, T41, 105 mm x 1.3 mm x 9.53 mm	50	Each
7100139227	3M™ Silver Cut-Off Wheel, T41, 115 mm x 1 mm x 22.2 mm	50	Each
7100139229	3M <sup>™</sup> Silver Cut-Off Wheel, T41, 115 mm x 1.6 mm x 22.2 mm	50	Each
7100139232	3M™ Silver Cut-Off Wheel, T41, 125 mm x 1 mm x 22.2 mm	50	Each
7100139234	3M™ Silver Cut-Off Wheel, T41, 125 mm x 1.6 mm x 22.2 mm	50	Each
7100139238	3M™ Silver Cut-Off Wheel, T41, 125 mm x 2 mm x 22.2 mm	50	Each
7100139235	3M™ Silver Cut-Off Wheel, T41, 150 mm x 1.6 mm x 22.2 mm	50	Each
7100141045	3M™ Silver Cut-Off Wheel, T41, 178 mm x 3 mm x 22.2 mm	50	Each
7100139240	3M™ Silver Cut-Off Wheel, T41, 180 mm x 2 mm x 22.2 mm	50	Each
7100141075	3M <sup>™</sup> Silver Cut-Off Wheel, T41, 230 mm x 3 mm x 22.2 mm	50	Each
7100141056	3M™ Silver Cut-Off Wheel, T42, 115 mm x 2.5 mm x 22.2 mm	50	Each
7100141069	3M <sup>™</sup> Silver Cut-Off Wheel, T42, 125 mm x 2.5 mm x 22.2 mm	50	Each
7100141067	$3M^{\text{\tiny M}}$ Silver Cut-Off Wheel, T42, 178 mm x 2.5 mm x 22.2 mm	50	Each
7100141070	3M™ Silver Cut-Off Wheel, T42, 230 mm x 2.5 mm x 22.2 mm	50	Each

### 3M™ Silver Depressed Centre Grinding Wheel

3M™ Silver Depressed Centre Grinding Wheel is our type 27 wheel, designed to deliver an unbeatable combination of performance and value that delivers a fast and consistent cut during grinding and heavy stock removal on stainless steel, mild steel, aerospace alloys and more.

- Suitable for heavy grinding, beveling and weld removal
- 3M Precision Shaped Grain cuts cleanly and fast, helping to increase productivity
- Long-lasting wheel provides great performance value



Product ID	Product Name	MOQ	OU
7100141123	3M <sup>™</sup> Silver Depressed Centre Grinding Wheel, T27, 100 mm x 7 mm x 16 mm	20	Each
7100141083	3M <sup>™</sup> Silver Depressed Centre Grinding Wheel, T27, 115 mm x 7 mm x 22.2 mm	20	Each
7100141086	3M <sup>™</sup> Silver Depressed Centre Grinding Wheel, T27, 125 mm x 7 mm x 22.2 mm	20	Each
7100141089	3M <sup>™</sup> Silver Depressed Centre Grinding Wheel, T27, 150 mm x 7 mm x 22.2 mm	20	Each
7100141096	3M <sup>™</sup> Silver Depressed Centre Grinding Wheel, T27, 178 mm x 7 mm x 22.2 mm	20	Each
7100141099	3M <sup>™</sup> Silver Depressed Centre Grinding Wheel, T27, 230 mm x 7 mm x 22.2 mm	20	Each

#### 3M™ Cut & Grind Wheel

3M™ Cut & Grind Wheels are engineered to help you get more work done for your dollar. They blast through tough jobs with a fast, smooth cut ... with less pressure ... and with less chatter on back gouging and root pass grinding. 3M Precision Shaped Grain technology slices through metal with super-sharp, micro-replicated points for a cooler, faster and longer lasting cut than conventional crushed abrasive grain. Plus, these long-lasting wheels need fewer changes, so you can power through the daily grind much faster.



- 3M™ Cut & Grind wheels use 3M precision-shaped grain technology that increases the speed and life of the abrasive
- Designed for the cost driven customer. Delivers high performance at an affordable price
- Versatile: Rigid reinforced resin bonded wheel is designed to be used as both a grinding wheel and a cutoff wheel on mild and stainless-steel substrates

Product ID	Product Name	MOQ	OU
7100214038	3M™ Cut and Grind Wheel, T27, 115 mm x 4.2 mm x 22.2 mm	20	Each
7100214085	3M™ Cut and Grind Wheel, T27, 127 mm x 4.2 mm x 22.2 mm	20	Each
7100214087	3M™ Cut and Grind Wheel, T27, 152 mm x 4.2 mm x 22.2 mm	20	Each
7100214088	3M™ Cut and Grind Wheel, T27, 180 mm x 4.2 mm x 22.2 mm	20	Each
7100214089	3M™ Cut and Grind Wheel, T27, 230 mm x 4.2 mm x 22.2 mm	20	Each

## 3M™ Cubitron™ II Flexible Grinding Wheels

The 3M™ Cubitron™ II Flexible Grinding Wheel is designed to help you grind, shape and sand as fast as possible on a variety of metal materials. Utilising 3M Precision Shaped Grain that cuts fast and cool, while still offering enhanced flexibility.



- Designed to grind, shape and sand on a variety of metal materials
- 3M™ Precision Shaped Grain offer excellent cut rate and enhanced flexibility vs standard depressed center grinding wheels
- Resin bond helps retain strength and performance under grinding operations

Product ID	Product Name	MOQ	OU
7100140055	3M™ Cubitron™ II Flexible Grinding Wheels, T27, 100mm x 3mm x 16mm	200	Each
7100140056	3M™ Cubitron™ II Flexible Grinding Wheels, T27, 115 mm x 3 mm x 22.2 mm	200	Each
7100140059	3M <sup>™</sup> Cubitron <sup>™</sup> II Flexible Grinding Wheels, T27, 115 mm x 3 mm x 22.2 mm	200	Each
7100140057	3M™ Cubitron™ II Flexible Grinding Wheels, T27, 125 mm x 3 mm x 22.2 mm	200	Each
7100140060	3M <sup>™</sup> Cubitron <sup>™</sup> II Flexible Grinding Wheels, T27, 125 mm x 3 mm x 22.2 mm, 80+	200	Each
7100140058	3M <sup>™</sup> Cubitron <sup>™</sup> II Flexible Grinding Wheels, T27, 178 mm x 4 mm x 22.2 mm	100	Each



## **Deburring & Finishing Wheels**

## Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW

Utilizes 3M proprietary Precision Shaped Grain technology for higher cutting and durability performance in deburring and blending applications.

- Minimal dust and debris less dust equals less cleanup
- Perform faster deburring
- A soft, strong and smooth wheel with good control



Product ID	Product Name	MOQ	OU
7100256411	Scotch-Brite <sup>™</sup> Deburr and Finish PRO Unitized Wheel DP-UW, 6C Medium+, 76 mm x 12.7 mm x 6.35 mm, 20 ea/Case	20	Each
7100083512	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 25.4 mm x 25.4 mm x 4.76 mm, 6C MED+	50	Each
7100290254	Scotch-Brite <sup>™</sup> Deburr and Finish PRO Unitized Wheel DP-UW, 25.4 mm x 25.4 mm x 4.76 mm, 9C XCRS+	1	Each
7100053413	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 50 mm x 3.175 mm x 6.35 mm, 6C MED+	60	Each
7100053414	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 50 mm x 6.35 mm x 6.35 mm, MED	60	Each
7100290249	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 50.8 mm x 6.35 mm x 6.35 mm, 9C XCRS+	60	Each
7100053418	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 3.18 mm x 6.35 mm, 6C MED+	40	Each
7100105326	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 3.175 mm x 6.35 mm, 8C CRS+	40	Each
7100256513	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 6.35 mm x 6.35 mm, 2S Fine	40	Each
7010365693	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 6.35 mm x 6.35 mm, 4C MED+	40	Each
7100256410	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 6.35 mm x 6.35 mm, 6C Med+	40	Each
7100256508	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 6.35 mm x 6.35 mm, 8C CRS+	40	Each
7010310029	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 12.7 mm x 6.35 mm, 4C MED+	20	Each
7100256517	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 12.7 mm x 6.35 mm, 8C CRS+	20	Each
7100110912	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 12.7 mm x 9.52 mm, 8 CRS+	20	Each
7100053421	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 19 mm x 6.35 mm, 6C MED+	20	Each
7010329496	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76 mm x 19 mm x 6.35 mm, 8C CRS+	20	Each
7100290246	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76.2 mm x 6.35 mm x 6.35 mm, 9C XCRS+	40	Each
7100290244	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 76.2 mm x 12.7 mm x 6.35 mm, 9C XCRS+	20	Each
7100290250	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 127 mm x 3.175 mm x 25.4 mm, 9C XCRS+	16	Each
7100290101	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 127 mm x 6.35 mm x 25.4 mm, 9C XCRS+	10	Each
7100088615	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 3.2 mm x 25.4 mm, 6C MED+	16	Each
7010310028	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 3.175 mm x 12.7 mm, 6C MED+	16	Each
7100256509	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 6.35 mm x 25.4 mm, 6C Med+	8	Each
7100256521	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 12.7 mm x 12.7 mm, 6C Med+	4	Each
7100256514	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 12.7 mm x 25.4 mm, 2S Fine	4	Each
7100256507	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 12.7 mm x 25.4 mm, 8C CRS+	4	Each
7100256518	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 25.4 mm x 12.7 mm, 6C Med+	2	Each
7100256522	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 25.4 mm x 25.4 mm, 6C Med+	2	Each
7100256520	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 25.4 mm x 25.4 mm, 8C CRS+	2	Each
7100256515	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152 mm x 25.4 mm x 25.4 mm, 2S Fine	2	Each
7100290255	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152.4 mm x 3.175 mm x 12.7 mm, 9C XCRS+	16	Each
7100290763	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152.4 mm x 3.175 mm x 25.4 mm, 9C XCRS+	16	Each
7100290251	Scotch-Brite <sup>™</sup> Deburr and Finish PRO Unitized Wheel DP-UW, 152.4 mm x 6.35 mm x 22.23 mm, 9C XCRS+	8	Each



### Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW

Utilizes 3M proprietary Precision Shaped Grain technology for higher cutting and durability performance in deburring and blending applications.

- Minimal dust and debris less dust equals less cleanup
- Perform faster deburring
- A soft, strong and smooth wheel with good control

41
€0+ Debur & Finish t
Scotch-Brite 314
r & Finish PRO AC MED+ Debu
te 3M Scotch-Br
MED+ Deburr & Floish PRF
otch Brite 3

Product ID	Product Name	MOQ	OU
7100290100	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152.4 mm x 6.35 mm x 25.4 mm, 9C XCRS+	8	Each
7100290253	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152.4 mm x 12.7 mm x 12.7 mm, 9C XCRS+	4	Each
7100290252	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 152.4 mm x 12.7 mm x 25.4 mm, 9C XCRS+	4	Each
7100108778	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 203 mm x 12.7 mm x 12.7 mm, A CRS	1	Each
7100290248	Scotch-Brite™ Deburr and Finish PRO Unitized Wheel DP-UW, 203.2 mm X 6.35 mm X 6.35 mm, 9C XCRS+	8	Each

#### Scotch-Brite™ EXL Unitized Wheel XL-UW

Scotch-Brite<sup>TM</sup> EXL Unitized Wheels feature a soft, conformable consistency that effectively smoothes, deburrs and finishes the edges of metal alloys, as well as many plastics and composites. There are a variety of densities and grades starting from a very soft 2 density for applications requiring a conformability to a hard, aggressive 8 density for maximum cut and durability.



- Wheel edge can be dressed for effective deburring, finishing and polishing of all metal alloys and many plastics and composites
- Tough, layered, unitized construction can operate clockwise or counterclockwise directions
- Densities and grades ranging from soft and conformable to hard and aggressive offer utility for a wide variety of applications

Product ID	Product Name	MOQ	OU
7100256317	Scotch-Brite™ EXL Unitized Wheel XL-UW, 76 mm x 6.35 mm x 6.35 mm, 2A Med	40	Each
7100256412	Scotch-Brite™ EXL Unitized Wheel XL-UW, 76 mm x 12.7 mm x 6.35 mm, 2A Med	20	Each
7100256328	Scotch-Brite™ EXL Unitized Wheel XL-UW, 152 mm x 6.35 mm x 12.7 mm, 2S Fine	8	Each
7000000690	Scotch-Brite™ EXL Unitized Wheel XL-UW, 25mm x 25mm x 4.84mm, 2S FIN	50	Each
7000046104	Scotch-Brite <sup>™</sup> EXL Unitized Wheel XL-UW, 152 mm x 6.35 mm x 12.7 mm, 3S FIN	8	Each

## Scotch-Brite™ EX3 Deburring Wheel X3-WL

Scotch-Brite™ EX3 Deburring Wheel is a convolute-constructed, hard, durable deburring wheel suited for applications where edge retention is a must. The wheel performs best when consistently presented with a sharp edge or metal burrs. A unique resin system resists smearing and heat buildup.



- Highest edge retention and durability in the Scotch-Brite™ Deburring Wheel line provides aggressive edge deburring
- Specially engineered to condition sharp edges and metal burrs
- Convolute construction provides a balanced, smooth running wheel throughout product life

Product ID	Product Name	MOQ	OU
7000046167	Scotch-Brite <sup>™</sup> EX3 Deburring Wheel X3-WL, 203 mm x 12.7 mm x 76.2 mm, 9S FIN	4	Each

### Scotch-Brite™ EX2 Deburring Wheel X2-WL

Scotch-Brite™ EX2 Deburring Wheel is a convolute-constructed wheel that provides mid-range aggressiveness and hardness for deburring, edge radius, blending, polishing, and finishing. Our deburring wheel performs best when consistently presented with a sharp edge or metal burrs.



- Wheel edge can be dressed for effective deburring, finishing and polishing of all metal alloys and many plastics and composites
- Tough, layered, unitized construction can operate clockwise or counterclockwise directions
- Densities and grades ranging from soft and conformable to hard and aggressive offer utility for a wide variety of applications

Product ID	Product Name	MOQ	OU
7000046098	Scotch-Brite™ EX2 Deburring Wheel X2-WL, 254 mm x 25.4 mm x 127 mm, 9S FIN	2	Each

## Scotch-Brite™ Deburring Wheel

When you need an aggressive wheel for a variety of deburring tasks and surfaces, the Scotch-Brite™ Deburring Wheel is a good place to start. This silicon carbide wheel offers a hard, 11 density rating in both medium and fine grades for light to medium edge deburring on carbon steels, stainless steel, titanium; soft metals such as aluminum, copper and brass; composites, plastics and glass.



- Hard density conformable wheel performs effective burr removal without undercutting the workpiece
- Convolute construction keeps the wheel running smooth, producing consistent results
- Scotch-Brite™ non-woven material resists loading and continuously supplies fresh abrasives for continuous cutting action

Product ID	Product Name	MOQ	OU
7000028491	Scotch-Brite <sup>™</sup> Deburring Wheel DB-WL, 152 mm x 25 mm x 25.4 mm, 7S FIN	3	Each
7000028488	Scotch-Brite <sup>™</sup> Deburring Wheel DB-WL, 152 mm x 25 mm x 25.4 mm, 9S FIN	3	Each
7000046089	Scotch-Brite <sup>™</sup> Deburring Wheel DB-WL, 203 mm x 25 mm x 76.2 mm, 7S FIN	3	Each
7000046086	Scotch-Brite <sup>™</sup> Deburring Wheel DB-WL, 203 mm x 25 mm x 76.2 mm, 9S FIN	3	Each
7000028493	Scotch-Brite <sup>™</sup> Deburring Wheel DB-WL, 203 mm x 50 mm x 76.2 mm, 7S FIN	2	Each
7000046088	Scotch-Brite <sup>™</sup> Deburring Wheel DB-WL, 203 mm x 50 mm x 76.2 mm, 9S FIN	2	Each

## Scotch-Brite™ Finishing Wheel

Scotch-Brite™ Finishing Wheels provide consistent results throughout product life. Will not change the geometry of the workpiece and produce uniform surface finishes without chatter marks, especially on stainless steel.



- Aluminium Oxide/Silicon Carbide construction
- Highly conformable for consistent finishing on contoured, curved and other surfaces
- Moderate aggressiveness and lighter density provide controlled wear for consistent results

Product ID	Product Name	MOQ	OU
7000028484	Scotch-Brite™ Finishing Wheel FS-WL, 152 mm x 25 mm x 25.4 mm, 2S CRS	3	Each
7000028494	Scotch-Brite <sup>™</sup> Finishing Wheel FS-WL, 152 mm x 25 mm x 25.4 mm, 6S FIN	3	Each



## Scotch-Brite™ Light Deburring Wheel

Scotch-Brite™ Light Deburring Wheel is a smooth running, convolute-constructed wheel that provides a clean system for light deburring, polishing, and finishing. Our wheels are made for soft construction and smooth operation, requiring less effort by the operator than a harder wheel.

- Provides a clean and economical system for removing fine burrs, resulting in a polished finish
- Conformability offers consistent finishing while keeping fresh abrasive mineral continuously exposed
- Non-woven web runs cool and lessens impact on heat-sensitive materials



Product ID	Product Name	MOQ	OU
7000000730	Scotch-Brite <sup>™</sup> Light Deburring Wheel LD-WL, 152 mm x 25.4 mm x 25.4 mm, 7S FIN	3	Each

### Scotch-Brite™ Roloc™ EXL Unitized Wheel XL-DR


Scotch-Brite™ Roloc™ EXL Unitized Wheel is strong and effective for edge deburring and finishing. Our wheel performs well in a variety of metal working applications and machined parts where close tolerances are important.



- Strong unitized construction provides effective edge deburring and finishing
- Hard densities offer good edge retention, which helps maintain consistent shape and cutting action
- Soft densities offer conformability and flexibility for finishing flat, contoured, or irregular surfaces without damaging the part

Product ID	Product Name	MOQ	OU
7000045976	Scotch-Brite™ Roloc™ EXL Unitized Wheel XL-DR, 50 mm x 6 mm, 2S FIN	60	Each
7100000858	Scotch-Brite™ Roloc™ EXL Unitized Wheel XL-DR, 76 mm x 6 mm, 2A MED	40	Each
7100005209	Scotch-Brite™ Roloc™ EXL Unitized Wheel XL-DR, 76 mm x 6 mm, 2S FIN	40	Each
7000028469	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> EXL Unitized Wheel XL-DR, 76 mm x 6 mm, 6A MED	40	Each





## **Bristle Brushes & Discs**

#### Scotch-Brite™ Shaft Mounted Bristle Disc BB-ZS

Scotch-Brite™ Shaft Mounted Bristle Discs are made of plastic impregnated with 3M™ Cubitron™ abrasive grain and moulded into a disc and mounted on a spindle.

- Shaft mounted for quick and easy change
- Works well on irregular surfaces
- Flexible



Product ID	Product Name	MOQ	OU
7000078180	Scotch-Brite <sup>™</sup> Shaft Mounted Bristle Disc BB-ZS, 50 mm, P80, Yellow, Type C	6	Each
7000078175	Scotch-Brite™ Shaft Mounted Bristle Disc BB-ZS, 50 mm, P120, White, Type C	6	Each
7000078179	Scotch-Brite <sup>™</sup> Shaft Mounted Bristle Disc BB-ZS, 50 mm, P220, Brown, Type C	6	Each
7000078178	Scotch-Brite™ Shaft Mounted Bristle Disc BB-ZS, 75 mm, P220, Brown, Type C	6	Each
7000078176	Scotch-Brite™ Shaft Mounted Bristle Disc BB-ZS, 76 mm, P80, Yellow, Type C	6	Each
7000078177	Scotch-Brite™ Shaft Mounted Bristle Disc BB-ZS, 76 mm, P120, White, Type C	6	Each

#### Scotch-Brite™ Bristle Disc BD-ZB

Scotch-Brite™ Bristle Disc, using ceramic abrasive grain and molded, flexible bristles, provides more surface contact than wire brushes and maintains abrasive property throughout the life of the disc. The fast-running disc removes paint, stains, adhesives, weld burns, rust, heavy oxides, and surface contaminants from large areas.



- Molded, abrasive-filled bristles strip, deburr, blend, finish, polish, clean, and remove coatings more effectively, with less pressure than wire brushes
- Proprietary 3M<sup>™</sup> Ceramic Abrasive Grain provides aggressive cutting and consistent finish quality throughout the life of the disc
- Flexible bristles require less pressure than wire brushes and conform to contours, even on complex parts

Product ID	Product Name	MOQ	OU
7000062861	Scotch-Brite	5	Each
7100138287	Scotch-Brite™ Bristle Disc BD-ZB, 115 mm, P50, Green, M14	10	Each
7100138288	Scotch-Brite™ Bristle Disc BD-ZB, 115 mm, P80, Yellow, M14	10	Each
7100138289	Scotch-Brite™ Bristle Disc BD-ZB, 115 mm, P120, White, M14	10	Each

## Scotch-Brite™ Radial Bristle Brush Type S BB-ZB

Scotch-Brite™ Radial Bristle Brush, using our proprietary ceramic abrasive grain blended with aluminum oxide and molded, flexible bristles, provides more surface contact than wire brushes and maintains abrasive property throughout the life of the brush. Our brush removes paint, stains, adhesives, weld burns, rust, heavy oxides, and surface contaminants.



- Molded, abrasive filled bristles finish, polish, and deburr, more effectively than wire brushes
- Proprietary 3M™ Ceramic Abrasive Grain blend provides high degree of finish quality throughout the life of the disc
- Cleans with minimal pressure

Product ID	Product Name	MOQ	OU
7000046180	Scotch-Brite™ Radial Bristle Brush BB-ZB, 152 mm x 11.11 mm x 25.4 mm, 6 Micron, Peach, Type C, With Adaptor	5	Each
7100138300	Scotch-Brite™ Radial Bristle Brush BB-ZB, 152 mm x 11.11 mm x 25.4 mm, P80, Yellow, Type C, With adapter	5	Each
7100138298	Scotch-Brite™ Radial Bristle Brush BB-ZB, 152 mm x 11.11 mm x 25.4 mm, P120, White, Type C, With adapter	5	Each
7000021284	Scotch-Brite™ Radial Bristle Brush BB-ZB, 152 mm x 11.11 mm x 25.4 mm, P400, Blue, Type C, With adapter	5	Each
7100138290	Scotch-Brite™ Radial Bristle Brush BB-ZB, 152 mm x 12.7 mm x 25.4 mm, P36, Brown, Type A, With adapter	5	Each
7100138347	Scotch-Brite™ Radial Bristle Brush BB-ZB, 152 mm x 12.7 mm x 25.4 mm, P50, Green, Type A, With adapter	5	Each
7100138291	Scotch-Brite™ Radial Bristle Brush BB-ZB, 152 mm x 12.7 mm x 25.4 mm, P80, Yellow, Type A, With adapter	5	Each
7100138299	Scotch-Brite <sup>™</sup> Radial Bristle Brush BB-ZB, 152 mm x 12.7 mm x 25.4 mm, P220, Red, Type C, With adapter	5	Each
7000046181	Scotch-Brite™ Radial Bristle Brush BB-ZB, 152 mm x 22 mm x 25.4 mm, 1 Micron, Light green, Type C, With Adaptor	5	Each
7100138337	Scotch-Brite™ Radial Bristle Brush BB-ZB, 193.7 mm x 25.4 mm x 31.8 mm, P80, Yellow, Type C, With adapter	2	Each
7100138338	Scotch-Brite™ Radial Bristle Brush BB-ZB, 193.7 mm x 25.4 mm x 31.8 mm, P120, White, Type C, With adapter	2	Each
7100138335	Scotch-Brite™ Radial Bristle Brush BB-ZB, 193.7 mm x 25.4 mm x 31.8 mm, P220, Red, Type C, With adapter	2	Each
7100138332	Scotch-Brite™ Radial Bristle Brush BB-ZB, 203 mm x 25.4 mm x 31.8 mm, P50, Green, Type S, With adapter	2	Each
7100138333	Scotch-Brite™ Radial Bristle Brush BB-ZB, 203 mm x 25.4 mm x 31.8 mm, P80, Yellow, Type S, With adapter	2	Each
7100138334	Scotch-Brite <sup>™</sup> Radial Bristle Brush BB-ZB, 203 mm x 25.4 mm x 31.8 mm, P120, White, Type S, With adapter	2	Each
7100138336	Scotch-Brite™ Radial Bristle Brush BB-ZB, Type C, 193.7 mm x 25.4 mm x 31.8 mm, P400 with Flange	2	Each

### Scotch-Brite™ Radial Bristle Disc

Scotch-Brite™ Radial Bristle Disc, using proprietary 3M™ Ceramic Abrasive Grain and molded, flexible bristles, provides more surface contact than wire brushes and maintains abrasive property throughout the life of the disc. Our fast-running disc removes paint, stains, adhesives, weld burns, rust, heavy oxides, and surface contaminants from large areas.



- Molded, abrasive-filled bristles strip, deburr, blend, finish, polish, clean, and remove coatings more effectively, with less pressure than wire brushes
- Proprietary 3M<sup>™</sup> Ceramic Abrasive Grain provides aggressive cutting and consistent finish quality throughout the life of the disc
- Flexible bristles require less pressure than wire brushes and conform to contours, even on complex parts

Product ID	Product Name	MOQ	OU
7000046161	Scotch-Brite™ Radial Bristle Disc RB-ZB, 76.2 mm x 9 mm, 6 μm, Type C	80	Each
7000046125	Scotch-Brite <sup>™</sup> Radial Bristle Disc RD-ZB, 14 mm x 1.58 mm, P400, Blue, Type C	192	Each
7000000764	Scotch-Brite™ Radial Bristle Disc RD-ZB, 14 mm x 4.23 mm, P120, White, Type C	192	Each
7100002321	Scotch-Brite™ Radial Bristle Disc RD-ZB, 14.28 mm x 1.58 mm, P220, Red	192	Each
7000046127	Scotch-Brite™ Radial Bristle Disc RD-ZB, 14.28 mm x 1.58 mm, Pol 1, Type C	192	Each
7000000766	Scotch-Brite™ Radial Bristle Disc RD-ZB, 19 mm x 1.58 mm, 1 Micron, Light Green, Type C	192	Each
7000000765	Scotch-Brite™ Radial Bristle Disc RD-ZB, 19 mm x 1.58 mm, 6 Micron, Type C	192	Each
7000000757	Scotch-Brite™ Radial Bristle Disc RD-ZB, 19 mm x 1.58 mm, P80, Yellow, Type C	192	Each
7000000758	Scotch-Brite <sup>™</sup> Radial Bristle Disc RD-ZB, 19 mm x 1.58 mm, P220, Red, Type C	192	Each
7000000759	Scotch-Brite™ Radial Bristle Disc RD-ZB, 19 mm x 1.58 mm, P400, Blue, Type C	192	Each
7000000760	Scotch-Brite <sup>™</sup> Radial Bristle Disc RD-ZB, 19 mm x 1.58 mm, Pumice, Type C	192	Each
7100138342	Scotch-Brite™ Radial Bristle Disc RD-ZB, 19.1 mm x 1.59 mm, P120, White, Type C	192	Each
7100138326	Scotch-Brite™ Radial Bristle Disc RD-ZB, 25 mm x 3.18 mm, P36, Brown, Type C	96	Each
7000000761	Scotch-Brite™ Radial Bristle Disc RD-ZB, 25 mm x 3.18 mm, P50, Green, Type C	96	Each
7000000762	Scotch-Brite™ Radial Bristle Disc RD-ZB, 25 mm x 3.18 mm, P80, Yellow, Type C	96	Each
7000000763	Scotch-Brite™ Radial Bristle Disc RD-ZB, 25 mm x 3.18 mm, P120, White, Type C	96	Each
7000046159	Scotch-Brite™ Radial Bristle Disc RD-ZB, 50 mm x 9.53 mm, 6 Micron, Peach, Type C	80	Each
7000046158	Scotch-Brite™ Radial Bristle Disc RD-ZB, 50 mm x 9.53 mm, 6 Micron, Peach, Type C	80	Each
7100138293	Scotch-Brite™ Radial Bristle Disc RD-ZB, 50.8 mm x 9.53 mm, P80, Yellow, Type C	80	Each
7100138294	Scotch-Brite <sup>™</sup> Radial Bristle Disc RD-ZB, 50.8 mm x 9.53 mm, P120, White, Type C	80	Each
7100138295	Scotch-Brite™ Radial Bristle Disc RD-ZB, 50.8 mm x 9.53 mm, P220, Red, Type C	80	Each
7000028529	Scotch-Brite <sup>™</sup> Radial Bristle Disc RD-ZB, 50.8 mm x 9.53 mm, P400, Blue, Type C	80	Each
7100138323	Scotch-Brite™ Radial Bristle Disc RD-ZB, 75 mm x 9.53 mm, P50, Green, Type C	40	Each
7000000771	Scotch-Brite™ Radial Bristle Disc RD-ZB, 75 mm x 9.53 mm, P80, Yellow, Type C	80	Each
7100138297	Scotch-Brite™ Radial Bristle Disc RD-ZB, 75 mm x 9.53 mm, P220, Red, Type C	80	Each
7000028532	Scotch-Brite™ Radial Bristle Disc RD-ZB, 75 mm x 9.53 mm, P400, Blue, Type C	80	Each
7100007341	Scotch-Brite™ Radial Bristle Disc RD-ZB, 75 mm, 1 Micron, Light Green, Type C	80	Each
7000000749	Scotch-Brite™ Radial Bristle Disc RD-ZB, 76 mm x 9.52 mm, P120, White, Type C	40	Each
7100138296	Scotch-Brite <sup>™</sup> Radial Bristle Disc RD-ZB, 76 mm x 9.52 mm, P120, White, Type C	80	Each
7100138324	Scotch-Brite™ Radial Bristle Disc RD-ZB, 76.2 mm x 9.53 mm, P80, Yellow	40	Each



### Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB

Scotch-Brite™ Radial Bristle Brush Replacement Discs can be used to refill or expand the width of our Scotch-Brite™ Radial Bristle Brush (adapter sold separately). The molded, flexible bristles are filled with proprietary 3M™ Ceramic Abrasive Grain to provide a high quality finish with minimal pressure. Use the brush to effectively clean, finish, polish and deburr irregular surfaces.



- Molded, abrasive filled bristles clean, finish, polish, and deburr
- Additional discs allow for a greater range of brush widths
- Proprietary 3M<sup>™</sup> Ceramic Abrasive Grain blend provides high degree of finish quality throughout the life of the disc

Product ID	Product Name	MOQ	OU
7100138292	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 152 mm, P36, Type A	80	Each
7100138327	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 152 mm, P50, Green, Type A	2	Pack
7100138194	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 152 mm, P80, Yellow, Type A	80	Each
7100138301	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 152 mm, P80, Yellow, Type C	80	Each
7000021285	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 152 mm, P120, White, Type C	2	Pack
7100138302	Scotch-Brite <sup>™</sup> Radial Bristle Brush Replacement Disc BB-ZB, 152 mm, P220, Red, Type C	80	Each
7000144604	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 152 mm, P400, Blue, Type C	80	Each
7100138303	Scotch-Brite <sup>™</sup> Radial Bristle Brush Replacement Disc BB-ZB, 193.7 mm, P80, Yellow, Type C	70	Each
7100138304	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 193.7 mm, P120, White, Type C	70	Each
7100138341	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 193.7 mm, P220, Red, Type C	1	Pack
7100138339	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 203 mm, P50, Green, Type S	1	Pack
7100138340	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 203 mm, P80, Type S,	1	Pack
7100038608	Scotch-Brite™ Radial Bristle Brush Replacement Disc BB-ZB, 203.2 mm, P120, Type S,	1	Pack

#### Scotch-Brite™ Roloc™ Bristle Disc RD-ZB

Scotch-Brite™ Roloc™ Bristle Disc, using proprietary ceramic abrasive grain blended with aluminum oxide and molded, flexible bristles, provide more surface contact than wire brushes and retain abrasive properties throughout the life of the disc.



- Molded, abrasive filled bristles strip, deburr, blend, finish, polish, clean, and remove coatings more effectively than wire brushes
- Proprietary 3M<sup>™</sup> Ceramic Abrasive Grain blend provides high degree of finish quality throughout the life of the disc
- Bristle spacing is ideal for coating removal and other high-loading substances

Product ID	Product Name	MOQ	OU
7100138319	Scotch-Brite™ Roloc™ Bristle Disc RD-ZB, 25 mm x 15.8 mm, P80, Yellow	80	Each
7000000740	Scotch-Brite™ Roloc™ Bristle Disc RD-ZB, 25.4 mm x 15.8 mm, P50, Green	20	Each
7000000741	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Bristle Disc RD-ZB, 25.4 mm x 15.8 mm, P120, White,	80	Each
7100151522	Scotch-Brite™ Roloc™ Bristle Disc RD-ZB, 50 mm, P80	10	Each
7100138305	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Bristle Disc RD-ZB, 76 mm x 15.8mm, P50, Green	40	Each
7100138307	Scotch-Brite™ Roloc™ Bristle Disc RD-ZB, 76 mm x 15.8mm, P80, Yellow	10	Each
7100138306	Scotch-Brite™ Roloc™ Bristle Disc RD-ZB, 76 mm x 15.8mm, P120, White	10	Each
7100138285	Scotch-Brite™ Roloc™ Bristle Disc RD-ZB, TR, Green, 50 mm x 15.9 mm, Tapered	40	Each
7100138286	Scotch-Brite™ Roloc™ Bristle Disc RD-ZB, White, 50 mm x 15.8 mm, P120, 07528	40	Each

### Scotch-Brite™ Roloc™ Bristle Disc RD-ZB

Scotch-Brite™ Roloc™ Bristle Disc, using proprietary ceramic abrasive grain blended with aluminum oxide and molded, flexible bristles, provide more surface contact than wire brushes and retain abrasive properties throughout the life of the disc.



- Molded, abrasive filled bristles strip, deburr, blend, finish, polish, clean, and remove coatings more
  effectively than wire brushes
- Proprietary 3M<sup>™</sup> Ceramic Abrasive Grain blend provides high degree of finish quality throughout the life of the disc
- Bristle spacing is ideal for coating removal and other high-loading substances

Product ID	Product Name	MOQ	OU
7100138284	Scotch-Brite <sup>™</sup> Roloc <sup>™</sup> Bristle Disc RD-ZB, Yellow, 50 mm x 15.8 mm, P80, 07525	40	Each

### Scotch-Brite™ Roloc™ Body Man's Bristle Disc

Our Scotch-Brite™ Roloc™ Body Man's Bristle Disc is made with stiff polymer bristles that are spaced out and form a radial pattern for optimum load resistance. The disc will not get clogged by debris, making it a good match for cleaning on high-loading substrates and great for removing rubberized undercoating, seam sealer, rust and paint.



- Molded, abrasive-filled bristles strip, deburr, blend, finish, polish, clean, and remove coatings more effectively, with less pressure than wire brushes
- Proprietary 3M<sup>™</sup> Ceramic Abrasive Grain provides aggressive cutting and consistent finish quality throughout the life of the disc
- Flexible bristles require less pressure than wire brushes and conform to contours, even on complex parts

Product ID	Product Name	MOQ	OU
7000000775	Scotch-Brite™ Roloc™ Bristle Disc, RD-ZB, Purple, 50 mm, 36	24	Each

### 3M™ Stripe Off Wheel

Our 3M™ Stripe Off Wheel was designed for high-speed removal of vinyl, decals, tape, graphics and double sided molding striping and trim. We engineered this wheel to help operators achieve effective and efficient decal removal without damaging the surface below.



- Engineered to remove unwanted decals and stripes without damaging the substrate
- $\bullet$  Also works well for removal of vinyl, tape and graphics
- 4 inch diameter and 5/8 inch thickness make this wheel great for small, hard-to-remove detailing

Product ID	Product Name	MOQ	OU
7100150191	3M <sup>™</sup> Clean and Strip <sup>™</sup> Stripe off wheel, Beige, 100 mm x 16 mm	5	Each



## Flap Brushes

## Scotch-Brite™ Cut and Polish Flap Brush CP-FB

Scotch-Brite™ Cut and Polish Flap Brushes are a versatile, high-performance alternative to conventional bristle brushes and messy, technique-dependent buffing compounds. These long-lasting, precision-made brushes give you improved consistency and greater control over a number of critical metal prep and finishing tasks, including cleaning, deburring, polishing, and aesthetic finishing.




- Aluminum Oxide mineral cuts fast and sharp for aggressive cleaning and bright finishing
- Available in very fine (VFN) and medium (MED) grades to help achieve desired finishes
- Great for cleaning, deburring, polishing and finishing

Product ID	Product Name	MOQ	OU
7000077966	Scotch-Brite™ Cut and Polish Flap Brush CP-FB, A MED, 75 mm x 45 mm	10	Each

### Scotch-Brite™ Clean and Strip Flap Brush

Scotch-Brite™ Clean and Strip Flap Brushes are impregnated with aluminium oxide abrasive mineral and bonded to a fibre core.



- Uniform surface finish
- Features an abrasive mineral bonded to a fibre core

Product ID	Product Name	MOQ	OU
7000091730	Scotch-Brite™ Clean and Strip Flap Brush, 100 mm x 100 mm x 19 mm, A CRS	2	Each

### Scotch-Brite™ Shaft Mounted Flap Brush

Scotch-Brite™ Shaft Mounted Flap Brushes are made of flaps of non-woven material mounted on a spindle. Our brushes offer a fine, matt scratch pattern.

- Fine, matt scratch pattern
- No chatter marks
- Light deburring



Product ID	Product Name	MOQ	OU
7100093971	Scotch-Brite™ Shaft Mounted Flap Brush PF-ZS, 75 mm x 45 mm x 6 mm, AMED	10	Each
7100093973	Scotch-Brite™ Shaft Mounted Flap Brush PF-ZS, 100 mm x 45 mm x 6 mm, AMED	10	Each

## Scotch-Brite™ Roloc™ Cut and Polish Flap Brush

Our Scotch-Brite™ Roloc™ Cut and Polish Flap Brush uses our unique non-woven web design, binding synthetic fibers and abrasive particles to create a conformable, three-dimensional material to provide a smooth and polished finish.

- Aluminum oxide mineral easily removes surface imperfections, helping to cut faster
- Easy abrasive wheel attachment
- Heavy-duty design prolongs service life

Product ID	Product Name	MOQ	OU
7000077928	Scotch-Brite™ Roloc™ Cut and Polish Flap Brush PF-ZR, 50 mm x 25 mm, A MED	25	Each
7000077904	Scotch-Brite™ Roloc™ Cut and Polish Flap Brush PF-ZR, 75 mm x 35 mm, AMED	10	Each



# **Sheets & Rolls**

# Non-woven Sheets & Rolls

#### Scotch-Brite™ Durable Flex Roll

Scotch-Brite™ Durable Flex Roll is an aggressive and long lasting non-woven roll. Our flex rolls are used for deburring, finishing, blending, and cleaning.

- Aggressive and long lasting non-woven roll
- Reinforced low-stretch backing offers good flexibility and great edge durability
- Use for deburring, finishing, blending, and cleaning





#### Scotch-Brite™ 7447 PRO Roll

Scotch-Brite™ 7447 PRO Roll combines flexible fibres with finely graded aluminium oxide particles for a sharp consistent cut. Use our 7447 PRO instead of steel wool, wire brushes, sandpaper and other non-woven products for cleaning or finishing.



- With fast cutting denser mineral coating on fibres compared to 7447, for a uniform scratch
- Very fine grade aluminium oxide abrasive cleans and finishes efficiently
- Long lasting nylon non-woven material resists tearing, loading and rust

Product ID	Product Name	MOQ	OU
7100288556	Scotch-Brite <sup>™</sup> Roll 7447 Pro, AVFN, 100 mm x 10 m, 4 Roll/Case	4	Roll
7100288455	Scotch-Brite™ Roll 7447 Pro, AVFN, 125 mm x 10 m, 3 Roll/Case	3	Roll

#### Scotch-Brite™ 7448 PRO Roll

Scotch-Brite™ 7448 PRO Roll comprises of durable, precision coated fibres that cut fast and provide consistent finishes. Our unique design of ultra-fine mineral and coated, flexible fibres is perfect for prepping surfaces for paint and primer, general scuffing and hand blending.



- Use for light scuffing and surface prep for better subsequent coating adhesion
- Ideal for cleaning, scuffing, finishing, and light paint removal on a variety of metals and plastics
- Denser mineral placement than 7448 which allows for uniform scratch and a faster cut rate

Product ID	Product Name	MOQ	OU
7100288456	Scotch-Brite™ Roll 7448 Pro, SUFN, 100 mm x 10 m, 4 Roll/Case	4	Roll
7100288457	Scotch-Brite™ Roll 7448 Pro, SUFN, 125 mm x 10 m, 3 Roll/Case	3	Roll

# Sheets & Rolls

### Scotch-Brite™ Cut and Polish Sheet 7440

Scotch-Brite™ Cut and Polish Sheet features a tough, tight and dense web that is conformable – allowing it to adapt to unique contours and get into hard to reach areas. Our cut and polish sheets can be used manually or on an in-line sander for metalworking, paint prep or coating and corrosion removal.



- Dense construction allows for aggressive blending, cleaning and polishing on metal surfaces
- Load resistant design assures consistent action across the sheet
- Conformable and soft for an even finish

Product ID	Product Name	MOQ	OU
7100182601	Scotch-Brite™ Cut and Polish Sheet 7440, 158 mm x 224 mm, A MED, Brown	60	Each

### Scotch-Brite™ Clean and Finish Sheet CF-SH

Scotch-Brite™ Clean and Finish Sheet uses a conformable non-woven web and a variety of mineral types to blend, clean, and finish. It also works well for contour finishing and lacquer finishing and polishing. The sheet is flexible, making it effective for getting into hard-to-reach areas to produce a uniform finish.



- Abrasive mineral adhered to non-woven web are ideal for cleaning, blending, finishing, and light coating and corrosion removal
- Can be used with polishing compounds to create a gloss finish on wood
- Conformable pad gets into corners and over contoured surfaces to produce a uniform finish

Product ID	Product Name	MOQ	OU
7100182599	Scotch-Brite™ Clean and Finish Sheet CF-SH, 158 mm x 224 mm, A VFN, Green	60	Each

#### Scotch-Brite™ Clean and Finish Roll CF-RL

Scotch-Brite™ Clean and Finish Roll provides consistent surface conditioning for the life of the product. Our clean and finish roll stock can be cut into any length.



- Cut-to-fit roll stock provides uniform finishing, blending, polishing, contour finishing, and cleaning
- Conformable pad gets into hard-to-reach areas
- Suitable for hand use or on oscillating and dual pad rubbing machines

Product ID	Product Name	MOQ	OU
7100182496	Scotch-Brite™ Clean and Finish Roll CF-RL, 120 mm x 10 m, A VFN HP	42	Roll
7100182533	Scotch-Brite™ Clean and Finish Roll CF-RL, 930 mm x 10 m, S UFN	6	Roll
7100182820	Scotch-Brite™ Clean and Finish Roll CF-RL, 100 m x 965 mm, A VFN	1	Roll
7100182231	Scotch-Brite <sup>™</sup> Clean and Finish Roll CF-RL, 100 mm x 10 m, A VFN	4	Roll
7100182499	Scotch-Brite™ Clean and Finish Roll CF-RL, 100 mm x 10 m, S UFN	4	Roll
7100182457	Scotch-Brite <sup>™</sup> Clean and Finish Roll CF-RL, 150 mm x 115 mm, A VFN	4	Roll

# Sheets & Rolls

### Scotch-Brite™ Wear Resistant Roll

Scotch-Brite™ Wear Resistant Rolls are for cleaning, finishing and light deburring.

- Do not alter geometry of workpiece
- Use for cleaning, finishing and light deburring
- Machine and manual applications



Product ID	Product Name	MOQ	OU
7100182515	Scotch-Brite <sup>™</sup> Wear Resistant Roll WR-RL, 115 mm x 10 m, A MED	4	Roll
7100182517	Scotch-Brite™ Wear Resistant Roll WR-RL, 300 mm x 10 m, A FIN	18	Roll

### Scotch-Brite™ General Purpose Sheet

Scotch-Brite™ General Purpose Sheet is an all-purpose web for cleaning, deburring and finishing applications. Our sheets give a controlled, repeatable cut.

- Controlled, repeatable cut
- Consistent finish
- Does not change the geometry of the workpiece



Product ID	Product Name	MOQ	OU
7100182594	Scotch-Brite™ General Purpose Sheet GP-SH, 158 mm x 224 mm, A FIN	60	Each

### Scotch-Brite™ Multi-Flex Sheet Roll MX-SR

Scotch-Brite™ Multi-Flex Sheet is a thin, tough, highly conformable, sharp cutting, non-woven abrasive.

- Highly conformable
- Sharp cutting
- Cleaning and finishing



Product ID	Product Name	MOQ	OU
7100182456	Scotch-Brite™ Multi-Flex Sheet Roll MX-SR, 100 mm x 200 mm, A VFN, No Hole	4	Roll



# Handheld Abrasives

# **Hand Pads**

# Scotch-Brite™ Durable Flex Hand Pad MX-HP

Our Scotch-Brite™ Durable Flex Hand Pad combines ultra flexibility with effective cutting action and precise hand control to accomplish tough cleaning jobs or produce fine finishing results.



- Superior alternative to steel wool, wire brushes, sandpaper, and other nonwoven products for cleaning
  or finishing tasks
- Suitable for use on wood, paints, metal, plastics, ceramics, porcelain, glass, rubber or composites
- Reusable pad resists tearing, splintering, loading and will never rust, providing a long, useful life

Product ID	Product Name	MOQ	OU
7100209414	Scotch-Brite™ Durable Flex Hand Pad MX-HP, 114 mm x 228 mm, A VFN	100	Each
7100209618	Scotch-Brite <sup>™</sup> Durable Flex Hand Pad MX-HP, 114 mm x 228 mm, S ULF	100	Each
7100182487	Scotch-Brite™ Durable Flex Hand Pad MX-HP, 200 mm x 100 mm, A VFN, Precut	4	Roll
7100182488	Scotch-Brite™ Durable Flex Hand Pad MX-HP, 200 mm x 100 mm, S UFN, Precut	4	Roll

#### Scotch-Brite™ Hand Pad 7447

Scotch-Brite<sup>™</sup> General Purpose Hand Pad 7447 combines flexibility with effective cutting action and precise hand control to accomplish tough cleaning jobs or produce fine finishing results, use after use. Very fine grade aluminum oxide abrasives cut fast and fine, leaving a smooth, finished surface. Suitable for use on a wide variety of materials and for many different tasks.



- Superior alternative to steel wool, wire brushes, sandpaper, and other nonwoven products for cleaning or finishing tasks
- Very fine grade aluminum oxide abrasive cleans, finishes, grains, denibs, and defuzzes
- Suitable for use on wood, metal, plastics, ceramics, porcelain, glass, rubber, or composites

Product ID	Product Name	MOQ	OU
7000000728	Scotch-Brite <sup>™</sup> Hand Pad 7447, 152 mm x 228 mm, A VFN	60	Each
7000027560	Scotch-Brite™ Hand Pad 7447, 152 mm x 228 mm, A VFN, Bulk,	1	Case
7100182554	Scotch-Brite™ Hand Pad 7447, 158 mm x 224 mm, A VFN	60	Each

#### Scotch-Brite™ Hand Pad 7447+

Scotch-Brite™ General Purpose Hand Pad 7447+ combines flexibility with effective cutting action and precise hand control to accomplish tough cleaning jobs or produce fine finishing results, use after use. Very fine grade aluminum oxide abrasives cut fast and fine, leaving a smooth, finished surface. Suitable for use on a wide variety of materials and for many different tasks.



- Superior alternative to steel wool, wire brushes, sandpaper, and other nonwoven products for cleaning or finishing tasks
- Very fine grade aluminum oxide abrasive cleans, finishes, grains, denibs, and defuzzes
- Suitable for use on wood, metal, plastics, ceramics, porcelain, glass, rubber, or composites

Product ID	Product Name	MOQ	OU
7100182588	Scotch-Brite™ Hand Pad 7447+, 158 mm x 224 mm, A VFN	60	Each

# Handheld Abrasives

### Scotch-Brite™ Hand Pad 7448+

Scotch-Brite™ Ultra Fine Hand Pad 7448+ combines durability for long life, flexibility for reaching tight areas, and can be used in place of steel wool for conditioning metal surfaces and paint prep. Unlike fine steel wool, Scotch-Brite pads will not shred during use, rust after use, or leave fine metal splinters.

- Ultra fine finishing action outperforms steel wool for cleaning, blending, prepping and finishing on metal, wood, plastics and composites
- Performs like steel wool grade 00 without shredding, rusting, or splintering
- Pad conforms to irregular surfaces and gets into corners without losing performance

Product ID	Product Name	MOQ	OU
7100182555	Scotch-Brite™ Hand Pad 7448+, 158 mm x 224 mm, S UFN, Grey	60	Each

### Scotch-Brite™ Hand Pad 7447 PRO

Scotch-Brite™ 7447 PRO Hand Pad combines flexibility with effective cutting action and precise hand control to help you accomplish tough cleaning jobs or produce fine finishing results, use after use. The tightly graded abrasive particles in this new pad provide a consistent, uniform scratch throughout life of the hand pad.




- Very fine grade aluminum oxide abrasive cleans, finishes, grains, denibs, and defuzzes
- Pad resists tearing, splintering, shredding, loading and will never rust, providing a long, useful life

Product ID	Product Name	MOQ	OU
7100288524	Scotch-Brite™ Handpad 7447 PRO, AVFN, 158 mm x 224 mm, 60 Ea/Case	60	Each

#### Scotch-Brite™ Hand Pad 7448 PRO

We developed Scotch-Brite™ 7448 PRO Hand Pad to combine durability for long life, flexibility for reaching tight areas, and to be used in place of steel wool for conditioning metal surfaces and paint prep in less time than conventional non-woven abrasive products. The tightly graded abrasive particles in our new pad provide a consistent, uniform scratch throughout life of the hand pad.



- Scotch-Brite™ PRO cuts faster and produces a more consistent finish than conventional non-woven abrasive products
- Performs like steel wool grade 00 without shredding, rusting, or splintering

Product ID	Product Name	MOQ	OU
7100288566	Scotch-Brite <sup>™</sup> Handpad 7448 PRO, SUFN, 158 mm x 224 mm, 60 Ea/Case	60	Each





# Handheld Abrasives

# Scotch-Brite™ Heavy Duty Hand Pad 7440

The Scotch-Brite<sup>™</sup> Heavy Duty Hand Pad 7440 is our most aggressive and durable hand pad. Its super dense construction makes it an excellent choice for your heaviest cleaning, deburring, and finishing applications.

- Aggressive, durable pad is an excellent choice for your heaviest cleaning, deburring and finishing applications
- Very high density Scotch-Brite™ pad is super aggressive for quick stock removal
- Durable construction withstands extremely heavy use on the toughest surfaces



Product ID	Product Name	MOQ	OU
7100080459	Scotch-Brite™ Heavy Duty Hand Pad 7440, 152 mm x 228 mm, CRS	40	Each

### Scotch-Brite™ Hand Pad Pre-Cut on a Roll CF-SR

Scotch-Brite™ Hand Pads pre-cut on a roll, combines flexibility with effective cutting action and precise hand control to accomplish tough cleaning jobs or produce fine finishing results, use after use. Very fine grade aluminum oxide abrasives cut fast and fine, leaving a smooth, finished surface.

- Superior alternative to steel wool, wire brushes, sandpaper, and other nonwoven products for cleaning or finishing tasks
- Cleans, finishes, grains, denibs, and defuzzes
- Suitable for use on wood, metal, plastics, ceramics, porcelain, glass, rubber, or composites



Product ID	Product Name	MOQ	OU
7100182225	Scotch-Brite™ Hand Pad Pre-Cut on a Roll CF-SR, 150 mm x 115 mm, S UFN, Grey	4	Roll

#### 3M™ Tack Pad

Surface preparation for spraying primers, base coat or clear coat paints is a smooth transition as dust is drawn into the tack pad leaving a drag-free surface. Hands are less sticky due to the reduction of adhesive transfer.

- Helps reduce adhesive transfer to the hands
- Hands are less sticky due to the reduction of adhesive transfer
- Leaves no drag marks behind while dust is drawn into the tack pad



Product ID	Product Name	MOQ	OU
7100193601	3M <sup>™</sup> Tack Pad, 175 mm x 235 mm, 07910	60	Each





# What's in this catalogue?

In this catalogue we have only included our Core Belt Range. These are our stocked items that represent a sub-set of our overall belt offering to the market. This sub-set covers the most common sizes and material requirements.

Choose the required material from the **Configurable Product Code Tables overleaf** Log-on to bCom and search for the

There are 1000's of potential belt size and material combinations, all carrying different prices.

To make ordering easy for our customers, we use Configurable **Product Codes that represent** a variety of material and grade combinations.

These universal product codes can be applied to any available size combination to create a unique price using our bCOM distributor ordering portal - they are listed on the next pages for your reference.

- chosen Product Code
- Enter required width, length and quantity values
- **Click GET PRICE**



# Configurable product codes.



# 3M<sup>™</sup> Conventional Mineral

SAP ID	Material	Grade
7100080482	307D	P120
7100080483	307D	P150
7100080484	307D	P180
7100080485	307D	P220
7100080486	307D	P240
7100080487	307D	P320
7100080488	307D	P400

SAPID	Material	Grade
7100080489	307D	P600
7100091777	384F	36+
7100091779	384F	50+
7100091799	384F	60+
7100091802	384F	80+
7100091804	384F	120+
7100091806	384F	150+
7100091808	384F	180+
7100091813	384F	220+
7100091815	384F	240+
7100091817	384F	320+
7100091819	384F	400+



# **Scotch-Brite**<sup>™</sup> **Non-woven**

SAP ID Material Grade	
7100013687 DF-BL ACRS	
7100012444 DF-BL AFIN	
7100013155 DF-BL AMED	
7100253860 FN-BC AMED	
7100156430 SC-BF ACRS	
7100012858 SC-BF AMED	
7100013611 SC-BF AVFN	

SAPID	Material	Grade
7100013507	SC-BL	ACRS
7100171628	SC-BL	AMED
7100000134	SC-BL	AVFN
7100012618	SC-BL	SSFN
7100012150	SC-BL	SVFN
7100048459	SC-BL	TYPT
7100013534	SC-BS	ACRS
7100012358	SC-BS	AMED
7100012347	SC-BS	AVFN
7100012085	SC-BS	SSFN



# Configurable product codes.



# 3M<sup>™</sup> Trizact<sup>™</sup> Micro and Macro-replicated

SAP ID	Material	Grade
7100052788	217EA	A6
7100052787	217EA	A16
7100052786	217EA	A30
7100052768	217EA	A45
7100052769	217EA	A65
7100052770	217EA	A80
7100052771	217EA	A100
7100007882	237AA	A6
7100007878	237AA	A16
7100007880	237AA	A30
7100007881	237AA	A45
7100007883	237AA	A65
7100007884	237AA	A80
7100007877	237AA	A100
7100007879	237AA	A160
7100051346	253FA	A6

SAPID	Material	Grade
7100049039	253FA	A16
7100051853	253FA	A30
7100052775	253FA	A45
7100052778	253FA	A100
7100052733	307EA	A6
7100052732	307EA	A16
7100052731	307EA	A30
7100052730	307EA	A45
7100052729	307EA	A65
7100052728	307EA	A80
7100112315	307EA	A100
7100052831	337DC	A30
7100052826	337DC	A45
7100048818	337DC	A65
7100052827	337DC	A100
7100052828	337DC	A160
7100052829	337DC	A300
7100065454	347FC	A30
7100065455	347FC	A45
7100065456	347FC	A65
7100065457	347FC	A100
7100065458	347FC	A160
7100065459	347FC	A300
7100070052	363FC	A45
7100070054	363FC	A65
7100052841	363FC	A100
7100052840	363FC	A160
7100052839	363FC	A300



# **Cloth belts**

Focus

### 3M™ Cubitron™ 3 Cloth Belt 1184F

Introducing the 3M<sup>™</sup> Cubitron<sup>™</sup> 3 Cloth Belt 1184F, featuring a re-engineered 3M Precision-Shaped Grain. Designed to give you the performance boost you need, this belt outperforms competitive belts, as well as previous-generation 3M belts. This cloth belt delivers up to 86% faster cut rate compared to crushed ceramic competitors - providing the ultimate in performance. Available in 36+ grit for medium and high-pressure applications like gate grinding and other heavy grinding.



- 3M RE-ENGINEERED PRECISION-SHAPED GRAIN: Helps increase cut rate and abrasive life to boost productivity
- OPTIMIZED FOR ROBOTICS: Built for manual and automated applications designed for faster performance
- LONGER LIFE: Fewer changeouts needed and less downtime

Product ID	Product Name	MOQ	OU
7100329008	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 13 mm x 457 mm	1	Each
7100329007	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 13 mm x 610 mm	1	Each
7100329006	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 50 mm x 2000 mm	1	Each
7100329005	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cloth Belt 1184F, 36+ YF weight, 50 mm x 2500 mm	1	Each
7100329004	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 50 mm x 3500 mm	1	Each
7100329003	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cloth Belt 1184F, 36+ YF weight, 50 mm x 4000 mm	1	Each
7100326912	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 75 mm x 2000 mm	1	Each
7100329009	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 75 mm x 2500 mm	1	Each
7100329010	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 75 mm x 3000 mm	1	Each
7100329014	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 100 mm x 1220 mm	1	Each
7100329013	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 100 mm x 2000 mm	1	Each
7100329046	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 100 mm x 2200 mm	1	Each
7100329012	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cloth Belt 1184F, 36+ YF weight, 100 mm x 3000 mm	1	Each
7100329047	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 100 mm x 3200 mm	1	Each
7100329011	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cloth Belt 1184F, 36+ YF weight, 120 mm x 2500 mm	1	Each
7100329043	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 150 mm x 2000 mm	1	Each
7100329045	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 150 mm x 2900 mm	1	Each
7100329044	3M™ Cubitron™ 3 Cloth Belt 1184F, 36+ YF weight, 150 mm x 3500 mm	1	Each
7100313150	3M <sup>™</sup> Cubitron <sup>™</sup> 3 Cloth Belt 1184F, 36+ YF-weight, Config	1	Each

# Belts

# 3M™ Cubitron™ II Cloth Belt 984F

3M™ Cubitron™ II Cloth Belts 984F offer revolutionary performance with 3M Precision Shaped Grain that slices clean through metal. Our 984F belts contain a grinding aid, making it ideal for medium to high pressure applications.



- Minimise operator fatigue as 3M Precision Shaped Grain requires less grinding pressure
- Cool running temperature reduces risk of discolouration and heat related stress cracks
- 3M Precision Shaped Grain fractures into self-sharpening points, cutting exceptionally fast and increasing productivity

Product ID	Product Name	MOQ	OU
7100218943	3M™ Cubitron™ II Cloth Belt 984F, 10 mm x 305 mm, 80+	100	Each
7000060872	3M™ Cubitron™ II Cloth Belt 984F, 10 mm x 330 mm, 60+	100	Each
7000060879	3M™ Cubitron™ II Cloth Belt 984F, 10 mm x 330 mm, 80+	200	Each
7000060889	3M™ Cubitron™ II Cloth Belt 984F, 12 mm x 330 mm, 60+	100	Each
7000060887	3M™ Cubitron™ II Cloth Belt 984F, 12 mm x 330 mm, 80+	100	Each
7100218990	3M™ Cubitron™ II Cloth Belt 984F, 12 mm x 520 mm, 36+	100	Each
7000060873	3M™ Cubitron™ II Cloth Belt 984F, 13 mm x 305 mm, 60+	100	Each
7000060865	3M™ Cubitron™ II Cloth Belt 984F, 13 mm x 457 mm, 60+	100	Each
7000060866	3M™ Cubitron™ II Cloth Belt 984F, 13 mm x 457 mm, 80+	100	Each
7000060862	3M™ Cubitron™ II Cloth Belt 984F, 13 mm x 610 mm, 36+	100	Each
7000060867	3M™ Cubitron™ II Cloth Belt 984F, 13 mm x 610 mm, 60+	100	Each
7000060868	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 13 mm x 610 mm, 80+	100	Each
7000060870	3M™ Cubitron™ II Cloth Belt 984F, 20 mm x 457 mm, 60+	100	Each
7000060863	3M™ Cubitron™ II Cloth Belt 984F, 20 mm x 520 mm, 36+	100	Each
7000060869	3M™ Cubitron™ II Cloth Belt 984F, 20 mm x 520 mm, 60+	100	Each
7000060880	3M™ Cubitron™ II Cloth Belt 984F, 20 mm x 520 mm, 80+	100	Each
7000060823	3M™ Cubitron™ II Cloth Belt 984F, 25 mm x 4000 mm, 36+	40	Each
7100219014	3M™ Cubitron™ II Cloth Belt 984F, 30 mm x 1250 mm, 80+	40	Each
7000060768	3M™ Cubitron™ II Cloth Belt 984F, 38 mm x 1525 mm, 36+	40	Each
7100218996	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 787 mm, 36+	30	Each
7100218988	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 1000 mm, 36+	30	Each
7100219008	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 1500 mm, 36+	30	Each
7000060748	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 2000 mm, 36+	30	Each
7000060848	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 2000 mm, 60+	30	Each
7000060849	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 50 mm x 2000 mm, 80+	30	Each
7000060741	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 2500 mm, 36+	30	Each
7100218978	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 2500 mm, 60+	30	Each
7100218982	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 2740 mm, 60+	30	Each
7000060743	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 3500 mm, 36+	30	Each
7100218948	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 3500 mm, 60+	30	Each
7100218973	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 3500 mm, 80+	30	Each
7000060754	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 4000 mm, 36+	30	Each
7000060780	3M™ Cubitron™ II Cloth Belt 984F, 50 mm x 4000 mm, 60+	30	Each
7100219016	3M™ Cubitron™ II Cloth Belt 984F, 60 mm x 2175 mm, 36+	30	Each
7000060749	3M™ Cubitron™ II Cloth Belt 984F, 60 mm x 3500 mm, 36+	30	Each



# 3M™ Cubitron™ II Cloth Belt 984F

3M™ Cubitron™ II Cloth Belts 984F offer revolutionary performance with 3M Precision Shaped Grain that slices clean through metal. Our 984F belts contain a grinding aid, making it ideal for medium to high pressure applications.



- Minimise operator fatigue as 3M Precision Shaped Grain requires less grinding pressure
- Cool running temperature reduces risk of discolouration and heat related stress cracks
- 3M Precision Shaped Grain fractures into self-sharpening points, cutting exceptionally fast and increasing productivity

7002193021         3M* Cubitron* II Cloth Belt 984F, 70 mm x 2000 mm, 36+         20         Each           7000219059         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 36+         20         Each           7000080778         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 60+         20         Each           7000080777         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 80+         20         Each           7000080726         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           7000080727         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           7000080728         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           7000219024         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 80+         20         Each           7000219025         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 80+         20         Each           700219026         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 80+         20         Each           700219027         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 80+         20         Each           700219028         3M* Cubitron* II Cloth Belt 984F, 70 mm x 2000 mm, 80+         20         Each           700219029         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2500 mm, 36+	Product ID	Product Name	MOQ	OU
700066753         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 80+         20         Each           700066778         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 80+         20         Each           700066772         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2250 mm, 36+         20         Each           700066762         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           700066762         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           700066763         3M* Cubitron* II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           700066766         3M* Cubitron* II Cloth Belt 984F, 80 mm x 2000 mm, 80+         20         Each           700076776         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           700218901         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           7100218921         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           7100218922         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           7100218923         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           7100218930         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2500 mm, 36+	7100219021	3M™ Cubitron™ II Cloth Belt 984F, 70 mm x 2000 mm, 60+	30	Each
7000660778         3M** Cubitron* II Cloth Belt 984F, 75 mm x 2000 mm, 80+         20         Each           7000660777         3M** Cubitron* II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           7000660762         3M** Cubitron* II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           700060742         3M** Cubitron* II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           700060766         3M** Cubitron* II Cloth Belt 984F, 75 mm x 4000 mm, 36+         20         Each           700060766         3M** Cubitron* II Cloth Belt 984F, 100 mm x 2000 mm, 80+         20         Each           700060767         3M** Cubitron* II Cloth Belt 984F, 100 mm x 2000 mm, 80+         20         Each           7000218928         3M** Cubitron* II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           700218921         3M** Cubitron* II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           700218922         3M** Cubitron* II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           700218922         3M** Cubitron* II Cloth Belt 984F, 100 mm x 2450 mm, 36+         20         Each           700218928         3M** Cubitron* II Cloth Belt 984F, 100 mm x 2450 mm, 36+         20         Each           700218929         3M** Cubitron* II Cloth Belt 984F, 100 mm x 3450 mm,	7100219059	3M™ Cubitron™ II Cloth Belt 984F, 70 mm x 4000 mm, 36+	20	Each
7000060777         3M**Cubitron** II Cloth Belt 984F, 75 mm x 2050 mm, 36+         20         Each           7000060742         3M**Cubitron** II Cloth Belt 984F, 75 mm x 2550 mm, 36+         20         Each           7000060742         3M**Cubitron** II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           7000060766         3M**Cubitron** II Cloth Belt 984F, 75 mm x 4000 mm, 36+         20         Each           7000060766         3M**Cubitron** II Cloth Belt 984F, 80 mm x 9000 mm, 36+         20         Each           700019005         3M**Cubitron** II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7000219021         3M**Cubitron** II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           700219022         3M**Cubitron** II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           700219021         3M**Cubitron** II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           700219022         3M**Cubitron** II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           700219030         3M**Cubitron** II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           700219030         3M**Cubitron** II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           700219070         3M**Cubitron** II Cloth Belt 984F, 100 mm x 2500 mm	7000060753	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 75 mm x 2000 mm, 36+	20	Each
700060762         3M" Cubitron" II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           700060742         3M" Cubitron" II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           700060762         3M" Cubitron" II Cloth Belt 984F, 75 mm x 4000 mm, 36+         20         Each           700060766         3M" Cubitron" II Cloth Belt 984F, 75 mm x 3000 mm, 36+         20         Each           700060767         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 60+         20         Each           7100219022         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           7100219022         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           7100219023         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           71002198072         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           7100219808         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7100219000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2350 mm, 36+         20         Each           700219000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7000219000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+	7000060778	3M™ Cubitron™ II Cloth Belt 984F, 75 mm x 2000 mm, 60+	20	Each
7000060742         3M" Cubitron" II Cloth Belt 984F, 75 mm x 2500 mm, 36+         20         Each           700029024         3M" Cubitron" II Cloth Belt 984F, 75 mm x 4000 mm, 36+         20         Each           7000060766         3M" Cubitron" II Cloth Belt 984F, 75 mm x 3000 mm, 36+         20         Each           7000060767         3M" Cubitron" II Cloth Belt 984F, 100 mm x 1200 mm, 36+         20         Each           7000060767         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           700018981         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           7100219922         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           7100219972         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           700018989         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7000219900         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           7000219010         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3000 mm, 36+         20         Each           7000219020         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7000219030         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+ </td <td>7000060777</td> <td>3M<sup>™</sup> Cubitron<sup>™</sup> II Cloth Belt 984F, 75 mm x 2000 mm, 80+</td> <td>20</td> <td>Each</td>	7000060777	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 75 mm x 2000 mm, 80+	20	Each
7100219024         3M" Cubitron" II Cloth Belt 984F, 75 mm x 4000 mm, 36+         20         Each           7000060766         3M" Cubitron" II Cloth Belt 984F, 75 mm x 3000 mm, 36+         20         Each           7100219005         3M" Cubitron" II Cloth Belt 984F, 80 mm x 9000 mm, 80+         20         Each           7000060767         3M" Cubitron" II Cloth Belt 984F, 100 mm x 1220 mm, 36+         20         Each           7100219981         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           7100218972         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           7100218969         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           700060776         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           700060776         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           700060776         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           700018970         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           700018971         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7000060775         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+ <td>7000060762</td> <td>3M™ Cubitron™ II Cloth Belt 984F, 75 mm x 2250 mm, 36+</td> <td>20</td> <td>Each</td>	7000060762	3M™ Cubitron™ II Cloth Belt 984F, 75 mm x 2250 mm, 36+	20	Each
7000060766         3M" Cubitron" II Cloth Belt 984F, 75 mm x 3000 mm, 36+         20         Each           7100219005         3M" Cubitron" II Cloth Belt 984F, 80 mm x 9000 mm, 80+         20         Each           7000060767         3M" Cubitron" II Cloth Belt 984F, 100 mm x 1220 mm, 36+         20         Each           7100218981         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           7100218972         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           7100218973         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           7100218970         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7100219000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7100219000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           7100219070         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700016076         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700021897         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7000060755         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+	7000060742	3M™ Cubitron™ II Cloth Belt 984F, 75 mm x 2500 mm, 36+	20	Each
7100219005         3M* Cubitron* II Cloth Belt 984F, 80 mm x 9000 mm, 80+         20         Each           7000060767         3M* Cubitron* II Cloth Belt 984F, 100 mm x 1220 mm, 36+         20         Each           7100218981         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2000 mm, 60+         20         Each           7100218902         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           7100218972         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           7100218969         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7100218969         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7100219000         3M* Cubitron* II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           700060776         3M* Cubitron* II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           700060778         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700060773         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700060773         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700010218993         3M* Cubitron* II Cloth Belt 984F, 100 mm x 2000 mm, 36	7100219024	3M™ Cubitron™ II Cloth Belt 984F, 75 mm x 4000 mm, 36+	20	Each
7000060767         3M" Cubitron" II Cloth Belt 984F, 100 mm x 1220 mm, 36+         20         Each           7100218981         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 60+         20         Each           7100218972         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           7100218969         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           7000060776         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           700019000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3450 mm, 36+         20         Each           7000060746         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           7000060740         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           700019000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7000190773         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7000060755         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700018099         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         10         Each           7100218991         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2000 mm, 36	7000060766	3M™ Cubitron™ II Cloth Belt 984F, 75 mm x 3000 mm, 36+	20	Each
7100218981         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 60+         20         Each           7100219022         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           7100218972         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           7100218969         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7000060776         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7100219000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3450 mm, 36+         20         Each           7000060746         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           700018977         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7000060733         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7000060755         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700018999         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           7100218991         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2000 mm, 36+         10         Each           7100218993         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2000 mm, 3	7100219005	3M™ Cubitron™ II Cloth Belt 984F, 80 mm x 9000 mm, 80+	20	Each
7100219022         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2200 mm, 36+         20         Each           7100218972         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2250 mm, 36+         20         Each           7100218969         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           7000060776         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7100219000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           700060746         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           700060773         3M" Cubitron" II Cloth Belt 984F, 100 mm x 9000 mm, 36+         20         Each           700060755         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700018999         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3000 mm, 36+         20         Each           7100218999         3M" Cubitron" II Cloth Belt 984F, 102 mm x 4270 mm, 36+         20         Each           7100218999         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2200 mm, 36+         10         Each           7100218991         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2500 mm, 36+         10         Each           7100218997         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2500 mm, 36+	7000060767	3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 1220 mm, 36+	20	Each
7100218972       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2250 mm, 36+       20       Each         7100218969       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2500 mm, 36+       20       Each         7000060776       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+       20       Each         7100219000       3M" Cubitron" II Cloth Belt 984F, 100 mm x 3450 mm, 36+       20       Each         700060746       3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+       20       Each         700060773       3M" Cubitron" II Cloth Belt 984F, 100 mm x 9000 mm, 80+       20       Each         700060755       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+       20       Each         700060756       3M" Cubitron" II Cloth Belt 984F, 100 mm x 3000 mm, 36+       20       Each         7100218999       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+       20       Each         7100218991       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7100218991       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7100218967       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100219017       3M" Cubitron" II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7100219025	7100218981	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 100 mm x 2000 mm, 60+	20	Each
7100218969         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2500 mm, 36+         20         Each           700060776         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+         20         Each           7100219000         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3450 mm, 36+         20         Each           700060746         3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+         20         Each           7100218977         3M" Cubitron" II Cloth Belt 984F, 100 mm x 9000 mm, 80+         20         Each           700060773         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700060755         3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+         20         Each           700060756         3M" Cubitron" II Cloth Belt 984F, 102 mm x 4270 mm, 36+         20         Each           7100218999         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2000 mm, 36+         10         Each           7100218961         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2300 mm, 36+         10         Each           7100218961         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2800 mm, 36+         10         Each           7100218967         3M" Cubitron" II Cloth Belt 984F, 120 mm x 2800 mm, 36+         10         Each           7100219017         3M" Cubitron" II Cloth Belt 984F, 150 mm x 2000 mm, 36+<	7100219022	3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 2200 mm, 36+	20	Each
7000060776       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2740 mm, 36+       20       Each         7100219000       3M" Cubitron" II Cloth Belt 984F, 100 mm x 3450 mm, 36+       20       Each         700060746       3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+       20       Each         7100218977       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 80+       20       Each         70006073       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+       20       Each         700060756       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+       20       Each         7100218999       3M" Cubitron" II Cloth Belt 984F, 102 mm x 2000 mm, 36+       20       Each         7100218968       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2000 mm, 36+       10       Each         7100218991       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218961       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218971       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100219072       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2000 mm, 36+       10       Each         7100219073       3M" Cubitron" II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7100219025	7100218972	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 100 mm x 2250 mm, 36+	20	Each
T100219000   3M* Cubitron* II Cloth Belt 984F, 100 mm x 3450 mm, 36+   20   Each	7100218969	3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 2500 mm, 36+	20	Each
7000060746       3M" Cubitron" II Cloth Belt 984F, 100 mm x 3500 mm, 36+       20       Each         7100218977       3M" Cubitron" II Cloth Belt 984F, 100 mm x 9000 mm, 80+       20       Each         700060773       3M" Cubitron" II Cloth Belt 984F, 100 mm x 1000 mm, 36+       20       Each         700060755       3M" Cubitron" II Cloth Belt 984F, 100 mm x 2000 mm, 36+       20       Each         700060756       3M" Cubitron" II Cloth Belt 984F, 100 mm x 3000 mm, 36+       20       Each         7100218999       3M" Cubitron" II Cloth Belt 984F, 120 mm x 4270 mm, 36+       20       Each         7100218968       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7100218991       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7100218991       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218967       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2800 mm, 36+       10       Each         7100219073       3M" Cubitron" II Cloth Belt 984F, 120 mm x 2000 mm, 36+       10       Each         7100219011       3M" Cubitron" II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7100219025       3M" Cubitron" II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775	7000060776	3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 2740 mm, 36+	20	Each
7100218977       3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 9000 mm, 80+       20       Each         7000060773       3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 1000 mm, 36+       20       Each         7000060755       3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 2000 mm, 36+       20       Each         7000060756       3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 3000 mm, 36+       20       Each         7100218999       3M™ Cubitron™ II Cloth Belt 984F, 102 mm x 4270 mm, 36+       20       Each         7100218968       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 1000 mm, 36+       10       Each         7100218991       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7100218967       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218967       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2800 mm, 36+       10       Each         7100219017       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+       10       Each         7100219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each         7000060789 <td>7100219000</td> <td>3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 3450 mm, 36+</td> <td>20</td> <td>Each</td>	7100219000	3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 3450 mm, 36+	20	Each
7000060773       3M** Cubitron** II Cloth Belt 984F, 100 mm x 1000 mm, 36+       20       Each         7000060755       3M** Cubitron** II Cloth Belt 984F, 100 mm x 2000 mm, 36+       20       Each         7000060756       3M** Cubitron** II Cloth Belt 984F, 100 mm x 3000 mm, 36+       20       Each         7100218999       3M** Cubitron** II Cloth Belt 984F, 102 mm x 4270 mm, 36+       20       Each         7100218968       3M** Cubitron** II Cloth Belt 984F, 120 mm x 1000 mm, 36+       10       Each         7100218991       3M** Cubitron** II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7000060757       3M** Cubitron** II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218967       3M** Cubitron** II Cloth Belt 984F, 120 mm x 2800 mm, 36+       10       Each         7100219017       3M** Cubitron** II Cloth Belt 984F, 120 mm x 9000 mm, 36+       10       Each         7100219011       3M** Cubitron** II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M** Cubitron** II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060753       3M** Cubitron** II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M** Cubitron** II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each <t< td=""><td>7000060746</td><td>3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 3500 mm, 36+</td><td>20</td><td>Each</td></t<>	7000060746	3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 3500 mm, 36+	20	Each
7000060755       3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 2000 mm, 36+       20       Each         7000060756       3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 3000 mm, 36+       20       Each         7100218999       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 4270 mm, 36+       20       Each         7100218968       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 1000 mm, 36+       10       Each         7100218991       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7000060757       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218967       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2800 mm, 36+       10       Each         7100219017       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+       10       Each         7100219011       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 4000 mm, 36+       10       Each         7000219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7100218977	3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 9000 mm, 80+	20	Each
7000060756 3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 3000 mm, 36+  7100218999 3M™ Cubitron™ II Cloth Belt 984F, 102 mm x 4270 mm, 36+  7100218968 3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 1000 mm, 36+  7100218991 3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2300 mm, 36+  7100218991 3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2300 mm, 36+  7100218991 3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2500 mm, 36+  7100218967 3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2800 mm, 36+  7100219017 3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+  7100219011 3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+  7100219025 3M™ Cubitron™ II Cloth Belt 984F, 145 mm x 4000 mm, 36+  7100060751 3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+  7000060751 3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+  7000060775 3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+  10 Each  7000060789 3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+  10 Each  7000060822 3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+  10 Each	7000060773	3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 1000 mm, 36+	20	Each
7100218999       3M™ Cubitron™ II Cloth Belt 984F, 102 mm x 4270 mm, 36+       20       Each         7100218968       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 1000 mm, 36+       10       Each         7100218991       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7000060757       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218967       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2800 mm, 36+       10       Each         7100219017       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+       10       Each         7100219011       3M™ Cubitron™ II Cloth Belt 984F, 145 mm x 4000 mm, 36+       10       Each         7100219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 30+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7000060755	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 100 mm x 2000 mm, 36+	20	Each
7100218968       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 1000 mm, 36+       10       Each         7100218991       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7000060757       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218967       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2800 mm, 36+       10       Each         7100219017       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+       10       Each         7100219011       3M™ Cubitron™ II Cloth Belt 984F, 145 mm x 4000 mm, 36+       10       Each         7100219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7000060756	3M™ Cubitron™ II Cloth Belt 984F, 100 mm x 3000 mm, 36+	20	Each
7100218991       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2300 mm, 36+       10       Each         7000060757       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218967       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2800 mm, 36+       10       Each         7100219017       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+       10       Each         7100219011       3M™ Cubitron™ II Cloth Belt 984F, 145 mm x 4000 mm, 36+       10       Each         7100219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each	7100218999	3M™ Cubitron™ II Cloth Belt 984F, 102 mm x 4270 mm, 36+	20	Each
7000060757       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2500 mm, 36+       10       Each         7100218967       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2800 mm, 36+       10       Each         7100219017       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+       10       Each         7100219011       3M™ Cubitron™ II Cloth Belt 984F, 145 mm x 4000 mm, 36+       10       Each         7100219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7100218968	3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 1000 mm, 36+	10	Each
7100218967       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2800 mm, 36+       10       Each         7100219017       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+       10       Each         7100219011       3M™ Cubitron™ II Cloth Belt 984F, 145 mm x 4000 mm, 36+       10       Each         7100219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7100218991	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 120 mm x 2300 mm, 36+	10	Each
7100219017       3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+       10       Each         7100219011       3M™ Cubitron™ II Cloth Belt 984F, 145 mm x 4000 mm, 36+       10       Each         7100219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7000060757	3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2500 mm, 36+	10	Each
7100219011       3M™ Cubitron™ II Cloth Belt 984F, 145 mm x 4000 mm, 36+       10       Each         7100219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7100218967	3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 2800 mm, 36+	10	Each
7100219025       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+       10       Each         7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7100219017	3M™ Cubitron™ II Cloth Belt 984F, 120 mm x 9000 mm, 36+	10	Each
7000060751       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+       10       Each         7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7100219011	3M™ Cubitron™ II Cloth Belt 984F, 145 mm x 4000 mm, 36+	10	Each
7000060775       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+       10       Each         7000060789       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+       10       Each         7000060822       3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+       10       Each	7100219025	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 1000 mm, 36+	10	Each
7000060789 3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+ 10 Each 7000060822 3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+ 10 Each	7000060751	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 36+	10	Each
7000060822 3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+ 10 Each	7000060775	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 60+	10	Each
	7000060789	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2000 mm, 80+	10	Each
7100218966 3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2500 mm, 36+ 10 Each	7000060822	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2250 mm, 36+	10	Each
	7100218966	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2500 mm, 36+	10	Each



# 3M™ Cubitron™ II Cloth Belt 984F

3M™ Cubitron™ II Cloth Belts 984F offer revolutionary performance with 3M Precision Shaped Grain that slices clean through metal. Our 984F belts contain a grinding aid, making it ideal for medium to high pressure applications.



- Minimise operator fatigue as 3M Precision Shaped Grain requires less grinding pressure
- Cool running temperature reduces risk of discolouration and heat related stress cracks
- 3M Precision Shaped Grain fractures into self-sharpening points, cutting exceptionally fast and increasing productivity

Product ID	Product Name	MOQ	OU
7100218980	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2500 mm, 60+	10	Each
7100218975	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 2500 mm, 80+	10	Each
7000060788	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 150 mm x 3500 mm, 80+	10	Each
7000060771	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 10700 mm, 36+	6	Each
7000060790	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 150 mm x 3500 m, 60+	10	Each
7000060752	3M™ Cubitron™ II Cloth Belt 984F, 150 mm x 3500 mm, 36+	10	Each
7100038905	3M™ Cubitron™ II Cloth Belt 984F, 190 mm x 2360 mm, 80+	10	Each
7000060772	3M™ Cubitron™ II Cloth Belt 984F, 200 mm x 4250 mm, 36+	5	Each
7100218965	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 300 mm x 2000 mm, 36+	10	Each
7100218964	3M™ Cubitron™ II Cloth Belt 984F, 300 mm x 3000 mm, 36+	10	Each
7100218976	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 300 mm x 3000 mm, 80+	10	Each
7100218962	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 300 mm x 3500 mm, 36+	5	Each
7100218985	3M™ Cubitron™ II Cloth Belt 984F, 300 mm x 3500 mm, 60+	10	Each
7100218945	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 984F, 300 mm x 3500 mm, 80+	10	Each
7100144158	3M™ Cubitron™ II Cloth Belt 984F, 300 mm x 16900 mm, 36+	10	Each
7100007990	3M™ Cubitron™ II Cloth Belt 984F, Config Belt, 36+	1	Each
7100007991	3M™ Cubitron™ II Cloth Belt 984F, Config Belt, 60+	1	Each
7100007992	3M™ Cubitron™ II Cloth Belt 984F, Config Belt, 80+	1	Each
7100082475	3M™ Cubitron™ II Cloth Belt 984F, Config Belt, 120+	1	Each



# 3M™ Cubitron™ II Cloth Belt 947A

3M™ Cubitron™ II Cloth Belt 947A features Precision Shaped Grain on a X-weight, poly-cotton backing. Our 974A belts are resin bonded for improved heat resistance and are recommended to be used dry.



- Precision Shaped Grain cuts exceptionally fast, helping to increase productivity
- Requires less pressure, reducing operator fatigue
- Suitable for dry applications

Product ID	Product Name	MOQ	OU
7100176940	3M™ Cubitron™ II Cloth Belt 947A, 10 mm x 330 mm, 40+	100	Each
7100069960	3M™ Cubitron™ II Cloth Belt 947A, 10 mm x 330 mm, 60+	100	Each
7100070629	3M™ Cubitron™ II Cloth Belt 947A, 10 mm x 330 mm, 80+	100	Each
7100218984	3M™ Cubitron™ II Cloth Belt 947A, 10 mm x 330 mm, 120+	100	Each
7100219058	3M™ Cubitron™ II Cloth Belt 947A, 12 mm x 330 mm, 60+	100	Each
7100219041	3M™ Cubitron™ II Cloth Belt 947A, 13 mm x 305 mm, 80+	100	Each
7100026792	3M™ Cubitron™ II Cloth Belt 947A, 13 mm x 457 mm, 40+	100	Each
7100026527	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 947A, 13 mm x 457 mm, 60+	100	Each
7100026427	3M™ Cubitron™ II Cloth Belt 947A, 13 mm x 457 mm, 80+	100	Each
7100026526	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 947A, 13 mm x 610 mm, 60+	100	Each
7100026755	3M™ Cubitron™ II Cloth Belt 947A, 13 mm x 610 mm, 80+	100	Each
7100026547	3M™ Cubitron™ II Cloth Belt 947A, 13 mm x 610 mm, 120+	100	Each
7100028819	3M™ Cubitron™ II Cloth Belt 947A, 19 mm x 457 mm, 40+	100	Each
7100027081	3M™ Cubitron™ II Cloth Belt 947A, 19 mm x 457 mm, 60+	100	Each
7100027618	3M™ Cubitron™ II Cloth Belt 947A, 19 mm x 457 mm, 120+	100	Each
7100026793	3M™ Cubitron™ II Cloth Belt 947A, 19 mm x 520 mm, 40+	100	Each
7100026791	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 947A, 19 mm x 520 mm, 80+	100	Each
7100218955	3M™ Cubitron™ II Cloth Belt 947A, 20 mm x 480 mm, 60+	100	Each
7100218954	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 947A, 20 mm x 520 mm, 60+	100	Each
7100047970	3M™ Cubitron™ II Cloth Belt 947A, 20 mm x 520 mm, 80+	100	Each
7100218950	3M™ Cubitron™ II Cloth Belt 947A, 20 mm x 520 mm, 120+	100	Each
7100218993	3M™ Cubitron™ II Cloth Belt 947A, 50 mm x 450 mm, 120+	30	Each
7100218953	3M™ Cubitron™ II Cloth Belt 947A, 50 mm x 2500 mm, 40+	30	Each
7100219040	3M™ Cubitron™ II Cloth Belt 947A, 60+, 13 mm x 305 mm	100	Each
7100025847	3M™ Cubitron™ II Cloth Belt 947A, 75 mm x 2000 mm, 60+	20	Each
7100026546	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 947A, 75 mm x 2000 mm, 120+	20	Each
7100026426	3M™ Cubitron™ II Cloth Belt 947A, 100 mm x 289 mm, 60+	20	Each
7100026670	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 947A, 100 mm x 289 mm, 80+	20	Each
7100219001	3M™ Cubitron™ II Cloth Belt 947A, 100 mm x 9000 mm, 60+	20	Each
7100219068	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 947A, 100 mm x 9000 mm, 80+	20	Each
7100026529	3M™ Cubitron™ II Cloth Belt 947A, 100 mm x 9000 mm, 120+	20	Each
7100219007	3M™ Cubitron™ II Cloth Belt 947A, 120 mm x 2000 mm, 120+	10	Each
7100219146	3M™ Cubitron™ II Cloth Belt 947A, 345 mm x 1615 mm, 120+	5	Each
7100171627	3M™ Cubitron™ II Cloth Belt 947A, Config Belt, 40+	1	Each
7100023234	3M™ Cubitron™ II Cloth Belt 947A, Config Belt, 60+	1	Each
7100023179	3M™ Cubitron™ II Cloth Belt 947A, Config Belt, 80+	1	Each
7100023178	3M™ Cubitron™ II Cloth Belt 947A, Config Belt, 120+	1	Each



Focus

### 3M™ Cubitron™ II Cloth Belt 726A

3M™ Cubitron™ II Cloth Belt 726A is widely used in the metal blending and finishing application. Grades from 80+ to 400+. Suitable for manual, robot, and automated processes. This flexible belt makes this product a good choice when using a soft contact wheel or slack of belt.



- J-weight backing
- Precision Shaped Grain abrasive material
- Used for Metalworking applications

Product ID	Product Name	MOQ	OU
7100289610	3M™ Cubitron™ II Cloth Belt 726A, 80+ J-weight, Config	1	Each
7100289609	3M™ Cubitron™ II Cloth Belt 726A, 120+ J-weight, Config	1	Each
7100289608	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 726A, 150+ J-weight, Config	1	Each
7100289607	3M™ Cubitron™ II Cloth Belt 726A, 180+ J-weight, Config	1	Each
7100289606	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 726A, 220+ J-weight, Config	1	Each
7100289605	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 726A, 240+ J-weight, Config	1	Each
7100289604	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 726A, 320+ J-weight, Config	1	Each
7100289603	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 726A, 400+ J-weight, Config	1	Each

# 3M™ Cubitron™ II Cloth Belt 784F

3M™ Cubitron™ II Cloth Belt 784F features 3M Precision Shaped Grain. Our cloth belts are a precise mix of shaped ceramic and premium aluminium oxide. They have a flexible J-weight cotton backing and open coat construction. The belts also feature a waterproof backing and grinding aid.



- Up to two times longer life than comparable aluminium oxide belts, resists deterioration from heat
- Consistent, faster results on medium pressure applications
- Conformable for grinding and blending both straight and contoured surfaces

Product ID	Product Name	MOQ	OU
7100219054	3M™ Cubitron™ II Cloth Belt 784F, 10 mm x 330 mm, 60+	100	Each
7100219053	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 10 mm x 330 mm, 80+	100	Each
7100218971	3M™ Cubitron™ II Cloth Belt 784F, 12 mm x 330 mm, 60+	100	Each
7100218959	3M™ Cubitron™ II Cloth Belt 784F, 13 mm x 305 mm, 60+	100	Each
7100218935	3M™ Cubitron™ II Cloth Belt 784F, 13 mm x 305 mm, 80+	100	Each
7100218942	3M™ Cubitron™ II Cloth Belt 784F, 13 mm x 457 mm, 60+	100	Each
7100218934	3M™ Cubitron™ II Cloth Belt 784F, 13 mm x 457 mm, 80+	100	Each
7100218941	3M™ Cubitron™ II Cloth Belt 784F, 13 mm x 610 mm, 60+	100	Each
7100219038	3M™ Cubitron™ II Cloth Belt 784F, 13 mm x 610 mm, 80+	100	Each
7100142081	3M™ Cubitron™ II Cloth Belt 784F, 20 mm x 457 mm, 50+	100	Each
7100218938	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 20 mm x 457 mm, 60+	100	Each
7100218937	3M™ Cubitron™ II Cloth Belt 784F, 20 mm x 520 mm, 60+	100	Each
7100181788	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 20 mm x 520 mm, 80+	100	Each
7100219049	3M™ Cubitron™ II Cloth Belt 784F, 40 mm x 314 mm, 120+	30	Each
7100219050	3M™ Cubitron™ II Cloth Belt 784F, 50 mm x 2010 mm, 36+	30	Each
7100219030	3M™ Cubitron™ II Cloth Belt 784F, 50 mm x 4000 mm, 36+	30	Each



# 3M™ Cubitron™ II Cloth Belt 784F

3M™ Cubitron™ II Cloth Belt 784F features 3M Precision Shaped Grain. Our cloth belts are a precise mix of shaped ceramic and premium aluminium oxide. They have a flexible J-weight cotton backing and open coat construction. The belts also feature a waterproof backing and grinding aid.



- Up to two times longer life than comparable aluminium oxide belts, resists deterioration from heat
- Consistent, faster results on medium pressure applications
- Conformable for grinding and blending both straight and contoured surfaces

Product ID	Product Name	MOQ	OU
7100219028	3M™ Cubitron™ II Cloth Belt 784F, 75 mm x 2000 mm, 36+	20	Each
7100146406	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 75 mm x 2000 mm, 60+	20	Each
7100218932	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 75 mm x 2000 mm, 80+	20	Each
7100219046	3M™ Cubitron™ II Cloth Belt 784F, 75 mm x 2000 mm, 120+	20	Each
7100219056	3M™ Cubitron™ II Cloth Belt 784F, 100 mm x 289 mm, 60+	20	Each
7100219055	3M™ Cubitron™ II Cloth Belt 784F, 100 mm x 289 mm, 80+	20	Each
7100219057	3M™ Cubitron™ II Cloth Belt 784F, 100 mm x 2250 mm, 80+	20	Each
7100219071	3M™ Cubitron™ II Cloth Belt 784F, 100 mm x 3000 mm, 36+	20	Each
7100144567	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 100 mm x 3150 mm, 50+	20	Each
7100219023	3M™ Cubitron™ II Cloth Belt 784F, 100 mm x 3500 mm, 50+	20	Each
7100219043	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 100 mm x 9000 mm, 80+	20	Each
7100219037	3M™ Cubitron™ II Cloth Belt 784F, 150 mm x 2000 mm, 36+	10	Each
7100218940	3M™ Cubitron™ II Cloth Belt 784F, 150 mm x 2000 mm, 60+	10	Each
7100219051	3M™ Cubitron™ II Cloth Belt 784F, 150 mm x 2000 mm, 120+	10	Each
7100219036	3M™ Cubitron™ II Cloth Belt 784F, 150 mm x 2500 mm, 36+	10	Each
7100218933	3M™ Cubitron™ II Cloth Belt 784F, 150 mm x 2500 mm, 80+	10	Each
7100218939	3M™ Cubitron™ II Cloth Belt 784F, 150 mm x 3000 mm, 60+	10	Each
7100219045	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 150 mm x 3500 mm, 36+	10	Each
7100219013	3M™ Cubitron™ II Cloth Belt 784F, 150 mm x 3500 mm, 50+	10	Each
7100219033	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 220 mm x 2000 mm, 36+	10	Each
7100219004	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, 220 mm x 2000 mm, 50+	10	Each
7100181358	3M™ Cubitron™ II Cloth Belt 784F, 300 mm x 16900 mm, 36+	10	Each
7100218936	3M™ Cubitron™ II Cloth Belt 784F, 300 mm x 22285 mm, 60+	20	Each
7100219052	3M™ Cubitron™ II Cloth Belt 784F, 1300 mm x 1900 mm, 36+	2	Each
7100171629	3M™ Cubitron™ II Cloth Belt 784F, Config Belt, 36+	1	Each
7100091823	3M™ Cubitron™ II Cloth Belt 784F, Config Belt, 50+	1	Each
7100091825	3M™ Cubitron™ II Cloth Belt 784F, Config Belt, 60+	1	Each
7100091827	3M™ Cubitron™ II Cloth Belt 784F, Config Belt, 80+	1	Each
7100091829	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, Config Belt, 120+	1	Each
7100091831	3M™ Cubitron™ II Cloth Belt 784F, Config Belt, 150+	1	Each
7100091833	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 784F, Config Belt, 180+	1	Each



### 3M™ Cubitron™ II Cloth Belt 994F

Our 3M™ Cubitron™ II Cloth Belt 994F features 3M Precision Shaped Ceramic Grain which cuts fast and self-renews during grinding. These high-performing products are ideal for medium to high pressure applications on carbon steel.



- 3M Precision Shaped Grain (PSG) continuously fractures and self-renews for an exceptionally fast cut
- Suitable for wet and dry applications
- ZF-weight backing excels in high pressure applications

Product ID	Product Name	MOQ	OU
7000060890	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 994F, 50 mm x 3500 mm, 36+	30	Each
7100047077	3M <sup>™</sup> Cubitron <sup>™</sup> II Cloth Belt 994F, Config Belt, 36+	1	Each

### 3M™ Trizact™ Cloth Belt 217EA

3M™ Trizact™ Cloth Belt 217EA uses our proprietary microreplication technology where micron-graded aluminum oxide particles are formed into tiny pyramids of abrasive mineral and then coated on a J weight rayon backing. As these pyramids wear, fresh, sharp mineral is continually exposed to produce a consistent cut and a predictable, fine finish.



- Flexible J-weight backing flows over contoured surfaces for consistent finishing
- Produces finer finishes than conventional electrostatically coated abrasives
- Ideal for light pressure applications allows abrasive to break down and maintain cut and produce consistent finishes

Product ID	Product Name	MOQ	OU
7100052788	3M™ Trizact™ Cloth Belt 217EA, Config Belt, A6	1	Each
7100052787	3M™ Trizact™ Cloth Belt 217EA, Config Belt, A16	1	Each
7100052786	3M™ Trizact™ Cloth Belt 217EA, Config Belt, A30	1	Each
7100052768	3M™ Trizact™ Cloth Belt 217EA, Config Belt, A45	1	Each
7100052769	3M™ Trizact™ Cloth Belt 217EA, Config Belt, A65	1	Each
7100052770	3M <sup>™</sup> Trizact <sup>™</sup> Cloth Belt 217EA, Config Belt, A80	1	Each
7100052771	3M™ Trizact™ Cloth Belt 217EA, Config Belt, A100	1	Each



# 3M™ Trizact™ Cloth Belt 237AA

3M™ Trizact™ Cloth Belt 237AA uses proprietary microreplication technology where micron-graded aluminum oxide particles are formed into tiny pyramids of abrasive mineral and then coated on an X weight cloth backing. As these pyramids wear, fresh, sharp mineral is continually exposed to produce a consistent cut and a predictable, fine finish.



- $\bullet \, \mathsf{Self}\text{-}\mathsf{sharpening} \,\, \mathsf{pyramids} \,\, \mathsf{start} \,\, \mathsf{sharp}, \, \mathsf{stay} \,\, \mathsf{sharp}, \, \mathsf{and} \,\, \mathsf{run} \,\, \mathsf{cooler} \,\, \mathsf{than} \,\, \mathsf{conventional} \,\, \mathsf{abrasives} \,$
- Flexible backing for consistent finish over contours
- Ideal for intermediate finishing and fine polishing prior to plating or buffing

7000060078       3M™ Trizact™ Cloth Belt 237AA, 50 mm x 450 mm, A30       30         7000060076       3M™ Trizact™ Cloth Belt 237AA, 50 mm x 450 mm, A100       30         7100219029       3M™ Trizact™ Cloth Belt 237AA, 50 mm x 2500 mm, A100       30         7000060033       3M™ Trizact™ Cloth Belt 237AA, 75 mm x 2000 mm, A30       20         7000060897       3M™ Trizact™ Cloth Belt 237AA, 75 mm x 2000 mm, A45       20	Each Each Each Each
7100219029       3M™ Trizact™ Cloth Belt 237AA, 50 mm x 2500 mm, A100       30         7000060033       3M™ Trizact™ Cloth Belt 237AA, 75 mm x 2000 mm, A30       20         7000060897       3M™ Trizact™ Cloth Belt 237AA, 75 mm x 2000 mm, A45       20	Each
7000060033 3M™ Trizact™ Cloth Belt 237AA, 75 mm x 2000 mm, A30 20 7000060897 3M™ Trizact™ Cloth Belt 237AA, 75 mm x 2000 mm, A45 20	
7000060897 3M™ Trizact™ Cloth Belt 237AA, 75 mm x 2000 mm, A45 20	Each
	Each
7000059968 3M™ Trizact™ Cloth Belt 237AA, 75 mm x 2000 mm, A65 20	Each
7100219035 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 289 mm, A16 20	Each
7100219073 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 289 mm, A30 20	Each
7100219066 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 289 mm, A45 20	Each
7100219145 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 289 mm, A65 20	Each
7100219067 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 289 mm, A80 20	Each
7100219061 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 289 mm, A100 20	Each
7100219060 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 289 mm, A160 20	Each
7100219009 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 4000 mm, A100 20	Each
7100218952 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 9000 mm, A80 10	Each
7100218951 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 9000 mm, A100 10	Each
7100219002 3M™ Trizact™ Cloth Belt 237AA, 100 mm x 9000 mm, A160 10	Each
7000059967 3M™ Trizact™ Cloth Belt 237AA, 300 mm x 3500 mm, A30	Each
7100007882 3M™ Trizact™ Cloth Belt 237AA, Config Belt, A6 1	Each
7100007878 3M™ Trizact™ Cloth Belt 237AA, Config Belt, A16 1	Each
7100007880 3M™ Trizact™ Cloth Belt 237AA, Config Belt, A30 1	Each
7100007881 3M™ Trizact™ Cloth Belt 237AA, Config Belt, A45	Each
7100007883 3M™ Trizact™ Cloth Belt 237AA, Config Belt, A65	Each
7100007884 3M™ Trizact™ Cloth Belt 237AA, Config Belt, A80 1	Each
7100007877 3M™ Trizact™ Cloth Belt 237AA, Config Belt, A100 1	Each
7100007879 3M™ Trizact™ Cloth Belt 237AA, Config Belt, A160 1	Each



## 3M™ Trizact™ Cloth Belt 307EA

3M™ Trizact™ Cloth Belt 307EA uses our proprietary microreplication technology where micron-graded aluminum oxide particles are formed into tiny pyramids of abrasive mineral and then coated on a rayon backing. As these pyramids wear, fresh, sharp mineral is continually exposed to produce a consistent cut and a predictable, fine finish.



- Self-sharpening pyramids start sharp, stay sharp, and run cooler than conventional abrasives
- Flexible backing flows over contoured surfaces for consistent finishing
- Ideal for intermediate finishing and fine polishing prior to plating or buffing

Product ID	Product Name	MOQ	OU
7100168938	3M™ Trizact™ Cloth Belt 307EA, 25 mm x 4000 mm, A16	40	Each
7100218983	3M™ Trizact™ Cloth Belt 307EA, 40 mm x 3500 mm, A16	30	Each
7100218961	3M <sup>™</sup> Trizact <sup>™</sup> Cloth Belt 307EA, 50 mm x 1520 mm, A100	30	Each
7000060356	3M™ Trizact™ Cloth Belt 307EA, 50 mm x 1525 mm, A16	30	Each
7100218974	3M <sup>™</sup> Trizact <sup>™</sup> Cloth Belt 307EA, 50 mm x 2500 mm, A16	30	Each
7100218960	3M™ Trizact™ Cloth Belt 307EA, 50 mm x 2500 mm, A30	30	Each
7100045155	3M™ Trizact™ Cloth Belt 307EA, 50 mm x 3350 mm, A45	60	Each
7100166994	3M™ Trizact™ Cloth Belt 307EA, 50 mm x 4000 mm, A16	30	Each
7100219020	3M™ Trizact™ Cloth Belt 307EA, 100 mm x 4000 mm, A45	20	Each
7100218956	3M™ Trizact™ Cloth Belt 307EA, 300 mm x 3500 mm, A30	10	Each
7100218957	3M™ Trizact™ Cloth Belt 307EA, 300 mm x 3500 mm, A65	10	Each
7100218922	3M <sup>™</sup> Trizact <sup>™</sup> Cloth Belt 307EA, 300 mm x 3500 mm, A100	10	Each
7100052733	3M™ Trizact™ Cloth Belt 307EA, Config Belt, A6	1	Each
7100052732	3M <sup>™</sup> Trizact <sup>™</sup> Cloth Belt 307EA, Config Belt, A16	1	Each
7100052731	3M™ Trizact™ Cloth Belt 307EA, Config Belt, A30	1	Each
7100052730	3M™ Trizact™ Cloth Belt 307EA, Config Belt, A45	1	Each
7100052729	3M™ Trizact™ Cloth Belt 307EA, Config Belt, A65	1	Each
7100052728	3M™ Trizact™ Cloth Belt 307EA, Config Belt, A80	1	Each
7100112315	3M™ Trizact™ Cloth Belt 307EA, Config Belt, A100	1	Each

### 3M™ Trizact™ Cloth Belt 363FC

3M™ Trizact™ Cloth Belt 363FC features an aluminium oxide mineral bonded to a YF-weight polyester cloth backing. Our 363FC belts are available in grades A300 to A35.



- Trizact™ abrasives can last up to five times longer than conventional abrasives
- Waterproof polyester YF-weight backing allows users to rinse the belt reducing clogging of the abrasive
- Resin bond helps to resist thermal and chemical deterioration

Product ID	Product Name	MOQ	OU
7100219062	3M™ Trizact™ Cloth Belt 363FC, 150 mm x 3500 mm, A65	10	Each
7100070052	3M™ Trizact™ Cloth Belt 363FC, Config Belt, A45	1	Each
7100070054	3M™ Trizact™ Cloth Belt 363FC, Config Belt, A65	1	Each
7100052841	3M™ Trizact™ Cloth Belt 363FC, Config Belt, A100	1	Each
7100052840	3M™ Trizact™ Cloth Belt 363FC, Config Belt, A160	1	Each
7100052839	3M™ Trizact™ Cloth Belt 363FC, Config Belt, A300	1	Each



### 3M™ Trizact™ Cloth Belt 337DC

A Trizact™ abrasive belt on an X-weight backing used for Medium Pressure metal working: mill line removal, intermediate scratch refinement, consistent dimensioning, and consistent finishing applications.

- Excellent finish consistency
- Works well under medium pressure conditions
- Structured patterned abrasive



Product ID	Product Name	MOQ	OU
7100219074	3M <sup>™</sup> Trizact <sup>™</sup> Cloth Belt 337DC, 100 mm x 289 mm, A30	20	Each
7100219064	3M™ Trizact™ Cloth Belt 337DC, 100 mm x 289 mm, A65	60	Each
7100218992	3M™ Trizact™ Cloth Belt 337DC, 100 mm x 289 mm, A160	60	Each
7100052831	3M™ Trizact™ Cloth Belt 337DC, Config Belt, A30	1	Each
7100052826	3M™ Trizact™ Cloth Belt 337DC, Config Belt, A45	1	Each
7100048818	3M™ Trizact™ Cloth Belt 337DC, Config Belt, A65	1	Each
7100052827	3M™ Trizact™ Cloth Belt 337DC, Config Belt, A100	1	Each
7100052828	3M™ Trizact™ Cloth Belt 337DC, Config Belt, A160	1	Each
7100052829	3M™ Trizact™ Cloth Belt 337DC, Config Belt, A300	1	Each

Focus

### 3M™ Cloth Belt 767F

3M™ Cloth Belt 767F is a high-performance abrasive belt built for versatility and value. Powered by 3M Precision-Shaped Grain, it lasts longer and cuts faster than alumina zirconia belts — and it's priced for affordability and everyday use. This combination of performance and value can increase productivity while also helping lower your overall abrasive spend.



- Delivers long-lasting performance and versatility at a value price
- Contains 3M Precision-Shaped Grain, which cuts faster and lasts longer than conventional abrasive grain
- Proven to outperform traditional alumina zirconia belts in cut-rate and life

Product ID	Product Name	MOQ	OU
7100266289	3M <sup>™</sup> Cloth Belt 767F, 36+, Config	1	Each
7100266290	3M™ Cloth Belt 767F, 60+, Config	1	Each
7100266291	3M <sup>™</sup> Cloth Belt 767F, 80+, Config	1	Each
7100266292	3M™ Cloth Belt 767F, 120+, Config	1	Each



# 3M™ Cloth Belt 384F

3M™ Cloth Belt 384F is a general purpose, premium aluminium oxide cloth belt with an extra durable backing. Our belts feature fast-cutting abrasive grains that are resin-bonded to a durable X-weight polyester cloth backing. They are recommended for use on metal substrates and wood.



- Consistent, reliable performance on all substrates
- Waterproof backing holds up for wet and dry applications
- X-weight cloth backing withstands heavy sanding and grinding

Product ID	Product Name	MOQ	OU
7100091777	3M <sup>™</sup> Cloth Belt 384F, Config Belt, 36+	1	Each
7100091779	3M <sup>™</sup> Cloth Belt 384F, Config Belt, 50+	1	Each
7100091799	3M™ Cloth Belt 384F, Config Belt, 60+	1	Each
7100091802	3M™ Cloth Belt 384F, Config Belt, 80+	1	Each
7100091804	3M™ Cloth Belt 384F, Config Belt, 120+	1	Each
7100091806	3M™ Cloth Belt 384F, Config Belt, 150+	1	Each
7100091808	3M <sup>™</sup> Cloth Belt 384F, Config Belt, 180+	1	Each
7100091813	3M <sup>™</sup> Cloth Belt 384F, Config Belt, 220+	1	Each
7100091815	3M <sup>™</sup> Cloth Belt 384F, Config Belt, 240+	1	Each
7100091817	3M <sup>™</sup> Cloth Belt 384F, Config Belt, P320	1	Each
7100091819	3M <sup>™</sup> Cloth Belt 384F, Config Belt, P400	1	Each



# **Non-woven Belts**

### Scotch-Brite™ Durable Flex Belt DF-BL

Scotch-Brite™ Durable Flex Belt is engineered to perform tough detail work such as deburring, blending, and finishing, on a variety of metals. The reinforced, low-stretch backing and superior edge durability aid in supplying an aggressive cutting ability.

- Tough, non-woven belt is effective for deburring, blending and cleaning
- Higher flexibility resists "chunking" and performs well on belt sanders with small contact wheels
- Low-stretch backing provides aggressive conditioning capability



Product ID	Product Name	MOQ	OU
7000145907	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 20 mm x 520 mm, A MED	50	Each
7000067873	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 6 mm x 305 mm, A MED	150	Each
7000067935	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 6 mm x 457 mm, A CRS, Brown	25	Each
7000067933	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 6 mm x 457 mm, A FIN, Blue	150	Each
7100219034	Scotch-Brite™ Durable Flex Belt DF-BL, 6 mm x 457 mm, A MED, Red	25	Each
7000067941	Scotch-Brite™ Durable Flex Belt DF-BL, 6 mm x 610 mm, A CRS, Brown	150	Each
7000067940	Scotch-Brite™ Durable Flex Belt DF-BL, 6 mm x 610 mm, A FIN, Blue	25	Each
7100219015	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 6 mm x 610 mm, A MED, Red	25	Each
7100219018	Scotch-Brite™ Durable Flex Belt DF-BL, 10 mm x 330 mm, A CRS, Brown	25	Each
7100218994	Scotch-Brite™ Durable Flex Belt DF-BL, 10 mm x 330 mm, A FIN, Blue	25	Each
7100219026	Scotch-Brite™ Durable Flex Belt DF-BL, 12 mm x 330 mm, A CRS, Brown	25	Each
7100219042	Scotch-Brite™ Durable Flex Belt DF-BL, 13 mm 457 mm, A FIN, Blue	25	Each
7100218947	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 13 mm x 457 mm, A CRS, Brown	25	Each
7100218963	Scotch-Brite™ Durable Flex Belt DF-BL, 13 mm x 457 mm, A MED, Red	25	Each
7100218986	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 13 mm x 610 mm, A CRS, Brown	25	Each
7100219006	Scotch-Brite™ Durable Flex Belt DF-BL, 13 mm x 610 mm, A FIN, Blue	25	Each
7100218979	Scotch-Brite™ Durable Flex Belt DF-BL, 13 mm x 610 mm, A MED, Red	25	Each
7100146031	Scotch-Brite™ Durable Flex Belt DF-BL, 13 mm x 1120 mm, A MED, Red	50	Each
7000067944	Scotch-Brite™ Durable Flex Belt DF-BL, 19 mm x 457 mm, A CRS, Brown	150	Each
7000067943	Scotch-Brite™ Durable Flex Belt DF-BL, 19 mm x 457 mm, A MED, Red	150	Each
7000067942	Scotch-Brite™ Durable Flex Belt DF-BL, 19 mm x 457mm, A FIN, Blue	150	Each
7000067868	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 19 mm x 2500 mm, A MED, Red	50	Each
7100218946	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 20 mm x 520 mm, A CRS, Brown	10	Each
7100201780	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 20 mm x 760 mm, A MED, Red	50	Each
7100143972	Scotch-Brite™ Durable Flex Belt DF-BL, 20 mm x 1500 mm, A MED, Red	1	Each
7100218970	Scotch-Brite™ Durable Flex Belt DF-BL, 25 mm x 457 mm, A FIN, Blue	10	Each
7000067872	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 25 mm x 480 mm, A FIN, Blue	50	Each
7100219010	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 50 mm x 1100 mm, A MED, Red	6	Each
7100219027	Scotch-Brite™ Durable Flex Belt DF-BL, 50 mm x 2500 mm, A MED, Red	6	Each
7100219003	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 60 mm x 2400 mm , A CRS, Brown	6	Each
7100219048	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 100 mm x 289 mm, A CRS, Brown	5	Each
7100219047	Scotch-Brite™ Durable Flex Belt DF-BL, 100 mm x 289 mm, A FIN, Blue	5	Each
7100219044	Scotch-Brite <sup>™</sup> Durable Flex Belt DF-BL, 100 mm x 289 mm, A MED, Red	5	Each
7100255864	Scotch-Brite™ Durable Flex Belt DF-BL, A MED, Red, 50 mm x 1525 mm, 6 ea/Case	30	Each



### Scotch-Brite™ Durable Flex Belt DF-BL

Scotch-Brite™ Durable Flex Belt is engineered to perform tough detail work such as deburring, blending, and finishing, on a variety of metals. The reinforced, low-stretch backing and superior edge durability aid in supplying an aggressive cutting ability.

- Tough, non-woven belt is effective for deburring, blending and cleaning
- Higher flexibility resists "chunking" and performs well on belt sanders with small contact wheels
- Low-stretch backing provides aggressive conditioning capability



Product ID	Product Name	MOQ	OU
7100242873	Scotch-Brite™ Durable Flex Belt DF-BL, A/O Coarse, 25.4 mm x 3759.2 mm	1	Each
7100013687	Scotch-Brite™ Durable Flex Belt DF-BL, Config Belt, A CRS, Brown	1	Each
7100012444	Scotch-Brite™ Durable Flex Belt DF-BL, Config Belt, A FIN, Blue	1	Each
7100013155	Scotch-Brite™ Durable Flex Belt DF-BL, Config Belt, A MED, Red	1	Each
7100022777	Scotch-Brite™ Durable Flex Roll DF-BL, 317 mm x 25000 mm, A CRS	4	Roll
7100022778	Scotch-Brite™ Durable Flex Roll DF-BL, 317 mm x 25000 mm, A MED	4	Roll
7000067928	Scotch-Brite™ Surface Conditioning Belt, DF-BL, Maroon, 13 mm x 305 mm, AMED	150	Each

# Scotch-Brite™ Surface Conditioning Low Stretch Belt SC-BL

A non-woven belt used for cleaning, finishing, blending and deburring applications. The firm, stretch-resistant backing is suited for high belt tensions.



- Provides beautiful and consistent finish
- Long life
- Resists loading

Product ID	Product Name	MOQ	OU
7000068085	Scotch-Brite™ SC Surface Conditioning Low Stretch Belt SC-BL, 100 mm x 3000 mm, S SFN	50	Each
7000067929	Scotch-Brite™ Surface Conditioning Belt, DF-BL, Brown, 13 mm x 305 mm, ACRS	150	Each
7000068084	Scotch-Brite <sup>™</sup> Surface Conditioning Low Stretch Belt SC-BL, 6 mm x 533 mm, A CRS, Brown	150	Each



# **Holders & Back-up Pads**

# 3M™ High Performance Ribbed Back-Up Pad

Use 3M™ Ribbed Back Up Pad with 3M™ Cubitron™ II and 3M™ Cubitron™ III discs for improved disc cut and lifespan. Our pad features a unique rib pattern and is resistant to temperatures over 212° F (100°C). It helps to improve efficiency and reduce costs.



- Unique rib pattern
- Resistant to temperatures over 212° F (100°C)
- Use to extend the cut rate and lifespan of 3M™ Cubitron™ II discs

Product ID	Product Name	MOQ	OU
7100135643	3M™ High Performance Ribbed Back-Up Pad, 115 mm	50	Each
7000105441	3M <sup>™</sup> High Performance Ribbed Back-Up Pad, 115 mm, Black	10	Each
7000032409	3M <sup>™</sup> High Performance Ribbed Back-Up Pad, 115 mm, Red	10	Each
7000032410	3M <sup>™</sup> High Performance Ribbed Back-Up Pad, 125 mm, Red	10	Each
7000105442	3M™ High Performance Ribbed Back-Up Pad, 127 mm, Black	10	Each
7000032411	3M™ High Performance Ribbed Back-Up Pad, 180 mm, Red	15	Each

## 3M™ Flat Fibre Disc Back-up Pad

Use 3M™ Ribbed Back Up Pad with 3M™ Cubitron™ II and 3M™ Cubitron™ III discs for improved disc cut and lifespan. Our pad features a unique rib pattern and is resistant to temperatures over 212° F (100°C). It helps to improve efficiency and reduce costs.



- Specially Designed, Hard, Ribbed Backup Pad
- Hard rubber construction works with fibre disc backing for consistent support
- Reduces vibration for greater operator comfort

Product ID	Product Name	MOQ	OU
7100242134	3M™ Flat Fibre Disc Back-up Pad, 150 mm, PN64829	15	Each
7100016545	3M <sup>™</sup> High Performance Ribbed Back-Up Pad, 178 mm, PN09921	5	Each
7000061711	3M™ Flat Fibre Disc Back-up Pad, 115 mm, Flat, Red,	10	Each
7000061712	3M™ Flat Fibre Disc Back-up Pad, 125 mm	10	Each
7100097174	3M™ Flat Fibre Disc Back-up Pad, 125 mm, Low Profile	50	Each
7000008959	3M™ Flat Semi-Flexible Pad, Black, 100 mm x M10-1.5	10	Each
7000105439	3M™ Flat Semi-Flexible Pad, Black, 115 mm x M14	10	Each

## 3M™ Center Pin Back-Up Pad

The Scotch-Brite™ Centre-Pin Back Up Pads are used in conjunction with Scotch-Brite™ Surface Conditioning discs.



- Quick and easy placement and centering of discs
- Does not interfere with work surface
- Allows disc to be used at usual angle

Product ID	Product Name	MOQ	OU
7000086469	3M™ Center Pin Back-Up Pad, 100 mm, 5/8	5	Each
7000086456	3M™ Center Pin Back-Up Pad, 100 mm, M10	5	Each
7000086468	3M™ Center Pin Back-Up Pad, 100 mm, M14	5	Each
7000061390	3M™ Center Pin Back-Up Pad, 115 mm, M14	5	Each
7000061389	3M™ Center Pin Back-Up Pad, 125 mm, M14	5	Each
7000086464	3M™ Center Pin Back-Up Pad, 178 mm, M14	5	Each

# 3M Xtract™ Low Profile Back-up Pad

3M Xtract™ Low Profile Back-up Pads are firm yet flexible to provide versatility for flat sanding applications and are designed to securely hold a 3M Xtract Disc on a random orbital sander (sold separately). Part of the 3M Xtract Series, designed for optimal dust removal, , enabling a vacuum to extract dust off the workpiece to prolong disc life and enhance productivity. Use this back-up pad with coarse grades where good leveling is needed.



- 3M Xtract™ proprietrary multi-hole pattern provides superior dust extraction to prevent loading, increase productivity, and provide a cleaner work environment
- One piece threaded shank for low vibration and improved balance
- Low profile firm density foam and blunt 35 degree tapered edge provide durability and an aggressive cut

Product ID	Product Name	MOQ	OU
7000028147	3M Xtract <sup>™</sup> Low Profile Back-up Pad, 76 mm x 12.7 mm x 6mm	10	Each
7100037832	3M Xtract <sup>™</sup> Low Profile Back-up Pad, 127 mm x 9.52 mm x 7.93 mm	10	Each
7100027464	3M Xtract <sup>™</sup> Low Profile Back-up Pad, 152 mm x 9.52 mm x 7.93 mm	1	Each

# A

# **Abrasive Tools & Accessories**

## 3M Xtract™ Low Profile Finishing Back-up Pad

3M Xtract™ Low Profile Finishing Back-up Pad is constructed of soft density foam with a 10 degree blunt tapered edge and is recommended for finishing applications on flat or contoured surfaces. Part of the 3M Xtract™ Series, designed for optimal dust removal, enabling a vacuum to extract dust off the workpiece to prolong disc life and enhance productivity. Use this disc pad with grades 220 and higher 3M Xtract™ Discs (sold separately).



- 3M Xtract™ proprietrary multi-hole pattern provides superior dust extraction to prevent loading, increase productivity, and provide a cleaner work environment
- Low profile soft density beige foam provides flexibility to conform to a variety of complex surface geometries
- 3M™ Hookit™ attachment system provides easy disc changes and optimizes disc life

Product ID	Product Name	MOQ	OU
7100022038	3M Xtract <sup>™</sup> Low Profile Finishing Back-up Pad, 152 mm x 9.52 mm x 15.8 mm, 53 Hole	10	Each
7100009657	3M Xtract <sup>™</sup> Low Profile Finishing Back-up Pad, 20290, 127 mm x 17.5 mmx 7.93 mm, 44 HLS	10	Each
7000118613	3M Xtract <sup>™</sup> Low Profile Finishing Back-up Pad, 20425, 152 mm x 17.5 mm x 7.9 mm, 53 HLS	10	Each

# 3M Xtract™ Back-up Pad

3M Xtract™ Back-up Pads hold a 3M Xtract Disc (sold separately) for applications that require conformability and edge flexibility. Part of the 3M Xtract Series, designed for optimal dust removal, enabling a vacuum to extract dust off the workpiece to prolong disc life and enhance productivity. It has a tapered edge ideal for feather-edging or blending a painted area to match the rest of the workpiece.



- 3M Xtract™ proprietrary multi-hole pattern provides superior dust extraction to prevent loading, increase productivity, and provide a cleaner work environment
- Medium density foam provides some conformability for surface sanding
- Tapered edge performs well when flexibility is needed for feather-edging or blending a painted area

Product ID	Product Name	MOQ	OU
7100273845	3M Xtract <sup>™</sup> Back-up Pad, 89052, 127 mm, Extra Hard, Black, 10 ea/Case	10	Each
7100273863	3M Xtract™ Back-up Pad, 89053, 152 mm, Extra Hard, Black, 10 ea/Case	10	Each
7100270476	3M Xtract <sup>™</sup> Back-up Pad, 89409, 152 mm, Hard, Red, 10 ea/Case	10	Each
7100273463	3M Xtract™ Back-up Pad, 89410, 127 mm, Hard, Red, 10 ea/Case	10	Each
7100278691	3M™ Hookit™ Clean Sanding Back-up Pad, 89925, 5 in x 11/16 in 5/16 in-24 External, 10 ea/Case	10	Each

### 3M™ Soft Interface Disc Pad

Constructed of a soft durable foam. When used with a Clean Sanding Backup Pad it increases conformability allowing the technician to follow contours and get in closer to most edges while maximizing dust extraction.

- Constructed out of a soft, durable foam
- Helps with following contours and getting in closer to most edges while maximizing dust extraction
- Proprietary multi-hole Clean Sanding pattern helps capture and remove more dust than 5- or 6-hole systems and prolongs disc life



Product ID	Product Name	MOQ	OU
7100006170	3M™ Clean Sanding Soft Interface Disc Pad, 127 mm x 12.7 mm x 19 mm MultiHole,	10	Each
7100009658	3M™ Soft Interface Disc Pad, 127 mm x 12.5 mm	10	Each



#### 3M™ Hookit™ Disc Pad

3M™ Hookit™ Disc Pad securely holds a 3M™ Hookit sanding or finishing disc or 3M™ Finesse-it™ buffing pad for use with a hand-held sanding tool such as a rotary, orbital, or random orbital sander. The 45 degree tapered edge provides flexibility and allows the sanded area to be feather-edged or more easily blended.

- J hooks securely hold a 3M<sup>™</sup> Hookit<sup>™</sup> disc or 3M<sup>™</sup> Finesse-it<sup>™</sup> buffing pad
- For use with a random orbital sander, rotary sander, or right angle grinder
- 3M™ Hookit™ system provides easy removal and re-use



Product ID	Product Name	MOQ	OU
7100032853	3M Xtract <sup>™</sup> Standard Back-up Pad, 05876, 152 mm x 19 mm x 7.93 mm, External 6 Holes, 10 ea/Case	10	Each
7000028168	3M <sup>™</sup> Hookit <sup>™</sup> D/F Disc Pad, 3 in x 4 in x 1/2 in, 4 Hole	10	Each
7000028353	3M <sup>™</sup> Hookit <sup>™</sup> Disc Pad,947, 177 mm x 25.4 mm, 5/8,	1	Each
7100001985	3M <sup>™</sup> Hookit <sup>™</sup> Disc Pad, 76 mm	5	Each
7100034710	3M™ Hookit™ Disc Pad, 127 mm x 12.5 mm, 5/16 External	5	Each
7100032506	3M™ Hookit™ Disc Pad, 127 mm x 19 mm, 5/16 External, 5 Hole,	10	Each
7100027274	3M™ Hookit™ Disc Pad, 127 mm x 19 mm, 5/16 External	10	Each
7000045702	3M <sup>™</sup> Hookit <sup>™</sup> Disc Pad, 178 mm, M14	1	Each

### 3M™ Hookit™ Roloc™ Disc Pad

3M™ Hookit™ Roloc™ Disc Pad is for use if a sanding tool is preferred over hand sanding. Use with Hookit™ abrasive discs. The Roloc™ sanding pad can be used with a 1 inch Roloc™ disc pad or with tools equipped with the Roloc™ attachment system.





- Use with Hookit<sup>™</sup> abrasive discs
- Features hook material
- Can be used on disc sanders and mini random orbital sanders

Product ID	Product Name	MOQ	OU
7000045755	3M™ Hookit™ Roloc™ Disc Pad, 27 mm x 8 mm	20	Each

### 3M™ Hookit™ Disc Hand Pad

A back-up pad for use with 3M Clean Sanding abrsaive discs of all types when sanding by hand and not with a tool.





• Made with soft foam for conformability and reduces finger marks.



Product ID	Product Name	MOQ	OU
7000028331	3M™ Hookit™ Disc Hand Pad, 76 mm	10	Each

## 3M™ Clean Sanding Disc Pad Hook Saver

Protects the hooks on a new Hookit™ Disc Pad with an inexpensive attachment device to be consumed in the application in place of a more expensive disc pad.

- Use in place of an expensive disc pad during applications
- Protect hooks on a new Hookit<sup>™</sup> Disc Pad
- Get an inexpensive attachment device



Product ID	Product Name	MOQ	OU
7000045011	3M Xtract <sup>™</sup> Disc Pad Hook Saver 20443, 127 × 19,1 mm, 31 Holes, 20 ea/Case	20	Each
7000045251	3M™ Clean Sanding Disc Pad Hook Saver, 76 mm	20	Each
7000042703	3M™ Clean Sanding Disc Pad Hook Saver, 150 mm, 52 Holes, 20446	20	Each

# 3M™ Hookit™ Clean Sanding Disc Pad

Designed for use with Clean Sanding Hookit™ Discs. Pad is made with soft density foam for better conformability and allows the disc to flex which gives longer abrasive life in loading applications.

- Multi hole design pattern helps to keep work environments cleaner
- Clean Sanding Solution promotes greater operator and task efficiency
- Hookit<sup>™</sup> system for easy attachment and removal



Product ID	Product Name	MOQ	OU
7000028151	3M™ Hookit™ Clean Sanding Disc Pad, 75 mm x 100 mm x 12 mm, Red Foam, 33 Hole, PN20435	10	Each
7000119342	3M™ Hookit™ Clean Sanding Pad 28531, 70 mm x 198 mm x 12.7 mm 33 Holes Red Foam, 5 per case	5	Each
7100025357	3M™ Hookit™ Clean Sanding Pad, 70 mm x 198 mm x 12.7 mm, Herringbone, PN28784	5	Each
7010360095	3M™ Hookit™ Clean Sanding Soft Disc Pad, 20428, 76 mm x 19 mm x 6.35 mm, External 6 Holes, 10 ea/Case	10	Each

### 3M™ Hookit™ Center Water Feed Disc Hand Pad

Our 3M™ Hookit™ Center Water Feed Disc Hand Pads have a proprietary feed system that dispenses water for wet sanding of plastics, primer surface, paint, fiberglass and other materials. The water flushes residue off of the sanding disc which keeps it from loading. These firm, yellow disks feature 3M™ Hookit™ hook-and-loop attachment surfaces, and are available in both contoured and bullet shapes.



- Proprietary center water feed system allows water to flush sanding residue
- Designed for use with 3-inches x 7/8-inches Hookit™ microfinishing film discs or Hookit™ Wetordry™ discs
- Water flushes the sanding residue and provides longer abrasive life

Product ID	Product Name	MOQ	OU
7000000601	3M <sup>™</sup> Hookit <sup>™</sup> Back-Up Pad, Yellow, 76 mm x 22 mm, Centre Hole	10	Each

#### 3M™ Hookit™ Low Profile Disc Pad

For use with Hookit™ abrasive discs. Use with random orbital sanders with 5/16-24 INT threads. Made with a low profile shape where surface leveling and high stock removal is desired.

- Holder enables use of 3M<sup>™</sup> Hookit<sup>™</sup> discs (sold separately) on a disc sander, rotary sander, or random orbital sander
- New one piece threaded shank reduces vibration and improves balance
- Low profile firm density foam is well-suited for flat sanding applications



Product ID	Product Name	MOQ	OU
7100026249	3M™ Hookit™ Low Profile Disc Pad, 127 mm x 9.5 mm, 5/16-24 External	10	Each

# 3M™ Hookit™ Low Profile Finishing Disc Pad

3M™ Hookit™ Low Profile Finishing Disc Pad is 5" in diameter and constructed of 11/16" soft density foam with a 15 degree blunt tapered edge and is recommended for finishing applications on flat or contoured surfaces where dust evacuation is not required. Use this disc pad with a 5° 3M™ Hookit™ disc (sold separately).



- Low profile 11/16" soft density yellow pad provides flexibility to reduce loading
- 15 degree tapered edge is ideal for final finishing on flat or contoured surfaces
- Use with 5" 3M™ Hookit™ disc (sold separately)

Product ID	Product Name	MOQ	OU
7100028484	3M <sup>™</sup> Hookit <sup>™</sup> D/F Low Profile Finishing Disc Pad, 125 mm x 17 mm, 6/16-24 External	1	Each
7100035324	3M™ Hookit™ Low Profile Finishing Disc Pad, 5 in x 11/16 in 5/16-24 External	1	Each

# 3M™ Roloc™+ Holder

3M™ Roloc™+ Holder is a rugged, plastic holder, designed to support all Roloc products, including discs and combo wheels. Our holder features a deeper internal thread to accept products with Roloc buttons.

- Supports all Roloc™ products
- A deeper internal thread accepts products with Roloc™ buttons
- Rugged and hardwearing design



Product ID	Product Name	MOQ	OU
7000033538	3M™ Roloc™+ Holder, No 4, 75 mm	5	Each

#### 3M™ Interface Pad

The 3M™ Interface Pad is our 1/2-inch thick, medium density foam pad that provides additional surface conformability when used with a 3M™ Hookit™ backup pad on a 3M™ Random Orbital Sander. The additional conformability helps when sanding critical surfaces with fine grade abrasives, after leveling and refining sanding steps are complete, but before final surface finishing steps.



- Medium density foam provides additional flexibility on contours
- Ideal for sanding curves, angles and contours
- Applies effortlessly between Hookit<sup>™</sup> discs and Hookit<sup>™</sup> back-up pads for quick changeouts

Product ID	Product Name	MOQ	OU
7100009701	3M™ Clean Sanding Interface Disc Pad, 5 in x 1/2 in x 3/4 in 31 Holes	10	Each

# **Power Sanders**

#### 3M™ Disc Sander

3M™ Disc Sanders are packed with ergonomic comfort features and ideal for small-scale grinding and deburring applications as well as paint prep and weld burn clean-up.



- Precision-balanced motor supports light grinding and deburring
- Lightweight, compact design and comfortable grip with 3M™ Gripping Material generate less vibration and noise, and allow for greater operator control
- Ergonomic 97-degree head helps reduce wrist strain over 90-degree models

Product ID	Product Name	MOQ	OU
7100083511	3M™ Disc Sander, 2 in, 0.5 hp, 6mm Collet	1	Each
7100083997	3M <sup>™</sup> Disc Sander, 50 mm, 0.3HP,20.000 RPM, 6 mm Collet	1	Each
7100083278	3M <sup>™</sup> Disc Sander, 50 mm, 0.5HP,20.000 RPM, 6 mm Collet	1	Each
7000060285	3M™ Disc Sander, 50 mm, Pistol grip	1	Each
7100142459	3M <sup>™</sup> Disc Sander, 75 mm, 1 HP,15.000 RPM, 6 mm Collet	1	Each

#### 3M™ Elite Self-Generated Vacuum Random Orbital Sander

Our line of 3M™ Elite Self-Generated Vacuum Random Orbital Sanders feature a self-generated vacuum (SGV) and deliver professional, dust-free performance and a swirl-free finish, hour after hour in high-production industrial environments where dust extraction is required.



- Precision-balanced steel workings and powerful air driven motors run smoothly with less vibration, ideal for high production industrial environments
- Improved durability, ergonomics and noise level maximize comfort and control for prolonged use
- Pneumatic power exceeds the capability of standard electric sanders, supplying hours of continual use

Product ID	Product Name	MOQ	OU
7100010670	3M™ Self-Generated Vacuum Random Elite Orbital Sander, 76 mm, 2.5 mm orbit	1	Each
7000060298	3M <sup>™</sup> Self-Generated Vacuum Random Elite Orbital Sander, 76 mm, 5 mm orbit	1	Each

### 3M™ Self-Generated Vacuum Random Orbital Sander

3M™ Elite Self-Generated Vacuum Random Orbital Sander (SGV) is designed to deliver a swirl-free finish in high production industrial environments requiring dust extraction. Our sanders enhance 3M abrasive performance and incorporate 3M™ Clean Sanding Filter Bags – for effective dust removal.

- Precision-balanced steel workings run smoothly with less vibration, ideal for high production industrial environments
- Improved durability, ergonomics and noise level maximize comfort and control for prolonged use
- Pneumatic power exceeds the capability of standard electric sanders, supplying hours of continual use





### 3M™ Non-Vacuum Random Orbital Sander Elite Series

3M™ Elite Non-Vacuum Random Orbital Sander combines durable, grip featuring 3M™ Gripping Material lightweight construction with a powerful precision balanced motor for professional performance and a swirl free finish. Our sander is great for high production industrial environments where dust extraction is not requi-



- Precision-balanced steel workings and a powerful motor offer optimal performance with less vibration in high production industrial environments
- Ergonomically engineered with features such as extended curved wrist support and 3M™ Gripping Material to maximize operator comfort during prolonged use
- Pneumatic power provides many hours of continuous use, far exceeding standard electric sanders (power hose and air compressor sold separately)

Product ID	Product Name	MOQ	OU
7000060286	3M <sup>™</sup> Non-Vacuum Random Orbital Sander Elite Series, 75 mm, 4.76 mm Orbit	1	Each
7000060288	3M™ Non-Vacuum Random Orbital Sander Elite Series, 76 mm, 2.5 mm orbit	1	Each

### 3M™ Random Orbital Sander Elite Series

Our line of 3M™ Elite Central-Vacuum-Ready Random Orbital Sanders deliver professional, dust-free performance along with a swirl-free finish, hour after hour in high-production industrial environments where dust extraction is required.



- Precision-balanced steel workings and powerful air driven motors run smoothly with less vibration, ideal for high production industrial environments
- Improved durability, ergonomics and noise level maximize comfort and control for prolonged use
- Pneumatic power exceeds the capability of standard electric sanders, supplying hours of continual use

Product ID	Product Name	MOQ	OU
7000060297	3M™ Central Vacuum Random Orbital Sander Elite Series, 70 mm x 198 mm, 3.2 mm orbit	1	Each
7000032227	3M™ Central Vacuum Random Orbital Sander Elite Series, 76 mm, 2.5 mm orbit	1	Each
7000060295	3M <sup>™</sup> Central Vacuum Random Orbital Sander Elite Series, 76 mm, 5 mm orbit	1	Each

# 3M Xtract™ Pneumatic Random Orbital Sander

The 3M Xtract™ Pneumatic Random Orbital Sander is a key component of the 3M Xtract™ sanding system. Along with 3M Xtract™ Net Discs and the 3M Xtract™ Portable Dust Extractor, this powerful 0.28 HP (209W) sander helps enable virtually dust-free sanding.



- Vacuum-ready for use with 3M Xtract™ Portable Dust Extractor or central vacuum system
- Self-Generated Vacuum provides a compact vacuum solution
- Non-vacuum options available

7100258884 3M Xtract <sup>™</sup> Pneumatic Random Orbital Sander, 88941, 125 mm, Central Vacuum, 2.5 mm Orbit, 1 per case 1 7100258886 3M Xtract <sup>™</sup> Pneumatic Random Orbital Sander, 88942, 125 mm, Central Vacuum, 5 mm Orbit, 1 per case 1 7100258885 3M Xtract <sup>™</sup> Pneumatic Random Orbital Sander, 88943, 125 mm, Central Vacuum, 8 mm Orbit, 1 per case 1	Each Each Each Each
, , , , , , , , , , , , , , , , , , , ,	Each
7100258885 3M Xtract <sup>™</sup> Pneumatic Random Orbital Sander, 88943, 125 mm, Central Vacuum, 8 mm Orbit, 1 per case 1	
• •	Each
7100258887 3M Xtract™ Pneumatic Random Orbital Sander, 88944, 125 mm, Central Vacuum, 9.5 mm Orbit, 1 per case 1	
7100264073 3M Xtract™ Pneumatic Random Orbital Sander, 88945, 125 mm, Self-Generated Vacuum, 2.5 mm Orbit, 1 per case	Each
7100264068 3M Xtract™ Pneumatic Random Orbital Sander, 88946, 125 mm, Self-Generated Vacuum, 5 mm Orbit, 1 per case 1	Each
7100264239 3M Xtract™ Pneumatic Random Orbital Sander, 88947, 125 mm, Self-Generated Vacuum, 8 mm Orbit, 1 per case 1	Each
7100264069 3M Xtract™ Pneumatic Random Orbital Sander, 88948, 125 mm, Self-Generated Vacuum, 9.5 mm Orbit, 1 per case	Each
7100259232 3M Xtract <sup>™</sup> Pneumatic Random Orbital Sander, 88953,150 mm, Central Vacuum, 2.5 mm Orbit, 1 per case 1	Each
7100258801 3M Xtract™ Pneumatic Random Orbital Sander, 88954, 150 mm, Central Vacuum, 5 mm Orbit, 1 per case 1	Each
7100258707 3M Xtract <sup>™</sup> Pneumatic Random Orbital Sander, 88955, 150 mm, Central Vacuum, 8 mm Orbit, 1 per case 1	Each
7100258799 3M Xtract™ Pneumatic Random Orbital Sander, 88956, 150 mm, Central Vacuum, 9.5 mm Orbit, 1 per case 1	Each
7100264077 3M Xtract™ Pneumatic Random Orbital Sander, 88957, 150 mm, Self-Generated Vacuum, 2.5 mm Orbit, 1 per case	Each
7100264079 3M Xtract™ Pneumatic Random Orbital Sander, 88958, 150 mm, Self-Generated Vacuum, 5 mm Orbit, 1 per case	Each
7100264078 3M Xtract™ Pneumatic Random Orbital Sander, 88959, 150 mm, Self-Generated Vacuum, 8 mm Orbit, 1 per case 1	Each
7100264070 3M Xtract™ Pneumatic Random Orbital Sander, 88960, 150 mm, Self-Generated Vacuum, 9.5 mm Orbit, 1 per case	Each

## Abrasive Tools & Accessories

### 3M Xtract™ Electric Random Orbital Sander

New to the 3M line up, ergonomic design combined with a powerful motor.

- Ergonomic, lightweight design
- Soft touch grip with molded-in grip features
- Powerful 350W motor



Product ID	Product Name	MOQ	OU
7100263555	3M Xtract <sup>™</sup> Electric Random Orbital Sander, 88835, 125 mm, Central Vacuum, 5 mm Orbit, 240V, Plug Type E	1	Each
7100263558	3M Xtract <sup>™</sup> Electric Random Orbital Sander, 88837, 150 mm, Central Vacuum, 5 mm Orbit, 240V, Plug Type E	1	Each
7100263559	3M Xtract <sup>™</sup> Electric Random Orbital Sander, 88839, 125 mm, Central Vacuum, 2.5 mm Orbit, 240V, Plug Type E	1	Each
7100263549	3M Xtract <sup>™</sup> Electric Random Orbital Sander, 88841, 150 mm, Central Vacuum, 2.5 mm Orbit, 240V, Plug Type E	1	Each
7100263554	3M Xtract <sup>™</sup> Electric Random Orbital Sander, 88845, 150 mm, Central Vacuum, 5 mm Orbit, 240V, Plug Type G	1	Each
7100263533	3M Xtract <sup>™</sup> Electric Random Orbital Sander, 88851, 125 mm, Central Vacuum, 5 mm Orbit, 110V, Plug Type EN60309	1	Each
7100263534	3M Xtract <sup>™</sup> Electric Random Orbital Sander, 88853, 150 mm, Central Vacuum, 5 mm Orbit, 110V, Plug Type EN60309	1	Each
7100263546	3M Xtract <sup>™</sup> Electric Random Orbital Sander, 88855, 125 mm, Central Vacuum, 2.5 mm Orbit, 110V, Plug Type EN60309	1	Each
7100263547	3M Xtract <sup>™</sup> Electric Random Orbital Sander, 88857, 150 mm, Central Vacuum, 2.5 mm Orbit, 110V, Plug Type EN60309	1	Each

### 3M™ Palm-Style Mini Random Orbital Sander

A compact, palm-style, mini random orbital sander that is light weight for easier control and reduced operator fatigue. It has a Roloc™ fixing to accept the full range of Finesse-it™ Roloc™ sanding backup pads. Includes 3M™ Roloc™ 02345 with Stikit™ face.

- Compact, palm-style
- Light weight for easier control and reduced operator fatigue





## Abrasive Tools & Accessories

### 3M™ Pneumatic Random Orbital Sander

Lightweight and rugged, the 3M™ Pneumatic Random Orbital Sander is designed with a high power-to-weight ratio to help you get more work done in less time and with less strain.



- Power tool is lighter and more comfortable to use
- Guard-free design for better visibility and ease-of-use
- Lighter weight, smaller size and vibration-reducing side handle for improved operator comfort

Product ID	Product Name	MOQ	OU
7100258879	3M <sup>™</sup> Pneumatic Random Orbital Sander, 88936, 125 mm, Non-Vacuum, 2.5 mm Orbit, 1 per case	1	Each
7100258878	3M <sup>™</sup> Pneumatic Random Orbital Sander, 88937, 125 mm, Non-Vacuum, 5 mm Orbit, 1 per case	1	Each
7100258882	3M <sup>™</sup> Pneumatic Random Orbital Sander, 88939, 125 mm, Non-Vacuum, 8 mm Orbit, 1 per case	1	Each
7100258883	3M <sup>™</sup> Pneumatic Random Orbital Sander, 88940, 125 mm, Non-Vacuum, 9.5 mm Orbit, 1 per case	1	Each
7100258787	3M <sup>™</sup> Pneumatic Random Orbital Sander, 88949, 152 mm, Non-Vacuum, 3/32 in Orbit	1	Each
7100258652	3M <sup>™</sup> Pneumatic Random Orbital Sander, 88950, 150 mm, Non-Vacuum, 5 mm Orbit, 1 per case	1	Each
7100258651	3M <sup>™</sup> Pneumatic Random Orbital Sander, 88951, 150 mm, Non-Vacuum, 8 mm Orbit, 1 per case	1	Each
7100258800	3M <sup>™</sup> Pneumatic Random Orbital Sander, 88952, 150 mm, Non-Vacuum, 9.5 mm Orbit, 1 per case	1	Each

## **Power Grinders**

### 3M™ Electric Angle Grinder

3M™ Electric Angle Grinder is designed for use with 3M abrasives and accessories to create a comprehensive system to achieve a more professional finish in less processing time. Our electric angle grinder has a powerful 1900 watt motor and an ergonomic handle to reduce vibration and enhance operator comfort.



- HIGH-POWERED GRINDING: High torque and high rotational speed in a lightweight, powerful and versatile tool
- DESIGNED FOR OPERATOR COMFORT: Ergonomic design features a low-vibration handle and speed control for different jobs
- MAXIMISE PRODUCTIVITY TO MINIMISE PROCESSING TIME: Designed for use with 3M abrasives and accessories

Product ID	Product Name	MOQ	OU
7100281321	3M <sup>™</sup> Electric Angle Grinder 14144, 115 mm, Plug Type G, 1 ea/case	1	Each
7100249666	3M <sup>™</sup> Electric Angle Grinder, 1900W, 115 mm, Plug Type E, 14253	1	Each
7100249665	3M <sup>™</sup> Electric Angle Grinder, 1900W, 125 mm, Plug Type E, 14273	1	Each
7100289510	3M <sup>™</sup> Electric Angle Grinder, Kit, 73846, 115 mm, 1900W, w/982CX Slotted Disc (25) & Ribbed BUP, 1 Kit/Case	1	Kit
7100289436	3M <sup>™</sup> Electric Angle Grinder, Kit, 73981, 125 mm, 1900W, w/982CX Slotted Disc (25) & Ribbed BUP, 1 Kit/Case	1	Kit
7100249667	3M <sup>™</sup> Electric Angle Grinder, Variable Speed, 1900W, 115 mm, Plug Type E, 14281	1	Each
7100249668	3M™ Electric Angle Grinder, Variable Speed, 1900W, 125 mm, Plug Type E, 14291	1	Each

## Abrasive Tools & Accessories

## **Dust Extraction Systems**

### 3M Xtract™ Portable Dust Extractor

The innovative 3M Xtract™ Portable Dust Extractor allows for maximum dust extraction, right at your side. Easily connect compatible electric or pneumatic 3M Xtract™ Random Orbital sanders for on-demand vacuum dust extraction. Includes high-collection HEPA filters to help keep your work environment virtually dust-free.

- Powerful industrial vacuum unit connects to 3M Xtract™ Random Orbital Sanders to remove dust from the work surface
- Automatic on/off compatibility with pneumatic and electric sanders
- Compact, sturdy design stands up to harsh industrial conditions



### 3M Xtract™ Filter Bag

Using our 3M Xtract™ Filter Bag helps achieve maximum utility from your 3M Xtract Clean Sanding Discs because we designed 3M Xtract Clean Sanding products work together as a system to deliver superior results. Take portable, lightweight dust management to the next level by using a Filter Bag together with a powerful 3M Xtract Self-Generated Vacuum Random Orbital Sander (disc and tools sold separately).



- Part of the 3M Xtract™ Series, designed for optimal dust removal. Thorough dust collection enhances the
  performance of 3M Xtract Discs (sold separately)
- Filter is rated for optimal work environment
- Large and Extra Large sizes save time because operators can change bags less frequently

Product ID	Product Name	MOQ	OU
7100296134	3M Xtract™ Filter Bag, 65968, Extra Large, 5/inner, 20 ea/Case	20	Each
7100296135	3M Xtract™ Filter Bag, Large, 10/inner, 50 ea/Case	50	Each



Product ID	Page
7000000393	20
7000000402	20
7000000403	20
7000000404	20
7000000405	21
7000000406	21
7000000407	21
7000000601	104
7000000690	61
7000000704	47
7000000728	78
7000000730	63
7000000740	69
7000000740	69
7000000741	68
7000000749	47
	47
7000000751	47
7000000752	
7000000753	47
7000000754	47
7000000755	47
7000000756	47
7000000757	68
7000000758	68
7000000759	68
7000000760	68
7000000761	68
7000000762	68
7000000763	68
7000000764	68
7000000765	68
7000000766	68
7000000771	68
7000000775	70
7000008959	100
7000021279	47
7000021280	47
7000021284	67
7000021285	69
7000027560	78
7000028142	30
7000028143	30
7000028147	101
7000028151	104
7000028168	103
7000028191	20
7000028192	20
7000028193	21
7000028194	20
7000028195	20
7000028196	20
7000028197	20
7000028199	21
7000028200	21
7000028201	20
7000028203	20
7000028204	20
7000028331	103

Product ID	Page
7000028353	103
7000028469	63
7000028484	62
7000028488	62
7000028491	62
7000028493	62
7000028494	62
7000028501	47
7000028506	47
7000028507	47
7000028508	47
7000028509	47
7000028529	68
7000028532	68
7000032165	109
7000032227	107
7000032409	100
7000032410	100
7000032411	100
7000033538	105
7000034236	30
7000042703	104
7000042733	48
7000044902	43
7000045011	104
7000045159	21
7000045160	21
7000045161	21
7000045166	43
7000045167	43
7000045171	43
7000045172	43
7000045175	43
7000045176	43
7000045186	21
7000045187	21
7000045188	21
7000045180	20
7000045230	20
7000045254	104
7000045251	103
7000045755	103
7000045755	47
7000045888	
7000045976	63 49
7000046009	49
7000046010	38
7000046018	38
7000046019	39
7000046034	62
7000046088	62
7000046088	62
7000046089	39
7000046091	62
7000046098	61
7000046104	47
7000046108	47
7000046111	48

Product ID	Page
7000046112	48
7000046113	47
7000046114	47
7000046125	68
7000046127	68
7000046149	48
7000046158	68
7000046159	68
7000046161	68
7000046167	61
7000046180	67
7000046181	67
7000046214	39
7000046218	48
7000046219	48
7000046220	48
7000046221	48
7000046244	40
7000046245	40
7000046246	40
7000046247	40
7000046248	40
7000046249	40
7000046250	49
7000046251	49
7000046263	40
7000046264	40
7000059967	93
7000059968	93
7000060033	93
7000060076	93
7000060078	93
7000060285	106
7000060286	107
7000060288	107
7000060295	107
7000060297	107
7000060298	106
7000060301	107
7000060356	94
7000060741	86
7000060742	87
7000060743	86
7000060746	87
7000060748	86
7000060749	86
7000060751	87
7000060752	88
7000060753	87
7000060754	86
7000060755	87
7000060756	87
7000060757	87
7000060762	87
7000060766	87
7000060767	87
7000060768	86
7000060771	88
•	

Product ID	Page
7000060772	88
7000060773	87
7000060775	87
7000060776	87
7000060777	87
7000060778	87
7000060780	86
7000060788	88
7000060789	87
7000060790	88
7000060822	87
7000060823	86
7000060848	86
7000060849	86
7000060862	86
7000060863	86
7000060865	86
7000060866	86
7000060867	86
7000060868	86
7000060869	86
7000060870	86
7000060870	86
7000060872	86
7000060879	86
7000060880	86
7000060887	86
7000060889	86
7000060890	92
7000060897	93
7000061389	101
7000061390	101
7000061711	100
7000061712	100
7000062861	66
7000067868	97
7000067872	97
7000067873	97
7000067928	98
7000067929	98
7000067933	97
7000067935	97
7000067940	97
7000067941	97
7000067942	97
7000067943	97
7000067944	97
7000068084	98
7000068085	98
7000077904	72
7000077928	72
7000077940	37
7000077966	71
7000078175	66
7000078176	66
7000078177	66
7000078178	66
7000078179	66

Product ID	Page
7000078180	66
7000086456	101
7000086464	101
7000086468	101
7000086469	101
7000091730	71
7000104357	25
7000104359	25
7000104360	25
7000104361	25
7000104365	25
7000104366	25
7000104367	25
7000104368	25
7000104371	25
7000104372	25
7000104373	25
7000104374	25
7000104375	25
7000104376	25
7000104377	25
7000104378	25
7000104379	25
7000105439	100
7000105441	100
7000105442	100
7000118429	43
7000118613	102
7000119342	104
7000119606	35
7000119607	35
7000119608	35
7000121082	48
7000121083	48
7000144562	20
7000144604	69
7000145907	97
7010029932	35
7010029933	35
7010029934	35
7010029935	35
7010029936	29
7010029938	29
7010029939	29
7010029944	30
7010295274	50
7010300983	50
7010310028	60
7010310029	60
7010329036	41
7010329346	50
7010329496	60
7010360095	104
7010361116	44
7010365693	60
7010412238	40
7100000858	63
7100001473	43

Product ID	Page
7100001474	43
7100001475	43
7100001985	103
7100002321	68
7100005209	63
7100006170	102
7100007009	47
7100007318	49
7100007341	68
7100007877	93
7100007878	93
7100007879	93
7100007880	93
7100007881	93
7100007882	93
7100007883	93
7100007884	88
7100007990	88
7100007991	88
7100007992	49
7100009310	102
7100009658	102
7100009701	106
7100010261	29
7100010263	29
7100010670	106
7100011144	25
7100011310	25
7100011569	25
7100012444	98
7100013155	98
7100013687	98
7100016545	100
7100019197	49
7100022038	102
7100022777	98
7100022778	98
7100023178	89
7100023179	89
7100023234	89
7100025357	104
7100025847	89
7100026188	25
7100026249	105
7100026426	89
7100026427	89
7100026526	89
	89
7100026529 7100026546	89 89
7100026547	89
7100026547	89
7100026775	89
7100026791	89
7100026792	89
7100026793	89

7100027081

Product ID	Page
7100027274	103
7100027464	101
7100027618	89
7100028484	105
7100028668	29
7100028819	89
7100029968	48
7100032506	103
7100032853	103
7100034710	103
7100035324	105
7100037832	101
7100038608	69
7100038905	88
7100045070	27
7100045071	27
7100045072	27
7100045073	27
7100045155	94
7100046325	28
7100046326	28
7100046327	28
7100046328	28
7100047077	92
7100047970	89
7100048019	49
7100048818	95
7100052728	94
7100052729	94
7100052730	94
7100052731	94
7100052732	94
7100052733	94
7100052768	92
7100052769	92
7100052770	92
7100052771	92
7100052786	92
7100052787	92
7100052788	92
7100052826	95
7100052827	95
7100052828	95
7100052829	95
7100052831	95
7100052839	94
7100052840	94
7100052841	94
7100053413	60
7100053414	60
7100053418	60
7100053421	60
7100064174	28
7100064175	27
7100064176	28
7100064177 7100064178	27
	27
7100064179	28

Product ID	Page
7100064270	27
7100064271	27
7100064272	29
7100064273	29
7100064274	29
7100065918	27
7100069960	89
7100070052	94
7100070054	94
7100070629	89
7100076898	44
7100076925	44
7100076926	44
7100076933	44
7100076934	44
7100077039	44
7100077040	44
7100077047	44
7100077620	29
7100077621	29
7100077622	30
7100077623	30
7100077624	30
7100077625	30
7100077626	30
7100077975	30
7100078152	35
7100078153	35
7100078154	36
7100078155	36
7100078156	36
7100078157	35
7100078158	36
7100078159	36
7100078180	35
7100078181	35
7100080459	80
7100081365	50
7100081366	50
7100081367	50
7100081368	50
7100082475	88
7100083278	106
7100083511	106
7100083512	60
7100083997	106
7100085514	32
7100088615	60
7100091777	96
7100091779	96
7100091799	96
7100091802	96
7100091804	96
7100091806	96
7100091808	96
7100091813	96
7100091815	96
7100091817	96

Product ID	Page
7100091819	96
7100091823	91
7100091825	91
7100091827	91
7100091829	91
7100091831	91
7100091833	91
7100093971	71
7100093973	71
7100093978	49
7100097174	100
7100099091	22
7100099092	22
7100099093	22
7100099094	22
7100099095	22
7100099237	22
7100099238	23
7100099240	23
7100099241	23
7100099243	23
7100099245	23
7100099247	23
7100099249	22
7100099250	22
7100099252	23
7100099254	23
7100099256	23
7100099257	23
7100099258	23
7100099260	23
7100099264	22
7100099284	22
7100099545	22
7100099546	23
7100099576	22
7100099370	23
7100099787	23
7100099788	
7100099791	23
7100100885	45
	45
7100100961	45
7100100962	45
7100100964	45
7100100966	45
7100100974	45
7100100976	45
7100100979	45
7100100981	45
7100100982	45
7100100986	45
7100100989	45
7100100999	45
7100105326	60
7100105847	24
7100105848	24
7100105849	24
7100105850	24

Product ID         Page           7100105851         24           7100105852         24           7100105853         24           7100105854         24           7100105855         24           7100105856         24           7100105857         24           7100105858         24           7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105864         24           7100105865         24           7100105866         24           7100105867         24           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106717         27           7100106718         28           7100106764         28           7100106765         28           7100106766         28           710010910         50           710011238         27           710011238         27           7100113096         32           7100113075 <th></th> <th></th>		
7100105852         24           7100105853         24           7100105854         24           7100105855         24           7100105856         24           7100105857         24           7100105858         24           7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105864         24           7100105865         24           7100105866         24           7100105867         24           7100105867         24           7100105867         24           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106716         27           7100106764         28           710010977         61           7100110910         50           710011912         60           710011238         27           710011239         32           7100113075         32           7100113107	Product ID	Page
7100105853         24           7100105854         24           7100105855         24           7100105856         24           7100105857         24           7100105858         24           7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105864         24           7100105865         24           7100105866         24           7100105867         24           7100105867         24           7100105867         24           7100106714         28           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           710010910         50           710010910         50           710011910         50           7100119280         32           7100113075         32           7100113076         32           7100113107         32           7100113110         32           7100113110	7100105851	24
7100105854         24           7100105855         24           7100105856         24           7100105857         24           7100105858         24           7100105859         24           7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105866         24           7100105867         24           7100105867         24           7100105867         24           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106716         27           7100106742         28           7100106764         28           710010910         50           710011930         50           710011930         50           7100112315         94           7100113075         32           7100113076         32           7100113107         32           7100113109	7100105852	24
7100105855         24           7100105856         24           7100105857         24           7100105857         24           7100105858         24           7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105864         24           7100105865         24           7100105866         24           7100105867         24           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106716         27           7100106764         28           7100106768         28           710010910         50           710011930         50           7100112315         94           710011238         27           7100113075         32           7100113080         32           7100113107         32           7100113109	7100105853	24
7100105856         24           7100105857         24           7100105858         24           7100105859         24           7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105866         24           7100105867         24           7100105867         24           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100108778         61           710010910         50           710011921         60           710011930         50           710011930         30           7100112315         94           7100113075         32           7100113076         32           7100113107         32           7100113109         32           7100113110	7100105854	24
7100105857         24           7100105858         24           7100105859         24           7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105866         24           7100105866         24           7100105867         24           7100106714         28           7100106714         28           7100106717         27           7100106714         28           7100106717         27           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100108778         61           710010910         50           710011912         60           7100119238         27           7100119390         32           7100113075         32           7100113080         32           7100113107         32           7100113109         32           7100113110         32           7100113110	7100105855	24
7100105858         24           7100105869         24           7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105865         24           7100105866         24           7100105867         24           7100106714         28           7100106714         28           7100106717         27           7100106742         28           7100106764         28           7100106768         28           7100108778         61           710010910         50           710011912         60           7100112315         94           710011238         27           7100112390         32           7100113075         32           7100113080         32           7100113107         32           7100113109         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113113	7100105856	24
7100105859         24           7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105864         24           7100105865         24           7100105867         24           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100106765         28           7100106766         28           7100108778         61           7100109110         50           710011921         60           710011930         50           7100119315         94           710011238         27           7100113075         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114	7100105857	24
7100105860         24           7100105861         24           7100105862         24           7100105863         24           7100105864         24           7100105865         24           7100105867         24           7100106714         28           7100106714         28           7100106717         27           7100106742         28           7100106764         28           7100106766         28           7100106768         28           710010910         50           7100109110         50           710011930         50           710011930         50           710011238         27           7100112315         94           7100112380         32           7100113075         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114	7100105858	24
7100105861         24           7100105862         24           7100105863         24           7100105864         24           7100105865         24           7100105866         24           7100105867         24           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100106766         28           710010910         50           710010912         60           710011238         27           710011238         27           7100113075         32           7100113076         32           7100113079         32           7100113107         32           7100113109         32           7100113109         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113115         32           7100113111         32           7100113113	7100105859	24
7100105862         24           7100105863         24           7100105864         24           7100105865         24           7100105866         24           7100105867         24           7100106714         28           7100106714         28           7100106717         27           7100106742         28           7100106764         28           7100106766         28           7100109778         61           7100109110         50           710010912         60           710011238         27           7100112390         32           7100112315         94           7100112980         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113115         32           7100113110         32           7100113113	7100105860	24
7100105863         24           7100105864         24           7100105865         24           7100105866         24           7100105867         24           7100106678         28           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100106768         28           7100109778         61           7100109110         50           710011912         60           710011928         27           7100112315         94           7100112380         32           7100113076         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113115         32           7100113116         32           7100113117	7100105861	24
7100105864         24           7100105865         24           7100105866         24           7100105867         24           7100106678         28           7100106714         28           7100106717         27           7100106742         28           7100106764         28           7100106768         28           7100109778         61           710010910         50           710010912         60           710011238         27           710011238         27           7100112390         32           7100113075         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113115         32           7100113111         32           7100113113         32           7100113114	7100105862	24
7100105865         24           7100105866         24           7100105867         24           7100106678         28           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100106768         28           7100109178         61           710010919         50           710010910         50           710010912         60           710011238         27           710011239         32           7100112315         94           710011238         27           7100112390         32           7100113075         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113120         32           7100113121	7100105863	24
7100105866         24           7100105867         24           7100106678         28           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100106768         28           7100108778         61           7100109110         50           710010912         60           7100112315         94           710011238         27           7100112980         32           7100113075         32           7100113076         32           7100113080         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113115         32           7100113116         32           7100113117         32           7100113118	7100105864	24
7100105867         24           7100106678         28           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100106768         28           7100108778         61           7100109110         50           7100109130         50           710010912         60           7100112315         94           710011238         27           7100112980         32           7100113075         32           7100113076         32           7100113080         32           7100113107         32           7100113109         32           7100113109         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113119         32           7100113119         32           7100113119	7100105865	24
7100106678         28           7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100106768         28           710010910         50           7100109110         50           710010912         60           7100112315         94           7100112315         94           7100112980         32           7100113075         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113142	7100105866	24
7100106714         28           7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100106768         28           710010910         50           7100109110         50           710010912         60           7100112315         94           7100112980         32           7100113075         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113120         32           7100113121         32           7100113142         32           7100113143	7100105867	24
7100106716         27           7100106717         27           7100106742         28           7100106764         28           7100106766         28           7100108778         61           7100109110         50           710010912         60           710011238         27           7100112315         94           7100112980         32           7100113075         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113119         32           7100113119         32           7100113119         32           7100113119         32           7100113119         32           7100113119	7100106678	28
7100106717         27           7100106742         28           7100106764         28           7100106766         28           7100108778         61           7100109110         50           710010912         60           7100112315         94           7100112980         32           7100113075         32           7100113076         32           7100113079         32           7100113107         32           7100113109         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113119         32           7100113119         32           7100113119         32           7100113119         32           7100113119         32           7100113120         32           7100113142 <td>7100106714</td> <td>28</td>	7100106714	28
7100106742         28           7100106764         28           7100106766         28           7100108778         61           7100109110         50           710010912         60           7100112315         94           7100112315         94           7100112980         32           7100113075         32           7100113080         32           7100113096         32           7100113107         32           7100113108         32           7100113109         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100113143         32           7100138284 <td>7100106716</td> <td>27</td>	7100106716	27
7100106742         28           7100106764         28           7100106766         28           7100108778         61           7100109110         50           710010912         60           7100112315         94           7100112315         94           7100112980         32           7100113075         32           7100113080         32           7100113096         32           7100113107         32           7100113108         32           7100113109         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100113143         32           7100138284 <td>7100106717</td> <td>27</td>	7100106717	27
7100106766         28           7100106768         28           7100108778         61           7100109110         50           710010912         60           7100112315         94           7100112980         32           7100113075         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113108         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113115         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113120         32           7100113121         32           7100113139         32           7100113142         32           7100113143         32           7100113143         32           7100138194         69           7100138284 <td>7100106742</td> <td></td>	7100106742	
7100106768         28           7100108778         61           7100109110         50           710010912         60           7100112315         94           7100112315         94           7100112980         32           7100113075         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113115         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113116         32           7100113120         32           7100113121         32           7100113126         32           7100113139         32           7100113142         32           7100113143         32           7100138284         70           7100138284         70           7100138286 <td>7100106764</td> <td>28</td>	7100106764	28
7100108778         61           7100109110         50           710010912         60           710011238         27           7100112315         94           7100112980         32           7100113075         32           7100113076         32           7100113090         32           7100113091         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113115         32           7100113116         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113139         32           7100113142         32           7100113143         32           7100138284         70           7100138284         70           7100138286         69           7100138286         69	7100106766	28
7100109110         50           7100109130         50           7100110912         60           7100112315         94           7100112980         32           7100113075         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113110         32           7100113111         32           7100113112         32           7100113113         32           7100113114         32           7100113119         32           7100113120         32           7100113121         32           7100113126         32           7100113139         32           7100113142         32           7100113143         32           7100138284         70           7100138284         70           7100138286         69           7100138286 <td>7100106768</td> <td>28</td>	7100106768	28
7100109130         50           7100110912         60           7100112315         94           7100112980         32           7100113075         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113119         32           7100113119         32           7100113119         32           7100113119         32           7100113120         32           7100113121         32           7100113139         32           7100113142         32           7100113143         32           7100138194         69           7100138284         70           7100138286         69           7100138286         69	7100108778	61
7100110912         60           7100112315         94           7100112980         32           7100112980         32           7100113075         32           7100113076         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113119         32           7100113119         32           7100113120         32           7100113121         32           7100113126         32           7100113139         32           7100113142         32           7100113143         32           7100138194         69           7100138284         70           7100138286         69           7100138286         69	7100109110	50
7100111238         27           7100112315         94           7100112980         32           7100113075         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113119         32           7100113119         32           7100113119         32           7100113120         32           7100113121         32           7100113126         32           7100113139         32           7100113142         32           7100113143         32           7100138284         70           7100138284         70           7100138286         69           7100138286         69	7100109130	50
7100112315         94           7100112980         32           7100113075         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113119         32           7100113110         32           7100113111         32           7100113112         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           710013143         32           7100138284         70           7100138285         69           7100138286         69	7100110912	60
7100112980         32           7100113075         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113127         32           7100113129         32           7100113142         32           7100113143         32           7100113143         32           7100136838         43           7100138284         70           7100138284         70           7100138286         69           7100138286         69	7100111238	27
7100113075         32           7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113119         32           7100113120         32           7100113121         32           7100113126         32           7100113139         32           7100113142         32           7100113143         32           7100113143         32           7100138194         69           7100138284         70           7100138286         69           7100138286         69	7100112315	94
7100113076         32           7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100113143         32           7100136838         43           7100138194         69           7100138284         70           7100138286         69           7100138286         69	7100112980	32
7100113080         32           7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100113143         32           7100136838         43           7100138194         69           7100138284         70           7100138286         69           7100138286         69	7100113075	32
7100113096         32           7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100113143         32           7100136838         43           7100138194         69           7100138284         70           7100138286         69           7100138286         69	7100113076	32
7100113107         32           7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100126838         43           7100138194         69           7100138284         70           7100138285         69           7100138286         69	7100113080	32
7100113109         32           7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100126838         43           7100138194         69           7100138284         70           7100138285         69           7100138286         69	7100113096	
7100113110         32           7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100126838         43           7100138194         69           7100138284         70           7100138285         69           7100138286         69	7100113107	32
7100113111         32           7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100126838         43           7100138194         69           7100138284         70           7100138285         69           7100138286         69	7100113109	32
7100113113         32           7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113142         32           7100113143         32           7100126838         43           7100138194         69           7100138284         70           7100138285         69           7100138286         69	7100113110	32
7100113114         32           7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113139         32           7100113142         32           7100113143         32           7100126838         43           7100135643         100           7100138194         69           7100138284         70           7100138285         69           7100138286         69	7100113111	32
7100113117         32           7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113139         32           7100113142         32           7100113143         32           7100126838         43           7100135643         100           7100138284         70           7100138285         69           7100138286         69	7100113113	32
7100113118         32           7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113139         32           7100113142         32           7100113143         32           7100126838         43           7100135643         100           7100138194         69           7100138284         70           7100138285         69           7100138286         69	7100113114	32
7100113120         32           7100113121         32           7100113126         32           7100113137         32           7100113139         32           7100113142         32           7100113143         32           7100126838         43           7100135643         100           7100138194         69           7100138284         70           7100138286         69           7100138286         69	7100113117	32
7100113121         32           7100113126         32           7100113137         32           7100113139         32           7100113142         32           7100113143         32           7100126838         43           7100135643         100           7100138194         69           7100138284         70           7100138286         69	7100113118	32
7100113126         32           7100113137         32           7100113139         32           7100113142         32           7100113143         32           7100126838         43           7100135643         100           7100138194         69           7100138284         70           7100138286         69	7100113120	32
7100113137         32           7100113139         32           7100113142         32           7100113143         32           7100126838         43           7100135643         100           7100138194         69           7100138284         70           7100138286         69	7100113121	32
7100113139         32           7100113142         32           7100113143         32           7100126838         43           7100135643         100           7100138194         69           7100138284         70           7100138285         69           7100138286         69	7100113126	32
7100113142     32       7100113143     32       7100126838     43       7100135643     100       7100138194     69       7100138284     70       7100138285     69       7100138286     69	7100113137	32
7100113143         32           7100126838         43           7100135643         100           7100138194         69           7100138284         70           7100138285         69           7100138286         69		
7100126838         43           7100135643         100           7100138194         69           7100138284         70           7100138285         69           7100138286         69		
7100135643         100           7100138194         69           7100138284         70           7100138285         69           7100138286         69		
7100138194     69       7100138284     70       7100138285     69       7100138286     69		
7100138284     70       7100138285     69       7100138286     69		
7100138285 69 7100138286 69		
7100138286 69	1	
7100138287 66		
	7100138287	66

Product ID	Page
7100138288	66
7100138289	66
7100138290	67
7100138291	67
7100138292	69
7100138293	68
7100138294	68
7100138295	68
7100138296	68
7100138297	68
7100138298	67
7100138299	67
7100138300	67
7100138301	69
7100138302	69
7100138303	69
7100138304	69
7100138305	69
7100138306	69
7100138307	69
7100138319	69
7100138323	68
7100138324	68
7100138326	68
7100138327	69
7100138332	67
7100138333	67
7100138334	67
7100138335	67
7100138336	67
7100138337	67
7100138338	67
7100138339	69
7100138340	69
7100138341	69
7100138342	68
7100138347	67
7100139207	57
7100139209	57
7100139211	57
7100139213	57
7100139216	57
7100139217	57
7100139218	57
7100139219	57
7100139223	57
7100139227	57
7100139229	57
7100139232	57
7100139234	57
7100139235	57
7100139238	57
7100139240	57
7100140055	59
7100140056	59
7100140057	59
7100140058	59
7100140059	59

Product ID	Page
7100140060	59
7100141045	57
7100141056	57
7100141067	57
7100141069	57
7100141070	57
7100141075	57
7100141083	58
7100141086	58
7100141089	58
7100141096	58
7100141099	58
7100141123	58
7100141692	27
7100142081	90
7100142459	106
7100143972	97
7100144158	88
7100144567	91
7100145316	27
7100145362	27
7100145363	27
7100145403	28
7100145404	27
7100145405	28
7100145407	29
7100145430	28
7100145431	28
7100145433	27
7100145436	28
7100145452	27
7100145455	27
7100145460	27
7100145462	29
7100145469	29
7100145477	28
7100146031	97
7100146406	91
7100150191	70
7100151522	69
7100166994	94
7100168938	94
7100169949	32
7100169950	32
7100169959	32
7100169962	32
7100171627	89
7100171629	91
7100173790	46
7100173795	46
7100175138	37
7100175139	37
7100175140	37
7100175521	46
7100176347	36
7100176348	36
7100176374	36
7100176940	89
7 10017 0040	09

Product ID	Page
7100179815	46
7100181358	91
7100181788	90
7100182225	80
7100182231	75
7100182456	76
7100182457	75
7100182483	74
7100182484	74
7100182487	78
7100182488	78
7100182496	75
7100182499	75
7100182515	76
7100182517	76
7100182533	75
7100182554	78
7100182555	79
7100182579	40
7100182579	78
7100182588	76
7100182594	75
7100182601	75
7100182637	40 75
7100182820	34
7100187013	34
7100187014	34
7100187015 7100187016	34
7100187017	34
7100197017	35
7100190717	35
7100190719	35
7100190720	35
7100190721	35
7100190722	34
7100190723	34
7100190724	34
7100190725	34
7100190726	34
7100191877	37
7100192330	36
7100192331	36
7100192332	36
7100192333	36
7100192334	36
7100192335	36
7100192336	37
7100192337	37
7100192338	37
7100192339	37
7100192340	37
7100192341	37
7100192704	46
7100192705	46
7100192706	46
7100192707	36
7100192708	36
_	

Product ID	Page
7100192709	36
7100192710	36
7100192711	36
7100192712	46
7100192733	46
7100192734	46
7100192735	37
7100192736	37
7100192737	37
7100192738	37
7100192739	37
7100193601	80
7100196538	26
7100196539	26
7100196540	26
7100196789	26
7100196790	26
7100196791	26
7100196792	26
7100196793	26
7100196794	26
7100196797	26
7100196798	26
7100196799	26
7100196800	26
7100196812	26
7100196813	26
7100196815	26
7100196816	26
7100196817	26 26
7100196818 7100196819	26
7100196819	26
7100196821	26
7100190021	26
7100197431	26
7100200101	38
7100200101	38
7100200772	39
7100201780	97
7100209414	78
7100209618	78
7100211074	31
7100214038	58
7100214085	58
7100214087	58
7100214088	58
7100214089	58
7100218922	94
7100218932	91
7100218933	91
7100218934	90
7100218935	90
7100218936	91
7100218937	90
7100218938	90
7100218939	91
7100218940	91

Product ID	Pogo
	Page
7100218941	90
7100218942	90
7100218943	86
7100218945	88
7100218946	97
7100218947	97
7100218948	86
7100218950	89
7100218951	93
7100218952	93
7100218953	89
7100218954	89
7100218955	89
7100218956	94
7100218957	94
7100218959	90
7100218960	94
7100218961	94
7100218962	88
7100218963	97
7100218964	88
7100218965	88
7100218966	87
7100218967	87
7100218968	87
7100218969	87
7100218970	97
7100218971	90
7100218972	87
7100218973	86
7100218974	94
7100218975	88
7100218976	88
7100218977	87
7100218978	86
7100218979	97
7100218980	88
7100218981	87
7100218982	86
7100218983	94
7100218984	89
7100218985	88
7100218986	97
7100218988	86
7100218990	86
7100218991	87
7100218992	95
7100218993	89
7100218994	97
7100218996	86
7100218999	87
7100219000	87
7100219001	89
7100219002	93
7100219003	97
7100219004	91
7100219005	87
7100219006	97

Product ID	Page
7100219007	89
7100219008	86
7100219009	93
7100219010	97
7100219011	87
7100219013	91
7100219014	86
7100219015	97
7100219016	86
7100219017	87
7100219018	97
7100219010	94
7100219021	87
7100219022	87
7100219023	91
7100219024	87
7100219025	87
7100219026	97
7100219027	97
7100219028	91
7100219029	93
7100219030	90
7100219033	91
7100219034	97
7100219035	93
7100219036	91
7100219037	91
7100219038	90
7100219040	89
7100219041	89
7100219042	97
7100219043	91
7100219044	97
7100219045	91
7100219046	91
7100219047	97
7100219048	97
7100219049	90
7100219050	90
7100219051	91
7100219052	91
7100219052	90
7100219053	90
7100219054	91
7100219056	91
7100219057	91
7100219058	89
7100219059	87
7100219060	93
7100219061	93
7100219062	94
7100219064	95
7100219066	93
7100219067	93
7100219068	89
7100219071	91
7100219073	93
7100219074	95
-	

Product ID	Page
7100219145	93
7100219146	89
7100222628	31
7100222630	31
7100222757	31
7100226878	34
7100226879	34
7100226884	35
7100226885	35
7100226886	35
7100226887	35
7100226888	35
7100226890	34
7100226891	34
7100226892	34
7100233439	38
7100233440	38
7100233440	38
	38
7100233606	
7100233607	39
7100233608	38
7100233609	38
7100233614	39
7100233623	38
7100233774	38
7100233775	38
7100233776	38
7100233777	38
7100233779	39
7100233780	38
7100233781	38
7100233783	39
7100233794	38
7100233795	38
7100233797	39
7100233801	39
7100233803	38
7100233804	38
7100233805	38
7100233806	38
7100233809	38
7100233811	39
7100233812	38
7100233813	38
7100233816	39
7100233819	39
7100234045	38
7100234046	39
7100239219	26
7100239223	26
7100239224	26
7100240279	26
7100242134	100
7100242873	98
7100246422	27
7100246524	27
7100246525	28
7100246533	27

Product ID	Page
7100246534	27
7100246535	27
7100248337	27
7100248339	27
7100249319	29
7100249320	29
7100249321	29
7100249322	29
7100249427	29
7100249431	29
7100249443	29
7100249473	29
7100249665	110
7100249666	110
7100249667	110
7100249668	110
7100255864	97
7100256317	61
7100256328	61
7100256410	60
7100256411	60
7100256412	61
7100256507	60
7100256508	60
7100256509	60
7100256513	60
7100256514	60
7100256515	
7100256517	60
7100256517	
7100256520	60
	60
7100256521	60
	60
7100258651	110
7100258652	110
7100258707	108
7100258787	110
7100258799	108
7100258800	110
7100258801	108
7100258878	110
7100258879	110
7100258882	110
7100258883	110
7100258884	108
7100258885	108
7100258886	108
7100258887	108
7100259232	108
7100259732	111
7100260424	111
7100263533	109
7100263534	109
7100263546	109
7100263547	109
7100263549	109
7100263554	109
7100263555	109

Product ID	Page
7100263558	109
7100263559	109
7100264068	108
7100264069	108
7100264070	108
7100264073	108
7100264077	108
7100264078	108
7100264079	108
7100264089	52
7100264090	51
7100264091	51
7100264092	51
7100264138	52
7100264139	51
7100264141	52
7100264142	52
7100264150	51
	52
7100264151	
7100264156	52
7100264159	51
7100264161	52
7100264164	51
7100264165	51
7100264166	52
7100264167	51
7100264168	52
7100264169	51
7100264170	51
7100264171	51
7100264172	51
7100264173	52
7100264174	51
7100264193	51
7100264194	52
7100264195	52
7100264196	52
7100264197	51
7100264198	51
7100264199	52
7100264203	51
7100264204	52
7100264239	108
7100264427	51
7100264428	52
7100264429	52
7100264438	51
7100266289	95
7100266290	95
7100266291	95
7100266292	95
7100270476	102
7100270872	51
7100270072	51
7100271030	52
7100271030	52
7100272236	51
7100272237	52
, 100212201	32

Product ID	Page
7100273463	102
7100273845	102
7100273863	102
7100274222	42
7100274223	42
7100274224	42
7100274225	41
7100274226	41
7100274227	41
7100274228	42
7100274229	42
7100274270	41
7100274271	42
7100274272	41
7100274273	41
7100274274	42
7100274275	41
7100274277	42
7100274279	41
7100274660	41
7100274661	41
7100274662	42
7100274663	42
7100274664	41
7100274665	41
7100274666	42
7100274667	42
7100274668	42
7100274669	42
7100274670	42
7100274671	42
7100274704	42
7100274705	41
7100274706	41
7100275253	42
7100275255	42
7100275256	42
7100275258	42
7100275259	41
7100275260	41
7100275261	41
7100275836	42
7100275837	42
7100275838	42
7100275844	42
7100275845	42
7100275899	42
7100276268	42
7100278691	102
7100281321	110
7100281803	33
7100281804	33
7100281806	33
7100281810	33
7100281811	33
7100281011	33
7100282510	33
7100282510	33
. 100202010	

Product ID	Page
7100284216	33
7100284218 7100284266	33
	33
7100284267	34
7100284268	33
7100284271	34
7100284340	33
7100284341	33
7100284342	
7100284343	33
7100284344	33
7100284353	33
7100284356	33
7100284506	33
7100284508	33
7100284518	33
7100284520	33
7100284521	33
7100284530	33
7100284531	33
7100284565	33
7100284662	33
7100284769	33
7100284886	33
7100288455	74
7100288456	74
7100288457	74
7100288524	79
7100288556	74
7100288566	79
7100289436	110
7100289510	110
7100289603	90
7100289604	
7100289605	90
7100289606	90
7100289607	90
7100289608	90
7100289609	90
7100289610	90
7100290100 7100290101	61
	60
7100290244	60
7100290246 7100290248	60
	61
7100290249 7100290250	60 60
7100290251 7100290252	60
	61
7100290253 7100290254	61
7100290254	60 60
7100290255	50
7100290763 7100291543	50 50
7100296134	111
7100296135 7100303829	111 54
7 100000028	54

Product ID	Page
7100303830	54
7100303831	54
7100303832	54
7100303861	54
7100303963	55
7100303971	56
7100303972	56
7100303973	56
7100303974	56
7100303975	56
7100303979	55
7100303980	55
7100303981	55
7100303982	55
7100303983	55
7100303993	54
7100303994	54
7100303995	54
7100303996	54
7100303997	54
7100303998	54
7100303999	54
7100304000	54
7100304003	54
7100304056	54
7100304120	54
7100304121	54
7100304123	54
7100304124	54
7100304127	54
7100304127	54
7100304304	54
7100304305	54
7100304300	56
7100305148	54
7100305230	56
7100305446	56
	56
7100305447 7100305448	
	56
7100305449	56 56
7100305450	
7100305453	55
7100308530	18
7100308531	18
7100309787	19
7100309789	19
7100309790	18
7100309794	18
7100309795	19
7100309798	19
7100309904	18
7100309905	18
7100310794	19
7100312955	55
7100313150	85
7100326912	85
7100329003	85
7100329004	85

Product ID	Page
7100329005	85
7100329006	85
7100329007	85
7100329008	85
7100329009	85
7100329010	85
7100329011	85
7100329012	85
7100329013	85
7100329014	85
7100329043	85
7100329044	85
7100329045	85
7100329046	85
7100329047	85

### 3M TERMS OF SALE

### 1. Application

- 1.1 These conditions apply to all contracts between 3M and the Buyer referred to in the order and override all conditions stipulated by the Buyer (even if submitted in a later document); any other agreements between the parties relating to the subject matter of this order are terminated (except an agreement into which these conditions are incorporated).
- 1.2 No variation of these conditions is permitted unless agreed in writing by an authorised officer of 3M. Lead times for delivery shall be as set out in 3M's quotation or proposal or if none is specified 3M's standard lead times shall apply.

#### 2. Description

- 2.1 The description of the goods or services to be supplied by 3M shall be as set out in 3M's quotation, as modified by any written specification supplied by 3M, or otherwise agreed in writing by an authorised officer of 3M.
- 2.2 3M may amend any specification if required by any applicable statute or regulation, or by notification to the Buyer following which the applicable specification shall be that as so amended.
- 2.3 All samples, drawings, images, descriptive matter and advertising materials produced by 3M and any descriptions or illustrations contained in 3M's literature, digital media or emails are produced solely to describe the goods or services approximately and do not form part of the agreement into which these conditions are incorporated.

#### 3. Price

- 3.1 Save where expressly stated otherwise by 3M the price to be paid for the goods or the services will be 3M's price at the date when the goods are dispatched or the services are provided.
- 3.2 The price of goods includes the cost of 3M's standard packaging and standard delivery within the UK and Ireland by 3M's normal transportation; the price does not include VAT. Where the price is based on pallets and/or packaging being returned to 3M, then failure to do so by the Buyer will result in a surcharge at 3M's standard rate.

### 4. Payment

- 4.1 Unless otherwise specified on 3M's invoice, payment for the goods or services must be received in cleared funds no later than thirty days of the date of invoice.
- 4.2 3M reserves the right to charge interest on overdue sums at the rate of 4% per annum above the Base Rate for the time being of Lloyds Bank plc calculated on a daily basis from the due date of payment in Clause 4.1 until the date upon which payment is made.
- 4.3 3M may at any time require the Buyer to make payment in advance of delivery or require security for payment.
- 4.4 If the Buyer fails to make payment by the due date or when required, 3M may (without prejudice to any other remedy which it may have) cancel this contract and/or any other contract between the Buyer and 3M and/or suspend delivery under this or any other contract until payment is made.
- 4.5 The Buyer will have no statutory or other right of set off.

#### Delivery

- 5.1 Delivery dates are approximate only and 3M shall not be responsible for any loss or damage arising from any delay in delivering all or part of any goods ordered or delay in the provision of any services.
- 5.2 Without prejudice to Clause 5.1, 3M will not be liable for any delay in delivery or non-delivery of goods or services or any other breach of these conditions caused by any circumstances beyond 3M's reasonable control including without limitation, any Act of God, explosion, fire, flood, war, hostilities, accident, delay in delivery or non-delivery by 3M's suppliers, breakdowns or accidents to machinery, labour strike or dispute, order or decree of any court or action of any governmental authority, or any other causes or any circumstances beyond 3M's control; on the occurrence of any of the above events 3M reserves the right to cancel or suspend the whole or part of any delivery or service provision.
- 5.3 In the case of any order for goods of a type or description not normally held in stock by 3M, and therefore specially made ordered or imported by 3M to meet such order, the Buyer will accept goods 10% more or 10% less than ordered, the total price of the order being correspondingly adjusted.
- 5.4 Where 3M references the international rules for the interpretation of trade terms prepared by the International Chamber of Commerce (Incoterms) in the relevant contract or proposal, such terms shall apply to delivery save that where they conflict with these conditions, these conditions shall prevail. For deliveries outside of the UK mainland the term of sale shall be FCA 3M UK warehouse unless otherwise mutually agreed in writing by 3M and Buyer.
- 5.5 Goods supplied may be subject to export controls. The Buyer should refer to 3M's packing list accompanying the goods for any export control status.

#### Risk

Risk in all goods supplied to the Buyer will pass to the Buyer on delivery. Unloading shall be at the Buyer's risk.

### 7. Inspection

- 7.1 If the goods or any of them are damaged or lost while in the custody of a carrier, 3M will (at its option) either replace such goods or refund to the Buyer the price paid for them, but 3M's liability in connection with any such goods will not exceed the cost of replacement or the price paid by the Buyer.
- 7.2 3M will not be under any liability under 7.1 above unless the following conditions are strictly complied with:

- 7.2:1 In the event of non-delivery of a whole consignment of goods the Buyer must inform 3M in writing within ten days of the date of the invoice.
- 7.2:2 In the case of damage to goods or loss of part of a consignment, the consignment must be inspected in the presence of the carrier. If any goods are damaged or lost the consignment note must be endorsed accordingly and the Buyer must notify 3M within forty-eight hours of delivery, such notification to be confirmed in writing within the following five days. 3M shall have no further liability for such damage or loss.

#### 8. Liabilities and Warranties

- 8.1 Nothing in this clause will be deemed to exclude or restrict 3M's liability for (i) death or personal injury resulting from its negligence; (ii) fraud or fraudulent misrepresentation; (iii) breach of any obligation as to title implied by section 12 of the Sale of Goods Act 1979; and/or (iv) any act, omission or matter, liability for which may not be legally excluded or limited.
- 8.2 If any goods supplied or any services supplied or provided by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same (or the defective part) or refund to the Buyer the price of the goods or services (or a pro-rated amount of the price if not all the goods are defective).
- 8.3 The Buyer will determine the suitability of the goods for its intended use and will not rely upon any representations made by or on behalf of 3M.
- 8.4 3M's liability under these conditions shall never exceed the cost of replacement or the price paid by the Buyer for the goods or services.
- 8.5 3M will not be liable for any consequential or indirect loss or damage (whether for loss of profit, loss of business, depletion of goodwill or otherwise) costs, expenses or other claims for consequential compensation whatsoever suffered by the Buyer whether this loss or damage arises from a breach of duty, in contract or in tort or in any other way (including loss or damage arising from 3M's negligence).
- 8.6 The Buyer shall at all times comply with standards of business conduct that are consistent with 3M's Code of Conduct located at <a href="www.3m.com/businessconduct and">www.3m.com/businessconduct and</a> all applicable laws, statutes, regulations and codes relating to anti-bribery including but not limited to the US Foreign Corrupt Practices Act and the UK Bribery Act 2010 ("Bribery Laws") and shall maintain in place its own polices and adequate procedures, to ensure full compliance with the Bribery Laws. The Buyer shall promptly report to 3M any request or demand for any undue financial or other advantage of any kind received by or offered to the Buyer in connection with 3M's goods or services.
- 8.7 Except as set out in these conditions, all other warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

### 9. Assignment

- 9.1 3M may assign, or deal in any other manner with, any contract between 3M and Buyer or any part of them, including sub-contracting any of its obligations under such contracts to any third party or agent.
- 9.2 The Buyer shall not be entitled to assign, or deal in any other manner with, any contracts between 3M and Buyer or any part of them, including sub-contracting any of its obligations under such contracts, without the prior written consent of 3M.

### 10. <u>Termination</u>

If there is appointed a Receiver, Administrator or Administrative Receiver of the Buyer's property or assets or any part of them, or a court order is made or a resolution is passed for the winding-up of the Buyer (except for the purpose of amalgamation or reconstruction) or if the Buyer commits any act of bankruptcy, or any bankruptcy petition is presented against the Buyer (or any analogous proceedings under the law of any country outside the United Kingdom are commenced), 3M may by notice in writing to the Buyer cancel all orders and contracts between 3M and the Buyer or any part of them remaining unfulfilled.

### 11. General

- 11.1 If any provision, or part of a provision, of these conditions is found by any court or administrative body of competent jurisdiction to be invalid, illegal or unenforceable (a "void provision") such invalidity, illegality or unenforceability shall not affect the other provisions of the conditions, which shall remain in full force and effect. If a void provision would be valid, legal and enforceable if some part of it were deleted, that void provision shall apply with such modification as may be necessary to make it valid, legal and enforceable and if it cannot be made valid, legal and enforceable it shall be deemed to be deleted.
- 11.2 No provision of the conditions shall be enforceable under the Contracts (Rights of Third Parties) Act 1999 by any person who is not a party to the contract between 3M and Buyer.
- 11.3 A failure to exercise, or delay in exercising a right, power or remedy provided to 3M by these conditions or by law does not constitute a waiver of that, or any other, right, power or remedy and shall not (and nor shall any single or partial exercise of any such right, power or remedy) preclude the further exercise of that, or any other, right, power or remedy.

### 12. <u>Jurisdiction</u>

- 12.1 All contracts between 3M and the Buyer where the goods are shipped to or services are provided in the Republic of Ireland shall be governed by and construed in accordance with the Laws of the Republic of Ireland, and the Buyer agrees to submit to the jurisdiction of the Courts of law in the Republic of Ireland in respect of them.
- 12.2 Except as provided above, all contracts between 3M and the Buyer shall be governed by and construed in accordance with the Laws of England, and the Buyer agrees to submit to the jurisdiction of the Courts of law in England in respect of them.

Effective 1 January 2017

