

3M

Aqua-Pure
WATER FILTERS



**Cleaner, clearer,
drinking water.**

3M Aqua-Pure® Product Catalogue

Providing water filtration solutions for over 50 years.

We are taking a different approach to help you meet your water quality needs. We are helping to bring together 50 plus years history of providing water quality products with 3M's over 100 years history of technology innovation.

There is now a rising demand for cleaner, purified water on a global scale. Water is constantly exposed to many elements, pollutants, chemicals and contaminants through the water cycle, such as chlorine to counter forms of bacteria and toxins that may develop. Clean, pure and safe water is critical to healthy living.

As early as the 1920s, the company focused on liquid filtration and continually pioneered, advanced and patented finer, more sophisticated filtration solutions in the residential market under our Aqua-Pure brand.


We have the ability to apply our technologies, often in combination, to provide our customers with the best solutions. Our products are developed to provide professional quality, with long-lasting, reliable results, backed with 3M expertise, innovation and history.

Our solutions are designed for accessibility, ease of installation and replacement, and durability. This combination provides all customers the ongoing assurance that 3M Aqua-Pure is the clear choice.

We believe that everyone has the right to high-quality, cleaner, clearer water. We hope that you will join us in committing to bringing this important right to homes in your area.

Contents

Aqua-Pure Undersink Water Filter Range	4
Aqua-Pure Whole of House Water Filter Range	6
Aqua-Pure Replacement Cartridges	8
Undersink Quick Sanitary Change Filter Replacement Cartridges	8
Whole of House Quick Sanitary Change Filter Replacement Cartridges	9
Drop-in Style Filter Cartridges	10
Aqua-Pure Whole of House Housings	11



Undersink Water Filter Range

Installed under the kitchen sink, Aqua-Pure products are designed to provide you with great tasting drinking water on tap. Choose the system that best fits your needs and start enjoying bottled water quality right from your tap.



Water filter system with dedicated filter tap

- ▶ **AP9000+**
- Reduces sediment*, chlorine, taste & odour and bacteria*. Protects from protozoan cysts, cryptosporidium & giardia down to 0.2 micron at maximum flow rate up to 3.8 lpm
- Filter tap has a build-in LED cartridge life indicator that turns from blue to red when it's time to change your filter
- Easy installation and Watermark certified

Replacement cartridge: AP9350+

Capacity^: 11,356 litres

Operating pressure: 172-862 kPa

Operating temperature: 4.4-38°C

Inclusion:
Complete filter system
Interchangeable spout filter tap
Basic plumbing fittings

Approx. required space (h) x (w):
Vertical mounting: 330 x 280mm
Horizontal mounting: 280 x 330mm

Item ID: AK200125800

Water filter system for existing mixer tap

- ▶ **AP9100+**
- Reduces sediment*, chlorine, taste & odour and bacteria*. Protects from protozoan cysts, cryptosporidium & giardia down to 0.2 micron at maximum flow rate up to 5.7 lpm
- Easy installation, no drilling required and Watermark certified

Replacement cartridge: AP9950+

Capacity^: 18,927 litres

Operating pressure: 172-862 kPa

Operating temperature: 4.4-38°C

Inclusion:
Complete filter system
Basic plumbing fittings

Approx. required space (h) x (w):
Vertical mounting: 435 x 280mm
Horizontal mounting: 280 x 435 mm

Item ID: AK200125842

'Quick change conversion' water filter

- ▶ **AP9300**
- Reduces sediment*, chlorine, taste & odour and bacteria*. Protects from protozoan cysts, cryptosporidium & giardia down to 1 micron at maximum flow rate up to 3.8 lpm
- Designed to replace old style drop-in filter to the new design filter for easy installation
- Easy installation

Replacement cartridge: AP9351

Capacity^: 13,249 litres

Operating pressure: 172-862 kPa

Operating temperature: 4.4-38°C

Inclusion:
Complete filter system
Basic plumbing fittings

Approx. required space (h) x (w):
Vertical mounting: 330 x 280 mm
Horizontal mounting: 280 x 330mm

Item ID: AK200116965

Twin water filter with dedicated filter tap

- ▶ **AP2200C**
- Reduces sediment, chlorine, taste & odour. Protects from cysts, cryptosporidium & giardia down to 0.5 micron at a maximum flow rate up to 5.6 lpm
- Easy installation and Watermark certified

Replacement cartridge:
AP110, AP187, AP117

Capacity^: 7,570 litres

Operating pressure:
172-862 kPa

Operating temperature: 4.4-38°C

Inclusion:
Complete filter system
Single spout faucet
Basic plumbing fittings

Approx. required space (h) x (w):
Vertical mounting: 400 x 300mm
Horizontal mounting: 300 x 400mm

Item ID: AK200039423

* Tested in accordance to manufacturer's internal laboratory standard.

^ Stated capacity is based on Chlorine removal capacity. Life of cartridge is also dependent on sediment loading of incoming water supply.

Whole of House Water Filter Range

Whole house water filter systems are great solutions to help protect your pipes and appliances as well as offer you great tasting drinking water from anywhere in the home.



Water filter for sediment reduction

- ▶ **AP902**
- Reduces sediment* down to 5 microns at maximum flow rate up to 75 lpm
- 1" BSP male inlet/outlet connections with a 1" centre core to help provide high-flow ratings
- Easy installation and Watermark certified

Replacement cartridge: AP910R

Capacity: 378,000 litres

Operating pressure: 172-862 kPa

Operating temperature: 4.4-38°C

Inclusion:
Complete filter system
Basic plumbing fittings

Approx. required space (h) x (w):
Vertical mounting: 620 x 210 mm

Item ID: AK200124332

Water filter for sediment, chlorine, taste & odour reduction

- ▶ **AP903**
- Reduces sediment*, chlorine, taste and odour down to 5 microns at maximum flow rate up to 37.8 lpm
- 1" BSP male inlet/outlet connections with a 1" centre core to help provide high-flow ratings
- Easy installation and Watermark certified

Replacement cartridge: AP917HD

Capacity^: 378,000 litres

Operating pressure: 172-862 kPa

Operating temperature: 4.4-38°C

Inclusion:
Complete filter system
Basic plumbing fittings

Approx. required space (h) x (w):
Vertical mounting: 620 x 210 mm

Item ID: AK200124340

Water filter for sediment, scale, chlorine, taste & odour reduction

- ▶ **AP904**
- Reduces sediment*, chlorine, taste and odour down to 5 microns at maximum flow rate up to 37.8 lpm
- 1" BSP male inlet/outlet connections with a 1" centre core to help provide high-flow ratings
- Easy installation and Watermark certified

Replacement cartridge: AP917HD-S

Capacity^: 378,000 litres

Operating pressure: 172-862 kPa

Operating temperature: 4.4-38°C

Inclusion:
Complete filter system
Basic plumbing fittings

Approx. required space (h) x (w):
Vertical mounting: 620 x 210 mm

Item ID: AK200124910

Water filter for sediment, chlorine, taste & odour reduction

- ▶ **AP212**
- Reduces sediment*, chlorine, taste & odour, dirt and rust down to 5 microns at maximum flow rate up to 30 lpm
- 3/4" BSP connections
- Easy installation

Replacement cartridge:
1 x AP110 and 2 x AP117

Capacity^: 37,850 litres

Operating pressure:
172-862 kPa

Operating temperature: 4.4-38°C

Inclusion:
Complete filter system
Basic plumbing fittings

Approx. required space (h) x (w):
Vertical mounting: 620 x 210 mm

Item ID: AK200041361

Note: Filter unit must be protected from physical impact, extreme heat or cold environment & direct sunlight

* Tested in accordance to manufacturer's internal laboratory standard.

^ Stated capacity is based on Chlorine removal capacity. Life of cartridge is also dependent on sediment loading of incoming water supply.

Replacement Cartridges



Undersink Quick Sanitary Change Filter Replacement Cartridges



Advanced Filtration Media Cartridges- Undersink

Enhanced Carbon Blocks are a high performance complete solution designed to remove a wide range of contaminants

- Providing superior sediment holding capabilities
- Sanitary Quick Change (SQC) design for easy change out
- Pre-activation is not required

Item ID	Model	Micron	Max. flow rate	Capacity^	Replacement cartridge to suit system
AK200125891	AP9350	W 0.2	3.8 lpm	11,356L	AP9000+, AP9400+, AP9000, AP9300, AP9400, AP900CP
AK200125909	AP9950	W 0.2	5.7 lpm	18,927L	AP9100+, AP9100, AP9100CP
AK200125875	AP9250	W 0.2	2.8 lpm	2,839L	AP9200+
AK200116973	AP9351	1	2.8 lpm	13,249L	AP9000CP, AP9000, AP9300
AK200115686	AP9112	W 1	5.7 lpm	37,850L	AP9000, AP9100, AP9400
AK200069610	AP8112	W 1	5.7 lpm	37,850L	AP8000

^ Stated capacity is based on Chlorine removal capacity. Life of cartridge is also dependent on sediment loading of incoming water supply.

Whole of House Quick Sanitary Change Filter Replacement Cartridges



Advanced Filtration Media Cartridges - Whole of House

Enhanced Carbon Blocks are a high performance complete solution designed to remove a wide range of contaminants in one single unit

- Providing superior sediment holding capabilities
- Sanitary Quick Change (SQC) design for easy change out
- Pre-activation is not required

Item ID	Model	Micron	Max. flow rate	Capacity	Replacement cartridge to suit system
AK200126881	AP910R	W 5	75 lpm*	378,000L	AP902
AK200126899	AP917HD	W 5	37.8 lpm*	378,000L^	AP903
AK200126907	AP917HD-S	W 5	37.8 lpm*	378,000L^	AP904

* Tested in accordance to manufacturer's internal laboratory standard.

^ Stated capacity is based on Chlorine removal capacity. Life of cartridge is also dependent on sediment loading of incoming water supply.



Drop-in Style Filter Cartridges



Sediment Reduction Cartridges

The best sediment filter there is. Rigid bonded and graded density give the ability for long life and low pressure drops

Also does not flex and shed under pressure

Item ID	Model	Micron	Max. flow rate	Replacement cartridge to suit system
AK200069271	AP110R 	5	15 lpm	AP2200C, APUV-1, AP1610, AP212, AP11 S/T
AK200069438	AP124R	50	30 lpm	AP2200C, APUV-1, AP212, AP11 S/T
AK200070055	CG100	0.5	4 lpm	AP11 S/T
70020164177	AP810-1	5	≤80 lpm	AP801
70020170547	AP811-1	25	≤80 lpm	AP801
70020162437	AP810-2	5	≤160 lpm	AP802
70020176742	AP811-2	25	≤160 lpm	AP802
Twin Pack Cartridges				
AK200069255	AP110 	5	15 lpm	AP2200C, APUV-1, AP212, AP11 S/T
AK200069420	AP124	50	30 lpm	AP2200C, APUV-1, AP212, AP11 S/T



Chlorine, Taste & Odour Reduction Cartridges

Offers enhanced efficiency in the reduction of sediment, dirt, rust, offensive taste / odour, chlorine, giardia and cryptosporidium cysts and range of organic chemicals

- AP187 is a fine mesh carbon block cartridge bonded in a high density integral structure
- AP117 is made of Granulated Activated Carbon (GAC) for chlorine, taste and odour reduction

Item ID	Model	Micron	Max. flow rate	Replacement cartridge to suit system
AK200069453	AP187	0.5	6 lpm	APBT301C, AP220C
AK200069388	AP117	5	11 lpm	APBT301, AP2200C, AP1610, AP212, AP11S/T, APRO13212
AK200069628	AP815-1	5	≤19 lpm	AP801

Whole of House Housings





Whole of House Housings are ideal for treating water in homes with standard flow rates. Its rugged and robust design is suitable for point of use and point of entry applications helping extend the life of appliances, taps and fixtures by reducing abrasive dirt, grit and sand.



High Performance Housings

AP11S/T and AP12S/T treat water in homes with standard flow rates. Both are rugged and robust in design with positive seals to ensure cartridges will seal without bypass. Suitable for point of use or point of entry applications with suitable cartridges

- Suitable for point of use or point of entry applications with suitable cartridges
- 1-High height is 10" and 2-High height is 20"

Item ID	Model	Description	Max. flow rate ¹	Operating Pressure	Operating Temperature
AK200040579	AP11S 	1 high 3/4" BSPT opaque filter housing	≤15 lpm	862 kPa (125 psi)	4.4-38°C
AK200040686	AP11T 	1 high 3/4" BSPT transparent filter	≤15 lpm	862 kPa (125 psi)	4.4-38°C
AK200040678	AP12S 	2 high 3/4" BSPT opaque filter housing	≤30 lpm	862 kPa (125 psi)	4.4-38°C
AK200040660	AP12T 	2 high 3/4" BSPT transparent filter	≤30 lpm	862 kPa (125 psi)	4.4-38°C



Stainless Steel Housings

Made of 304 stainless steel for high pressure systems. Specifically for high-rise building and commercial applications cartridges

- 304 stainless steel sump and head
- 1-High height is 10"

Item ID	Model	Description	Max. flow rate ¹	Operating Pressure	Operating Temperature [#]
AK200038664	AP1610	1 high 3/4" metal filter housing	22.7 lpm	10 bar (145 psi)	4.4-38°C

¹Flow rate is dependent on choice of filter cartridge used.

[#] Temperature attainable depending on cartridge choice.

Global experience. Local support.

With more than 50 years experience in improving water quality and 3M's over 100 years history of technology innovation, we are taking a different approach to help you meet your water quality needs.

Our 3M Team is always here to help.

Call us on 1300 FILTER (345 837) or visit [AquaPure.com.au](https://www.aquapure.com.au) for more information regarding Water Filtration solutions.

Don't see your product on the shelf?

Contact your local plumbing store to special order it for you or visit [AquaPure.com.au/Wheretobuy](https://www.aquapure.com.au/Wheretobuy)



3M Australia Pty Ltd
3M Purification Division
Bldg A, 1 Rivett Road
North Ryde NSW 2113

Phone 1300 FILTER (345 837)
Web [AquaPure.com.au](https://www.aquapure.com.au)

3M and Aqua-Pure are trademarks of 3M.
© 3M 2022. All rights reserved.
AV011502489